

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332967-840

Luminaire Tested: **S124RDIP-S1020D810U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332967-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1020D810U840-4F0-1E-UDD-A  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7648.6 lumens  
Efficiency: N/A  
Efficacy: 140.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	46	42
3	84	75	67	62	78	70	63	58	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	32
5	71	59	51	45	66	56	49	43	49	43	39	43	38	35	37	33	31	28
6	65	53	45	40	61	50	43	38	44	39	34	39	34	31	33	30	27	24
7	61	48	40	35	56	46	38	33	40	35	30	35	31	27	31	27	24	22
8	56	44	36	31	52	42	35	30	37	31	27	32	28	24	28	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24	30	25	22	26	22	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13988	13988	13988	13988
5°	16226	14030	12400	14030
10°	19194	13969	11068	13969
15°	22172	13840	9510	13840
20°	24686	13662	8600	13662
25°	25483	13488	7985	13488
30°	22309	13276	7614	13276
35°	17366	12962	7389	12962
40°	13022	12603	7268	12603
45°	10282	12028	7205	12028
50°	8681	11362	6997	11362
55°	7567	10632	6622	10632
60°	6807	9875	5861	9875
65°	6002	9054	5041	9054
70°	5403	8207	4548	8207
75°	4529	7274	3877	7274
80°	3831	6197	3636	6197
85°	3233	4844	3233	4844



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.9	2.2
10°-20°	506.4	6.6
20°-30°	792.1	10.4
30°-40°	880.6	11.5
40°-50°	781.3	10.2
50°-60°	608.8	8.0
60°-70°	398.6	5.2
70°-80°	196.0	2.6
80°-90°	51.4	0.7
90°-100°	36.1	0.5
100°-110°	230.2	3.0
110°-120°	440.4	5.8
120°-130°	559.1	7.3
130°-140°	598.2	7.8
140°-150°	559.3	7.3
150°-160°	451.1	5.9
160°-170°	290.9	3.8
170°-180°	100.3	1.3
0°-30°	1466.4	19.2
0°-40°	2347.0	30.7
0°-60°	3737.0	48.9
0°-90°	4383.0	57.3
90°-120°	706.7	9.2
90°-150°	2423.3	31.7
90°-180°	3266.0	42.7
0°-180°	7648.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1733	1733	1733	1733	1733	
5°	2002	1731	1530	1731	2002	203
15°	2653	1656	1138	1656	2653	754
25°	2861	1514	896	1514	2861	1269
35°	1762	1315	750	1315	1762	1105
45°	901	1054	631	1054	901	713
55°	538	755	470	755	538	489
65°	314	474	264	474	314	316
75°	145	233	124	233	145	160
85°	35	52	35	52	35	40
90°	24	2	24	2	24	12
95°	23	43	23	43	23	18
105°	225	238	225	238	225	196
115°	447	444	447	444	447	442
125°	628	624	628	624	628	560
135°	779	774	779	774	779	600
145°	897	892	897	892	897	561
155°	978	978	978	978	978	451
165°	1027	1032	1027	1032	1027	290
175°	1049	1056	1049	1056	1049	100
180°	1056	1056	1056	1056	1056	



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1827.7	1832.7	1827.7	1827.1	1821.6	1819.9	1817.7	1810.4	1797.0	1789.2	1790.8
5°	2002.3	2019.6	2009.9	2008.5	1993.2	1977.8	1968.0	1945.7	1922.0	1905.9	1892.6
7.5°	2204.1	2214.1	2208.1	2198.3	2173.4	2159.3	2136.7	2107.2	2064.7	2032.1	2002.4
10°	2341.5	2349.9	2347.1	2329.0	2310.8	2273.8	2252.8	2211.7	2157.9	2115.4	2075.5
12.5°	2476.7	2485.6	2461.0	2461.8	2427.5	2398.3	2365.1	2313.3	2251.2	2196.3	2146.5
15°	2652.9	2641.7	2641.7	2627.8	2589.3	2548.9	2514.7	2460.2	2382.0	2316.3	2247.3
17.5°	2790.9	2794.7	2789.0	2756.0	2725.9	2684.0	2621.3	2557.8	2485.2	2397.1	2326.4
20°	2873.5	2873.5	2867.2	2844.9	2805.8	2761.1	2693.4	2624.2	2532.1	2443.5	2363.9
22.5°	2907.0	2909.2	2901.8	2883.4	2848.2	2804.6	2746.9	2676.7	2581.8	2481.9	2383.4
25°	2860.9	2874.2	2875.6	2870.6	2860.2	2833.7	2784.1	2712.2	2627.1	2518.8	2412.7
27.5°	2626.7	2643.4	2658.1	2682.2	2714.3	2731.1	2733.3	2696.7	2622.4	2518.3	2411.5
30°	2393.2	2407.1	2452.6	2511.8	2557.9	2599.8	2636.2	2645.8	2604.0	2510.4	2398.0
32.5°	2134.0	2153.0	2198.4	2262.2	2338.9	2409.9	2491.4	2533.0	2531.9	2475.8	2371.8
35°	1762.1	1776.0	1818.0	1884.9	1977.1	2082.5	2211.7	2312.2	2380.6	2375.7	2312.2
37.5°	1421.1	1436.8	1479.1	1534.8	1624.2	1754.6	1879.7	2018.1	2144.7	2215.7	2194.4
40°	1235.7	1236.4	1277.6	1334.8	1418.6	1532.4	1668.5	1822.1	1963.1	2078.3	2100.6
42.5°	1089.3	1089.4	1116.7	1178.4	1238.8	1345.8	1475.8	1628.3	1793.3	1926.4	1985.6
45°	900.6	906.9	929.2	966.2	1013.7	1104.4	1208.4	1350.2	1535.2	1692.9	1791.4
47.5°	762.7	771.8	786.1	816.3	854.0	914.5	1000.6	1127.9	1278.4	1452.0	1592.1
50°	691.2	692.6	710.6	727.4	760.2	808.4	883.8	990.0	1128.1	1295.1	1450.7
52.5°	629.8	629.4	640.4	661.6	688.2	725.8	786.7	883.2	1005.8	1155.4	1316.1
55°	537.6	541.1	549.5	566.1	586.4	613.0	661.2	733.8	830.1	957.9	1103.8
57.5°	467.5	469.3	475.8	482.9	501.5	520.8	556.9	607.3	688.6	793.2	929.2
60°	421.6	422.3	424.4	434.9	449.6	467.8	492.2	534.7	603.2	698.8	806.4
62.5°	377.0	378.2	381.4	389.1	400.4	413.0	438.6	472.8	529.5	611.2	708.0
65°	314.2	314.9	319.7	322.6	331.6	342.7	361.6	384.7	423.7	492.2	565.5
67.5°	262.5	262.5	262.8	266.5	272.9	280.2	291.5	309.9	339.4	381.4	446.1
70°	228.9	228.9	230.4	232.5	236.0	242.3	248.5	262.5	284.2	318.3	367.9
72.5°	197.7	198.2	199.7	200.1	201.9	207.0	211.7	220.7	236.7	262.5	302.6
75°	145.2	147.3	150.8	153.6	157.0	156.4	161.3	166.8	171.8	187.1	210.2
77.5°	108.1	106.9	107.3	109.8	110.2	110.9	114.3	118.7	122.3	129.6	137.8
80°	82.4	82.4	84.4	85.1	84.4	85.1	88.7	90.8	92.2	94.9	102.6
82.5°	62.3	63.4	62.7	63.4	63.8	64.5	67.5	67.9	69.3	70.4	73.6
85°	34.9	35.6	36.3	34.9	34.9	34.9	36.3	37.0	38.4	37.7	39.1
87.5°	17.1	16.4	16.9	16.8	17.3	16.6	17.0	17.9	16.6	16.9	16.6
90°	23.7	23.3	23.0	22.6	22.3	21.6	20.5	19.5	18.4	17.4	16.0
92.5°	21.8	21.7	21.6	21.6	21.5	20.9	19.9	18.9	17.8	16.8	15.3
95°	22.9	22.7	22.5	22.4	22.2	21.6	20.5	19.5	18.4	17.4	17.2
97.5°	22.1	21.9	21.7	21.6	21.4	21.3	21.2	21.1	20.9	20.8	40.4
100°	22.1	21.9	21.7	21.6	21.4	22.8	25.8	28.8	31.7	34.7	59.0
102.5°	22.7	22.7	22.6	22.6	22.6	38.7	70.9	103.0	135.2	167.4	170.6
105°	225.0	231.4	237.6	244.0	250.3	252.7	251.1	249.5	247.9	246.3	245.5
107.5°	313.7	313.0	312.3	311.6	310.9	310.2	309.4	308.7	307.9	307.2	306.0
110°	352.1	351.6	351.1	350.6	350.0	349.6	349.3	348.9	348.6	348.2	347.2



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	390.7	390.0	389.4	388.7	388.0	387.7	387.8	387.9	388.0	388.0	387.5
115°	447.0	447.0	447.0	447.0	447.0	446.8	446.4	446.1	445.7	445.4	445.6
117.5°	504.1	504.1	504.2	504.3	504.3	504.4	504.5	504.5	504.6	504.7	504.3
120°	540.1	540.5	540.8	541.2	541.5	541.5	541.2	540.8	540.5	540.1	540.3
122.5°	575.4	575.8	576.1	576.5	576.8	576.9	576.7	576.5	576.3	576.1	575.8
125°	628.5	628.3	628.1	628.0	627.8	627.4	626.9	626.4	625.9	625.4	625.7
127.5°	675.1	675.3	675.4	675.5	675.7	675.8	675.9	676.0	676.1	676.2	675.4
130°	706.7	706.7	706.7	706.7	706.7	706.6	706.4	706.3	706.1	705.9	705.4
132.5°	735.8	735.9	736.0	736.2	736.3	736.3	736.1	736.0	735.8	735.6	734.9
135°	779.3	779.0	778.6	778.3	777.9	777.6	777.2	776.9	776.5	776.2	775.5
137.5°	816.6	816.7	816.8	816.9	817.0	816.9	816.5	816.1	815.8	815.4	814.6
140°	842.5	842.3	842.1	842.0	841.8	841.4	840.9	840.4	839.9	839.3	839.0
142.5°	863.9	863.9	863.9	863.8	863.8	863.6	863.2	862.8	862.5	862.1	861.9
145°	897.0	896.7	896.3	896.0	895.5	895.3	895.1	894.9	894.8	894.6	894.6
147.5°	924.3	924.1	923.9	923.8	923.6	923.4	923.3	923.2	923.0	922.9	923.0
150°	942.0	941.8	941.6	941.5	941.3	941.2	941.2	941.2	941.2	941.2	941.4
152.5°	957.2	957.3	957.4	957.5	957.6	957.5	957.3	956.9	956.6	956.3	956.6
155°	977.5	978.1	978.6	979.1	979.7	979.6	978.9	978.2	977.4	976.7	977.2
157.5°	994.6	995.5	996.4	997.3	998.3	998.3	997.3	996.4	995.5	994.6	995.2
160°	1005.9	1007.0	1008.0	1009.2	1010.2	1010.2	1009.2	1008.0	1007.0	1005.9	1006.1
162.5°	1014.8	1016.0	1017.1	1018.3	1019.6	1019.7	1018.5	1017.5	1016.5	1015.4	1015.6
165°	1027.2	1028.9	1030.5	1032.0	1033.6	1033.7	1032.3	1030.9	1029.5	1028.0	1028.0
167.5°	1036.6	1038.3	1040.1	1041.9	1043.6	1043.7	1042.2	1040.7	1039.1	1037.5	1037.6
170°	1042.3	1044.0	1045.8	1047.5	1049.2	1049.5	1048.0	1046.6	1045.2	1043.9	1043.7
172.5°	1045.4	1047.3	1049.2	1051.2	1053.0	1053.3	1051.9	1050.5	1049.0	1047.6	1047.4
175°	1049.4	1051.5	1053.6	1055.7	1057.8	1058.0	1056.5	1054.9	1053.3	1051.8	1051.6
177.5°	1051.9	1053.6	1055.3	1056.9	1058.6	1058.9	1057.8	1056.7	1055.5	1054.4	1054.2
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1785.2	1777.5	1773.5	1764.5	1753.9	1748.4	1743.3	1736.1	1726.6	1716.6	1709.3
5°	1875.8	1859.1	1838.2	1813.0	1790.7	1769.1	1750.2	1731.3	1709.7	1687.4	1665.1
7.5°	1968.8	1935.9	1900.3	1859.1	1819.1	1782.6	1749.1	1717.0	1680.6	1648.1	1618.5
10°	2033.7	1988.9	1939.3	1887.0	1834.6	1789.3	1744.6	1704.1	1659.4	1619.6	1586.1
12.5°	2086.2	2033.7	1974.0	1908.8	1845.8	1791.0	1739.6	1686.8	1636.0	1592.9	1548.1
15°	2173.2	2101.3	2021.0	1942.9	1861.2	1786.5	1717.4	1656.0	1598.0	1537.3	1494.7
17.5°	2233.1	2147.9	2050.2	1956.3	1859.8	1771.7	1691.9	1618.8	1552.0	1490.0	1439.3
20°	2268.9	2174.6	2066.5	1959.6	1851.4	1757.2	1671.3	1590.3	1521.3	1454.2	1401.8
22.5°	2289.0	2184.7	2066.5	1954.6	1842.5	1740.4	1646.2	1561.9	1486.6	1419.6	1361.6
25°	2295.4	2183.7	2063.0	1934.5	1811.6	1703.4	1605.7	1514.2	1430.5	1363.4	1302.0
27.5°	2286.5	2155.0	2031.2	1899.5	1772.7	1658.6	1556.0	1460.0	1376.0	1304.1	1241.1
30°	2273.1	2132.0	1999.4	1862.6	1734.1	1624.6	1516.3	1424.2	1336.9	1262.2	1198.7
32.5°	2244.0	2104.2	1961.5	1821.3	1691.1	1578.2	1475.5	1382.8	1297.3	1220.9	1153.5
35°	2186.6	2044.8	1889.9	1746.1	1618.2	1501.0	1404.6	1315.2	1233.6	1152.0	1080.7
37.5°	2110.7	1965.9	1811.8	1654.3	1526.4	1415.6	1327.3	1243.3	1163.7	1089.0	1010.2
40°	2039.2	1907.2	1748.1	1591.7	1460.5	1353.6	1272.0	1195.9	1115.6	1041.6	962.7
42.5°	1952.7	1840.3	1679.4	1522.5	1392.9	1290.0	1213.9	1139.4	1066.4	994.7	912.4
45°	1808.2	1722.9	1572.2	1421.4	1290.8	1188.9	1119.1	1053.5	989.3	920.8	843.3
47.5°	1642.5	1584.9	1454.7	1300.3	1179.5	1087.8	1020.4	966.7	912.4	844.0	776.1
50°	1527.5	1490.5	1364.8	1223.9	1108.6	1024.1	955.0	904.7	859.4	793.8	733.1
52.5°	1404.6	1384.9	1278.8	1144.0	1032.7	949.9	890.8	845.6	799.6	745.2	688.3
55°	1217.5	1228.0	1137.9	1021.4	916.7	846.9	793.0	755.4	716.3	670.2	626.2
57.5°	1026.2	1064.5	1004.0	901.7	803.5	739.0	698.5	666.8	634.0	595.8	558.3
60°	911.7	943.8	909.7	819.6	733.8	673.7	636.0	611.6	578.8	543.8	515.2
62.5°	800.0	834.4	814.2	741.4	661.7	610.1	576.8	554.0	529.6	499.2	469.4
65°	659.7	682.1	672.3	622.1	565.5	521.5	490.8	474.0	451.7	429.4	402.8
67.5°	505.3	548.5	542.7	516.0	467.2	432.8	412.7	397.9	377.6	360.9	343.0
70°	415.4	455.1	454.4	432.8	406.3	374.2	360.2	347.7	329.5	313.5	298.8
72.5°	340.0	376.5	381.8	365.3	347.1	322.9	309.4	300.7	283.2	272.2	260.2
75°	238.0	264.6	271.6	271.6	263.2	250.6	238.7	233.2	220.7	210.9	203.9
77.5°	156.1	172.9	183.8	186.2	187.5	183.3	173.6	169.7	160.0	156.5	149.9
80°	110.3	121.5	134.0	138.3	141.7	140.4	136.1	133.3	124.3	120.8	118.0
82.5°	76.2	82.4	92.7	101.9	101.0	104.6	101.0	98.8	91.9	90.6	87.9
85°	39.8	40.5	41.9	48.2	51.7	53.0	53.7	52.3	50.3	50.3	45.3
87.5°	16.4	15.5	16.4	16.0	16.2	18.0	19.3	19.5	18.2	16.9	15.6
90°	14.5	13.1	11.7	10.1	8.2	6.3	4.3	2.3	4.3	6.3	8.2
92.5°	13.9	12.5	11.1	10.4	10.3	10.2	10.1	10.0	10.1	10.2	10.3
95°	17.1	16.9	16.7	19.6	25.5	31.5	37.5	43.4	37.5	31.5	25.5
97.5°	60.0	79.6	99.2	107.1	103.4	99.7	95.9	92.2	95.9	99.7	103.4
100°	83.2	107.3	131.6	142.1	139.0	135.8	132.7	129.5	132.7	135.8	139.0
102.5°	173.7	176.8	180.1	180.5	178.1	175.8	173.5	171.2	173.5	175.8	178.1
105°	244.6	243.7	242.9	241.9	240.9	239.7	238.7	237.6	238.7	239.7	240.9
107.5°	304.8	303.6	302.4	301.5	301.0	300.4	299.9	299.4	299.9	300.4	301.0
110°	346.1	345.1	344.0	343.3	342.6	342.1	341.6	341.1	341.6	342.1	342.6





TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	387.0	386.6	386.1	385.4	384.4	383.4	382.4	381.5	382.4	383.4	384.4
115°	445.7	445.9	446.1	445.9	445.4	444.8	444.2	443.7	444.2	444.8	445.4
117.5°	503.9	503.5	503.2	502.6	501.9	501.2	500.5	499.8	500.5	501.2	501.9
120°	540.5	540.6	540.8	540.5	539.9	539.2	538.5	537.8	538.5	539.2	539.9
122.5°	575.6	575.3	575.1	574.8	574.3	573.9	573.5	573.1	573.5	573.9	574.3
125°	626.1	626.4	626.7	626.6	625.9	625.2	624.5	623.8	624.5	625.2	625.9
127.5°	674.6	673.8	673.0	672.5	672.4	672.2	672.0	671.8	672.0	672.2	672.4
130°	704.9	704.3	703.8	703.5	703.3	703.1	703.0	702.8	703.0	703.1	703.3
132.5°	734.3	733.6	733.0	732.5	732.2	731.8	731.4	731.1	731.4	731.8	732.2
135°	774.8	774.1	773.4	773.2	773.3	773.5	773.7	773.9	773.7	773.5	773.3
137.5°	813.9	813.0	812.2	811.8	811.7	811.7	811.6	811.5	811.6	811.7	811.7
140°	838.7	838.3	838.0	837.6	837.3	836.9	836.6	836.2	836.6	836.9	837.3
142.5°	861.7	861.4	861.2	860.8	860.2	859.6	858.9	858.3	858.9	859.6	860.2
145°	894.6	894.6	894.6	894.3	893.8	893.3	892.8	892.2	892.8	893.3	893.8
147.5°	923.2	923.4	923.6	923.2	922.2	921.2	920.3	919.3	920.3	921.2	922.2
150°	941.6	941.7	941.9	941.6	941.0	940.3	939.6	938.9	939.6	940.3	941.0
152.5°	957.0	957.4	957.7	957.6	956.9	956.3	955.8	955.2	955.8	956.3	956.9
155°	977.8	978.4	978.9	979.1	978.9	978.7	978.5	978.4	978.5	978.7	978.9
157.5°	995.8	996.3	996.9	997.3	997.4	997.5	997.6	997.7	997.6	997.5	997.4
160°	1006.3	1006.5	1006.6	1007.0	1007.5	1008.0	1008.6	1009.2	1008.6	1008.0	1007.5
162.5°	1015.8	1015.9	1016.1	1016.5	1017.2	1017.8	1018.5	1019.3	1018.5	1017.8	1017.2
165°	1028.0	1028.0	1028.0	1028.5	1029.4	1030.3	1031.2	1032.0	1031.2	1030.3	1029.4
167.5°	1037.7	1037.8	1037.9	1038.4	1039.4	1040.3	1041.2	1042.1	1041.2	1040.3	1039.4
170°	1043.5	1043.3	1043.2	1043.6	1044.6	1045.7	1046.7	1047.8	1046.7	1045.7	1044.6
172.5°	1047.3	1047.1	1046.9	1047.4	1048.4	1049.5	1050.6	1051.6	1050.6	1049.5	1048.4
175°	1051.4	1051.3	1051.1	1051.5	1052.6	1053.6	1054.6	1055.7	1054.6	1053.6	1052.6
177.5°	1053.9	1053.6	1053.3	1053.7	1054.6	1055.6	1056.6	1057.6	1056.6	1055.6	1054.6
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1701.4	1695.9	1688.6	1680.2	1670.2	1661.2	1657.4	1660.7	1662.3	1657.9	1657.4
5°	1649.7	1632.2	1618.2	1597.3	1580.5	1566.6	1556.8	1552.7	1554.0	1542.9	1540.0
7.5°	1591.4	1570.7	1547.9	1523.0	1499.9	1479.4	1468.5	1462.7	1450.9	1445.8	1437.3
10°	1554.0	1526.1	1503.8	1474.4	1447.9	1423.5	1411.6	1401.8	1390.0	1384.4	1372.5
12.5°	1515.5	1483.1	1458.5	1428.1	1401.0	1371.5	1360.2	1342.1	1323.5	1311.8	1296.6
15°	1461.2	1422.1	1392.1	1355.7	1323.6	1290.1	1260.1	1226.6	1214.1	1187.5	1172.2
17.5°	1397.7	1358.0	1320.8	1272.1	1222.5	1180.9	1148.9	1116.8	1097.6	1080.7	1072.9
20°	1355.7	1319.5	1267.8	1211.2	1156.1	1110.0	1084.2	1063.3	1042.3	1030.5	1022.1
22.5°	1316.1	1269.7	1209.7	1148.7	1093.6	1057.5	1035.6	1014.1	997.0	985.7	974.6
25°	1249.6	1188.9	1125.4	1055.6	1017.8	986.4	962.7	945.2	934.8	920.1	914.5
27.5°	1181.3	1107.8	1037.7	990.8	951.5	922.8	902.1	889.0	875.8	866.4	859.1
30°	1128.8	1054.2	991.4	946.6	906.9	883.1	866.4	851.0	840.5	832.8	827.3
32.5°	1076.9	1002.2	949.5	901.4	870.0	846.9	829.0	817.5	809.3	799.3	796.0
35°	1001.8	935.4	889.4	846.2	814.1	793.0	779.1	767.2	760.2	757.5	755.4
37.5°	929.6	875.4	825.8	790.3	761.6	745.2	728.7	722.9	718.1	713.1	715.3
40°	883.8	832.8	788.9	751.1	728.1	710.0	700.2	693.3	689.0	689.0	689.0
42.5°	844.1	794.4	751.4	717.7	694.6	679.2	668.4	662.5	661.2	660.6	663.9
45°	782.6	736.5	693.3	665.3	645.8	630.4	624.1	619.2	619.2	622.1	622.7
47.5°	721.5	678.4	643.7	612.4	594.5	584.9	579.5	576.9	577.2	580.0	583.2
50°	684.2	641.6	607.3	579.5	562.7	553.6	548.8	547.3	548.8	548.8	553.6
52.5°	643.4	605.3	571.6	548.2	529.2	520.7	518.0	516.0	516.8	519.2	521.2
55°	583.6	549.5	517.4	494.9	481.0	475.4	469.2	469.8	468.5	469.8	469.8
57.5°	523.7	493.0	463.1	445.5	433.1	425.1	418.2	420.1	418.1	417.8	416.7
60°	485.2	451.7	428.0	411.9	397.9	390.9	384.7	386.1	384.0	382.5	379.8
62.5°	443.3	415.4	392.7	377.3	366.1	358.0	351.7	350.3	345.5	340.7	334.6
65°	382.5	359.5	339.3	324.7	314.2	307.9	303.0	298.8	288.3	277.1	271.6
67.5°	323.6	306.9	288.0	275.6	267.1	258.8	249.5	242.4	232.6	226.5	223.0
70°	285.5	269.4	253.4	241.6	232.5	224.8	214.3	209.4	202.5	199.7	196.2
72.5°	249.2	234.3	219.3	208.6	198.9	193.0	184.7	179.9	176.7	175.6	172.2
75°	194.1	182.2	171.1	161.3	153.6	149.4	145.9	142.4	141.0	134.7	131.3
77.5°	141.6	133.8	126.7	119.8	114.3	111.6	104.8	100.8	98.5	95.5	94.8
80°	110.3	104.7	97.8	93.5	85.8	83.1	80.3	79.6	78.9	78.2	77.5
82.5°	82.9	77.4	70.4	67.9	65.7	64.1	62.4	61.7	61.0	61.4	61.3
85°	41.9	39.1	39.1	38.4	37.7	37.0	36.3	36.3	35.6	36.3	35.6
87.5°	16.0	15.8	16.1	15.2	16.1	16.4	16.0	16.2	17.0	16.1	16.2
90°	10.1	11.7	13.1	14.5	16.0	17.4	18.4	19.5	20.5	21.6	22.3
92.5°	10.4	11.1	12.5	13.9	15.3	16.8	17.8	18.9	19.9	20.9	21.5
95°	19.6	16.7	16.9	17.1	17.2	17.4	18.4	19.5	20.5	21.6	22.2
97.5°	107.1	99.2	79.6	60.0	40.4	20.8	20.9	21.1	21.2	21.3	21.4
100°	142.1	131.6	107.3	83.2	59.0	34.7	31.7	28.8	25.8	22.8	21.4
102.5°	180.5	180.1	176.8	173.7	170.6	167.4	135.2	103.0	70.9	38.7	22.6
105°	241.9	242.9	243.7	244.6	245.5	246.3	247.9	249.5	251.1	252.7	250.3
107.5°	301.5	302.4	303.6	304.8	306.0	307.2	307.9	308.7	309.4	310.2	310.9
110°	343.3	344.0	345.1	346.1	347.2	348.2	348.6	348.9	349.3	349.6	350.0



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	385.4	386.1	386.6	387.0	387.5	388.0	388.0	387.9	387.8	387.7	388.0
115°	445.9	446.1	445.9	445.7	445.6	445.4	445.7	446.1	446.4	446.8	447.0
117.5°	502.6	503.2	503.5	503.9	504.3	504.7	504.6	504.5	504.5	504.4	504.3
120°	540.5	540.8	540.6	540.5	540.3	540.1	540.5	540.8	541.2	541.5	541.5
122.5°	574.8	575.1	575.3	575.6	575.8	576.1	576.3	576.5	576.7	576.9	576.8
125°	626.6	626.7	626.4	626.1	625.7	625.4	625.9	626.4	626.9	627.4	627.8
127.5°	672.5	673.0	673.8	674.6	675.4	676.2	676.1	676.0	675.9	675.8	675.7
130°	703.5	703.8	704.3	704.9	705.4	705.9	706.1	706.3	706.4	706.6	706.7
132.5°	732.5	733.0	733.6	734.3	734.9	735.6	735.8	736.0	736.1	736.3	736.3
135°	773.2	773.4	774.1	774.8	775.5	776.2	776.5	776.9	777.2	777.6	777.9
137.5°	811.8	812.2	813.0	813.9	814.6	815.4	815.8	816.1	816.5	816.9	817.0
140°	837.6	838.0	838.3	838.7	839.0	839.3	839.9	840.4	840.9	841.4	841.8
142.5°	860.8	861.2	861.4	861.7	861.9	862.1	862.5	862.8	863.2	863.6	863.8
145°	894.3	894.6	894.6	894.6	894.6	894.6	894.8	894.9	895.1	895.3	895.5
147.5°	923.2	923.6	923.4	923.2	923.0	922.9	923.0	923.2	923.3	923.4	923.6
150°	941.6	941.9	941.7	941.6	941.4	941.2	941.2	941.2	941.2	941.2	941.3
152.5°	957.6	957.7	957.4	957.0	956.6	956.3	956.6	956.9	957.3	957.5	957.6
155°	979.1	978.9	978.4	977.8	977.2	976.7	977.4	978.2	978.9	979.6	979.7
157.5°	997.3	996.9	996.3	995.8	995.2	994.6	995.5	996.4	997.3	998.3	998.3
160°	1007.0	1006.6	1006.5	1006.3	1006.1	1005.9	1007.0	1008.0	1009.2	1010.2	1010.2
162.5°	1016.5	1016.1	1015.9	1015.8	1015.6	1015.4	1016.5	1017.5	1018.5	1019.7	1019.6
165°	1028.5	1028.0	1028.0	1028.0	1028.0	1028.0	1029.5	1030.9	1032.3	1033.7	1033.6
167.5°	1038.4	1037.9	1037.8	1037.7	1037.6	1037.5	1039.1	1040.7	1042.2	1043.7	1043.6
170°	1043.6	1043.2	1043.3	1043.5	1043.7	1043.9	1045.2	1046.6	1048.0	1049.5	1049.2
172.5°	1047.4	1046.9	1047.1	1047.3	1047.4	1047.6	1049.0	1050.5	1051.9	1053.3	1053.0
175°	1051.5	1051.1	1051.3	1051.4	1051.6	1051.8	1053.3	1054.9	1056.5	1058.0	1057.8
177.5°	1053.7	1053.3	1053.6	1053.9	1054.2	1054.4	1055.5	1056.7	1057.8	1058.9	1058.6
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1654.0	1655.1	1651.2	1650.1	1651.2	1655.1	1654.0	1657.4	1657.9	1662.3	1660.7
5°	1534.5	1533.1	1529.5	1530.2	1529.5	1533.1	1534.5	1540.0	1542.9	1554.0	1552.7
7.5°	1432.3	1426.8	1428.4	1422.8	1428.4	1426.8	1432.3	1437.3	1445.8	1450.9	1462.7
10°	1369.7	1362.0	1355.7	1350.2	1355.7	1362.0	1369.7	1372.5	1384.4	1390.0	1401.8
12.5°	1284.2	1277.7	1269.2	1270.9	1269.2	1277.7	1284.2	1296.6	1311.8	1323.5	1342.1
15°	1163.1	1152.6	1135.9	1137.9	1135.9	1152.6	1163.1	1172.2	1187.5	1214.1	1226.6
17.5°	1060.5	1060.6	1052.9	1054.7	1052.9	1060.6	1060.5	1072.9	1080.7	1097.6	1116.8
20°	1007.4	1002.5	1003.2	1001.1	1003.2	1002.5	1007.4	1022.1	1030.5	1042.3	1063.3
22.5°	970.6	964.5	959.7	955.3	959.7	964.5	970.6	974.6	985.7	997.0	1014.1
25°	908.3	904.0	897.8	896.4	897.8	904.0	908.3	914.5	920.1	934.8	945.2
27.5°	853.5	852.7	850.2	847.0	850.2	852.7	853.5	859.1	866.4	875.8	889.0
30°	821.7	820.3	818.9	816.8	818.9	820.3	821.7	827.3	832.8	840.5	851.0
32.5°	793.2	792.3	790.9	791.1	790.9	792.3	793.2	796.0	799.3	809.3	817.5
35°	752.6	751.8	750.5	749.8	750.5	751.8	752.6	755.4	757.5	760.2	767.2
37.5°	714.6	716.4	715.6	715.4	715.6	716.4	714.6	715.3	713.1	718.1	722.9
40°	688.3	689.0	690.4	689.7	690.4	689.0	688.3	689.0	689.0	689.0	693.3
42.5°	666.6	666.7	668.6	666.3	668.6	666.7	666.6	663.9	660.6	661.2	662.5
45°	627.6	631.8	631.1	631.1	631.1	631.8	627.6	622.7	622.1	619.2	619.2
47.5°	585.0	588.7	589.7	589.5	589.7	588.7	585.0	583.2	580.0	577.2	576.9
50°	557.1	555.7	557.8	557.1	557.8	555.7	557.1	553.6	548.8	548.8	547.3
52.5°	523.0	523.3	523.2	522.5	523.2	523.3	523.0	521.2	519.2	516.8	516.0
55°	470.5	471.2	469.8	470.5	469.8	471.2	470.5	469.8	469.8	468.5	469.8
57.5°	413.5	410.2	411.6	409.9	411.6	410.2	413.5	416.7	417.8	418.1	420.1
60°	372.8	367.2	365.8	363.0	365.8	367.2	372.8	379.8	382.5	384.0	386.1
62.5°	327.0	323.1	318.3	320.5	318.3	323.1	327.0	334.6	340.7	345.5	350.3
65°	266.0	263.2	261.1	263.9	261.1	263.2	266.0	271.6	277.1	288.3	298.8
67.5°	220.2	218.6	218.6	217.2	218.6	218.6	220.2	223.0	226.5	232.6	242.4
70°	196.2	194.1	194.1	192.7	194.1	194.1	196.2	196.2	199.7	202.5	209.4
72.5°	171.6	169.5	170.1	169.3	170.1	169.5	171.6	172.2	175.6	176.7	179.9
75°	127.0	123.6	123.6	124.3	123.6	123.6	127.0	131.3	134.7	141.0	142.4
77.5°	94.8	94.1	95.1	93.8	95.1	94.1	94.8	94.8	95.5	98.5	100.8
80°	77.5	76.7	76.1	78.2	76.1	76.7	77.5	77.5	78.2	78.9	79.6
82.5°	60.2	60.1	59.9	62.5	59.9	60.1	60.2	61.3	61.4	61.0	61.7
85°	36.3	34.9	36.3	34.9	36.3	34.9	36.3	35.6	36.3	35.6	36.3
87.5°	17.4	16.9	16.4	17.1	16.4	16.9	17.4	16.2	16.1	17.0	16.2
90°	22.6	23.0	23.3	23.7	23.3	23.0	22.6	22.3	21.6	20.5	19.5
92.5°	21.6	21.6	21.7	21.8	21.7	21.6	21.6	21.5	20.9	19.9	18.9
95°	22.4	22.5	22.7	22.9	22.7	22.5	22.4	22.2	21.6	20.5	19.5
97.5°	21.6	21.7	21.9	22.1	21.9	21.7	21.6	21.4	21.3	21.2	21.1
100°	21.6	21.7	21.9	22.1	21.9	21.7	21.6	21.4	22.8	25.8	28.8
102.5°	22.6	22.6	22.7	22.7	22.7	22.6	22.6	22.6	38.7	70.9	103.0
105°	244.0	237.6	231.4	225.0	231.4	237.6	244.0	250.3	252.7	251.1	249.5
107.5°	311.6	312.3	313.0	313.7	313.0	312.3	311.6	310.9	310.2	309.4	308.7
110°	350.6	351.1	351.6	352.1	351.6	351.1	350.6	350.0	349.6	349.3	348.9



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	388.7	389.4	390.0	390.7	390.0	389.4	388.7	388.0	387.7	387.8	387.9
115°	447.0	447.0	447.0	447.0	447.0	447.0	447.0	447.0	446.8	446.4	446.1
117.5°	504.3	504.2	504.1	504.1	504.1	504.2	504.3	504.3	504.4	504.5	504.5
120°	541.2	540.8	540.5	540.1	540.5	540.8	541.2	541.5	541.5	541.2	540.8
122.5°	576.5	576.1	575.8	575.4	575.8	576.1	576.5	576.8	576.9	576.7	576.5
125°	628.0	628.1	628.3	628.5	628.3	628.1	628.0	627.8	627.4	626.9	626.4
127.5°	675.5	675.4	675.3	675.1	675.3	675.4	675.5	675.7	675.8	675.9	676.0
130°	706.7	706.7	706.7	706.7	706.7	706.7	706.7	706.7	706.6	706.4	706.3
132.5°	736.2	736.0	735.9	735.8	735.9	736.0	736.2	736.3	736.3	736.1	736.0
135°	778.3	778.6	779.0	779.3	779.0	778.6	778.3	777.9	777.6	777.2	776.9
137.5°	816.9	816.8	816.7	816.6	816.7	816.8	816.9	817.0	816.9	816.5	816.1
140°	842.0	842.1	842.3	842.5	842.3	842.1	842.0	841.8	841.4	840.9	840.4
142.5°	863.8	863.9	863.9	863.9	863.9	863.9	863.8	863.8	863.6	863.2	862.8
145°	896.0	896.3	896.7	897.0	896.7	896.3	896.0	895.5	895.3	895.1	894.9
147.5°	923.8	923.9	924.1	924.3	924.1	923.9	923.8	923.6	923.4	923.3	923.2
150°	941.5	941.6	941.8	942.0	941.8	941.6	941.5	941.3	941.2	941.2	941.2
152.5°	957.5	957.4	957.3	957.2	957.3	957.4	957.5	957.6	957.5	957.3	956.9
155°	979.1	978.6	978.1	977.5	978.1	978.6	979.1	979.7	979.6	978.9	978.2
157.5°	997.3	996.4	995.5	994.6	995.5	996.4	997.3	998.3	998.3	997.3	996.4
160°	1009.2	1008.0	1007.0	1005.9	1007.0	1008.0	1009.2	1010.2	1010.2	1009.2	1008.0
162.5°	1018.3	1017.1	1016.0	1014.8	1016.0	1017.1	1018.3	1019.6	1019.7	1018.5	1017.5
165°	1032.0	1030.5	1028.9	1027.2	1028.9	1030.5	1032.0	1033.6	1033.7	1032.3	1030.9
167.5°	1041.9	1040.1	1038.3	1036.6	1038.3	1040.1	1041.9	1043.6	1043.7	1042.2	1040.7
170°	1047.5	1045.8	1044.0	1042.3	1044.0	1045.8	1047.5	1049.2	1049.5	1048.0	1046.6
172.5°	1051.2	1049.2	1047.3	1045.4	1047.3	1049.2	1051.2	1053.0	1053.3	1051.9	1050.5
175°	1055.7	1053.6	1051.5	1049.4	1051.5	1053.6	1055.7	1057.8	1058.0	1056.5	1054.9
177.5°	1056.9	1055.3	1053.6	1051.9	1053.6	1055.3	1056.9	1058.6	1058.9	1057.8	1056.7
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1657.4	1661.2	1670.2	1680.2	1688.6	1695.9	1701.4	1709.3	1716.6	1726.6	1736.1
5°	1556.8	1566.6	1580.5	1597.3	1618.2	1632.2	1649.7	1665.1	1687.4	1709.7	1731.3
7.5°	1468.5	1479.4	1499.9	1523.0	1547.9	1570.7	1591.4	1618.5	1648.1	1680.6	1717.0
10°	1411.6	1423.5	1447.9	1474.4	1503.8	1526.1	1554.0	1586.1	1619.6	1659.4	1704.1
12.5°	1360.2	1371.5	1401.0	1428.1	1458.5	1483.1	1515.5	1548.1	1592.9	1636.0	1686.8
15°	1260.1	1290.1	1323.6	1355.7	1392.1	1422.1	1461.2	1494.7	1537.3	1598.0	1656.0
17.5°	1148.9	1180.9	1222.5	1272.1	1320.8	1358.0	1397.7	1439.3	1490.0	1552.0	1618.8
20°	1084.2	1110.0	1156.1	1211.2	1267.8	1319.5	1355.7	1401.8	1454.2	1521.3	1590.3
22.5°	1035.6	1057.5	1093.6	1148.7	1209.7	1269.7	1316.1	1361.6	1419.6	1486.6	1561.9
25°	962.7	986.4	1017.8	1055.6	1125.4	1188.9	1249.6	1302.0	1363.4	1430.5	1514.2
27.5°	902.1	922.8	951.5	990.8	1037.7	1107.8	1181.3	1241.1	1304.1	1376.0	1460.0
30°	866.4	883.1	906.9	946.6	991.4	1054.2	1128.8	1198.7	1262.2	1336.9	1424.2
32.5°	829.0	846.9	870.0	901.4	949.5	1002.2	1076.9	1153.5	1220.9	1297.3	1382.8
35°	779.1	793.0	814.1	846.2	889.4	935.4	1001.8	1080.7	1152.0	1233.6	1315.2
37.5°	728.7	745.2	761.6	790.3	825.8	875.4	929.6	1010.2	1089.0	1163.7	1243.3
40°	700.2	710.0	728.1	751.1	788.9	832.8	883.8	962.7	1041.6	1115.6	1195.9
42.5°	668.4	679.2	694.6	717.7	751.4	794.4	844.1	912.4	994.7	1066.4	1139.4
45°	624.1	630.4	645.8	665.3	693.3	736.5	782.6	843.3	920.8	989.3	1053.5
47.5°	579.5	584.9	594.5	612.4	643.7	678.4	721.5	776.1	844.0	912.4	966.7
50°	548.8	553.6	562.7	579.5	607.3	641.6	684.2	733.1	793.8	859.4	904.7
52.5°	518.0	520.7	529.2	548.2	571.6	605.3	643.4	688.3	745.2	799.6	845.6
55°	469.2	475.4	481.0	494.9	517.4	549.5	583.6	626.2	670.2	716.3	755.4
57.5°	418.2	425.1	433.1	445.5	463.1	493.0	523.7	558.3	595.8	634.0	666.8
60°	384.7	390.9	397.9	411.9	428.0	451.7	485.2	515.2	543.8	578.8	611.6
62.5°	351.7	358.0	366.1	377.3	392.7	415.4	443.3	469.4	499.2	529.6	554.0
65°	303.0	307.9	314.2	324.7	339.3	359.5	382.5	402.8	429.4	451.7	474.0
67.5°	249.5	258.8	267.1	275.6	288.0	306.9	323.6	343.0	360.9	377.6	397.9
70°	214.3	224.8	232.5	241.6	253.4	269.4	285.5	298.8	313.5	329.5	347.7
72.5°	184.7	193.0	198.9	208.6	219.3	234.3	249.2	260.2	272.2	283.2	300.7
75°	145.9	149.4	153.6	161.3	171.1	182.2	194.1	203.9	210.9	220.7	233.2
77.5°	104.8	111.6	114.3	119.8	126.7	133.8	141.6	149.9	156.5	160.0	169.7
80°	80.3	83.1	85.8	93.5	97.8	104.7	110.3	118.0	120.8	124.3	133.3
82.5°	62.4	64.1	65.7	67.9	70.4	77.4	82.9	87.9	90.6	91.9	98.8
85°	36.3	37.0	37.7	38.4	39.1	39.1	41.9	45.3	50.3	50.3	52.3
87.5°	16.0	16.4	16.1	15.2	16.1	15.8	16.0	15.6	16.9	18.2	19.5
90°	18.4	17.4	16.0	14.5	13.1	11.7	10.1	8.2	6.3	4.3	2.3
92.5°	17.8	16.8	15.3	13.9	12.5	11.1	10.4	10.3	10.2	10.1	10.0
95°	18.4	17.4	17.2	17.1	16.9	16.7	19.6	25.5	31.5	37.5	43.4
97.5°	20.9	20.8	40.4	60.0	79.6	99.2	107.1	103.4	99.7	95.9	92.2
100°	31.7	34.7	59.0	83.2	107.3	131.6	142.1	139.0	135.8	132.7	129.5
102.5°	135.2	167.4	170.6	173.7	176.8	180.1	180.5	178.1	175.8	173.5	171.2
105°	247.9	246.3	245.5	244.6	243.7	242.9	241.9	240.9	239.7	238.7	237.6
107.5°	307.9	307.2	306.0	304.8	303.6	302.4	301.5	301.0	300.4	299.9	299.4
110°	348.6	348.2	347.2	346.1	345.1	344.0	343.3	342.6	342.1	341.6	341.1



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	388.0	388.0	387.5	387.0	386.6	386.1	385.4	384.4	383.4	382.4	381.5
115°	445.7	445.4	445.6	445.7	445.9	446.1	445.9	445.4	444.8	444.2	443.7
117.5°	504.6	504.7	504.3	503.9	503.5	503.2	502.6	501.9	501.2	500.5	499.8
120°	540.5	540.1	540.3	540.5	540.6	540.8	540.5	539.9	539.2	538.5	537.8
122.5°	576.3	576.1	575.8	575.6	575.3	575.1	574.8	574.3	573.9	573.5	573.1
125°	625.9	625.4	625.7	626.1	626.4	626.7	626.6	625.9	625.2	624.5	623.8
127.5°	676.1	676.2	675.4	674.6	673.8	673.0	672.5	672.4	672.2	672.0	671.8
130°	706.1	705.9	705.4	704.9	704.3	703.8	703.5	703.3	703.1	703.0	702.8
132.5°	735.8	735.6	734.9	734.3	733.6	733.0	732.5	732.2	731.8	731.4	731.1
135°	776.5	776.2	775.5	774.8	774.1	773.4	773.2	773.3	773.5	773.7	773.9
137.5°	815.8	815.4	814.6	813.9	813.0	812.2	811.8	811.7	811.7	811.6	811.5
140°	839.9	839.3	839.0	838.7	838.3	838.0	837.6	837.3	836.9	836.6	836.2
142.5°	862.5	862.1	861.9	861.7	861.4	861.2	860.8	860.2	859.6	858.9	858.3
145°	894.8	894.6	894.6	894.6	894.6	894.6	894.3	893.8	893.3	892.8	892.2
147.5°	923.0	922.9	923.0	923.2	923.4	923.6	923.2	922.2	921.2	920.3	919.3
150°	941.2	941.2	941.4	941.6	941.7	941.9	941.6	941.0	940.3	939.6	938.9
152.5°	956.6	956.3	956.6	957.0	957.4	957.7	957.6	956.9	956.3	955.8	955.2
155°	977.4	976.7	977.2	977.8	978.4	978.9	979.1	978.9	978.7	978.5	978.4
157.5°	995.5	994.6	995.2	995.8	996.3	996.9	997.3	997.4	997.5	997.6	997.7
160°	1007.0	1005.9	1006.1	1006.3	1006.5	1006.6	1007.0	1007.5	1008.0	1008.6	1009.2
162.5°	1016.5	1015.4	1015.6	1015.8	1015.9	1016.1	1016.5	1017.2	1017.8	1018.5	1019.3
165°	1029.5	1028.0	1028.0	1028.0	1028.0	1028.0	1028.5	1029.4	1030.3	1031.2	1032.0
167.5°	1039.1	1037.5	1037.6	1037.7	1037.8	1037.9	1038.4	1039.4	1040.3	1041.2	1042.1
170°	1045.2	1043.9	1043.7	1043.5	1043.3	1043.2	1043.6	1044.6	1045.7	1046.7	1047.8
172.5°	1049.0	1047.6	1047.4	1047.3	1047.1	1046.9	1047.4	1048.4	1049.5	1050.6	1051.6
175°	1053.3	1051.8	1051.6	1051.4	1051.3	1051.1	1051.5	1052.6	1053.6	1054.6	1055.7
177.5°	1055.5	1054.4	1054.2	1053.9	1053.6	1053.3	1053.7	1054.6	1055.6	1056.6	1057.6
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1743.3	1748.4	1753.9	1764.5	1773.5	1777.5	1785.2	1790.8	1789.2	1797.0	1810.4
5°	1750.2	1769.1	1790.7	1813.0	1838.2	1859.1	1875.8	1892.6	1905.9	1922.0	1945.7
7.5°	1749.1	1782.6	1819.1	1859.1	1900.3	1935.9	1968.8	2002.4	2032.1	2064.7	2107.2
10°	1744.6	1789.3	1834.6	1887.0	1939.3	1988.9	2033.7	2075.5	2115.4	2157.9	2211.7
12.5°	1739.6	1791.0	1845.8	1908.8	1974.0	2033.7	2086.2	2146.5	2196.3	2251.2	2313.3
15°	1717.4	1786.5	1861.2	1942.9	2021.0	2101.3	2173.2	2247.3	2316.3	2382.0	2460.2
17.5°	1691.9	1771.7	1859.8	1956.3	2050.2	2147.9	2233.1	2326.4	2397.1	2485.2	2557.8
20°	1671.3	1757.2	1851.4	1959.6	2066.5	2174.6	2268.9	2363.9	2443.5	2532.1	2624.2
22.5°	1646.2	1740.4	1842.5	1954.6	2066.5	2184.7	2289.0	2383.4	2481.9	2581.8	2676.7
25°	1605.7	1703.4	1811.6	1934.5	2063.0	2183.7	2295.4	2412.7	2518.8	2627.1	2712.2
27.5°	1556.0	1658.6	1772.7	1899.5	2031.2	2155.0	2286.5	2411.5	2518.3	2622.4	2696.7
30°	1516.3	1624.6	1734.1	1862.6	1999.4	2132.0	2273.1	2398.0	2510.4	2604.0	2645.8
32.5°	1475.5	1578.2	1691.1	1821.3	1961.5	2104.2	2244.0	2371.8	2475.8	2531.9	2533.0
35°	1404.6	1501.0	1618.2	1746.1	1889.9	2044.8	2186.6	2312.2	2375.7	2380.6	2312.2
37.5°	1327.3	1415.6	1526.4	1654.3	1811.8	1965.9	2110.7	2194.4	2215.7	2144.7	2018.1
40°	1272.0	1353.6	1460.5	1591.7	1748.1	1907.2	2039.2	2100.6	2078.3	1963.1	1822.1
42.5°	1213.9	1290.0	1392.9	1522.5	1679.4	1840.3	1952.7	1985.6	1926.4	1793.3	1628.3
45°	1119.1	1188.9	1290.8	1421.4	1572.2	1722.9	1808.2	1791.4	1692.9	1535.2	1350.2
47.5°	1020.4	1087.8	1179.5	1300.3	1454.7	1584.9	1642.5	1592.1	1452.0	1278.4	1127.9
50°	955.0	1024.1	1108.6	1223.9	1364.8	1490.5	1527.5	1450.7	1295.1	1128.1	990.0
52.5°	890.8	949.9	1032.7	1144.0	1278.8	1384.9	1404.6	1316.1	1155.4	1005.8	883.2
55°	793.0	846.9	916.7	1021.4	1137.9	1228.0	1217.5	1103.8	957.9	830.1	733.8
57.5°	698.5	739.0	803.5	901.7	1004.0	1064.5	1026.2	929.2	793.2	688.6	607.3
60°	636.0	673.7	733.8	819.6	909.7	943.8	911.7	806.4	698.8	603.2	534.7
62.5°	576.8	610.1	661.7	741.4	814.2	834.4	800.0	708.0	611.2	529.5	472.8
65°	490.8	521.5	565.5	622.1	672.3	682.1	659.7	565.5	492.2	423.7	384.7
67.5°	412.7	432.8	467.2	516.0	542.7	548.5	505.3	446.1	381.4	339.4	309.9
70°	360.2	374.2	406.3	432.8	454.4	455.1	415.4	367.9	318.3	284.2	262.5
72.5°	309.4	322.9	347.1	365.3	381.8	376.5	340.0	302.6	262.5	236.7	220.7
75°	238.7	250.6	263.2	271.6	271.6	264.6	238.0	210.2	187.1	171.8	166.8
77.5°	173.6	183.3	187.5	186.2	183.8	172.9	156.1	137.8	129.6	122.3	118.7
80°	136.1	140.4	141.7	138.3	134.0	121.5	110.3	102.6	94.9	92.2	90.8
82.5°	101.0	104.6	101.0	101.9	92.7	82.4	76.2	73.6	70.4	69.3	67.9
85°	53.7	53.0	51.7	48.2	41.9	40.5	39.8	39.1	37.7	38.4	37.0
87.5°	19.3	18.0	16.2	16.0	16.4	15.5	16.4	16.6	16.9	16.6	17.9
90°	4.3	6.3	8.2	10.1	11.7	13.1	14.5	16.0	17.4	18.4	19.5
92.5°	10.1	10.2	10.3	10.4	11.1	12.5	13.9	15.3	16.8	17.8	18.9
95°	37.5	31.5	25.5	19.6	16.7	16.9	17.1	17.2	17.4	18.4	19.5
97.5°	95.9	99.7	103.4	107.1	99.2	79.6	60.0	40.4	20.8	20.9	21.1
100°	132.7	135.8	139.0	142.1	131.6	107.3	83.2	59.0	34.7	31.7	28.8
102.5°	173.5	175.8	178.1	180.5	180.1	176.8	173.7	170.6	167.4	135.2	103.0
105°	238.7	239.7	240.9	241.9	242.9	243.7	244.6	245.5	246.3	247.9	249.5
107.5°	299.9	300.4	301.0	301.5	302.4	303.6	304.8	306.0	307.2	307.9	308.7
110°	341.6	342.1	342.6	343.3	344.0	345.1	346.1	347.2	348.2	348.6	348.9





TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	382.4	383.4	384.4	385.4	386.1	386.6	387.0	387.5	388.0	388.0	387.9
115°	444.2	444.8	445.4	445.9	446.1	445.9	445.7	445.6	445.4	445.7	446.1
117.5°	500.5	501.2	501.9	502.6	503.2	503.5	503.9	504.3	504.7	504.6	504.5
120°	538.5	539.2	539.9	540.5	540.8	540.6	540.5	540.3	540.1	540.5	540.8
122.5°	573.5	573.9	574.3	574.8	575.1	575.3	575.6	575.8	576.1	576.3	576.5
125°	624.5	625.2	625.9	626.6	626.7	626.4	626.1	625.7	625.4	625.9	626.4
127.5°	672.0	672.2	672.4	672.5	673.0	673.8	674.6	675.4	676.2	676.1	676.0
130°	703.0	703.1	703.3	703.5	703.8	704.3	704.9	705.4	705.9	706.1	706.3
132.5°	731.4	731.8	732.2	732.5	733.0	733.6	734.3	734.9	735.6	735.8	736.0
135°	773.7	773.5	773.3	773.2	773.4	774.1	774.8	775.5	776.2	776.5	776.9
137.5°	811.6	811.7	811.7	811.8	812.2	813.0	813.9	814.6	815.4	815.8	816.1
140°	836.6	836.9	837.3	837.6	838.0	838.3	838.7	839.0	839.3	839.9	840.4
142.5°	858.9	859.6	860.2	860.8	861.2	861.4	861.7	861.9	862.1	862.5	862.8
145°	892.8	893.3	893.8	894.3	894.6	894.6	894.6	894.6	894.6	894.8	894.9
147.5°	920.3	921.2	922.2	923.2	923.6	923.4	923.2	923.0	922.9	923.0	923.2
150°	939.6	940.3	941.0	941.6	941.9	941.7	941.6	941.4	941.2	941.2	941.2
152.5°	955.8	956.3	956.9	957.6	957.7	957.4	957.0	956.6	956.3	956.6	956.9
155°	978.5	978.7	978.9	979.1	978.9	978.4	977.8	977.2	976.7	977.4	978.2
157.5°	997.6	997.5	997.4	997.3	996.9	996.3	995.8	995.2	994.6	995.5	996.4
160°	1008.6	1008.0	1007.5	1007.0	1006.6	1006.5	1006.3	1006.1	1005.9	1007.0	1008.0
162.5°	1018.5	1017.8	1017.2	1016.5	1016.1	1015.9	1015.8	1015.6	1015.4	1016.5	1017.5
165°	1031.2	1030.3	1029.4	1028.5	1028.0	1028.0	1028.0	1028.0	1028.0	1029.5	1030.9
167.5°	1041.2	1040.3	1039.4	1038.4	1037.9	1037.8	1037.7	1037.6	1037.5	1039.1	1040.7
170°	1046.7	1045.7	1044.6	1043.6	1043.2	1043.3	1043.5	1043.7	1043.9	1045.2	1046.6
172.5°	1050.6	1049.5	1048.4	1047.4	1046.9	1047.1	1047.3	1047.4	1047.6	1049.0	1050.5
175°	1054.6	1053.6	1052.6	1051.5	1051.1	1051.3	1051.4	1051.6	1051.8	1053.3	1054.9
177.5°	1056.6	1055.6	1054.6	1053.7	1053.3	1053.6	1053.9	1054.2	1054.4	1055.5	1056.7
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7	1732.7
2.5°	1817.7	1819.9	1821.6	1827.1	1827.7	1832.7	1827.7
5°	1968.0	1977.8	1993.2	2008.5	2009.9	2019.6	2002.3
7.5°	2136.7	2159.3	2173.4	2198.3	2208.1	2214.1	2204.1
10°	2252.8	2273.8	2310.8	2329.0	2347.1	2349.9	2341.5
12.5°	2365.1	2398.3	2427.5	2461.8	2461.0	2485.6	2476.7
15°	2514.7	2548.9	2589.3	2627.8	2641.7	2641.7	2652.9
17.5°	2621.3	2684.0	2725.9	2756.0	2789.0	2794.7	2790.9
20°	2693.4	2761.1	2805.8	2844.9	2867.2	2873.5	2873.5
22.5°	2746.9	2804.6	2848.2	2883.4	2901.8	2909.2	2907.0
25°	2784.1	2833.7	2860.2	2870.6	2875.6	2874.2	2860.9
27.5°	2733.3	2731.1	2714.3	2682.2	2658.1	2643.4	2626.7
30°	2636.2	2599.8	2557.9	2511.8	2452.6	2407.1	2393.2
32.5°	2491.4	2409.9	2338.9	2262.2	2198.4	2153.0	2134.0
35°	2211.7	2082.5	1977.1	1884.9	1818.0	1776.0	1762.1
37.5°	1879.7	1754.6	1624.2	1534.8	1479.1	1436.8	1421.1
40°	1668.5	1532.4	1418.6	1334.8	1277.6	1236.4	1235.7
42.5°	1475.8	1345.8	1238.8	1178.4	1116.7	1089.4	1089.3
45°	1208.4	1104.4	1013.7	966.2	929.2	906.9	900.6
47.5°	1000.6	914.5	854.0	816.3	786.1	771.8	762.7
50°	883.8	808.4	760.2	727.4	710.6	692.6	691.2
52.5°	786.7	725.8	688.2	661.6	640.4	629.4	629.8
55°	661.2	613.0	586.4	566.1	549.5	541.1	537.6
57.5°	556.9	520.8	501.5	482.9	475.8	469.3	467.5
60°	492.2	467.8	449.6	434.9	424.4	422.3	421.6
62.5°	438.6	413.0	400.4	389.1	381.4	378.2	377.0
65°	361.6	342.7	331.6	322.6	319.7	314.9	314.2
67.5°	291.5	280.2	272.9	266.5	262.8	262.5	262.5
70°	248.5	242.3	236.0	232.5	230.4	228.9	228.9
72.5°	211.7	207.0	201.9	200.1	199.7	198.2	197.7
75°	161.3	156.4	157.0	153.6	150.8	147.3	145.2
77.5°	114.3	110.9	110.2	109.8	107.3	106.9	108.1
80°	88.7	85.1	84.4	85.1	84.4	82.4	82.4
82.5°	67.5	64.5	63.8	63.4	62.7	63.4	62.3
85°	36.3	34.9	34.9	34.9	36.3	35.6	34.9
87.5°	17.0	16.6	17.3	16.8	16.9	16.4	17.1
90°	20.5	21.6	22.3	22.6	23.0	23.3	23.7
92.5°	19.9	20.9	21.5	21.6	21.6	21.7	21.8
95°	20.5	21.6	22.2	22.4	22.5	22.7	22.9
97.5°	21.2	21.3	21.4	21.6	21.7	21.9	22.1
100°	25.8	22.8	21.4	21.6	21.7	21.9	22.1
102.5°	70.9	38.7	22.6	22.6	22.6	22.7	22.7
105°	251.1	252.7	250.3	244.0	237.6	231.4	225.0
107.5°	309.4	310.2	310.9	311.6	312.3	313.0	313.7
110°	349.3	349.6	350.0	350.6	351.1	351.6	352.1



TEST NUMBER: P332967-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	387.8	387.7	388.0	388.7	389.4	390.0	390.7
115°	446.4	446.8	447.0	447.0	447.0	447.0	447.0
117.5°	504.5	504.4	504.3	504.3	504.2	504.1	504.1
120°	541.2	541.5	541.5	541.2	540.8	540.5	540.1
122.5°	576.7	576.9	576.8	576.5	576.1	575.8	575.4
125°	626.9	627.4	627.8	628.0	628.1	628.3	628.5
127.5°	675.9	675.8	675.7	675.5	675.4	675.3	675.1
130°	706.4	706.6	706.7	706.7	706.7	706.7	706.7
132.5°	736.1	736.3	736.3	736.2	736.0	735.9	735.8
135°	777.2	777.6	777.9	778.3	778.6	779.0	779.3
137.5°	816.5	816.9	817.0	816.9	816.8	816.7	816.6
140°	840.9	841.4	841.8	842.0	842.1	842.3	842.5
142.5°	863.2	863.6	863.8	863.8	863.9	863.9	863.9
145°	895.1	895.3	895.5	896.0	896.3	896.7	897.0
147.5°	923.3	923.4	923.6	923.8	923.9	924.1	924.3
150°	941.2	941.2	941.3	941.5	941.6	941.8	942.0
152.5°	957.3	957.5	957.6	957.5	957.4	957.3	957.2
155°	978.9	979.6	979.7	979.1	978.6	978.1	977.5
157.5°	997.3	998.3	998.3	997.3	996.4	995.5	994.6
160°	1009.2	1010.2	1010.2	1009.2	1008.0	1007.0	1005.9
162.5°	1018.5	1019.7	1019.6	1018.3	1017.1	1016.0	1014.8
165°	1032.3	1033.7	1033.6	1032.0	1030.5	1028.9	1027.2
167.5°	1042.2	1043.7	1043.6	1041.9	1040.1	1038.3	1036.6
170°	1048.0	1049.5	1049.2	1047.5	1045.8	1044.0	1042.3
172.5°	1051.9	1053.3	1053.0	1051.2	1049.2	1047.3	1045.4
175°	1056.5	1058.0	1057.8	1055.7	1053.6	1051.5	1049.4
177.5°	1057.8	1058.9	1058.6	1056.9	1055.3	1053.6	1051.9
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7

(END OF REPORT)