

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332970-840

Luminaire Tested: **S124RDIP-S1020D810U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332970-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1020D810U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7481.7 lumens  
Efficiency: N/A  
Efficacy: 137.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332970-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332970-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	100	95	91	88	92	89	86	83	77	74	72	66	64	62	55	54	53	48
2	91	84	77	72	84	78	73	68	68	64	60	58	55	52	49	47	45	41
3	83	74	66	61	77	69	62	57	60	55	51	51	48	45	44	41	39	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	38	39	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	41	37	34	35	32	29	26
6	65	53	44	39	60	49	42	37	43	37	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	24	21	19
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	22	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14721	14721	14721
5°	14755	14574	14665
10°	14662	14399	14399
15°	14493	14097	13992
20°	14262	13698	13447
25°	13967	13233	12897
30°	13679	12743	12209
35°	13361	12232	11517
40°	12978	11653	10771
45°	12625	11079	10011
50°	12223	10417	9207
55°	11792	9728	8332
60°	11317	8972	7440
65°	10883	8029	6562
70°	10249	6987	5570
75°	9451	5792	4529
80°	8243	4412	4156
85°	6984	4011	3751



TEST NUMBER: P332970-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.3	2.3
10°-20°	477.7	6.4
20°-30°	689.8	9.2
30°-40°	781.8	10.5
40°-50°	755.0	10.1
50°-60°	627.8	8.4
60°-70°	433.5	5.8
70°-80°	219.7	2.9
80°-90°	59.4	0.8
90°-100°	36.1	0.5
100°-110°	230.2	3.1
110°-120°	440.4	5.9
120°-130°	559.1	7.5
130°-140°	598.2	8.0
140°-150°	559.3	7.5
150°-160°	451.1	6.0
160°-170°	290.9	3.9
170°-180°	100.3	1.3
0°-30°	1338.7	17.9
0°-40°	2120.6	28.3
0°-60°	3503.4	46.8
0°-90°	4216.1	56.4
90°-120°	706.7	9.4
90°-150°	2423.3	32.4
90°-180°	3266.0	43.7
0°-180°	7481.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1824	1824	1824	1824	1824	
5°	1821	1814	1798	1811	1810	173
15°	1734	1720	1687	1683	1674	488
25°	1568	1541	1486	1462	1448	722
35°	1356	1310	1241	1195	1169	847
45°	1106	1052	970	904	877	852
55°	838	780	691	621	592	749
65°	570	508	420	363	344	562
75°	303	251	186	155	145	320
85°	75	49	43	41	40	85
90°	2	11	17	22	24	6
95°	43	18	17	22	23	56
105°	238	242	246	252	225	249
115°	444	446	445	447	447	437
125°	624	627	625	628	628	557
135°	774	773	776	778	779	596
145°	892	894	895	895	897	557
155°	978	979	977	980	978	451
165°	1032	1028	1028	1034	1027	292
175°	1056	1051	1052	1058	1049	100
180°	1056	1056	1056	1056	1056	



TEST NUMBER: P332970-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1828.0	1826.9	1825.9	1825.0	1824.0	1822.1	1819.4	1816.6	1813.9	1811.2	1813.9
5°	1820.7	1819.5	1818.3	1816.9	1815.7	1813.2	1809.6	1805.8	1802.1	1798.4	1801.5
7.5°	1804.2	1802.9	1801.6	1800.3	1799.0	1795.9	1791.1	1786.2	1781.4	1776.6	1778.6
10°	1788.6	1787.1	1785.4	1783.9	1782.4	1778.8	1773.2	1767.7	1762.0	1756.5	1757.7
12.5°	1768.5	1766.7	1764.8	1763.1	1761.3	1757.1	1750.5	1743.9	1737.4	1730.8	1731.5
15°	1734.1	1731.3	1728.6	1725.8	1722.9	1717.7	1709.9	1702.1	1694.5	1686.7	1686.1
17.5°	1692.5	1688.5	1684.5	1680.4	1676.4	1669.7	1660.4	1651.1	1641.8	1632.4	1630.7
20°	1660.1	1656.1	1652.0	1648.0	1644.0	1636.7	1626.2	1615.6	1605.1	1594.5	1592.1
22.5°	1624.4	1619.8	1615.3	1610.8	1606.3	1598.3	1587.1	1575.8	1564.5	1553.2	1549.4
25°	1568.0	1562.4	1556.8	1551.3	1545.6	1536.5	1523.8	1511.1	1498.3	1485.6	1480.4
27.5°	1508.7	1501.8	1494.8	1487.7	1480.8	1470.5	1456.8	1443.3	1429.7	1416.0	1409.6
30°	1467.4	1459.7	1452.0	1444.2	1436.4	1425.2	1410.7	1396.0	1381.5	1367.0	1359.2
32.5°	1423.9	1415.1	1406.3	1397.7	1388.9	1377.0	1361.9	1346.9	1331.7	1316.7	1307.7
35°	1355.7	1345.8	1335.8	1326.0	1316.1	1303.3	1287.8	1272.3	1256.8	1241.2	1230.7
37.5°	1282.8	1272.6	1262.4	1252.1	1241.9	1228.2	1211.0	1193.9	1176.6	1159.4	1147.6
40°	1231.5	1221.2	1211.0	1200.7	1190.5	1176.6	1158.9	1141.1	1123.5	1105.8	1092.8
42.5°	1182.3	1171.6	1160.8	1150.1	1139.4	1124.8	1106.4	1087.9	1069.5	1051.1	1037.8
45°	1105.8	1094.4	1082.9	1071.4	1059.9	1044.8	1026.2	1007.6	989.0	970.4	955.2
47.5°	1026.8	1014.9	1003.1	991.3	979.4	963.8	944.4	925.0	905.6	886.4	870.6
50°	973.2	961.1	949.0	936.9	924.7	908.8	889.0	869.1	849.2	829.4	813.9
52.5°	918.5	906.6	894.7	882.9	871.0	855.0	834.6	814.3	793.9	773.6	757.8
55°	837.8	825.4	812.9	800.5	788.1	771.8	751.6	731.4	711.3	691.2	675.0
57.5°	757.9	745.0	732.1	719.1	706.3	689.8	670.0	650.2	630.3	610.5	594.1
60°	700.9	688.5	676.1	663.7	651.3	635.1	615.3	595.4	575.5	555.7	539.6
62.5°	649.5	636.6	623.7	610.8	597.9	581.3	560.9	540.6	520.2	499.9	484.9
65°	569.7	556.3	543.0	529.7	516.3	499.7	479.9	460.0	440.1	420.3	407.0
67.5°	486.8	473.9	461.2	448.4	435.6	420.0	401.5	383.1	364.7	346.3	334.8
70°	434.2	421.2	408.2	395.2	382.1	366.8	349.1	331.3	313.7	296.0	285.8
72.5°	378.4	366.6	354.8	343.1	331.2	317.0	300.3	283.6	266.9	250.2	241.5
75°	303.0	291.5	280.0	268.5	257.1	244.0	229.4	214.9	200.3	185.7	178.5
77.5°	226.5	216.7	207.0	197.2	187.5	176.7	164.9	153.2	141.4	129.6	125.4
80°	177.3	168.3	159.4	150.4	141.4	132.2	122.9	113.6	104.2	94.9	94.0
82.5°	134.9	126.6	118.4	110.1	101.9	95.0	89.8	84.4	79.1	73.7	73.0
85°	75.4	69.2	63.0	56.8	50.6	47.0	46.0	45.1	44.2	43.3	42.6
87.5°	26.2	24.5	22.9	21.4	19.8	19.0	19.0	19.1	19.1	19.1	19.1
90°	2.3	4.3	6.3	8.2	10.1	11.7	13.1	14.5	16.0	17.4	18.4
92.5°	10.0	10.1	10.2	10.3	10.4	11.1	12.5	13.9	15.3	16.8	17.8
95°	43.4	37.5	31.5	25.5	19.6	16.7	16.9	17.1	17.2	17.4	18.4
97.5°	92.2	95.9	99.7	103.4	107.1	99.2	79.6	60.0	40.4	20.8	20.9
100°	129.5	132.7	135.8	139.0	142.1	131.6	107.3	83.2	59.0	34.7	31.7
102.5°	171.2	173.5	175.8	178.1	180.5	180.1	176.8	173.7	170.6	167.4	135.2
105°	237.6	238.7	239.7	240.9	241.9	242.9	243.7	244.6	245.5	246.3	247.9
107.5°	299.4	299.9	300.4	301.0	301.5	302.4	303.6	304.8	306.0	307.2	307.9
110°	341.1	341.6	342.1	342.6	343.3	344.0	345.1	346.1	347.2	348.2	348.6



TEST NUMBER: P332970-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	381.5	382.4	383.4	384.4	385.4	386.1	386.6	387.0	387.5	388.0	388.0
115°	443.7	444.2	444.8	445.4	445.9	446.1	445.9	445.7	445.6	445.4	445.7
117.5°	499.8	500.5	501.2	501.9	502.6	503.2	503.5	503.9	504.3	504.7	504.6
120°	537.8	538.5	539.2	539.9	540.5	540.8	540.6	540.5	540.3	540.1	540.5
122.5°	573.1	573.5	573.9	574.3	574.8	575.1	575.3	575.6	575.8	576.1	576.3
125°	623.8	624.5	625.2	625.9	626.6	626.7	626.4	626.1	625.7	625.4	625.9
127.5°	671.8	672.0	672.2	672.4	672.5	673.0	673.8	674.6	675.4	676.2	676.1
130°	702.8	703.0	703.1	703.3	703.5	703.8	704.3	704.9	705.4	705.9	706.1
132.5°	731.1	731.4	731.8	732.2	732.5	733.0	733.6	734.3	734.9	735.6	735.8
135°	773.9	773.7	773.5	773.3	773.2	773.4	774.1	774.8	775.5	776.2	776.5
137.5°	811.5	811.6	811.7	811.7	811.8	812.2	813.0	813.9	814.6	815.4	815.8
140°	836.2	836.6	836.9	837.3	837.6	838.0	838.3	838.7	839.0	839.3	839.9
142.5°	858.3	858.9	859.6	860.2	860.8	861.2	861.4	861.7	861.9	862.1	862.5
145°	892.2	892.8	893.3	893.8	894.3	894.6	894.6	894.6	894.6	894.6	894.8
147.5°	919.3	920.3	921.2	922.2	923.2	923.6	923.4	923.2	923.0	922.9	923.0
150°	938.9	939.6	940.3	941.0	941.6	941.9	941.7	941.6	941.4	941.2	941.2
152.5°	955.2	955.8	956.3	956.9	957.6	957.7	957.4	957.0	956.6	956.3	956.6
155°	978.4	978.5	978.7	978.9	979.1	978.9	978.4	977.8	977.2	976.7	977.4
157.5°	997.7	997.6	997.5	997.4	997.3	996.9	996.3	995.8	995.2	994.6	995.5
160°	1009.2	1008.6	1008.0	1007.5	1007.0	1006.6	1006.5	1006.3	1006.1	1005.9	1007.0
162.5°	1019.3	1018.5	1017.8	1017.2	1016.5	1016.1	1015.9	1015.8	1015.6	1015.4	1016.5
165°	1032.0	1031.2	1030.3	1029.4	1028.5	1028.0	1028.0	1028.0	1028.0	1028.0	1029.5
167.5°	1042.1	1041.2	1040.3	1039.4	1038.4	1037.9	1037.8	1037.7	1037.6	1037.5	1039.1
170°	1047.8	1046.7	1045.7	1044.6	1043.6	1043.2	1043.3	1043.5	1043.7	1043.9	1045.2
172.5°	1051.6	1050.6	1049.5	1048.4	1047.4	1046.9	1047.1	1047.3	1047.4	1047.6	1049.0
175°	1055.7	1054.6	1053.6	1052.6	1051.5	1051.1	1051.3	1051.4	1051.6	1051.8	1053.3
177.5°	1057.6	1056.6	1055.6	1054.6	1053.7	1053.3	1053.6	1053.9	1054.2	1054.4	1055.5
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7



TEST NUMBER: P332970-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5	1823.5
2.5°	1816.6	1819.4	1822.1	1823.4	1823.1	1822.9	1822.6	1822.4
5°	1804.5	1807.7	1810.8	1812.0	1811.4	1810.8	1810.2	1809.6
7.5°	1780.6	1782.5	1784.5	1785.0	1784.0	1783.0	1782.0	1781.0
10°	1759.0	1760.2	1761.4	1761.4	1760.2	1759.0	1757.7	1756.5
12.5°	1732.2	1733.0	1733.7	1733.2	1731.5	1729.8	1728.1	1726.4
15°	1685.5	1684.8	1684.2	1682.7	1680.6	1678.4	1676.3	1674.1
17.5°	1629.0	1627.3	1625.6	1623.1	1619.7	1616.5	1613.2	1609.8
20°	1589.5	1587.1	1584.6	1581.3	1577.3	1573.3	1569.2	1565.2
22.5°	1545.7	1542.0	1538.3	1534.8	1531.5	1528.2	1524.9	1521.7
25°	1475.0	1469.8	1464.5	1460.3	1457.2	1454.1	1451.0	1447.9
27.5°	1403.0	1396.5	1390.0	1384.5	1380.1	1375.5	1371.1	1366.7
30°	1351.4	1343.6	1335.8	1329.5	1324.5	1319.6	1314.6	1309.7
32.5°	1298.7	1289.7	1280.7	1273.8	1269.1	1264.4	1259.7	1255.0
35°	1220.1	1209.6	1199.0	1191.0	1185.4	1179.8	1174.3	1168.6
37.5°	1135.9	1124.1	1112.3	1103.6	1098.0	1092.4	1086.8	1081.3
40°	1079.7	1066.7	1053.7	1044.4	1038.8	1033.2	1027.6	1022.1
42.5°	1024.5	1011.3	997.9	988.5	982.6	976.7	970.9	965.1
45°	940.0	924.7	909.6	899.2	893.6	888.0	882.4	876.9
47.5°	854.9	839.1	823.2	812.3	806.2	800.0	793.9	787.8
50°	798.3	782.8	767.3	756.6	750.7	744.8	738.9	733.1
52.5°	741.9	726.2	710.4	699.5	693.4	687.2	681.1	675.0
55°	658.8	642.8	626.6	615.6	609.7	603.8	597.9	592.0
57.5°	577.6	561.3	544.9	534.5	530.0	525.5	521.1	516.6
60°	523.4	507.3	491.2	480.6	475.6	470.7	465.7	460.8
62.5°	470.1	455.1	440.3	430.8	426.9	422.9	418.9	415.0
65°	393.5	380.2	366.9	358.4	354.7	350.9	347.2	343.5
67.5°	323.3	311.8	300.3	292.6	288.4	284.4	280.2	276.2
70°	275.5	265.3	255.1	248.3	245.3	242.2	239.0	236.0
72.5°	232.7	224.0	215.2	209.4	206.5	203.7	200.9	198.0
75°	171.5	164.3	157.1	152.7	150.8	149.0	147.0	145.2
77.5°	121.3	117.1	112.9	110.6	110.0	109.5	108.9	108.4
80°	93.1	92.2	91.2	90.6	90.3	90.0	89.7	89.4
82.5°	72.3	71.7	71.0	70.5	70.2	69.9	69.6	69.3
85°	42.0	41.4	40.8	40.5	40.5	40.5	40.5	40.5
87.5°	19.1	19.0	19.0	19.1	19.4	19.7	20.1	20.4
90°	19.5	20.5	21.6	22.3	22.6	23.0	23.3	23.7
92.5°	18.9	19.9	20.9	21.5	21.6	21.6	21.7	21.8
95°	19.5	20.5	21.6	22.2	22.4	22.5	22.7	22.9
97.5°	21.1	21.2	21.3	21.4	21.6	21.7	21.9	22.1
100°	28.8	25.8	22.8	21.4	21.6	21.7	21.9	22.1
102.5°	103.0	70.9	38.7	22.6	22.6	22.6	22.7	22.7
105°	249.5	251.1	252.7	250.3	244.0	237.6	231.4	225.0
107.5°	308.7	309.4	310.2	310.9	311.6	312.3	313.0	313.7
110°	348.9	349.3	349.6	350.0	350.6	351.1	351.6	352.1





TEST NUMBER: P332970-840

CATALOG NUMBER: S124RDIP-S1020D810U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	387.9	387.8	387.7	388.0	388.7	389.4	390.0	390.7
115°	446.1	446.4	446.8	447.0	447.0	447.0	447.0	447.0
117.5°	504.5	504.5	504.4	504.3	504.3	504.2	504.1	504.1
120°	540.8	541.2	541.5	541.5	541.2	540.8	540.5	540.1
122.5°	576.5	576.7	576.9	576.8	576.5	576.1	575.8	575.4
125°	626.4	626.9	627.4	627.8	628.0	628.1	628.3	628.5
127.5°	676.0	675.9	675.8	675.7	675.5	675.4	675.3	675.1
130°	706.3	706.4	706.6	706.7	706.7	706.7	706.7	706.7
132.5°	736.0	736.1	736.3	736.3	736.2	736.0	735.9	735.8
135°	776.9	777.2	777.6	777.9	778.3	778.6	779.0	779.3
137.5°	816.1	816.5	816.9	817.0	816.9	816.8	816.7	816.6
140°	840.4	840.9	841.4	841.8	842.0	842.1	842.3	842.5
142.5°	862.8	863.2	863.6	863.8	863.8	863.9	863.9	863.9
145°	894.9	895.1	895.3	895.5	896.0	896.3	896.7	897.0
147.5°	923.2	923.3	923.4	923.6	923.8	923.9	924.1	924.3
150°	941.2	941.2	941.2	941.3	941.5	941.6	941.8	942.0
152.5°	956.9	957.3	957.5	957.6	957.5	957.4	957.3	957.2
155°	978.2	978.9	979.6	979.7	979.1	978.6	978.1	977.5
157.5°	996.4	997.3	998.3	998.3	997.3	996.4	995.5	994.6
160°	1008.0	1009.2	1010.2	1010.2	1009.2	1008.0	1007.0	1005.9
162.5°	1017.5	1018.5	1019.7	1019.6	1018.3	1017.1	1016.0	1014.8
165°	1030.9	1032.3	1033.7	1033.6	1032.0	1030.5	1028.9	1027.2
167.5°	1040.7	1042.2	1043.7	1043.6	1041.9	1040.1	1038.3	1036.6
170°	1046.6	1048.0	1049.5	1049.2	1047.5	1045.8	1044.0	1042.3
172.5°	1050.5	1051.9	1053.3	1053.0	1051.2	1049.2	1047.3	1045.4
175°	1054.9	1056.5	1058.0	1057.8	1055.7	1053.6	1051.5	1049.4
177.5°	1056.7	1057.8	1058.9	1058.6	1056.9	1055.3	1053.6	1051.9
180°	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7	1055.7

(END OF REPORT)