

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332988-840

Luminaire Tested: **S124RDIP-S1195D365U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332988-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S1195D365U840-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6343.2 lumens  
Efficiency: N/A  
Efficacy: 127.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332988-840

CATALOG NUMBER: S124RDIP-S1195D365U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332988-840

CATALOG NUMBER: S124RDIP-S1195D365U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77				
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69	66				
2	95	88	82	76	91	84	78	74	77	72	68	70	67	63	64	61	59	56				
3	87	78	70	64	83	74	67	62	68	63	58	62	58	54	57	53	50	47				
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	51	47	44	41				
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	46	42	38	36				
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	42	38	34	32				
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	30	28				
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	36	31	27	25				
9	55	42	35	29	52	41	34	29	38	32	27	35	30	26	33	28	25	23				
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17002	17002	17002
5°	17040	16832	16936
10°	16934	16629	16629
15°	16739	16280	16160
20°	16472	15821	15530
25°	16131	15284	14895
30°	15800	14716	14100
35°	15431	14128	13302
40°	14989	13460	12440
45°	14582	12795	11562
50°	14117	12031	10633
55°	13619	11234	9623
60°	13070	10362	8591
65°	12567	9270	7578
70°	11837	8068	6434
75°	10914	6691	5231
80°	9521	5100	4798
85°	8068	4631	4335



TEST NUMBER: P332988-840

CATALOG NUMBER: S124RDIP-S1195D365U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	197.8	3.1
10°-20°	551.7	8.7
20°-30°	796.6	12.6
30°-40°	903.0	14.2
40°-50°	872.0	13.7
50°-60°	725.1	11.4
60°-70°	500.7	7.9
70°-80°	253.8	4.0
80°-90°	66.5	1.0
90°-100°	16.3	0.3
100°-110°	104.1	1.6
110°-120°	199.1	3.1
120°-130°	252.7	4.0
130°-140°	270.4	4.3
140°-150°	252.8	4.0
150°-160°	203.9	3.2
160°-170°	131.5	2.1
170°-180°	45.3	0.7
0°-30°	1546.1	24.4
0°-40°	2449.1	38.6
0°-60°	4046.2	63.8
0°-90°	4867.2	76.7
90°-120°	319.5	5.0
90°-150°	1095.3	17.3
90°-180°	1476.0	23.3
0°-180°	6343.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2106	2106	2106	2106	2106	
5°	2103	2096	2077	2092	2090	199
15°	2003	1987	1948	1944	1934	564
25°	1811	1780	1716	1689	1672	834
35°	1566	1513	1434	1380	1350	978
45°	1277	1215	1121	1044	1013	984
55°	968	901	798	717	684	865
65°	658	587	485	419	397	649
75°	350	289	214	179	168	369
85°	87	56	50	47	47	98
90°	1	5	8	10	11	5
95°	20	8	8	10	10	25
105°	107	110	111	114	102	112
115°	201	202	201	202	202	197
125°	282	283	283	284	284	252
135°	350	349	351	352	352	269
145°	403	404	404	405	406	252
155°	442	442	442	443	442	204
165°	466	465	465	467	464	132
175°	477	475	475	478	474	45
180°	477	477	477	477	477	



TEST NUMBER: P332988-840

CATALOG NUMBER: S124RDIP-S1195D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2111.1	2110.0	2108.9	2107.7	2106.6	2104.5	2101.3	2098.1	2095.0	2091.8	2095.0
5°	2102.7	2101.3	2099.9	2098.5	2097.1	2094.2	2089.9	2085.6	2081.3	2077.0	2080.5
7.5°	2083.8	2082.2	2080.7	2079.2	2077.7	2074.2	2068.6	2063.1	2057.4	2051.8	2054.2
10°	2065.7	2063.9	2062.1	2060.3	2058.5	2054.4	2048.0	2041.5	2035.1	2028.6	2030.0
12.5°	2042.5	2040.4	2038.3	2036.2	2034.2	2029.3	2021.7	2014.2	2006.5	1998.9	1999.8
15°	2002.8	1999.5	1996.4	1993.2	1989.9	1983.8	1974.9	1965.9	1956.9	1947.9	1947.2
17.5°	1954.8	1950.0	1945.4	1940.8	1936.1	1928.4	1917.6	1906.9	1896.1	1885.4	1883.4
20°	1917.3	1912.7	1908.0	1903.4	1898.7	1890.3	1878.1	1865.9	1853.7	1841.6	1838.7
22.5°	1876.0	1870.9	1865.6	1860.4	1855.1	1846.0	1832.9	1819.9	1806.9	1793.8	1789.5
25°	1810.9	1804.4	1798.0	1791.6	1785.1	1774.5	1759.9	1745.1	1730.5	1715.8	1709.7
27.5°	1742.5	1734.4	1726.4	1718.3	1710.1	1698.3	1682.5	1666.9	1651.1	1635.5	1627.9
30°	1694.9	1685.9	1676.9	1667.9	1659.0	1646.1	1629.2	1612.4	1595.6	1578.7	1569.7
32.5°	1644.5	1634.4	1624.3	1614.2	1604.1	1590.3	1572.9	1555.5	1538.0	1520.7	1510.3
35°	1565.8	1554.3	1542.9	1531.4	1519.9	1505.2	1487.3	1469.5	1451.5	1433.6	1421.4
37.5°	1481.7	1469.8	1457.9	1446.1	1434.3	1418.5	1398.7	1378.8	1359.0	1339.1	1325.4
40°	1422.3	1410.5	1398.7	1386.8	1374.9	1358.9	1338.5	1318.0	1297.6	1277.2	1262.1
42.5°	1365.5	1353.1	1340.7	1328.3	1316.0	1299.1	1277.8	1256.5	1235.3	1214.0	1198.6
45°	1277.2	1263.8	1250.6	1237.4	1224.2	1206.7	1185.3	1163.8	1142.3	1120.7	1103.2
47.5°	1185.9	1172.2	1158.5	1144.8	1131.1	1113.1	1090.8	1068.3	1046.0	1023.7	1005.4
50°	1124.0	1109.9	1096.0	1082.1	1068.0	1049.6	1026.6	1003.7	980.8	957.9	940.0
52.5°	1060.8	1047.0	1033.4	1019.7	1006.0	987.3	963.9	940.4	916.9	893.3	875.1
55°	967.6	953.2	938.9	924.5	910.2	891.4	868.1	844.9	821.5	798.2	779.6
57.5°	875.3	860.4	845.5	830.6	815.7	796.8	773.9	750.8	727.9	705.0	686.1
60°	809.5	795.2	780.8	766.5	752.1	733.6	710.6	687.7	664.7	641.8	623.2
62.5°	750.1	735.3	720.3	705.5	690.5	671.4	647.8	624.3	600.8	577.3	560.1
65°	657.9	642.5	627.1	611.7	596.3	577.1	554.2	531.3	508.4	485.3	470.0
67.5°	562.1	547.3	532.6	517.9	503.1	485.0	463.7	442.5	421.2	399.9	386.7
70°	501.5	486.5	471.4	456.4	441.3	423.5	403.1	382.7	362.3	341.8	330.0
72.5°	437.0	423.4	409.8	396.2	382.5	366.1	346.8	327.5	308.2	288.9	278.8
75°	349.9	336.7	323.4	310.1	296.9	281.9	265.0	248.1	231.4	214.5	206.2
77.5°	261.6	250.3	239.0	227.8	216.5	204.1	190.5	176.9	163.3	149.7	144.8
80°	204.8	194.4	184.0	173.6	163.2	152.7	141.9	131.2	120.4	109.7	108.6
82.5°	155.8	146.2	136.7	127.1	117.6	109.8	103.6	97.5	91.3	85.1	84.3
85°	87.1	79.9	72.7	65.5	58.4	54.3	53.2	52.1	51.1	50.0	49.3
87.5°	29.9	27.8	25.7	23.5	21.4	20.3	20.1	20.0	19.8	19.6	19.4
90°	1.1	1.9	2.8	3.7	4.5	5.4	6.0	6.6	7.2	7.9	8.3
92.5°	4.5	4.5	4.5	4.6	4.6	5.0	5.7	6.3	7.0	7.6	8.1
95°	19.6	17.0	14.2	11.5	8.9	7.6	7.6	7.7	7.8	7.9	8.3
97.5°	41.7	43.3	45.0	46.8	48.4	44.8	36.0	27.2	18.3	9.4	9.5
100°	58.6	60.0	61.4	62.8	64.2	59.5	48.6	37.6	26.7	15.8	14.3
102.5°	77.4	78.5	79.5	80.5	81.6	81.4	80.0	78.6	77.1	75.6	61.1
105°	107.4	107.9	108.4	108.9	109.4	109.8	110.2	110.6	111.0	111.4	112.1
107.5°	135.3	135.5	135.8	136.0	136.3	136.6	137.2	137.7	138.3	138.9	139.2
110°	154.2	154.4	154.6	154.9	155.1	155.5	155.9	156.4	156.9	157.4	157.5



TEST NUMBER: P332988-840

CATALOG NUMBER: S124RDIP-S1195D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.5	172.9	173.3	173.7	174.2	174.5	174.7	174.9	175.1	175.4	175.3
115°	200.6	200.9	201.1	201.3	201.6	201.6	201.6	201.5	201.4	201.3	201.5
117.5°	225.9	226.2	226.5	226.9	227.2	227.4	227.6	227.8	227.9	228.1	228.1
120°	243.1	243.4	243.7	244.0	244.3	244.4	244.4	244.3	244.2	244.1	244.3
122.5°	259.0	259.2	259.4	259.6	259.8	259.9	260.0	260.1	260.2	260.4	260.4
125°	282.0	282.3	282.6	282.9	283.3	283.3	283.2	283.0	282.9	282.7	282.9
127.5°	303.7	303.8	303.8	303.9	304.0	304.2	304.6	304.9	305.3	305.7	305.6
130°	317.6	317.7	317.8	317.9	318.0	318.1	318.3	318.6	318.8	319.1	319.1
132.5°	330.5	330.6	330.7	330.9	331.0	331.2	331.5	331.8	332.1	332.4	332.5
135°	349.7	349.7	349.6	349.5	349.4	349.5	349.9	350.2	350.5	350.8	351.0
137.5°	366.8	366.9	366.9	366.9	367.0	367.2	367.5	367.8	368.2	368.5	368.7
140°	378.0	378.1	378.3	378.4	378.6	378.7	378.9	379.1	379.2	379.4	379.6
142.5°	388.0	388.2	388.5	388.8	389.1	389.3	389.4	389.5	389.6	389.7	389.8
145°	403.3	403.5	403.7	404.0	404.2	404.3	404.3	404.3	404.3	404.3	404.5
147.5°	415.5	416.0	416.4	416.9	417.3	417.5	417.4	417.3	417.2	417.2	417.2
150°	424.3	424.6	425.0	425.4	425.7	425.8	425.7	425.6	425.5	425.5	425.5
152.5°	431.8	432.0	432.3	432.5	432.8	432.8	432.7	432.5	432.4	432.3	432.4
155°	442.2	442.3	442.3	442.4	442.5	442.4	442.2	441.9	441.7	441.5	441.8
157.5°	451.0	450.9	450.9	450.8	450.8	450.6	450.4	450.1	449.8	449.6	450.0
160°	456.2	455.9	455.7	455.4	455.1	455.0	454.9	454.8	454.7	454.6	455.1
162.5°	460.7	460.4	460.1	459.8	459.5	459.3	459.2	459.1	459.1	459.0	459.5
165°	466.5	466.1	465.6	465.2	464.8	464.6	464.6	464.6	464.6	464.6	465.3
167.5°	471.0	470.6	470.2	469.8	469.4	469.2	469.1	469.1	469.0	469.0	469.7
170°	473.6	473.1	472.6	472.2	471.7	471.5	471.6	471.7	471.7	471.8	472.4
172.5°	475.3	474.8	474.3	473.9	473.4	473.2	473.3	473.4	473.4	473.5	474.1
175°	477.2	476.7	476.3	475.7	475.2	475.0	475.1	475.2	475.3	475.3	476.2
177.5°	478.1	477.6	477.2	476.7	476.3	476.1	476.3	476.4	476.5	476.6	477.2
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P332988-840

CATALOG NUMBER: S124RDIP-S1195D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0	2106.0
2.5°	2098.1	2101.3	2104.5	2105.9	2105.6	2105.3	2105.0	2104.8
5°	2084.2	2087.7	2091.3	2092.7	2092.0	2091.3	2090.6	2089.9
7.5°	2056.4	2058.7	2061.0	2061.5	2060.4	2059.3	2058.1	2057.0
10°	2031.4	2032.9	2034.4	2034.4	2032.9	2031.4	2030.0	2028.6
12.5°	2000.6	2001.6	2002.4	2001.8	1999.8	1997.8	1995.8	1993.8
15°	1946.5	1945.8	1945.1	1943.5	1941.0	1938.4	1936.0	1933.5
17.5°	1881.4	1879.4	1877.3	1874.5	1870.7	1866.8	1863.1	1859.3
20°	1835.8	1832.9	1830.1	1826.3	1821.7	1817.1	1812.3	1807.7
22.5°	1785.2	1780.9	1776.7	1772.6	1768.8	1764.9	1761.2	1757.4
25°	1703.5	1697.5	1691.4	1686.6	1682.9	1679.4	1675.8	1672.2
27.5°	1620.4	1612.9	1605.4	1599.0	1593.9	1588.7	1583.6	1578.4
30°	1560.7	1551.9	1542.9	1535.5	1529.7	1524.1	1518.3	1512.6
32.5°	1499.9	1489.4	1479.0	1471.2	1465.7	1460.3	1454.8	1449.4
35°	1409.2	1397.0	1384.8	1375.5	1369.1	1362.6	1356.1	1349.7
37.5°	1311.8	1298.2	1284.6	1274.6	1268.1	1261.6	1255.3	1248.8
40°	1247.1	1232.0	1217.0	1206.2	1199.7	1193.3	1186.9	1180.4
42.5°	1183.3	1167.9	1152.6	1141.6	1134.8	1128.1	1121.4	1114.6
45°	1085.6	1068.0	1050.5	1038.4	1032.1	1025.6	1019.2	1012.7
47.5°	987.2	969.1	950.9	938.2	931.1	924.0	916.9	909.8
50°	922.0	904.1	886.2	873.8	867.1	860.2	853.4	846.6
52.5°	857.0	838.8	820.5	807.9	800.8	793.8	786.6	779.5
55°	760.9	742.4	723.7	710.9	704.2	697.3	690.5	683.7
57.5°	667.2	648.2	629.3	617.3	612.2	606.9	601.8	596.6
60°	604.5	585.9	567.2	555.1	549.4	543.6	537.9	532.1
62.5°	542.9	525.7	508.5	497.6	493.0	488.5	483.8	479.3
65°	454.5	439.2	423.7	413.8	409.6	405.3	401.0	396.7
67.5°	373.4	360.1	346.9	337.9	333.2	328.4	323.7	318.9
70°	318.2	306.4	294.6	286.9	283.3	279.7	276.1	272.6
72.5°	268.7	258.6	248.5	241.9	238.5	235.3	232.0	228.6
75°	198.0	189.8	181.5	176.3	174.2	172.0	169.9	167.7
77.5°	140.1	135.2	130.5	127.7	127.0	126.4	125.8	125.1
80°	107.6	106.4	105.3	104.6	104.3	103.9	103.6	103.2
82.5°	83.6	82.8	82.0	81.4	81.1	80.7	80.4	80.0
85°	48.6	47.9	47.2	46.8	46.8	46.8	46.8	46.8
87.5°	19.3	19.1	18.9	18.9	19.3	19.6	19.9	20.2
90°	8.8	9.3	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	8.5	9.0	9.5	9.7	9.8	9.8	9.8	9.9
95°	8.8	9.3	9.8	10.0	10.1	10.2	10.3	10.3
97.5°	9.5	9.6	9.6	9.7	9.8	9.8	9.9	10.0
100°	13.0	11.6	10.3	9.7	9.8	9.8	9.9	10.0
102.5°	46.6	32.0	17.5	10.2	10.2	10.2	10.3	10.3
105°	112.8	113.5	114.2	113.1	110.3	107.4	104.5	101.7
107.5°	139.6	139.9	140.3	140.6	140.9	141.2	141.5	141.8
110°	157.7	157.8	158.0	158.2	158.4	158.8	159.0	159.2





TEST NUMBER: P332988-840

CATALOG NUMBER: S124RDIP-S1195D365U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	175.3	175.3	175.2	175.4	175.7	176.0	176.3	176.6
115°	201.6	201.8	202.0	202.0	202.0	202.0	202.0	202.0
117.5°	228.0	228.0	228.0	227.9	227.9	227.9	227.9	227.8
120°	244.4	244.6	244.8	244.8	244.6	244.4	244.3	244.1
122.5°	260.5	260.6	260.7	260.7	260.5	260.4	260.2	260.1
125°	283.2	283.4	283.6	283.8	283.9	284.0	284.0	284.1
127.5°	305.6	305.5	305.5	305.4	305.4	305.3	305.2	305.2
130°	319.2	319.3	319.4	319.4	319.4	319.4	319.4	319.4
132.5°	332.6	332.8	332.9	332.9	332.8	332.6	332.6	332.5
135°	351.1	351.3	351.4	351.6	351.7	351.9	352.1	352.2
137.5°	368.9	369.1	369.2	369.3	369.2	369.2	369.1	369.1
140°	379.8	380.1	380.3	380.5	380.6	380.6	380.7	380.8
142.5°	390.0	390.2	390.3	390.4	390.5	390.5	390.5	390.5
145°	404.6	404.7	404.7	404.8	405.0	405.2	405.3	405.5
147.5°	417.3	417.4	417.4	417.5	417.6	417.6	417.7	417.8
150°	425.5	425.5	425.5	425.5	425.6	425.7	425.7	425.8
152.5°	432.5	432.6	432.8	432.8	432.7	432.7	432.7	432.6
155°	442.1	442.4	442.7	442.8	442.5	442.3	442.1	441.8
157.5°	450.4	450.8	451.2	451.2	450.8	450.4	450.0	449.6
160°	455.7	456.2	456.6	456.6	456.2	455.7	455.1	454.6
162.5°	459.9	460.4	460.9	460.8	460.3	459.8	459.2	458.7
165°	466.0	466.6	467.3	467.2	466.5	465.7	465.0	464.3
167.5°	470.4	471.1	471.7	471.7	470.9	470.1	469.3	468.6
170°	473.1	473.7	474.3	474.2	473.5	472.7	471.9	471.1
172.5°	474.8	475.4	476.1	475.9	475.1	474.2	473.4	472.5
175°	476.9	477.6	478.3	478.2	477.2	476.3	475.2	474.3
177.5°	477.7	478.2	478.7	478.5	477.8	477.0	476.3	475.4
180°	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2

(END OF REPORT)