

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333267-930

Luminaire Tested: **S125DIP-S1090D590U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333267-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D590U930-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5351.3 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333267-930
CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333267-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68		
1	102	97	93	90	96	92	88	85	82	79	77	72	70	69	64	62	61	57		
2	93	85	78	73	87	80	75	70	72	67	63	64	60	57	56	54	51	48		
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	50	46	44	40		
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	44	41	38	34		
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30		
6	66	53	45	39	62	50	43	37	45	39	34	41	36	32	36	32	29	26		
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23		
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	31	26	23	21		
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19		
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8985	8985	8985
5°	9005	8919	8976
10°	8950	8857	8907
15°	8852	8750	8787
20°	8715	8601	8616
25°	8565	8424	8416
30°	8380	8232	8192
35°	8183	8027	7914
40°	7981	7804	7692
45°	7761	7600	7448
50°	7519	7354	7133
55°	7287	7076	6877
60°	7009	6795	6554
65°	6677	6460	6240
70°	6360	6069	5861
75°	5794	5602	5410
80°	5159	5077	4950
85°	4483	4565	4320



TEST NUMBER: P333267-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.2	2.5
10°-20°	370.5	6.9
20°-30°	547.1	10.2
30°-40°	638.4	11.9
40°-50°	641.2	12.0
50°-60°	562.8	10.5
60°-70°	419.4	7.8
70°-80°	239.8	4.5
80°-90°	71.0	1.3
90°-100°	167.2	3.1
100°-110°	359.4	6.7
110°-120°	337.3	6.3
120°-130°	273.4	5.1
130°-140°	219.4	4.1
140°-150°	165.6	3.1
150°-160°	116.5	2.2
160°-170°	68.7	1.3
170°-180°	22.3	0.4
0°-30°	1048.8	19.6
0°-40°	1687.2	31.5
0°-60°	2891.2	54.0
0°-90°	3621.4	67.7
90°-120°	864.0	16.1
90°-150°	1522.3	28.4
90°-180°	1730.0	32.3
0°-180°	5351.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1391	1391	1391	1391	1391	
5°	1389	1386	1376	1385	1385	132
15°	1324	1320	1309	1314	1314	373
25°	1202	1196	1182	1184	1181	553
35°	1038	1033	1018	1012	1004	649
45°	850	845	832	819	816	655
55°	647	643	628	619	611	578
65°	437	434	423	413	408	433
75°	232	230	224	221	217	248
85°	60	62	62	60	58	68
90°	0	4	7	10	11	4
95°	15	45	412	187	109	16
105°	53	73	337	664	616	55
115°	94	113	271	583	686	92
125°	130	153	260	464	541	115
135°	152	183	258	389	449	118
145°	178	203	259	322	354	111
155°	203	218	252	285	297	93
165°	221	227	242	256	260	62
175°	230	230	232	235	234	22
180°	231	231	231	231	231	



TEST NUMBER: P333267-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1394.7	1394.2	1393.5	1392.9	1392.4	1391.1	1389.1	1387.2	1385.2	1383.2	1385.2
5°	1389.0	1388.5	1388.0	1387.6	1387.1	1385.6	1383.2	1380.7	1378.3	1375.8	1378.0
7.5°	1376.2	1375.7	1375.2	1374.8	1374.3	1372.6	1369.9	1367.3	1364.6	1361.9	1364.1
10°	1364.8	1364.3	1363.8	1363.3	1362.9	1361.2	1358.5	1355.8	1353.2	1350.5	1352.4
12.5°	1350.7	1349.8	1348.9	1348.0	1347.2	1345.5	1343.0	1340.5	1338.0	1335.5	1337.1
15°	1324.0	1323.3	1322.6	1321.8	1321.1	1319.4	1316.7	1314.0	1311.3	1308.6	1309.9
17.5°	1293.5	1292.4	1291.3	1290.2	1289.2	1287.2	1284.4	1281.7	1278.9	1276.0	1277.6
20°	1268.0	1267.5	1267.0	1266.5	1266.0	1264.1	1260.9	1257.8	1254.6	1251.4	1253.1
22.5°	1242.4	1241.5	1240.6	1239.7	1238.8	1236.9	1234.0	1230.9	1228.0	1225.0	1226.1
25°	1201.9	1200.7	1199.5	1198.2	1197.0	1194.8	1191.6	1188.5	1185.3	1182.1	1182.6
27.5°	1154.5	1153.8	1153.1	1152.3	1151.6	1149.7	1146.3	1143.0	1139.8	1136.5	1136.6
30°	1123.7	1123.0	1122.3	1121.5	1120.8	1118.6	1114.9	1111.3	1107.6	1103.9	1103.4
32.5°	1090.3	1089.2	1088.0	1086.9	1085.8	1083.6	1080.3	1077.0	1073.7	1070.5	1069.6
35°	1037.9	1036.9	1035.9	1034.9	1034.0	1031.8	1028.3	1024.9	1021.5	1018.1	1016.8
37.5°	983.5	982.3	981.0	979.8	978.6	976.4	973.1	970.0	966.7	963.5	961.6
40°	946.6	945.3	944.1	942.9	941.7	939.3	935.9	932.5	929.0	925.6	923.4
42.5°	906.9	905.9	904.9	903.8	902.8	900.6	897.2	893.7	890.3	886.9	884.8
45°	849.7	848.7	847.7	846.8	845.8	843.8	840.9	838.0	835.0	832.1	829.2
47.5°	788.1	788.1	788.1	788.2	788.2	786.5	783.0	779.4	775.9	772.4	769.4
50°	748.4	747.7	747.0	746.2	745.5	743.6	740.7	737.8	734.8	731.9	728.7
52.5°	707.9	707.4	706.9	706.3	705.8	703.9	700.8	697.7	694.6	691.4	688.6
55°	647.2	646.5	645.7	645.0	644.2	642.1	638.7	635.3	631.9	628.4	626.2
57.5°	583.1	582.7	582.4	582.0	581.6	579.9	577.0	574.1	571.3	568.3	565.5
60°	542.6	541.6	540.6	539.6	538.7	536.9	534.2	531.5	528.8	526.1	523.7
62.5°	500.3	499.5	498.8	498.0	497.3	495.7	493.3	491.1	488.8	486.5	483.8
65°	436.9	436.4	435.9	435.5	435.0	433.4	430.7	428.0	425.3	422.7	420.4
67.5°	375.5	374.5	373.5	372.4	371.5	369.9	367.9	365.9	363.9	361.9	360.0
70°	336.8	335.6	334.4	333.1	331.9	330.2	328.0	325.8	323.6	321.4	319.9
72.5°	294.6	293.7	292.9	292.0	291.2	290.1	288.7	287.2	285.8	284.4	282.7
75°	232.2	231.7	231.2	230.7	230.2	229.4	228.2	227.0	225.8	224.5	223.8
77.5°	174.8	174.6	174.4	174.2	174.0	173.6	172.8	172.2	171.5	170.8	170.4
80°	138.7	138.7	138.7	138.7	138.7	138.4	137.9	137.5	137.0	136.5	136.2
82.5°	107.0	106.6	106.2	105.8	105.4	105.2	105.1	105.0	104.8	104.8	104.4
85°	60.5	60.7	61.0	61.2	61.5	61.6	61.6	61.6	61.6	61.6	61.4
87.5°	23.9	24.0	24.1	24.3	24.5	24.6	24.5	24.5	24.4	24.4	24.5
90°	0.5	0.9	1.9	2.8	3.8	4.6	5.1	6.0	6.5	7.4	7.9
92.5°	5.7	6.8	10.8	16.6	24.5	38.2	63.5	106.2	152.4	149.9	121.4
95°	15.3	15.8	19.6	24.6	34.9	55.8	105.6	207.9	336.2	412.1	403.2
97.5°	25.5	26.0	28.6	33.8	43.0	58.0	91.0	165.9	300.3	440.0	510.2
100°	32.5	33.5	35.4	40.4	49.3	63.3	90.3	150.7	267.9	420.0	536.2
102.5°	40.4	40.9	42.4	47.9	56.0	69.5	93.6	144.4	243.3	384.6	520.6
105°	52.6	52.6	54.9	59.5	66.9	80.0	100.4	141.9	219.5	337.2	470.7
107.5°	64.5	65.4	67.6	71.4	79.2	90.9	110.7	146.1	209.5	304.5	419.7
110°	73.1	73.9	75.8	80.0	87.0	99.1	118.1	150.2	206.5	289.3	390.7



TEST NUMBER: P333267-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	81.6	82.5	84.0	88.2	95.1	106.9	125.2	155.4	206.5	280.4	369.1
115°	93.9	94.9	96.3	100.4	107.5	119.0	136.2	163.2	207.9	270.7	345.5
117.5°	105.1	106.5	108.0	112.2	120.1	131.3	147.7	172.2	210.9	266.0	331.5
120°	112.5	114.0	115.8	120.0	127.9	139.5	155.8	178.1	213.9	263.7	323.7
122.5°	120.3	121.4	122.9	127.0	135.7	147.3	163.6	184.8	216.5	261.9	317.0
125°	130.2	131.2	133.5	137.6	146.5	158.6	173.9	194.0	220.9	259.5	307.9
127.5°	137.9	139.3	142.4	147.7	157.0	169.1	183.8	202.3	225.8	258.4	299.5
130°	142.8	144.1	147.9	153.9	163.7	175.8	190.2	207.9	228.9	257.6	293.9
132.5°	146.5	148.3	152.7	159.6	169.7	181.7	196.2	212.7	232.2	257.6	289.4
135°	152.5	154.4	160.0	167.5	177.2	189.7	204.2	219.5	236.7	257.6	284.1
137.5°	160.2	161.6	166.8	174.2	183.8	196.7	209.9	224.5	240.9	258.2	279.4
140°	164.6	166.0	171.6	179.0	187.9	200.5	213.9	227.9	242.8	258.6	277.2
142.5°	169.8	170.9	176.1	183.5	192.0	203.8	216.5	229.8	243.9	258.9	275.3
145°	177.7	178.6	183.2	189.7	198.1	208.8	220.9	232.5	245.1	258.6	272.6
147.5°	185.8	186.4	190.4	196.4	203.7	213.1	223.7	234.2	245.6	257.4	269.6
150°	190.7	191.6	194.9	200.9	207.4	215.3	225.6	235.3	245.6	256.2	267.4
152.5°	195.9	196.4	199.3	204.6	210.8	217.9	227.4	236.0	245.2	254.8	264.8
155°	202.8	202.8	205.5	210.2	214.8	221.4	229.3	236.7	244.2	252.1	260.4
157.5°	208.9	208.8	211.1	215.1	219.2	224.0	230.9	237.2	243.0	249.2	256.3
160°	213.0	212.5	214.4	217.7	221.4	225.6	231.6	237.2	241.8	247.4	253.0
162.5°	216.4	215.9	217.8	220.6	223.6	227.1	232.4	236.8	240.8	245.2	250.1
165°	221.4	220.5	221.8	224.1	226.0	228.9	232.5	236.3	239.0	241.8	245.6
167.5°	224.7	224.3	225.1	226.4	227.7	229.4	232.5	235.1	236.4	238.6	241.2
170°	227.0	226.5	227.0	227.9	228.9	230.2	232.5	234.4	235.3	236.7	238.6
172.5°	228.4	227.6	228.0	229.0	229.6	230.2	232.2	233.7	233.8	234.5	235.9
175°	230.2	229.3	229.8	230.2	230.2	230.2	231.6	232.5	232.0	232.0	232.5
177.5°	231.1	230.3	230.3	230.6	230.3	230.3	231.1	231.4	230.6	230.6	231.1
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333267-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1387.2	1389.1	1391.1	1392.0	1391.8	1391.6	1391.4	1391.2
5°	1380.2	1382.4	1384.6	1385.6	1385.4	1385.1	1384.9	1384.6
7.5°	1366.2	1368.4	1370.5	1371.5	1371.3	1371.0	1370.8	1370.5
10°	1354.4	1356.3	1358.3	1359.2	1358.9	1358.7	1358.5	1358.2
12.5°	1338.6	1340.2	1341.7	1342.6	1342.5	1342.4	1342.4	1342.3
15°	1311.1	1312.3	1313.5	1314.2	1314.2	1314.2	1314.2	1314.2
17.5°	1279.1	1280.6	1282.1	1282.3	1281.1	1279.9	1278.6	1277.4
20°	1254.8	1256.5	1258.3	1258.5	1257.3	1256.1	1254.8	1253.6
22.5°	1227.3	1228.4	1229.5	1229.6	1228.8	1228.0	1227.2	1226.3
25°	1183.1	1183.6	1184.1	1183.9	1183.2	1182.4	1181.7	1181.0
27.5°	1136.7	1136.8	1136.9	1136.6	1135.9	1135.1	1134.4	1133.7
30°	1102.9	1102.4	1102.0	1101.4	1100.7	1099.9	1099.2	1098.5
32.5°	1068.7	1067.8	1067.0	1065.8	1064.5	1063.2	1061.8	1060.5
35°	1015.6	1014.4	1013.2	1011.6	1009.7	1007.7	1005.8	1003.8
37.5°	959.9	958.1	956.3	954.8	953.7	952.5	951.4	950.3
40°	921.2	919.0	916.8	915.3	914.6	913.9	913.1	912.4
42.5°	882.9	880.8	878.9	877.3	876.2	875.1	873.9	872.8
45°	826.2	823.3	820.4	818.5	817.7	817.0	816.3	815.5
47.5°	766.5	763.4	760.5	758.1	756.4	754.7	753.0	751.3
50°	725.5	722.4	719.2	716.7	715.0	713.3	711.6	709.9
52.5°	685.8	683.1	680.3	677.9	676.0	674.1	672.2	670.3
55°	624.0	621.8	619.6	617.7	616.0	614.2	612.5	610.8
57.5°	562.7	559.9	557.0	555.1	554.2	553.3	552.4	551.4
60°	521.2	518.8	516.3	514.2	512.5	510.8	509.1	507.4
62.5°	481.2	478.6	475.9	473.9	472.6	471.3	469.9	468.6
65°	418.2	416.0	413.8	412.2	411.2	410.3	409.3	408.3
67.5°	358.2	356.3	354.4	353.2	352.6	352.0	351.5	350.9
70°	318.5	317.0	315.5	314.3	313.3	312.3	311.4	310.4
72.5°	281.1	279.4	277.8	276.5	275.5	274.5	273.5	272.6
75°	223.1	222.3	221.6	220.7	219.7	218.7	217.8	216.8
77.5°	169.9	169.5	169.1	168.5	167.8	167.1	166.4	165.8
80°	136.0	135.7	135.5	135.1	134.6	134.1	133.6	133.1
82.5°	103.9	103.5	103.1	102.7	102.6	102.6	102.5	102.3
85°	61.1	60.9	60.7	60.3	59.8	59.3	58.8	58.3
87.5°	24.5	24.6	24.8	24.7	24.4	24.0	23.6	23.2
90°	8.4	8.8	9.3	10.2	10.2	10.2	10.7	10.7
92.5°	82.4	59.8	45.0	38.2	32.2	31.1	30.4	29.7
95°	334.4	263.7	206.5	167.5	134.4	120.4	116.8	109.3
97.5°	498.0	448.4	392.7	338.3	309.7	283.6	270.1	264.2
100°	572.0	549.3	501.3	453.0	420.9	387.4	370.2	362.7
102.5°	597.0	611.0	588.0	555.3	521.0	497.2	478.5	472.9
105°	582.3	646.0	666.4	661.3	646.5	631.1	621.8	616.2
107.5°	529.8	614.8	667.4	691.6	699.2	699.1	696.0	692.3
110°	491.1	579.5	645.1	684.6	705.5	714.4	717.6	717.6



TEST NUMBER: P333267-930

CATALOG NUMBER: S125DIP-S1090D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	460.6	544.5	610.8	657.5	688.0	703.2	711.3	714.6
115°	422.2	494.4	558.1	608.8	645.1	667.4	680.4	686.5
117.5°	397.5	459.7	514.5	561.1	597.4	620.4	633.3	637.1
120°	384.2	439.9	491.1	532.1	566.5	588.8	601.4	605.0
122.5°	374.1	425.8	471.4	509.7	540.4	560.8	573.4	576.7
125°	359.5	406.9	447.4	480.9	507.0	526.0	536.2	540.9
127.5°	344.6	388.9	426.6	458.0	481.6	498.5	508.1	510.2
130°	335.3	376.3	412.5	442.7	466.0	481.4	490.6	493.4
132.5°	326.0	364.4	397.3	426.4	449.6	465.0	473.5	476.7
135°	313.9	346.0	375.8	402.3	422.7	438.1	446.5	449.2
137.5°	303.7	329.6	354.4	376.9	395.2	409.2	416.9	420.0
140°	298.1	320.0	341.4	360.9	378.1	390.2	397.1	399.5
142.5°	293.3	311.8	330.2	347.2	361.7	371.9	378.5	380.5
145°	287.0	301.3	315.8	328.3	339.5	347.4	352.5	354.4
147.5°	281.0	292.7	303.8	313.2	322.1	328.4	331.4	332.2
150°	277.6	287.9	296.7	305.1	312.1	317.6	319.5	320.0
152.5°	273.9	283.1	291.1	297.7	303.5	307.9	309.8	310.3
155°	268.3	275.8	282.3	287.4	292.0	295.3	296.7	297.2
157.5°	262.8	268.9	273.9	277.9	281.5	284.2	285.5	285.4
160°	259.0	263.7	268.3	271.6	274.8	277.2	278.1	277.6
162.5°	254.9	259.3	263.1	266.0	268.6	270.5	270.7	270.6
165°	249.2	252.5	255.4	257.6	259.5	260.4	260.4	260.4
167.5°	243.9	246.1	248.2	249.8	250.8	251.6	251.2	251.1
170°	240.9	242.3	243.7	244.6	245.6	246.1	246.1	245.6
172.5°	237.6	239.0	239.9	240.5	240.8	241.6	240.8	240.4
175°	233.9	233.9	234.9	234.9	234.9	235.3	234.4	233.9
177.5°	231.4	231.8	231.8	231.8	231.4	231.8	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6

(END OF REPORT)