

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332886-840

Luminaire Tested: **S124RDIP-S350D1035U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332886-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S350D1035U840-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5615.5 lumens
Efficiency: N/A
Efficacy: 150.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332886-840

CATALOG NUMBER: S124RDIP-S350D1035U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332886-840

CATALOG NUMBER: S124RDIP-S350D1035U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	71	67	75	69	64	60	54	50	48	40	38	36	27	25	24	19
3	77	68	61	55	68	61	55	50	47	43	40	35	33	30	24	22	21	16
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	11
7	55	43	35	30	49	39	32	28	31	26	22	23	20	17	16	14	12	9
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5040	5040	5040
5°	5051	4989	5020
10°	5019	4930	4930
15°	4962	4826	4790
20°	4883	4689	4603
25°	4782	4530	4415
30°	4683	4363	4180
35°	4574	4188	3943
40°	4443	3990	3687
45°	4322	3793	3427
50°	4185	3567	3152
55°	4037	3330	2853
60°	3873	3073	2546
65°	3725	2749	2245
70°	3510	2391	1907
75°	3235	1984	1550
80°	2822	1511	1423
85°	2399	1371	1278



TEST NUMBER: P332886-840

CATALOG NUMBER: S124RDIP-S350D1035U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	1.0
10°-20°	163.5	2.9
20°-30°	236.1	4.2
30°-40°	267.7	4.8
40°-50°	258.5	4.6
50°-60°	214.9	3.8
60°-70°	148.4	2.6
70°-80°	75.2	1.3
80°-90°	23.2	0.4
90°-100°	46.1	0.8
100°-110°	293.9	5.2
110°-120°	562.3	10.0
120°-130°	713.8	12.7
130°-140°	763.7	13.6
140°-150°	714.1	12.7
150°-160°	575.9	10.3
160°-170°	371.4	6.6
170°-180°	128.0	2.3
0°-30°	458.3	8.2
0°-40°	726.0	12.9
0°-60°	1199.4	21.4
0°-90°	1446.2	25.8
90°-120°	902.3	16.1
90°-150°	3094.0	55.1
90°-180°	4169.0	74.2
0°-180°	5615.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	624	624	624	624	624	
5°	623	621	616	620	620	59
15°	594	589	577	576	573	167
25°	537	528	509	501	496	247
35°	464	448	425	409	400	290
45°	379	360	332	310	300	292
55°	287	267	237	213	203	256
65°	195	174	144	124	118	193
75°	104	86	64	53	50	110
85°	26	17	15	14	14	29
90°	3	14	22	28	30	4
95°	55	23	22	28	29	71
105°	304	309	315	321	287	317
115°	566	569	569	570	571	557
125°	796	800	798	801	802	711
135°	988	987	991	993	995	761
145°	1139	1142	1142	1143	1145	712
155°	1249	1250	1247	1251	1248	576
165°	1318	1313	1312	1320	1312	372
175°	1348	1342	1343	1351	1340	128
180°	1348	1348	1348	1348	1348	



TEST NUMBER: P332886-840

CATALOG NUMBER: S124RDIP-S350D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	625.8	625.4	625.1	624.8	624.4	623.8	622.9	622.0	621.0	620.1	621.0
5°	623.3	622.9	622.5	622.1	621.6	620.8	619.5	618.2	616.9	615.7	616.7
7.5°	617.6	617.2	616.8	616.3	615.9	614.8	613.2	611.5	609.9	608.2	608.8
10°	612.3	611.8	611.3	610.8	610.2	608.9	607.0	605.1	603.2	601.4	601.8
12.5°	605.4	604.8	604.2	603.6	603.0	601.6	599.3	597.0	594.8	592.5	592.8
15°	593.7	592.7	591.8	590.8	589.9	588.0	585.4	582.7	580.1	577.4	577.2
17.5°	579.5	578.0	576.6	575.3	573.9	571.6	568.5	565.2	562.1	558.9	558.3
20°	568.4	566.9	565.6	564.2	562.8	560.4	556.7	553.1	549.5	545.8	545.0
22.5°	556.1	554.5	553.0	551.5	549.9	547.1	543.3	539.5	535.6	531.7	530.5
25°	536.8	534.9	533.0	531.1	529.2	526.0	521.7	517.4	512.9	508.6	506.8
27.5°	516.5	514.1	511.7	509.4	507.0	503.4	498.8	494.1	489.5	484.8	482.5
30°	502.4	499.7	497.1	494.4	491.8	488.0	482.9	478.0	472.9	468.0	465.3
32.5°	487.5	484.4	481.5	478.5	475.4	471.4	466.3	461.1	456.0	450.8	447.7
35°	464.1	460.7	457.4	453.9	450.5	446.2	440.9	435.6	430.3	425.0	421.3
37.5°	439.2	435.7	432.2	428.7	425.2	420.5	414.5	408.7	402.8	397.0	392.9
40°	421.6	418.1	414.5	411.1	407.6	402.8	396.8	390.7	384.7	378.6	374.2
42.5°	404.8	401.1	397.4	393.7	390.1	385.1	378.8	372.4	366.2	359.8	355.3
45°	378.6	374.7	370.7	366.8	362.8	357.7	351.3	345.0	338.6	332.2	327.0
47.5°	351.5	347.5	343.5	339.3	335.3	329.9	323.4	316.7	310.0	303.5	298.0
50°	333.2	329.0	324.9	320.7	316.6	311.1	304.4	297.5	290.7	284.0	278.6
52.5°	314.5	310.3	306.3	302.3	298.2	292.7	285.7	278.7	271.8	264.8	259.4
55°	286.8	282.6	278.3	274.1	269.8	264.2	257.3	250.4	243.5	236.6	231.1
57.5°	259.4	255.0	250.6	246.2	241.8	236.2	229.3	222.6	215.8	208.9	203.4
60°	239.9	235.7	231.5	227.2	223.0	217.4	210.7	203.8	197.0	190.3	184.7
62.5°	222.4	217.9	213.5	209.1	204.7	199.0	192.1	185.1	178.1	171.2	166.0
65°	195.0	190.5	185.9	181.4	176.7	171.1	164.3	157.4	150.7	143.9	139.4
67.5°	166.6	162.3	157.8	153.5	149.2	143.8	137.4	131.2	124.8	118.6	114.6
70°	148.7	144.2	139.8	135.3	130.8	125.5	119.5	113.4	107.3	101.3	97.9
72.5°	129.6	125.5	121.5	117.4	113.4	108.6	102.8	97.0	91.4	85.6	82.7
75°	103.7	99.8	95.8	91.9	88.0	83.5	78.6	73.5	68.6	63.6	61.1
77.5°	77.6	74.2	70.9	67.6	64.2	60.5	56.5	52.4	48.4	44.3	42.9
80°	60.7	57.7	54.5	51.5	48.4	45.2	42.1	38.9	35.6	32.5	32.2
82.5°	46.2	43.3	40.5	37.7	34.8	32.5	30.7	28.9	27.1	25.2	25.0
85°	25.9	23.7	21.6	19.4	17.3	16.1	15.8	15.5	15.1	14.8	14.6
87.5°	9.4	9.2	9.0	8.9	8.7	8.7	9.0	9.3	9.5	9.8	10.0
90°	3.0	5.5	8.0	10.4	12.9	15.0	16.8	18.6	20.4	22.2	23.5
92.5°	12.7	12.8	12.9	13.1	13.2	14.2	16.0	17.8	19.6	21.4	22.7
95°	55.4	47.9	40.2	32.6	24.9	21.3	21.5	21.7	21.9	22.2	23.5
97.5°	117.8	122.5	127.2	132.0	136.7	126.6	101.6	76.6	51.6	26.7	26.8
100°	165.3	169.4	173.4	177.4	181.5	168.0	137.1	106.2	75.2	44.3	40.6
102.5°	218.5	221.6	224.5	227.4	230.4	229.8	225.8	221.8	217.7	213.7	172.6
105°	303.5	304.8	306.1	307.5	308.8	310.0	311.1	312.3	313.5	314.6	316.6
107.5°	382.2	382.9	383.6	384.3	385.0	386.1	387.6	389.1	390.6	392.1	393.1
110°	435.6	436.2	436.9	437.5	438.2	439.2	440.5	441.9	443.2	444.5	445.0



TEST NUMBER: P332886-840

CATALOG NUMBER: S124RDIP-S350D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.2	488.4	489.6	490.8	492.0	492.9	493.5	494.1	494.7	495.3	495.3
115°	566.5	567.2	567.9	568.6	569.3	569.5	569.3	569.1	568.8	568.6	569.1
117.5°	638.1	639.0	640.0	640.9	641.8	642.4	642.9	643.4	643.9	644.4	644.3
120°	686.5	687.4	688.3	689.2	690.1	690.4	690.2	690.0	689.7	689.5	690.0
122.5°	731.6	732.3	732.8	733.3	733.9	734.3	734.6	734.9	735.2	735.5	735.8
125°	796.4	797.3	798.2	799.1	800.0	800.2	799.8	799.3	798.9	798.4	799.1
127.5°	857.7	857.9	858.2	858.4	858.6	859.2	860.3	861.3	862.3	863.3	863.2
130°	897.3	897.5	897.7	897.9	898.1	898.6	899.3	899.9	900.6	901.3	901.5
132.5°	933.5	933.9	934.3	934.7	935.1	935.7	936.6	937.5	938.3	939.2	939.4
135°	988.0	987.7	987.5	987.2	987.0	987.3	988.3	989.2	990.1	991.0	991.4
137.5°	1036.1	1036.2	1036.3	1036.4	1036.5	1037.0	1038.0	1039.1	1040.0	1041.0	1041.5
140°	1067.6	1068.0	1068.5	1068.9	1069.3	1069.9	1070.3	1070.8	1071.2	1071.7	1072.3
142.5°	1095.8	1096.6	1097.4	1098.2	1099.0	1099.5	1099.8	1100.1	1100.3	1100.7	1101.2
145°	1139.1	1139.8	1140.5	1141.1	1141.9	1142.2	1142.2	1142.2	1142.2	1142.2	1142.5
147.5°	1173.7	1174.9	1176.2	1177.4	1178.7	1179.2	1178.9	1178.7	1178.5	1178.3	1178.5
150°	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5	1202.3	1202.1	1201.9	1201.6	1201.6
152.5°	1219.6	1220.3	1221.0	1221.7	1222.4	1222.6	1222.2	1221.8	1221.4	1221.0	1221.4
155°	1249.1	1249.3	1249.5	1249.7	1249.9	1249.7	1249.1	1248.4	1247.7	1247.1	1247.9
157.5°	1273.8	1273.7	1273.5	1273.4	1273.3	1272.8	1272.1	1271.3	1270.6	1269.8	1271.0
160°	1288.4	1287.7	1287.1	1286.4	1285.7	1285.3	1285.1	1284.8	1284.5	1284.3	1285.7
162.5°	1301.3	1300.4	1299.6	1298.7	1297.9	1297.4	1297.1	1296.9	1296.7	1296.5	1297.8
165°	1317.6	1316.5	1315.3	1314.2	1313.1	1312.5	1312.5	1312.5	1312.5	1312.5	1314.3
167.5°	1330.5	1329.4	1328.2	1327.1	1325.9	1325.2	1325.0	1324.9	1324.8	1324.6	1326.7
170°	1337.8	1336.5	1335.0	1333.7	1332.4	1331.8	1332.0	1332.3	1332.5	1332.7	1334.5
172.5°	1342.6	1341.3	1339.9	1338.6	1337.3	1336.7	1336.9	1337.2	1337.4	1337.6	1339.4
175°	1347.9	1346.6	1345.1	1343.8	1342.5	1341.9	1342.1	1342.4	1342.6	1342.8	1344.8
177.5°	1350.3	1349.0	1347.8	1346.6	1345.2	1344.8	1345.1	1345.5	1345.8	1346.3	1347.7
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9



TEST NUMBER: P332886-840

CATALOG NUMBER: S124RDIP-S350D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	624.3	624.3	624.3	624.3	624.3	624.3	624.3	624.3
2.5°	622.0	622.9	623.8	624.2	624.1	624.1	624.0	623.9
5°	617.8	618.8	620.0	620.4	620.2	620.0	619.7	619.5
7.5°	609.6	610.3	611.0	611.1	610.8	610.5	610.1	609.8
10°	602.2	602.6	603.0	603.0	602.6	602.2	601.8	601.4
12.5°	593.0	593.3	593.6	593.4	592.8	592.2	591.6	591.0
15°	577.0	576.8	576.5	576.1	575.3	574.6	573.9	573.1
17.5°	557.6	557.1	556.5	555.6	554.5	553.4	552.3	551.2
20°	544.2	543.3	542.5	541.4	540.0	538.6	537.2	535.8
22.5°	529.2	527.9	526.6	525.4	524.3	523.2	522.1	520.9
25°	504.9	503.2	501.4	500.0	498.9	497.8	496.8	495.6
27.5°	480.3	478.1	475.8	474.0	472.4	470.9	469.4	467.9
30°	462.6	460.0	457.4	455.1	453.4	451.8	450.1	448.4
32.5°	444.6	441.5	438.5	436.1	434.4	432.8	431.2	429.6
35°	417.7	414.1	410.5	407.8	405.9	403.9	402.0	400.1
37.5°	388.9	384.9	380.8	377.8	375.9	374.0	372.0	370.1
40°	369.6	365.2	360.7	357.6	355.7	353.8	351.8	349.9
42.5°	350.7	346.2	341.6	338.4	336.4	334.4	332.3	330.4
45°	321.8	316.6	311.3	307.8	305.9	304.0	302.1	300.2
47.5°	292.7	287.2	281.9	278.1	276.0	273.9	271.8	269.7
50°	273.3	268.0	262.7	259.0	257.0	255.0	253.0	251.0
52.5°	254.0	248.6	243.3	239.4	237.4	235.3	233.2	231.1
55°	225.6	220.0	214.5	210.8	208.7	206.7	204.7	202.7
57.5°	197.7	192.2	186.5	183.0	181.5	180.0	178.3	176.8
60°	179.2	173.7	168.1	164.5	162.8	161.2	159.5	157.7
62.5°	161.0	155.8	150.8	147.5	146.1	144.8	143.4	142.1
65°	134.7	130.2	125.6	122.7	121.4	120.2	118.9	117.5
67.5°	110.7	106.7	102.8	100.2	98.8	97.4	95.9	94.5
70°	94.3	90.8	87.4	85.0	83.9	82.9	81.8	80.8
72.5°	79.7	76.6	73.7	71.7	70.7	69.8	68.8	67.8
75°	58.7	56.2	53.8	52.3	51.6	51.0	50.4	49.7
77.5°	41.5	40.1	38.7	37.9	37.7	37.5	37.3	37.1
80°	31.9	31.5	31.2	31.0	30.9	30.8	30.7	30.6
82.5°	24.7	24.5	24.3	24.1	24.0	23.9	23.8	23.7
85°	14.4	14.1	13.9	13.8	13.8	13.8	13.8	13.8
87.5°	10.2	10.3	10.5	10.7	10.9	11.0	11.2	11.4
90°	24.8	26.3	27.6	28.5	28.9	29.4	29.8	30.2
92.5°	24.0	25.4	26.8	27.5	27.6	27.7	27.8	27.9
95°	24.8	26.3	27.6	28.4	28.6	28.8	29.0	29.2
97.5°	26.9	27.1	27.2	27.4	27.6	27.8	28.0	28.3
100°	36.8	32.9	29.1	27.4	27.6	27.8	28.0	28.3
102.5°	131.6	90.5	49.4	28.9	28.9	29.0	29.0	29.1
105°	318.6	320.5	322.6	319.6	311.5	303.5	295.4	287.3
107.5°	394.2	395.2	396.1	397.0	397.9	398.7	399.6	400.4
110°	445.5	446.0	446.4	447.0	447.6	448.3	449.0	449.6



TEST NUMBER: P332886-840

CATALOG NUMBER: S124RDIP-S350D1035U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	495.2	495.1	495.0	495.4	496.2	497.2	498.0	498.8
115°	569.5	570.0	570.4	570.6	570.6	570.6	570.6	570.6
117.5°	644.2	644.1	644.0	644.0	643.9	643.8	643.7	643.6
120°	690.4	690.8	691.4	691.4	690.8	690.4	690.0	689.5
122.5°	736.1	736.3	736.6	736.5	736.1	735.6	735.2	734.7
125°	799.8	800.4	801.1	801.5	801.8	802.0	802.2	802.4
127.5°	863.1	862.9	862.8	862.6	862.5	862.3	862.1	861.9
130°	901.7	901.9	902.1	902.3	902.3	902.3	902.3	902.3
132.5°	939.6	939.9	940.1	940.1	939.9	939.7	939.6	939.4
135°	991.9	992.3	992.8	993.2	993.7	994.1	994.5	995.0
137.5°	1042.0	1042.5	1043.0	1043.1	1043.0	1042.9	1042.7	1042.6
140°	1073.0	1073.7	1074.3	1074.8	1075.0	1075.2	1075.4	1075.7
142.5°	1101.7	1102.2	1102.7	1102.9	1103.0	1103.0	1103.1	1103.1
145°	1142.7	1142.9	1143.1	1143.5	1143.9	1144.3	1144.8	1145.2
147.5°	1178.6	1178.8	1179.0	1179.2	1179.4	1179.6	1179.9	1180.1
150°	1201.6	1201.6	1201.6	1201.7	1202.0	1202.2	1202.4	1202.6
152.5°	1221.7	1222.1	1222.4	1222.5	1222.4	1222.3	1222.1	1222.0
155°	1248.8	1249.7	1250.6	1250.7	1250.1	1249.4	1248.7	1248.1
157.5°	1272.1	1273.3	1274.4	1274.4	1273.3	1272.1	1271.0	1269.8
160°	1287.1	1288.4	1289.7	1289.7	1288.4	1287.1	1285.7	1284.3
162.5°	1299.1	1300.5	1301.8	1301.7	1300.2	1298.7	1297.2	1295.7
165°	1316.2	1318.0	1319.7	1319.6	1317.6	1315.6	1313.5	1311.5
167.5°	1328.6	1330.6	1332.5	1332.4	1330.2	1328.0	1325.6	1323.4
170°	1336.4	1338.1	1339.9	1339.7	1337.5	1335.2	1332.9	1330.7
172.5°	1341.2	1342.9	1344.7	1344.4	1342.0	1339.6	1337.2	1334.7
175°	1346.9	1348.9	1350.9	1350.5	1347.9	1345.1	1342.5	1339.8
177.5°	1349.1	1350.5	1352.0	1351.6	1349.5	1347.4	1345.1	1343.0
180°	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9	1347.9

(END OF REPORT)