

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332669-940

Luminaire Tested: **S124DIP-S1020D1205U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332669-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1020D1205U940-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7787.1 lumens  
Efficiency: N/A  
Efficacy: 119.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332669-940

CATALOG NUMBER: S124DIP-S1020D1205U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332669-940

CATALOG NUMBER: S124DIP-S1020D1205U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	31	25	46	36	29	24	31	25	21	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12421	12421	12421
5°	12459	12309	12399
10°	12381	12209	12269
15°	12232	12035	12066
20°	12032	11820	11832
25°	11805	11575	11541
30°	11527	11286	11182
35°	11239	10984	10838
40°	10940	10642	10446
45°	10628	10304	10106
50°	10282	10003	9693
55°	9909	9614	9301
60°	9536	9177	8898
65°	9116	8760	8407
70°	8641	8207	7886
75°	7923	7539	7346
80°	7053	6760	6592
85°	6169	5937	5826



TEST NUMBER: P332669-940

CATALOG NUMBER: S124DIP-S1020D1205U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.9	1.9
10°-20°	408.3	5.2
20°-30°	600.9	7.7
30°-40°	698.6	9.0
40°-50°	698.6	9.0
50°-60°	611.1	7.8
60°-70°	453.8	5.8
70°-80°	257.8	3.3
80°-90°	77.3	1.0
90°-100°	380.9	4.9
100°-110°	792.8	10.2
110°-120°	710.1	9.1
120°-130°	597.3	7.7
130°-140°	498.1	6.4
140°-150°	380.5	4.9
150°-160°	267.5	3.4
160°-170°	157.3	2.0
170°-180°	51.2	0.7
0°-30°	1154.1	14.8
0°-40°	1852.6	23.8
0°-60°	3162.3	40.6
0°-90°	3951.3	50.7
90°-120°	1883.9	24.2
90°-150°	3359.8	43.1
90°-180°	3836.0	49.3
0°-180°	7787.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1539	1539	1539	1539	1539	
5°	1537	1532	1519	1532	1530	146
15°	1464	1458	1440	1447	1444	412
25°	1325	1316	1300	1300	1296	609
35°	1140	1131	1114	1106	1100	713
45°	931	922	902	889	885	717
55°	704	700	683	669	661	630
65°	477	471	459	447	440	472
75°	254	248	242	237	236	270
85°	67	66	64	64	63	73
90°	1	8	19	21	22	5
95°	34	108	844	418	253	38
105°	121	176	680	1464	1458	129
115°	214	268	606	1165	1400	212
125°	297	353	603	991	1117	265
135°	353	421	598	880	999	273
145°	407	466	595	742	816	256
155°	463	500	578	655	683	213
165°	505	520	554	587	596	142
175°	526	527	532	539	537	50
180°	527	527	527	527	527	



TEST NUMBER: P332669-940

CATALOG NUMBER: S124DIP-S1020D1205U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1542.6	1541.9	1541.2	1540.6	1540.0	1538.4	1536.0	1533.6	1531.2	1528.7	1531.0
5°	1537.4	1536.3	1535.3	1534.1	1533.0	1531.0	1527.9	1524.9	1522.0	1518.9	1522.0
7.5°	1523.1	1522.0	1520.9	1519.8	1518.8	1516.5	1513.1	1509.8	1506.5	1503.2	1505.6
10°	1510.3	1509.2	1508.1	1507.0	1505.9	1503.6	1500.0	1496.5	1492.9	1489.3	1491.5
12.5°	1493.5	1492.5	1491.3	1490.2	1489.2	1486.7	1482.9	1479.2	1475.3	1471.6	1474.0
15°	1463.5	1462.3	1461.2	1460.2	1459.0	1456.4	1452.3	1448.2	1444.1	1440.0	1441.6
17.5°	1427.2	1425.8	1424.4	1423.1	1421.7	1419.1	1415.1	1411.3	1407.4	1403.6	1404.5
20°	1400.5	1399.2	1397.8	1396.4	1395.1	1392.3	1388.2	1384.1	1380.0	1375.9	1376.7
22.5°	1372.0	1370.1	1368.3	1366.5	1364.8	1361.7	1357.6	1353.5	1349.4	1345.3	1346.8
25°	1325.3	1323.5	1321.5	1319.6	1317.7	1314.8	1311.0	1307.2	1303.3	1299.5	1299.8
27.5°	1272.1	1270.2	1268.1	1266.1	1264.2	1261.4	1257.8	1254.3	1250.7	1247.1	1246.5
30°	1236.6	1234.4	1232.2	1230.0	1227.8	1224.9	1221.4	1217.8	1214.2	1210.7	1209.6
32.5°	1199.1	1197.1	1195.2	1193.2	1191.2	1188.3	1184.5	1180.8	1177.0	1173.2	1171.9
35°	1140.4	1138.5	1136.6	1134.7	1132.7	1129.9	1126.1	1122.2	1118.4	1114.5	1112.6
37.5°	1078.5	1076.7	1075.0	1073.3	1071.5	1068.6	1064.4	1060.3	1056.2	1052.1	1050.1
40°	1038.1	1035.9	1033.7	1031.5	1029.3	1026.2	1022.1	1018.0	1013.9	1009.8	1007.0
42.5°	994.7	993.4	992.0	990.8	989.4	986.5	982.0	977.4	972.9	968.3	965.1
45°	930.9	928.9	927.0	925.1	923.2	920.0	915.6	911.2	906.9	902.5	899.5
47.5°	864.0	862.7	861.4	860.1	858.7	856.0	852.0	847.9	843.9	839.8	836.4
50°	818.7	817.5	816.5	815.4	814.2	811.8	808.0	804.1	800.3	796.5	792.6
52.5°	774.3	772.9	771.6	770.3	769.0	766.3	762.2	758.2	754.1	750.1	746.7
55°	704.0	703.1	702.3	701.5	700.7	698.4	694.6	690.7	686.9	683.1	679.8
57.5°	636.9	636.0	635.1	634.1	633.2	630.8	627.1	623.3	619.5	615.7	612.6
60°	590.6	589.2	587.8	586.5	585.1	582.6	579.1	575.5	571.9	568.4	565.9
62.5°	545.2	544.0	542.9	541.7	540.6	538.1	534.3	530.6	526.7	523.0	520.8
65°	477.2	475.7	474.4	473.1	471.6	469.6	466.8	464.1	461.4	458.6	455.9
67.5°	408.6	407.3	406.1	404.8	403.5	401.6	399.0	396.4	393.7	391.1	388.4
70°	366.1	364.3	362.3	360.4	358.5	356.4	354.3	352.0	349.9	347.7	345.4
72.5°	320.8	318.9	317.0	315.0	313.2	311.3	309.5	307.8	306.0	304.3	302.6
75°	254.0	252.6	251.2	249.9	248.5	247.1	245.8	244.4	243.0	241.7	240.6
77.5°	190.1	189.5	188.9	188.3	187.7	186.8	185.6	184.4	183.2	182.0	181.6
80°	151.7	150.8	150.0	149.2	148.4	147.7	147.1	146.6	146.1	145.4	144.9
82.5°	114.1	113.8	113.4	113.0	112.6	112.4	112.3	112.2	112.1	111.9	111.6
85°	66.6	66.6	66.6	66.6	66.6	66.3	65.7	65.2	64.6	64.1	64.1
87.5°	25.9	26.0	26.5	26.4	26.4	26.2	27.2	27.0	27.2	27.4	27.2
90°	1.1	3.1	6.2	7.2	8.3	8.3	14.5	14.5	16.6	18.6	17.7
92.5°	11.8	17.2	26.9	39.6	54.8	76.2	128.9	209.3	287.7	328.7	273.8
95°	34.2	37.3	47.7	61.2	86.0	129.6	219.6	389.6	637.2	844.5	868.3
97.5°	61.3	61.3	70.3	82.7	104.1	140.5	209.9	350.3	596.4	889.5	1090.9
100°	78.7	78.7	86.0	98.4	118.2	151.3	212.4	329.5	540.9	833.0	1098.3
102.5°	95.3	97.0	103.4	115.0	133.8	165.4	220.7	323.7	503.5	762.6	1036.2
105°	121.3	124.3	129.6	142.0	160.6	190.6	240.4	326.4	471.4	679.8	923.2
107.5°	149.8	151.9	157.1	170.3	188.2	217.8	263.4	341.7	465.7	633.3	832.1
110°	168.9	170.9	176.1	188.6	207.2	235.2	280.8	353.3	467.3	617.6	786.5



TEST NUMBER: P332669-940

CATALOG NUMBER: S124DIP-S1020D1205U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.2	189.2	195.2	206.8	225.5	253.4	297.4	365.8	472.3	610.1	760.7
115°	213.5	216.6	223.8	234.2	253.9	281.9	323.2	385.5	481.8	606.2	736.7
117.5°	240.8	243.7	250.1	261.5	280.0	309.0	348.4	405.6	492.0	605.1	725.9
120°	259.0	261.1	268.4	279.7	297.4	326.4	365.8	419.6	499.4	605.1	720.1
122.5°	275.6	277.7	285.0	295.5	314.8	343.0	382.4	432.9	506.9	604.3	713.5
125°	297.4	301.5	307.7	319.1	338.9	367.8	405.1	452.8	518.1	603.1	702.5
127.5°	316.6	319.9	327.4	340.5	361.0	390.2	426.2	470.0	527.0	600.7	687.8
130°	327.4	331.5	339.8	355.4	375.1	405.1	440.4	480.8	533.6	599.9	678.7
132.5°	338.2	341.5	352.3	367.0	388.3	416.8	452.0	491.6	539.4	599.1	670.4
135°	353.3	357.5	367.8	385.5	407.2	434.2	468.3	505.7	548.1	597.9	658.0
137.5°	368.5	372.4	383.8	400.6	423.2	448.9	480.8	515.6	553.3	597.6	647.2
140°	379.2	382.4	393.8	411.3	433.1	458.0	489.1	522.2	557.5	596.8	641.4
142.5°	390.8	394.0	404.5	421.3	442.2	466.3	496.5	527.2	560.8	596.8	636.4
145°	407.2	410.4	420.7	435.2	454.9	477.7	504.6	532.6	562.7	594.8	627.9
147.5°	425.6	426.7	435.8	450.8	467.1	487.6	512.9	537.3	563.7	591.0	620.3
150°	437.3	438.3	446.6	459.1	474.6	494.3	517.0	539.8	563.7	588.5	614.5
152.5°	448.0	448.3	456.6	468.1	482.1	500.1	520.4	541.5	562.0	584.4	607.8
155°	463.2	464.2	470.4	480.8	492.2	507.7	525.3	543.0	559.5	578.2	597.9
157.5°	477.9	477.9	483.7	491.8	501.7	514.0	528.9	543.0	556.9	571.8	587.7
160°	487.0	487.0	491.2	498.4	506.7	518.1	530.5	543.0	554.4	566.8	580.2
162.5°	495.3	494.5	497.8	504.2	511.7	520.6	532.2	543.0	551.9	561.8	573.6
165°	504.6	504.6	506.7	511.8	517.0	523.3	532.6	540.9	547.1	554.4	562.7
167.5°	514.0	512.9	514.0	517.9	520.8	525.6	532.4	538.4	542.2	546.9	552.7
170°	518.1	517.0	518.1	521.2	523.3	526.4	531.5	536.7	538.8	541.9	546.1
172.5°	522.2	521.2	521.4	523.7	525.0	527.2	530.7	535.1	535.5	536.9	540.3
175°	526.4	525.3	525.3	526.4	527.4	527.4	529.5	532.6	531.5	531.5	533.6
177.5°	528.2	527.4	526.6	527.4	527.4	527.4	528.2	529.9	528.2	528.2	529.1
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4



TEST NUMBER: P332669-940

CATALOG NUMBER: S124DIP-S1020D1205U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6	1538.6
2.5°	1533.1	1535.3	1537.6	1538.6	1538.3	1538.1	1537.8	1537.7
5°	1524.9	1527.9	1531.0	1532.2	1531.7	1531.1	1530.5	1530.0
7.5°	1508.0	1510.4	1512.8	1513.9	1513.5	1513.1	1512.8	1512.5
10°	1493.7	1495.9	1498.1	1498.9	1498.3	1497.8	1497.3	1496.7
12.5°	1476.4	1478.8	1481.2	1482.0	1481.3	1480.5	1479.7	1479.0
15°	1443.3	1444.9	1446.6	1447.0	1446.2	1445.4	1444.6	1443.7
17.5°	1405.6	1406.7	1407.7	1407.9	1407.4	1406.9	1406.3	1405.7
20°	1377.5	1378.4	1379.2	1379.3	1378.8	1378.2	1377.7	1377.2
22.5°	1348.3	1349.8	1351.2	1351.5	1350.5	1349.5	1348.5	1347.6
25°	1300.0	1300.3	1300.6	1300.1	1299.0	1298.0	1296.8	1295.7
27.5°	1245.9	1245.2	1244.6	1243.6	1242.2	1240.8	1239.4	1238.1
30°	1208.5	1207.4	1206.3	1205.1	1203.7	1202.3	1201.0	1199.6
32.5°	1170.5	1169.3	1168.0	1166.6	1165.2	1163.9	1162.5	1161.1
35°	1110.7	1108.8	1106.9	1105.2	1103.8	1102.5	1101.1	1099.7
37.5°	1047.9	1045.9	1043.8	1041.9	1040.1	1038.2	1036.4	1034.7
40°	1004.2	1001.5	998.8	996.8	995.3	994.0	992.7	991.2
42.5°	962.0	958.8	955.6	953.5	952.6	951.6	950.7	949.9
45°	896.4	893.4	890.4	888.5	887.7	886.9	886.0	885.2
47.5°	833.0	829.6	826.3	823.5	821.4	819.3	817.3	815.2
50°	788.8	785.0	781.1	778.4	776.7	775.1	773.5	771.8
52.5°	743.3	739.9	736.5	733.8	731.6	729.6	727.5	725.4
55°	676.5	673.2	669.9	667.4	665.8	664.1	662.5	660.8
57.5°	609.5	606.4	603.2	600.8	599.2	597.7	596.1	594.5
60°	563.5	561.0	558.5	556.6	555.2	553.8	552.5	551.1
62.5°	518.5	516.2	514.0	512.2	510.9	509.4	508.1	506.8
65°	453.2	450.4	447.6	445.6	444.3	442.9	441.5	440.1
67.5°	385.8	383.2	380.6	379.1	378.6	378.3	377.9	377.6
70°	343.3	341.1	338.9	337.4	336.6	335.7	334.9	334.1
72.5°	300.8	299.0	297.3	296.0	295.2	294.4	293.6	292.7
75°	239.4	238.4	237.3	236.6	236.3	236.0	235.8	235.5
77.5°	181.3	181.0	180.7	180.1	179.4	178.7	178.0	177.3
80°	144.4	143.8	143.3	142.9	142.6	142.3	142.0	141.8
82.5°	111.3	110.9	110.7	110.3	110.0	109.8	109.5	109.2
85°	64.1	64.1	64.1	63.9	63.7	63.4	63.1	62.9
87.5°	27.4	27.6	27.8	27.8	28.0	28.3	28.0	28.0
90°	18.6	19.7	20.7	20.7	21.8	22.8	21.8	21.8
92.5°	203.5	153.1	121.9	101.1	88.9	83.3	79.8	79.8
95°	767.8	607.2	468.3	367.8	317.1	285.0	266.3	252.8
97.5°	1134.4	1074.7	973.4	865.2	790.8	728.4	697.3	675.8
100°	1249.6	1270.3	1219.6	1142.9	1052.8	989.5	958.5	950.2
102.5°	1243.8	1346.6	1361.3	1329.4	1274.1	1228.2	1195.5	1188.9
105°	1160.5	1339.8	1442.3	1484.8	1486.9	1478.6	1464.1	1457.9
107.5°	1042.1	1233.1	1377.5	1469.9	1521.1	1544.7	1555.1	1557.8
110°	970.9	1150.1	1300.4	1414.3	1487.9	1531.4	1550.2	1559.4





TEST NUMBER: P332669-940

CATALOG NUMBER: S124DIP-S1020D1205U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	918.6	1077.2	1219.1	1333.1	1416.7	1469.3	1495.4	1510.6
115°	866.2	993.7	1114.9	1214.4	1296.3	1358.4	1391.6	1399.9
117.5°	840.5	946.0	1041.3	1125.7	1195.5	1247.8	1281.3	1287.7
120°	828.9	925.3	1008.2	1081.7	1140.9	1186.4	1213.4	1224.8
122.5°	818.9	912.0	987.5	1052.0	1101.9	1140.9	1163.6	1175.0
125°	802.0	891.1	962.6	1019.6	1061.0	1091.1	1110.8	1117.0
127.5°	781.2	866.5	937.7	991.8	1033.5	1060.2	1076.8	1083.0
130°	764.7	846.6	917.0	972.0	1014.4	1040.3	1056.9	1063.1
132.5°	747.3	824.2	893.0	947.9	989.5	1018.8	1034.5	1040.7
135°	723.3	790.6	853.8	905.6	947.1	976.1	992.7	998.9
137.5°	701.5	758.5	811.7	858.5	897.3	926.0	939.6	947.1
140°	689.0	737.7	784.3	827.9	864.2	887.0	901.4	909.7
142.5°	677.4	720.3	760.4	798.1	830.2	851.3	864.2	870.0
145°	661.1	696.3	727.4	756.4	782.3	800.0	810.3	815.5
147.5°	647.6	675.6	700.4	723.3	742.3	757.4	765.4	767.1
150°	639.4	663.2	683.9	702.5	719.1	732.5	738.8	739.9
152.5°	630.2	650.7	669.8	685.1	699.2	710.2	713.9	715.0
155°	616.5	633.1	648.6	661.1	671.5	679.8	682.9	682.9
157.5°	601.8	615.7	628.7	638.7	646.6	652.8	654.7	654.7
160°	592.7	604.0	615.5	623.8	630.0	636.2	637.2	637.2
162.5°	583.5	593.3	602.3	609.7	614.2	620.5	621.5	620.6
165°	571.0	577.1	584.4	589.6	593.7	597.9	596.8	595.8
167.5°	558.7	563.5	569.3	572.4	574.4	577.1	576.9	576.1
170°	551.3	554.4	558.5	561.6	563.7	564.7	563.7	563.7
172.5°	544.6	546.9	549.4	551.6	552.9	553.9	552.9	551.3
175°	535.7	536.7	538.8	538.8	538.8	540.9	538.8	536.7
177.5°	529.9	530.7	530.7	531.5	530.7	531.5	529.9	528.2
180°	527.4	527.4	527.4	527.4	527.4	527.4	527.4	527.4

(END OF REPORT)