

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333330-930

Luminaire Tested: **S125DIP-S1270D1035U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333330-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D1035U930-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7210.6 lumens  
Efficiency: N/A  
Efficacy: 107.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333330-930  
CATALOG NUMBER: S125DIP-S1270D1035U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333330-930

CATALOG NUMBER: S125DIP-S1270D1035U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58				58
1	100	95	91	88	93	89	85	82	77	74	72	66	64	62	56	55	53	49				49
2	91	83	77	71	84	78	72	67	67	63	60	58	55	52	49	47	45	41				41
3	83	73	65	60	77	68	62	56	59	54	50	51	47	44	44	41	38	34				34
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33	30				30
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	32	29	26				26
6	64	52	43	38	59	49	41	36	43	37	32	37	32	29	32	28	25	23				23
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	22	20				20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20	18				18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	25	21	18	16				16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	17	15				15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10377	10377	10377
5°	10400	10301	10367
10°	10337	10228	10287
15°	10224	10105	10148
20°	10065	9933	9950
25°	9892	9728	9719
30°	9679	9508	9461
35°	9451	9270	9140
40°	9217	9012	8884
45°	8963	8777	8603
50°	8685	8493	8238
55°	8417	8173	7944
60°	8094	7848	7569
65°	7713	7459	7207
70°	7345	7009	6770
75°	6692	6470	6248
80°	5954	5861	5720
85°	5187	5276	4987



TEST NUMBER: P333330-930

CATALOG NUMBER: S125DIP-S1270D1035U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.5	2.1
10°-20°	427.9	5.9
20°-30°	631.9	8.8
30°-40°	737.3	10.2
40°-50°	740.5	10.3
50°-60°	650.0	9.0
60°-70°	484.3	6.7
70°-80°	276.9	3.8
80°-90°	82.8	1.1
90°-100°	292.6	4.1
100°-110°	629.0	8.7
110°-120°	590.3	8.2
120°-130°	478.4	6.6
130°-140°	383.9	5.3
140°-150°	289.7	4.0
150°-160°	203.9	2.8
160°-170°	120.2	1.7
170°-180°	39.1	0.5
0°-30°	1211.3	16.8
0°-40°	1948.6	27.0
0°-60°	3339.1	46.3
0°-90°	4183.2	58.0
90°-120°	1512.0	21.0
90°-150°	2664.1	36.9
90°-180°	3027.0	42.0
0°-180°	7210.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1607	1607	1607	1607	1607	
5°	1604	1601	1589	1600	1599	152
15°	1529	1525	1511	1517	1518	431
25°	1388	1381	1365	1367	1364	638
35°	1199	1193	1176	1169	1159	749
45°	981	976	961	946	942	756
55°	748	743	726	715	706	667
65°	505	501	488	477	472	501
75°	268	266	259	255	250	286
85°	70	71	71	70	67	78
90°	1	7	13	17	19	5
95°	27	79	721	327	191	29
105°	92	129	590	1162	1078	97
115°	164	198	474	1021	1201	162
125°	228	267	454	812	947	202
135°	267	321	451	681	786	207
145°	311	356	452	564	620	195
155°	355	382	441	499	520	163
165°	387	398	423	449	456	109
175°	403	403	406	411	409	38
180°	404	404	404	404	404	



TEST NUMBER: P333330-930

CATALOG NUMBER: S125DIP-S1270D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7
2.5°	1610.8	1610.1	1609.5	1608.7	1608.1	1606.6	1604.3	1602.1	1599.9	1597.6	1599.9
5°	1604.2	1603.6	1603.0	1602.5	1601.9	1600.3	1597.4	1594.6	1591.8	1588.9	1591.5
7.5°	1589.4	1588.9	1588.3	1587.7	1587.1	1585.3	1582.3	1579.2	1576.1	1573.0	1575.4
10°	1576.2	1575.6	1575.1	1574.5	1573.9	1572.1	1569.0	1565.9	1562.8	1559.7	1562.0
12.5°	1559.9	1558.9	1558.0	1556.9	1555.9	1554.0	1551.0	1548.2	1545.3	1542.4	1544.3
15°	1529.2	1528.4	1527.5	1526.6	1525.8	1523.8	1520.7	1517.6	1514.5	1511.4	1512.8
17.5°	1493.9	1492.6	1491.3	1490.1	1488.9	1486.6	1483.4	1480.2	1477.0	1473.7	1475.5
20°	1464.4	1463.8	1463.2	1462.6	1462.1	1460.0	1456.3	1452.6	1448.9	1445.3	1447.2
22.5°	1434.8	1433.9	1432.8	1431.8	1430.8	1428.6	1425.1	1421.7	1418.2	1414.8	1416.1
25°	1388.1	1386.7	1385.3	1383.9	1382.4	1379.9	1376.2	1372.6	1368.9	1365.2	1365.8
27.5°	1333.4	1332.6	1331.7	1330.9	1330.1	1327.7	1324.0	1320.1	1316.4	1312.6	1312.7
30°	1297.9	1297.0	1296.2	1295.3	1294.5	1291.9	1287.7	1283.4	1279.2	1275.0	1274.4
32.5°	1259.2	1257.9	1256.6	1255.3	1254.0	1251.5	1247.7	1243.9	1240.1	1236.3	1235.3
35°	1198.7	1197.6	1196.5	1195.3	1194.2	1191.6	1187.6	1183.7	1179.7	1175.8	1174.4
37.5°	1135.9	1134.5	1133.1	1131.6	1130.2	1127.6	1124.0	1120.2	1116.5	1112.8	1110.7
40°	1093.2	1091.8	1090.4	1088.9	1087.5	1084.8	1080.9	1076.9	1073.0	1069.0	1066.5
42.5°	1047.4	1046.3	1045.1	1043.8	1042.7	1040.1	1036.2	1032.2	1028.3	1024.3	1022.0
45°	981.3	980.2	979.1	978.0	976.8	974.5	971.2	967.8	964.4	961.0	957.6
47.5°	910.1	910.2	910.3	910.3	910.4	908.3	904.3	900.3	896.2	892.1	888.7
50°	864.4	863.6	862.7	861.9	861.0	858.8	855.5	852.1	848.7	845.3	841.6
52.5°	817.6	817.0	816.4	815.7	815.1	813.0	809.3	805.8	802.2	798.5	795.3
55°	747.5	746.6	745.8	744.9	744.0	741.7	737.7	733.8	729.8	725.9	723.3
57.5°	673.4	673.0	672.5	672.1	671.6	669.8	666.4	663.1	659.7	656.4	653.1
60°	626.6	625.6	624.4	623.3	622.2	620.0	616.9	613.8	610.7	607.6	604.8
62.5°	577.9	577.0	576.1	575.1	574.2	572.5	569.8	567.1	564.5	561.8	558.8
65°	504.7	504.1	503.5	503.0	502.4	500.5	497.4	494.3	491.2	488.1	485.6
67.5°	433.7	432.5	431.4	430.2	429.0	427.2	424.9	422.6	420.3	417.9	415.8
70°	389.0	387.6	386.1	384.7	383.4	381.3	378.8	376.3	373.7	371.2	369.5
72.5°	340.1	339.2	338.3	337.3	336.3	335.0	333.4	331.7	330.1	328.5	326.5
75°	268.2	267.7	267.1	266.5	266.0	265.0	263.6	262.1	260.7	259.3	258.4
77.5°	201.9	201.6	201.4	201.2	201.0	200.5	199.7	198.9	198.0	197.3	196.8
80°	160.1	160.1	160.1	160.1	160.1	159.9	159.3	158.7	158.2	157.6	157.4
82.5°	123.5	123.1	122.6	122.2	121.7	121.5	121.3	121.2	121.2	121.0	120.5
85°	70.0	70.2	70.4	70.8	71.0	71.2	71.2	71.2	71.2	71.2	70.9
87.5°	27.6	27.8	28.1	28.5	28.8	28.9	28.9	29.0	28.9	29.0	29.2
90°	0.8	1.6	3.3	4.9	6.5	8.2	9.0	10.6	11.4	13.0	13.9
92.5°	9.9	12.1	18.9	28.9	43.0	66.8	111.2	185.7	266.6	262.4	212.4
95°	26.8	27.6	34.2	43.1	61.1	97.7	184.7	363.8	588.5	721.1	705.6
97.5°	44.6	45.6	50.1	59.1	75.2	101.6	159.2	290.4	525.5	770.1	892.8
100°	57.0	58.6	61.9	70.8	86.3	110.7	157.9	263.7	468.8	734.9	938.4
102.5°	70.7	71.6	74.2	83.8	98.0	121.7	163.8	252.7	425.8	673.1	911.1
105°	92.0	92.0	96.0	104.2	117.2	140.0	175.8	248.3	384.2	590.0	823.7
107.5°	112.8	114.5	118.3	125.0	138.5	159.1	193.7	255.8	366.6	533.0	734.4
110°	127.8	129.4	132.6	140.0	152.2	173.3	206.8	262.9	361.3	506.2	683.6



TEST NUMBER: P333330-930

CATALOG NUMBER: S125DIP-S1270D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.8	144.4	147.0	154.3	166.5	187.0	219.1	272.0	361.3	490.6	645.9
115°	164.4	166.0	168.4	175.8	188.0	208.4	238.5	285.7	363.8	473.7	604.7
117.5°	183.9	186.4	189.0	196.3	210.2	229.8	258.4	301.3	369.2	465.4	580.2
120°	197.0	199.4	202.7	210.0	223.8	244.2	272.6	311.7	374.4	461.5	566.5
122.5°	210.7	212.4	215.0	222.3	237.5	257.9	286.3	323.4	379.0	458.2	554.7
125°	227.9	229.5	233.6	240.9	256.4	277.5	304.4	339.4	386.6	454.1	538.8
127.5°	241.4	243.9	249.1	258.4	274.8	296.0	321.8	354.0	395.3	452.2	524.2
130°	249.9	252.3	258.9	269.4	286.5	307.6	332.9	363.8	400.5	450.9	514.4
132.5°	256.4	259.4	267.3	279.2	296.9	318.0	343.3	372.3	406.3	450.9	506.5
135°	266.9	270.2	280.0	293.0	310.1	332.1	357.3	384.2	414.3	450.9	497.3
137.5°	280.3	282.7	291.9	304.9	321.6	344.3	367.2	393.0	421.6	451.8	489.0
140°	288.1	290.6	300.4	313.3	328.8	350.8	374.4	398.8	424.9	452.5	485.1
142.5°	297.3	299.1	308.1	321.1	336.0	356.6	379.0	402.0	426.8	453.1	481.8
145°	310.9	312.5	320.7	332.1	346.7	365.4	386.6	406.9	428.9	452.5	477.0
147.5°	325.2	326.2	333.2	343.8	356.4	372.9	391.5	409.9	429.7	450.4	471.9
150°	333.7	335.3	341.0	351.6	363.0	376.8	394.8	411.8	429.7	448.4	468.0
152.5°	342.8	343.8	348.9	358.1	368.8	381.4	398.0	413.1	429.1	445.9	463.4
155°	354.8	354.8	359.7	367.9	376.0	387.4	401.2	414.3	427.3	441.2	455.8
157.5°	365.6	365.4	369.3	376.3	383.5	392.2	404.0	415.1	425.2	436.3	448.6
160°	372.8	371.9	375.2	380.9	387.4	394.8	405.3	415.1	423.2	433.0	442.8
162.5°	378.6	377.8	381.1	386.1	391.3	397.4	406.6	414.4	421.3	429.1	437.6
165°	387.4	385.8	388.2	392.3	395.6	400.5	406.9	413.4	418.3	423.2	429.7
167.5°	393.3	392.5	394.0	396.2	398.5	401.5	406.9	411.5	413.8	417.5	422.1
170°	397.2	396.4	397.2	398.8	400.5	402.8	406.9	410.2	411.8	414.3	417.5
172.5°	399.8	398.4	399.2	400.7	401.7	402.8	406.3	408.9	409.2	410.3	412.9
175°	402.8	401.2	402.0	402.8	402.8	402.8	405.3	406.9	406.1	406.1	406.9
177.5°	404.3	403.0	403.0	403.7	403.0	403.0	404.3	405.0	403.7	403.7	404.3
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333330-930

CATALOG NUMBER: S125DIP-S1270D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7
2.5°	1602.1	1604.3	1606.6	1607.6	1607.4	1607.2	1607.0	1606.7
5°	1594.0	1596.6	1599.1	1600.3	1599.9	1599.7	1599.4	1599.1
7.5°	1577.8	1580.4	1582.8	1584.0	1583.7	1583.4	1583.1	1582.8
10°	1564.2	1566.5	1568.7	1569.7	1569.5	1569.1	1568.9	1568.6
12.5°	1546.1	1547.8	1549.6	1550.5	1550.5	1550.4	1550.4	1550.3
15°	1514.3	1515.6	1517.0	1517.8	1517.8	1517.8	1517.8	1517.8
17.5°	1477.2	1479.0	1480.7	1480.9	1479.5	1478.1	1476.7	1475.3
20°	1449.3	1451.2	1453.2	1453.5	1452.0	1450.7	1449.3	1447.8
22.5°	1417.4	1418.7	1420.0	1420.2	1419.2	1418.2	1417.2	1416.3
25°	1366.4	1366.9	1367.5	1367.3	1366.5	1365.6	1364.8	1363.9
27.5°	1312.8	1313.0	1313.0	1312.6	1311.8	1311.0	1310.1	1309.3
30°	1273.8	1273.3	1272.7	1272.0	1271.1	1270.3	1269.4	1268.6
32.5°	1234.3	1233.3	1232.2	1230.9	1229.5	1227.9	1226.4	1224.9
35°	1173.0	1171.6	1170.2	1168.3	1166.0	1163.8	1161.6	1159.3
37.5°	1108.6	1106.5	1104.4	1102.7	1101.4	1100.1	1098.8	1097.5
40°	1064.0	1061.4	1058.8	1057.2	1056.3	1055.5	1054.6	1053.8
42.5°	1019.7	1017.3	1015.0	1013.3	1011.9	1010.6	1009.3	1008.0
45°	954.2	950.8	947.5	945.3	944.4	943.6	942.7	941.9
47.5°	885.2	881.7	878.3	875.6	873.6	871.6	869.7	867.7
50°	838.0	834.3	830.6	827.8	825.8	823.9	821.9	819.9
52.5°	792.1	788.9	785.6	782.9	780.7	778.5	776.3	774.1
55°	720.7	718.2	715.7	713.4	711.4	709.5	707.4	705.5
57.5°	649.9	646.6	643.4	641.2	640.1	639.0	637.9	636.8
60°	601.9	599.2	596.3	593.9	591.9	590.0	588.0	586.0
62.5°	555.7	552.7	549.7	547.4	545.8	544.3	542.7	541.3
65°	483.1	480.5	477.9	476.1	475.0	473.9	472.7	471.6
67.5°	413.7	411.5	409.4	408.0	407.2	406.6	405.9	405.2
70°	367.8	366.1	364.4	363.0	361.8	360.7	359.6	358.5
72.5°	324.7	322.7	320.8	319.3	318.1	317.0	315.8	314.7
75°	257.6	256.7	255.9	254.9	253.8	252.7	251.5	250.4
77.5°	196.2	195.8	195.3	194.6	193.8	193.0	192.2	191.4
80°	157.0	156.8	156.5	156.0	155.5	154.9	154.3	153.8
82.5°	120.0	119.5	119.0	118.7	118.5	118.5	118.3	118.2
85°	70.6	70.4	70.0	69.6	69.1	68.5	67.9	67.3
87.5°	29.4	29.5	29.7	29.8	29.4	28.9	28.6	28.1
90°	14.7	15.5	16.3	17.9	17.9	17.9	18.8	18.8
92.5°	144.2	104.7	78.8	66.8	56.3	54.4	53.2	51.9
95°	585.2	461.5	361.3	293.0	235.2	210.8	204.3	191.3
97.5°	871.6	784.7	687.2	592.2	541.9	496.3	472.7	462.3
100°	1001.1	961.2	877.3	792.7	736.5	678.0	647.8	634.9
102.5°	1044.7	1069.3	1029.1	971.8	911.7	870.1	837.3	827.5
105°	1019.0	1130.5	1166.3	1157.3	1131.3	1104.5	1088.2	1078.4
107.5°	927.2	1076.0	1167.9	1210.4	1223.6	1223.4	1218.1	1211.5
110°	859.5	1014.1	1128.9	1198.1	1234.7	1250.1	1255.8	1255.8





TEST NUMBER: P333330-930

CATALOG NUMBER: S125DIP-S1270D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	806.1	952.9	1068.9	1150.6	1204.0	1230.6	1244.8	1250.6
115°	739.0	865.2	976.6	1065.4	1128.9	1167.9	1190.7	1201.3
117.5°	695.7	804.5	900.5	981.9	1045.4	1085.7	1108.3	1114.8
120°	672.3	770.0	859.5	931.1	991.3	1030.4	1052.4	1058.9
122.5°	654.7	745.2	824.9	892.0	945.7	981.5	1003.6	1009.4
125°	629.2	712.2	782.9	841.6	887.1	920.5	938.4	946.6
127.5°	603.1	680.6	746.7	801.5	842.9	872.3	889.2	892.8
130°	586.9	658.4	721.9	774.9	815.5	842.4	858.7	863.6
132.5°	570.5	637.6	695.2	746.2	786.8	813.8	828.7	834.2
135°	549.3	605.5	657.6	704.0	739.8	766.7	781.3	786.2
137.5°	531.5	576.9	620.2	659.6	691.6	716.1	729.6	734.9
140°	521.7	559.9	597.4	631.6	661.7	682.9	695.0	699.1
142.5°	513.2	545.6	577.9	607.5	633.1	650.9	662.5	665.9
145°	502.1	527.4	552.6	574.6	594.1	608.0	616.9	620.2
147.5°	491.8	512.3	531.7	548.2	563.7	574.8	580.0	581.5
150°	485.9	503.8	519.3	533.9	546.1	555.9	559.1	559.9
152.5°	479.4	495.3	509.5	520.9	531.2	539.0	542.2	543.0
155°	469.6	482.7	494.1	503.0	511.1	516.8	519.3	520.1
157.5°	459.8	470.6	479.4	486.4	492.8	497.4	499.7	499.5
160°	453.3	461.5	469.6	475.3	481.0	485.1	486.7	485.9
162.5°	446.2	453.6	460.5	465.5	469.9	473.4	473.7	473.5
165°	436.3	442.0	446.9	450.9	454.1	455.8	455.8	455.8
167.5°	426.8	430.6	434.3	437.2	438.9	440.3	439.7	439.5
170°	421.6	424.0	426.5	428.1	429.7	430.6	430.6	429.7
172.5°	415.7	418.2	420.0	420.9	421.3	422.7	421.4	420.6
175°	409.4	409.4	411.0	411.0	411.0	411.8	410.2	409.4
177.5°	405.0	405.6	405.6	405.6	405.0	405.6	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7

(END OF REPORT)