

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333312-930

Luminaire Tested: **S125DIP-S1270D590U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333312-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D590U930-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5912.1 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333312-930

CATALOG NUMBER: S125DIP-S1270D590U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333312-930

CATALOG NUMBER: S125DIP-S1270D590U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	112	112	112	112	106	106	106	106	95	95	95		85	85	85		75	75	75	71
1	102	98	94	90	97	93	89	86	83	80	78		74	72	70		66	65	63	59
2	93	85	79	74	88	81	75	71	73	68	64		65	62	59		58	56	53	50
3	85	75	67	61	80	71	64	59	64	59	54		58	53	50		52	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46		51	47	43		46	42	39	36
5	72	59	51	45	67	57	49	43	51	45	40		46	41	37		42	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35		42	37	32		38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31		38	33	29		35	30	27	24
8	57	44	36	30	54	42	35	30	38	32	28		35	30	26		32	27	24	22
9	53	40	33	27	50	39	31	26	35	29	25		32	27	23		29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22		30	25	21		27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10377	10377	10377
5°	10400	10301	10367
10°	10337	10228	10287
15°	10224	10105	10148
20°	10065	9933	9950
25°	9892	9728	9719
30°	9679	9508	9461
35°	9451	9270	9140
40°	9217	9012	8884
45°	8963	8777	8603
50°	8685	8493	8238
55°	8417	8173	7944
60°	8094	7848	7569
65°	7713	7459	7207
70°	7345	7009	6770
75°	6692	6470	6248
80°	5954	5861	5720
85°	5187	5276	4987



TEST NUMBER: P333312-930

CATALOG NUMBER: S125DIP-S1270D590U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.5	2.6
10°-20°	427.9	7.2
20°-30°	631.9	10.7
30°-40°	737.3	12.5
40°-50°	740.5	12.5
50°-60°	650.0	11.0
60°-70°	484.3	8.2
70°-80°	276.9	4.7
80°-90°	81.9	1.4
90°-100°	167.2	2.8
100°-110°	359.4	6.1
110°-120°	337.3	5.7
120°-130°	273.4	4.6
130°-140°	219.4	3.7
140°-150°	165.6	2.8
150°-160°	116.5	2.0
160°-170°	68.7	1.2
170°-180°	22.3	0.4
0°-30°	1211.3	20.5
0°-40°	1948.6	33.0
0°-60°	3339.1	56.5
0°-90°	4182.3	70.7
90°-120°	864.0	14.6
90°-150°	1522.3	25.7
90°-180°	1730.0	29.3
0°-180°	5912.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1607	1607	1607	1607	1607	
5°	1604	1601	1589	1600	1599	152
15°	1529	1525	1511	1517	1518	431
25°	1388	1381	1365	1367	1364	638
35°	1199	1193	1176	1169	1159	749
45°	981	976	961	946	942	756
55°	748	743	726	715	706	667
65°	505	501	488	477	472	501
75°	268	266	259	255	250	286
85°	70	71	71	70	67	78
90°	0	4	7	10	11	5
95°	15	45	412	187	109	16
105°	53	73	337	664	616	55
115°	94	113	271	583	686	92
125°	130	153	260	464	541	115
135°	152	183	258	389	449	118
145°	178	203	259	322	354	111
155°	203	218	252	285	297	93
165°	221	227	242	256	260	62
175°	230	230	232	235	234	22
180°	231	231	231	231	231	



TEST NUMBER: P333312-930

CATALOG NUMBER: S125DIP-S1270D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7
2.5°	1610.8	1610.1	1609.5	1608.7	1608.1	1606.6	1604.3	1602.1	1599.9	1597.6	1599.9
5°	1604.2	1603.6	1603.0	1602.5	1601.9	1600.3	1597.4	1594.6	1591.8	1588.9	1591.5
7.5°	1589.4	1588.9	1588.3	1587.7	1587.1	1585.3	1582.3	1579.2	1576.1	1573.0	1575.4
10°	1576.2	1575.6	1575.1	1574.5	1573.9	1572.1	1569.0	1565.9	1562.8	1559.7	1562.0
12.5°	1559.9	1558.9	1558.0	1556.9	1555.9	1554.0	1551.0	1548.2	1545.3	1542.4	1544.3
15°	1529.2	1528.4	1527.5	1526.6	1525.8	1523.8	1520.7	1517.6	1514.5	1511.4	1512.8
17.5°	1493.9	1492.6	1491.3	1490.1	1488.9	1486.6	1483.4	1480.2	1477.0	1473.7	1475.5
20°	1464.4	1463.8	1463.2	1462.6	1462.1	1460.0	1456.3	1452.6	1448.9	1445.3	1447.2
22.5°	1434.8	1433.9	1432.8	1431.8	1430.8	1428.6	1425.1	1421.7	1418.2	1414.8	1416.1
25°	1388.1	1386.7	1385.3	1383.9	1382.4	1379.9	1376.2	1372.6	1368.9	1365.2	1365.8
27.5°	1333.4	1332.6	1331.7	1330.9	1330.1	1327.7	1324.0	1320.1	1316.4	1312.6	1312.7
30°	1297.9	1297.0	1296.2	1295.3	1294.5	1291.9	1287.7	1283.4	1279.2	1275.0	1274.4
32.5°	1259.2	1257.9	1256.6	1255.3	1254.0	1251.5	1247.7	1243.9	1240.1	1236.3	1235.3
35°	1198.7	1197.6	1196.5	1195.3	1194.2	1191.6	1187.6	1183.7	1179.7	1175.8	1174.4
37.5°	1135.9	1134.5	1133.1	1131.6	1130.2	1127.6	1124.0	1120.2	1116.5	1112.8	1110.7
40°	1093.2	1091.8	1090.4	1088.9	1087.5	1084.8	1080.9	1076.9	1073.0	1069.0	1066.5
42.5°	1047.4	1046.3	1045.1	1043.8	1042.7	1040.1	1036.2	1032.2	1028.3	1024.3	1022.0
45°	981.3	980.2	979.1	978.0	976.8	974.5	971.2	967.8	964.4	961.0	957.6
47.5°	910.1	910.2	910.3	910.3	910.4	908.3	904.3	900.3	896.2	892.1	888.7
50°	864.4	863.6	862.7	861.9	861.0	858.8	855.5	852.1	848.7	845.3	841.6
52.5°	817.6	817.0	816.4	815.7	815.1	813.0	809.3	805.8	802.2	798.5	795.3
55°	747.5	746.6	745.8	744.9	744.0	741.7	737.7	733.8	729.8	725.9	723.3
57.5°	673.4	673.0	672.5	672.1	671.6	669.8	666.4	663.1	659.7	656.4	653.1
60°	626.6	625.6	624.4	623.3	622.2	620.0	616.9	613.8	610.7	607.6	604.8
62.5°	577.9	577.0	576.1	575.1	574.2	572.5	569.8	567.1	564.5	561.8	558.8
65°	504.7	504.1	503.5	503.0	502.4	500.5	497.4	494.3	491.2	488.1	485.6
67.5°	433.7	432.5	431.4	430.2	429.0	427.2	424.9	422.6	420.3	417.9	415.8
70°	389.0	387.6	386.1	384.7	383.4	381.3	378.8	376.3	373.7	371.2	369.5
72.5°	340.1	339.2	338.3	337.3	336.3	335.0	333.4	331.7	330.1	328.5	326.5
75°	268.2	267.7	267.1	266.5	266.0	265.0	263.6	262.1	260.7	259.3	258.4
77.5°	201.9	201.6	201.4	201.2	201.0	200.5	199.7	198.9	198.0	197.3	196.8
80°	160.1	160.1	160.1	160.1	160.1	159.9	159.3	158.7	158.2	157.6	157.4
82.5°	123.5	123.1	122.6	122.2	121.7	121.5	121.3	121.2	121.2	121.0	120.5
85°	70.0	70.2	70.4	70.8	71.0	71.2	71.2	71.2	71.2	71.2	70.9
87.5°	27.6	27.6	27.8	28.0	28.2	28.3	28.1	28.1	28.0	28.0	28.0
90°	0.5	0.9	1.9	2.8	3.8	4.6	5.1	6.0	6.5	7.4	7.9
92.5°	5.7	6.8	10.8	16.6	24.5	38.2	63.5	106.2	152.4	149.9	121.4
95°	15.3	15.8	19.6	24.6	34.9	55.8	105.6	207.9	336.2	412.1	403.2
97.5°	25.5	26.0	28.6	33.8	43.0	58.0	91.0	165.9	300.3	440.0	510.2
100°	32.5	33.5	35.4	40.4	49.3	63.3	90.3	150.7	267.9	420.0	536.2
102.5°	40.4	40.9	42.4	47.9	56.0	69.5	93.6	144.4	243.3	384.6	520.6
105°	52.6	52.6	54.9	59.5	66.9	80.0	100.4	141.9	219.5	337.2	470.7
107.5°	64.5	65.4	67.6	71.4	79.2	90.9	110.7	146.1	209.5	304.5	419.7
110°	73.1	73.9	75.8	80.0	87.0	99.1	118.1	150.2	206.5	289.3	390.7



TEST NUMBER: P333312-930

CATALOG NUMBER: S125DIP-S1270D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	81.6	82.5	84.0	88.2	95.1	106.9	125.2	155.4	206.5	280.4	369.1
115°	93.9	94.9	96.3	100.4	107.5	119.0	136.2	163.2	207.9	270.7	345.5
117.5°	105.1	106.5	108.0	112.2	120.1	131.3	147.7	172.2	210.9	266.0	331.5
120°	112.5	114.0	115.8	120.0	127.9	139.5	155.8	178.1	213.9	263.7	323.7
122.5°	120.3	121.4	122.9	127.0	135.7	147.3	163.6	184.8	216.5	261.9	317.0
125°	130.2	131.2	133.5	137.6	146.5	158.6	173.9	194.0	220.9	259.5	307.9
127.5°	137.9	139.3	142.4	147.7	157.0	169.1	183.8	202.3	225.8	258.4	299.5
130°	142.8	144.1	147.9	153.9	163.7	175.8	190.2	207.9	228.9	257.6	293.9
132.5°	146.5	148.3	152.7	159.6	169.7	181.7	196.2	212.7	232.2	257.6	289.4
135°	152.5	154.4	160.0	167.5	177.2	189.7	204.2	219.5	236.7	257.6	284.1
137.5°	160.2	161.6	166.8	174.2	183.8	196.7	209.9	224.5	240.9	258.2	279.4
140°	164.6	166.0	171.6	179.0	187.9	200.5	213.9	227.9	242.8	258.6	277.2
142.5°	169.8	170.9	176.1	183.5	192.0	203.8	216.5	229.8	243.9	258.9	275.3
145°	177.7	178.6	183.2	189.7	198.1	208.8	220.9	232.5	245.1	258.6	272.6
147.5°	185.8	186.4	190.4	196.4	203.7	213.1	223.7	234.2	245.6	257.4	269.6
150°	190.7	191.6	194.9	200.9	207.4	215.3	225.6	235.3	245.6	256.2	267.4
152.5°	195.9	196.4	199.3	204.6	210.8	217.9	227.4	236.0	245.2	254.8	264.8
155°	202.8	202.8	205.5	210.2	214.8	221.4	229.3	236.7	244.2	252.1	260.4
157.5°	208.9	208.8	211.1	215.1	219.2	224.0	230.9	237.2	243.0	249.2	256.3
160°	213.0	212.5	214.4	217.7	221.4	225.6	231.6	237.2	241.8	247.4	253.0
162.5°	216.4	215.9	217.8	220.6	223.6	227.1	232.4	236.8	240.8	245.2	250.1
165°	221.4	220.5	221.8	224.1	226.0	228.9	232.5	236.3	239.0	241.8	245.6
167.5°	224.7	224.3	225.1	226.4	227.7	229.4	232.5	235.1	236.4	238.6	241.2
170°	227.0	226.5	227.0	227.9	228.9	230.2	232.5	234.4	235.3	236.7	238.6
172.5°	228.4	227.6	228.0	229.0	229.6	230.2	232.2	233.7	233.8	234.5	235.9
175°	230.2	229.3	229.8	230.2	230.2	230.2	231.6	232.5	232.0	232.0	232.5
177.5°	231.1	230.3	230.3	230.6	230.3	230.3	231.1	231.4	230.6	230.6	231.1
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333312-930

CATALOG NUMBER: S125DIP-S1270D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7
2.5°	1602.1	1604.3	1606.6	1607.6	1607.4	1607.2	1607.0	1606.7
5°	1594.0	1596.6	1599.1	1600.3	1599.9	1599.7	1599.4	1599.1
7.5°	1577.8	1580.4	1582.8	1584.0	1583.7	1583.4	1583.1	1582.8
10°	1564.2	1566.5	1568.7	1569.7	1569.5	1569.1	1568.9	1568.6
12.5°	1546.1	1547.8	1549.6	1550.5	1550.5	1550.4	1550.4	1550.3
15°	1514.3	1515.6	1517.0	1517.8	1517.8	1517.8	1517.8	1517.8
17.5°	1477.2	1479.0	1480.7	1480.9	1479.5	1478.1	1476.7	1475.3
20°	1449.3	1451.2	1453.2	1453.5	1452.0	1450.7	1449.3	1447.8
22.5°	1417.4	1418.7	1420.0	1420.2	1419.2	1418.2	1417.2	1416.3
25°	1366.4	1366.9	1367.5	1367.3	1366.5	1365.6	1364.8	1363.9
27.5°	1312.8	1313.0	1313.0	1312.6	1311.8	1311.0	1310.1	1309.3
30°	1273.8	1273.3	1272.7	1272.0	1271.1	1270.3	1269.4	1268.6
32.5°	1234.3	1233.3	1232.2	1230.9	1229.5	1227.9	1226.4	1224.9
35°	1173.0	1171.6	1170.2	1168.3	1166.0	1163.8	1161.6	1159.3
37.5°	1108.6	1106.5	1104.4	1102.7	1101.4	1100.1	1098.8	1097.5
40°	1064.0	1061.4	1058.8	1057.2	1056.3	1055.5	1054.6	1053.8
42.5°	1019.7	1017.3	1015.0	1013.3	1011.9	1010.6	1009.3	1008.0
45°	954.2	950.8	947.5	945.3	944.4	943.6	942.7	941.9
47.5°	885.2	881.7	878.3	875.6	873.6	871.6	869.7	867.7
50°	838.0	834.3	830.6	827.8	825.8	823.9	821.9	819.9
52.5°	792.1	788.9	785.6	782.9	780.7	778.5	776.3	774.1
55°	720.7	718.2	715.7	713.4	711.4	709.5	707.4	705.5
57.5°	649.9	646.6	643.4	641.2	640.1	639.0	637.9	636.8
60°	601.9	599.2	596.3	593.9	591.9	590.0	588.0	586.0
62.5°	555.7	552.7	549.7	547.4	545.8	544.3	542.7	541.3
65°	483.1	480.5	477.9	476.1	475.0	473.9	472.7	471.6
67.5°	413.7	411.5	409.4	408.0	407.2	406.6	405.9	405.2
70°	367.8	366.1	364.4	363.0	361.8	360.7	359.6	358.5
72.5°	324.7	322.7	320.8	319.3	318.1	317.0	315.8	314.7
75°	257.6	256.7	255.9	254.9	253.8	252.7	251.5	250.4
77.5°	196.2	195.8	195.3	194.6	193.8	193.0	192.2	191.4
80°	157.0	156.8	156.5	156.0	155.5	154.9	154.3	153.8
82.5°	120.0	119.5	119.0	118.7	118.5	118.5	118.3	118.2
85°	70.6	70.4	70.0	69.6	69.1	68.5	67.9	67.3
87.5°	28.1	28.2	28.3	28.3	27.8	27.4	27.0	26.6
90°	8.4	8.8	9.3	10.2	10.2	10.2	10.7	10.7
92.5°	82.4	59.8	45.0	38.2	32.2	31.1	30.4	29.7
95°	334.4	263.7	206.5	167.5	134.4	120.4	116.8	109.3
97.5°	498.0	448.4	392.7	338.3	309.7	283.6	270.1	264.2
100°	572.0	549.3	501.3	453.0	420.9	387.4	370.2	362.7
102.5°	597.0	611.0	588.0	555.3	521.0	497.2	478.5	472.9
105°	582.3	646.0	666.4	661.3	646.5	631.1	621.8	616.2
107.5°	529.8	614.8	667.4	691.6	699.2	699.1	696.0	692.3
110°	491.1	579.5	645.1	684.6	705.5	714.4	717.6	717.6



TEST NUMBER: P333312-930

CATALOG NUMBER: S125DIP-S1270D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	460.6	544.5	610.8	657.5	688.0	703.2	711.3	714.6
115°	422.2	494.4	558.1	608.8	645.1	667.4	680.4	686.5
117.5°	397.5	459.7	514.5	561.1	597.4	620.4	633.3	637.1
120°	384.2	439.9	491.1	532.1	566.5	588.8	601.4	605.0
122.5°	374.1	425.8	471.4	509.7	540.4	560.8	573.4	576.7
125°	359.5	406.9	447.4	480.9	507.0	526.0	536.2	540.9
127.5°	344.6	388.9	426.6	458.0	481.6	498.5	508.1	510.2
130°	335.3	376.3	412.5	442.7	466.0	481.4	490.6	493.4
132.5°	326.0	364.4	397.3	426.4	449.6	465.0	473.5	476.7
135°	313.9	346.0	375.8	402.3	422.7	438.1	446.5	449.2
137.5°	303.7	329.6	354.4	376.9	395.2	409.2	416.9	420.0
140°	298.1	320.0	341.4	360.9	378.1	390.2	397.1	399.5
142.5°	293.3	311.8	330.2	347.2	361.7	371.9	378.5	380.5
145°	287.0	301.3	315.8	328.3	339.5	347.4	352.5	354.4
147.5°	281.0	292.7	303.8	313.2	322.1	328.4	331.4	332.2
150°	277.6	287.9	296.7	305.1	312.1	317.6	319.5	320.0
152.5°	273.9	283.1	291.1	297.7	303.5	307.9	309.8	310.3
155°	268.3	275.8	282.3	287.4	292.0	295.3	296.7	297.2
157.5°	262.8	268.9	273.9	277.9	281.5	284.2	285.5	285.4
160°	259.0	263.7	268.3	271.6	274.8	277.2	278.1	277.6
162.5°	254.9	259.3	263.1	266.0	268.6	270.5	270.7	270.6
165°	249.2	252.5	255.4	257.6	259.5	260.4	260.4	260.4
167.5°	243.9	246.1	248.2	249.8	250.8	251.6	251.2	251.1
170°	240.9	242.3	243.7	244.6	245.6	246.1	246.1	245.6
172.5°	237.6	239.0	239.9	240.5	240.8	241.6	240.8	240.4
175°	233.9	233.9	234.9	234.9	234.9	235.3	234.4	233.9
177.5°	231.4	231.8	231.8	231.8	231.4	231.8	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6

(END OF REPORT)