

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333151-930

Luminaire Tested: **S125DIP-S375D1205U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333151-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1205U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5180.3 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	28	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	53	47	42	42	37	34	30	28	25	20	19	17	13
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	40	34	52	43	36	31	33	29	25	25	21	19	16	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2866	2866	2866	2866
5°	3319	2877	2519	2877
10°	3862	2861	2207	2861
15°	4275	2841	2035	2841
20°	4786	2808	1898	2808
25°	5606	2770	1831	2770
30°	6055	2732	1773	2732
35°	4978	2663	1735	2663
40°	3538	2566	1693	2566
45°	2719	2437	1669	2437
50°	2321	2275	1666	2275
55°	2066	2117	1680	2117
60°	1864	1944	1723	1944
65°	1722	1771	1768	1771
70°	1565	1590	1794	1590
75°	1382	1402	1777	1402
80°	1164	1142	1625	1142
85°	926	823	1312	823



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	0.8
10°-20°	127.2	2.5
20°-30°	206.6	4.0
30°-40°	252.0	4.9
40°-50°	229.2	4.4
50°-60°	182.6	3.5
60°-70°	127.2	2.5
70°-80°	67.8	1.3
80°-90°	19.8	0.4
90°-100°	46.5	0.9
100°-110°	286.3	5.5
110°-120°	519.2	10.0
120°-130°	666.3	12.9
130°-140°	716.7	13.8
140°-150°	672.7	13.0
150°-160°	544.2	10.5
160°-170°	351.9	6.8
170°-180°	121.4	2.3
0°-30°	376.5	7.3
0°-40°	628.5	12.1
0°-60°	1040.3	20.1
0°-90°	1255.1	24.2
90°-120°	851.9	16.4
90°-150°	2907.7	56.1
90°-180°	3925.0	75.8
0°-180°	5180.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	512	444	388	444	512	52
15°	639	425	304	425	639	183
25°	787	389	257	389	787	359
35°	631	338	220	338	631	386
45°	298	267	183	267	298	238
55°	184	188	149	188	184	165
65°	113	116	116	116	113	112
75°	55	56	71	56	55	60
85°	12	11	18	11	12	15
90°	23	1	23	1	23	10
95°	20	54	20	54	20	16
105°	281	279	281	279	281	254
115°	519	523	519	523	519	515
125°	744	744	744	744	744	662
135°	924	928	924	928	924	713
145°	1073	1076	1073	1076	1073	670
155°	1176	1184	1176	1184	1176	542
165°	1243	1250	1243	1250	1243	351
175°	1272	1278	1272	1278	1272	121
180°	1278	1278	1278	1278	1278	



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	469.4	468.9	468.2	467.1	468.0	465.4	464.2	462.1	459.5	458.6	457.5
5°	512.0	513.0	514.0	510.0	510.4	507.7	501.7	496.8	492.8	487.7	484.1
7.5°	563.3	561.1	560.8	558.3	553.9	550.3	544.0	536.0	528.2	519.3	511.9
10°	588.9	589.1	587.4	584.4	579.7	576.3	568.0	560.1	550.5	539.2	531.1
12.5°	608.2	609.0	606.8	602.8	600.5	592.9	586.4	577.0	565.6	556.5	544.2
15°	639.4	637.3	635.9	630.7	626.8	618.9	608.5	598.7	586.3	574.8	563.3
17.5°	669.4	671.2	668.3	663.7	651.3	642.1	628.3	614.8	599.3	583.9	570.2
20°	696.3	697.8	693.5	685.3	670.7	661.5	643.2	625.8	608.0	588.2	573.1
22.5°	729.8	728.6	722.7	710.4	697.7	680.6	660.8	639.7	617.3	594.9	574.9
25°	786.7	778.8	775.2	759.9	743.2	718.1	691.0	660.1	632.3	602.7	577.1
27.5°	818.3	815.8	811.8	801.2	783.6	756.8	724.8	687.1	647.8	610.5	576.9
30°	812.0	812.4	812.7	809.3	798.0	777.9	746.0	705.6	658.8	616.8	578.0
32.5°	755.9	762.7	769.3	777.1	780.2	776.3	756.4	719.8	671.7	624.0	577.4
35°	631.4	633.6	654.8	676.0	704.6	726.8	741.7	725.5	685.0	630.1	576.7
37.5°	492.4	502.6	517.3	541.1	582.4	619.5	667.1	688.9	675.9	632.2	575.4
40°	419.7	429.2	438.8	463.1	497.9	542.7	596.8	642.9	653.7	625.8	570.8
42.5°	363.7	371.1	381.8	400.1	429.2	468.9	520.6	580.9	618.0	607.5	561.3
45°	297.7	302.4	310.6	325.1	346.3	377.3	422.9	488.9	546.3	565.3	538.8
47.5°	254.8	254.8	261.2	271.2	286.4	312.8	346.6	398.2	459.6	505.0	502.9
50°	231.0	230.0	235.1	243.8	255.8	273.4	305.6	346.8	405.8	457.2	471.6
52.5°	210.4	210.6	213.7	220.1	230.2	245.2	269.2	306.5	356.8	409.6	436.6
55°	183.5	182.7	186.3	190.6	198.0	207.8	225.1	253.6	294.5	346.4	381.5
57.5°	158.7	160.9	162.2	165.3	171.4	178.0	192.6	213.4	245.9	290.5	327.5
60°	144.3	146.3	147.5	150.5	155.4	161.1	172.4	189.3	216.6	255.1	291.8
62.5°	131.3	133.0	133.4	136.1	140.1	145.5	154.4	168.7	190.3	223.9	259.8
65°	112.7	112.7	113.4	116.3	118.1	123.0	129.8	140.1	157.5	183.7	214.4
67.5°	94.7	95.6	95.4	96.6	98.3	102.2	107.0	115.5	128.4	147.5	172.1
70°	82.9	83.6	83.5	84.4	86.3	88.7	92.7	100.8	110.0	126.4	147.5
72.5°	72.3	72.6	72.2	73.4	74.5	76.6	81.1	85.4	94.0	107.9	125.2
75°	55.4	55.8	56.2	56.9	58.0	59.2	61.4	65.7	71.4	81.8	92.9
77.5°	41.5	40.8	41.7	41.6	42.2	43.1	45.1	47.4	52.0	58.6	67.2
80°	31.3	31.5	31.5	31.6	32.6	33.2	34.8	36.5	40.1	45.0	51.0
82.5°	22.8	23.3	23.0	23.4	24.1	24.5	25.5	26.9	28.9	32.9	37.2
85°	12.5	11.5	11.9	12.2	12.2	12.5	13.2	13.8	14.9	16.4	18.1
87.5°	8.2	8.3	8.4	8.2	8.2	8.1	8.5	8.3	8.5	8.7	9.0
90°	22.7	22.1	21.4	20.9	20.2	19.4	18.3	17.3	16.2	15.2	13.7
92.5°	21.2	21.0	20.6	20.3	20.1	19.4	18.3	17.3	16.2	15.2	13.9
95°	19.9	19.9	19.9	19.9	19.9	19.4	18.3	17.3	16.2	15.2	23.2
97.5°	19.9	19.9	19.9	19.9	19.9	22.8	28.8	34.7	40.7	46.6	62.5
100°	19.9	20.7	21.6	22.4	23.2	39.4	70.8	102.2	133.5	164.9	164.0
102.5°	119.2	133.5	147.8	162.2	176.5	186.6	192.6	198.4	204.4	210.3	209.9
105°	281.4	281.6	281.8	282.0	282.3	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	354.7	355.4	356.0	356.6	357.3	357.6	357.5	357.5	357.4	357.4	357.0
110°	405.5	405.4	405.1	404.9	404.7	404.9	405.5	406.2	406.8	407.4	407.0



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	451.0	451.3	451.6	451.9	452.2	452.7	453.6	454.4	455.2	455.9	455.7
115°	519.3	520.5	521.8	523.0	524.3	525.4	526.2	527.0	527.9	528.7	528.5
117.5°	592.0	592.6	593.1	593.6	594.2	595.0	596.1	597.2	598.3	599.4	598.6
120°	636.7	637.8	638.9	639.9	641.0	641.7	642.1	642.5	642.9	643.4	642.7
122.5°	679.2	680.4	681.6	682.8	684.0	684.9	685.3	685.7	686.2	686.6	686.3
125°	743.8	744.4	745.1	745.7	746.3	747.1	747.9	748.8	749.6	750.4	750.4
127.5°	798.2	799.7	801.3	802.9	804.5	805.4	805.9	806.3	806.8	807.3	807.4
130°	837.6	838.7	839.8	840.7	841.8	842.7	843.3	843.9	844.6	845.2	845.0
132.5°	874.0	875.1	876.1	877.2	878.2	878.8	878.9	879.1	879.2	879.3	879.8
135°	923.8	925.1	926.3	927.6	928.9	929.8	930.2	930.6	931.0	931.4	931.8
137.5°	973.9	974.9	976.1	977.1	978.3	978.8	978.7	978.6	978.5	978.4	978.8
140°	1003.5	1004.7	1006.0	1007.2	1008.4	1008.9	1008.4	1008.0	1007.6	1007.2	1007.5
142.5°	1031.5	1032.7	1034.0	1035.3	1036.6	1037.1	1037.1	1037.0	1036.9	1036.8	1036.5
145°	1072.6	1073.8	1075.1	1076.4	1077.7	1078.2	1078.0	1077.7	1077.6	1077.3	1077.3
147.5°	1106.5	1108.1	1109.5	1111.1	1112.6	1113.2	1113.0	1112.7	1112.5	1112.2	1112.0
150°	1128.5	1130.2	1131.9	1133.6	1135.2	1135.9	1135.5	1135.1	1134.6	1134.2	1133.8
152.5°	1149.0	1150.5	1152.0	1153.5	1155.0	1155.6	1155.2	1154.7	1154.3	1153.9	1153.5
155°	1175.9	1177.5	1179.2	1181.0	1182.6	1183.2	1182.5	1181.9	1181.3	1180.6	1180.2
157.5°	1198.4	1200.1	1201.8	1203.5	1205.2	1205.7	1205.0	1204.4	1203.6	1203.0	1203.0
160°	1212.8	1214.6	1216.2	1217.9	1219.6	1220.0	1219.1	1218.3	1217.5	1216.6	1216.4
162.5°	1225.7	1227.6	1229.4	1231.3	1233.1	1233.5	1232.3	1231.1	1230.0	1228.7	1228.6
165°	1243.2	1244.8	1246.5	1248.2	1249.9	1250.1	1248.9	1247.6	1246.3	1245.0	1244.8
167.5°	1255.3	1257.2	1259.1	1260.9	1262.9	1263.1	1261.5	1260.0	1258.5	1257.0	1256.8
170°	1262.1	1264.0	1265.9	1267.8	1269.7	1269.8	1268.1	1266.4	1264.8	1263.1	1262.8
172.5°	1266.6	1268.5	1270.5	1272.4	1274.2	1274.4	1272.9	1271.4	1269.9	1268.4	1268.0
175°	1272.5	1274.4	1276.4	1278.2	1280.1	1280.2	1278.6	1276.8	1275.1	1273.5	1273.3
177.5°	1275.9	1277.2	1278.6	1280.0	1281.3	1281.4	1280.3	1279.0	1277.9	1276.7	1276.5
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	456.6	455.6	454.4	452.2	449.7	448.3	446.3	444.9	442.2	439.9	437.5
5°	479.8	474.9	470.4	464.6	458.2	454.0	449.1	443.7	438.0	432.2	425.7
7.5°	503.9	495.1	485.8	475.6	465.7	456.6	447.8	439.4	431.4	421.7	413.5
10°	519.9	509.0	497.3	483.6	470.2	458.5	446.7	436.3	425.7	414.5	404.5
12.5°	536.1	521.5	505.0	489.9	473.9	459.7	445.8	432.5	419.3	406.8	395.1
15°	547.5	534.7	519.4	497.9	479.8	460.4	442.0	424.9	408.8	394.8	380.2
17.5°	555.0	538.4	522.0	501.5	477.8	456.1	435.1	415.5	397.5	379.8	365.7
20°	556.3	539.3	522.2	502.1	477.8	452.9	431.9	408.5	389.1	370.7	353.4
22.5°	555.9	536.6	518.0	497.3	473.5	450.6	425.3	401.4	380.3	362.3	344.2
25°	551.6	531.1	507.7	486.8	463.4	439.1	413.5	388.7	367.2	346.7	328.7
27.5°	548.0	521.5	495.0	470.6	448.0	425.7	401.2	375.8	352.0	331.2	314.3
30°	543.7	514.5	484.7	459.3	436.1	414.5	391.3	366.4	341.5	321.2	303.1
32.5°	539.8	505.7	474.3	446.6	422.1	401.0	379.7	356.0	331.6	311.0	292.9
35°	532.2	492.8	456.8	425.6	399.4	377.7	359.8	337.8	315.4	295.4	278.1
37.5°	522.6	475.9	437.2	404.5	375.8	352.9	336.3	319.4	297.8	278.6	262.9
40°	515.0	463.8	422.9	389.4	359.6	335.9	320.4	304.4	286.6	268.6	252.1
42.5°	505.6	453.0	408.5	372.3	342.9	319.8	303.5	290.0	274.2	257.5	242.1
45°	488.1	433.3	385.1	346.3	316.5	293.7	277.0	266.8	254.9	239.0	226.1
47.5°	462.4	409.7	359.8	319.8	289.0	267.9	252.2	242.4	234.1	222.3	210.5
50°	439.7	392.1	341.5	301.8	271.1	249.8	235.3	226.4	219.3	210.3	200.2
52.5°	414.3	369.9	323.6	284.3	253.9	232.9	218.7	210.9	205.0	198.5	188.7
55°	373.7	336.1	293.1	255.8	227.8	207.2	194.8	188.0	183.1	178.2	172.2
57.5°	329.2	299.7	261.7	227.6	201.7	183.0	171.5	164.9	161.0	158.5	155.0
60°	297.8	272.6	239.9	208.7	183.5	166.9	155.6	150.5	147.3	145.3	142.6
62.5°	268.7	248.0	217.7	189.3	167.2	151.6	141.5	136.5	133.5	132.4	130.3
65°	225.9	209.9	184.8	161.3	142.4	129.1	120.6	115.9	114.0	112.8	113.0
67.5°	183.6	173.9	153.8	133.7	118.6	107.5	100.6	97.0	96.0	94.6	94.6
70°	157.8	150.5	133.5	116.0	102.6	94.0	88.0	84.2	83.2	82.5	82.3
72.5°	135.1	128.7	114.0	100.0	87.9	80.3	75.3	73.1	71.5	71.1	71.0
75°	101.5	98.0	86.3	75.2	66.9	61.6	58.2	56.2	55.0	54.8	55.0
77.5°	72.2	69.1	61.6	53.7	48.5	44.5	41.7	40.9	39.7	39.7	39.5
80°	54.2	52.2	47.5	41.3	36.9	33.5	32.0	30.7	30.3	29.8	30.3
82.5°	39.3	37.1	33.9	29.9	26.3	24.4	22.8	22.4	22.2	21.9	22.0
85°	19.4	19.6	17.7	14.7	13.2	12.1	11.1	11.1	10.9	10.8	10.9
87.5°	9.0	8.5	7.6	6.8	5.7	4.9	4.5	4.2	4.2	4.3	4.8
90°	12.2	10.8	9.3	7.7	6.0	4.3	2.6	1.0	2.6	4.3	6.0
92.5°	12.6	11.3	9.9	9.9	11.1	12.2	13.5	14.6	13.5	12.2	11.1
95°	31.1	39.1	47.2	51.4	52.1	52.7	53.4	54.0	53.4	52.7	52.1
97.5°	78.3	94.1	110.0	117.3	116.2	115.0	113.9	112.8	113.9	115.0	116.2
100°	163.2	162.3	161.5	160.8	160.1	159.5	158.9	158.2	158.9	159.5	160.1
102.5°	209.4	208.8	208.3	207.7	206.8	206.1	205.3	204.5	205.3	206.1	206.8
105°	282.3	282.3	282.3	281.9	281.1	280.2	279.4	278.6	279.4	280.2	281.1
107.5°	356.5	356.1	355.7	355.6	355.6	355.6	355.6	355.6	355.6	355.6	355.6
110°	406.6	406.2	405.8	405.5	405.5	405.5	405.5	405.5	405.5	405.5	405.5



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	455.4	455.2	454.9	454.5	454.0	453.6	453.1	452.6	453.1	453.6	454.0
115°	528.3	528.1	527.9	527.3	526.2	525.1	524.1	523.0	524.1	525.1	526.2
117.5°	597.8	597.0	596.2	595.8	595.9	595.9	596.0	596.0	596.0	595.9	595.9
120°	642.1	641.5	640.8	640.7	640.8	641.1	641.2	641.5	641.2	641.1	640.8
122.5°	686.0	685.7	685.4	684.9	684.0	683.2	682.5	681.7	682.5	683.2	684.0
125°	750.4	750.4	750.4	749.7	748.2	746.7	745.3	743.8	745.3	746.7	748.2
127.5°	807.6	807.6	807.8	807.3	806.2	805.2	804.2	803.2	804.2	805.2	806.2
130°	844.8	844.6	844.3	843.8	842.7	841.6	840.6	839.5	840.6	841.6	842.7
132.5°	880.2	880.7	881.2	880.8	879.5	878.3	877.1	875.9	877.1	878.3	879.5
135°	932.3	932.7	933.1	932.7	931.4	930.2	928.9	927.6	928.9	930.2	931.4
137.5°	979.2	979.6	979.9	979.6	978.4	977.4	976.3	975.2	976.3	977.4	978.4
140°	1007.6	1007.9	1008.0	1008.0	1007.5	1007.1	1006.7	1006.2	1006.7	1007.1	1007.5
142.5°	1036.2	1035.9	1035.6	1035.3	1035.1	1034.9	1034.5	1034.3	1034.5	1034.9	1035.1
145°	1077.3	1077.3	1077.3	1077.1	1076.7	1076.3	1075.9	1075.5	1075.9	1076.3	1076.7
147.5°	1111.7	1111.4	1111.2	1111.1	1111.2	1111.3	1111.3	1111.4	1111.3	1111.3	1111.2
150°	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1133.8	1133.3	1132.9
152.5°	1153.1	1152.7	1152.2	1152.4	1153.4	1154.3	1155.3	1156.2	1155.3	1154.3	1153.4
155°	1179.7	1179.3	1178.9	1179.3	1180.6	1181.9	1183.2	1184.4	1183.2	1181.9	1180.6
157.5°	1202.9	1202.9	1202.8	1203.1	1204.0	1204.7	1205.4	1206.2	1205.4	1204.7	1204.0
160°	1216.2	1216.0	1215.8	1216.3	1217.6	1218.9	1220.1	1221.4	1220.1	1218.9	1217.6
162.5°	1228.3	1228.1	1227.9	1228.4	1229.7	1230.9	1232.2	1233.5	1232.2	1230.9	1229.7
165°	1244.6	1244.4	1244.2	1244.7	1246.0	1247.2	1248.5	1249.8	1248.5	1247.2	1246.0
167.5°	1256.5	1256.4	1256.1	1256.7	1258.0	1259.3	1260.6	1261.9	1260.6	1259.3	1258.0
170°	1262.7	1262.4	1262.2	1262.8	1264.3	1265.8	1267.3	1268.8	1267.3	1265.8	1264.3
172.5°	1267.6	1267.2	1266.8	1267.4	1268.9	1270.3	1271.8	1273.3	1271.8	1270.3	1268.9
175°	1273.1	1272.8	1272.6	1273.2	1274.4	1275.7	1276.9	1278.2	1276.9	1275.7	1274.4
177.5°	1276.4	1276.2	1276.0	1276.4	1277.5	1278.5	1279.4	1280.5	1279.4	1278.5	1277.5
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	436.2	434.5	433.2	430.2	428.4	426.2	424.4	426.4	424.3	425.2	423.8
5°	422.6	417.3	413.5	408.1	403.3	399.0	395.8	395.3	393.7	393.0	390.7
7.5°	406.2	399.6	393.1	386.0	379.9	373.8	369.9	366.6	364.5	361.7	359.7
10°	396.6	387.7	380.2	371.5	363.9	357.3	352.1	349.4	347.0	343.4	342.1
12.5°	384.7	375.5	366.3	357.0	349.8	342.4	337.9	333.9	332.2	328.2	327.8
15°	370.4	356.6	347.6	338.2	328.2	322.1	318.4	314.1	312.2	309.3	307.3
17.5°	353.4	341.0	329.8	320.0	311.4	306.4	301.7	298.7	295.5	293.6	290.2
20°	341.0	329.3	318.0	307.6	301.0	295.2	291.5	288.6	285.2	284.3	280.9
22.5°	330.6	317.7	306.9	298.2	291.0	284.4	280.3	278.3	276.1	273.1	272.5
25°	313.6	300.3	291.1	282.4	276.0	269.9	267.2	264.7	262.4	260.3	259.6
27.5°	299.1	287.1	276.1	268.3	262.7	257.2	254.8	251.8	250.1	248.4	246.4
30°	288.8	276.5	266.9	259.4	253.4	248.5	245.8	243.8	242.3	240.8	239.6
32.5°	278.3	266.9	257.6	250.2	244.2	240.5	238.1	236.7	235.1	233.3	231.8
35°	264.3	251.8	242.8	236.4	231.7	228.9	226.2	224.9	223.1	223.1	221.5
37.5°	248.6	237.8	229.8	224.0	219.8	217.3	214.4	213.5	212.3	211.5	211.0
40°	239.3	229.3	221.8	215.9	211.4	209.3	207.0	205.5	204.8	203.8	203.5
42.5°	229.6	220.0	212.9	207.5	203.5	201.8	199.7	198.6	197.1	195.8	195.6
45°	214.9	205.7	199.1	194.8	191.4	189.3	188.0	185.7	185.0	183.5	183.3
47.5°	201.1	192.2	185.7	182.1	179.2	177.5	175.5	173.2	172.3	171.5	171.5
50°	190.6	182.5	176.5	173.2	170.3	167.9	165.8	164.3	163.7	163.7	164.1
52.5°	180.1	173.2	168.1	164.0	161.3	158.7	156.7	155.8	155.0	155.9	156.5
55°	164.7	157.7	153.9	149.9	147.3	144.3	143.3	143.0	142.4	143.9	144.7
57.5°	148.3	143.4	139.0	135.1	132.7	130.9	129.7	129.5	130.5	131.3	133.7
60°	137.9	132.2	128.3	125.3	122.5	121.3	120.9	120.6	121.3	123.4	126.6
62.5°	126.5	121.9	117.6	115.4	113.2	111.4	111.3	111.5	113.0	115.4	118.6
65°	109.7	105.7	102.9	100.2	98.5	97.4	97.8	98.5	100.2	103.5	107.0
67.5°	92.5	89.8	87.3	85.2	83.6	83.6	84.0	85.1	87.1	90.7	94.0
70°	81.6	78.6	76.5	75.6	74.2	73.5	74.6	76.5	78.2	81.6	84.4
72.5°	70.6	68.0	66.4	65.7	65.1	64.6	65.0	67.0	69.3	72.6	76.0
75°	54.2	53.3	52.2	51.4	50.9	51.3	51.6	53.5	55.4	58.9	62.7
77.5°	39.6	38.6	37.9	37.7	37.4	37.7	38.7	40.1	41.9	44.5	47.4
80°	29.9	29.6	29.2	29.0	29.0	29.2	30.7	31.6	33.3	35.8	38.1
82.5°	21.9	21.6	21.5	21.4	21.6	21.7	22.6	23.8	25.2	27.1	29.0
85°	11.5	11.1	11.7	11.9	11.5	12.1	12.5	13.2	13.8	14.7	15.7
87.5°	5.3	6.0	6.0	6.5	6.8	7.4	7.5	8.3	8.8	9.3	9.3
90°	7.7	9.3	10.8	12.2	13.7	15.2	16.2	17.3	18.3	19.4	20.2
92.5°	9.9	9.9	11.3	12.6	13.9	15.2	16.2	17.3	18.3	19.4	20.1
95°	51.4	47.2	39.1	31.1	23.2	15.2	16.2	17.3	18.3	19.4	19.9
97.5°	117.3	110.0	94.1	78.3	62.5	46.6	40.7	34.7	28.8	22.8	19.9
100°	160.8	161.5	162.3	163.2	164.0	164.9	133.5	102.2	70.8	39.4	23.2
102.5°	207.7	208.3	208.8	209.4	209.9	210.3	204.4	198.4	192.6	186.6	176.5
105°	281.9	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	355.6	355.7	356.1	356.5	357.0	357.4	357.4	357.5	357.5	357.6	357.3
110°	405.5	405.8	406.2	406.6	407.0	407.4	406.8	406.2	405.5	404.9	404.7



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	454.5	454.9	455.2	455.4	455.7	455.9	455.2	454.4	453.6	452.7	452.2
115°	527.3	527.9	528.1	528.3	528.5	528.7	527.9	527.0	526.2	525.4	524.3
117.5°	595.8	596.2	597.0	597.8	598.6	599.4	598.3	597.2	596.1	595.0	594.2
120°	640.7	640.8	641.5	642.1	642.7	643.4	642.9	642.5	642.1	641.7	641.0
122.5°	684.9	685.4	685.7	686.0	686.3	686.6	686.2	685.7	685.3	684.9	684.0
125°	749.7	750.4	750.4	750.4	750.4	750.4	749.6	748.8	747.9	747.1	746.3
127.5°	807.3	807.8	807.6	807.6	807.4	807.3	806.8	806.3	805.9	805.4	804.5
130°	843.8	844.3	844.6	844.8	845.0	845.2	844.6	843.9	843.3	842.7	841.8
132.5°	880.8	881.2	880.7	880.2	879.8	879.3	879.2	879.1	878.9	878.8	878.2
135°	932.7	933.1	932.7	932.3	931.8	931.4	931.0	930.6	930.2	929.8	928.9
137.5°	979.6	979.9	979.6	979.2	978.8	978.4	978.5	978.6	978.7	978.8	978.3
140°	1008.0	1008.0	1007.9	1007.6	1007.5	1007.2	1007.6	1008.0	1008.4	1008.9	1008.4
142.5°	1035.3	1035.6	1035.9	1036.2	1036.5	1036.8	1036.9	1037.0	1037.1	1037.1	1036.6
145°	1077.1	1077.3	1077.3	1077.3	1077.3	1077.3	1077.6	1077.7	1078.0	1078.2	1077.7
147.5°	1111.1	1111.2	1111.4	1111.7	1112.0	1112.2	1112.5	1112.7	1113.0	1113.2	1112.6
150°	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1134.6	1135.1	1135.5	1135.9	1135.2
152.5°	1152.4	1152.2	1152.7	1153.1	1153.5	1153.9	1154.3	1154.7	1155.2	1155.6	1155.0
155°	1179.3	1178.9	1179.3	1179.7	1180.2	1180.6	1181.3	1181.9	1182.5	1183.2	1182.6
157.5°	1203.1	1202.8	1202.9	1202.9	1203.0	1203.0	1203.6	1204.4	1205.0	1205.7	1205.2
160°	1216.3	1215.8	1216.0	1216.2	1216.4	1216.6	1217.5	1218.3	1219.1	1220.0	1219.6
162.5°	1228.4	1227.9	1228.1	1228.3	1228.6	1228.7	1230.0	1231.1	1232.3	1233.5	1233.1
165°	1244.7	1244.2	1244.4	1244.6	1244.8	1245.0	1246.3	1247.6	1248.9	1250.1	1249.9
167.5°	1256.7	1256.1	1256.4	1256.5	1256.8	1257.0	1258.5	1260.0	1261.5	1263.1	1262.9
170°	1262.8	1262.2	1262.4	1262.7	1262.8	1263.1	1264.8	1266.4	1268.1	1269.8	1269.7
172.5°	1267.4	1266.8	1267.2	1267.6	1268.0	1268.4	1269.9	1271.4	1272.9	1274.4	1274.2
175°	1273.2	1272.6	1272.8	1273.1	1273.3	1273.5	1275.1	1276.8	1278.6	1280.2	1280.1
177.5°	1276.4	1276.0	1276.2	1276.4	1276.5	1276.7	1277.9	1279.0	1280.3	1281.4	1281.3
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	422.9	424.0	423.1	424.3	423.1	424.0	422.9	423.8	425.2	424.3	426.4
5°	389.8	388.1	389.2	388.5	389.2	388.1	389.8	390.7	393.0	393.7	395.3
7.5°	359.2	357.6	355.7	354.8	355.7	357.6	359.2	359.7	361.7	364.5	366.6
10°	340.1	337.9	337.8	336.5	337.8	337.9	340.1	342.1	343.4	347.0	349.4
12.5°	326.0	324.1	322.0	321.4	322.0	324.1	326.0	327.8	328.2	332.2	333.9
15°	306.1	304.6	303.3	304.4	303.3	304.6	306.1	307.3	309.3	312.2	314.1
17.5°	289.6	288.4	288.1	286.7	288.1	288.4	289.6	290.2	293.6	295.5	298.7
20°	279.2	278.3	278.7	276.1	278.7	278.3	279.2	280.9	284.3	285.2	288.6
22.5°	270.9	269.0	268.8	268.3	268.8	269.0	270.9	272.5	273.1	276.1	278.3
25°	257.9	257.0	256.0	257.0	256.0	257.0	257.9	259.6	260.3	262.4	264.7
27.5°	246.5	245.4	245.2	245.3	245.2	245.4	246.5	246.4	248.4	250.1	251.8
30°	239.6	237.7	237.9	237.7	237.9	237.7	239.6	239.6	240.8	242.3	243.8
32.5°	232.1	230.8	230.6	230.2	230.6	230.8	232.1	231.8	233.3	235.1	236.7
35°	220.9	220.9	220.0	220.0	220.0	220.9	220.9	221.5	223.1	223.1	224.9
37.5°	210.5	210.3	209.8	209.9	209.8	210.3	210.5	211.0	211.5	212.3	213.5
40°	202.7	202.5	201.9	200.8	201.9	202.5	202.7	203.5	203.8	204.8	205.5
42.5°	195.2	194.5	194.3	193.9	194.3	194.5	195.2	195.6	195.8	197.1	198.6
45°	183.3	183.3	183.0	182.7	183.0	183.3	183.3	183.3	183.5	185.0	185.7
47.5°	171.8	172.1	172.8	172.7	172.8	172.1	171.8	171.5	171.5	172.3	173.2
50°	164.9	165.0	165.6	165.8	165.6	165.0	164.9	164.1	163.7	163.7	164.3
52.5°	157.2	158.2	159.0	158.8	159.0	158.2	157.2	156.5	155.9	155.0	155.8
55°	146.3	147.7	149.0	149.2	149.0	147.7	146.3	144.7	143.9	142.4	143.0
57.5°	135.7	137.5	138.9	139.4	138.9	137.5	135.7	133.7	131.3	130.5	129.5
60°	128.5	130.9	132.6	133.4	132.6	130.9	128.5	126.6	123.4	121.3	120.6
62.5°	121.6	124.3	126.0	126.1	126.0	124.3	121.6	118.6	115.4	113.0	111.5
65°	110.2	113.0	114.5	115.7	114.5	113.0	110.2	107.0	103.5	100.2	98.5
67.5°	98.0	100.9	102.5	103.4	102.5	100.9	98.0	94.0	90.7	87.1	85.1
70°	89.1	92.0	94.2	95.0	94.2	92.0	89.1	84.4	81.6	78.2	76.5
72.5°	80.4	82.9	84.7	85.6	84.7	82.9	80.4	76.0	72.6	69.3	67.0
75°	65.1	68.6	70.3	71.2	70.3	68.6	65.1	62.7	58.9	55.4	53.5
77.5°	50.2	53.3	54.4	54.9	54.4	53.3	50.2	47.4	44.5	41.9	40.1
80°	40.3	42.2	43.5	43.7	43.5	42.2	40.3	38.1	35.8	33.3	31.6
82.5°	31.0	32.5	32.9	33.4	32.9	32.5	31.0	29.0	27.1	25.2	23.8
85°	17.0	17.7	17.9	17.7	17.9	17.7	17.0	15.7	14.7	13.8	13.2
87.5°	9.8	9.7	9.9	10.3	9.9	9.7	9.8	9.3	9.3	8.8	8.3
90°	20.9	21.4	22.1	22.7	22.1	21.4	20.9	20.2	19.4	18.3	17.3
92.5°	20.3	20.6	21.0	21.2	21.0	20.6	20.3	20.1	19.4	18.3	17.3
95°	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.4	18.3	17.3
97.5°	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9	22.8	28.8	34.7
100°	22.4	21.6	20.7	19.9	20.7	21.6	22.4	23.2	39.4	70.8	102.2
102.5°	162.2	147.8	133.5	119.2	133.5	147.8	162.2	176.5	186.6	192.6	198.4
105°	282.0	281.8	281.6	281.4	281.6	281.8	282.0	282.3	282.3	282.3	282.3
107.5°	356.6	356.0	355.4	354.7	355.4	356.0	356.6	357.3	357.6	357.5	357.5
110°	404.9	405.1	405.4	405.5	405.4	405.1	404.9	404.7	404.9	405.5	406.2



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	451.9	451.6	451.3	451.0	451.3	451.6	451.9	452.2	452.7	453.6	454.4
115°	523.0	521.8	520.5	519.3	520.5	521.8	523.0	524.3	525.4	526.2	527.0
117.5°	593.6	593.1	592.6	592.0	592.6	593.1	593.6	594.2	595.0	596.1	597.2
120°	639.9	638.9	637.8	636.7	637.8	638.9	639.9	641.0	641.7	642.1	642.5
122.5°	682.8	681.6	680.4	679.2	680.4	681.6	682.8	684.0	684.9	685.3	685.7
125°	745.7	745.1	744.4	743.8	744.4	745.1	745.7	746.3	747.1	747.9	748.8
127.5°	802.9	801.3	799.7	798.2	799.7	801.3	802.9	804.5	805.4	805.9	806.3
130°	840.7	839.8	838.7	837.6	838.7	839.8	840.7	841.8	842.7	843.3	843.9
132.5°	877.2	876.1	875.1	874.0	875.1	876.1	877.2	878.2	878.8	878.9	879.1
135°	927.6	926.3	925.1	923.8	925.1	926.3	927.6	928.9	929.8	930.2	930.6
137.5°	977.1	976.1	974.9	973.9	974.9	976.1	977.1	978.3	978.8	978.7	978.6
140°	1007.2	1006.0	1004.7	1003.5	1004.7	1006.0	1007.2	1008.4	1008.9	1008.4	1008.0
142.5°	1035.3	1034.0	1032.7	1031.5	1032.7	1034.0	1035.3	1036.6	1037.1	1037.1	1037.0
145°	1076.4	1075.1	1073.8	1072.6	1073.8	1075.1	1076.4	1077.7	1078.2	1078.0	1077.7
147.5°	1111.1	1109.5	1108.1	1106.5	1108.1	1109.5	1111.1	1112.6	1113.2	1113.0	1112.7
150°	1133.6	1131.9	1130.2	1128.5	1130.2	1131.9	1133.6	1135.2	1135.9	1135.5	1135.1
152.5°	1153.5	1152.0	1150.5	1149.0	1150.5	1152.0	1153.5	1155.0	1155.6	1155.2	1154.7
155°	1181.0	1179.2	1177.5	1175.9	1177.5	1179.2	1181.0	1182.6	1183.2	1182.5	1181.9
157.5°	1203.5	1201.8	1200.1	1198.4	1200.1	1201.8	1203.5	1205.2	1205.7	1205.0	1204.4
160°	1217.9	1216.2	1214.6	1212.8	1214.6	1216.2	1217.9	1219.6	1220.0	1219.1	1218.3
162.5°	1231.3	1229.4	1227.6	1225.7	1227.6	1229.4	1231.3	1233.1	1233.5	1232.3	1231.1
165°	1248.2	1246.5	1244.8	1243.2	1244.8	1246.5	1248.2	1249.9	1250.1	1248.9	1247.6
167.5°	1260.9	1259.1	1257.2	1255.3	1257.2	1259.1	1260.9	1262.9	1263.1	1261.5	1260.0
170°	1267.8	1265.9	1264.0	1262.1	1264.0	1265.9	1267.8	1269.7	1269.8	1268.1	1266.4
172.5°	1272.4	1270.5	1268.5	1266.6	1268.5	1270.5	1272.4	1274.2	1274.4	1272.9	1271.4
175°	1278.2	1276.4	1274.4	1272.5	1274.4	1276.4	1278.2	1280.1	1280.2	1278.6	1276.8
177.5°	1280.0	1278.6	1277.2	1275.9	1277.2	1278.6	1280.0	1281.3	1281.4	1280.3	1279.0
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	424.4	426.2	428.4	430.2	433.2	434.5	436.2	437.5	439.9	442.2	444.9
5°	395.8	399.0	403.3	408.1	413.5	417.3	422.6	425.7	432.2	438.0	443.7
7.5°	369.9	373.8	379.9	386.0	393.1	399.6	406.2	413.5	421.7	431.4	439.4
10°	352.1	357.3	363.9	371.5	380.2	387.7	396.6	404.5	414.5	425.7	436.3
12.5°	337.9	342.4	349.8	357.0	366.3	375.5	384.7	395.1	406.8	419.3	432.5
15°	318.4	322.1	328.2	338.2	347.6	356.6	370.4	380.2	394.8	408.8	424.9
17.5°	301.7	306.4	311.4	320.0	329.8	341.0	353.4	365.7	379.8	397.5	415.5
20°	291.5	295.2	301.0	307.6	318.0	329.3	341.0	353.4	370.7	389.1	408.5
22.5°	280.3	284.4	291.0	298.2	306.9	317.7	330.6	344.2	362.3	380.3	401.4
25°	267.2	269.9	276.0	282.4	291.1	300.3	313.6	328.7	346.7	367.2	388.7
27.5°	254.8	257.2	262.7	268.3	276.1	287.1	299.1	314.3	331.2	352.0	375.8
30°	245.8	248.5	253.4	259.4	266.9	276.5	288.8	303.1	321.2	341.5	366.4
32.5°	238.1	240.5	244.2	250.2	257.6	266.9	278.3	292.9	311.0	331.6	356.0
35°	226.2	228.9	231.7	236.4	242.8	251.8	264.3	278.1	295.4	315.4	337.8
37.5°	214.4	217.3	219.8	224.0	229.8	237.8	248.6	262.9	278.6	297.8	319.4
40°	207.0	209.3	211.4	215.9	221.8	229.3	239.3	252.1	268.6	286.6	304.4
42.5°	199.7	201.8	203.5	207.5	212.9	220.0	229.6	242.1	257.5	274.2	290.0
45°	188.0	189.3	191.4	194.8	199.1	205.7	214.9	226.1	239.0	254.9	266.8
47.5°	175.5	177.5	179.2	182.1	185.7	192.2	201.1	210.5	222.3	234.1	242.4
50°	165.8	167.9	170.3	173.2	176.5	182.5	190.6	200.2	210.3	219.3	226.4
52.5°	156.7	158.7	161.3	164.0	168.1	173.2	180.1	188.7	198.5	205.0	210.9
55°	143.3	144.3	147.3	149.9	153.9	157.7	164.7	172.2	178.2	183.1	188.0
57.5°	129.7	130.9	132.7	135.1	139.0	143.4	148.3	155.0	158.5	161.0	164.9
60°	120.9	121.3	122.5	125.3	128.3	132.2	137.9	142.6	145.3	147.3	150.5
62.5°	111.3	111.4	113.2	115.4	117.6	121.9	126.5	130.3	132.4	133.5	136.5
65°	97.8	97.4	98.5	100.2	102.9	105.7	109.7	113.0	112.8	114.0	115.9
67.5°	84.0	83.6	83.6	85.2	87.3	89.8	92.5	94.6	94.6	96.0	97.0
70°	74.6	73.5	74.2	75.6	76.5	78.6	81.6	82.3	82.5	83.2	84.2
72.5°	65.0	64.6	65.1	65.7	66.4	68.0	70.6	71.0	71.1	71.5	73.1
75°	51.6	51.3	50.9	51.4	52.2	53.3	54.2	55.0	54.8	55.0	56.2
77.5°	38.7	37.7	37.4	37.7	37.9	38.6	39.6	39.5	39.7	39.7	40.9
80°	30.7	29.2	29.0	29.0	29.2	29.6	29.9	30.3	29.8	30.3	30.7
82.5°	22.6	21.7	21.6	21.4	21.5	21.6	21.9	22.0	21.9	22.2	22.4
85°	12.5	12.1	11.5	11.9	11.7	11.1	11.5	10.9	10.8	10.9	11.1
87.5°	7.5	7.4	6.8	6.5	6.0	6.0	5.3	4.8	4.3	4.2	4.2
90°	16.2	15.2	13.7	12.2	10.8	9.3	7.7	6.0	4.3	2.6	1.0
92.5°	16.2	15.2	13.9	12.6	11.3	9.9	9.9	11.1	12.2	13.5	14.6
95°	16.2	15.2	23.2	31.1	39.1	47.2	51.4	52.1	52.7	53.4	54.0
97.5°	40.7	46.6	62.5	78.3	94.1	110.0	117.3	116.2	115.0	113.9	112.8
100°	133.5	164.9	164.0	163.2	162.3	161.5	160.8	160.1	159.5	158.9	158.2
102.5°	204.4	210.3	209.9	209.4	208.8	208.3	207.7	206.8	206.1	205.3	204.5
105°	282.3	282.3	282.3	282.3	282.3	282.3	281.9	281.1	280.2	279.4	278.6
107.5°	357.4	357.4	357.0	356.5	356.1	355.7	355.6	355.6	355.6	355.6	355.6
110°	406.8	407.4	407.0	406.6	406.2	405.8	405.5	405.5	405.5	405.5	405.5



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	455.2	455.9	455.7	455.4	455.2	454.9	454.5	454.0	453.6	453.1	452.6
115°	527.9	528.7	528.5	528.3	528.1	527.9	527.3	526.2	525.1	524.1	523.0
117.5°	598.3	599.4	598.6	597.8	597.0	596.2	595.8	595.9	595.9	596.0	596.0
120°	642.9	643.4	642.7	642.1	641.5	640.8	640.7	640.8	641.1	641.2	641.5
122.5°	686.2	686.6	686.3	686.0	685.7	685.4	684.9	684.0	683.2	682.5	681.7
125°	749.6	750.4	750.4	750.4	750.4	750.4	749.7	748.2	746.7	745.3	743.8
127.5°	806.8	807.3	807.4	807.6	807.6	807.8	807.3	806.2	805.2	804.2	803.2
130°	844.6	845.2	845.0	844.8	844.6	844.3	843.8	842.7	841.6	840.6	839.5
132.5°	879.2	879.3	879.8	880.2	880.7	881.2	880.8	879.5	878.3	877.1	875.9
135°	931.0	931.4	931.8	932.3	932.7	933.1	932.7	931.4	930.2	928.9	927.6
137.5°	978.5	978.4	978.8	979.2	979.6	979.9	979.6	978.4	977.4	976.3	975.2
140°	1007.6	1007.2	1007.5	1007.6	1007.9	1008.0	1008.0	1007.5	1007.1	1006.7	1006.2
142.5°	1036.9	1036.8	1036.5	1036.2	1035.9	1035.6	1035.3	1035.1	1034.9	1034.5	1034.3
145°	1077.6	1077.3	1077.3	1077.3	1077.3	1077.3	1077.1	1076.7	1076.3	1075.9	1075.5
147.5°	1112.5	1112.2	1112.0	1111.7	1111.4	1111.2	1111.1	1111.2	1111.3	1111.3	1111.4
150°	1134.6	1134.2	1133.8	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2
152.5°	1154.3	1153.9	1153.5	1153.1	1152.7	1152.2	1152.4	1153.4	1154.3	1155.3	1156.2
155°	1181.3	1180.6	1180.2	1179.7	1179.3	1178.9	1179.3	1180.6	1181.9	1183.2	1184.4
157.5°	1203.6	1203.0	1203.0	1202.9	1202.9	1202.8	1203.1	1204.0	1204.7	1205.4	1206.2
160°	1217.5	1216.6	1216.4	1216.2	1216.0	1215.8	1216.3	1217.6	1218.9	1220.1	1221.4
162.5°	1230.0	1228.7	1228.6	1228.3	1228.1	1227.9	1228.4	1229.7	1230.9	1232.2	1233.5
165°	1246.3	1245.0	1244.8	1244.6	1244.4	1244.2	1244.7	1246.0	1247.2	1248.5	1249.8
167.5°	1258.5	1257.0	1256.8	1256.5	1256.4	1256.1	1256.7	1258.0	1259.3	1260.6	1261.9
170°	1264.8	1263.1	1262.8	1262.7	1262.4	1262.2	1262.8	1264.3	1265.8	1267.3	1268.8
172.5°	1269.9	1268.4	1268.0	1267.6	1267.2	1266.8	1267.4	1268.9	1270.3	1271.8	1273.3
175°	1275.1	1273.5	1273.3	1273.1	1272.8	1272.6	1273.2	1274.4	1275.7	1276.9	1278.2
177.5°	1277.9	1276.7	1276.5	1276.4	1276.2	1276.0	1276.4	1277.5	1278.5	1279.4	1280.5
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	446.3	448.3	449.7	452.2	454.4	455.6	456.6	457.5	458.6	459.5	462.1
5°	449.1	454.0	458.2	464.6	470.4	474.9	479.8	484.1	487.7	492.8	496.8
7.5°	447.8	456.6	465.7	475.6	485.8	495.1	503.9	511.9	519.3	528.2	536.0
10°	446.7	458.5	470.2	483.6	497.3	509.0	519.9	531.1	539.2	550.5	560.1
12.5°	445.8	459.7	473.9	489.9	505.0	521.5	536.1	544.2	556.5	565.6	577.0
15°	442.0	460.4	479.8	497.9	519.4	534.7	547.5	563.3	574.8	586.3	598.7
17.5°	435.1	456.1	477.8	501.5	522.0	538.4	555.0	570.2	583.9	599.3	614.8
20°	431.9	452.9	477.8	502.1	522.2	539.3	556.3	573.1	588.2	608.0	625.8
22.5°	425.3	450.6	473.5	497.3	518.0	536.6	555.9	574.9	594.9	617.3	639.7
25°	413.5	439.1	463.4	486.8	507.7	531.1	551.6	577.1	602.7	632.3	660.1
27.5°	401.2	425.7	448.0	470.6	495.0	521.5	548.0	576.9	610.5	647.8	687.1
30°	391.3	414.5	436.1	459.3	484.7	514.5	543.7	578.0	616.8	658.8	705.6
32.5°	379.7	401.0	422.1	446.6	474.3	505.7	539.8	577.4	624.0	671.7	719.8
35°	359.8	377.7	399.4	425.6	456.8	492.8	532.2	576.7	630.1	685.0	725.5
37.5°	336.3	352.9	375.8	404.5	437.2	475.9	522.6	575.4	632.2	675.9	688.9
40°	320.4	335.9	359.6	389.4	422.9	463.8	515.0	570.8	625.8	653.7	642.9
42.5°	303.5	319.8	342.9	372.3	408.5	453.0	505.6	561.3	607.5	618.0	580.9
45°	277.0	293.7	316.5	346.3	385.1	433.3	488.1	538.8	565.3	546.3	488.9
47.5°	252.2	267.9	289.0	319.8	359.8	409.7	462.4	502.9	505.0	459.6	398.2
50°	235.3	249.8	271.1	301.8	341.5	392.1	439.7	471.6	457.2	405.8	346.8
52.5°	218.7	232.9	253.9	284.3	323.6	369.9	414.3	436.6	409.6	356.8	306.5
55°	194.8	207.2	227.8	255.8	293.1	336.1	373.7	381.5	346.4	294.5	253.6
57.5°	171.5	183.0	201.7	227.6	261.7	299.7	329.2	327.5	290.5	245.9	213.4
60°	155.6	166.9	183.5	208.7	239.9	272.6	297.8	291.8	255.1	216.6	189.3
62.5°	141.5	151.6	167.2	189.3	217.7	248.0	268.7	259.8	223.9	190.3	168.7
65°	120.6	129.1	142.4	161.3	184.8	209.9	225.9	214.4	183.7	157.5	140.1
67.5°	100.6	107.5	118.6	133.7	153.8	173.9	183.6	172.1	147.5	128.4	115.5
70°	88.0	94.0	102.6	116.0	133.5	150.5	157.8	147.5	126.4	110.0	100.8
72.5°	75.3	80.3	87.9	100.0	114.0	128.7	135.1	125.2	107.9	94.0	85.4
75°	58.2	61.6	66.9	75.2	86.3	98.0	101.5	92.9	81.8	71.4	65.7
77.5°	41.7	44.5	48.5	53.7	61.6	69.1	72.2	67.2	58.6	52.0	47.4
80°	32.0	33.5	36.9	41.3	47.5	52.2	54.2	51.0	45.0	40.1	36.5
82.5°	22.8	24.4	26.3	29.9	33.9	37.1	39.3	37.2	32.9	28.9	26.9
85°	11.1	12.1	13.2	14.7	17.7	19.6	19.4	18.1	16.4	14.9	13.8
87.5°	4.5	4.9	5.7	6.8	7.6	8.5	9.0	9.0	8.7	8.5	8.3
90°	2.6	4.3	6.0	7.7	9.3	10.8	12.2	13.7	15.2	16.2	17.3
92.5°	13.5	12.2	11.1	9.9	9.9	11.3	12.6	13.9	15.2	16.2	17.3
95°	53.4	52.7	52.1	51.4	47.2	39.1	31.1	23.2	15.2	16.2	17.3
97.5°	113.9	115.0	116.2	117.3	110.0	94.1	78.3	62.5	46.6	40.7	34.7
100°	158.9	159.5	160.1	160.8	161.5	162.3	163.2	164.0	164.9	133.5	102.2
102.5°	205.3	206.1	206.8	207.7	208.3	208.8	209.4	209.9	210.3	204.4	198.4
105°	279.4	280.2	281.1	281.9	282.3	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	355.6	355.6	355.6	355.6	355.7	356.1	356.5	357.0	357.4	357.4	357.5
110°	405.5	405.5	405.5	405.5	405.8	406.2	406.6	407.0	407.4	406.8	406.2



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	453.1	453.6	454.0	454.5	454.9	455.2	455.4	455.7	455.9	455.2	454.4
115°	524.1	525.1	526.2	527.3	527.9	528.1	528.3	528.5	528.7	527.9	527.0
117.5°	596.0	595.9	595.9	595.8	596.2	597.0	597.8	598.6	599.4	598.3	597.2
120°	641.2	641.1	640.8	640.7	640.8	641.5	642.1	642.7	643.4	642.9	642.5
122.5°	682.5	683.2	684.0	684.9	685.4	685.7	686.0	686.3	686.6	686.2	685.7
125°	745.3	746.7	748.2	749.7	750.4	750.4	750.4	750.4	750.4	749.6	748.8
127.5°	804.2	805.2	806.2	807.3	807.8	807.6	807.6	807.4	807.3	806.8	806.3
130°	840.6	841.6	842.7	843.8	844.3	844.6	844.8	845.0	845.2	844.6	843.9
132.5°	877.1	878.3	879.5	880.8	881.2	880.7	880.2	879.8	879.3	879.2	879.1
135°	928.9	930.2	931.4	932.7	933.1	932.7	932.3	931.8	931.4	931.0	930.6
137.5°	976.3	977.4	978.4	979.6	979.9	979.6	979.2	978.8	978.4	978.5	978.6
140°	1006.7	1007.1	1007.5	1008.0	1008.0	1007.9	1007.6	1007.5	1007.2	1007.6	1008.0
142.5°	1034.5	1034.9	1035.1	1035.3	1035.6	1035.9	1036.2	1036.5	1036.8	1036.9	1037.0
145°	1075.9	1076.3	1076.7	1077.1	1077.3	1077.3	1077.3	1077.3	1077.3	1077.6	1077.7
147.5°	1111.3	1111.3	1111.2	1111.1	1111.2	1111.4	1111.7	1112.0	1112.2	1112.5	1112.7
150°	1133.8	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1134.6	1135.1
152.5°	1155.3	1154.3	1153.4	1152.4	1152.2	1152.7	1153.1	1153.5	1153.9	1154.3	1154.7
155°	1183.2	1181.9	1180.6	1179.3	1178.9	1179.3	1179.7	1180.2	1180.6	1181.3	1181.9
157.5°	1205.4	1204.7	1204.0	1203.1	1202.8	1202.9	1202.9	1203.0	1203.0	1203.6	1204.4
160°	1220.1	1218.9	1217.6	1216.3	1215.8	1216.0	1216.2	1216.4	1216.6	1217.5	1218.3
162.5°	1232.2	1230.9	1229.7	1228.4	1227.9	1228.1	1228.3	1228.6	1228.7	1230.0	1231.1
165°	1248.5	1247.2	1246.0	1244.7	1244.2	1244.4	1244.6	1244.8	1245.0	1246.3	1247.6
167.5°	1260.6	1259.3	1258.0	1256.7	1256.1	1256.4	1256.5	1256.8	1257.0	1258.5	1260.0
170°	1267.3	1265.8	1264.3	1262.8	1262.2	1262.4	1262.7	1262.8	1263.1	1264.8	1266.4
172.5°	1271.8	1270.3	1268.9	1267.4	1266.8	1267.2	1267.6	1268.0	1268.4	1269.9	1271.4
175°	1276.9	1275.7	1274.4	1273.2	1272.6	1272.8	1273.1	1273.3	1273.5	1275.1	1276.8
177.5°	1279.4	1278.5	1277.5	1276.4	1276.0	1276.2	1276.4	1276.5	1276.7	1277.9	1279.0
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	464.2	465.4	468.0	467.1	468.2	468.9	469.4
5°	501.7	507.7	510.4	510.0	514.0	513.0	512.0
7.5°	544.0	550.3	553.9	558.3	560.8	561.1	563.3
10°	568.0	576.3	579.7	584.4	587.4	589.1	588.9
12.5°	586.4	592.9	600.5	602.8	606.8	609.0	608.2
15°	608.5	618.9	626.8	630.7	635.9	637.3	639.4
17.5°	628.3	642.1	651.3	663.7	668.3	671.2	669.4
20°	643.2	661.5	670.7	685.3	693.5	697.8	696.3
22.5°	660.8	680.6	697.7	710.4	722.7	728.6	729.8
25°	691.0	718.1	743.2	759.9	775.2	778.8	786.7
27.5°	724.8	756.8	783.6	801.2	811.8	815.8	818.3
30°	746.0	777.9	798.0	809.3	812.7	812.4	812.0
32.5°	756.4	776.3	780.2	777.1	769.3	762.7	755.9
35°	741.7	726.8	704.6	676.0	654.8	633.6	631.4
37.5°	667.1	619.5	582.4	541.1	517.3	502.6	492.4
40°	596.8	542.7	497.9	463.1	438.8	429.2	419.7
42.5°	520.6	468.9	429.2	400.1	381.8	371.1	363.7
45°	422.9	377.3	346.3	325.1	310.6	302.4	297.7
47.5°	346.6	312.8	286.4	271.2	261.2	254.8	254.8
50°	305.6	273.4	255.8	243.8	235.1	230.0	231.0
52.5°	269.2	245.2	230.2	220.1	213.7	210.6	210.4
55°	225.1	207.8	198.0	190.6	186.3	182.7	183.5
57.5°	192.6	178.0	171.4	165.3	162.2	160.9	158.7
60°	172.4	161.1	155.4	150.5	147.5	146.3	144.3
62.5°	154.4	145.5	140.1	136.1	133.4	133.0	131.3
65°	129.8	123.0	118.1	116.3	113.4	112.7	112.7
67.5°	107.0	102.2	98.3	96.6	95.4	95.6	94.7
70°	92.7	88.7	86.3	84.4	83.5	83.6	82.9
72.5°	81.1	76.6	74.5	73.4	72.2	72.6	72.3
75°	61.4	59.2	58.0	56.9	56.2	55.8	55.4
77.5°	45.1	43.1	42.2	41.6	41.7	40.8	41.5
80°	34.8	33.2	32.6	31.6	31.5	31.5	31.3
82.5°	25.5	24.5	24.1	23.4	23.0	23.3	22.8
85°	13.2	12.5	12.2	12.2	11.9	11.5	12.5
87.5°	8.5	8.1	8.2	8.2	8.4	8.3	8.2
90°	18.3	19.4	20.2	20.9	21.4	22.1	22.7
92.5°	18.3	19.4	20.1	20.3	20.6	21.0	21.2
95°	18.3	19.4	19.9	19.9	19.9	19.9	19.9
97.5°	28.8	22.8	19.9	19.9	19.9	19.9	19.9
100°	70.8	39.4	23.2	22.4	21.6	20.7	19.9
102.5°	192.6	186.6	176.5	162.2	147.8	133.5	119.2
105°	282.3	282.3	282.3	282.0	281.8	281.6	281.4
107.5°	357.5	357.6	357.3	356.6	356.0	355.4	354.7
110°	405.5	404.9	404.7	404.9	405.1	405.4	405.5



TEST NUMBER: P333151-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	453.6	452.7	452.2	451.9	451.6	451.3	451.0
115°	526.2	525.4	524.3	523.0	521.8	520.5	519.3
117.5°	596.1	595.0	594.2	593.6	593.1	592.6	592.0
120°	642.1	641.7	641.0	639.9	638.9	637.8	636.7
122.5°	685.3	684.9	684.0	682.8	681.6	680.4	679.2
125°	747.9	747.1	746.3	745.7	745.1	744.4	743.8
127.5°	805.9	805.4	804.5	802.9	801.3	799.7	798.2
130°	843.3	842.7	841.8	840.7	839.8	838.7	837.6
132.5°	878.9	878.8	878.2	877.2	876.1	875.1	874.0
135°	930.2	929.8	928.9	927.6	926.3	925.1	923.8
137.5°	978.7	978.8	978.3	977.1	976.1	974.9	973.9
140°	1008.4	1008.9	1008.4	1007.2	1006.0	1004.7	1003.5
142.5°	1037.1	1037.1	1036.6	1035.3	1034.0	1032.7	1031.5
145°	1078.0	1078.2	1077.7	1076.4	1075.1	1073.8	1072.6
147.5°	1113.0	1113.2	1112.6	1111.1	1109.5	1108.1	1106.5
150°	1135.5	1135.9	1135.2	1133.6	1131.9	1130.2	1128.5
152.5°	1155.2	1155.6	1155.0	1153.5	1152.0	1150.5	1149.0
155°	1182.5	1183.2	1182.6	1181.0	1179.2	1177.5	1175.9
157.5°	1205.0	1205.7	1205.2	1203.5	1201.8	1200.1	1198.4
160°	1219.1	1220.0	1219.6	1217.9	1216.2	1214.6	1212.8
162.5°	1232.3	1233.5	1233.1	1231.3	1229.4	1227.6	1225.7
165°	1248.9	1250.1	1249.9	1248.2	1246.5	1244.8	1243.2
167.5°	1261.5	1263.1	1262.9	1260.9	1259.1	1257.2	1255.3
170°	1268.1	1269.8	1269.7	1267.8	1265.9	1264.0	1262.1
172.5°	1272.9	1274.4	1274.2	1272.4	1270.5	1268.5	1266.6
175°	1278.6	1280.2	1280.1	1278.2	1276.4	1274.4	1272.5
177.5°	1280.3	1281.4	1281.3	1280.0	1278.6	1277.2	1275.9
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2

(END OF REPORT)