

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332705-940

Luminaire Tested: **S124DIP-S1195D1035U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332705-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIP-S1195D1035U940-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7858.1 lumens  
Efficiency: N/A  
Efficacy: 117.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332705-940

CATALOG NUMBER: S124DIP-S1195D1035U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332705-940

CATALOG NUMBER: S124DIP-S1195D1035U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54	49
2	91	83	77	72	84	78	72	68	67	63	60	58	55	52	49	47	45	41
3	83	73	66	60	77	68	62	56	60	54	50	51	47	44	44	41	38	35
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33	30
5	70	58	49	43	65	54	47	41	47	41	37	41	36	33	35	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	37	32	29	32	28	25	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	25	23	20
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	29	24	21	25	21	18	16
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14346	14346	14346
5°	14389	14216	14319
10°	14299	14100	14170
15°	14125	13900	13936
20°	13897	13651	13664
25°	13635	13367	13331
30°	13313	13035	12915
35°	12980	12686	12518
40°	12635	12290	12064
45°	12273	11900	11671
50°	11875	11552	11195
55°	11444	11102	10742
60°	11013	10598	10277
65°	10527	10118	9712
70°	9982	9477	9106
75°	9148	8706	8484
80°	8140	7810	7610
85°	7123	6854	6725



TEST NUMBER: P332705-940

CATALOG NUMBER: S124DIP-S1195D1035U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.3	2.1
10°-20°	471.5	6.0
20°-30°	694.0	8.8
30°-40°	806.8	10.3
40°-50°	806.8	10.3
50°-60°	705.8	9.0
60°-70°	524.1	6.7
70°-80°	297.8	3.8
80°-90°	88.4	1.1
90°-100°	327.3	4.2
100°-110°	681.1	8.7
110°-120°	610.1	7.8
120°-130°	513.2	6.5
130°-140°	427.9	5.4
140°-150°	326.9	4.2
150°-160°	229.8	2.9
160°-170°	135.2	1.7
170°-180°	44.0	0.6
0°-30°	1332.9	17.0
0°-40°	2139.7	27.2
0°-60°	3652.3	46.5
0°-90°	4562.6	58.1
90°-120°	1618.5	20.6
90°-150°	2886.5	36.7
90°-180°	3295.0	41.9
0°-180°	7858.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1777	1777	1777	1777	1777	
5°	1776	1769	1754	1769	1767	168
15°	1690	1684	1663	1671	1667	476
25°	1531	1520	1501	1502	1497	704
35°	1317	1307	1287	1277	1270	823
45°	1075	1064	1042	1027	1022	828
55°	813	808	789	772	763	728
65°	551	544	530	516	508	545
75°	293	286	279	274	272	312
85°	77	77	74	74	73	85
90°	1	7	16	18	19	6
95°	29	93	726	359	217	33
105°	104	151	584	1257	1252	111
115°	183	230	521	1001	1203	182
125°	256	304	518	851	960	227
135°	304	361	514	756	858	235
145°	350	401	511	637	701	220
155°	398	430	497	563	587	183
165°	434	447	476	504	512	122
175°	452	453	457	463	461	43
180°	453	453	453	453	453	



TEST NUMBER: P332705-940

CATALOG NUMBER: S124DIP-S1195D1035U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1781.5	1780.8	1780.0	1779.3	1778.5	1776.7	1774.0	1771.2	1768.4	1765.7	1768.2
5°	1775.6	1774.3	1773.1	1771.8	1770.6	1768.2	1764.7	1761.2	1757.7	1754.3	1757.7
7.5°	1759.1	1757.8	1756.6	1755.2	1754.0	1751.5	1747.6	1743.7	1739.9	1736.0	1738.8
10°	1744.3	1743.0	1741.8	1740.4	1739.2	1736.5	1732.4	1728.3	1724.2	1720.1	1722.6
12.5°	1724.9	1723.7	1722.3	1721.1	1719.8	1717.0	1712.7	1708.3	1704.0	1699.6	1702.4
15°	1690.1	1688.9	1687.7	1686.4	1685.1	1682.1	1677.3	1672.6	1667.9	1663.1	1665.0
17.5°	1648.3	1646.7	1645.1	1643.6	1642.0	1639.0	1634.4	1630.0	1625.5	1621.0	1622.2
20°	1617.6	1616.0	1614.4	1612.8	1611.2	1608.0	1603.3	1598.6	1593.8	1589.0	1590.0
22.5°	1584.5	1582.4	1580.4	1578.2	1576.2	1572.7	1568.0	1563.3	1558.5	1553.7	1555.5
25°	1530.7	1528.5	1526.3	1524.0	1521.8	1518.5	1514.0	1509.7	1505.2	1500.7	1501.1
27.5°	1469.2	1466.9	1464.6	1462.3	1460.1	1456.9	1452.8	1448.7	1444.6	1440.4	1439.7
30°	1428.2	1425.7	1423.1	1420.6	1418.1	1414.7	1410.6	1406.5	1402.4	1398.3	1397.0
32.5°	1384.9	1382.6	1380.4	1378.0	1375.7	1372.4	1368.1	1363.7	1359.3	1355.0	1353.4
35°	1317.1	1314.9	1312.7	1310.5	1308.2	1304.9	1300.5	1296.1	1291.6	1287.2	1285.0
37.5°	1245.6	1243.6	1241.6	1239.6	1237.5	1234.1	1229.4	1224.7	1219.9	1215.1	1212.7
40°	1198.9	1196.4	1193.8	1191.3	1188.8	1185.2	1180.4	1175.6	1170.9	1166.2	1163.0
42.5°	1148.8	1147.3	1145.8	1144.2	1142.7	1139.3	1134.1	1128.8	1123.6	1118.3	1114.6
45°	1075.0	1072.8	1070.6	1068.4	1066.2	1062.6	1057.5	1052.4	1047.3	1042.3	1038.8
47.5°	997.8	996.3	994.8	993.3	991.8	988.7	984.0	979.4	974.6	970.0	966.1
50°	945.5	944.2	942.9	941.6	940.4	937.5	933.1	928.7	924.3	919.8	915.4
52.5°	894.2	892.7	891.2	889.7	888.1	885.0	880.4	875.7	871.0	866.3	862.4
55°	813.1	812.1	811.2	810.2	809.2	806.6	802.1	797.7	793.3	788.8	785.1
57.5°	735.6	734.5	733.4	732.4	731.3	728.5	724.2	719.8	715.4	711.1	707.5
60°	682.1	680.5	678.9	677.3	675.7	672.9	668.8	664.7	660.5	656.4	653.5
62.5°	629.6	628.3	627.0	625.6	624.4	621.5	617.2	612.8	608.4	604.0	601.5
65°	551.1	549.5	547.9	546.3	544.7	542.3	539.2	536.0	532.9	529.7	526.6
67.5°	471.9	470.5	469.0	467.5	466.1	463.8	460.7	457.7	454.7	451.7	448.6
70°	422.9	420.7	418.5	416.3	414.0	411.7	409.1	406.6	404.0	401.5	399.0
72.5°	370.5	368.3	366.0	363.8	361.7	359.5	357.5	355.4	353.5	351.4	349.4
75°	293.3	291.8	290.2	288.6	287.0	285.4	283.8	282.2	280.7	279.1	277.9
77.5°	219.5	218.8	218.2	217.5	216.8	215.7	214.4	212.9	211.6	210.2	209.8
80°	175.1	174.2	173.3	172.3	171.4	170.6	170.0	169.2	168.6	168.0	167.4
82.5°	131.9	131.4	131.0	130.5	130.1	129.8	129.7	129.6	129.4	129.3	128.9
85°	76.9	76.9	76.9	76.9	76.9	76.6	76.0	75.3	74.6	74.0	74.0
87.5°	29.8	29.9	30.1	30.1	30.1	29.8	30.6	30.3	30.4	30.6	30.4
90°	0.9	2.7	5.4	6.2	7.1	7.1	12.5	12.5	14.3	16.1	15.2
92.5°	10.2	14.8	23.2	34.0	47.0	65.5	110.8	179.9	247.1	282.4	235.2
95°	29.3	32.0	40.9	52.5	73.9	111.3	188.7	334.7	547.5	725.5	746.0
97.5°	52.7	52.7	60.4	71.1	89.3	120.7	180.4	300.9	512.4	764.1	937.2
100°	67.7	67.7	73.9	84.5	101.5	130.0	182.5	283.1	464.7	715.7	943.6
102.5°	81.9	83.3	88.8	98.8	115.0	142.0	189.6	278.1	432.7	655.2	890.2
105°	104.2	106.8	111.3	122.0	137.9	163.8	206.5	280.4	405.0	584.0	793.2
107.5°	128.8	130.5	134.9	146.3	161.7	187.1	226.3	293.6	400.0	544.1	714.8
110°	145.1	146.9	151.3	162.0	178.1	202.1	241.2	303.5	401.4	530.6	675.6



TEST NUMBER: P332705-940

CATALOG NUMBER: S124DIP-S1195D1035U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	160.8	162.6	167.7	177.7	193.7	217.8	255.5	314.2	405.7	524.1	653.6
115°	183.4	186.0	192.3	201.2	218.1	242.1	277.8	331.2	413.9	520.8	632.9
117.5°	206.9	209.4	214.9	224.7	240.5	265.5	299.3	348.4	422.7	519.9	623.7
120°	222.6	224.4	230.6	240.3	255.5	280.4	314.2	360.5	429.1	519.9	618.7
122.5°	236.8	238.5	244.8	253.9	270.5	294.6	328.5	371.9	435.5	519.2	613.0
125°	255.5	259.0	264.4	274.2	291.1	316.0	348.0	389.1	445.1	518.1	603.6
127.5°	272.1	274.9	281.3	292.5	310.1	335.3	366.2	403.8	452.7	516.1	590.9
130°	281.3	284.9	291.9	305.3	322.3	348.0	378.4	413.0	458.4	515.4	583.1
132.5°	290.5	293.4	302.6	315.3	333.7	358.0	388.3	422.3	463.4	514.7	576.0
135°	303.5	307.1	316.0	331.2	349.8	373.0	402.3	434.4	470.9	513.6	565.3
137.5°	316.6	319.9	329.8	344.1	363.6	385.7	413.0	443.0	475.4	513.4	556.0
140°	325.8	328.5	338.3	353.4	372.1	393.5	420.2	448.6	478.9	512.7	551.1
142.5°	335.8	338.5	347.5	361.9	380.0	400.6	426.6	452.9	481.8	512.7	546.8
145°	349.8	352.5	361.4	373.9	390.8	410.4	433.5	457.5	483.4	511.0	539.5
147.5°	365.7	366.6	374.4	387.3	401.3	418.9	440.7	461.6	484.3	507.7	532.9
150°	375.7	376.6	383.7	394.4	407.7	424.6	444.3	463.8	484.3	505.6	527.9
152.5°	385.0	385.1	392.3	402.2	414.1	429.6	447.1	465.2	482.9	502.0	522.2
155°	397.9	398.8	404.1	413.0	422.8	436.2	451.3	466.5	480.7	496.8	513.6
157.5°	410.5	410.5	415.5	422.5	431.1	441.6	454.3	466.5	478.4	491.2	504.9
160°	418.4	418.4	422.0	428.2	435.3	445.1	455.8	466.5	476.3	487.0	498.6
162.5°	425.5	424.8	427.7	433.2	439.6	447.3	457.2	466.5	474.1	482.7	492.8
165°	433.5	433.5	435.3	439.8	444.3	449.5	457.5	464.7	470.0	476.3	483.4
167.5°	441.6	440.7	441.6	445.0	447.5	451.5	457.4	462.5	465.7	469.8	474.8
170°	445.1	444.3	445.1	447.8	449.5	452.2	456.6	461.1	462.9	465.6	469.1
172.5°	448.6	447.8	447.9	449.9	450.9	452.9	455.9	459.7	460.0	461.3	464.1
175°	452.2	451.3	451.3	452.2	453.1	453.1	454.9	457.5	456.6	456.6	458.4
177.5°	453.8	453.1	452.4	453.1	453.1	453.1	453.8	455.2	453.8	453.8	454.5
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1



TEST NUMBER: P332705-940

CATALOG NUMBER: S124DIP-S1195D1035U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0	1777.0
2.5°	1770.7	1773.3	1775.8	1776.9	1776.6	1776.4	1776.1	1775.8
5°	1761.2	1764.7	1768.2	1769.6	1769.0	1768.4	1767.7	1767.0
7.5°	1741.6	1744.4	1747.1	1748.4	1748.0	1747.6	1747.2	1746.9
10°	1725.1	1727.7	1730.2	1731.2	1730.5	1729.9	1729.2	1728.6
12.5°	1705.1	1707.9	1710.7	1711.6	1710.7	1709.9	1709.0	1708.1
15°	1666.9	1668.8	1670.7	1671.2	1670.3	1669.3	1668.3	1667.4
17.5°	1623.4	1624.6	1625.8	1626.0	1625.4	1624.8	1624.2	1623.5
20°	1591.0	1591.9	1592.9	1593.0	1592.4	1591.8	1591.2	1590.5
22.5°	1557.2	1558.9	1560.6	1560.9	1559.8	1558.6	1557.5	1556.3
25°	1501.5	1501.7	1502.1	1501.6	1500.3	1499.1	1497.8	1496.6
27.5°	1438.9	1438.2	1437.3	1436.2	1434.6	1433.1	1431.5	1429.9
30°	1395.7	1394.5	1393.2	1391.8	1390.2	1388.7	1387.1	1385.5
32.5°	1351.9	1350.4	1348.9	1347.4	1345.8	1344.2	1342.6	1341.0
35°	1282.8	1280.6	1278.4	1276.5	1274.9	1273.3	1271.7	1270.2
37.5°	1210.3	1207.9	1205.5	1203.3	1201.2	1199.1	1197.0	1194.9
40°	1159.8	1156.6	1153.5	1151.1	1149.6	1148.0	1146.4	1144.8
42.5°	1111.0	1107.3	1103.7	1101.3	1100.2	1099.1	1098.1	1097.0
45°	1035.4	1031.9	1028.4	1026.2	1025.2	1024.2	1023.3	1022.3
47.5°	962.2	958.2	954.3	951.1	948.7	946.3	943.9	941.5
50°	911.0	906.5	902.1	898.9	897.1	895.2	893.2	891.4
52.5°	858.4	854.5	850.6	847.5	845.1	842.7	840.3	837.9
55°	781.2	777.5	773.6	770.8	768.9	767.0	765.1	763.2
57.5°	703.9	700.3	696.7	693.9	692.1	690.3	688.4	686.6
60°	650.7	647.9	645.1	642.8	641.2	639.6	638.1	636.5
62.5°	598.8	596.2	593.6	591.6	590.0	588.4	586.8	585.2
65°	523.3	520.2	517.0	514.7	513.1	511.5	509.9	508.4
67.5°	445.6	442.6	439.5	437.7	437.3	436.8	436.4	436.0
70°	396.5	394.0	391.4	389.7	388.7	387.8	386.8	385.8
72.5°	347.4	345.4	343.3	341.8	340.9	339.9	338.9	338.0
75°	276.5	275.3	274.0	273.2	273.0	272.6	272.2	272.0
77.5°	209.4	209.0	208.7	208.0	207.2	206.4	205.5	204.7
80°	166.7	166.1	165.5	165.1	164.7	164.3	164.1	163.7
82.5°	128.5	128.1	127.8	127.4	127.1	126.8	126.4	126.2
85°	74.0	74.0	74.0	73.9	73.6	73.2	72.9	72.6
87.5°	30.6	30.8	30.9	30.9	31.1	31.3	31.1	31.1
90°	16.1	16.9	17.8	17.8	18.7	19.6	18.7	18.7
92.5°	174.9	131.6	104.7	86.9	76.4	71.6	68.6	68.6
95°	659.6	521.7	402.3	316.0	272.4	244.8	228.8	217.2
97.5°	974.6	923.3	836.2	743.3	679.4	625.8	599.1	580.6
100°	1073.6	1091.4	1047.8	981.9	904.5	850.2	823.4	816.4
102.5°	1068.6	1156.9	1169.6	1142.1	1094.6	1055.3	1027.2	1021.5
105°	997.0	1151.0	1239.1	1275.7	1277.5	1270.3	1257.8	1252.5
107.5°	895.4	1059.4	1183.5	1262.8	1306.8	1327.1	1336.1	1338.4
110°	834.1	988.1	1117.2	1215.1	1278.4	1315.7	1331.8	1339.8





TEST NUMBER: P332705-940

CATALOG NUMBER: S124DIP-S1195D1035U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	789.3	925.4	1047.4	1145.3	1217.1	1262.3	1284.8	1297.7
115°	744.2	853.7	957.9	1043.3	1113.7	1167.1	1195.5	1202.7
117.5°	722.1	812.8	894.7	967.1	1027.2	1072.0	1100.8	1106.3
120°	712.1	795.0	866.2	929.3	980.1	1019.3	1042.4	1052.2
122.5°	703.6	783.5	848.4	903.7	946.6	980.1	999.7	1009.5
125°	689.0	765.5	827.0	875.9	911.6	937.4	954.3	959.7
127.5°	671.2	744.4	805.7	852.1	887.9	910.9	925.1	930.4
130°	657.0	727.3	787.8	835.0	871.5	893.8	908.0	913.4
132.5°	642.0	708.1	767.1	814.4	850.2	875.2	888.8	894.1
135°	621.3	679.2	733.5	778.0	813.7	838.6	852.8	858.2
137.5°	602.7	651.7	697.4	737.6	770.9	795.5	807.3	813.7
140°	592.0	633.8	673.9	711.2	742.4	762.1	774.5	781.6
142.5°	582.0	618.8	653.3	685.6	713.2	731.4	742.4	747.4
145°	567.9	598.2	624.9	649.9	672.1	687.2	696.2	700.6
147.5°	556.3	580.4	601.8	621.3	637.8	650.8	657.5	659.1
150°	549.3	569.7	587.5	603.6	617.8	629.4	634.7	635.6
152.5°	541.4	559.0	575.4	588.6	600.7	610.1	613.3	614.2
155°	529.7	543.9	557.2	567.9	576.8	584.0	586.7	586.7
157.5°	517.0	529.0	540.2	548.8	555.4	560.8	562.4	562.4
160°	509.2	519.0	528.8	535.9	541.3	546.6	547.5	547.5
162.5°	501.3	509.7	517.4	523.8	527.7	533.1	534.0	533.2
165°	490.5	495.9	502.0	506.5	510.1	513.6	512.7	511.8
167.5°	480.0	484.1	489.1	491.8	493.6	495.9	495.7	495.0
170°	473.6	476.3	479.8	482.5	484.3	485.2	484.3	484.3
172.5°	467.9	469.8	472.0	473.9	475.0	475.9	475.0	473.6
175°	460.2	461.1	462.9	462.9	462.9	464.7	462.9	461.1
177.5°	455.2	455.9	455.9	456.6	455.9	456.6	455.2	453.8
180°	453.1	453.1	453.1	453.1	453.1	453.1	453.1	453.1

(END OF REPORT)