

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333185-930

Luminaire Tested: **S125DIP-S610D810U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333185-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S610D810U930-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4325.2 lumens  
Efficiency: N/A  
Efficacy: 112.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333185-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333185-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	40	38	33
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24	21
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5057	5057	5057
5°	5068	5020	5052
10°	5037	4985	5013
15°	4983	4924	4945
20°	4904	4841	4849
25°	4821	4741	4737
30°	4716	4633	4610
35°	4606	4518	4454
40°	4491	4392	4330
45°	4369	4277	4192
50°	4233	4140	4015
55°	4102	3983	3871
60°	3945	3825	3689
65°	3758	3636	3512
70°	3580	3416	3299
75°	3261	3154	3047
80°	2901	2856	2786
85°	2527	2571	2438



TEST NUMBER: P333185-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.8	1.7
10°-20°	208.5	4.8
20°-30°	307.9	7.1
30°-40°	359.3	8.3
40°-50°	360.9	8.3
50°-60°	316.8	7.3
60°-70°	236.0	5.5
70°-80°	135.0	3.1
80°-90°	41.0	0.9
90°-100°	54.9	1.3
100°-110°	162.0	3.7
110°-120°	274.4	6.3
120°-130°	361.2	8.4
130°-140°	404.7	9.4
140°-150°	396.7	9.2
150°-160°	333.1	7.7
160°-170°	221.5	5.1
170°-180°	77.5	1.8
0°-30°	590.3	13.6
0°-40°	949.6	22.0
0°-60°	1627.2	37.6
0°-90°	2039.3	47.1
90°-120°	491.4	11.4
90°-150°	1653.9	38.2
90°-180°	2286.0	52.9
0°-180°	4325.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	783	783	783	783	783	
5°	782	780	774	780	779	74
15°	745	743	736	739	740	210
25°	676	673	665	666	665	311
35°	584	581	573	570	565	365
45°	478	476	468	461	459	368
55°	364	362	354	348	344	325
65°	246	244	238	232	230	244
75°	131	129	126	124	122	139
85°	34	35	35	34	33	38
90°	1	6	10	13	15	4
95°	41	43	49	53	55	44
105°	145	149	152	156	158	155
115°	275	277	279	278	277	272
125°	401	405	405	404	404	359
135°	522	525	526	526	523	402
145°	632	634	636	636	634	395
155°	723	723	724	726	723	333
165°	786	785	786	788	784	222
175°	817	815	815	818	814	78
180°	819	819	819	819	819	



TEST NUMBER: P333185-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	785.0	784.6	784.3	784.0	783.7	782.9	781.9	780.7	779.7	778.5	779.7
5°	781.8	781.5	781.2	780.9	780.6	779.8	778.4	777.1	775.7	774.3	775.6
7.5°	774.5	774.3	774.0	773.7	773.5	772.6	771.0	769.6	768.0	766.5	767.7
10°	768.1	767.8	767.6	767.3	767.0	766.1	764.6	763.1	761.6	760.1	761.2
12.5°	760.2	759.7	759.2	758.7	758.2	757.2	755.9	754.5	753.0	751.6	752.5
15°	745.2	744.8	744.4	744.0	743.6	742.6	741.1	739.6	738.0	736.5	737.2
17.5°	728.0	727.4	726.8	726.2	725.5	724.5	722.9	721.3	719.7	718.2	719.0
20°	713.6	713.3	713.1	712.8	712.5	711.5	709.7	707.9	706.1	704.3	705.3
22.5°	699.2	698.7	698.2	697.7	697.2	696.2	694.5	692.8	691.1	689.4	690.1
25°	676.5	675.7	675.1	674.4	673.7	672.5	670.7	668.9	667.1	665.3	665.6
27.5°	649.8	649.4	649.0	648.6	648.2	647.0	645.1	643.4	641.5	639.7	639.7
30°	632.4	632.0	631.6	631.2	630.8	629.6	627.5	625.4	623.4	621.3	621.0
32.5°	613.6	613.0	612.4	611.7	611.1	609.8	608.1	606.2	604.3	602.5	602.0
35°	584.2	583.6	583.0	582.5	582.0	580.7	578.8	576.8	574.9	573.0	572.3
37.5°	553.5	552.9	552.2	551.5	550.8	549.5	547.7	545.9	544.0	542.3	541.3
40°	532.7	532.1	531.3	530.7	529.9	528.6	526.8	524.8	522.9	521.0	519.8
42.5°	510.5	509.9	509.2	508.7	508.1	506.9	504.9	503.0	501.1	499.1	498.1
45°	478.3	477.7	477.1	476.5	476.1	474.9	473.3	471.7	469.9	468.3	466.7
47.5°	443.5	443.5	443.6	443.6	443.6	442.6	440.7	438.7	436.8	434.7	433.1
50°	421.3	420.8	420.4	420.0	419.6	418.6	416.9	415.2	413.6	412.0	410.2
52.5°	398.4	398.1	397.9	397.5	397.2	396.2	394.4	392.6	390.9	389.1	387.6
55°	364.3	363.8	363.4	363.0	362.6	361.4	359.5	357.6	355.6	353.7	352.5
57.5°	328.2	328.0	327.8	327.5	327.3	326.4	324.7	323.1	321.5	319.9	318.3
60°	305.4	304.8	304.3	303.7	303.2	302.1	300.7	299.1	297.6	296.1	294.7
62.5°	281.6	281.2	280.7	280.3	279.8	279.0	277.7	276.4	275.1	273.8	272.3
65°	245.9	245.6	245.4	245.1	244.8	243.9	242.4	240.9	239.4	237.9	236.6
67.5°	211.3	210.8	210.2	209.6	209.0	208.2	207.1	205.9	204.8	203.7	202.6
70°	189.6	188.9	188.2	187.5	186.8	185.8	184.6	183.4	182.1	180.9	180.0
72.5°	165.8	165.3	164.9	164.4	163.9	163.2	162.5	161.7	160.9	160.0	159.1
75°	130.7	130.4	130.1	129.9	129.6	129.1	128.4	127.8	127.0	126.4	126.0
77.5°	98.4	98.2	98.2	98.0	97.9	97.7	97.3	96.9	96.5	96.1	95.9
80°	78.0	78.0	78.0	78.0	78.0	77.9	77.6	77.4	77.1	76.8	76.6
82.5°	60.3	60.0	59.8	59.5	59.4	59.2	59.1	59.1	59.0	58.9	58.7
85°	34.1	34.2	34.3	34.5	34.7	34.7	34.7	34.7	34.7	34.7	34.6
87.5°	13.5	13.7	13.9	14.2	14.4	14.6	14.7	14.8	14.8	14.9	15.1
90°	0.7	1.8	2.9	4.1	5.1	6.2	7.3	8.2	9.2	10.2	10.9
92.5°	15.4	16.2	17.0	17.8	18.6	19.6	20.8	22.0	23.2	24.5	25.4
95°	41.4	41.7	42.0	42.3	42.6	43.5	44.8	46.2	47.7	49.1	50.1
97.5°	68.9	69.0	69.1	69.2	69.3	70.4	72.3	74.3	76.2	78.2	79.1
100°	89.3	89.3	89.3	89.3	89.3	90.2	92.0	93.8	95.7	97.5	98.8
102.5°	111.2	111.8	112.3	112.9	113.5	114.2	115.1	116.1	117.0	118.0	119.4
105°	145.4	146.1	146.8	147.5	148.2	149.0	149.9	150.7	151.5	152.4	153.2
107.5°	183.1	183.8	184.5	185.2	186.0	186.6	187.3	187.9	188.6	189.2	189.6
110°	209.1	209.9	210.5	211.2	212.0	212.5	213.0	213.4	213.8	214.2	214.7



TEST NUMBER: P333185-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	235.6	236.0	236.4	236.8	237.1	237.6	238.1	238.6	239.2	239.7	239.9
115°	274.8	275.3	275.9	276.5	277.0	277.4	277.8	278.0	278.3	278.6	278.4
117.5°	314.1	314.3	314.5	314.8	315.0	315.4	315.6	315.8	316.1	316.3	316.4
120°	338.5	339.2	340.0	340.6	341.4	341.8	341.9	342.1	342.2	342.3	342.3
122.5°	365.0	365.3	365.6	365.8	366.1	366.4	366.7	367.1	367.5	367.9	367.7
125°	401.0	401.9	402.7	403.6	404.4	404.9	405.0	405.2	405.3	405.4	405.2
127.5°	439.3	439.8	440.2	440.7	441.2	441.5	441.6	441.8	442.1	442.2	442.1
130°	462.2	462.9	463.7	464.3	465.0	465.5	465.8	466.1	466.4	466.7	466.5
132.5°	485.2	486.3	487.5	488.6	489.8	490.3	490.3	490.2	490.2	490.2	490.0
135°	521.5	522.4	523.2	524.1	524.9	525.4	525.5	525.7	525.8	525.9	525.9
137.5°	555.7	556.5	557.3	558.2	559.0	559.5	559.9	560.1	560.4	560.8	560.9
140°	577.6	578.3	579.0	579.8	580.4	581.0	581.4	581.9	582.3	582.7	583.0
142.5°	599.6	600.1	600.7	601.3	601.9	602.5	603.0	603.6	604.1	604.6	604.8
145°	631.8	632.3	632.9	633.5	634.1	634.5	635.0	635.4	635.9	636.3	636.3
147.5°	661.6	661.9	662.3	662.6	662.8	663.2	663.6	663.9	664.2	664.6	664.9
150°	681.5	681.3	681.3	681.1	680.9	681.2	681.8	682.3	682.9	683.5	683.5
152.5°	697.8	698.1	698.2	698.5	698.6	698.9	699.0	699.3	699.5	699.8	700.1
155°	722.9	722.9	722.9	722.9	722.9	723.0	723.2	723.3	723.4	723.6	724.1
157.5°	745.4	745.1	744.8	744.4	744.1	744.0	744.2	744.4	744.4	744.6	745.2
160°	758.6	758.2	757.8	757.4	756.9	756.8	756.9	757.1	757.2	757.4	758.0
162.5°	770.4	770.1	769.7	769.5	769.2	769.0	769.0	769.1	769.1	769.2	769.8
165°	786.1	785.8	785.5	785.2	785.0	784.9	785.0	785.1	785.3	785.5	786.0
167.5°	799.3	798.7	798.2	797.6	797.0	796.8	796.8	796.8	796.8	796.8	797.6
170°	806.5	805.9	805.4	804.8	804.2	803.9	803.9	803.9	803.9	803.9	804.8
172.5°	811.5	811.0	810.4	809.8	809.3	809.0	809.0	809.0	809.0	809.0	809.8
175°	817.3	816.8	816.2	815.6	815.1	814.7	814.7	814.7	814.7	814.7	815.6
177.5°	820.3	819.8	819.4	818.9	818.4	818.2	818.1	817.9	817.8	817.7	818.4
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333185-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	780.7	781.9	782.9	783.4	783.3	783.2	783.1	783.0
5°	776.8	778.0	779.3	779.8	779.7	779.6	779.4	779.3
7.5°	768.9	770.1	771.4	771.9	771.8	771.6	771.5	771.4
10°	762.3	763.4	764.5	765.0	764.8	764.7	764.5	764.4
12.5°	753.4	754.3	755.1	755.6	755.5	755.5	755.5	755.5
15°	737.9	738.6	739.3	739.6	739.6	739.6	739.6	739.6
17.5°	719.9	720.7	721.6	721.7	721.0	720.3	719.7	718.9
20°	706.2	707.2	708.2	708.3	707.6	706.9	706.2	705.6
22.5°	690.7	691.4	692.0	692.1	691.6	691.1	690.6	690.2
25°	665.9	666.1	666.4	666.3	665.9	665.5	665.1	664.7
27.5°	639.8	639.8	639.8	639.7	639.3	638.9	638.5	638.1
30°	620.8	620.5	620.2	619.9	619.5	619.1	618.6	618.2
32.5°	601.5	601.0	600.5	599.9	599.2	598.4	597.6	596.9
35°	571.6	571.0	570.2	569.3	568.3	567.1	566.1	564.9
37.5°	540.2	539.2	538.2	537.4	536.7	536.1	535.5	534.8
40°	518.4	517.2	516.0	515.2	514.8	514.4	514.0	513.6
42.5°	496.9	495.8	494.6	493.7	493.1	492.5	491.9	491.2
45°	465.0	463.3	461.7	460.6	460.2	459.8	459.4	459.0
47.5°	431.4	429.7	428.0	426.7	425.7	424.8	423.8	422.8
50°	408.4	406.6	404.8	403.4	402.4	401.5	400.5	399.6
52.5°	386.0	384.4	382.9	381.6	380.5	379.4	378.3	377.2
55°	351.2	350.0	348.8	347.6	346.7	345.7	344.8	343.8
57.5°	316.7	315.1	313.5	312.4	311.9	311.4	310.9	310.4
60°	293.3	292.0	290.6	289.4	288.5	287.5	286.5	285.6
62.5°	270.8	269.4	267.8	266.8	266.0	265.2	264.5	263.7
65°	235.4	234.2	232.9	232.0	231.5	230.9	230.4	229.8
67.5°	201.6	200.6	199.5	198.8	198.4	198.1	197.8	197.5
70°	179.2	178.4	177.6	176.9	176.3	175.8	175.2	174.7
72.5°	158.2	157.3	156.3	155.6	155.0	154.5	153.9	153.4
75°	125.6	125.1	124.7	124.3	123.7	123.1	122.6	122.1
77.5°	95.6	95.4	95.1	94.8	94.4	94.1	93.7	93.3
80°	76.6	76.4	76.2	76.1	75.7	75.5	75.3	74.9
82.5°	58.5	58.2	58.0	57.8	57.8	57.7	57.6	57.6
85°	34.4	34.2	34.2	33.9	33.7	33.3	33.1	32.9
87.5°	15.2	15.3	15.5	15.5	15.3	15.2	15.1	14.9
90°	11.6	12.3	13.0	13.6	14.0	14.4	14.8	15.3
92.5°	26.3	27.3	28.2	28.9	29.2	29.4	29.8	30.1
95°	51.0	52.1	53.1	53.7	54.0	54.3	54.5	54.8
97.5°	80.1	81.0	81.9	82.4	82.6	82.8	83.0	83.2
100°	100.1	101.3	102.6	103.5	103.7	104.0	104.3	104.5
102.5°	120.7	122.1	123.5	124.4	124.8	125.1	125.6	126.0
105°	154.1	154.9	155.8	156.4	156.9	157.3	157.7	158.1
107.5°	190.0	190.5	190.9	191.1	191.1	191.0	191.0	191.0
110°	215.1	215.5	215.9	216.1	215.9	215.7	215.6	215.5





TEST NUMBER: P333185-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	240.1	240.3	240.5	240.5	240.2	239.9	239.7	239.5
115°	278.3	278.2	278.0	277.9	277.8	277.6	277.4	277.4
117.5°	316.6	316.7	316.8	316.6	316.0	315.4	314.9	314.3
120°	342.3	342.3	342.3	342.1	341.5	341.0	340.4	339.8
122.5°	367.6	367.5	367.4	367.1	366.6	366.2	365.7	365.3
125°	404.9	404.6	404.3	404.1	404.0	403.8	403.7	403.6
127.5°	441.9	441.7	441.6	441.4	441.2	440.8	440.6	440.3
130°	466.4	466.3	466.1	465.9	465.6	465.3	465.0	464.7
132.5°	489.8	489.7	489.6	489.3	488.9	488.5	488.1	487.7
135°	525.9	525.9	525.9	525.7	525.1	524.6	524.0	523.4
137.5°	561.1	561.3	561.4	561.2	560.4	559.8	559.1	558.3
140°	583.3	583.5	583.8	583.6	582.9	582.2	581.5	580.8
142.5°	605.0	605.1	605.3	605.0	604.3	603.6	602.9	602.2
145°	636.3	636.3	636.3	636.0	635.6	635.2	634.8	634.3
147.5°	665.2	665.6	665.9	665.6	664.6	663.7	662.8	661.8
150°	683.5	683.5	683.5	683.3	683.0	682.7	682.4	682.2
152.5°	700.4	700.7	701.1	701.0	700.5	700.0	699.5	699.0
155°	724.7	725.3	725.9	725.8	725.0	724.4	723.7	722.9
157.5°	745.8	746.3	746.9	746.7	745.8	744.9	743.9	743.0
160°	758.6	759.0	759.6	759.6	758.9	758.1	757.4	756.8
162.5°	770.5	771.2	771.8	771.8	770.9	770.1	769.3	768.5
165°	786.6	787.2	787.7	787.6	786.7	785.9	785.0	784.2
167.5°	798.5	799.3	800.2	800.1	799.3	798.4	797.5	796.6
170°	805.6	806.5	807.3	807.2	806.2	805.3	804.3	803.3
172.5°	810.7	811.5	812.4	812.4	811.5	810.7	809.8	808.9
175°	816.4	817.3	818.2	818.1	817.1	816.1	815.1	814.2
177.5°	819.0	819.7	820.4	820.4	819.5	818.8	818.0	817.2
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2

(END OF REPORT)