

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333222-930

Luminaire Tested: **S125DIP-S850D590U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333222-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D590U930-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4516.2 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333222-930

CATALOG NUMBER: S125DIP-S850D590U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333222-930

CATALOG NUMBER: S125DIP-S850D590U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	86	83	79	76	74	68	67	65	59	58	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	38	35	31
5	70	58	50	44	65	55	47	42	48	42	38	43	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6912	6912	6912
5°	6928	6862	6906
10°	6885	6813	6852
15°	6811	6731	6760
20°	6704	6616	6628
25°	6589	6480	6475
30°	6447	6334	6302
35°	6296	6176	6089
40°	6139	6004	5918
45°	5971	5847	5731
50°	5785	5657	5488
55°	5606	5444	5291
60°	5391	5227	5043
65°	5136	4968	4800
70°	4893	4670	4509
75°	4457	4312	4162
80°	3968	3905	3812
85°	3453	3520	3320



TEST NUMBER: P333222-930

CATALOG NUMBER: S125DIP-S850D590U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	2.2
10°-20°	285.1	6.3
20°-30°	420.9	9.3
30°-40°	491.1	10.9
40°-50°	493.3	10.9
50°-60°	433.0	9.6
60°-70°	322.6	7.1
70°-80°	184.5	4.1
80°-90°	55.0	1.2
90°-100°	167.2	3.7
100°-110°	359.4	8.0
110°-120°	337.3	7.5
120°-130°	273.4	6.1
130°-140°	219.4	4.9
140°-150°	165.6	3.7
150°-160°	116.5	2.6
160°-170°	68.7	1.5
170°-180°	22.3	0.5
0°-30°	806.9	17.9
0°-40°	1298.0	28.7
0°-60°	2224.3	49.3
0°-90°	2786.3	61.7
90°-120°	864.0	19.1
90°-150°	1522.3	33.7
90°-180°	1730.0	38.3
0°-180°	4516.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1070	1070	1070	1070	1070	
5°	1069	1066	1058	1066	1065	101
15°	1019	1016	1007	1011	1011	287
25°	925	920	909	911	909	425
35°	798	795	783	779	772	499
45°	654	650	640	630	628	504
55°	498	495	484	476	470	444
65°	336	334	325	318	314	333
75°	179	177	173	170	167	190
85°	47	47	48	46	45	52
90°	0	4	7	10	11	3
95°	15	45	412	187	109	16
105°	53	73	337	664	616	55
115°	94	113	271	583	686	92
125°	130	153	260	464	541	115
135°	152	183	258	389	449	118
145°	178	203	259	322	354	111
155°	203	218	252	285	297	93
165°	221	227	242	256	260	62
175°	230	230	232	235	234	22
180°	231	231	231	231	231	



TEST NUMBER: P333222-930

CATALOG NUMBER: S125DIP-S850D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2
2.5°	1073.0	1072.5	1072.1	1071.6	1071.1	1070.2	1068.7	1067.2	1065.7	1064.2	1065.7
5°	1068.6	1068.2	1067.8	1067.5	1067.1	1065.9	1064.0	1062.2	1060.3	1058.4	1060.1
7.5°	1058.7	1058.4	1058.0	1057.6	1057.3	1056.1	1053.9	1051.9	1049.9	1047.7	1049.4
10°	1049.9	1049.6	1049.2	1048.8	1048.5	1047.3	1045.1	1043.1	1041.1	1038.9	1040.5
12.5°	1039.1	1038.4	1037.8	1037.1	1036.4	1035.1	1033.2	1031.3	1029.3	1027.4	1028.7
15°	1018.6	1018.1	1017.5	1016.9	1016.4	1015.0	1013.0	1010.9	1008.9	1006.7	1007.7
17.5°	995.1	994.3	993.4	992.6	991.8	990.3	988.1	986.0	983.8	981.7	982.8
20°	975.4	975.1	974.7	974.3	974.0	972.5	970.0	967.6	965.2	962.7	964.1
22.5°	955.8	955.1	954.5	953.7	953.1	951.6	949.3	947.0	944.7	942.4	943.3
25°	924.6	923.7	922.8	921.8	920.9	919.2	916.7	914.3	911.8	909.4	909.8
27.5°	888.2	887.7	887.1	886.6	886.0	884.4	881.9	879.4	876.9	874.3	874.4
30°	864.5	864.0	863.4	862.8	862.3	860.5	857.8	854.9	852.1	849.3	848.9
32.5°	838.8	837.9	837.1	836.2	835.4	833.6	831.1	828.6	826.1	823.5	822.9
35°	798.5	797.7	797.0	796.2	795.5	793.8	791.2	788.5	785.9	783.3	782.3
37.5°	756.7	755.7	754.7	753.8	752.8	751.1	748.7	746.2	743.7	741.3	739.8
40°	728.2	727.2	726.4	725.4	724.4	722.7	720.0	717.4	714.8	712.1	710.5
42.5°	697.7	696.9	696.1	695.4	694.6	692.8	690.2	687.5	684.9	682.3	680.8
45°	653.7	652.9	652.2	651.4	650.7	649.1	646.9	644.7	642.4	640.2	637.9
47.5°	606.3	606.3	606.3	606.3	606.4	605.1	602.3	599.7	597.0	594.3	591.9
50°	575.8	575.2	574.6	574.1	573.6	572.1	569.9	567.6	565.3	563.0	560.6
52.5°	544.6	544.2	543.8	543.4	543.0	541.5	539.2	536.7	534.3	531.9	529.8
55°	497.9	497.3	496.8	496.2	495.6	494.0	491.4	488.8	486.1	483.5	481.8
57.5°	448.6	448.3	448.0	447.7	447.4	446.1	443.9	441.7	439.4	437.2	435.0
60°	417.4	416.7	416.0	415.2	414.4	413.0	410.9	408.9	406.8	404.7	402.8
62.5°	384.9	384.3	383.8	383.1	382.5	381.3	379.6	377.8	376.0	374.2	372.3
65°	336.1	335.7	335.4	335.0	334.7	333.5	331.3	329.3	327.2	325.1	323.4
67.5°	288.9	288.1	287.3	286.5	285.8	284.5	283.1	281.5	280.0	278.4	277.0
70°	259.1	258.1	257.2	256.2	255.4	254.0	252.3	250.6	248.9	247.3	246.1
72.5°	226.6	225.9	225.3	224.7	224.0	223.1	222.1	220.9	219.9	218.8	217.5
75°	178.6	178.3	177.9	177.6	177.2	176.5	175.5	174.6	173.7	172.8	172.2
77.5°	134.4	134.3	134.2	134.0	133.9	133.5	133.0	132.5	131.9	131.4	131.1
80°	106.7	106.7	106.7	106.7	106.7	106.5	106.2	105.7	105.3	105.0	104.8
82.5°	82.3	82.0	81.7	81.4	81.1	80.9	80.8	80.8	80.7	80.6	80.3
85°	46.6	46.8	47.0	47.1	47.3	47.5	47.5	47.5	47.5	47.5	47.2
87.5°	18.3	18.5	18.7	18.8	19.0	19.2	19.1	19.2	19.1	19.1	19.2
90°	0.5	0.9	1.9	2.8	3.8	4.6	5.1	6.0	6.5	7.4	7.9
92.5°	5.7	6.8	10.8	16.6	24.5	38.2	63.5	106.2	152.4	149.9	121.4
95°	15.3	15.8	19.6	24.6	34.9	55.8	105.6	207.9	336.2	412.1	403.2
97.5°	25.5	26.0	28.6	33.8	43.0	58.0	91.0	165.9	300.3	440.0	510.2
100°	32.5	33.5	35.4	40.4	49.3	63.3	90.3	150.7	267.9	420.0	536.2
102.5°	40.4	40.9	42.4	47.9	56.0	69.5	93.6	144.4	243.3	384.6	520.6
105°	52.6	52.6	54.9	59.5	66.9	80.0	100.4	141.9	219.5	337.2	470.7
107.5°	64.5	65.4	67.6	71.4	79.2	90.9	110.7	146.1	209.5	304.5	419.7
110°	73.1	73.9	75.8	80.0	87.0	99.1	118.1	150.2	206.5	289.3	390.7



TEST NUMBER: P333222-930

CATALOG NUMBER: S125DIP-S850D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	81.6	82.5	84.0	88.2	95.1	106.9	125.2	155.4	206.5	280.4	369.1
115°	93.9	94.9	96.3	100.4	107.5	119.0	136.2	163.2	207.9	270.7	345.5
117.5°	105.1	106.5	108.0	112.2	120.1	131.3	147.7	172.2	210.9	266.0	331.5
120°	112.5	114.0	115.8	120.0	127.9	139.5	155.8	178.1	213.9	263.7	323.7
122.5°	120.3	121.4	122.9	127.0	135.7	147.3	163.6	184.8	216.5	261.9	317.0
125°	130.2	131.2	133.5	137.6	146.5	158.6	173.9	194.0	220.9	259.5	307.9
127.5°	137.9	139.3	142.4	147.7	157.0	169.1	183.8	202.3	225.8	258.4	299.5
130°	142.8	144.1	147.9	153.9	163.7	175.8	190.2	207.9	228.9	257.6	293.9
132.5°	146.5	148.3	152.7	159.6	169.7	181.7	196.2	212.7	232.2	257.6	289.4
135°	152.5	154.4	160.0	167.5	177.2	189.7	204.2	219.5	236.7	257.6	284.1
137.5°	160.2	161.6	166.8	174.2	183.8	196.7	209.9	224.5	240.9	258.2	279.4
140°	164.6	166.0	171.6	179.0	187.9	200.5	213.9	227.9	242.8	258.6	277.2
142.5°	169.8	170.9	176.1	183.5	192.0	203.8	216.5	229.8	243.9	258.9	275.3
145°	177.7	178.6	183.2	189.7	198.1	208.8	220.9	232.5	245.1	258.6	272.6
147.5°	185.8	186.4	190.4	196.4	203.7	213.1	223.7	234.2	245.6	257.4	269.6
150°	190.7	191.6	194.9	200.9	207.4	215.3	225.6	235.3	245.6	256.2	267.4
152.5°	195.9	196.4	199.3	204.6	210.8	217.9	227.4	236.0	245.2	254.8	264.8
155°	202.8	202.8	205.5	210.2	214.8	221.4	229.3	236.7	244.2	252.1	260.4
157.5°	208.9	208.8	211.1	215.1	219.2	224.0	230.9	237.2	243.0	249.2	256.3
160°	213.0	212.5	214.4	217.7	221.4	225.6	231.6	237.2	241.8	247.4	253.0
162.5°	216.4	215.9	217.8	220.6	223.6	227.1	232.4	236.8	240.8	245.2	250.1
165°	221.4	220.5	221.8	224.1	226.0	228.9	232.5	236.3	239.0	241.8	245.6
167.5°	224.7	224.3	225.1	226.4	227.7	229.4	232.5	235.1	236.4	238.6	241.2
170°	227.0	226.5	227.0	227.9	228.9	230.2	232.5	234.4	235.3	236.7	238.6
172.5°	228.4	227.6	228.0	229.0	229.6	230.2	232.2	233.7	233.8	234.5	235.9
175°	230.2	229.3	229.8	230.2	230.2	230.2	231.6	232.5	232.0	232.0	232.5
177.5°	231.1	230.3	230.3	230.6	230.3	230.3	231.1	231.4	230.6	230.6	231.1
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333222-930

CATALOG NUMBER: S125DIP-S850D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2
2.5°	1067.2	1068.7	1070.2	1070.9	1070.7	1070.6	1070.4	1070.2
5°	1061.8	1063.5	1065.2	1065.9	1065.8	1065.6	1065.4	1065.2
7.5°	1051.1	1052.7	1054.3	1055.1	1054.9	1054.8	1054.5	1054.3
10°	1042.0	1043.5	1045.0	1045.6	1045.5	1045.2	1045.1	1044.9
12.5°	1029.8	1031.0	1032.3	1032.8	1032.8	1032.7	1032.7	1032.7
15°	1008.7	1009.6	1010.6	1011.0	1011.0	1011.0	1011.0	1011.0
17.5°	984.1	985.2	986.3	986.5	985.5	984.6	983.7	982.8
20°	965.4	966.7	968.0	968.2	967.3	966.3	965.4	964.4
22.5°	944.1	945.0	945.9	946.0	945.3	944.7	944.0	943.5
25°	910.1	910.5	910.9	910.8	910.3	909.7	909.1	908.6
27.5°	874.5	874.6	874.7	874.4	873.8	873.3	872.7	872.1
30°	848.6	848.2	847.7	847.3	846.8	846.2	845.6	845.1
32.5°	822.1	821.5	820.8	819.9	819.0	817.9	816.9	816.0
35°	781.4	780.4	779.5	778.3	776.7	775.3	773.7	772.3
37.5°	738.4	737.0	735.6	734.5	733.7	732.8	732.0	731.1
40°	708.7	707.0	705.3	704.2	703.6	703.1	702.5	702.0
42.5°	679.2	677.7	676.1	674.9	674.1	673.2	672.3	671.5
45°	635.6	633.3	631.1	629.7	629.2	628.6	628.0	627.5
47.5°	589.6	587.3	585.1	583.3	582.0	580.7	579.3	578.0
50°	558.2	555.7	553.3	551.4	550.1	548.8	547.5	546.2
52.5°	527.7	525.5	523.3	521.5	520.1	518.6	517.1	515.7
55°	480.1	478.4	476.7	475.2	473.9	472.5	471.2	469.9
57.5°	432.9	430.7	428.5	427.1	426.3	425.7	424.9	424.2
60°	401.0	399.1	397.2	395.6	394.3	393.0	391.7	390.4
62.5°	370.2	368.2	366.2	364.6	363.6	362.6	361.6	360.5
65°	321.8	320.1	318.4	317.2	316.4	315.7	314.9	314.1
67.5°	275.6	274.1	272.7	271.7	271.3	270.8	270.4	269.9
70°	245.0	243.9	242.7	241.8	241.0	240.3	239.5	238.8
72.5°	216.2	215.0	213.7	212.6	211.9	211.2	210.4	209.6
75°	171.6	171.0	170.5	169.8	169.1	168.3	167.5	166.8
77.5°	130.8	130.4	130.0	129.6	129.1	128.6	128.1	127.5
80°	104.6	104.4	104.3	104.0	103.6	103.2	102.8	102.5
82.5°	79.9	79.6	79.2	79.1	79.0	78.9	78.8	78.8
85°	47.0	46.9	46.6	46.4	46.0	45.7	45.2	44.8
87.5°	19.3	19.4	19.5	19.5	19.2	18.9	18.7	18.4
90°	8.4	8.8	9.3	10.2	10.2	10.2	10.7	10.7
92.5°	82.4	59.8	45.0	38.2	32.2	31.1	30.4	29.7
95°	334.4	263.7	206.5	167.5	134.4	120.4	116.8	109.3
97.5°	498.0	448.4	392.7	338.3	309.7	283.6	270.1	264.2
100°	572.0	549.3	501.3	453.0	420.9	387.4	370.2	362.7
102.5°	597.0	611.0	588.0	555.3	521.0	497.2	478.5	472.9
105°	582.3	646.0	666.4	661.3	646.5	631.1	621.8	616.2
107.5°	529.8	614.8	667.4	691.6	699.2	699.1	696.0	692.3
110°	491.1	579.5	645.1	684.6	705.5	714.4	717.6	717.6



TEST NUMBER: P333222-930

CATALOG NUMBER: S125DIP-S850D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	460.6	544.5	610.8	657.5	688.0	703.2	711.3	714.6
115°	422.2	494.4	558.1	608.8	645.1	667.4	680.4	686.5
117.5°	397.5	459.7	514.5	561.1	597.4	620.4	633.3	637.1
120°	384.2	439.9	491.1	532.1	566.5	588.8	601.4	605.0
122.5°	374.1	425.8	471.4	509.7	540.4	560.8	573.4	576.7
125°	359.5	406.9	447.4	480.9	507.0	526.0	536.2	540.9
127.5°	344.6	388.9	426.6	458.0	481.6	498.5	508.1	510.2
130°	335.3	376.3	412.5	442.7	466.0	481.4	490.6	493.4
132.5°	326.0	364.4	397.3	426.4	449.6	465.0	473.5	476.7
135°	313.9	346.0	375.8	402.3	422.7	438.1	446.5	449.2
137.5°	303.7	329.6	354.4	376.9	395.2	409.2	416.9	420.0
140°	298.1	320.0	341.4	360.9	378.1	390.2	397.1	399.5
142.5°	293.3	311.8	330.2	347.2	361.7	371.9	378.5	380.5
145°	287.0	301.3	315.8	328.3	339.5	347.4	352.5	354.4
147.5°	281.0	292.7	303.8	313.2	322.1	328.4	331.4	332.2
150°	277.6	287.9	296.7	305.1	312.1	317.6	319.5	320.0
152.5°	273.9	283.1	291.1	297.7	303.5	307.9	309.8	310.3
155°	268.3	275.8	282.3	287.4	292.0	295.3	296.7	297.2
157.5°	262.8	268.9	273.9	277.9	281.5	284.2	285.5	285.4
160°	259.0	263.7	268.3	271.6	274.8	277.2	278.1	277.6
162.5°	254.9	259.3	263.1	266.0	268.6	270.5	270.7	270.6
165°	249.2	252.5	255.4	257.6	259.5	260.4	260.4	260.4
167.5°	243.9	246.1	248.2	249.8	250.8	251.6	251.2	251.1
170°	240.9	242.3	243.7	244.6	245.6	246.1	246.1	245.6
172.5°	237.6	239.0	239.9	240.5	240.8	241.6	240.8	240.4
175°	233.9	233.9	234.9	234.9	234.9	235.3	234.4	233.9
177.5°	231.4	231.8	231.8	231.8	231.4	231.8	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6

(END OF REPORT)