

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333634-930

Luminaire Tested: **S125RDIP-S1270D1205U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333634-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1205U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7938.9 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	33	31	28
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	32	28	32	28	25	27	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9999	9999	9999	9999
5°	11503	10012	8842	10012
10°	13195	9961	7802	9961
15°	14252	9859	6935	9859
20°	15716	9740	6403	9740
25°	18188	9583	5942	9583
30°	19792	9417	5640	9417
35°	16696	9224	5361	9224
40°	11659	8878	5123	8878
45°	8649	8411	4887	8411
50°	6897	7924	4687	7924
55°	5853	7320	4508	7320
60°	5057	6781	4220	6781
65°	4507	6195	3632	6195
70°	3960	5676	3312	5676
75°	3426	4916	3109	4916
80°	2600	4136	2600	4136
85°	2171	3253	2445	3253



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	1.9
10°-20°	435.1	5.5
20°-30°	689.8	8.7
30°-40°	831.9	10.5
40°-50°	742.9	9.4
50°-60°	569.7	7.2
60°-70°	370.2	4.7
70°-80°	180.0	2.3
80°-90°	45.6	0.6
90°-100°	46.5	0.6
100°-110°	286.3	3.6
110°-120°	519.2	6.5
120°-130°	666.3	8.4
130°-140°	716.7	9.0
140°-150°	672.7	8.5
150°-160°	544.2	6.9
160°-170°	351.9	4.4
170°-180°	121.4	1.5
0°-30°	1273.4	16.0
0°-40°	2105.3	26.5
0°-60°	3417.9	43.1
0°-90°	4013.7	50.6
90°-120°	851.9	10.7
90°-150°	2907.7	36.6
90°-180°	3925.0	49.4
0°-180°	7938.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1548	1548	1548	1548	1548	
5°	1774	1544	1364	1544	1774	177
15°	2132	1474	1037	1474	2132	611
25°	2552	1345	834	1345	2552	1172
35°	2118	1170	680	1170	2118	1279
45°	947	921	535	921	947	756
55°	520	650	400	650	520	472
65°	295	405	238	405	295	293
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	23	1	23	1	23	11
95°	20	54	20	54	20	16
105°	281	279	281	279	281	254
115°	519	523	519	523	519	515
125°	744	744	744	744	744	662
135°	924	928	924	928	924	713
145°	1073	1076	1073	1076	1073	670
155°	1176	1184	1176	1184	1176	542
165°	1243	1250	1243	1250	1243	351
175°	1272	1278	1272	1278	1272	121
180°	1278	1278	1278	1278	1278	



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1628.5	1627.5	1629.5	1623.9	1624.4	1615.8	1615.8	1609.2	1600.5	1593.9	1590.9
5°	1774.4	1775.7	1773.1	1763.6	1757.3	1747.8	1736.9	1717.8	1701.9	1686.7	1674.6
7.5°	1924.7	1925.6	1917.2	1914.2	1898.2	1886.5	1862.5	1836.5	1813.6	1784.4	1761.9
10°	2012.1	2011.5	2002.5	1995.6	1981.6	1963.8	1940.3	1909.8	1881.2	1849.4	1818.9
12.5°	2063.0	2061.3	2058.5	2050.0	2037.0	2021.3	2001.3	1971.3	1936.1	1901.3	1865.6
15°	2131.6	2127.1	2118.9	2108.0	2089.6	2071.2	2048.9	2022.3	1988.6	1949.2	1916.1
17.5°	2216.5	2216.6	2203.9	2188.9	2163.9	2131.4	2097.0	2053.9	2008.2	1964.8	1929.7
20°	2286.7	2284.7	2272.1	2242.8	2214.2	2173.5	2134.1	2081.4	2025.4	1968.9	1925.0
22.5°	2387.4	2382.4	2369.2	2330.8	2286.4	2234.0	2173.8	2109.3	2041.8	1977.5	1919.9
25°	2552.3	2548.5	2522.5	2477.9	2415.7	2334.9	2256.2	2167.8	2070.6	1986.1	1916.1
27.5°	2665.2	2661.0	2641.7	2604.7	2547.2	2462.3	2355.6	2237.6	2116.2	1999.9	1899.1
30°	2654.0	2663.5	2661.0	2643.9	2600.6	2524.3	2425.8	2293.0	2148.7	2012.1	1892.0
32.5°	2494.3	2502.9	2525.2	2558.9	2561.4	2530.9	2457.4	2334.7	2185.3	2029.9	1886.4
35°	2117.6	2129.1	2172.3	2240.3	2329.2	2403.6	2418.8	2352.8	2218.7	2051.5	1878.0
37.5°	1628.0	1690.5	1726.9	1798.5	1932.9	2069.7	2201.2	2249.7	2192.6	2042.7	1864.4
40°	1382.9	1398.2	1463.0	1543.7	1656.9	1799.2	1986.7	2122.1	2126.5	2022.3	1843.1
42.5°	1183.7	1203.0	1247.4	1311.9	1408.8	1551.1	1744.7	1923.3	2006.0	1966.3	1815.1
45°	947.0	961.6	994.0	1043.6	1117.9	1235.5	1402.0	1608.5	1772.5	1836.7	1740.1
47.5°	777.9	785.8	814.0	851.7	906.8	992.5	1121.4	1300.6	1497.3	1635.2	1621.6
50°	686.4	695.3	716.9	745.5	791.9	864.3	967.3	1116.6	1319.4	1487.8	1521.5
52.5°	615.2	622.6	636.0	663.1	701.4	757.1	840.2	975.3	1157.7	1336.8	1414.7
55°	519.8	525.0	535.7	551.0	581.6	621.6	693.3	786.8	934.3	1114.8	1229.1
57.5°	441.3	443.8	450.7	464.8	485.9	515.2	567.0	646.2	752.0	914.5	1040.7
60°	391.5	394.0	402.9	412.5	429.0	455.7	496.4	551.6	653.3	787.4	915.2
62.5°	351.8	353.4	357.2	366.7	381.2	401.8	433.8	478.9	559.8	677.6	798.3
65°	294.9	295.5	296.8	304.4	313.3	328.6	349.5	381.3	442.3	531.3	638.1
67.5°	240.3	241.1	245.6	248.3	257.6	265.5	277.9	302.1	345.1	405.1	488.1
70°	209.7	209.1	213.5	216.7	219.9	229.4	237.7	257.4	284.1	329.9	399.1
72.5°	181.2	179.6	181.5	182.6	186.9	193.3	201.6	213.7	234.2	265.8	318.8
75°	137.3	137.9	137.9	139.2	142.4	144.9	147.4	153.8	165.3	186.2	214.8
77.5°	96.4	95.3	98.0	98.4	100.3	103.1	105.3	107.8	112.5	121.2	135.9
80°	69.9	69.9	70.5	72.5	71.8	73.1	76.2	78.8	84.5	89.6	94.7
82.5°	53.6	53.2	53.7	54.1	54.1	55.3	56.4	56.9	59.1	61.6	65.2
85°	29.3	29.3	29.8	29.8	30.5	30.5	31.1	31.1	31.1	31.8	32.4
87.5°	15.7	15.1	14.4	14.3	14.8	15.6	14.8	14.1	13.9	13.7	13.9
90°	22.7	22.1	21.4	20.9	20.2	19.4	18.3	17.3	16.2	15.2	13.7
92.5°	21.2	21.0	20.6	20.3	20.1	19.4	18.3	17.3	16.2	15.2	13.9
95°	19.9	19.9	19.9	19.9	19.9	19.4	18.3	17.3	16.2	15.2	23.2
97.5°	19.9	19.9	19.9	19.9	19.9	22.8	28.8	34.7	40.7	46.6	62.5
100°	19.9	20.7	21.6	22.4	23.2	39.4	70.8	102.2	133.5	164.9	164.0
102.5°	119.2	133.5	147.8	162.2	176.5	186.6	192.6	198.4	204.4	210.3	209.9
105°	281.4	281.6	281.8	282.0	282.3	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	354.7	355.4	356.0	356.6	357.3	357.6	357.5	357.5	357.4	357.4	357.0
110°	405.5	405.4	405.1	404.9	404.7	404.9	405.5	406.2	406.8	407.4	407.0



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	451.0	451.3	451.6	451.9	452.2	452.7	453.6	454.4	455.2	455.9	455.7
115°	519.3	520.5	521.8	523.0	524.3	525.4	526.2	527.0	527.9	528.7	528.5
117.5°	592.0	592.6	593.1	593.6	594.2	595.0	596.1	597.2	598.3	599.4	598.6
120°	636.7	637.8	638.9	639.9	641.0	641.7	642.1	642.5	642.9	643.4	642.7
122.5°	679.2	680.4	681.6	682.8	684.0	684.9	685.3	685.7	686.2	686.6	686.3
125°	743.8	744.4	745.1	745.7	746.3	747.1	747.9	748.8	749.6	750.4	750.4
127.5°	798.2	799.7	801.3	802.9	804.5	805.4	805.9	806.3	806.8	807.3	807.4
130°	837.6	838.7	839.8	840.7	841.8	842.7	843.3	843.9	844.6	845.2	845.0
132.5°	874.0	875.1	876.1	877.2	878.2	878.8	878.9	879.1	879.2	879.3	879.8
135°	923.8	925.1	926.3	927.6	928.9	929.8	930.2	930.6	931.0	931.4	931.8
137.5°	973.9	974.9	976.1	977.1	978.3	978.8	978.7	978.6	978.5	978.4	978.8
140°	1003.5	1004.7	1006.0	1007.2	1008.4	1008.9	1008.4	1008.0	1007.6	1007.2	1007.5
142.5°	1031.5	1032.7	1034.0	1035.3	1036.6	1037.1	1037.1	1037.0	1036.9	1036.8	1036.5
145°	1072.6	1073.8	1075.1	1076.4	1077.7	1078.2	1078.0	1077.7	1077.6	1077.3	1077.3
147.5°	1106.5	1108.1	1109.5	1111.1	1112.6	1113.2	1113.0	1112.7	1112.5	1112.2	1112.0
150°	1128.5	1130.2	1131.9	1133.6	1135.2	1135.9	1135.5	1135.1	1134.6	1134.2	1133.8
152.5°	1149.0	1150.5	1152.0	1153.5	1155.0	1155.6	1155.2	1154.7	1154.3	1153.9	1153.5
155°	1175.9	1177.5	1179.2	1181.0	1182.6	1183.2	1182.5	1181.9	1181.3	1180.6	1180.2
157.5°	1198.4	1200.1	1201.8	1203.5	1205.2	1205.7	1205.0	1204.4	1203.6	1203.0	1203.0
160°	1212.8	1214.6	1216.2	1217.9	1219.6	1220.0	1219.1	1218.3	1217.5	1216.6	1216.4
162.5°	1225.7	1227.6	1229.4	1231.3	1233.1	1233.5	1232.3	1231.1	1230.0	1228.7	1228.6
165°	1243.2	1244.8	1246.5	1248.2	1249.9	1250.1	1248.9	1247.6	1246.3	1245.0	1244.8
167.5°	1255.3	1257.2	1259.1	1260.9	1262.9	1263.1	1261.5	1260.0	1258.5	1257.0	1256.8
170°	1262.1	1264.0	1265.9	1267.8	1269.7	1269.8	1268.1	1266.4	1264.8	1263.1	1262.8
172.5°	1266.6	1268.5	1270.5	1272.4	1274.2	1274.4	1272.9	1271.4	1269.9	1268.4	1268.0
175°	1272.5	1274.4	1276.4	1278.2	1280.1	1280.2	1278.6	1276.8	1275.1	1273.5	1273.3
177.5°	1275.9	1277.2	1278.6	1280.0	1281.3	1281.4	1280.3	1279.0	1277.9	1276.7	1276.5
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1590.9	1587.3	1580.7	1574.6	1567.0	1560.4	1555.8	1550.2	1543.1	1534.5	1527.3
5°	1661.3	1647.3	1628.9	1613.0	1592.7	1576.8	1560.2	1544.3	1528.4	1508.1	1490.4
7.5°	1739.4	1710.5	1682.4	1647.1	1615.0	1586.4	1558.9	1531.1	1503.9	1475.0	1447.2
10°	1787.1	1752.2	1713.4	1668.9	1628.2	1589.5	1553.9	1518.9	1482.1	1449.7	1414.7
12.5°	1831.9	1786.7	1742.4	1686.2	1637.4	1590.0	1544.7	1501.1	1461.8	1419.7	1382.2
15°	1872.3	1827.8	1778.2	1709.6	1641.6	1584.4	1531.0	1474.5	1425.5	1378.5	1336.5
17.5°	1887.9	1841.3	1783.7	1717.8	1643.4	1571.4	1502.7	1440.6	1383.1	1328.3	1281.1
20°	1881.8	1836.7	1777.6	1714.7	1635.2	1560.2	1485.9	1417.2	1353.1	1295.2	1245.0
22.5°	1867.1	1820.4	1763.3	1696.9	1621.5	1542.0	1462.5	1389.3	1322.0	1262.2	1207.4
25°	1844.9	1781.4	1723.0	1658.1	1586.3	1507.5	1425.5	1344.8	1273.0	1211.9	1152.3
27.5°	1821.9	1742.6	1668.3	1603.9	1528.0	1457.7	1378.6	1295.8	1220.3	1158.2	1096.9
30°	1801.1	1712.1	1630.1	1557.1	1485.2	1418.5	1343.5	1262.8	1185.3	1121.1	1058.8
32.5°	1775.2	1680.6	1590.5	1506.2	1437.0	1370.8	1302.8	1225.7	1150.2	1083.9	1020.7
35°	1742.6	1621.9	1524.0	1434.4	1357.5	1293.3	1232.3	1170.0	1094.4	1025.7	964.1
37.5°	1699.9	1562.9	1449.7	1352.0	1271.0	1206.5	1158.3	1101.4	1032.3	966.6	909.5
40°	1674.0	1520.2	1396.3	1299.7	1214.5	1146.5	1101.4	1053.1	990.2	928.5	871.3
42.5°	1639.4	1481.1	1342.4	1241.7	1156.0	1090.5	1045.0	1002.7	950.0	891.9	830.6
45°	1571.7	1405.2	1259.6	1151.6	1065.2	1000.9	958.4	920.9	880.8	827.4	774.0
47.5°	1483.4	1326.0	1173.7	1055.7	971.1	911.5	870.2	840.6	812.0	766.5	714.7
50°	1412.8	1260.9	1112.1	997.8	907.5	851.0	812.2	788.7	762.6	721.3	678.1
52.5°	1329.4	1193.8	1048.1	931.2	846.0	793.0	755.8	732.3	710.8	677.1	635.9
55°	1198.0	1079.1	945.7	839.5	761.4	708.0	672.4	650.1	637.5	608.9	576.4
57.5°	1046.4	961.2	843.5	741.2	672.1	619.3	593.2	574.3	559.9	539.7	516.8
60°	940.6	880.8	775.3	678.1	614.6	564.4	540.9	525.0	511.6	494.5	476.6
62.5°	833.3	789.9	698.1	614.6	556.1	514.0	492.0	477.7	462.3	450.7	433.4
65°	689.6	650.8	587.3	521.8	467.7	434.1	418.2	405.4	395.9	383.2	371.1
67.5°	536.4	520.7	476.8	431.6	392.9	362.9	349.2	340.3	328.8	321.2	312.9
70°	442.3	434.7	403.6	373.7	337.5	317.2	304.4	300.6	286.7	279.0	273.3
72.5°	359.0	355.4	337.5	316.7	291.2	273.4	261.7	257.4	248.5	242.4	238.7
75°	246.0	247.2	244.0	230.7	221.2	209.7	199.6	197.0	190.7	185.6	182.4
77.5°	155.6	162.1	162.3	161.7	157.8	150.9	146.7	144.8	138.5	136.6	135.9
80°	106.8	113.7	120.1	119.4	118.2	116.3	113.2	111.2	108.0	106.2	104.8
82.5°	71.2	77.7	83.0	86.4	86.2	84.3	82.1	81.2	80.6	79.2	78.9
85°	33.7	35.0	36.9	41.3	44.5	45.1	44.5	43.9	41.9	42.6	43.2
87.5°	14.1	13.9	14.0	13.8	12.9	15.1	16.3	16.5	15.8	15.1	14.4
90°	12.2	10.8	9.3	7.7	6.0	4.3	2.6	1.0	2.6	4.3	6.0
92.5°	12.6	11.3	9.9	9.9	11.1	12.2	13.5	14.6	13.5	12.2	11.1
95°	31.1	39.1	47.2	51.4	52.1	52.7	53.4	54.0	53.4	52.7	52.1
97.5°	78.3	94.1	110.0	117.3	116.2	115.0	113.9	112.8	113.9	115.0	116.2
100°	163.2	162.3	161.5	160.8	160.1	159.5	158.9	158.2	158.9	159.5	160.1
102.5°	209.4	208.8	208.3	207.7	206.8	206.1	205.3	204.5	205.3	206.1	206.8
105°	282.3	282.3	282.3	281.9	281.1	280.2	279.4	278.6	279.4	280.2	281.1
107.5°	356.5	356.1	355.7	355.6	355.6	355.6	355.6	355.6	355.6	355.6	355.6
110°	406.6	406.2	405.8	405.5	405.5	405.5	405.5	405.5	405.5	405.5	405.5



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	455.4	455.2	454.9	454.5	454.0	453.6	453.1	452.6	453.1	453.6	454.0
115°	528.3	528.1	527.9	527.3	526.2	525.1	524.1	523.0	524.1	525.1	526.2
117.5°	597.8	597.0	596.2	595.8	595.9	595.9	596.0	596.0	596.0	595.9	595.9
120°	642.1	641.5	640.8	640.7	640.8	641.1	641.2	641.5	641.2	641.1	640.8
122.5°	686.0	685.7	685.4	684.9	684.0	683.2	682.5	681.7	682.5	683.2	684.0
125°	750.4	750.4	750.4	749.7	748.2	746.7	745.3	743.8	745.3	746.7	748.2
127.5°	807.6	807.6	807.8	807.3	806.2	805.2	804.2	803.2	804.2	805.2	806.2
130°	844.8	844.6	844.3	843.8	842.7	841.6	840.6	839.5	840.6	841.6	842.7
132.5°	880.2	880.7	881.2	880.8	879.5	878.3	877.1	875.9	877.1	878.3	879.5
135°	932.3	932.7	933.1	932.7	931.4	930.2	928.9	927.6	928.9	930.2	931.4
137.5°	979.2	979.6	979.9	979.6	978.4	977.4	976.3	975.2	976.3	977.4	978.4
140°	1007.6	1007.9	1008.0	1008.0	1007.5	1007.1	1006.7	1006.2	1006.7	1007.1	1007.5
142.5°	1036.2	1035.9	1035.6	1035.3	1035.1	1034.9	1034.5	1034.3	1034.5	1034.9	1035.1
145°	1077.3	1077.3	1077.3	1077.1	1076.7	1076.3	1075.9	1075.5	1075.9	1076.3	1076.7
147.5°	1111.7	1111.4	1111.2	1111.1	1111.2	1111.3	1111.3	1111.4	1111.3	1111.3	1111.2
150°	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1133.8	1133.3	1132.9
152.5°	1153.1	1152.7	1152.2	1152.4	1153.4	1154.3	1155.3	1156.2	1155.3	1154.3	1153.4
155°	1179.7	1179.3	1178.9	1179.3	1180.6	1181.9	1183.2	1184.4	1183.2	1181.9	1180.6
157.5°	1202.9	1202.9	1202.8	1203.1	1204.0	1204.7	1205.4	1206.2	1205.4	1204.7	1204.0
160°	1216.2	1216.0	1215.8	1216.3	1217.6	1218.9	1220.1	1221.4	1220.1	1218.9	1217.6
162.5°	1228.3	1228.1	1227.9	1228.4	1229.7	1230.9	1232.2	1233.5	1232.2	1230.9	1229.7
165°	1244.6	1244.4	1244.2	1244.7	1246.0	1247.2	1248.5	1249.8	1248.5	1247.2	1246.0
167.5°	1256.5	1256.4	1256.1	1256.7	1258.0	1259.3	1260.6	1261.9	1260.6	1259.3	1258.0
170°	1262.7	1262.4	1262.2	1262.8	1264.3	1265.8	1267.3	1268.8	1267.3	1265.8	1264.3
172.5°	1267.6	1267.2	1266.8	1267.4	1268.9	1270.3	1271.8	1273.3	1271.8	1270.3	1268.9
175°	1273.1	1272.8	1272.6	1273.2	1274.4	1275.7	1276.9	1278.2	1276.9	1275.7	1274.4
177.5°	1276.4	1276.2	1276.0	1276.4	1277.5	1278.5	1279.4	1280.5	1279.4	1278.5	1277.5
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1522.2	1515.2	1510.0	1499.8	1492.7	1489.7	1484.1	1482.5	1488.2	1484.1	1483.6
5°	1477.0	1458.6	1444.0	1429.3	1413.4	1403.3	1388.0	1385.4	1381.7	1375.9	1374.7
7.5°	1422.7	1398.7	1379.9	1355.8	1334.7	1317.8	1298.8	1289.7	1284.8	1277.4	1267.5
10°	1386.1	1357.5	1332.1	1307.9	1281.9	1260.9	1241.9	1227.2	1217.6	1208.8	1205.0
12.5°	1350.0	1320.9	1288.3	1259.1	1230.0	1206.5	1185.4	1175.9	1165.3	1154.9	1146.0
15°	1294.0	1255.2	1219.6	1185.9	1161.1	1135.7	1115.3	1101.4	1085.5	1081.1	1063.9
17.5°	1234.4	1196.5	1154.8	1119.3	1090.5	1062.6	1040.2	1024.3	1012.4	996.1	988.1
20°	1197.3	1152.3	1111.6	1079.1	1047.3	1014.3	991.4	978.1	966.6	953.3	947.0
22.5°	1157.7	1113.6	1071.9	1033.9	1001.6	969.1	952.8	939.0	925.9	913.6	905.2
25°	1099.5	1055.0	1011.1	971.8	938.1	914.5	895.4	879.5	872.6	860.5	851.6
27.5°	1041.9	994.6	949.1	909.8	883.4	860.1	844.5	831.9	819.3	808.8	801.0
30°	1004.8	956.5	906.9	875.8	847.8	825.6	808.4	796.3	786.8	777.2	771.5
32.5°	967.7	917.9	873.8	840.2	813.8	794.5	776.9	765.3	755.3	744.7	738.0
35°	908.2	857.4	821.7	788.7	762.6	744.9	732.8	716.2	708.0	700.3	693.3
37.5°	852.9	805.6	767.1	738.1	715.5	697.8	682.2	673.3	663.1	656.2	650.4
40°	812.2	769.0	734.0	703.5	687.1	667.3	652.7	641.2	633.7	624.8	618.4
42.5°	775.6	735.5	701.5	674.1	653.5	636.8	622.7	611.2	601.6	595.3	589.9
45°	723.9	683.9	650.8	625.3	606.3	590.4	575.8	570.1	557.3	549.8	547.2
47.5°	670.3	634.5	602.6	579.2	559.6	544.6	530.9	519.3	512.3	504.8	500.7
50°	634.3	600.0	570.1	547.2	528.2	511.6	498.9	491.3	481.8	474.7	469.7
52.5°	598.2	566.4	536.5	514.6	498.1	481.6	467.4	459.7	450.7	446.3	442.7
55°	546.6	512.9	487.5	465.9	448.7	433.4	420.1	412.5	406.8	402.3	401.0
57.5°	488.1	461.4	437.7	418.3	400.5	386.1	374.5	367.2	362.2	361.5	357.7
60°	450.0	425.8	404.2	383.2	367.9	354.7	344.5	336.2	331.1	330.4	329.2
62.5°	411.8	388.7	368.6	350.2	336.5	323.6	314.0	304.7	301.7	298.5	295.6
65°	355.2	334.3	317.8	303.1	288.5	277.7	268.2	262.4	255.5	251.7	244.7
67.5°	299.7	283.5	267.6	255.3	243.8	233.5	225.6	217.1	212.4	209.4	204.2
70°	263.1	250.4	234.5	221.2	212.3	204.0	197.6	188.1	184.9	182.4	179.9
72.5°	228.5	217.4	204.0	193.2	184.3	176.5	169.2	164.7	161.6	159.0	157.5
75°	179.9	169.1	157.6	150.0	143.7	137.3	133.5	130.3	129.0	128.4	125.8
77.5°	132.1	126.4	117.2	111.1	106.9	104.4	100.9	99.3	99.1	96.4	95.5
80°	101.0	97.8	90.3	87.7	84.5	82.0	80.1	76.9	73.7	72.5	70.5
82.5°	75.1	71.9	68.9	64.8	62.1	60.7	58.7	57.6	58.0	56.2	55.3
85°	40.0	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.0	32.4	33.0
87.5°	14.3	14.6	14.3	15.7	14.4	15.2	15.4	15.2	15.3	15.6	15.2
90°	7.7	9.3	10.8	12.2	13.7	15.2	16.2	17.3	18.3	19.4	20.2
92.5°	9.9	9.9	11.3	12.6	13.9	15.2	16.2	17.3	18.3	19.4	20.1
95°	51.4	47.2	39.1	31.1	23.2	15.2	16.2	17.3	18.3	19.4	19.9
97.5°	117.3	110.0	94.1	78.3	62.5	46.6	40.7	34.7	28.8	22.8	19.9
100°	160.8	161.5	162.3	163.2	164.0	164.9	133.5	102.2	70.8	39.4	23.2
102.5°	207.7	208.3	208.8	209.4	209.9	210.3	204.4	198.4	192.6	186.6	176.5
105°	281.9	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	355.6	355.7	356.1	356.5	357.0	357.4	357.4	357.5	357.5	357.6	357.3
110°	405.5	405.8	406.2	406.6	407.0	407.4	406.8	406.2	405.5	404.9	404.7



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	454.5	454.9	455.2	455.4	455.7	455.9	455.2	454.4	453.6	452.7	452.2
115°	527.3	527.9	528.1	528.3	528.5	528.7	527.9	527.0	526.2	525.4	524.3
117.5°	595.8	596.2	597.0	597.8	598.6	599.4	598.3	597.2	596.1	595.0	594.2
120°	640.7	640.8	641.5	642.1	642.7	643.4	642.9	642.5	642.1	641.7	641.0
122.5°	684.9	685.4	685.7	686.0	686.3	686.6	686.2	685.7	685.3	684.9	684.0
125°	749.7	750.4	750.4	750.4	750.4	750.4	749.6	748.8	747.9	747.1	746.3
127.5°	807.3	807.8	807.6	807.6	807.4	807.3	806.8	806.3	805.9	805.4	804.5
130°	843.8	844.3	844.6	844.8	845.0	845.2	844.6	843.9	843.3	842.7	841.8
132.5°	880.8	881.2	880.7	880.2	879.8	879.3	879.2	879.1	878.9	878.8	878.2
135°	932.7	933.1	932.7	932.3	931.8	931.4	931.0	930.6	930.2	929.8	928.9
137.5°	979.6	979.9	979.6	979.2	978.8	978.4	978.5	978.6	978.7	978.8	978.3
140°	1008.0	1008.0	1007.9	1007.6	1007.5	1007.2	1007.6	1008.0	1008.4	1008.9	1008.4
142.5°	1035.3	1035.6	1035.9	1036.2	1036.5	1036.8	1036.9	1037.0	1037.1	1037.1	1036.6
145°	1077.1	1077.3	1077.3	1077.3	1077.3	1077.3	1077.6	1077.7	1078.0	1078.2	1077.7
147.5°	1111.1	1111.2	1111.4	1111.7	1112.0	1112.2	1112.5	1112.7	1113.0	1113.2	1112.6
150°	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1134.6	1135.1	1135.5	1135.9	1135.2
152.5°	1152.4	1152.2	1152.7	1153.1	1153.5	1153.9	1154.3	1154.7	1155.2	1155.6	1155.0
155°	1179.3	1178.9	1179.3	1179.7	1180.2	1180.6	1181.3	1181.9	1182.5	1183.2	1182.6
157.5°	1203.1	1202.8	1202.9	1202.9	1203.0	1203.0	1203.6	1204.4	1205.0	1205.7	1205.2
160°	1216.3	1215.8	1216.0	1216.2	1216.4	1216.6	1217.5	1218.3	1219.1	1220.0	1219.6
162.5°	1228.4	1227.9	1228.1	1228.3	1228.6	1228.7	1230.0	1231.1	1232.3	1233.5	1233.1
165°	1244.7	1244.2	1244.4	1244.6	1244.8	1245.0	1246.3	1247.6	1248.9	1250.1	1249.9
167.5°	1256.7	1256.1	1256.4	1256.5	1256.8	1257.0	1258.5	1260.0	1261.5	1263.1	1262.9
170°	1262.8	1262.2	1262.4	1262.7	1262.8	1263.1	1264.8	1266.4	1268.1	1269.8	1269.7
172.5°	1267.4	1266.8	1267.2	1267.6	1268.0	1268.4	1269.9	1271.4	1272.9	1274.4	1274.2
175°	1273.2	1272.6	1272.8	1273.1	1273.3	1273.5	1275.1	1276.8	1278.6	1280.2	1280.1
177.5°	1276.4	1276.0	1276.2	1276.4	1276.5	1276.7	1277.9	1279.0	1280.3	1281.4	1281.3
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1483.1	1477.5	1475.9	1478.0	1475.9	1477.5	1483.1	1483.6	1484.1	1488.2	1482.5
5°	1368.3	1362.0	1365.1	1363.8	1365.1	1362.0	1368.3	1374.7	1375.9	1381.7	1385.4
7.5°	1267.4	1259.5	1251.1	1253.8	1251.1	1259.5	1267.4	1267.5	1277.4	1284.8	1289.7
10°	1196.7	1190.3	1186.5	1189.7	1186.5	1190.3	1196.7	1205.0	1208.8	1217.6	1227.2
12.5°	1137.3	1133.4	1130.1	1128.7	1130.1	1133.4	1137.3	1146.0	1154.9	1165.3	1175.9
15°	1056.2	1048.6	1045.5	1037.2	1045.5	1048.6	1056.2	1063.9	1081.1	1085.5	1101.4
17.5°	981.6	979.1	970.9	967.3	970.9	979.1	981.6	988.1	996.1	1012.4	1024.3
20°	937.4	934.9	926.6	931.7	926.6	934.9	937.4	947.0	953.3	966.6	978.1
22.5°	900.8	895.2	892.5	891.0	892.5	895.2	900.8	905.2	913.6	925.9	939.0
25°	849.1	840.8	837.6	833.8	837.6	840.8	849.1	851.6	860.5	872.6	879.5
27.5°	797.4	793.0	788.8	787.8	788.8	793.0	797.4	801.0	808.8	819.3	831.9
30°	763.9	759.5	756.3	756.3	756.3	759.5	763.9	771.5	777.2	786.8	796.3
32.5°	733.9	730.5	727.3	726.8	727.3	730.5	733.9	738.0	744.7	755.3	765.3
35°	690.2	685.1	683.9	680.0	683.9	685.1	690.2	693.3	700.3	708.0	716.2
37.5°	644.8	640.6	640.5	640.1	640.5	640.6	644.8	650.4	656.2	663.1	673.3
40°	615.8	612.6	612.0	607.6	612.0	612.6	615.8	618.4	624.8	633.7	641.2
42.5°	584.8	583.2	581.0	579.1	581.0	583.2	584.8	589.9	595.3	601.6	611.2
45°	542.7	538.3	538.3	535.1	538.3	538.3	542.7	547.2	549.8	557.3	570.1
47.5°	499.3	495.9	496.2	492.9	496.2	495.9	499.3	500.7	504.8	512.3	519.3
50°	470.3	468.4	467.7	466.5	467.7	468.4	470.3	469.7	474.7	481.8	491.3
52.5°	441.3	440.4	442.9	440.0	442.9	440.4	441.3	442.7	446.3	450.7	459.7
55°	402.3	400.4	404.2	400.4	404.2	400.4	402.3	401.0	402.3	406.8	412.5
57.5°	357.4	355.6	359.1	357.2	359.1	355.6	357.4	357.7	361.5	362.2	367.2
60°	327.9	324.2	326.0	326.7	326.0	324.2	327.9	329.2	330.4	331.1	336.2
62.5°	292.9	290.6	292.0	289.0	292.0	290.6	292.9	295.6	298.5	301.7	304.7
65°	243.4	241.5	239.0	237.7	239.0	241.5	243.4	244.7	251.7	255.5	262.4
67.5°	204.5	199.9	199.8	200.8	199.8	199.9	204.5	204.2	209.4	212.4	217.1
70°	176.0	176.0	175.4	175.4	175.4	176.0	176.0	179.9	182.4	184.9	188.1
72.5°	156.2	155.7	154.6	154.1	154.6	155.7	156.2	157.5	159.0	161.6	164.7
75°	125.8	126.5	125.2	124.6	125.2	126.5	125.8	125.8	128.4	129.0	130.3
77.5°	92.9	90.3	91.6	90.3	91.6	90.3	92.9	95.5	96.4	99.1	99.3
80°	70.5	69.9	71.8	69.9	71.8	69.9	70.5	70.5	72.5	73.7	76.9
82.5°	55.8	55.2	56.1	54.6	56.1	55.2	55.8	55.3	56.2	58.0	57.6
85°	33.7	33.0	32.4	33.0	32.4	33.0	33.7	33.0	32.4	33.0	33.7
87.5°	15.9	15.5	15.6	15.7	15.6	15.5	15.9	15.2	15.6	15.3	15.2
90°	20.9	21.4	22.1	22.7	22.1	21.4	20.9	20.2	19.4	18.3	17.3
92.5°	20.3	20.6	21.0	21.2	21.0	20.6	20.3	20.1	19.4	18.3	17.3
95°	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.4	18.3	17.3
97.5°	19.9	19.9	19.9	19.9	19.9	19.9	19.9	19.9	22.8	28.8	34.7
100°	22.4	21.6	20.7	19.9	20.7	21.6	22.4	23.2	39.4	70.8	102.2
102.5°	162.2	147.8	133.5	119.2	133.5	147.8	162.2	176.5	186.6	192.6	198.4
105°	282.0	281.8	281.6	281.4	281.6	281.8	282.0	282.3	282.3	282.3	282.3
107.5°	356.6	356.0	355.4	354.7	355.4	356.0	356.6	357.3	357.6	357.5	357.5
110°	404.9	405.1	405.4	405.5	405.4	405.1	404.9	404.7	404.9	405.5	406.2



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	451.9	451.6	451.3	451.0	451.3	451.6	451.9	452.2	452.7	453.6	454.4
115°	523.0	521.8	520.5	519.3	520.5	521.8	523.0	524.3	525.4	526.2	527.0
117.5°	593.6	593.1	592.6	592.0	592.6	593.1	593.6	594.2	595.0	596.1	597.2
120°	639.9	638.9	637.8	636.7	637.8	638.9	639.9	641.0	641.7	642.1	642.5
122.5°	682.8	681.6	680.4	679.2	680.4	681.6	682.8	684.0	684.9	685.3	685.7
125°	745.7	745.1	744.4	743.8	744.4	745.1	745.7	746.3	747.1	747.9	748.8
127.5°	802.9	801.3	799.7	798.2	799.7	801.3	802.9	804.5	805.4	805.9	806.3
130°	840.7	839.8	838.7	837.6	838.7	839.8	840.7	841.8	842.7	843.3	843.9
132.5°	877.2	876.1	875.1	874.0	875.1	876.1	877.2	878.2	878.8	878.9	879.1
135°	927.6	926.3	925.1	923.8	925.1	926.3	927.6	928.9	929.8	930.2	930.6
137.5°	977.1	976.1	974.9	973.9	974.9	976.1	977.1	978.3	978.8	978.7	978.6
140°	1007.2	1006.0	1004.7	1003.5	1004.7	1006.0	1007.2	1008.4	1008.9	1008.4	1008.0
142.5°	1035.3	1034.0	1032.7	1031.5	1032.7	1034.0	1035.3	1036.6	1037.1	1037.1	1037.0
145°	1076.4	1075.1	1073.8	1072.6	1073.8	1075.1	1076.4	1077.7	1078.2	1078.0	1077.7
147.5°	1111.1	1109.5	1108.1	1106.5	1108.1	1109.5	1111.1	1112.6	1113.2	1113.0	1112.7
150°	1133.6	1131.9	1130.2	1128.5	1130.2	1131.9	1133.6	1135.2	1135.9	1135.5	1135.1
152.5°	1153.5	1152.0	1150.5	1149.0	1150.5	1152.0	1153.5	1155.0	1155.6	1155.2	1154.7
155°	1181.0	1179.2	1177.5	1175.9	1177.5	1179.2	1181.0	1182.6	1183.2	1182.5	1181.9
157.5°	1203.5	1201.8	1200.1	1198.4	1200.1	1201.8	1203.5	1205.2	1205.7	1205.0	1204.4
160°	1217.9	1216.2	1214.6	1212.8	1214.6	1216.2	1217.9	1219.6	1220.0	1219.1	1218.3
162.5°	1231.3	1229.4	1227.6	1225.7	1227.6	1229.4	1231.3	1233.1	1233.5	1232.3	1231.1
165°	1248.2	1246.5	1244.8	1243.2	1244.8	1246.5	1248.2	1249.9	1250.1	1248.9	1247.6
167.5°	1260.9	1259.1	1257.2	1255.3	1257.2	1259.1	1260.9	1262.9	1263.1	1261.5	1260.0
170°	1267.8	1265.9	1264.0	1262.1	1264.0	1265.9	1267.8	1269.7	1269.8	1268.1	1266.4
172.5°	1272.4	1270.5	1268.5	1266.6	1268.5	1270.5	1272.4	1274.2	1274.4	1272.9	1271.4
175°	1278.2	1276.4	1274.4	1272.5	1274.4	1276.4	1278.2	1280.1	1280.2	1278.6	1276.8
177.5°	1280.0	1278.6	1277.2	1275.9	1277.2	1278.6	1280.0	1281.3	1281.4	1280.3	1279.0
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1484.1	1489.7	1492.7	1499.8	1510.0	1515.2	1522.2	1527.3	1534.5	1543.1	1550.2
5°	1388.0	1403.3	1413.4	1429.3	1444.0	1458.6	1477.0	1490.4	1508.1	1528.4	1544.3
7.5°	1298.8	1317.8	1334.7	1355.8	1379.9	1398.7	1422.7	1447.2	1475.0	1503.9	1531.1
10°	1241.9	1260.9	1281.9	1307.9	1332.1	1357.5	1386.1	1414.7	1449.7	1482.1	1518.9
12.5°	1185.4	1206.5	1230.0	1259.1	1288.3	1320.9	1350.0	1382.2	1419.7	1461.8	1501.1
15°	1115.3	1135.7	1161.1	1185.9	1219.6	1255.2	1294.0	1336.5	1378.5	1425.5	1474.5
17.5°	1040.2	1062.6	1090.5	1119.3	1154.8	1196.5	1234.4	1281.1	1328.3	1383.1	1440.6
20°	991.4	1014.3	1047.3	1079.1	1111.6	1152.3	1197.3	1245.0	1295.2	1353.1	1417.2
22.5°	952.8	969.1	1001.6	1033.9	1071.9	1113.6	1157.7	1207.4	1262.2	1322.0	1389.3
25°	895.4	914.5	938.1	971.8	1011.1	1055.0	1099.5	1152.3	1211.9	1273.0	1344.8
27.5°	844.5	860.1	883.4	909.8	949.1	994.6	1041.9	1096.9	1158.2	1220.3	1295.8
30°	808.4	825.6	847.8	875.8	906.9	956.5	1004.8	1058.8	1121.1	1185.3	1262.8
32.5°	776.9	794.5	813.8	840.2	873.8	917.9	967.7	1020.7	1083.9	1150.2	1225.7
35°	732.8	744.9	762.6	788.7	821.7	857.4	908.2	964.1	1025.7	1094.4	1170.0
37.5°	682.2	697.8	715.5	738.1	767.1	805.6	852.9	909.5	966.6	1032.3	1101.4
40°	652.7	667.3	687.1	703.5	734.0	769.0	812.2	871.3	928.5	990.2	1053.1
42.5°	622.7	636.8	653.5	674.1	701.5	735.5	775.6	830.6	891.9	950.0	1002.7
45°	575.8	590.4	606.3	625.3	650.8	683.9	723.9	774.0	827.4	880.8	920.9
47.5°	530.9	544.6	559.6	579.2	602.6	634.5	670.3	714.7	766.5	812.0	840.6
50°	498.9	511.6	528.2	547.2	570.1	600.0	634.3	678.1	721.3	762.6	788.7
52.5°	467.4	481.6	498.1	514.6	536.5	566.4	598.2	635.9	677.1	710.8	732.3
55°	420.1	433.4	448.7	465.9	487.5	512.9	546.6	576.4	608.9	637.5	650.1
57.5°	374.5	386.1	400.5	418.3	437.7	461.4	488.1	516.8	539.7	559.9	574.3
60°	344.5	354.7	367.9	383.2	404.2	425.8	450.0	476.6	494.5	511.6	525.0
62.5°	314.0	323.6	336.5	350.2	368.6	388.7	411.8	433.4	450.7	462.3	477.7
65°	268.2	277.7	288.5	303.1	317.8	334.3	355.2	371.1	383.2	395.9	405.4
67.5°	225.6	233.5	243.8	255.3	267.6	283.5	299.7	312.9	321.2	328.8	340.3
70°	197.6	204.0	212.3	221.2	234.5	250.4	263.1	273.3	279.0	286.7	300.6
72.5°	169.2	176.5	184.3	193.2	204.0	217.4	228.5	238.7	242.4	248.5	257.4
75°	133.5	137.3	143.7	150.0	157.6	169.1	179.9	182.4	185.6	190.7	197.0
77.5°	100.9	104.4	106.9	111.1	117.2	126.4	132.1	135.9	136.6	138.5	144.8
80°	80.1	82.0	84.5	87.7	90.3	97.8	101.0	104.8	106.2	108.0	111.2
82.5°	58.7	60.7	62.1	64.8	68.9	71.9	75.1	78.9	79.2	80.6	81.2
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.0	43.2	42.6	41.9	43.9
87.5°	15.4	15.2	14.4	15.7	14.3	14.6	14.3	14.4	15.1	15.8	16.5
90°	16.2	15.2	13.7	12.2	10.8	9.3	7.7	6.0	4.3	2.6	1.0
92.5°	16.2	15.2	13.9	12.6	11.3	9.9	9.9	11.1	12.2	13.5	14.6
95°	16.2	15.2	23.2	31.1	39.1	47.2	51.4	52.1	52.7	53.4	54.0
97.5°	40.7	46.6	62.5	78.3	94.1	110.0	117.3	116.2	115.0	113.9	112.8
100°	133.5	164.9	164.0	163.2	162.3	161.5	160.8	160.1	159.5	158.9	158.2
102.5°	204.4	210.3	209.9	209.4	208.8	208.3	207.7	206.8	206.1	205.3	204.5
105°	282.3	282.3	282.3	282.3	282.3	282.3	281.9	281.1	280.2	279.4	278.6
107.5°	357.4	357.4	357.0	356.5	356.1	355.7	355.6	355.6	355.6	355.6	355.6
110°	406.8	407.4	407.0	406.6	406.2	405.8	405.5	405.5	405.5	405.5	405.5



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	455.2	455.9	455.7	455.4	455.2	454.9	454.5	454.0	453.6	453.1	452.6
115°	527.9	528.7	528.5	528.3	528.1	527.9	527.3	526.2	525.1	524.1	523.0
117.5°	598.3	599.4	598.6	597.8	597.0	596.2	595.8	595.9	595.9	596.0	596.0
120°	642.9	643.4	642.7	642.1	641.5	640.8	640.7	640.8	641.1	641.2	641.5
122.5°	686.2	686.6	686.3	686.0	685.7	685.4	684.9	684.0	683.2	682.5	681.7
125°	749.6	750.4	750.4	750.4	750.4	750.4	749.7	748.2	746.7	745.3	743.8
127.5°	806.8	807.3	807.4	807.6	807.6	807.8	807.3	806.2	805.2	804.2	803.2
130°	844.6	845.2	845.0	844.8	844.6	844.3	843.8	842.7	841.6	840.6	839.5
132.5°	879.2	879.3	879.8	880.2	880.7	881.2	880.8	879.5	878.3	877.1	875.9
135°	931.0	931.4	931.8	932.3	932.7	933.1	932.7	931.4	930.2	928.9	927.6
137.5°	978.5	978.4	978.8	979.2	979.6	979.9	979.6	978.4	977.4	976.3	975.2
140°	1007.6	1007.2	1007.5	1007.6	1007.9	1008.0	1008.0	1007.5	1007.1	1006.7	1006.2
142.5°	1036.9	1036.8	1036.5	1036.2	1035.9	1035.6	1035.3	1035.1	1034.9	1034.5	1034.3
145°	1077.6	1077.3	1077.3	1077.3	1077.3	1077.3	1077.1	1076.7	1076.3	1075.9	1075.5
147.5°	1112.5	1112.2	1112.0	1111.7	1111.4	1111.2	1111.1	1111.2	1111.3	1111.3	1111.4
150°	1134.6	1134.2	1133.8	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2
152.5°	1154.3	1153.9	1153.5	1153.1	1152.7	1152.2	1152.4	1153.4	1154.3	1155.3	1156.2
155°	1181.3	1180.6	1180.2	1179.7	1179.3	1178.9	1179.3	1180.6	1181.9	1183.2	1184.4
157.5°	1203.6	1203.0	1203.0	1202.9	1202.9	1202.8	1203.1	1204.0	1204.7	1205.4	1206.2
160°	1217.5	1216.6	1216.4	1216.2	1216.0	1215.8	1216.3	1217.6	1218.9	1220.1	1221.4
162.5°	1230.0	1228.7	1228.6	1228.3	1228.1	1227.9	1228.4	1229.7	1230.9	1232.2	1233.5
165°	1246.3	1245.0	1244.8	1244.6	1244.4	1244.2	1244.7	1246.0	1247.2	1248.5	1249.8
167.5°	1258.5	1257.0	1256.8	1256.5	1256.4	1256.1	1256.7	1258.0	1259.3	1260.6	1261.9
170°	1264.8	1263.1	1262.8	1262.7	1262.4	1262.2	1262.8	1264.3	1265.8	1267.3	1268.8
172.5°	1269.9	1268.4	1268.0	1267.6	1267.2	1266.8	1267.4	1268.9	1270.3	1271.8	1273.3
175°	1275.1	1273.5	1273.3	1273.1	1272.8	1272.6	1273.2	1274.4	1275.7	1276.9	1278.2
177.5°	1277.9	1276.7	1276.5	1276.4	1276.2	1276.0	1276.4	1277.5	1278.5	1279.4	1280.5
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1555.8	1560.4	1567.0	1574.6	1580.7	1587.3	1590.9	1590.9	1593.9	1600.5	1609.2
5°	1560.2	1576.8	1592.7	1613.0	1628.9	1647.3	1661.3	1674.6	1686.7	1701.9	1717.8
7.5°	1558.9	1586.4	1615.0	1647.1	1682.4	1710.5	1739.4	1761.9	1784.4	1813.6	1836.5
10°	1553.9	1589.5	1628.2	1668.9	1713.4	1752.2	1787.1	1818.9	1849.4	1881.2	1909.8
12.5°	1544.7	1590.0	1637.4	1686.2	1742.4	1786.7	1831.9	1865.6	1901.3	1936.1	1971.3
15°	1531.0	1584.4	1641.6	1709.6	1778.2	1827.8	1872.3	1916.1	1949.2	1988.6	2022.3
17.5°	1502.7	1571.4	1643.4	1717.8	1783.7	1841.3	1887.9	1929.7	1964.8	2008.2	2053.9
20°	1485.9	1560.2	1635.2	1714.7	1777.6	1836.7	1881.8	1925.0	1968.9	2025.4	2081.4
22.5°	1462.5	1542.0	1621.5	1696.9	1763.3	1820.4	1867.1	1919.9	1977.5	2041.8	2109.3
25°	1425.5	1507.5	1586.3	1658.1	1723.0	1781.4	1844.9	1916.1	1986.1	2070.6	2167.8
27.5°	1378.6	1457.7	1528.0	1603.9	1668.3	1742.6	1821.9	1899.1	1999.9	2116.2	2237.6
30°	1343.5	1418.5	1485.2	1557.1	1630.1	1712.1	1801.1	1892.0	2012.1	2148.7	2293.0
32.5°	1302.8	1370.8	1437.0	1506.2	1590.5	1680.6	1775.2	1886.4	2029.9	2185.3	2334.7
35°	1232.3	1293.3	1357.5	1434.4	1524.0	1621.9	1742.6	1878.0	2051.5	2218.7	2352.8
37.5°	1158.3	1206.5	1271.0	1352.0	1449.7	1562.9	1699.9	1864.4	2042.7	2192.6	2249.7
40°	1101.4	1146.5	1214.5	1299.7	1396.3	1520.2	1674.0	1843.1	2022.3	2126.5	2122.1
42.5°	1045.0	1090.5	1156.0	1241.7	1342.4	1481.1	1639.4	1815.1	1966.3	2006.0	1923.3
45°	958.4	1000.9	1065.2	1151.6	1259.6	1405.2	1571.7	1740.1	1836.7	1772.5	1608.5
47.5°	870.2	911.5	971.1	1055.7	1173.7	1326.0	1483.4	1621.6	1635.2	1497.3	1300.6
50°	812.2	851.0	907.5	997.8	1112.1	1260.9	1412.8	1521.5	1487.8	1319.4	1116.6
52.5°	755.8	793.0	846.0	931.2	1048.1	1193.8	1329.4	1414.7	1336.8	1157.7	975.3
55°	672.4	708.0	761.4	839.5	945.7	1079.1	1198.0	1229.1	1114.8	934.3	786.8
57.5°	593.2	619.3	672.1	741.2	843.5	961.2	1046.4	1040.7	914.5	752.0	646.2
60°	540.9	564.4	614.6	678.1	775.3	880.8	940.6	915.2	787.4	653.3	551.6
62.5°	492.0	514.0	556.1	614.6	698.1	789.9	833.3	798.3	677.6	559.8	478.9
65°	418.2	434.1	467.7	521.8	587.3	650.8	689.6	638.1	531.3	442.3	381.3
67.5°	349.2	362.9	392.9	431.6	476.8	520.7	536.4	488.1	405.1	345.1	302.1
70°	304.4	317.2	337.5	373.7	403.6	434.7	442.3	399.1	329.9	284.1	257.4
72.5°	261.7	273.4	291.2	316.7	337.5	355.4	359.0	318.8	265.8	234.2	213.7
75°	199.6	209.7	221.2	230.7	244.0	247.2	246.0	214.8	186.2	165.3	153.8
77.5°	146.7	150.9	157.8	161.7	162.3	162.1	155.6	135.9	121.2	112.5	107.8
80°	113.2	116.3	118.2	119.4	120.1	113.7	106.8	94.7	89.6	84.5	78.8
82.5°	82.1	84.3	86.2	86.4	83.0	77.7	71.2	65.2	61.6	59.1	56.9
85°	44.5	45.1	44.5	41.3	36.9	35.0	33.7	32.4	31.8	31.1	31.1
87.5°	16.3	15.1	12.9	13.8	14.0	13.9	14.1	13.9	13.7	13.9	14.1
90°	2.6	4.3	6.0	7.7	9.3	10.8	12.2	13.7	15.2	16.2	17.3
92.5°	13.5	12.2	11.1	9.9	9.9	11.3	12.6	13.9	15.2	16.2	17.3
95°	53.4	52.7	52.1	51.4	47.2	39.1	31.1	23.2	15.2	16.2	17.3
97.5°	113.9	115.0	116.2	117.3	110.0	94.1	78.3	62.5	46.6	40.7	34.7
100°	158.9	159.5	160.1	160.8	161.5	162.3	163.2	164.0	164.9	133.5	102.2
102.5°	205.3	206.1	206.8	207.7	208.3	208.8	209.4	209.9	210.3	204.4	198.4
105°	279.4	280.2	281.1	281.9	282.3	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	355.6	355.6	355.6	355.6	355.7	356.1	356.5	357.0	357.4	357.4	357.5
110°	405.5	405.5	405.5	405.5	405.8	406.2	406.6	407.0	407.4	406.8	406.2



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	453.1	453.6	454.0	454.5	454.9	455.2	455.4	455.7	455.9	455.2	454.4
115°	524.1	525.1	526.2	527.3	527.9	528.1	528.3	528.5	528.7	527.9	527.0
117.5°	596.0	595.9	595.9	595.8	596.2	597.0	597.8	598.6	599.4	598.3	597.2
120°	641.2	641.1	640.8	640.7	640.8	641.5	642.1	642.7	643.4	642.9	642.5
122.5°	682.5	683.2	684.0	684.9	685.4	685.7	686.0	686.3	686.6	686.2	685.7
125°	745.3	746.7	748.2	749.7	750.4	750.4	750.4	750.4	750.4	749.6	748.8
127.5°	804.2	805.2	806.2	807.3	807.8	807.6	807.6	807.4	807.3	806.8	806.3
130°	840.6	841.6	842.7	843.8	844.3	844.6	844.8	845.0	845.2	844.6	843.9
132.5°	877.1	878.3	879.5	880.8	881.2	880.7	880.2	879.8	879.3	879.2	879.1
135°	928.9	930.2	931.4	932.7	933.1	932.7	932.3	931.8	931.4	931.0	930.6
137.5°	976.3	977.4	978.4	979.6	979.9	979.6	979.2	978.8	978.4	978.5	978.6
140°	1006.7	1007.1	1007.5	1008.0	1008.0	1007.9	1007.6	1007.5	1007.2	1007.6	1008.0
142.5°	1034.5	1034.9	1035.1	1035.3	1035.6	1035.9	1036.2	1036.5	1036.8	1036.9	1037.0
145°	1075.9	1076.3	1076.7	1077.1	1077.3	1077.3	1077.3	1077.3	1077.3	1077.6	1077.7
147.5°	1111.3	1111.3	1111.2	1111.1	1111.2	1111.4	1111.7	1112.0	1112.2	1112.5	1112.7
150°	1133.8	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1134.6	1135.1
152.5°	1155.3	1154.3	1153.4	1152.4	1152.2	1152.7	1153.1	1153.5	1153.9	1154.3	1154.7
155°	1183.2	1181.9	1180.6	1179.3	1178.9	1179.3	1179.7	1180.2	1180.6	1181.3	1181.9
157.5°	1205.4	1204.7	1204.0	1203.1	1202.8	1202.9	1202.9	1203.0	1203.0	1203.6	1204.4
160°	1220.1	1218.9	1217.6	1216.3	1215.8	1216.0	1216.2	1216.4	1216.6	1217.5	1218.3
162.5°	1232.2	1230.9	1229.7	1228.4	1227.9	1228.1	1228.3	1228.6	1228.7	1230.0	1231.1
165°	1248.5	1247.2	1246.0	1244.7	1244.2	1244.4	1244.6	1244.8	1245.0	1246.3	1247.6
167.5°	1260.6	1259.3	1258.0	1256.7	1256.1	1256.4	1256.5	1256.8	1257.0	1258.5	1260.0
170°	1267.3	1265.8	1264.3	1262.8	1262.2	1262.4	1262.7	1262.8	1263.1	1264.8	1266.4
172.5°	1271.8	1270.3	1268.9	1267.4	1266.8	1267.2	1267.6	1268.0	1268.4	1269.9	1271.4
175°	1276.9	1275.7	1274.4	1273.2	1272.6	1272.8	1273.1	1273.3	1273.5	1275.1	1276.8
177.5°	1279.4	1278.5	1277.5	1276.4	1276.0	1276.2	1276.4	1276.5	1276.7	1277.9	1279.0
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1615.8	1615.8	1624.4	1623.9	1629.5	1627.5	1628.5
5°	1736.9	1747.8	1757.3	1763.6	1773.1	1775.7	1774.4
7.5°	1862.5	1886.5	1898.2	1914.2	1917.2	1925.6	1924.7
10°	1940.3	1963.8	1981.6	1995.6	2002.5	2011.5	2012.1
12.5°	2001.3	2021.3	2037.0	2050.0	2058.5	2061.3	2063.0
15°	2048.9	2071.2	2089.6	2108.0	2118.9	2127.1	2131.6
17.5°	2097.0	2131.4	2163.9	2188.9	2203.9	2216.6	2216.5
20°	2134.1	2173.5	2214.2	2242.8	2272.1	2284.7	2286.7
22.5°	2173.8	2234.0	2286.4	2330.8	2369.2	2382.4	2387.4
25°	2256.2	2334.9	2415.7	2477.9	2522.5	2548.5	2552.3
27.5°	2355.6	2462.3	2547.2	2604.7	2641.7	2661.0	2665.2
30°	2425.8	2524.3	2600.6	2643.9	2661.0	2663.5	2654.0
32.5°	2457.4	2530.9	2561.4	2558.9	2525.2	2502.9	2494.3
35°	2418.8	2403.6	2329.2	2240.3	2172.3	2129.1	2117.6
37.5°	2201.2	2069.7	1932.9	1798.5	1726.9	1690.5	1628.0
40°	1986.7	1799.2	1656.9	1543.7	1463.0	1398.2	1382.9
42.5°	1744.7	1551.1	1408.8	1311.9	1247.4	1203.0	1183.7
45°	1402.0	1235.5	1117.9	1043.6	994.0	961.6	947.0
47.5°	1121.4	992.5	906.8	851.7	814.0	785.8	777.9
50°	967.3	864.3	791.9	745.5	716.9	695.3	686.4
52.5°	840.2	757.1	701.4	663.1	636.0	622.6	615.2
55°	693.3	621.6	581.6	551.0	535.7	525.0	519.8
57.5°	567.0	515.2	485.9	464.8	450.7	443.8	441.3
60°	496.4	455.7	429.0	412.5	402.9	394.0	391.5
62.5°	433.8	401.8	381.2	366.7	357.2	353.4	351.8
65°	349.5	328.6	313.3	304.4	296.8	295.5	294.9
67.5°	277.9	265.5	257.6	248.3	245.6	241.1	240.3
70°	237.7	229.4	219.9	216.7	213.5	209.1	209.7
72.5°	201.6	193.3	186.9	182.6	181.5	179.6	181.2
75°	147.4	144.9	142.4	139.2	137.9	137.9	137.3
77.5°	105.3	103.1	100.3	98.4	98.0	95.3	96.4
80°	76.2	73.1	71.8	72.5	70.5	69.9	69.9
82.5°	56.4	55.3	54.1	54.1	53.7	53.2	53.6
85°	31.1	30.5	30.5	29.8	29.8	29.3	29.3
87.5°	14.8	15.6	14.8	14.3	14.4	15.1	15.7
90°	18.3	19.4	20.2	20.9	21.4	22.1	22.7
92.5°	18.3	19.4	20.1	20.3	20.6	21.0	21.2
95°	18.3	19.4	19.9	19.9	19.9	19.9	19.9
97.5°	28.8	22.8	19.9	19.9	19.9	19.9	19.9
100°	70.8	39.4	23.2	22.4	21.6	20.7	19.9
102.5°	192.6	186.6	176.5	162.2	147.8	133.5	119.2
105°	282.3	282.3	282.3	282.0	281.8	281.6	281.4
107.5°	357.5	357.6	357.3	356.6	356.0	355.4	354.7
110°	405.5	404.9	404.7	404.9	405.1	405.4	405.5



TEST NUMBER: P333634-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	453.6	452.7	452.2	451.9	451.6	451.3	451.0
115°	526.2	525.4	524.3	523.0	521.8	520.5	519.3
117.5°	596.1	595.0	594.2	593.6	593.1	592.6	592.0
120°	642.1	641.7	641.0	639.9	638.9	637.8	636.7
122.5°	685.3	684.9	684.0	682.8	681.6	680.4	679.2
125°	747.9	747.1	746.3	745.7	745.1	744.4	743.8
127.5°	805.9	805.4	804.5	802.9	801.3	799.7	798.2
130°	843.3	842.7	841.8	840.7	839.8	838.7	837.6
132.5°	878.9	878.8	878.2	877.2	876.1	875.1	874.0
135°	930.2	929.8	928.9	927.6	926.3	925.1	923.8
137.5°	978.7	978.8	978.3	977.1	976.1	974.9	973.9
140°	1008.4	1008.9	1008.4	1007.2	1006.0	1004.7	1003.5
142.5°	1037.1	1037.1	1036.6	1035.3	1034.0	1032.7	1031.5
145°	1078.0	1078.2	1077.7	1076.4	1075.1	1073.8	1072.6
147.5°	1113.0	1113.2	1112.6	1111.1	1109.5	1108.1	1106.5
150°	1135.5	1135.9	1135.2	1133.6	1131.9	1130.2	1128.5
152.5°	1155.2	1155.6	1155.0	1153.5	1152.0	1150.5	1149.0
155°	1182.5	1183.2	1182.6	1181.0	1179.2	1177.5	1175.9
157.5°	1205.0	1205.7	1205.2	1203.5	1201.8	1200.1	1198.4
160°	1219.1	1220.0	1219.6	1217.9	1216.2	1214.6	1212.8
162.5°	1232.3	1233.5	1233.1	1231.3	1229.4	1227.6	1225.7
165°	1248.9	1250.1	1249.9	1248.2	1246.5	1244.8	1243.2
167.5°	1261.5	1263.1	1262.9	1260.9	1259.1	1257.2	1255.3
170°	1268.1	1269.8	1269.7	1267.8	1265.9	1264.0	1262.1
172.5°	1272.9	1274.4	1274.2	1272.4	1270.5	1268.5	1266.6
175°	1278.6	1280.2	1280.1	1278.2	1276.4	1274.4	1272.5
177.5°	1280.3	1281.4	1281.3	1280.0	1278.6	1277.2	1275.9
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2

(END OF REPORT)