

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332506-940

Luminaire Tested: **S124DIP-S350D590U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332506-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D590U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3178.2 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332506-940

CATALOG NUMBER: S124DIP-S350D590U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332506-940

CATALOG NUMBER: S124DIP-S350D590U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	42	36
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	37	35	30
3	80	70	63	57	73	65	58	53	54	49	45	43	40	37	34	32	30	25
4	73	62	54	48	66	57	50	45	48	42	38	39	35	32	30	28	26	22
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	25	22	19
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	23	20	17	15
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4252	4252	4252
5°	4265	4214	4245
10°	4238	4180	4200
15°	4187	4120	4131
20°	4119	4046	4050
25°	4041	3963	3951
30°	3947	3864	3828
35°	3847	3761	3710
40°	3744	3643	3577
45°	3639	3528	3460
50°	3520	3425	3318
55°	3392	3291	3184
60°	3265	3142	3047
65°	3121	2999	2879
70°	2960	2809	2700
75°	2711	2583	2514
80°	2413	2315	2255
85°	2112	2029	1991



TEST NUMBER: P332506-940

CATALOG NUMBER: S124DIP-S350D590U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	1.6
10°-20°	139.8	4.4
20°-30°	205.7	6.5
30°-40°	239.2	7.5
40°-50°	239.2	7.5
50°-60°	209.2	6.6
60°-70°	155.4	4.9
70°-80°	88.3	2.8
80°-90°	27.4	0.9
90°-100°	43.4	1.4
100°-110°	128.5	4.0
110°-120°	218.1	6.9
120°-130°	287.6	9.0
130°-140°	322.9	10.2
140°-150°	317.3	10.0
150°-160°	266.9	8.4
160°-170°	177.6	5.6
170°-180°	62.2	2.0
0°-30°	395.1	12.4
0°-40°	634.2	20.0
0°-60°	1082.6	34.1
0°-90°	1353.7	42.6
90°-120°	389.9	12.3
90°-150°	1317.8	41.5
90°-180°	1824.0	57.4
0°-180°	3178.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	524	50
15°	501	499	493	495	494	141
25°	454	451	445	445	444	209
35°	390	387	382	379	376	244
45°	319	316	309	305	303	246
55°	241	240	234	229	226	216
65°	163	161	157	153	151	162
75°	87	85	83	81	81	92
85°	23	23	22	22	22	25
90°	2	7	11	14	15	3
95°	30	35	39	40	40	34
105°	118	119	121	123	124	126
115°	222	222	221	220	220	219
125°	323	323	322	321	320	288
135°	416	419	420	419	417	322
145°	506	508	508	508	507	317
155°	580	580	579	581	579	267
165°	631	630	629	631	630	178
175°	657	654	654	657	654	62
180°	658	658	658	658	658	



TEST NUMBER: P332506-940

CATALOG NUMBER: S124DIP-S350D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	528.1	527.9	527.6	527.4	527.2	526.6	525.8	525.0	524.2	523.3	524.1
5°	526.3	525.9	525.6	525.2	524.9	524.1	523.1	522.1	521.0	520.0	521.0
7.5°	521.5	521.0	520.7	520.3	520.0	519.2	518.0	516.9	515.8	514.6	515.4
10°	517.0	516.7	516.3	515.9	515.6	514.8	513.5	512.3	511.1	509.9	510.6
12.5°	511.3	511.0	510.6	510.1	509.8	509.0	507.7	506.4	505.1	503.8	504.6
15°	501.0	500.6	500.2	499.9	499.5	498.6	497.2	495.8	494.4	493.0	493.6
17.5°	488.6	488.1	487.7	487.2	486.7	485.8	484.5	483.1	481.8	480.5	480.8
20°	479.5	479.0	478.6	478.0	477.6	476.7	475.3	473.9	472.4	471.0	471.4
22.5°	469.7	469.0	468.4	467.8	467.2	466.2	464.8	463.4	462.0	460.6	461.1
25°	453.7	453.1	452.5	451.7	451.1	450.1	448.8	447.5	446.2	444.9	445.0
27.5°	435.5	434.8	434.2	433.5	432.8	431.9	430.6	429.4	428.2	427.0	426.8
30°	423.4	422.6	421.9	421.1	420.4	419.4	418.1	416.9	415.7	414.5	414.1
32.5°	410.5	409.8	409.1	408.5	407.8	406.8	405.6	404.2	403.0	401.6	401.2
35°	390.4	389.8	389.1	388.4	387.8	386.8	385.5	384.1	382.9	381.6	380.9
37.5°	369.3	368.6	368.0	367.5	366.8	365.9	364.4	363.0	361.6	360.2	359.4
40°	355.3	354.6	353.9	353.1	352.4	351.3	349.9	348.5	347.1	345.7	344.7
42.5°	340.5	340.1	339.7	339.2	338.8	337.7	336.2	334.6	333.1	331.5	330.4
45°	318.7	318.0	317.4	316.7	316.0	315.0	313.4	311.9	310.5	309.0	307.9
47.5°	295.8	295.3	294.9	294.4	294.0	293.1	291.7	290.3	288.9	287.5	286.3
50°	280.3	279.9	279.6	279.1	278.7	277.9	276.6	275.3	273.9	272.7	271.3
52.5°	265.1	264.6	264.1	263.7	263.2	262.3	260.9	259.6	258.2	256.8	255.7
55°	241.0	240.8	240.4	240.1	239.9	239.1	237.7	236.5	235.1	233.8	232.7
57.5°	218.0	217.8	217.4	217.1	216.8	216.0	214.6	213.4	212.0	210.8	209.7
60°	202.2	201.7	201.3	200.7	200.3	199.5	198.2	197.0	195.8	194.6	193.8
62.5°	186.6	186.3	185.8	185.5	185.0	184.2	182.9	181.6	180.3	179.1	178.3
65°	163.4	162.9	162.4	161.9	161.5	160.8	159.8	158.9	157.9	157.0	156.0
67.5°	139.9	139.5	139.0	138.6	138.1	137.5	136.6	135.7	134.8	133.8	133.0
70°	125.4	124.7	124.0	123.4	122.7	122.0	121.3	120.6	119.8	119.0	118.2
72.5°	109.9	109.1	108.5	107.9	107.2	106.6	105.9	105.4	104.8	104.2	103.5
75°	86.9	86.5	86.1	85.5	85.1	84.6	84.2	83.6	83.2	82.8	82.4
77.5°	65.1	64.9	64.6	64.5	64.3	63.9	63.6	63.1	62.7	62.3	62.2
80°	51.9	51.6	51.4	51.1	50.8	50.6	50.4	50.2	50.0	49.8	49.6
82.5°	39.1	39.0	38.8	38.7	38.5	38.4	38.4	38.4	38.3	38.3	38.3
85°	22.8	22.8	22.8	22.8	22.8	22.7	22.5	22.3	22.1	21.9	21.9
87.5°	9.1	9.3	9.5	9.6	9.8	9.9	10.0	10.2	10.3	10.3	10.4
90°	1.5	2.8	4.0	5.3	6.5	7.6	8.5	9.4	10.3	11.1	11.9
92.5°	10.9	12.3	13.7	15.2	16.6	17.6	18.3	18.9	19.5	20.2	20.5
95°	30.5	31.6	32.5	33.5	34.6	35.5	36.3	37.1	37.9	38.6	39.0
97.5°	53.3	54.1	54.9	55.7	56.5	57.4	58.3	59.3	60.2	61.2	61.5
100°	71.2	71.7	72.1	72.6	73.0	73.7	74.7	75.8	76.8	77.8	78.0
102.5°	89.9	90.1	90.2	90.4	90.6	91.2	92.1	93.0	94.0	94.9	95.2
105°	118.5	118.6	118.7	118.9	119.0	119.2	119.7	120.1	120.6	121.0	121.4
107.5°	148.5	148.6	148.7	148.9	149.1	149.2	149.2	149.3	149.4	149.5	149.7
110°	168.9	169.1	169.3	169.5	169.8	169.8	169.7	169.6	169.5	169.3	169.2



TEST NUMBER: P332506-940

CATALOG NUMBER: S124DIP-S350D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	190.0	190.0	190.1	190.1	190.2	190.1	189.9	189.7	189.5	189.3	189.2
115°	221.8	221.8	221.8	221.8	221.8	221.6	221.4	221.1	221.0	220.7	220.6
117.5°	251.6	251.7	251.8	251.9	252.0	252.0	251.8	251.6	251.5	251.4	250.9
120°	271.6	272.1	272.5	273.0	273.4	273.5	273.1	272.8	272.4	272.1	271.5
122.5°	292.3	292.5	292.7	292.8	293.0	293.1	292.9	292.7	292.6	292.5	292.0
125°	323.0	323.0	323.0	323.0	323.0	322.9	322.8	322.7	322.5	322.4	322.2
127.5°	350.7	351.1	351.4	351.8	352.0	352.1	352.0	351.8	351.6	351.4	351.2
130°	370.2	370.6	371.0	371.3	371.6	371.8	371.8	371.8	371.8	371.8	371.6
132.5°	390.2	390.5	390.7	390.9	391.2	391.3	391.2	391.1	391.0	390.9	390.7
135°	416.5	417.2	417.9	418.6	419.3	419.5	419.5	419.5	419.5	419.5	419.4
137.5°	445.2	445.5	445.9	446.1	446.5	446.7	446.9	447.1	447.3	447.5	447.2
140°	464.3	464.6	464.8	465.0	465.2	465.4	465.4	465.4	465.4	465.4	465.2
142.5°	481.8	482.1	482.3	482.5	482.8	482.8	482.7	482.6	482.5	482.4	482.4
145°	506.0	506.5	506.9	507.4	507.8	508.1	508.3	508.4	508.5	508.5	508.5
147.5°	530.0	530.6	531.1	531.6	532.3	532.4	532.4	532.3	532.2	532.1	532.0
150°	544.7	545.2	545.6	546.1	546.5	546.7	546.7	546.7	546.7	546.7	546.7
152.5°	558.6	558.8	559.1	559.4	559.6	559.8	559.9	560.0	560.1	560.2	560.4
155°	579.8	579.8	579.8	579.8	579.8	579.7	579.6	579.5	579.4	579.3	579.7
157.5°	597.7	597.4	597.3	597.1	596.9	596.7	596.7	596.7	596.7	596.6	597.0
160°	608.2	608.1	608.1	608.0	607.8	607.7	607.6	607.5	607.3	607.3	607.6
162.5°	618.0	617.8	617.4	617.2	616.9	616.6	616.5	616.4	616.4	616.2	616.8
165°	631.2	630.8	630.4	630.2	629.8	629.5	629.3	629.1	628.8	628.7	629.3
167.5°	641.2	640.8	640.2	639.8	639.4	639.1	639.1	639.2	639.2	639.2	639.9
170°	646.9	646.4	645.8	645.2	644.6	644.4	644.5	644.6	644.8	644.9	645.6
172.5°	650.9	650.5	650.1	649.6	649.1	648.9	648.9	648.9	648.9	649.0	649.7
175°	656.6	656.0	655.5	654.9	654.3	654.0	653.9	653.8	653.6	653.5	654.3
177.5°	658.4	658.0	657.5	657.1	656.6	656.4	656.4	656.4	656.4	656.4	657.0
180°	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6



TEST NUMBER: P332506-940

CATALOG NUMBER: S124DIP-S350D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	524.9	525.7	526.4	526.7	526.6	526.6	526.5	526.4
5°	522.1	523.1	524.1	524.5	524.3	524.1	524.0	523.8
7.5°	516.2	517.1	517.9	518.3	518.2	518.0	517.9	517.8
10°	511.4	512.1	512.9	513.2	513.0	512.7	512.6	512.4
12.5°	505.4	506.2	507.1	507.4	507.1	506.8	506.6	506.3
15°	494.1	494.6	495.3	495.3	495.1	494.8	494.5	494.3
17.5°	481.2	481.5	481.9	482.0	481.8	481.6	481.4	481.3
20°	471.6	471.9	472.2	472.3	472.0	471.8	471.6	471.4
22.5°	461.5	462.1	462.6	462.7	462.4	462.0	461.6	461.4
25°	445.1	445.1	445.2	445.1	444.7	444.3	444.0	443.6
27.5°	426.5	426.3	426.1	425.7	425.3	424.8	424.3	423.8
30°	413.8	413.4	413.0	412.6	412.1	411.6	411.2	410.7
32.5°	400.7	400.3	399.8	399.4	399.0	398.4	398.0	397.5
35°	380.2	379.6	378.9	378.4	377.9	377.5	376.9	376.5
37.5°	358.7	358.0	357.3	356.7	356.1	355.4	354.8	354.2
40°	343.8	342.9	342.0	341.3	340.7	340.3	339.8	339.4
42.5°	329.3	328.2	327.2	326.5	326.1	325.8	325.5	325.2
45°	306.9	305.9	304.9	304.2	303.9	303.6	303.4	303.1
47.5°	285.2	284.0	282.9	282.0	281.2	280.5	279.8	279.1
50°	270.0	268.8	267.4	266.4	265.9	265.4	264.7	264.2
52.5°	254.5	253.3	252.2	251.2	250.5	249.8	249.1	248.3
55°	231.6	230.4	229.3	228.5	227.9	227.4	226.8	226.2
57.5°	208.7	207.6	206.5	205.7	205.2	204.6	204.1	203.5
60°	192.9	192.1	191.2	190.6	190.1	189.6	189.1	188.7
62.5°	177.5	176.7	175.9	175.3	174.9	174.4	174.0	173.4
65°	155.2	154.2	153.3	152.6	152.1	151.6	151.1	150.7
67.5°	132.1	131.2	130.3	129.7	129.7	129.5	129.4	129.2
70°	117.5	116.8	116.0	115.5	115.2	114.9	114.7	114.4
72.5°	103.0	102.4	101.7	101.3	101.0	100.8	100.5	100.2
75°	81.9	81.6	81.2	81.0	80.9	80.8	80.7	80.6
77.5°	62.1	62.0	61.9	61.7	61.4	61.2	60.9	60.7
80°	49.4	49.2	49.0	49.0	48.8	48.7	48.6	48.5
82.5°	38.1	38.0	37.9	37.8	37.7	37.5	37.5	37.4
85°	21.9	21.9	21.9	21.9	21.8	21.8	21.6	21.5
87.5°	10.6	10.8	10.9	11.0	11.1	11.1	11.1	11.1
90°	12.6	13.2	13.9	14.4	14.6	14.8	15.1	15.2
92.5°	21.0	21.4	21.8	22.0	22.2	22.3	22.5	22.6
95°	39.3	39.7	40.0	40.2	40.2	40.2	40.2	40.2
97.5°	62.0	62.3	62.8	63.0	63.0	63.0	63.0	63.0
100°	78.3	78.5	78.7	78.8	78.8	78.8	78.8	78.8
102.5°	95.5	95.9	96.1	96.4	96.5	96.6	96.7	96.8
105°	121.7	122.1	122.4	122.7	123.1	123.4	123.8	124.1
107.5°	150.1	150.3	150.7	150.9	150.8	150.8	150.8	150.8
110°	168.9	168.7	168.4	168.5	168.9	169.2	169.5	169.9



TEST NUMBER: P332506-940

CATALOG NUMBER: S124DIP-S350D590U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	189.2	189.1	189.1	189.1	189.2	189.2	189.3	189.4
115°	220.5	220.4	220.3	220.2	220.1	219.9	219.8	219.7
117.5°	250.6	250.2	249.8	249.5	249.2	249.1	248.8	248.6
120°	271.0	270.4	269.8	269.7	269.9	270.1	270.4	270.5
122.5°	291.7	291.3	290.9	290.5	290.1	289.7	289.3	288.9
125°	322.0	321.7	321.6	321.3	321.1	320.8	320.7	320.4
127.5°	351.0	350.8	350.5	350.4	350.2	350.0	349.8	349.6
130°	371.3	371.1	370.9	370.5	370.1	369.6	369.2	368.7
132.5°	390.5	390.2	390.0	389.8	389.6	389.4	389.2	389.1
135°	419.1	418.9	418.7	418.4	418.0	417.7	417.4	417.1
137.5°	446.8	446.6	446.3	446.1	446.2	446.3	446.4	446.5
140°	465.1	465.0	464.9	464.8	464.7	464.6	464.5	464.3
142.5°	482.4	482.4	482.3	482.3	482.3	482.3	482.2	482.2
145°	508.4	508.3	508.1	507.9	507.6	507.2	506.8	506.6
147.5°	531.9	531.8	531.7	531.6	531.5	531.4	531.3	531.2
150°	546.7	546.7	546.7	546.7	546.5	546.4	546.4	546.3
152.5°	560.7	561.0	561.2	561.2	561.0	560.6	560.4	560.1
155°	580.1	580.6	581.1	581.1	580.6	580.1	579.7	579.3
157.5°	597.4	597.7	598.1	598.0	597.6	597.3	596.8	596.5
160°	608.0	608.2	608.6	608.5	608.0	607.3	606.8	606.3
162.5°	617.4	618.0	618.7	618.7	618.1	617.5	617.0	616.4
165°	630.0	630.6	631.3	631.4	631.0	630.5	630.1	629.6
167.5°	640.5	641.2	641.9	641.9	641.2	640.5	639.8	639.1
170°	646.2	646.9	647.6	647.6	646.8	646.0	645.2	644.4
172.5°	650.5	651.3	652.0	652.0	651.2	650.4	649.6	648.9
175°	655.1	655.9	656.7	656.7	655.9	655.1	654.3	653.5
177.5°	657.6	658.3	658.9	658.9	658.2	657.5	656.7	655.9
180°	657.6	657.6	657.6	657.6	657.6	657.6	657.6	657.6

(END OF REPORT)