

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332515-940

Luminaire Tested: **S124DIP-S350D810U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332515-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S350D810U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3855.2 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332515-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332515-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	76	66	63	61	51	50	48	37	37	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	36	34	29	27	26	21
4	72	61	53	47	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	23	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4252	4252	4252
5°	4265	4214	4245
10°	4238	4180	4200
15°	4187	4120	4131
20°	4119	4046	4050
25°	4041	3963	3951
30°	3947	3864	3828
35°	3847	3761	3710
40°	3744	3643	3577
45°	3639	3528	3460
50°	3520	3425	3318
55°	3392	3291	3184
60°	3265	3142	3047
65°	3121	2999	2879
70°	2960	2809	2700
75°	2711	2583	2514
80°	2413	2315	2255
85°	2112	2029	1991



TEST NUMBER: P332515-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.6	1.3
10°-20°	139.8	3.6
20°-30°	205.7	5.3
30°-40°	239.2	6.2
40°-50°	239.2	6.2
50°-60°	209.2	5.4
60°-70°	155.4	4.0
70°-80°	88.3	2.3
80°-90°	28.2	0.7
90°-100°	59.5	1.5
100°-110°	176.1	4.6
110°-120°	298.9	7.8
120°-130°	394.2	10.2
130°-140°	442.7	11.5
140°-150°	435.0	11.3
150°-160°	365.9	9.5
160°-170°	243.4	6.3
170°-180°	85.2	2.2
0°-30°	395.1	10.2
0°-40°	634.2	16.5
0°-60°	1082.6	28.1
0°-90°	1354.4	35.1
90°-120°	534.5	13.9
90°-150°	1806.3	46.9
90°-180°	2501.0	64.9
0°-180°	3855.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	527	527	527	527	527	
5°	526	524	520	524	524	50
15°	501	499	493	495	494	141
25°	454	451	445	445	444	209
35°	390	387	382	379	376	244
45°	319	316	309	305	303	246
55°	241	240	234	229	226	216
65°	163	161	157	153	151	162
75°	87	85	83	81	81	92
85°	23	23	22	22	22	25
90°	2	10	15	19	21	4
95°	42	48	53	55	55	47
105°	162	163	166	168	170	172
115°	304	304	303	302	301	300
125°	443	443	442	441	439	394
135°	571	575	575	574	572	442
145°	694	696	697	696	694	434
155°	795	795	794	796	794	366
165°	865	863	862	865	863	244
175°	900	897	896	900	896	85
180°	901	901	901	901	901	



TEST NUMBER: P332515-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	528.1	527.9	527.6	527.4	527.2	526.6	525.8	525.0	524.2	523.3	524.1
5°	526.3	525.9	525.6	525.2	524.9	524.1	523.1	522.1	521.0	520.0	521.0
7.5°	521.5	521.0	520.7	520.3	520.0	519.2	518.0	516.9	515.8	514.6	515.4
10°	517.0	516.7	516.3	515.9	515.6	514.8	513.5	512.3	511.1	509.9	510.6
12.5°	511.3	511.0	510.6	510.1	509.8	509.0	507.7	506.4	505.1	503.8	504.6
15°	501.0	500.6	500.2	499.9	499.5	498.6	497.2	495.8	494.4	493.0	493.6
17.5°	488.6	488.1	487.7	487.2	486.7	485.8	484.5	483.1	481.8	480.5	480.8
20°	479.5	479.0	478.6	478.0	477.6	476.7	475.3	473.9	472.4	471.0	471.4
22.5°	469.7	469.0	468.4	467.8	467.2	466.2	464.8	463.4	462.0	460.6	461.1
25°	453.7	453.1	452.5	451.7	451.1	450.1	448.8	447.5	446.2	444.9	445.0
27.5°	435.5	434.8	434.2	433.5	432.8	431.9	430.6	429.4	428.2	427.0	426.8
30°	423.4	422.6	421.9	421.1	420.4	419.4	418.1	416.9	415.7	414.5	414.1
32.5°	410.5	409.8	409.1	408.5	407.8	406.8	405.6	404.2	403.0	401.6	401.2
35°	390.4	389.8	389.1	388.4	387.8	386.8	385.5	384.1	382.9	381.6	380.9
37.5°	369.3	368.6	368.0	367.5	366.8	365.9	364.4	363.0	361.6	360.2	359.4
40°	355.3	354.6	353.9	353.1	352.4	351.3	349.9	348.5	347.1	345.7	344.7
42.5°	340.5	340.1	339.7	339.2	338.8	337.7	336.2	334.6	333.1	331.5	330.4
45°	318.7	318.0	317.4	316.7	316.0	315.0	313.4	311.9	310.5	309.0	307.9
47.5°	295.8	295.3	294.9	294.4	294.0	293.1	291.7	290.3	288.9	287.5	286.3
50°	280.3	279.9	279.6	279.1	278.7	277.9	276.6	275.3	273.9	272.7	271.3
52.5°	265.1	264.6	264.1	263.7	263.2	262.3	260.9	259.6	258.2	256.8	255.7
55°	241.0	240.8	240.4	240.1	239.9	239.1	237.7	236.5	235.1	233.8	232.7
57.5°	218.0	217.8	217.4	217.1	216.8	216.0	214.6	213.4	212.0	210.8	209.7
60°	202.2	201.7	201.3	200.7	200.3	199.5	198.2	197.0	195.8	194.6	193.8
62.5°	186.6	186.3	185.8	185.5	185.0	184.2	182.9	181.6	180.3	179.1	178.3
65°	163.4	162.9	162.4	161.9	161.5	160.8	159.8	158.9	157.9	157.0	156.0
67.5°	139.9	139.5	139.0	138.6	138.1	137.5	136.6	135.7	134.8	133.8	133.0
70°	125.4	124.7	124.0	123.4	122.7	122.0	121.3	120.6	119.8	119.0	118.2
72.5°	109.9	109.1	108.5	107.9	107.2	106.6	105.9	105.4	104.8	104.2	103.5
75°	86.9	86.5	86.1	85.5	85.1	84.6	84.2	83.6	83.2	82.8	82.4
77.5°	65.1	64.9	64.6	64.5	64.3	63.9	63.6	63.1	62.7	62.3	62.2
80°	51.9	51.6	51.4	51.1	50.8	50.6	50.4	50.2	50.0	49.8	49.6
82.5°	39.1	39.0	38.8	38.7	38.5	38.4	38.4	38.4	38.3	38.3	38.3
85°	22.8	22.8	22.8	22.8	22.8	22.7	22.5	22.3	22.1	21.9	21.9
87.5°	9.2	9.5	9.7	10.0	10.3	10.5	10.6	10.8	11.0	11.1	11.3
90°	2.1	3.8	5.5	7.2	8.9	10.3	11.6	12.8	14.1	15.3	16.2
92.5°	14.9	16.9	18.8	20.8	22.7	24.2	25.0	25.9	26.8	27.6	28.2
95°	41.8	43.2	44.6	46.0	47.4	48.7	49.8	50.8	51.9	53.0	53.4
97.5°	73.0	74.2	75.3	76.4	77.5	78.7	80.0	81.2	82.5	83.8	84.4
100°	97.6	98.2	98.8	99.4	100.0	101.1	102.5	103.9	105.2	106.6	107.0
102.5°	123.2	123.5	123.8	124.0	124.2	125.0	126.3	127.5	128.9	130.1	130.5
105°	162.5	162.6	162.7	162.9	163.1	163.5	164.1	164.7	165.3	165.9	166.4
107.5°	203.6	203.8	203.9	204.1	204.3	204.5	204.6	204.6	204.7	204.8	205.3
110°	231.5	231.8	232.0	232.4	232.6	232.7	232.6	232.5	232.3	232.1	231.8



TEST NUMBER: P332515-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.5	260.5	260.6	260.6	260.7	260.6	260.3	260.0	259.8	259.5	259.4
115°	304.0	304.0	304.0	304.0	304.0	303.8	303.4	303.2	302.8	302.6	302.4
117.5°	344.9	345.1	345.2	345.3	345.4	345.4	345.2	344.9	344.7	344.6	344.0
120°	372.3	372.9	373.5	374.2	374.8	374.8	374.3	373.9	373.4	373.0	372.2
122.5°	400.7	400.9	401.2	401.4	401.7	401.7	401.5	401.3	401.1	400.8	400.3
125°	442.6	442.6	442.6	442.6	442.6	442.6	442.5	442.3	442.1	442.0	441.7
127.5°	480.7	481.2	481.7	482.1	482.6	482.7	482.4	482.2	482.0	481.7	481.4
130°	507.5	508.0	508.5	508.9	509.3	509.6	509.6	509.6	509.6	509.6	509.3
132.5°	534.8	535.2	535.6	535.8	536.2	536.3	536.2	536.1	535.9	535.8	535.5
135°	571.0	571.9	572.8	573.7	574.7	575.2	575.2	575.2	575.2	575.2	574.8
137.5°	610.3	610.7	611.1	611.5	612.0	612.3	612.6	612.9	613.1	613.3	613.0
140°	636.5	636.8	637.1	637.4	637.8	637.8	637.8	637.8	637.8	637.8	637.8
142.5°	660.5	660.8	661.1	661.4	661.7	661.8	661.6	661.6	661.4	661.3	661.3
145°	693.7	694.3	694.9	695.5	696.2	696.5	696.7	696.8	697.0	697.1	697.0
147.5°	726.6	727.3	728.0	728.8	729.5	729.9	729.7	729.6	729.4	729.3	729.2
150°	746.6	747.3	747.9	748.5	749.1	749.4	749.4	749.4	749.4	749.4	749.4
152.5°	765.6	766.0	766.3	766.7	767.0	767.3	767.4	767.6	767.7	767.9	768.2
155°	794.7	794.7	794.7	794.7	794.7	794.6	794.5	794.3	794.2	794.1	794.6
157.5°	819.3	818.9	818.7	818.4	818.1	818.0	818.0	818.0	817.9	817.9	818.3
160°	833.7	833.6	833.5	833.3	833.1	832.9	832.9	832.7	832.5	832.4	832.9
162.5°	847.1	846.8	846.3	846.0	845.5	845.3	845.1	845.0	844.8	844.6	845.5
165°	865.1	864.7	864.2	863.7	863.3	862.9	862.6	862.3	861.9	861.7	862.6
167.5°	879.0	878.2	877.6	877.0	876.4	876.0	876.0	876.1	876.1	876.1	877.1
170°	886.7	886.0	885.2	884.4	883.7	883.3	883.5	883.7	883.8	884.0	884.8
172.5°	892.3	891.7	891.0	890.4	889.7	889.4	889.5	889.5	889.5	889.6	890.6
175°	900.0	899.2	898.4	897.7	896.9	896.4	896.3	896.1	896.0	895.8	896.9
177.5°	902.5	901.9	901.3	900.6	900.0	899.7	899.7	899.7	899.7	899.7	900.5
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3



TEST NUMBER: P332515-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	526.7	526.7	526.7	526.7	526.7	526.7	526.7	526.7
2.5°	524.9	525.7	526.4	526.7	526.6	526.6	526.5	526.4
5°	522.1	523.1	524.1	524.5	524.3	524.1	524.0	523.8
7.5°	516.2	517.1	517.9	518.3	518.2	518.0	517.9	517.8
10°	511.4	512.1	512.9	513.2	513.0	512.7	512.6	512.4
12.5°	505.4	506.2	507.1	507.4	507.1	506.8	506.6	506.3
15°	494.1	494.6	495.3	495.3	495.1	494.8	494.5	494.3
17.5°	481.2	481.5	481.9	482.0	481.8	481.6	481.4	481.3
20°	471.6	471.9	472.2	472.3	472.0	471.8	471.6	471.4
22.5°	461.5	462.1	462.6	462.7	462.4	462.0	461.6	461.4
25°	445.1	445.1	445.2	445.1	444.7	444.3	444.0	443.6
27.5°	426.5	426.3	426.1	425.7	425.3	424.8	424.3	423.8
30°	413.8	413.4	413.0	412.6	412.1	411.6	411.2	410.7
32.5°	400.7	400.3	399.8	399.4	399.0	398.4	398.0	397.5
35°	380.2	379.6	378.9	378.4	377.9	377.5	376.9	376.5
37.5°	358.7	358.0	357.3	356.7	356.1	355.4	354.8	354.2
40°	343.8	342.9	342.0	341.3	340.7	340.3	339.8	339.4
42.5°	329.3	328.2	327.2	326.5	326.1	325.8	325.5	325.2
45°	306.9	305.9	304.9	304.2	303.9	303.6	303.4	303.1
47.5°	285.2	284.0	282.9	282.0	281.2	280.5	279.8	279.1
50°	270.0	268.8	267.4	266.4	265.9	265.4	264.7	264.2
52.5°	254.5	253.3	252.2	251.2	250.5	249.8	249.1	248.3
55°	231.6	230.4	229.3	228.5	227.9	227.4	226.8	226.2
57.5°	208.7	207.6	206.5	205.7	205.2	204.6	204.1	203.5
60°	192.9	192.1	191.2	190.6	190.1	189.6	189.1	188.7
62.5°	177.5	176.7	175.9	175.3	174.9	174.4	174.0	173.4
65°	155.2	154.2	153.3	152.6	152.1	151.6	151.1	150.7
67.5°	132.1	131.2	130.3	129.7	129.7	129.5	129.4	129.2
70°	117.5	116.8	116.0	115.5	115.2	114.9	114.7	114.4
72.5°	103.0	102.4	101.7	101.3	101.0	100.8	100.5	100.2
75°	81.9	81.6	81.2	81.0	80.9	80.8	80.7	80.6
77.5°	62.1	62.0	61.9	61.7	61.4	61.2	60.9	60.7
80°	49.4	49.2	49.0	49.0	48.8	48.7	48.6	48.5
82.5°	38.1	38.0	37.9	37.8	37.7	37.5	37.5	37.4
85°	21.9	21.9	21.9	21.9	21.8	21.8	21.6	21.5
87.5°	11.5	11.8	11.9	12.0	12.1	12.1	12.2	12.3
90°	17.2	18.1	19.1	19.7	20.0	20.3	20.6	21.0
92.5°	28.7	29.2	29.9	30.2	30.4	30.6	30.8	30.9
95°	53.9	54.4	54.8	55.1	55.1	55.1	55.1	55.1
97.5°	84.9	85.4	86.1	86.3	86.3	86.3	86.3	86.3
100°	107.3	107.6	107.9	108.1	108.1	108.1	108.1	108.1
102.5°	131.0	131.3	131.8	132.1	132.2	132.3	132.5	132.6
105°	166.8	167.3	167.7	168.3	168.7	169.2	169.6	170.1
107.5°	205.7	206.1	206.5	206.8	206.7	206.7	206.7	206.6
110°	231.5	231.2	230.9	231.0	231.5	231.9	232.4	232.8



TEST NUMBER: P332515-940

CATALOG NUMBER: S124DIP-S350D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	259.3	259.3	259.2	259.2	259.3	259.4	259.5	259.6
115°	302.2	302.1	301.9	301.8	301.7	301.5	301.3	301.1
117.5°	343.5	343.0	342.4	342.0	341.7	341.3	341.1	340.7
120°	371.4	370.6	369.9	369.6	370.0	370.2	370.6	370.9
122.5°	399.8	399.3	398.8	398.2	397.6	397.1	396.5	396.0
125°	441.4	441.0	440.8	440.4	440.1	439.8	439.5	439.2
127.5°	481.1	480.8	480.5	480.2	479.9	479.7	479.5	479.2
130°	509.0	508.6	508.4	507.9	507.3	506.7	506.0	505.4
132.5°	535.2	534.8	534.6	534.3	534.0	533.8	533.5	533.3
135°	574.5	574.2	573.9	573.5	573.0	572.6	572.1	571.7
137.5°	612.5	612.2	611.7	611.5	611.6	611.7	611.8	612.0
140°	637.6	637.4	637.2	637.1	636.9	636.8	636.6	636.5
142.5°	661.2	661.2	661.2	661.1	661.1	661.1	661.0	661.0
145°	696.8	696.7	696.5	696.2	695.7	695.3	694.8	694.4
147.5°	729.1	729.0	728.8	728.7	728.5	728.3	728.3	728.1
150°	749.4	749.4	749.4	749.3	749.2	749.0	748.9	748.7
152.5°	768.6	768.9	769.3	769.3	768.9	768.5	768.1	767.7
155°	795.2	795.9	796.5	796.5	795.9	795.2	794.6	794.1
157.5°	818.8	819.3	819.7	819.7	819.2	818.7	818.1	817.6
160°	833.3	833.7	834.2	834.1	833.3	832.5	831.8	831.0
162.5°	846.3	847.1	848.0	848.0	847.2	846.5	845.7	844.9
165°	863.5	864.4	865.4	865.5	864.9	864.2	863.6	863.1
167.5°	878.0	879.0	879.9	879.9	878.9	877.9	877.0	876.0
170°	885.8	886.7	887.7	887.6	886.5	885.5	884.3	883.2
172.5°	891.6	892.7	893.8	893.8	892.7	891.5	890.5	889.4
175°	898.0	899.0	900.2	900.2	899.0	898.0	896.9	895.8
177.5°	901.4	902.3	903.2	903.1	902.1	901.2	900.2	899.1
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3

(END OF REPORT)