

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332541-940

Luminaire Tested: **S124DIP-S575D365U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332541-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D365U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3526.8 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332541-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332541-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	51	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	38
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	25
7	60	47	39	34	56	45	37	32	40	34	30	36	31	27	31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6990	6990	6990
5°	7012	6928	6978
10°	6968	6871	6906
15°	6884	6774	6791
20°	6772	6653	6659
25°	6644	6515	6495
30°	6488	6352	6293
35°	6326	6182	6099
40°	6157	5989	5879
45°	5981	5799	5688
50°	5786	5630	5456
55°	5576	5410	5234
60°	5365	5165	5007
65°	5129	4932	4732
70°	4865	4617	4440
75°	4457	4242	4133
80°	3966	3808	3710
85°	3473	3344	3279



TEST NUMBER: P332541-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	2.3
10°-20°	229.8	6.5
20°-30°	338.2	9.6
30°-40°	393.2	11.1
40°-50°	393.2	11.1
50°-60°	343.9	9.8
60°-70°	255.4	7.2
70°-80°	145.1	4.1
80°-90°	43.1	1.2
90°-100°	14.4	0.4
100°-110°	91.9	2.6
110°-120°	175.8	5.0
120°-130°	223.1	6.3
130°-140°	238.7	6.8
140°-150°	223.2	6.3
150°-160°	180.0	5.1
160°-170°	116.1	3.3
170°-180°	40.0	1.1
0°-30°	649.5	18.4
0°-40°	1042.7	29.6
0°-60°	1779.8	50.5
0°-90°	2223.4	63.0
90°-120°	282.1	8.0
90°-150°	967.2	27.4
90°-180°	1303.0	36.9
0°-180°	3526.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	862	861	82
15°	824	820	810	814	812	232
25°	746	741	731	732	729	343
35°	642	637	627	622	619	401
45°	524	519	508	501	498	404
55°	396	394	384	376	372	355
65°	268	265	258	251	248	266
75°	143	139	136	133	132	152
85°	38	37	36	36	35	41
90°	1	4	7	9	10	3
95°	17	7	7	9	9	22
105°	95	97	98	100	90	99
115°	177	178	178	178	178	174
125°	249	250	250	250	251	222
135°	309	309	310	310	311	238
145°	356	357	357	357	358	222
155°	390	391	390	391	390	180
165°	412	410	410	413	410	116
175°	421	420	420	422	419	40
180°	421	421	421	421	421	



TEST NUMBER: P332541-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	868.2	867.8	867.5	867.1	866.7	865.9	864.5	863.2	861.7	860.4	861.7
5°	865.3	864.7	864.1	863.4	862.8	861.7	860.0	858.3	856.6	854.9	856.6
7.5°	857.2	856.6	856.0	855.4	854.8	853.5	851.7	849.8	847.8	846.0	847.4
10°	850.0	849.4	848.8	848.2	847.6	846.2	844.3	842.2	840.3	838.2	839.5
12.5°	840.6	840.0	839.4	838.7	838.1	836.8	834.6	832.5	830.4	828.2	829.6
15°	823.7	823.0	822.4	821.8	821.2	819.7	817.4	815.1	812.8	810.5	811.4
17.5°	803.3	802.5	801.7	800.9	800.1	798.7	796.5	794.3	792.1	790.0	790.5
20°	788.3	787.5	786.8	786.0	785.2	783.6	781.3	779.0	776.7	774.4	774.8
22.5°	772.1	771.2	770.2	769.1	768.1	766.4	764.1	761.8	759.5	757.2	758.0
25°	745.9	744.8	743.8	742.7	741.6	740.0	737.8	735.7	733.5	731.4	731.6
27.5°	716.0	714.9	713.7	712.7	711.5	710.0	707.9	706.0	703.9	702.0	701.6
30°	696.0	694.7	693.5	692.2	691.1	689.4	687.4	685.4	683.4	681.4	680.8
32.5°	674.8	673.8	672.6	671.5	670.5	668.8	666.7	664.6	662.5	660.3	659.6
35°	641.9	640.8	639.7	638.6	637.6	635.9	633.7	631.6	629.5	627.3	626.2
37.5°	607.0	606.0	605.0	604.0	603.1	601.5	599.1	596.8	594.5	592.2	591.0
40°	584.2	583.0	581.8	580.6	579.3	577.6	575.2	572.9	570.6	568.3	566.8
42.5°	559.8	559.1	558.4	557.6	556.9	555.2	552.7	550.1	547.5	545.0	543.2
45°	523.9	522.8	521.7	520.7	519.6	517.8	515.3	512.8	510.4	507.9	506.2
47.5°	486.2	485.5	484.8	484.0	483.3	481.8	479.6	477.2	474.9	472.7	470.7
50°	460.7	460.1	459.5	458.9	458.3	456.9	454.8	452.5	450.4	448.3	446.1
52.5°	435.8	435.1	434.3	433.5	432.8	431.3	429.0	426.8	424.5	422.1	420.3
55°	396.2	395.7	395.3	394.8	394.4	393.1	390.9	388.7	386.6	384.4	382.5
57.5°	358.5	357.9	357.4	356.9	356.3	355.1	352.9	350.8	348.7	346.5	344.7
60°	332.3	331.6	330.8	330.0	329.3	327.9	325.9	323.9	321.9	319.9	318.5
62.5°	306.8	306.2	305.5	304.9	304.3	302.8	300.8	298.6	296.5	294.4	293.1
65°	268.5	267.8	267.0	266.3	265.5	264.3	262.8	261.2	259.7	258.2	256.5
67.5°	230.0	229.3	228.5	227.8	227.1	226.0	224.5	223.1	221.6	220.1	218.6
70°	206.1	205.0	203.9	202.9	201.8	200.6	199.4	198.1	196.9	195.6	194.5
72.5°	180.6	179.5	178.4	177.3	176.2	175.2	174.2	173.3	172.3	171.2	170.2
75°	142.9	142.1	141.4	140.6	139.8	139.1	138.3	137.5	136.8	136.0	135.4
77.5°	107.0	106.6	106.3	106.0	105.7	105.1	104.4	103.8	103.1	102.5	102.2
80°	85.3	84.9	84.4	84.0	83.5	83.1	82.8	82.5	82.2	81.9	81.6
82.5°	64.3	64.0	63.8	63.6	63.4	63.2	63.2	63.1	63.0	63.0	62.8
85°	37.5	37.5	37.5	37.5	37.5	37.3	37.0	36.7	36.4	36.1	36.1
87.5°	14.6	14.6	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.8
90°	1.0	1.7	2.5	3.3	4.0	4.7	5.3	5.8	6.3	7.0	7.3
92.5°	4.0	4.0	4.0	4.1	4.1	4.5	5.0	5.5	6.2	6.7	7.1
95°	17.3	15.0	12.6	10.2	7.8	6.7	6.7	6.8	6.9	7.0	7.3
97.5°	36.8	38.3	39.8	41.3	42.7	39.6	31.7	24.0	16.1	8.3	8.4
100°	51.7	53.0	54.2	55.5	56.7	52.5	42.9	33.2	23.5	13.9	12.7
102.5°	68.3	69.3	70.2	71.1	72.1	71.9	70.6	69.4	68.0	66.8	53.9
105°	94.9	95.2	95.7	96.1	96.6	96.9	97.3	97.6	98.0	98.4	99.0
107.5°	119.5	119.7	119.9	120.1	120.4	120.6	121.2	121.6	122.1	122.6	122.9
110°	136.2	136.3	136.5	136.8	137.0	137.3	137.7	138.1	138.6	139.0	139.1



TEST NUMBER: P332541-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	152.3	152.7	153.0	153.4	153.8	154.1	154.3	154.4	154.6	154.9	154.8
115°	177.1	177.4	177.5	177.7	178.0	178.0	178.0	177.9	177.8	177.7	177.9
117.5°	199.5	199.7	200.0	200.4	200.6	200.8	201.0	201.2	201.3	201.4	201.4
120°	214.6	214.9	215.2	215.4	215.7	215.8	215.8	215.7	215.6	215.5	215.7
122.5°	228.7	228.9	229.1	229.3	229.4	229.5	229.6	229.7	229.8	230.0	230.0
125°	249.0	249.2	249.5	249.8	250.1	250.1	250.0	249.9	249.8	249.6	249.8
127.5°	268.1	268.2	268.2	268.3	268.4	268.6	268.9	269.2	269.6	269.9	269.8
130°	280.4	280.5	280.6	280.7	280.8	280.9	281.1	281.3	281.5	281.8	281.8
132.5°	291.9	291.9	292.0	292.2	292.3	292.5	292.7	293.0	293.3	293.6	293.6
135°	308.8	308.8	308.7	308.6	308.5	308.6	309.0	309.2	309.5	309.8	310.0
137.5°	323.9	324.0	324.0	324.0	324.0	324.2	324.5	324.8	325.1	325.4	325.6
140°	333.8	333.9	334.0	334.1	334.3	334.4	334.6	334.7	334.8	335.0	335.2
142.5°	342.6	342.8	343.0	343.3	343.6	343.8	343.8	343.9	344.0	344.1	344.2
145°	356.1	356.3	356.5	356.8	357.0	357.0	357.0	357.0	357.0	357.0	357.1
147.5°	366.8	367.3	367.7	368.1	368.5	368.6	368.5	368.5	368.4	368.4	368.4
150°	374.7	375.0	375.2	375.6	375.9	375.9	375.9	375.8	375.7	375.7	375.7
152.5°	381.3	381.5	381.7	381.9	382.2	382.2	382.1	381.9	381.8	381.7	381.8
155°	390.5	390.6	390.6	390.7	390.7	390.7	390.5	390.2	390.0	389.9	390.1
157.5°	398.2	398.1	398.1	398.1	398.1	397.9	397.7	397.4	397.2	397.0	397.3
160°	402.8	402.5	402.3	402.2	401.9	401.8	401.7	401.6	401.5	401.4	401.9
162.5°	406.8	406.5	406.3	406.0	405.7	405.6	405.5	405.4	405.4	405.3	405.7
165°	411.9	411.5	411.2	410.8	410.5	410.3	410.3	410.3	410.3	410.3	410.9
167.5°	415.9	415.5	415.2	414.8	414.5	414.3	414.2	414.2	414.1	414.1	414.7
170°	418.2	417.8	417.3	417.0	416.5	416.3	416.4	416.5	416.5	416.6	417.1
172.5°	419.7	419.3	418.8	418.5	418.0	417.9	417.9	418.0	418.0	418.1	418.7
175°	421.3	420.9	420.5	420.1	419.6	419.5	419.5	419.6	419.7	419.7	420.4
177.5°	422.1	421.7	421.3	420.9	420.5	420.4	420.5	420.6	420.7	420.8	421.3
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3



TEST NUMBER: P332541-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	862.9	864.2	865.4	865.9	865.8	865.7	865.6	865.4
5°	858.3	860.0	861.7	862.4	862.0	861.7	861.4	861.1
7.5°	848.7	850.1	851.4	852.0	851.9	851.7	851.5	851.2
10°	840.7	842.0	843.2	843.6	843.3	843.0	842.7	842.4
12.5°	831.0	832.3	833.7	834.1	833.7	833.2	832.9	832.4
15°	812.3	813.2	814.1	814.4	814.0	813.5	813.0	812.5
17.5°	791.1	791.7	792.3	792.4	792.1	791.8	791.5	791.2
20°	775.3	775.8	776.2	776.3	776.0	775.7	775.4	775.1
22.5°	758.8	759.6	760.5	760.6	760.1	759.6	759.0	758.4
25°	731.6	731.8	732.0	731.7	731.1	730.5	729.9	729.2
27.5°	701.2	700.8	700.4	699.9	699.1	698.4	697.6	696.8
30°	680.2	679.6	678.9	678.2	677.4	676.7	675.9	675.1
32.5°	658.8	658.1	657.4	656.6	655.9	655.1	654.2	653.5
35°	625.1	624.0	622.9	622.1	621.3	620.5	619.7	618.9
37.5°	589.9	588.6	587.5	586.4	585.4	584.3	583.4	582.3
40°	565.3	563.7	562.1	561.0	560.2	559.5	558.7	557.9
42.5°	541.4	539.6	537.8	536.6	536.2	535.7	535.1	534.6
45°	504.5	502.8	501.1	500.1	499.6	499.2	498.6	498.2
47.5°	468.9	466.9	465.0	463.5	462.4	461.1	459.9	458.8
50°	443.9	441.8	439.6	438.1	437.1	436.2	435.3	434.4
52.5°	418.3	416.4	414.6	413.0	411.8	410.6	409.5	408.3
55°	380.8	378.9	377.0	375.6	374.7	373.8	372.8	371.9
57.5°	343.0	341.3	339.5	338.1	337.2	336.4	335.5	334.6
60°	317.1	315.8	314.3	313.3	312.5	311.7	310.9	310.1
62.5°	291.9	290.5	289.3	288.3	287.5	286.8	286.0	285.2
65°	255.0	253.5	252.0	250.8	250.0	249.2	248.5	247.7
67.5°	217.1	215.7	214.2	213.3	213.1	212.9	212.7	212.5
70°	193.2	192.0	190.7	189.9	189.4	189.0	188.5	188.1
72.5°	169.2	168.3	167.3	166.6	166.1	165.7	165.2	164.7
75°	134.7	134.1	133.6	133.1	133.0	132.9	132.7	132.5
77.5°	102.0	101.8	101.7	101.4	100.9	100.6	100.1	99.8
80°	81.2	81.0	80.6	80.4	80.3	80.1	80.0	79.8
82.5°	62.6	62.4	62.2	62.1	62.0	61.8	61.6	61.4
85°	36.1	36.1	36.1	36.0	35.8	35.7	35.6	35.4
87.5°	14.9	15.0	15.1	15.1	15.2	15.2	15.2	15.2
90°	7.8	8.2	8.6	8.9	9.0	9.2	9.3	9.5
92.5°	7.5	7.9	8.4	8.6	8.6	8.6	8.6	8.7
95°	7.8	8.2	8.6	8.8	8.9	9.0	9.1	9.1
97.5°	8.4	8.5	8.5	8.6	8.6	8.6	8.7	8.8
100°	11.5	10.3	9.1	8.6	8.6	8.6	8.7	8.8
102.5°	41.1	28.3	15.4	9.0	9.0	9.0	9.1	9.1
105°	99.6	100.2	100.9	99.9	97.4	94.9	92.3	89.8
107.5°	123.2	123.5	123.9	124.1	124.4	124.7	124.9	125.2
110°	139.3	139.4	139.6	139.7	139.9	140.2	140.4	140.5



TEST NUMBER: P332541-940

CATALOG NUMBER: S124DIP-S575D365U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	154.8	154.8	154.7	154.9	155.2	155.4	155.7	156.0
115°	178.0	178.2	178.3	178.3	178.3	178.3	178.3	178.3
117.5°	201.3	201.3	201.3	201.3	201.3	201.3	201.3	201.2
120°	215.8	216.0	216.2	216.2	216.0	215.8	215.7	215.5
122.5°	230.1	230.2	230.2	230.2	230.1	230.0	229.8	229.7
125°	250.0	250.2	250.4	250.6	250.7	250.7	250.7	250.8
127.5°	269.8	269.7	269.7	269.7	269.7	269.6	269.5	269.5
130°	281.9	282.0	282.0	282.0	282.0	282.0	282.0	282.0
132.5°	293.7	293.8	293.9	293.9	293.8	293.7	293.7	293.6
135°	310.0	310.2	310.3	310.5	310.6	310.8	310.9	311.0
137.5°	325.7	325.9	326.0	326.1	326.0	326.0	325.9	325.9
140°	335.4	335.6	335.8	336.0	336.1	336.1	336.2	336.3
142.5°	344.4	344.6	344.6	344.7	344.8	344.8	344.8	344.8
145°	357.2	357.3	357.3	357.4	357.6	357.8	357.8	358.0
147.5°	368.5	368.5	368.5	368.6	368.7	368.7	368.8	368.9
150°	375.7	375.7	375.7	375.7	375.8	375.9	375.9	375.9
152.5°	381.9	382.0	382.2	382.2	382.1	382.1	382.1	382.0
155°	390.4	390.7	390.9	391.0	390.7	390.6	390.4	390.1
157.5°	397.7	398.1	398.4	398.4	398.1	397.7	397.3	397.0
160°	402.3	402.8	403.1	403.1	402.8	402.3	401.9	401.4
162.5°	406.1	406.5	407.0	406.9	406.4	406.0	405.5	405.0
165°	411.4	412.0	412.6	412.5	411.9	411.3	410.6	410.0
167.5°	415.4	416.0	416.5	416.5	415.8	415.1	414.4	413.8
170°	417.8	418.3	418.8	418.7	418.1	417.4	416.7	416.0
172.5°	419.3	419.8	420.4	420.3	419.5	418.7	418.0	417.2
175°	421.1	421.7	422.3	422.2	421.3	420.5	419.6	418.8
177.5°	421.8	422.2	422.7	422.5	421.9	421.2	420.5	419.8
180°	421.3	421.3	421.3	421.3	421.3	421.3	421.3	421.3

(END OF REPORT)