

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333531-930

Luminaire Tested: **S125RDIP-S610D590U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333531-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D590U930-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3668.7 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333531-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333531-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5297	5297	5297
5°	5309	5249	5281
10°	5269	5200	5200
15°	5207	5094	5053
20°	5126	4947	4887
25°	5032	4802	4697
30°	4915	4633	4486
35°	4796	4459	4249
40°	4684	4278	4016
45°	4549	4074	3763
50°	4413	3852	3497
55°	4255	3640	3216
60°	4097	3384	2913
65°	3909	3085	2566
70°	3697	2713	2211
75°	3401	2286	1839
80°	2998	1796	1543
85°	2527	1467	1378



TEST NUMBER: P333531-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.1	2.1
10°-20°	215.5	5.9
20°-30°	312.5	8.5
30°-40°	356.2	9.7
40°-50°	347.2	9.5
50°-60°	292.3	8.0
60°-70°	204.9	5.6
70°-80°	105.3	2.9
80°-90°	27.9	0.8
90°-100°	167.2	4.6
100°-110°	359.4	9.8
110°-120°	337.3	9.2
120°-130°	273.4	7.5
130°-140°	219.4	6.0
140°-150°	165.6	4.5
150°-160°	116.5	3.2
160°-170°	68.7	1.9
170°-180°	22.3	0.6
0°-30°	605.2	16.5
0°-40°	961.4	26.2
0°-60°	1600.8	43.6
0°-90°	1938.9	52.8
90°-120°	864.0	23.5
90°-150°	1522.3	41.5
90°-180°	1730.0	47.2
0°-180°	3668.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	820	820	820	820	820	
5°	819	816	810	815	815	78
15°	779	774	762	761	756	219
25°	706	696	674	666	659	325
35°	608	593	566	548	539	381
45°	498	479	446	422	412	384
55°	378	357	323	296	286	338
65°	256	234	202	178	168	253
75°	136	117	92	79	74	144
85°	34	23	20	19	19	38
90°	0	4	7	10	11	2
95°	15	45	412	187	109	16
105°	53	73	337	664	616	55
115°	94	113	271	583	686	92
125°	130	153	260	464	541	115
135°	152	183	258	389	449	118
145°	178	203	259	322	354	111
155°	203	218	252	285	297	93
165°	221	227	242	256	260	62
175°	230	230	232	235	234	22
180°	231	231	231	231	231	



TEST NUMBER: P333531-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2
2.5°	821.7	821.3	821.0	820.7	820.4	819.6	818.5	817.4	816.3	815.2	816.3
5°	818.9	818.4	817.8	817.3	816.7	815.7	814.2	812.7	811.1	809.6	811.0
7.5°	810.9	810.3	809.8	809.3	808.8	807.6	805.8	804.0	802.2	800.3	801.3
10°	803.4	803.0	802.6	802.2	801.8	800.6	798.7	796.8	794.8	792.9	793.3
12.5°	795.0	794.5	793.9	793.4	792.9	791.3	788.8	786.2	783.6	781.0	781.3
15°	778.7	777.8	777.0	776.2	775.3	773.5	770.6	767.7	764.8	761.9	761.8
17.5°	760.2	759.0	757.7	756.4	755.1	752.7	749.0	745.4	741.8	738.2	737.4
20°	745.8	744.4	743.1	741.7	740.3	737.4	733.0	728.6	724.2	719.8	719.1
22.5°	729.9	728.6	727.2	725.9	724.5	721.5	716.8	712.2	707.6	703.0	701.6
25°	706.2	704.1	702.1	700.0	697.9	694.3	689.3	684.1	679.1	673.9	672.2
27.5°	678.9	676.5	673.9	671.4	668.9	665.0	659.5	654.0	648.6	643.1	640.6
30°	659.1	656.5	653.9	651.3	648.7	644.4	638.6	632.9	627.1	621.3	618.2
32.5°	639.8	636.7	633.7	630.6	627.5	623.1	617.2	611.3	605.4	599.5	596.0
35°	608.3	605.0	601.7	598.4	595.1	590.4	584.2	578.0	571.8	565.6	561.6
37.5°	577.5	573.4	569.4	565.4	561.4	556.2	549.8	543.4	537.0	530.6	525.9
40°	555.6	551.5	547.4	543.2	539.2	533.8	527.2	520.6	514.0	507.4	502.1
42.5°	532.9	528.6	524.4	520.2	515.9	510.4	503.5	496.7	489.9	483.1	478.0
45°	498.1	494.1	490.1	486.1	482.1	476.3	468.7	461.1	453.6	446.0	440.5
47.5°	462.0	457.8	453.6	449.4	445.2	439.2	431.6	424.0	416.4	408.7	403.1
50°	439.2	434.6	430.1	425.6	421.0	414.8	407.0	399.2	391.3	383.4	377.6
52.5°	414.4	409.8	405.1	400.5	395.8	389.8	382.4	375.0	367.5	360.1	353.9
55°	377.9	373.5	369.1	364.7	360.3	354.2	346.5	338.8	331.1	323.3	317.2
57.5°	341.0	336.2	331.5	326.9	322.1	316.0	308.6	301.2	293.8	286.3	280.2
60°	317.2	312.3	307.5	302.7	297.9	291.8	284.3	276.9	269.5	262.0	256.0
62.5°	291.9	287.3	282.7	278.1	273.5	267.4	259.9	252.3	244.8	237.3	231.6
65°	255.8	251.2	246.5	241.8	237.1	231.1	223.8	216.5	209.2	201.9	196.4
67.5°	220.0	215.3	210.7	206.0	201.3	195.5	188.5	181.5	174.5	167.5	162.5
70°	195.8	191.1	186.4	181.7	177.0	171.2	164.4	157.5	150.6	143.7	139.4
72.5°	171.9	167.4	162.8	158.2	153.7	148.1	141.7	135.3	128.8	122.4	118.5
75°	136.3	132.2	128.0	123.9	119.8	114.8	109.0	103.2	97.4	91.6	88.6
77.5°	100.9	97.5	94.2	90.9	87.6	83.6	79.0	74.4	69.8	65.1	63.0
80°	80.6	77.2	73.9	70.6	67.3	63.8	59.8	56.0	52.2	48.3	47.0
82.5°	60.7	57.7	54.8	51.8	48.8	46.0	43.4	40.7	38.1	35.5	34.9
85°	34.1	31.6	29.1	26.7	24.1	22.6	21.9	21.2	20.5	19.8	19.6
87.5°	11.5	10.8	10.2	9.6	9.0	8.8	8.8	8.9	8.8	8.9	9.0
90°	0.5	0.9	1.9	2.8	3.8	4.6	5.1	6.0	6.5	7.4	7.9
92.5°	5.7	6.8	10.8	16.6	24.5	38.2	63.5	106.2	152.4	149.9	121.4
95°	15.3	15.8	19.6	24.6	34.9	55.8	105.6	207.9	336.2	412.1	403.2
97.5°	25.5	26.0	28.6	33.8	43.0	58.0	91.0	165.9	300.3	440.0	510.2
100°	32.5	33.5	35.4	40.4	49.3	63.3	90.3	150.7	267.9	420.0	536.2
102.5°	40.4	40.9	42.4	47.9	56.0	69.5	93.6	144.4	243.3	384.6	520.6
105°	52.6	52.6	54.9	59.5	66.9	80.0	100.4	141.9	219.5	337.2	470.7
107.5°	64.5	65.4	67.6	71.4	79.2	90.9	110.7	146.1	209.5	304.5	419.7
110°	73.1	73.9	75.8	80.0	87.0	99.1	118.1	150.2	206.5	289.3	390.7



TEST NUMBER: P333531-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	81.6	82.5	84.0	88.2	95.1	106.9	125.2	155.4	206.5	280.4	369.1
115°	93.9	94.9	96.3	100.4	107.5	119.0	136.2	163.2	207.9	270.7	345.5
117.5°	105.1	106.5	108.0	112.2	120.1	131.3	147.7	172.2	210.9	266.0	331.5
120°	112.5	114.0	115.8	120.0	127.9	139.5	155.8	178.1	213.9	263.7	323.7
122.5°	120.3	121.4	122.9	127.0	135.7	147.3	163.6	184.8	216.5	261.9	317.0
125°	130.2	131.2	133.5	137.6	146.5	158.6	173.9	194.0	220.9	259.5	307.9
127.5°	137.9	139.3	142.4	147.7	157.0	169.1	183.8	202.3	225.8	258.4	299.5
130°	142.8	144.1	147.9	153.9	163.7	175.8	190.2	207.9	228.9	257.6	293.9
132.5°	146.5	148.3	152.7	159.6	169.7	181.7	196.2	212.7	232.2	257.6	289.4
135°	152.5	154.4	160.0	167.5	177.2	189.7	204.2	219.5	236.7	257.6	284.1
137.5°	160.2	161.6	166.8	174.2	183.8	196.7	209.9	224.5	240.9	258.2	279.4
140°	164.6	166.0	171.6	179.0	187.9	200.5	213.9	227.9	242.8	258.6	277.2
142.5°	169.8	170.9	176.1	183.5	192.0	203.8	216.5	229.8	243.9	258.9	275.3
145°	177.7	178.6	183.2	189.7	198.1	208.8	220.9	232.5	245.1	258.6	272.6
147.5°	185.8	186.4	190.4	196.4	203.7	213.1	223.7	234.2	245.6	257.4	269.6
150°	190.7	191.6	194.9	200.9	207.4	215.3	225.6	235.3	245.6	256.2	267.4
152.5°	195.9	196.4	199.3	204.6	210.8	217.9	227.4	236.0	245.2	254.8	264.8
155°	202.8	202.8	205.5	210.2	214.8	221.4	229.3	236.7	244.2	252.1	260.4
157.5°	208.9	208.8	211.1	215.1	219.2	224.0	230.9	237.2	243.0	249.2	256.3
160°	213.0	212.5	214.4	217.7	221.4	225.6	231.6	237.2	241.8	247.4	253.0
162.5°	216.4	215.9	217.8	220.6	223.6	227.1	232.4	236.8	240.8	245.2	250.1
165°	221.4	220.5	221.8	224.1	226.0	228.9	232.5	236.3	239.0	241.8	245.6
167.5°	224.7	224.3	225.1	226.4	227.7	229.4	232.5	235.1	236.4	238.6	241.2
170°	227.0	226.5	227.0	227.9	228.9	230.2	232.5	234.4	235.3	236.7	238.6
172.5°	228.4	227.6	228.0	229.0	229.6	230.2	232.2	233.7	233.8	234.5	235.9
175°	230.2	229.3	229.8	230.2	230.2	230.2	231.6	232.5	232.0	232.0	232.5
177.5°	231.1	230.3	230.3	230.6	230.3	230.3	231.1	231.4	230.6	230.6	231.1
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333531-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2
2.5°	817.4	818.5	819.6	820.1	820.0	819.9	819.8	819.7
5°	812.4	813.8	815.1	815.7	815.4	815.1	814.9	814.6
7.5°	802.3	803.2	804.2	804.5	804.2	803.9	803.6	803.3
10°	793.7	794.1	794.6	794.6	794.1	793.7	793.3	792.9
12.5°	781.6	782.0	782.2	782.0	781.4	780.8	780.2	779.5
15°	761.7	761.5	761.4	760.7	759.5	758.2	757.0	755.7
17.5°	736.8	736.1	735.4	734.5	733.5	732.5	731.5	730.4
20°	718.4	717.7	717.1	716.1	714.9	713.6	712.4	711.1
22.5°	700.3	698.9	697.6	696.3	695.4	694.3	693.3	692.3
25°	670.4	668.6	666.8	665.1	663.7	662.1	660.6	659.1
27.5°	638.1	635.6	633.1	631.1	629.7	628.2	626.7	625.3
30°	615.0	611.8	608.6	606.4	605.2	604.0	602.8	601.5
32.5°	592.5	589.1	585.5	583.0	581.4	579.8	578.3	576.7
35°	557.6	553.6	549.6	546.7	544.7	542.7	540.9	538.9
37.5°	521.1	516.2	511.4	508.1	506.2	504.4	502.6	500.7
40°	496.8	491.6	486.4	483.0	481.4	479.6	478.0	476.4
42.5°	473.0	468.0	463.0	459.3	456.9	454.4	452.0	449.6
45°	435.0	429.5	424.0	420.2	418.2	416.0	414.0	412.0
47.5°	397.4	391.7	386.0	382.0	379.8	377.5	375.2	372.9
50°	371.9	366.1	360.3	356.4	354.3	352.3	350.2	348.1
52.5°	347.7	341.4	335.3	331.1	329.1	327.0	324.9	322.9
55°	311.0	304.8	298.6	294.4	292.2	290.0	287.8	285.6
57.5°	274.2	268.2	262.1	258.0	256.1	254.1	252.3	250.3
60°	249.9	243.9	237.8	233.7	231.7	229.6	227.6	225.5
62.5°	226.0	220.4	214.7	210.9	208.9	206.8	204.7	202.7
65°	190.9	185.4	179.9	176.1	174.1	172.0	169.9	167.9
67.5°	157.4	152.4	147.3	144.0	142.4	140.7	139.0	137.4
70°	135.2	130.9	126.6	123.7	122.1	120.4	118.7	117.1
72.5°	114.5	110.6	106.6	104.1	103.1	101.9	100.9	99.7
75°	85.6	82.6	79.6	77.5	76.6	75.7	74.7	73.7
77.5°	60.9	58.8	56.7	55.3	54.5	53.8	53.2	52.4
80°	45.8	44.6	43.4	42.6	42.3	42.1	41.7	41.5
82.5°	34.2	33.7	33.1	32.8	32.6	32.4	32.3	32.1
85°	19.6	19.4	19.2	19.2	19.0	18.8	18.8	18.6
87.5°	9.1	9.2	9.3	9.5	9.3	9.2	9.2	9.0
90°	8.4	8.8	9.3	10.2	10.2	10.2	10.7	10.7
92.5°	82.4	59.8	45.0	38.2	32.2	31.1	30.4	29.7
95°	334.4	263.7	206.5	167.5	134.4	120.4	116.8	109.3
97.5°	498.0	448.4	392.7	338.3	309.7	283.6	270.1	264.2
100°	572.0	549.3	501.3	453.0	420.9	387.4	370.2	362.7
102.5°	597.0	611.0	588.0	555.3	521.0	497.2	478.5	472.9
105°	582.3	646.0	666.4	661.3	646.5	631.1	621.8	616.2
107.5°	529.8	614.8	667.4	691.6	699.2	699.1	696.0	692.3
110°	491.1	579.5	645.1	684.6	705.5	714.4	717.6	717.6



TEST NUMBER: P333531-930

CATALOG NUMBER: S125RDIP-S610D590U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	460.6	544.5	610.8	657.5	688.0	703.2	711.3	714.6
115°	422.2	494.4	558.1	608.8	645.1	667.4	680.4	686.5
117.5°	397.5	459.7	514.5	561.1	597.4	620.4	633.3	637.1
120°	384.2	439.9	491.1	532.1	566.5	588.8	601.4	605.0
122.5°	374.1	425.8	471.4	509.7	540.4	560.8	573.4	576.7
125°	359.5	406.9	447.4	480.9	507.0	526.0	536.2	540.9
127.5°	344.6	388.9	426.6	458.0	481.6	498.5	508.1	510.2
130°	335.3	376.3	412.5	442.7	466.0	481.4	490.6	493.4
132.5°	326.0	364.4	397.3	426.4	449.6	465.0	473.5	476.7
135°	313.9	346.0	375.8	402.3	422.7	438.1	446.5	449.2
137.5°	303.7	329.6	354.4	376.9	395.2	409.2	416.9	420.0
140°	298.1	320.0	341.4	360.9	378.1	390.2	397.1	399.5
142.5°	293.3	311.8	330.2	347.2	361.7	371.9	378.5	380.5
145°	287.0	301.3	315.8	328.3	339.5	347.4	352.5	354.4
147.5°	281.0	292.7	303.8	313.2	322.1	328.4	331.4	332.2
150°	277.6	287.9	296.7	305.1	312.1	317.6	319.5	320.0
152.5°	273.9	283.1	291.1	297.7	303.5	307.9	309.8	310.3
155°	268.3	275.8	282.3	287.4	292.0	295.3	296.7	297.2
157.5°	262.8	268.9	273.9	277.9	281.5	284.2	285.5	285.4
160°	259.0	263.7	268.3	271.6	274.8	277.2	278.1	277.6
162.5°	254.9	259.3	263.1	266.0	268.6	270.5	270.7	270.6
165°	249.2	252.5	255.4	257.6	259.5	260.4	260.4	260.4
167.5°	243.9	246.1	248.2	249.8	250.8	251.6	251.2	251.1
170°	240.9	242.3	243.7	244.6	245.6	246.1	246.1	245.6
172.5°	237.6	239.0	239.9	240.5	240.8	241.6	240.8	240.4
175°	233.9	233.9	234.9	234.9	234.9	235.3	234.4	233.9
177.5°	231.4	231.8	231.8	231.8	231.4	231.8	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6

(END OF REPORT)