

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332559-940

Luminaire Tested: **S124DIP-S575D810U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332559-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIP-S575D810U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5108.5 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332559-940

CATALOG NUMBER: S124DIP-S575D810U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332559-940

CATALOG NUMBER: S124DIP-S575D810U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	96	92	88	85	88	84	81	78	70	67	65	57	55	53	44	43	42	37
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36	31
3	80	71	63	58	73	65	58	53	54	49	45	44	41	38	35	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17
7	57	45	37	32	52	41	34	29	35	29	26	29	25	22	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	17	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6990	6990	6990
5°	7012	6928	6978
10°	6968	6871	6906
15°	6884	6774	6791
20°	6772	6653	6659
25°	6644	6515	6495
30°	6488	6352	6293
35°	6326	6182	6099
40°	6157	5989	5879
45°	5981	5799	5688
50°	5786	5630	5456
55°	5576	5410	5234
60°	5365	5165	5007
65°	5129	4932	4732
70°	4865	4617	4440
75°	4457	4242	4133
80°	3966	3808	3710
85°	3473	3344	3279



TEST NUMBER: P332559-940

CATALOG NUMBER: S124DIP-S575D810U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	1.6
10°-20°	229.8	4.5
20°-30°	338.2	6.6
30°-40°	393.2	7.7
40°-50°	393.2	7.7
50°-60°	343.9	6.7
60°-70°	255.4	5.0
70°-80°	145.1	2.8
80°-90°	44.6	0.9
90°-100°	31.9	0.6
100°-110°	203.3	4.0
110°-120°	388.9	7.6
120°-130°	493.7	9.7
130°-140°	528.2	10.3
140°-150°	493.9	9.7
150°-160°	398.3	7.8
160°-170°	256.9	5.0
170°-180°	88.5	1.7
0°-30°	649.5	12.7
0°-40°	1042.7	20.4
0°-60°	1779.8	34.8
0°-90°	2224.9	43.6
90°-120°	624.1	12.2
90°-150°	2139.8	41.9
90°-180°	2884.0	56.5
0°-180°	5108.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	865	862	855	862	861	82
15°	824	820	810	814	812	232
25°	746	741	731	732	729	343
35°	642	637	627	622	619	401
45°	524	519	508	501	498	404
55°	396	394	384	376	372	355
65°	268	265	258	251	248	266
75°	143	139	136	133	132	152
85°	38	37	36	36	35	41
90°	2	10	15	19	21	4
95°	38	16	15	19	20	49
105°	210	214	218	222	199	220
115°	392	394	393	395	395	385
125°	551	553	552	554	555	492
135°	683	683	685	687	688	526
145°	788	790	790	791	792	492
155°	864	864	862	865	863	398
165°	911	908	908	913	907	257
175°	932	928	929	934	927	89
180°	932	932	932	932	932	



TEST NUMBER: P332559-940

CATALOG NUMBER: S124DIP-S575D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	868.2	867.8	867.5	867.1	866.7	865.9	864.5	863.2	861.7	860.4	861.7
5°	865.3	864.7	864.1	863.4	862.8	861.7	860.0	858.3	856.6	854.9	856.6
7.5°	857.2	856.6	856.0	855.4	854.8	853.5	851.7	849.8	847.8	846.0	847.4
10°	850.0	849.4	848.8	848.2	847.6	846.2	844.3	842.2	840.3	838.2	839.5
12.5°	840.6	840.0	839.4	838.7	838.1	836.8	834.6	832.5	830.4	828.2	829.6
15°	823.7	823.0	822.4	821.8	821.2	819.7	817.4	815.1	812.8	810.5	811.4
17.5°	803.3	802.5	801.7	800.9	800.1	798.7	796.5	794.3	792.1	790.0	790.5
20°	788.3	787.5	786.8	786.0	785.2	783.6	781.3	779.0	776.7	774.4	774.8
22.5°	772.1	771.2	770.2	769.1	768.1	766.4	764.1	761.8	759.5	757.2	758.0
25°	745.9	744.8	743.8	742.7	741.6	740.0	737.8	735.7	733.5	731.4	731.6
27.5°	716.0	714.9	713.7	712.7	711.5	710.0	707.9	706.0	703.9	702.0	701.6
30°	696.0	694.7	693.5	692.2	691.1	689.4	687.4	685.4	683.4	681.4	680.8
32.5°	674.8	673.8	672.6	671.5	670.5	668.8	666.7	664.6	662.5	660.3	659.6
35°	641.9	640.8	639.7	638.6	637.6	635.9	633.7	631.6	629.5	627.3	626.2
37.5°	607.0	606.0	605.0	604.0	603.1	601.5	599.1	596.8	594.5	592.2	591.0
40°	584.2	583.0	581.8	580.6	579.3	577.6	575.2	572.9	570.6	568.3	566.8
42.5°	559.8	559.1	558.4	557.6	556.9	555.2	552.7	550.1	547.5	545.0	543.2
45°	523.9	522.8	521.7	520.7	519.6	517.8	515.3	512.8	510.4	507.9	506.2
47.5°	486.2	485.5	484.8	484.0	483.3	481.8	479.6	477.2	474.9	472.7	470.7
50°	460.7	460.1	459.5	458.9	458.3	456.9	454.8	452.5	450.4	448.3	446.1
52.5°	435.8	435.1	434.3	433.5	432.8	431.3	429.0	426.8	424.5	422.1	420.3
55°	396.2	395.7	395.3	394.8	394.4	393.1	390.9	388.7	386.6	384.4	382.5
57.5°	358.5	357.9	357.4	356.9	356.3	355.1	352.9	350.8	348.7	346.5	344.7
60°	332.3	331.6	330.8	330.0	329.3	327.9	325.9	323.9	321.9	319.9	318.5
62.5°	306.8	306.2	305.5	304.9	304.3	302.8	300.8	298.6	296.5	294.4	293.1
65°	268.5	267.8	267.0	266.3	265.5	264.3	262.8	261.2	259.7	258.2	256.5
67.5°	230.0	229.3	228.5	227.8	227.1	226.0	224.5	223.1	221.6	220.1	218.6
70°	206.1	205.0	203.9	202.9	201.8	200.6	199.4	198.1	196.9	195.6	194.5
72.5°	180.6	179.5	178.4	177.3	176.2	175.2	174.2	173.3	172.3	171.2	170.2
75°	142.9	142.1	141.4	140.6	139.8	139.1	138.3	137.5	136.8	136.0	135.4
77.5°	107.0	106.6	106.3	106.0	105.7	105.1	104.4	103.8	103.1	102.5	102.2
80°	85.3	84.9	84.4	84.0	83.5	83.1	82.8	82.5	82.2	81.9	81.6
82.5°	64.3	64.0	63.8	63.6	63.4	63.2	63.2	63.1	63.0	63.0	62.8
85°	37.5	37.5	37.5	37.5	37.5	37.3	37.0	36.7	36.4	36.1	36.1
87.5°	14.9	15.1	15.2	15.5	15.7	15.9	16.1	16.1	16.2	16.4	16.6
90°	2.1	3.8	5.5	7.2	8.9	10.3	11.6	12.8	14.1	15.3	16.2
92.5°	8.8	8.9	9.0	9.1	9.2	9.8	11.1	12.3	13.6	14.8	15.7
95°	38.3	33.1	27.8	22.6	17.3	14.7	14.9	15.1	15.2	15.3	16.2
97.5°	81.4	84.7	88.0	91.3	94.6	87.6	70.3	53.0	35.7	18.4	18.5
100°	114.3	117.2	119.9	122.7	125.5	116.2	94.8	73.5	52.1	30.7	28.0
102.5°	151.1	153.2	155.2	157.3	159.3	159.0	156.1	153.4	150.6	147.8	119.4
105°	209.8	210.8	211.7	212.7	213.6	214.5	215.2	216.0	216.8	217.5	218.9
107.5°	264.4	264.8	265.3	265.8	266.3	267.0	268.0	269.1	270.2	271.3	271.9
110°	301.2	301.7	302.1	302.6	303.1	303.7	304.7	305.6	306.6	307.5	307.8



TEST NUMBER: P332559-940

CATALOG NUMBER: S124DIP-S575D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	336.9	337.7	338.6	339.4	340.3	340.9	341.3	341.7	342.1	342.6	342.6
115°	391.8	392.3	392.8	393.2	393.7	393.9	393.7	393.5	393.4	393.2	393.5
117.5°	441.3	441.9	442.6	443.2	443.8	444.3	444.6	445.0	445.3	445.7	445.6
120°	474.8	475.5	476.1	476.7	477.2	477.5	477.3	477.2	477.1	476.9	477.2
122.5°	506.0	506.4	506.8	507.1	507.6	507.8	508.0	508.3	508.5	508.7	508.9
125°	550.8	551.4	552.1	552.7	553.3	553.4	553.1	552.9	552.5	552.2	552.7
127.5°	593.2	593.3	593.5	593.7	593.8	594.2	594.9	595.7	596.4	597.1	597.0
130°	620.5	620.7	620.8	621.0	621.2	621.4	621.9	622.4	622.9	623.3	623.5
132.5°	645.6	645.9	646.2	646.5	646.8	647.2	647.7	648.4	648.9	649.5	649.7
135°	683.3	683.1	683.0	682.8	682.7	682.9	683.5	684.1	684.7	685.4	685.6
137.5°	716.6	716.7	716.8	716.8	716.8	717.2	717.9	718.6	719.3	720.0	720.3
140°	738.3	738.7	739.0	739.3	739.6	739.9	740.2	740.6	740.8	741.1	741.6
142.5°	757.9	758.4	759.0	759.6	760.1	760.5	760.6	760.9	761.1	761.3	761.6
145°	787.8	788.4	788.8	789.3	789.7	790.0	790.0	790.0	790.0	790.0	790.1
147.5°	811.7	812.6	813.4	814.3	815.2	815.6	815.4	815.2	815.0	814.9	815.0
150°	829.0	829.6	830.3	830.9	831.4	831.7	831.5	831.4	831.3	831.1	831.1
152.5°	843.5	844.0	844.5	845.0	845.5	845.6	845.3	845.1	844.7	844.5	844.7
155°	863.9	864.0	864.2	864.3	864.5	864.3	863.9	863.4	862.9	862.5	863.1
157.5°	881.0	880.9	880.8	880.7	880.7	880.3	879.8	879.3	878.8	878.2	879.0
160°	891.1	890.6	890.1	889.7	889.2	888.9	888.8	888.6	888.4	888.2	889.2
162.5°	900.0	899.4	898.8	898.2	897.6	897.2	897.1	897.0	896.8	896.6	897.6
165°	911.2	910.5	909.7	908.9	908.2	907.8	907.8	907.8	907.8	907.8	909.0
167.5°	920.2	919.4	918.6	917.7	916.9	916.5	916.4	916.3	916.2	916.1	917.5
170°	925.2	924.3	923.4	922.4	921.5	921.1	921.2	921.4	921.6	921.8	922.9
172.5°	928.5	927.6	926.7	925.8	924.9	924.4	924.6	924.8	924.9	925.1	926.3
175°	932.2	931.2	930.3	929.4	928.4	928.1	928.3	928.4	928.5	928.7	930.1
177.5°	933.9	933.0	932.1	931.2	930.4	930.1	930.3	930.6	930.9	931.0	932.0
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2



TEST NUMBER: P332559-940

CATALOG NUMBER: S124DIP-S575D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.9	865.9	865.9	865.9	865.9	865.9	865.9	865.9
2.5°	862.9	864.2	865.4	865.9	865.8	865.7	865.6	865.4
5°	858.3	860.0	861.7	862.4	862.0	861.7	861.4	861.1
7.5°	848.7	850.1	851.4	852.0	851.9	851.7	851.5	851.2
10°	840.7	842.0	843.2	843.6	843.3	843.0	842.7	842.4
12.5°	831.0	832.3	833.7	834.1	833.7	833.2	832.9	832.4
15°	812.3	813.2	814.1	814.4	814.0	813.5	813.0	812.5
17.5°	791.1	791.7	792.3	792.4	792.1	791.8	791.5	791.2
20°	775.3	775.8	776.2	776.3	776.0	775.7	775.4	775.1
22.5°	758.8	759.6	760.5	760.6	760.1	759.6	759.0	758.4
25°	731.6	731.8	732.0	731.7	731.1	730.5	729.9	729.2
27.5°	701.2	700.8	700.4	699.9	699.1	698.4	697.6	696.8
30°	680.2	679.6	678.9	678.2	677.4	676.7	675.9	675.1
32.5°	658.8	658.1	657.4	656.6	655.9	655.1	654.2	653.5
35°	625.1	624.0	622.9	622.1	621.3	620.5	619.7	618.9
37.5°	589.9	588.6	587.5	586.4	585.4	584.3	583.4	582.3
40°	565.3	563.7	562.1	561.0	560.2	559.5	558.7	557.9
42.5°	541.4	539.6	537.8	536.6	536.2	535.7	535.1	534.6
45°	504.5	502.8	501.1	500.1	499.6	499.2	498.6	498.2
47.5°	468.9	466.9	465.0	463.5	462.4	461.1	459.9	458.8
50°	443.9	441.8	439.6	438.1	437.1	436.2	435.3	434.4
52.5°	418.3	416.4	414.6	413.0	411.8	410.6	409.5	408.3
55°	380.8	378.9	377.0	375.6	374.7	373.8	372.8	371.9
57.5°	343.0	341.3	339.5	338.1	337.2	336.4	335.5	334.6
60°	317.1	315.8	314.3	313.3	312.5	311.7	310.9	310.1
62.5°	291.9	290.5	289.3	288.3	287.5	286.8	286.0	285.2
65°	255.0	253.5	252.0	250.8	250.0	249.2	248.5	247.7
67.5°	217.1	215.7	214.2	213.3	213.1	212.9	212.7	212.5
70°	193.2	192.0	190.7	189.9	189.4	189.0	188.5	188.1
72.5°	169.2	168.3	167.3	166.6	166.1	165.7	165.2	164.7
75°	134.7	134.1	133.6	133.1	133.0	132.9	132.7	132.5
77.5°	102.0	101.8	101.7	101.4	100.9	100.6	100.1	99.8
80°	81.2	81.0	80.6	80.4	80.3	80.1	80.0	79.8
82.5°	62.6	62.4	62.2	62.1	62.0	61.8	61.6	61.4
85°	36.1	36.1	36.1	36.0	35.8	35.7	35.6	35.4
87.5°	16.8	16.9	17.1	17.3	17.3	17.4	17.5	17.5
90°	17.2	18.1	19.1	19.7	20.0	20.3	20.6	21.0
92.5°	16.7	17.6	18.5	19.0	19.1	19.1	19.2	19.3
95°	17.2	18.1	19.1	19.6	19.8	19.9	20.1	20.2
97.5°	18.6	18.7	18.8	18.9	19.1	19.2	19.4	19.5
100°	25.4	22.7	20.2	18.9	19.1	19.2	19.4	19.5
102.5°	91.0	62.6	34.2	20.0	20.0	20.0	20.1	20.1
105°	220.3	221.7	223.1	221.1	215.4	209.8	204.3	198.7
107.5°	272.6	273.2	273.9	274.6	275.2	275.7	276.3	277.0
110°	308.1	308.4	308.7	309.1	309.6	310.0	310.5	310.9



TEST NUMBER: P332559-940

CATALOG NUMBER: S124DIP-S575D810U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	342.5	342.4	342.3	342.6	343.2	343.8	344.4	345.0
115°	393.9	394.1	394.5	394.7	394.7	394.7	394.7	394.7
117.5°	445.5	445.5	445.4	445.3	445.3	445.2	445.1	445.1
120°	477.5	477.9	478.1	478.1	477.9	477.5	477.2	476.9
122.5°	509.1	509.3	509.4	509.3	509.1	508.7	508.5	508.1
125°	553.1	553.6	554.0	554.4	554.6	554.6	554.8	555.0
127.5°	596.9	596.8	596.7	596.6	596.5	596.4	596.3	596.1
130°	623.7	623.8	623.9	624.0	624.0	624.0	624.0	624.0
132.5°	649.9	650.0	650.1	650.1	650.1	649.9	649.8	649.7
135°	686.0	686.3	686.6	686.9	687.2	687.5	687.9	688.1
137.5°	720.6	720.9	721.3	721.4	721.3	721.2	721.1	721.0
140°	742.1	742.5	743.0	743.3	743.5	743.6	743.8	744.0
142.5°	761.9	762.2	762.6	762.8	762.8	762.9	762.9	762.9
145°	790.2	790.4	790.6	790.8	791.1	791.4	791.8	792.0
147.5°	815.2	815.3	815.4	815.6	815.7	815.8	816.0	816.2
150°	831.1	831.1	831.1	831.2	831.3	831.4	831.6	831.8
152.5°	845.0	845.3	845.4	845.5	845.4	845.3	845.3	845.2
155°	863.7	864.3	865.0	865.0	864.5	864.1	863.6	863.2
157.5°	879.9	880.7	881.5	881.5	880.7	879.9	879.0	878.2
160°	890.1	891.1	892.0	892.0	891.1	890.1	889.2	888.2
162.5°	898.5	899.4	900.4	900.3	899.2	898.1	897.2	896.1
165°	910.3	911.5	912.8	912.7	911.2	909.9	908.5	907.0
167.5°	918.9	920.2	921.6	921.5	920.0	918.4	916.9	915.3
170°	924.2	925.4	926.7	926.5	925.0	923.5	921.9	920.3
172.5°	927.6	928.8	930.1	929.8	928.2	926.5	924.8	923.1
175°	931.5	932.9	934.2	934.1	932.2	930.3	928.4	926.6
177.5°	933.1	934.1	935.0	934.8	933.3	931.8	930.3	928.8
180°	932.2	932.2	932.2	932.2	932.2	932.2	932.2	932.2

(END OF REPORT)