

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333577-930

Luminaire Tested: **S125RDIP-S850D1205U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333577-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D1205U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6576.3 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333577-930

CATALOG NUMBER: S125RDIP-S850D1205U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333577-930

CATALOG NUMBER: S125RDIP-S850D1205U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	84	87	84	80	78	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	36	34	29
3	80	71	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	55	49	66	57	51	45	47	42	38	38	35	32	30	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7240	7240	7240
5°	7257	7175	7219
10°	7202	7108	7108
15°	7117	6964	6907
20°	7007	6762	6681
25°	6879	6565	6420
30°	6718	6334	6131
35°	6556	6095	5807
40°	6403	5847	5490
45°	6218	5569	5142
50°	6031	5267	4782
55°	5816	4977	4396
60°	5599	4627	3981
65°	5344	4219	3506
70°	5053	3709	3021
75°	4649	3127	2515
80°	4095	2455	2109
85°	3453	2008	1882



TEST NUMBER: P333577-930

CATALOG NUMBER: S125RDIP-S850D1205U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	1.6
10°-20°	294.6	4.5
20°-30°	427.2	6.5
30°-40°	486.9	7.4
40°-50°	474.6	7.2
50°-60°	399.5	6.1
60°-70°	280.0	4.3
70°-80°	143.9	2.2
80°-90°	39.0	0.6
90°-100°	46.5	0.7
100°-110°	286.3	4.4
110°-120°	519.2	7.9
120°-130°	666.3	10.1
130°-140°	716.7	10.9
140°-150°	672.7	10.2
150°-160°	544.2	8.3
160°-170°	351.9	5.4
170°-180°	121.4	1.8
0°-30°	827.2	12.6
0°-40°	1314.1	20.0
0°-60°	2188.2	33.3
0°-90°	2651.2	40.3
90°-120°	851.9	13.0
90°-150°	2907.7	44.2
90°-180°	3925.0	59.7
0°-180°	6576.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1121	1121	1121	1121	1121	
5°	1119	1116	1107	1115	1114	106
15°	1064	1059	1042	1040	1033	300
25°	965	952	921	910	901	444
35°	832	810	773	749	737	520
45°	681	655	610	577	563	525
55°	516	488	442	405	390	462
65°	350	320	276	243	229	346
75°	186	160	125	107	101	197
85°	47	32	27	26	25	52
90°	1	8	15	20	23	4
95°	54	49	15	20	20	69
105°	279	282	282	282	281	295
115°	523	528	529	525	519	518
125°	744	750	750	747	744	664
135°	928	933	931	929	924	715
145°	1076	1077	1077	1078	1073	672
155°	1184	1179	1181	1183	1176	545
165°	1250	1244	1245	1250	1243	353
175°	1278	1273	1274	1280	1272	122
180°	1278	1278	1278	1278	1278	



TEST NUMBER: P333577-930

CATALOG NUMBER: S125RDIP-S850D1205U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1
2.5°	1123.1	1122.7	1122.2	1121.8	1121.3	1120.3	1118.8	1117.3	1115.8	1114.3	1115.8
5°	1119.4	1118.7	1117.9	1117.1	1116.4	1115.0	1112.9	1110.8	1108.7	1106.7	1108.6
7.5°	1108.4	1107.7	1106.9	1106.2	1105.5	1103.9	1101.5	1098.9	1096.5	1094.0	1095.3
10°	1098.2	1097.6	1097.1	1096.5	1095.9	1094.4	1091.8	1089.1	1086.5	1083.9	1084.3
12.5°	1086.7	1086.0	1085.2	1084.6	1083.9	1081.7	1078.2	1074.6	1071.1	1067.6	1068.0
15°	1064.4	1063.2	1062.1	1060.9	1059.8	1057.3	1053.4	1049.4	1045.5	1041.5	1041.3
17.5°	1039.1	1037.4	1035.7	1034.0	1032.2	1028.8	1023.9	1018.9	1013.9	1008.9	1008.0
20°	1019.5	1017.6	1015.7	1013.8	1011.9	1008.0	1002.0	996.0	989.9	983.9	983.0
22.5°	997.8	995.9	994.0	992.1	990.3	986.2	979.8	973.5	967.2	960.9	959.0
25°	965.3	962.5	959.6	956.8	954.0	949.1	942.2	935.1	928.2	921.3	918.8
27.5°	928.1	924.6	921.2	917.8	914.4	908.9	901.5	894.0	886.6	879.1	875.6
30°	900.9	897.3	893.8	890.2	886.6	880.8	873.0	865.1	857.2	849.3	845.0
32.5°	874.5	870.3	866.2	862.0	857.8	851.7	843.7	835.6	827.5	819.5	814.7
35°	831.5	827.0	822.5	817.9	813.4	806.9	798.5	790.0	781.5	773.1	767.6
37.5°	789.3	783.8	778.4	772.8	767.4	760.3	751.5	742.7	734.0	725.3	718.8
40°	759.5	753.9	748.2	742.6	736.9	729.6	720.6	711.5	702.5	693.5	686.3
42.5°	728.4	722.6	716.8	710.9	705.2	697.7	688.3	679.0	669.6	660.3	653.5
45°	680.8	675.3	669.8	664.4	658.9	651.0	640.7	630.4	620.0	609.7	602.1
47.5°	631.5	625.7	620.0	614.2	608.5	600.4	590.0	579.5	569.1	558.6	550.9
50°	600.3	594.1	587.9	581.7	575.5	567.0	556.3	545.6	534.8	524.2	516.2
52.5°	566.5	560.1	553.8	547.4	541.0	532.8	522.7	512.6	502.4	492.3	483.8
55°	516.5	510.5	504.5	498.5	492.4	484.1	473.6	463.1	452.6	442.0	433.5
57.5°	466.0	459.6	453.1	446.7	440.3	432.0	421.8	411.6	401.5	391.3	383.1
60°	433.5	427.0	420.4	413.8	407.2	398.8	388.7	378.5	368.4	358.2	349.9
62.5°	399.0	392.7	386.5	380.1	373.8	365.6	355.2	345.0	334.6	324.3	316.7
65°	349.7	343.3	336.9	330.5	324.1	315.9	306.0	296.0	286.0	276.1	268.5
67.5°	300.8	294.3	288.0	281.6	275.2	267.2	257.6	248.1	238.6	228.9	222.1
70°	267.6	261.1	254.8	248.3	242.0	234.1	224.7	215.2	205.9	196.4	190.6
72.5°	235.1	228.8	222.6	216.3	210.1	202.5	193.7	184.9	176.1	167.3	161.9
75°	186.3	180.7	175.0	169.3	163.7	156.9	149.0	141.1	133.2	125.3	121.2
77.5°	137.9	133.3	128.8	124.3	119.8	114.4	108.0	101.7	95.4	89.1	86.2
80°	110.1	105.6	101.0	96.5	92.0	87.2	81.9	76.6	71.3	66.0	64.3
82.5°	83.0	78.9	74.8	70.8	66.7	62.9	59.3	55.7	52.0	48.4	47.6
85°	46.6	43.2	39.8	36.4	33.0	30.8	29.9	28.9	28.0	27.1	26.9
87.5°	15.7	15.1	14.3	13.6	12.9	12.6	12.8	12.9	13.0	13.2	13.4
90°	1.0	2.6	4.3	6.0	7.7	9.3	10.8	12.2	13.7	15.2	16.2
92.5°	14.6	13.5	12.2	11.1	9.9	9.9	11.3	12.6	13.9	15.2	16.2
95°	54.0	53.4	52.7	52.1	51.4	47.2	39.1	31.1	23.2	15.2	16.2
97.5°	112.8	113.9	115.0	116.2	117.3	110.0	94.1	78.3	62.5	46.6	40.7
100°	158.2	158.9	159.5	160.1	160.8	161.5	162.3	163.2	164.0	164.9	133.5
102.5°	204.5	205.3	206.1	206.8	207.7	208.3	208.8	209.4	209.9	210.3	204.4
105°	278.6	279.4	280.2	281.1	281.9	282.3	282.3	282.3	282.3	282.3	282.3
107.5°	355.6	355.6	355.6	355.6	355.6	355.7	356.1	356.5	357.0	357.4	357.4
110°	405.5	405.5	405.5	405.5	405.5	405.8	406.2	406.6	407.0	407.4	406.8



TEST NUMBER: P333577-930

CATALOG NUMBER: S125RDIP-S850D1205U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	452.6	453.1	453.6	454.0	454.5	454.9	455.2	455.4	455.7	455.9	455.2
115°	523.0	524.1	525.1	526.2	527.3	527.9	528.1	528.3	528.5	528.7	527.9
117.5°	596.0	596.0	595.9	595.9	595.8	596.2	597.0	597.8	598.6	599.4	598.3
120°	641.5	641.2	641.1	640.8	640.7	640.8	641.5	642.1	642.7	643.4	642.9
122.5°	681.7	682.5	683.2	684.0	684.9	685.4	685.7	686.0	686.3	686.6	686.2
125°	743.8	745.3	746.7	748.2	749.7	750.4	750.4	750.4	750.4	750.4	749.6
127.5°	803.2	804.2	805.2	806.2	807.3	807.8	807.6	807.6	807.4	807.3	806.8
130°	839.5	840.6	841.6	842.7	843.8	844.3	844.6	844.8	845.0	845.2	844.6
132.5°	875.9	877.1	878.3	879.5	880.8	881.2	880.7	880.2	879.8	879.3	879.2
135°	927.6	928.9	930.2	931.4	932.7	933.1	932.7	932.3	931.8	931.4	931.0
137.5°	975.2	976.3	977.4	978.4	979.6	979.9	979.6	979.2	978.8	978.4	978.5
140°	1006.2	1006.7	1007.1	1007.5	1008.0	1008.0	1007.9	1007.6	1007.5	1007.2	1007.6
142.5°	1034.3	1034.5	1034.9	1035.1	1035.3	1035.6	1035.9	1036.2	1036.5	1036.8	1036.9
145°	1075.5	1075.9	1076.3	1076.7	1077.1	1077.3	1077.3	1077.3	1077.3	1077.3	1077.6
147.5°	1111.4	1111.3	1111.3	1111.2	1111.1	1111.2	1111.4	1111.7	1112.0	1112.2	1112.5
150°	1134.2	1133.8	1133.3	1132.9	1132.5	1132.5	1132.9	1133.3	1133.8	1134.2	1134.6
152.5°	1156.2	1155.3	1154.3	1153.4	1152.4	1152.2	1152.7	1153.1	1153.5	1153.9	1154.3
155°	1184.4	1183.2	1181.9	1180.6	1179.3	1178.9	1179.3	1179.7	1180.2	1180.6	1181.3
157.5°	1206.2	1205.4	1204.7	1204.0	1203.1	1202.8	1202.9	1202.9	1203.0	1203.0	1203.6
160°	1221.4	1220.1	1218.9	1217.6	1216.3	1215.8	1216.0	1216.2	1216.4	1216.6	1217.5
162.5°	1233.5	1232.2	1230.9	1229.7	1228.4	1227.9	1228.1	1228.3	1228.6	1228.7	1230.0
165°	1249.8	1248.5	1247.2	1246.0	1244.7	1244.2	1244.4	1244.6	1244.8	1245.0	1246.3
167.5°	1261.9	1260.6	1259.3	1258.0	1256.7	1256.1	1256.4	1256.5	1256.8	1257.0	1258.5
170°	1268.8	1267.3	1265.8	1264.3	1262.8	1262.2	1262.4	1262.7	1262.8	1263.1	1264.8
172.5°	1273.3	1271.8	1270.3	1268.9	1267.4	1266.8	1267.2	1267.6	1268.0	1268.4	1269.9
175°	1278.2	1276.9	1275.7	1274.4	1273.2	1272.6	1272.8	1273.1	1273.3	1273.5	1275.1
177.5°	1280.5	1279.4	1278.5	1277.5	1276.4	1276.0	1276.2	1276.4	1276.5	1276.7	1277.9
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2



TEST NUMBER: P333577-930

CATALOG NUMBER: S125RDIP-S850D1205U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1
2.5°	1117.3	1118.8	1120.3	1121.0	1120.9	1120.7	1120.5	1120.4
5°	1110.4	1112.3	1114.2	1115.0	1114.6	1114.2	1113.9	1113.5
7.5°	1096.7	1098.0	1099.3	1099.7	1099.3	1098.9	1098.5	1098.0
10°	1084.9	1085.5	1086.1	1086.1	1085.5	1084.9	1084.3	1083.9
12.5°	1068.4	1068.8	1069.2	1069.0	1068.1	1067.2	1066.4	1065.5
15°	1041.1	1040.9	1040.7	1039.8	1038.1	1036.4	1034.7	1033.0
17.5°	1007.1	1006.2	1005.2	1004.0	1002.7	1001.3	999.9	998.5
20°	982.0	981.0	980.2	978.8	977.1	975.4	973.7	972.1
22.5°	957.2	955.4	953.5	951.9	950.5	949.1	947.7	946.3
25°	916.4	914.0	911.5	909.2	907.1	905.1	903.0	900.9
27.5°	872.2	868.8	865.4	862.7	860.7	858.7	856.7	854.7
30°	840.7	836.3	831.9	829.0	827.3	825.6	823.9	822.1
32.5°	809.9	805.1	800.4	796.9	794.8	792.6	790.4	788.3
35°	762.1	756.7	751.2	747.2	744.5	741.9	739.3	736.6
37.5°	712.2	705.6	699.1	694.6	692.0	689.4	686.9	684.4
40°	679.1	672.1	664.9	660.1	657.9	655.7	653.4	651.2
42.5°	646.6	639.8	632.9	627.8	624.5	621.2	617.8	614.6
45°	594.6	587.1	579.5	574.4	571.5	568.8	565.9	563.0
47.5°	543.2	535.4	527.7	522.2	519.1	516.0	512.8	509.7
50°	508.3	500.4	492.5	487.1	484.4	481.5	478.7	475.9
52.5°	475.3	466.8	458.3	452.6	449.8	446.9	444.2	441.3
55°	425.1	416.6	408.1	402.4	399.4	396.4	393.4	390.4
57.5°	374.8	366.6	358.2	352.8	350.1	347.4	344.8	342.1
60°	341.6	333.3	325.1	319.5	316.7	313.9	311.0	308.2
62.5°	308.9	301.3	293.6	288.4	285.5	282.7	279.9	277.0
65°	261.0	253.5	245.9	240.8	237.9	235.1	232.3	229.4
67.5°	215.2	208.3	201.4	196.8	194.6	192.3	190.0	187.8
70°	184.7	179.0	173.1	169.1	166.8	164.5	162.3	160.0
72.5°	156.5	151.2	145.8	142.4	140.8	139.3	137.9	136.3
75°	117.1	112.9	108.8	106.1	104.7	103.4	102.1	100.8
77.5°	83.2	80.4	77.5	75.6	74.6	73.6	72.6	71.7
80°	62.7	61.0	59.3	58.2	57.9	57.5	57.1	56.7
82.5°	46.9	46.1	45.2	44.8	44.5	44.4	44.1	43.9
85°	26.7	26.5	26.3	26.2	25.9	25.8	25.6	25.4
87.5°	13.6	13.9	14.0	14.1	14.1	14.1	14.0	14.0
90°	17.3	18.3	19.4	20.2	20.9	21.4	22.1	22.7
92.5°	17.3	18.3	19.4	20.1	20.3	20.6	21.0	21.2
95°	17.3	18.3	19.4	19.9	19.9	19.9	19.9	19.9
97.5°	34.7	28.8	22.8	19.9	19.9	19.9	19.9	19.9
100°	102.2	70.8	39.4	23.2	22.4	21.6	20.7	19.9
102.5°	198.4	192.6	186.6	176.5	162.2	147.8	133.5	119.2
105°	282.3	282.3	282.3	282.3	282.0	281.8	281.6	281.4
107.5°	357.5	357.5	357.6	357.3	356.6	356.0	355.4	354.7
110°	406.2	405.5	404.9	404.7	404.9	405.1	405.4	405.5



TEST NUMBER: P333577-930

CATALOG NUMBER: S125RDIP-S850D1205U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	454.4	453.6	452.7	452.2	451.9	451.6	451.3	451.0
115°	527.0	526.2	525.4	524.3	523.0	521.8	520.5	519.3
117.5°	597.2	596.1	595.0	594.2	593.6	593.1	592.6	592.0
120°	642.5	642.1	641.7	641.0	639.9	638.9	637.8	636.7
122.5°	685.7	685.3	684.9	684.0	682.8	681.6	680.4	679.2
125°	748.8	747.9	747.1	746.3	745.7	745.1	744.4	743.8
127.5°	806.3	805.9	805.4	804.5	802.9	801.3	799.7	798.2
130°	843.9	843.3	842.7	841.8	840.7	839.8	838.7	837.6
132.5°	879.1	878.9	878.8	878.2	877.2	876.1	875.1	874.0
135°	930.6	930.2	929.8	928.9	927.6	926.3	925.1	923.8
137.5°	978.6	978.7	978.8	978.3	977.1	976.1	974.9	973.9
140°	1008.0	1008.4	1008.9	1008.4	1007.2	1006.0	1004.7	1003.5
142.5°	1037.0	1037.1	1037.1	1036.6	1035.3	1034.0	1032.7	1031.5
145°	1077.7	1078.0	1078.2	1077.7	1076.4	1075.1	1073.8	1072.6
147.5°	1112.7	1113.0	1113.2	1112.6	1111.1	1109.5	1108.1	1106.5
150°	1135.1	1135.5	1135.9	1135.2	1133.6	1131.9	1130.2	1128.5
152.5°	1154.7	1155.2	1155.6	1155.0	1153.5	1152.0	1150.5	1149.0
155°	1181.9	1182.5	1183.2	1182.6	1181.0	1179.2	1177.5	1175.9
157.5°	1204.4	1205.0	1205.7	1205.2	1203.5	1201.8	1200.1	1198.4
160°	1218.3	1219.1	1220.0	1219.6	1217.9	1216.2	1214.6	1212.8
162.5°	1231.1	1232.3	1233.5	1233.1	1231.3	1229.4	1227.6	1225.7
165°	1247.6	1248.9	1250.1	1249.9	1248.2	1246.5	1244.8	1243.2
167.5°	1260.0	1261.5	1263.1	1262.9	1260.9	1259.1	1257.2	1255.3
170°	1266.4	1268.1	1269.8	1269.7	1267.8	1265.9	1264.0	1262.1
172.5°	1271.4	1272.9	1274.4	1274.2	1272.4	1270.5	1268.5	1266.6
175°	1276.8	1278.6	1280.2	1280.1	1278.2	1276.4	1274.4	1272.5
177.5°	1279.0	1280.3	1281.4	1281.3	1280.0	1278.6	1277.2	1275.9
180°	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2	1278.2

(END OF REPORT)