

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333566-930

Luminaire Tested: **S125RDIP-S850D810U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333566-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S850D810U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4936.3 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333566-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333566-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	60	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	53	48	52	47	43	45	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	29	33	29	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	22	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7240	7240	7240
5°	7257	7175	7219
10°	7202	7108	7108
15°	7117	6964	6907
20°	7007	6762	6681
25°	6879	6565	6420
30°	6718	6334	6131
35°	6556	6095	5807
40°	6403	5847	5490
45°	6218	5569	5142
50°	6031	5267	4782
55°	5816	4977	4396
60°	5599	4627	3981
65°	5344	4219	3506
70°	5053	3709	3021
75°	4649	3127	2515
80°	4095	2455	2109
85°	3453	2008	1882



TEST NUMBER: P333566-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	2.1
10°-20°	294.6	6.0
20°-30°	427.2	8.7
30°-40°	486.9	9.9
40°-50°	474.6	9.6
50°-60°	399.5	8.1
60°-70°	280.0	5.7
70°-80°	143.9	2.9
80°-90°	38.1	0.8
90°-100°	54.9	1.1
100°-110°	162.0	3.3
110°-120°	274.4	5.6
120°-130°	361.2	7.3
130°-140°	404.7	8.2
140°-150°	396.7	8.0
150°-160°	333.1	6.7
160°-170°	221.5	4.5
170°-180°	77.5	1.6
0°-30°	827.2	16.8
0°-40°	1314.1	26.6
0°-60°	2188.2	44.3
0°-90°	2650.3	53.7
90°-120°	491.4	10.0
90°-150°	1653.9	33.5
90°-180°	2286.0	46.3
0°-180°	4936.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1121	1121	1121	1121	1121	
5°	1119	1116	1107	1115	1114	106
15°	1064	1059	1042	1040	1033	300
25°	965	952	921	910	901	444
35°	832	810	773	749	737	520
45°	681	655	610	577	563	525
55°	516	488	442	405	390	462
65°	350	320	276	243	229	346
75°	186	160	125	107	101	197
85°	47	32	27	26	25	52
90°	1	6	10	13	15	4
95°	41	43	49	53	55	44
105°	145	149	152	156	158	155
115°	275	277	279	278	277	272
125°	401	405	405	404	404	359
135°	522	525	526	526	523	402
145°	632	634	636	636	634	395
155°	723	723	724	726	723	333
165°	786	785	786	788	784	222
175°	817	815	815	818	814	78
180°	819	819	819	819	819	



TEST NUMBER: P333566-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1
2.5°	1123.1	1122.7	1122.2	1121.8	1121.3	1120.3	1118.8	1117.3	1115.8	1114.3	1115.8
5°	1119.4	1118.7	1117.9	1117.1	1116.4	1115.0	1112.9	1110.8	1108.7	1106.7	1108.6
7.5°	1108.4	1107.7	1106.9	1106.2	1105.5	1103.9	1101.5	1098.9	1096.5	1094.0	1095.3
10°	1098.2	1097.6	1097.1	1096.5	1095.9	1094.4	1091.8	1089.1	1086.5	1083.9	1084.3
12.5°	1086.7	1086.0	1085.2	1084.6	1083.9	1081.7	1078.2	1074.6	1071.1	1067.6	1068.0
15°	1064.4	1063.2	1062.1	1060.9	1059.8	1057.3	1053.4	1049.4	1045.5	1041.5	1041.3
17.5°	1039.1	1037.4	1035.7	1034.0	1032.2	1028.8	1023.9	1018.9	1013.9	1008.9	1008.0
20°	1019.5	1017.6	1015.7	1013.8	1011.9	1008.0	1002.0	996.0	989.9	983.9	983.0
22.5°	997.8	995.9	994.0	992.1	990.3	986.2	979.8	973.5	967.2	960.9	959.0
25°	965.3	962.5	959.6	956.8	954.0	949.1	942.2	935.1	928.2	921.3	918.8
27.5°	928.1	924.6	921.2	917.8	914.4	908.9	901.5	894.0	886.6	879.1	875.6
30°	900.9	897.3	893.8	890.2	886.6	880.8	873.0	865.1	857.2	849.3	845.0
32.5°	874.5	870.3	866.2	862.0	857.8	851.7	843.7	835.6	827.5	819.5	814.7
35°	831.5	827.0	822.5	817.9	813.4	806.9	798.5	790.0	781.5	773.1	767.6
37.5°	789.3	783.8	778.4	772.8	767.4	760.3	751.5	742.7	734.0	725.3	718.8
40°	759.5	753.9	748.2	742.6	736.9	729.6	720.6	711.5	702.5	693.5	686.3
42.5°	728.4	722.6	716.8	710.9	705.2	697.7	688.3	679.0	669.6	660.3	653.5
45°	680.8	675.3	669.8	664.4	658.9	651.0	640.7	630.4	620.0	609.7	602.1
47.5°	631.5	625.7	620.0	614.2	608.5	600.4	590.0	579.5	569.1	558.6	550.9
50°	600.3	594.1	587.9	581.7	575.5	567.0	556.3	545.6	534.8	524.2	516.2
52.5°	566.5	560.1	553.8	547.4	541.0	532.8	522.7	512.6	502.4	492.3	483.8
55°	516.5	510.5	504.5	498.5	492.4	484.1	473.6	463.1	452.6	442.0	433.5
57.5°	466.0	459.6	453.1	446.7	440.3	432.0	421.8	411.6	401.5	391.3	383.1
60°	433.5	427.0	420.4	413.8	407.2	398.8	388.7	378.5	368.4	358.2	349.9
62.5°	399.0	392.7	386.5	380.1	373.8	365.6	355.2	345.0	334.6	324.3	316.7
65°	349.7	343.3	336.9	330.5	324.1	315.9	306.0	296.0	286.0	276.1	268.5
67.5°	300.8	294.3	288.0	281.6	275.2	267.2	257.6	248.1	238.6	228.9	222.1
70°	267.6	261.1	254.8	248.3	242.0	234.1	224.7	215.2	205.9	196.4	190.6
72.5°	235.1	228.8	222.6	216.3	210.1	202.5	193.7	184.9	176.1	167.3	161.9
75°	186.3	180.7	175.0	169.3	163.7	156.9	149.0	141.1	133.2	125.3	121.2
77.5°	137.9	133.3	128.8	124.3	119.8	114.4	108.0	101.7	95.4	89.1	86.2
80°	110.1	105.6	101.0	96.5	92.0	87.2	81.9	76.6	71.3	66.0	64.3
82.5°	83.0	78.9	74.8	70.8	66.7	62.9	59.3	55.7	52.0	48.4	47.6
85°	46.6	43.2	39.8	36.4	33.0	30.8	29.9	28.9	28.0	27.1	26.9
87.5°	15.7	14.9	14.0	13.2	12.4	12.0	12.1	12.1	12.1	12.2	12.3
90°	0.7	1.8	2.9	4.1	5.1	6.2	7.3	8.2	9.2	10.2	10.9
92.5°	15.4	16.2	17.0	17.8	18.6	19.6	20.8	22.0	23.2	24.5	25.4
95°	41.4	41.7	42.0	42.3	42.6	43.5	44.8	46.2	47.7	49.1	50.1
97.5°	68.9	69.0	69.1	69.2	69.3	70.4	72.3	74.3	76.2	78.2	79.1
100°	89.3	89.3	89.3	89.3	89.3	90.2	92.0	93.8	95.7	97.5	98.8
102.5°	111.2	111.8	112.3	112.9	113.5	114.2	115.1	116.1	117.0	118.0	119.4
105°	145.4	146.1	146.8	147.5	148.2	149.0	149.9	150.7	151.5	152.4	153.2
107.5°	183.1	183.8	184.5	185.2	186.0	186.6	187.3	187.9	188.6	189.2	189.6
110°	209.1	209.9	210.5	211.2	212.0	212.5	213.0	213.4	213.8	214.2	214.7



TEST NUMBER: P333566-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	235.6	236.0	236.4	236.8	237.1	237.6	238.1	238.6	239.2	239.7	239.9
115°	274.8	275.3	275.9	276.5	277.0	277.4	277.8	278.0	278.3	278.6	278.4
117.5°	314.1	314.3	314.5	314.8	315.0	315.4	315.6	315.8	316.1	316.3	316.4
120°	338.5	339.2	340.0	340.6	341.4	341.8	341.9	342.1	342.2	342.3	342.3
122.5°	365.0	365.3	365.6	365.8	366.1	366.4	366.7	367.1	367.5	367.9	367.7
125°	401.0	401.9	402.7	403.6	404.4	404.9	405.0	405.2	405.3	405.4	405.2
127.5°	439.3	439.8	440.2	440.7	441.2	441.5	441.6	441.8	442.1	442.2	442.1
130°	462.2	462.9	463.7	464.3	465.0	465.5	465.8	466.1	466.4	466.7	466.5
132.5°	485.2	486.3	487.5	488.6	489.8	490.3	490.3	490.2	490.2	490.2	490.0
135°	521.5	522.4	523.2	524.1	524.9	525.4	525.5	525.7	525.8	525.9	525.9
137.5°	555.7	556.5	557.3	558.2	559.0	559.5	559.9	560.1	560.4	560.8	560.9
140°	577.6	578.3	579.0	579.8	580.4	581.0	581.4	581.9	582.3	582.7	583.0
142.5°	599.6	600.1	600.7	601.3	601.9	602.5	603.0	603.6	604.1	604.6	604.8
145°	631.8	632.3	632.9	633.5	634.1	634.5	635.0	635.4	635.9	636.3	636.3
147.5°	661.6	661.9	662.3	662.6	662.8	663.2	663.6	663.9	664.2	664.6	664.9
150°	681.5	681.3	681.3	681.1	680.9	681.2	681.8	682.3	682.9	683.5	683.5
152.5°	697.8	698.1	698.2	698.5	698.6	698.9	699.0	699.3	699.5	699.8	700.1
155°	722.9	722.9	722.9	722.9	722.9	723.0	723.2	723.3	723.4	723.6	724.1
157.5°	745.4	745.1	744.8	744.4	744.1	744.0	744.2	744.4	744.4	744.6	745.2
160°	758.6	758.2	757.8	757.4	756.9	756.8	756.9	757.1	757.2	757.4	758.0
162.5°	770.4	770.1	769.7	769.5	769.2	769.0	769.0	769.1	769.1	769.2	769.8
165°	786.1	785.8	785.5	785.2	785.0	784.9	785.0	785.1	785.3	785.5	786.0
167.5°	799.3	798.7	798.2	797.6	797.0	796.8	796.8	796.8	796.8	796.8	797.6
170°	806.5	805.9	805.4	804.8	804.2	803.9	803.9	803.9	803.9	803.9	804.8
172.5°	811.5	811.0	810.4	809.8	809.3	809.0	809.0	809.0	809.0	809.0	809.8
175°	817.3	816.8	816.2	815.6	815.1	814.7	814.7	814.7	814.7	814.7	815.6
177.5°	820.3	819.8	819.4	818.9	818.4	818.2	818.1	817.9	817.8	817.7	818.4
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333566-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1	1121.1
2.5°	1117.3	1118.8	1120.3	1121.0	1120.9	1120.7	1120.5	1120.4
5°	1110.4	1112.3	1114.2	1115.0	1114.6	1114.2	1113.9	1113.5
7.5°	1096.7	1098.0	1099.3	1099.7	1099.3	1098.9	1098.5	1098.0
10°	1084.9	1085.5	1086.1	1086.1	1085.5	1084.9	1084.3	1083.9
12.5°	1068.4	1068.8	1069.2	1069.0	1068.1	1067.2	1066.4	1065.5
15°	1041.1	1040.9	1040.7	1039.8	1038.1	1036.4	1034.7	1033.0
17.5°	1007.1	1006.2	1005.2	1004.0	1002.7	1001.3	999.9	998.5
20°	982.0	981.0	980.2	978.8	977.1	975.4	973.7	972.1
22.5°	957.2	955.4	953.5	951.9	950.5	949.1	947.7	946.3
25°	916.4	914.0	911.5	909.2	907.1	905.1	903.0	900.9
27.5°	872.2	868.8	865.4	862.7	860.7	858.7	856.7	854.7
30°	840.7	836.3	831.9	829.0	827.3	825.6	823.9	822.1
32.5°	809.9	805.1	800.4	796.9	794.8	792.6	790.4	788.3
35°	762.1	756.7	751.2	747.2	744.5	741.9	739.3	736.6
37.5°	712.2	705.6	699.1	694.6	692.0	689.4	686.9	684.4
40°	679.1	672.1	664.9	660.1	657.9	655.7	653.4	651.2
42.5°	646.6	639.8	632.9	627.8	624.5	621.2	617.8	614.6
45°	594.6	587.1	579.5	574.4	571.5	568.8	565.9	563.0
47.5°	543.2	535.4	527.7	522.2	519.1	516.0	512.8	509.7
50°	508.3	500.4	492.5	487.1	484.4	481.5	478.7	475.9
52.5°	475.3	466.8	458.3	452.6	449.8	446.9	444.2	441.3
55°	425.1	416.6	408.1	402.4	399.4	396.4	393.4	390.4
57.5°	374.8	366.6	358.2	352.8	350.1	347.4	344.8	342.1
60°	341.6	333.3	325.1	319.5	316.7	313.9	311.0	308.2
62.5°	308.9	301.3	293.6	288.4	285.5	282.7	279.9	277.0
65°	261.0	253.5	245.9	240.8	237.9	235.1	232.3	229.4
67.5°	215.2	208.3	201.4	196.8	194.6	192.3	190.0	187.8
70°	184.7	179.0	173.1	169.1	166.8	164.5	162.3	160.0
72.5°	156.5	151.2	145.8	142.4	140.8	139.3	137.9	136.3
75°	117.1	112.9	108.8	106.1	104.7	103.4	102.1	100.8
77.5°	83.2	80.4	77.5	75.6	74.6	73.6	72.6	71.7
80°	62.7	61.0	59.3	58.2	57.9	57.5	57.1	56.7
82.5°	46.9	46.1	45.2	44.8	44.5	44.4	44.1	43.9
85°	26.7	26.5	26.3	26.2	25.9	25.8	25.6	25.4
87.5°	12.5	12.6	12.8	12.8	12.7	12.6	12.6	12.6
90°	11.6	12.3	13.0	13.6	14.0	14.4	14.8	15.3
92.5°	26.3	27.3	28.2	28.9	29.2	29.4	29.8	30.1
95°	51.0	52.1	53.1	53.7	54.0	54.3	54.5	54.8
97.5°	80.1	81.0	81.9	82.4	82.6	82.8	83.0	83.2
100°	100.1	101.3	102.6	103.5	103.7	104.0	104.3	104.5
102.5°	120.7	122.1	123.5	124.4	124.8	125.1	125.6	126.0
105°	154.1	154.9	155.8	156.4	156.9	157.3	157.7	158.1
107.5°	190.0	190.5	190.9	191.1	191.1	191.0	191.0	191.0
110°	215.1	215.5	215.9	216.1	215.9	215.7	215.6	215.5



TEST NUMBER: P333566-930

CATALOG NUMBER: S125RDIP-S850D810U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	240.1	240.3	240.5	240.5	240.2	239.9	239.7	239.5
115°	278.3	278.2	278.0	277.9	277.8	277.6	277.4	277.4
117.5°	316.6	316.7	316.8	316.6	316.0	315.4	314.9	314.3
120°	342.3	342.3	342.3	342.1	341.5	341.0	340.4	339.8
122.5°	367.6	367.5	367.4	367.1	366.6	366.2	365.7	365.3
125°	404.9	404.6	404.3	404.1	404.0	403.8	403.7	403.6
127.5°	441.9	441.7	441.6	441.4	441.2	440.8	440.6	440.3
130°	466.4	466.3	466.1	465.9	465.6	465.3	465.0	464.7
132.5°	489.8	489.7	489.6	489.3	488.9	488.5	488.1	487.7
135°	525.9	525.9	525.9	525.7	525.1	524.6	524.0	523.4
137.5°	561.1	561.3	561.4	561.2	560.4	559.8	559.1	558.3
140°	583.3	583.5	583.8	583.6	582.9	582.2	581.5	580.8
142.5°	605.0	605.1	605.3	605.0	604.3	603.6	602.9	602.2
145°	636.3	636.3	636.3	636.0	635.6	635.2	634.8	634.3
147.5°	665.2	665.6	665.9	665.6	664.6	663.7	662.8	661.8
150°	683.5	683.5	683.5	683.3	683.0	682.7	682.4	682.2
152.5°	700.4	700.7	701.1	701.0	700.5	700.0	699.5	699.0
155°	724.7	725.3	725.9	725.8	725.0	724.4	723.7	722.9
157.5°	745.8	746.3	746.9	746.7	745.8	744.9	743.9	743.0
160°	758.6	759.0	759.6	759.6	758.9	758.1	757.4	756.8
162.5°	770.5	771.2	771.8	771.8	770.9	770.1	769.3	768.5
165°	786.6	787.2	787.7	787.6	786.7	785.9	785.0	784.2
167.5°	798.5	799.3	800.2	800.1	799.3	798.4	797.5	796.6
170°	805.6	806.5	807.3	807.2	806.2	805.3	804.3	803.3
172.5°	810.7	811.5	812.4	812.4	811.5	810.7	809.8	808.9
175°	816.4	817.3	818.2	818.1	817.1	816.1	815.1	814.2
177.5°	819.0	819.7	820.4	820.4	819.5	818.8	818.0	817.2
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2

(END OF REPORT)