

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333279

Luminaire Tested: **S125DIP-S1090D1035U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333279
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1035U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8203.1 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	39	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10270	10270	10270	10270
5°	11893	10305	9022	10305
10°	13837	10251	7906	10251
15°	15317	10176	7293	10176
20°	17145	10057	6801	10057
25°	20085	9922	6560	9922
30°	21694	9790	6352	9790
35°	17837	9541	6215	9541
40°	12678	9195	6066	9195
45°	9740	8729	5980	8729
50°	8314	8151	5968	8151
55°	7402	7585	6019	7585
60°	6678	6966	6173	6966
65°	6168	6343	6333	6343
70°	5608	5697	6424	5697
75°	4951	5018	6366	5018
80°	4166	4091	5824	4091
85°	3298	2949	4698	2949



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.1	1.9
10°-20°	455.8	5.6
20°-30°	740.1	9.0
30°-40°	902.8	11.0
40°-50°	821.3	10.0
50°-60°	654.2	8.0
60°-70°	455.6	5.6
70°-80°	243.0	3.0
80°-90°	64.1	0.8
90°-100°	358.9	4.4
100°-110°	771.5	9.4
110°-120°	724.1	8.8
120°-130°	586.8	7.2
130°-140°	470.9	5.7
140°-150°	355.4	4.3
150°-160°	250.1	3.0
160°-170°	147.4	1.8
170°-180°	48.0	0.6
0°-30°	1349.0	16.4
0°-40°	2251.8	27.5
0°-60°	3727.3	45.4
0°-90°	4490.0	54.7
90°-120°	1854.5	22.6
90°-150°	3267.6	39.8
90°-180°	3713.0	45.3
0°-180°	8203.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1834	1590	1392	1590	1834	185
15°	2291	1522	1091	1522	2291	656
25°	2819	1392	921	1392	2819	1287
35°	2262	1210	788	1210	2262	1385
45°	1066	956	655	956	1066	854
55°	657	674	535	674	657	592
65°	404	415	414	415	404	401
75°	198	201	255	201	198	214
85°	44	40	63	40	44	52
90°	23	1	23	1	23	17
95°	235	33	235	33	235	332
105°	1323	113	1323	113	1323	1315
115°	1474	202	1474	202	1474	1440
125°	1161	280	1161	280	1161	1050
135°	964	327	964	327	964	747
145°	761	381	761	381	761	483
155°	638	435	638	435	638	297
165°	559	475	559	475	559	160
175°	502	494	502	494	502	49
180°	495	495	495	495	495	



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1682.0	1679.8	1677.7	1673.3	1676.6	1667.4	1663.1	1655.5	1646.3	1643.1	1639.3
5°	1834.5	1837.9	1841.3	1827.1	1828.4	1819.0	1797.4	1779.8	1765.7	1747.4	1734.6
7.5°	2018.1	2010.1	2009.5	2000.3	1984.5	1971.8	1949.1	1920.2	1892.3	1860.4	1834.1
10°	2109.9	2110.6	2104.5	2093.7	2076.8	2064.7	2035.0	2006.6	1972.2	1931.7	1902.7
12.5°	2179.0	2181.8	2174.2	2159.6	2151.3	2124.1	2100.9	2067.1	2026.2	1993.8	1949.7
15°	2290.8	2283.4	2278.0	2259.7	2245.6	2217.2	2180.1	2145.0	2100.4	2059.3	2018.1
17.5°	2398.5	2404.4	2394.3	2377.7	2333.7	2300.6	2250.8	2202.8	2147.3	2092.1	2042.9
20°	2494.6	2500.0	2484.5	2455.5	2402.8	2369.8	2304.3	2242.2	2178.1	2107.2	2053.2
22.5°	2614.5	2610.2	2589.2	2545.1	2499.5	2438.3	2367.5	2291.9	2211.5	2131.5	2059.7
25°	2818.6	2790.2	2777.4	2722.8	2662.7	2572.9	2475.7	2365.0	2265.1	2159.2	2067.4
27.5°	2931.7	2922.8	2908.5	2870.4	2807.3	2711.3	2596.7	2461.8	2320.9	2187.1	2067.0
30°	2909.0	2910.4	2911.7	2899.6	2859.1	2786.9	2672.8	2527.7	2360.3	2209.8	2070.7
32.5°	2708.2	2732.7	2756.2	2784.0	2795.4	2781.5	2710.1	2579.0	2406.7	2235.7	2068.6
35°	2262.4	2269.9	2346.1	2421.7	2524.3	2604.0	2657.3	2599.2	2454.1	2257.7	2066.0
37.5°	1764.1	1800.5	1853.3	1938.7	2086.8	2219.4	2389.9	2468.3	2421.5	2264.9	2061.3
40°	1503.8	1537.5	1572.0	1659.0	1783.9	1944.5	2138.2	2303.6	2342.1	2242.2	2045.1
42.5°	1302.9	1329.7	1367.9	1433.3	1537.7	1680.0	1865.0	2081.1	2214.1	2176.3	2011.1
45°	1066.4	1083.3	1113.0	1165.0	1240.6	1351.9	1515.3	1751.5	1957.4	2025.5	1930.4
47.5°	912.8	912.7	935.8	971.7	1026.2	1120.8	1241.6	1426.7	1646.6	1809.3	1801.7
50°	827.5	824.1	842.3	873.4	916.6	979.4	1094.8	1242.6	1453.8	1638.1	1689.4
52.5°	754.1	754.5	765.7	788.6	824.8	878.4	964.6	1097.9	1278.4	1467.5	1564.1
55°	657.4	654.7	667.5	683.1	709.4	744.5	806.6	908.5	1054.9	1241.2	1366.8
57.5°	568.8	576.3	581.4	592.2	614.1	637.6	689.9	764.7	880.9	1040.8	1173.5
60°	517.0	524.4	528.5	539.3	556.8	577.1	617.6	678.3	776.2	913.9	1045.5
62.5°	470.6	476.4	477.7	487.4	501.8	521.5	553.3	604.4	681.7	802.1	931.0
65°	403.6	403.6	406.3	416.4	423.2	440.7	465.0	502.2	564.3	658.1	768.1
67.5°	339.1	342.3	341.7	346.1	352.3	366.0	383.4	414.0	460.0	528.5	616.5
70°	297.0	299.7	299.0	302.4	309.1	317.9	332.1	361.1	394.2	452.9	528.5
72.5°	259.2	260.3	258.5	263.0	267.0	274.7	290.5	306.0	336.9	386.5	448.6
75°	198.4	199.8	201.1	203.8	207.9	211.9	220.0	235.6	255.8	292.9	332.8
77.5°	148.8	146.2	149.4	149.0	151.3	154.4	161.6	169.8	186.4	209.9	240.7
80°	112.0	112.7	112.7	113.4	116.8	118.8	124.9	130.9	143.8	161.3	182.9
82.5°	81.8	83.6	82.5	83.7	86.5	88.0	91.4	96.4	103.8	117.6	133.2
85°	44.5	41.2	42.5	43.9	43.9	44.5	47.2	49.3	53.3	58.7	64.8
87.5°	17.6	18.6	19.0	19.0	19.5	19.1	21.1	20.9	22.3	23.7	25.5
90°	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0	17.0	16.0	14.0
92.5°	63.7	65.3	66.7	69.1	81.9	96.6	128.4	176.9	260.5	321.8	327.0
95°	234.6	250.6	258.6	288.5	359.4	443.2	566.0	717.8	865.5	884.5	721.8
97.5°	567.0	579.8	608.7	664.7	726.3	842.9	962.5	1069.0	1095.1	944.6	644.5
100°	778.7	794.6	831.6	903.4	972.3	1076.1	1179.0	1227.9	1151.0	901.4	575.0
102.5°	1015.0	1027.0	1067.2	1118.3	1191.9	1262.2	1311.5	1281.4	1117.5	825.6	522.3
105°	1322.7	1334.7	1354.7	1387.6	1419.5	1430.5	1386.6	1249.8	1010.3	723.7	471.2
107.5°	1486.0	1494.0	1500.6	1500.8	1484.6	1432.5	1319.7	1137.2	900.8	653.7	449.6
110°	1540.3	1540.3	1533.3	1514.4	1469.5	1384.6	1243.8	1054.2	838.5	620.9	443.2



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1533.9	1526.8	1509.4	1476.8	1411.2	1311.1	1168.8	988.7	792.2	601.8	443.2
115°	1473.5	1460.5	1432.5	1384.6	1306.7	1197.9	1061.2	906.4	741.7	581.0	446.2
117.5°	1367.4	1359.4	1331.7	1282.2	1204.3	1104.5	986.7	853.3	711.6	570.8	452.8
120°	1298.8	1290.8	1263.8	1215.9	1142.0	1054.2	944.4	824.6	694.8	566.0	459.2
122.5°	1238.1	1230.9	1203.9	1160.0	1094.1	1011.8	914.0	803.0	680.4	562.0	464.8
125°	1161.0	1151.0	1129.0	1088.1	1032.2	960.3	873.5	771.7	660.9	557.0	474.2
127.5°	1095.1	1090.7	1069.9	1033.8	983.1	915.8	834.8	739.7	642.9	554.6	484.8
130°	1059.2	1053.2	1033.2	1000.3	950.4	885.5	807.6	719.8	630.9	553.0	491.2
132.5°	1023.2	1016.4	998.1	965.1	915.2	852.7	782.0	699.8	621.3	553.0	498.3
135°	964.3	958.3	940.4	907.4	863.5	806.6	742.7	673.8	609.9	553.0	508.1
137.5°	901.4	894.9	878.3	848.3	809.0	760.7	707.6	651.9	599.8	554.2	517.1
140°	857.5	852.5	837.6	811.6	774.7	732.7	686.8	639.9	595.0	555.0	521.1
142.5°	816.8	812.6	798.4	776.5	745.1	708.8	669.2	629.5	591.0	555.8	523.5
145°	760.7	756.7	745.7	728.7	704.8	677.8	646.9	615.9	585.0	555.0	526.1
147.5°	713.2	711.4	705.0	691.4	672.4	652.1	628.3	603.2	578.8	552.4	527.1
150°	686.8	685.8	681.8	669.8	654.9	636.9	617.9	596.0	574.0	550.0	527.1
152.5°	666.0	665.0	661.1	651.5	638.9	624.9	607.5	588.0	568.4	546.9	526.3
155°	637.9	636.9	633.9	626.9	616.9	606.0	592.0	576.0	559.0	541.1	524.1
157.5°	612.7	612.9	610.1	604.4	596.6	588.0	577.2	564.0	550.2	535.1	521.5
160°	596.0	597.0	595.0	590.0	583.0	576.0	566.0	556.0	543.1	531.1	519.1
162.5°	580.8	581.0	580.6	576.4	571.0	564.8	556.4	547.3	536.7	526.3	516.7
165°	559.0	559.0	559.0	557.0	553.0	548.1	542.1	535.1	527.1	519.1	513.1
167.5°	539.1	539.3	540.1	538.3	536.3	532.7	528.1	523.5	517.7	512.1	507.5
170°	527.1	528.1	528.1	527.1	525.1	523.1	520.1	517.1	512.1	508.1	505.1
172.5°	515.9	516.9	518.5	516.7	516.3	515.1	512.9	509.9	506.5	503.3	501.9
175°	502.1	503.1	505.1	504.1	504.1	504.1	502.1	502.1	499.1	498.1	498.1
177.5°	495.1	495.1	497.5	496.7	497.5	497.5	497.5	496.7	495.9	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1636.1	1632.3	1628.0	1620.4	1611.2	1606.4	1598.8	1594.0	1584.2	1576.1	1567.5
5°	1719.1	1701.6	1685.4	1664.4	1641.5	1626.6	1609.1	1589.5	1569.3	1548.3	1525.4
7.5°	1805.1	1774.0	1740.3	1704.0	1668.5	1635.8	1604.6	1574.0	1545.4	1510.8	1481.5
10°	1862.9	1823.7	1781.9	1732.6	1684.7	1642.8	1600.3	1563.2	1525.4	1484.9	1449.1
12.5°	1920.6	1868.5	1809.4	1755.3	1697.6	1647.1	1597.1	1549.7	1502.2	1457.4	1415.6
15°	1961.4	1915.5	1860.8	1783.9	1719.1	1649.6	1583.4	1522.0	1464.6	1414.7	1362.1
17.5°	1988.3	1929.1	1870.4	1796.6	1711.7	1633.9	1559.0	1488.7	1424.0	1360.7	1309.9
20°	1993.1	1932.4	1871.0	1798.7	1711.7	1622.6	1547.7	1463.3	1393.8	1328.3	1266.2
22.5°	1991.5	1922.7	1855.8	1781.5	1696.6	1614.5	1523.9	1437.9	1362.5	1298.1	1233.3
25°	1976.3	1902.7	1819.0	1744.1	1660.4	1573.3	1481.5	1392.4	1315.5	1241.9	1177.8
27.5°	1963.6	1868.1	1773.4	1686.0	1605.2	1525.4	1437.5	1346.3	1260.9	1186.4	1126.0
30°	1947.9	1843.3	1736.6	1645.5	1562.5	1484.9	1401.9	1312.8	1223.7	1150.8	1086.0
32.5°	1933.9	1812.0	1699.4	1600.2	1512.3	1436.8	1360.3	1275.5	1188.0	1114.1	1049.3
35°	1906.7	1765.7	1636.8	1524.7	1430.9	1353.3	1289.2	1210.2	1129.9	1058.3	996.2
37.5°	1872.3	1704.9	1566.6	1449.1	1346.3	1264.5	1204.8	1144.2	1067.1	998.1	942.0
40°	1845.3	1661.7	1515.3	1395.1	1288.5	1203.4	1148.1	1090.7	1026.6	962.5	903.1
42.5°	1811.3	1622.9	1463.4	1334.1	1228.5	1145.7	1087.6	1038.9	982.3	922.5	867.4
45°	1748.8	1552.4	1379.6	1240.6	1133.9	1052.2	992.2	955.7	913.2	856.5	809.9
47.5°	1656.9	1467.7	1289.0	1145.5	1035.5	959.8	903.5	868.5	838.6	796.4	754.2
50°	1575.3	1404.6	1223.7	1081.3	971.3	895.0	843.0	811.3	785.6	753.2	717.5
52.5°	1484.1	1325.2	1159.4	1018.6	909.7	834.5	783.6	755.7	734.3	711.1	675.9
55°	1339.1	1204.1	1050.2	916.6	816.0	742.4	697.9	673.6	656.1	638.5	616.9
57.5°	1179.4	1073.8	937.5	815.3	722.7	655.8	614.2	590.6	576.9	567.9	555.2
60°	1067.1	976.7	859.2	747.8	657.4	598.0	557.5	539.3	527.8	520.4	510.9
62.5°	962.9	888.6	779.8	678.2	599.1	542.9	506.8	489.1	478.1	474.5	466.7
65°	809.3	751.9	662.1	577.8	510.3	462.3	432.0	415.1	408.3	404.3	405.0
67.5°	657.9	623.0	550.9	478.9	425.1	384.9	360.6	347.6	344.2	338.8	338.7
70°	565.6	539.3	478.5	415.8	367.8	336.8	315.2	301.7	298.3	295.6	295.0
72.5°	484.1	461.0	408.3	358.0	314.9	287.7	269.8	261.7	256.2	254.6	254.5
75°	363.8	351.0	309.1	269.3	239.6	220.7	208.6	201.1	197.1	196.4	197.1
77.5°	258.6	247.4	220.8	192.6	173.9	159.6	149.3	146.7	142.1	142.3	141.6
80°	194.4	187.0	170.1	147.8	132.3	120.1	114.7	110.0	108.7	106.6	108.7
82.5°	140.9	133.0	121.5	107.3	94.5	87.2	81.8	80.3	79.5	78.6	79.0
85°	69.5	70.2	63.4	52.6	47.2	43.2	39.8	39.8	39.1	38.5	39.1
87.5°	26.4	24.9	22.5	20.5	17.4	15.4	14.4	14.8	13.4	13.2	14.2
90°	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0	2.0	4.0	6.0
92.5°	227.8	136.4	81.9	52.7	35.5	23.2	14.8	12.2	14.8	23.2	35.5
95°	446.2	226.6	119.8	74.9	52.9	41.9	33.9	32.9	33.9	41.9	52.9
97.5°	356.2	195.3	124.6	92.2	72.5	61.5	55.9	54.7	55.9	61.5	72.5
100°	323.4	193.7	135.8	105.8	86.8	75.9	71.9	69.9	71.9	75.9	86.8
102.5°	309.9	200.9	149.3	120.2	102.8	91.0	87.8	86.7	87.8	91.0	102.8
105°	304.5	215.6	171.7	143.8	127.8	117.8	112.8	112.8	112.8	117.8	127.8
107.5°	313.7	237.6	195.1	169.9	153.3	145.1	140.4	138.4	140.4	145.1	153.3
110°	322.4	253.6	212.6	186.7	171.7	162.7	158.7	156.7	158.7	162.7	171.7



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	333.6	268.7	229.4	204.2	189.3	180.3	177.1	175.1	177.1	180.3	189.3
115°	350.4	292.5	255.6	230.6	215.6	206.6	203.6	201.7	203.6	206.6	215.6
117.5°	369.6	316.9	281.9	257.8	240.8	231.8	228.6	225.6	228.6	231.8	240.8
120°	382.3	334.4	299.5	274.5	257.6	248.6	244.6	241.6	244.6	248.6	257.6
122.5°	396.7	351.2	316.3	291.3	272.7	263.7	260.5	258.4	260.5	263.7	272.7
125°	416.3	373.4	340.4	314.5	295.5	286.5	281.5	279.5	281.5	286.5	295.5
127.5°	434.2	394.7	363.0	337.0	316.9	305.5	299.1	296.1	299.1	305.5	316.9
130°	446.2	408.3	377.3	351.4	330.4	317.5	309.5	306.5	309.5	317.5	330.4
132.5°	456.6	421.1	390.1	364.2	342.4	327.8	318.2	314.5	318.2	327.8	342.4
135°	471.2	438.2	407.3	380.3	359.4	343.4	331.4	327.4	331.4	343.4	359.4
137.5°	482.0	450.4	422.3	394.5	374.0	358.0	346.8	343.8	346.8	358.0	374.0
140°	489.2	459.2	430.3	403.3	384.3	368.4	356.4	353.4	356.4	368.4	384.3
142.5°	493.1	464.8	437.4	412.1	393.9	377.9	366.8	364.6	366.8	377.9	393.9
145°	499.1	474.2	448.2	425.3	407.3	393.3	383.3	381.3	383.3	393.3	407.3
147.5°	502.7	480.2	457.4	437.2	421.7	408.7	400.1	398.9	400.1	408.7	421.7
150°	505.1	484.2	462.2	445.2	431.3	418.3	411.3	409.3	411.3	418.3	431.3
152.5°	506.7	488.2	467.8	452.4	439.2	427.9	421.7	420.5	421.7	427.9	439.2
155°	508.1	492.1	475.2	461.2	451.2	441.2	435.2	435.2	435.2	441.2	451.2
157.5°	509.1	495.5	481.0	470.4	461.6	453.0	448.2	448.4	448.2	453.0	461.6
160°	509.1	497.1	484.2	475.2	467.2	460.2	456.2	457.2	456.2	460.2	467.2
162.5°	508.3	498.7	487.4	480.0	473.6	467.4	463.4	464.4	463.4	467.4	473.6
165°	507.1	499.1	491.2	485.2	481.2	476.2	473.2	475.2	473.2	476.2	481.2
167.5°	504.7	499.1	492.5	488.8	486.0	483.2	481.4	482.4	481.4	483.2	486.0
170°	503.1	499.1	494.1	491.2	489.2	487.2	486.2	487.2	486.2	487.2	489.2
172.5°	501.5	498.3	494.1	492.7	491.5	489.6	488.6	490.4	488.6	489.6	491.5
175°	499.1	497.1	494.1	494.1	494.1	493.1	492.1	494.1	492.1	493.1	494.1
177.5°	496.7	495.9	494.3	494.3	495.1	494.3	494.3	495.9	494.3	494.3	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1562.6	1556.7	1551.8	1541.0	1535.1	1527.0	1520.5	1527.5	1520.0	1523.2	1518.4
5°	1513.9	1495.0	1481.5	1461.9	1445.1	1429.5	1418.1	1416.0	1410.6	1407.9	1399.8
7.5°	1455.3	1431.7	1408.5	1382.8	1361.2	1339.2	1325.2	1313.6	1305.9	1295.8	1288.9
10°	1420.8	1389.0	1362.1	1331.0	1304.0	1280.4	1261.5	1252.0	1243.3	1230.4	1225.7
12.5°	1378.1	1345.3	1312.4	1279.2	1253.2	1226.9	1210.7	1196.4	1190.3	1175.9	1174.4
15°	1327.0	1277.7	1245.3	1211.5	1175.8	1154.2	1140.7	1125.1	1118.4	1108.3	1100.8
17.5°	1265.9	1221.9	1181.4	1146.5	1115.8	1097.6	1080.9	1070.2	1058.6	1052.0	1039.8
20°	1221.7	1179.8	1139.3	1102.2	1078.6	1057.6	1044.1	1034.0	1021.9	1018.5	1006.4
22.5°	1184.4	1138.2	1099.4	1068.2	1042.4	1018.8	1004.2	997.3	988.9	978.5	976.1
25°	1123.8	1075.9	1042.8	1011.8	988.8	967.2	957.1	948.3	940.2	932.8	930.1
27.5°	1071.4	1028.6	989.3	961.3	941.3	921.6	912.7	902.0	896.1	890.1	882.8
30°	1034.7	990.8	956.4	929.4	907.8	890.3	880.8	873.4	868.0	862.6	858.5
32.5°	996.9	956.3	922.9	896.5	874.9	861.6	853.3	848.0	842.1	835.6	830.5
35°	947.0	902.4	870.0	847.1	830.2	820.1	810.6	805.9	799.1	799.1	793.7
37.5°	890.7	852.2	823.6	802.7	787.5	778.5	768.2	765.0	760.7	757.8	755.9
40°	857.2	821.4	794.4	773.5	757.3	749.9	741.8	736.4	733.7	730.3	728.9
42.5°	822.6	788.5	762.6	743.3	729.2	722.9	715.3	711.5	706.1	701.7	700.9
45°	770.1	737.0	713.4	697.9	685.7	678.3	673.6	665.5	662.8	657.4	656.7
47.5°	720.3	688.6	665.4	652.7	642.0	635.9	628.5	620.4	617.3	614.6	614.3
50°	683.1	654.0	632.4	620.3	610.2	601.4	594.0	588.6	586.5	586.5	587.9
52.5°	645.3	620.5	602.2	587.3	577.8	568.4	561.6	558.3	555.2	558.5	560.9
55°	589.9	564.9	551.4	537.3	527.8	517.0	513.6	512.3	510.3	515.7	518.4
57.5°	531.3	513.8	498.0	483.9	475.4	469.2	464.6	463.8	467.6	470.2	478.9
60°	494.1	473.8	459.6	448.8	438.7	434.7	433.3	432.0	434.7	442.1	453.6
62.5°	453.0	436.6	421.3	413.2	405.8	399.0	398.8	399.6	405.0	413.5	424.9
65°	392.8	378.6	368.5	359.1	353.0	348.9	350.3	353.0	359.1	370.5	383.4
67.5°	331.7	322.0	312.9	305.2	299.4	299.4	300.8	304.8	312.0	325.2	336.9
70°	292.3	281.5	274.0	270.7	265.9	263.2	267.3	274.0	280.1	292.3	302.4
72.5°	252.8	243.7	237.9	235.6	233.5	231.4	232.7	240.0	248.2	260.4	272.1
75°	194.4	191.0	187.0	184.3	182.2	183.6	184.9	191.7	198.4	211.3	224.8
77.5°	141.9	138.4	135.9	135.3	134.2	134.9	138.6	143.6	150.2	159.6	169.8
80°	107.3	106.0	104.6	103.9	103.9	104.6	110.0	113.4	119.5	128.2	136.3
82.5°	78.2	77.3	77.1	76.9	77.5	77.6	80.9	85.3	90.3	96.9	103.9
85°	41.2	39.8	41.8	42.5	41.2	43.2	44.5	47.2	49.3	52.6	56.0
87.5°	15.1	16.6	16.2	17.2	17.4	18.9	18.5	20.9	22.2	23.4	23.3
90°	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0	19.0	20.0	22.0
92.5°	52.7	81.9	136.4	227.8	327.0	321.8	260.5	176.9	128.4	96.6	81.9
95°	74.9	119.8	226.6	446.2	721.8	884.5	865.5	717.8	566.0	443.2	359.4
97.5°	92.2	124.6	195.3	356.2	644.5	944.6	1095.1	1069.0	962.5	842.9	726.3
100°	105.8	135.8	193.7	323.4	575.0	901.4	1151.0	1227.9	1179.0	1076.1	972.3
102.5°	120.2	149.3	200.9	309.9	522.3	825.6	1117.5	1281.4	1311.5	1262.2	1191.9
105°	143.8	171.7	215.6	304.5	471.2	723.7	1010.3	1249.8	1386.6	1430.5	1419.5
107.5°	169.9	195.1	237.6	313.7	449.6	653.7	900.8	1137.2	1319.7	1432.5	1484.6
110°	186.7	212.6	253.6	322.4	443.2	620.9	838.5	1054.2	1243.8	1384.6	1469.5



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	204.2	229.4	268.7	333.6	443.2	601.8	792.2	988.7	1168.8	1311.1	1411.2
115°	230.6	255.6	292.5	350.4	446.2	581.0	741.7	906.4	1061.2	1197.9	1306.7
117.5°	257.8	281.9	316.9	369.6	452.8	570.8	711.6	853.3	986.7	1104.5	1204.3
120°	274.5	299.5	334.4	382.3	459.2	566.0	694.8	824.6	944.4	1054.2	1142.0
122.5°	291.3	316.3	351.2	396.7	464.8	562.0	680.4	803.0	914.0	1011.8	1094.1
125°	314.5	340.4	373.4	416.3	474.2	557.0	660.9	771.7	873.5	960.3	1032.2
127.5°	337.0	363.0	394.7	434.2	484.8	554.6	642.9	739.7	834.8	915.8	983.1
130°	351.4	377.3	408.3	446.2	491.2	553.0	630.9	719.8	807.6	885.5	950.4
132.5°	364.2	390.1	421.1	456.6	498.3	553.0	621.3	699.8	782.0	852.7	915.2
135°	380.3	407.3	438.2	471.2	508.1	553.0	609.9	673.8	742.7	806.6	863.5
137.5°	394.5	422.3	450.4	482.0	517.1	554.2	599.8	651.9	707.6	760.7	809.0
140°	403.3	430.3	459.2	489.2	521.1	555.0	595.0	639.9	686.8	732.7	774.7
142.5°	412.1	437.4	464.8	493.1	523.5	555.8	591.0	629.5	669.2	708.8	745.1
145°	425.3	448.2	474.2	499.1	526.1	555.0	585.0	615.9	646.9	677.8	704.8
147.5°	437.2	457.4	480.2	502.7	527.1	552.4	578.8	603.2	628.3	652.1	672.4
150°	445.2	462.2	484.2	505.1	527.1	550.0	574.0	596.0	617.9	636.9	654.9
152.5°	452.4	467.8	488.2	506.7	526.3	546.9	568.4	588.0	607.5	624.9	638.9
155°	461.2	475.2	492.1	508.1	524.1	541.1	559.0	576.0	592.0	606.0	616.9
157.5°	470.4	481.0	495.5	509.1	521.5	535.1	550.2	564.0	577.2	588.0	596.6
160°	475.2	484.2	497.1	509.1	519.1	531.1	543.1	556.0	566.0	576.0	583.0
162.5°	480.0	487.4	498.7	508.3	516.7	526.3	536.7	547.3	556.4	564.8	571.0
165°	485.2	491.2	499.1	507.1	513.1	519.1	527.1	535.1	542.1	548.1	553.0
167.5°	488.8	492.5	499.1	504.7	507.5	512.1	517.7	523.5	528.1	532.7	536.3
170°	491.2	494.1	499.1	503.1	505.1	508.1	512.1	517.1	520.1	523.1	525.1
172.5°	492.7	494.1	498.3	501.5	501.9	503.3	506.5	509.9	512.9	515.1	516.3
175°	494.1	494.1	497.1	499.1	498.1	498.1	499.1	502.1	502.1	504.1	504.1
177.5°	494.3	494.3	495.9	496.7	495.1	495.1	495.9	496.7	497.5	497.5	497.5
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1515.1	1518.9	1515.7	1520.0	1515.7	1518.9	1515.1	1518.4	1523.2	1520.0	1527.5
5°	1396.5	1390.4	1394.4	1391.7	1394.4	1390.4	1396.5	1399.8	1407.9	1410.6	1416.0
7.5°	1286.9	1281.1	1274.4	1271.3	1274.4	1281.1	1286.9	1288.9	1295.8	1305.9	1313.6
10°	1218.3	1210.9	1210.2	1205.5	1210.2	1210.9	1218.3	1225.7	1230.4	1243.3	1252.0
12.5°	1168.1	1161.2	1153.5	1151.5	1153.5	1161.2	1168.1	1174.4	1175.9	1190.3	1196.4
15°	1096.8	1091.4	1086.7	1090.7	1086.7	1091.4	1096.8	1100.8	1108.3	1118.4	1125.1
17.5°	1037.5	1033.1	1032.3	1027.3	1032.3	1033.1	1037.5	1039.8	1052.0	1058.6	1070.2
20°	1000.3	996.9	998.3	989.5	998.3	996.9	1000.3	1006.4	1018.5	1021.9	1034.0
22.5°	970.6	964.0	963.2	961.4	963.2	964.0	970.6	976.1	978.5	988.9	997.3
25°	924.0	920.6	917.3	920.6	917.3	920.6	924.0	930.1	932.8	940.2	948.3
27.5°	883.4	879.3	878.4	878.8	878.4	879.3	883.4	882.8	890.1	896.1	902.0
30°	858.5	851.8	852.5	851.8	852.5	851.8	858.5	858.5	862.6	868.0	873.4
32.5°	831.5	826.9	826.0	824.8	826.0	826.9	831.5	830.5	835.6	842.1	848.0
35°	791.7	791.7	788.3	788.3	788.3	791.7	791.7	793.7	799.1	799.1	805.9
37.5°	754.3	753.6	751.6	751.9	751.6	753.6	754.3	755.9	757.8	760.7	765.0
40°	726.2	725.6	723.5	719.5	723.5	725.6	726.2	728.9	730.3	733.7	736.4
42.5°	699.2	697.0	696.0	694.7	696.0	697.0	699.2	700.9	701.7	706.1	711.5
45°	656.7	656.7	655.4	654.7	655.4	656.7	656.7	656.7	657.4	662.8	665.5
47.5°	615.4	616.6	619.2	618.8	619.2	616.6	615.4	614.3	614.6	617.3	620.4
50°	590.6	591.3	593.3	594.0	593.3	591.3	590.6	587.9	586.5	586.5	588.6
52.5°	563.0	567.0	569.5	569.1	569.5	567.0	563.0	560.9	558.5	555.2	558.3
55°	524.4	529.2	533.9	534.6	533.9	529.2	524.4	518.4	515.7	510.3	512.3
57.5°	486.2	492.8	497.8	499.5	497.8	492.8	486.2	478.9	470.2	467.6	463.8
60°	460.3	469.1	475.2	477.9	475.2	469.1	460.3	453.6	442.1	434.7	432.0
62.5°	435.5	445.3	451.4	451.9	451.4	445.3	435.5	424.9	413.5	405.0	399.6
65°	394.8	405.0	410.4	414.4	410.4	405.0	394.8	383.4	370.5	359.1	353.0
67.5°	351.1	361.2	367.2	370.4	367.2	361.2	351.1	336.9	325.2	312.0	304.8
70°	319.3	329.4	337.5	340.2	337.5	329.4	319.3	302.4	292.3	280.1	274.0
72.5°	287.9	297.0	303.5	306.7	303.5	297.0	287.9	272.1	260.4	248.2	240.0
75°	233.5	245.7	251.8	255.1	251.8	245.7	233.5	224.8	211.3	198.4	191.7
77.5°	180.1	191.1	194.8	196.5	194.8	191.1	180.1	169.8	159.6	150.2	143.6
80°	144.4	151.2	155.9	156.6	155.9	151.2	144.4	136.3	128.2	119.5	113.4
82.5°	111.0	116.6	118.1	119.9	118.1	116.6	111.0	103.9	96.9	90.3	85.3
85°	60.7	63.4	64.1	63.4	64.1	63.4	60.7	56.0	52.6	49.3	47.2
87.5°	24.4	23.8	24.0	25.1	24.0	23.8	24.4	23.3	23.4	22.2	20.9
90°	22.0	22.0	23.0	23.0	23.0	22.0	22.0	22.0	20.0	19.0	18.0
92.5°	69.1	66.7	65.3	63.7	65.3	66.7	69.1	81.9	96.6	128.4	176.9
95°	288.5	258.6	250.6	234.6	250.6	258.6	288.5	359.4	443.2	566.0	717.8
97.5°	664.7	608.7	579.8	567.0	579.8	608.7	664.7	726.3	842.9	962.5	1069.0
100°	903.4	831.6	794.6	778.7	794.6	831.6	903.4	972.3	1076.1	1179.0	1227.9
102.5°	1118.3	1067.2	1027.0	1015.0	1027.0	1067.2	1118.3	1191.9	1262.2	1311.5	1281.4
105°	1387.6	1354.7	1334.7	1322.7	1334.7	1354.7	1387.6	1419.5	1430.5	1386.6	1249.8
107.5°	1500.8	1500.6	1494.0	1486.0	1494.0	1500.6	1500.8	1484.6	1432.5	1319.7	1137.2
110°	1514.4	1533.3	1540.3	1540.3	1540.3	1533.3	1514.4	1469.5	1384.6	1243.8	1054.2



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1476.8	1509.4	1526.8	1533.9	1526.8	1509.4	1476.8	1411.2	1311.1	1168.8	988.7
115°	1384.6	1432.5	1460.5	1473.5	1460.5	1432.5	1384.6	1306.7	1197.9	1061.2	906.4
117.5°	1282.2	1331.7	1359.4	1367.4	1359.4	1331.7	1282.2	1204.3	1104.5	986.7	853.3
120°	1215.9	1263.8	1290.8	1298.8	1290.8	1263.8	1215.9	1142.0	1054.2	944.4	824.6
122.5°	1160.0	1203.9	1230.9	1238.1	1230.9	1203.9	1160.0	1094.1	1011.8	914.0	803.0
125°	1088.1	1129.0	1151.0	1161.0	1151.0	1129.0	1088.1	1032.2	960.3	873.5	771.7
127.5°	1033.8	1069.9	1090.7	1095.1	1090.7	1069.9	1033.8	983.1	915.8	834.8	739.7
130°	1000.3	1033.2	1053.2	1059.2	1053.2	1033.2	1000.3	950.4	885.5	807.6	719.8
132.5°	965.1	998.1	1016.4	1023.2	1016.4	998.1	965.1	915.2	852.7	782.0	699.8
135°	907.4	940.4	958.3	964.3	958.3	940.4	907.4	863.5	806.6	742.7	673.8
137.5°	848.3	878.3	894.9	901.4	894.9	878.3	848.3	809.0	760.7	707.6	651.9
140°	811.6	837.6	852.5	857.5	852.5	837.6	811.6	774.7	732.7	686.8	639.9
142.5°	776.5	798.4	812.6	816.8	812.6	798.4	776.5	745.1	708.8	669.2	629.5
145°	728.7	745.7	756.7	760.7	756.7	745.7	728.7	704.8	677.8	646.9	615.9
147.5°	691.4	705.0	711.4	713.2	711.4	705.0	691.4	672.4	652.1	628.3	603.2
150°	669.8	681.8	685.8	686.8	685.8	681.8	669.8	654.9	636.9	617.9	596.0
152.5°	651.5	661.1	665.0	666.0	665.0	661.1	651.5	638.9	624.9	607.5	588.0
155°	626.9	633.9	636.9	637.9	636.9	633.9	626.9	616.9	606.0	592.0	576.0
157.5°	604.4	610.1	612.9	612.7	612.9	610.1	604.4	596.6	588.0	577.2	564.0
160°	590.0	595.0	597.0	596.0	597.0	595.0	590.0	583.0	576.0	566.0	556.0
162.5°	576.4	580.6	581.0	580.8	581.0	580.6	576.4	571.0	564.8	556.4	547.3
165°	557.0	559.0	559.0	559.0	559.0	559.0	557.0	553.0	548.1	542.1	535.1
167.5°	538.3	540.1	539.3	539.1	539.3	540.1	538.3	536.3	532.7	528.1	523.5
170°	527.1	528.1	528.1	527.1	528.1	528.1	527.1	525.1	523.1	520.1	517.1
172.5°	516.7	518.5	516.9	515.9	516.9	518.5	516.7	516.3	515.1	512.9	509.9
175°	504.1	505.1	503.1	502.1	503.1	505.1	504.1	504.1	504.1	502.1	502.1
177.5°	496.7	497.5	495.1	495.1	495.1	497.5	496.7	497.5	497.5	497.5	496.7
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1520.5	1527.0	1535.1	1541.0	1551.8	1556.7	1562.6	1567.5	1576.1	1584.2	1594.0
5°	1418.1	1429.5	1445.1	1461.9	1481.5	1495.0	1513.9	1525.4	1548.3	1569.3	1589.5
7.5°	1325.2	1339.2	1361.2	1382.8	1408.5	1431.7	1455.3	1481.5	1510.8	1545.4	1574.0
10°	1261.5	1280.4	1304.0	1331.0	1362.1	1389.0	1420.8	1449.1	1484.9	1525.4	1563.2
12.5°	1210.7	1226.9	1253.2	1279.2	1312.4	1345.3	1378.1	1415.6	1457.4	1502.2	1549.7
15°	1140.7	1154.2	1175.8	1211.5	1245.3	1277.7	1327.0	1362.1	1414.7	1464.6	1522.0
17.5°	1080.9	1097.6	1115.8	1146.5	1181.4	1221.9	1265.9	1309.9	1360.7	1424.0	1488.7
20°	1044.1	1057.6	1078.6	1102.2	1139.3	1179.8	1221.7	1266.2	1328.3	1393.8	1463.3
22.5°	1004.2	1018.8	1042.4	1068.2	1099.4	1138.2	1184.4	1233.3	1298.1	1362.5	1437.9
25°	957.1	967.2	988.8	1011.8	1042.8	1075.9	1123.8	1177.8	1241.9	1315.5	1392.4
27.5°	912.7	921.6	941.3	961.3	989.3	1028.6	1071.4	1126.0	1186.4	1260.9	1346.3
30°	880.8	890.3	907.8	929.4	956.4	990.8	1034.7	1086.0	1150.8	1223.7	1312.8
32.5°	853.3	861.6	874.9	896.5	922.9	956.3	996.9	1049.3	1114.1	1188.0	1275.5
35°	810.6	820.1	830.2	847.1	870.0	902.4	947.0	996.2	1058.3	1129.9	1210.2
37.5°	768.2	778.5	787.5	802.7	823.6	852.2	890.7	942.0	998.1	1067.1	1144.2
40°	741.8	749.9	757.3	773.5	794.4	821.4	857.2	903.1	962.5	1026.6	1090.7
42.5°	715.3	722.9	729.2	743.3	762.6	788.5	822.6	867.4	922.5	982.3	1038.9
45°	673.6	678.3	685.7	697.9	713.4	737.0	770.1	809.9	856.5	913.2	955.7
47.5°	628.5	635.9	642.0	652.7	665.4	688.6	720.3	754.2	796.4	838.6	868.5
50°	594.0	601.4	610.2	620.3	632.4	654.0	683.1	717.5	753.2	785.6	811.3
52.5°	561.6	568.4	577.8	587.3	602.2	620.5	645.3	675.9	711.1	734.3	755.7
55°	513.6	517.0	527.8	537.3	551.4	564.9	589.9	616.9	638.5	656.1	673.6
57.5°	464.6	469.2	475.4	483.9	498.0	513.8	531.3	555.2	567.9	576.9	590.6
60°	433.3	434.7	438.7	448.8	459.6	473.8	494.1	510.9	520.4	527.8	539.3
62.5°	398.8	399.0	405.8	413.2	421.3	436.6	453.0	466.7	474.5	478.1	489.1
65°	350.3	348.9	353.0	359.1	368.5	378.6	392.8	405.0	404.3	408.3	415.1
67.5°	300.8	299.4	299.4	305.2	312.9	322.0	331.7	338.7	338.8	344.2	347.6
70°	267.3	263.2	265.9	270.7	274.0	281.5	292.3	295.0	295.6	298.3	301.7
72.5°	232.7	231.4	233.5	235.6	237.9	243.7	252.8	254.5	254.6	256.2	261.7
75°	184.9	183.6	182.2	184.3	187.0	191.0	194.4	197.1	196.4	197.1	201.1
77.5°	138.6	134.9	134.2	135.3	135.9	138.4	141.9	141.6	142.3	142.1	146.7
80°	110.0	104.6	103.9	103.9	104.6	106.0	107.3	108.7	106.6	108.7	110.0
82.5°	80.9	77.6	77.5	76.9	77.1	77.3	78.2	79.0	78.6	79.5	80.3
85°	44.5	43.2	41.2	42.5	41.8	39.8	41.2	39.1	38.5	39.1	39.8
87.5°	18.5	18.9	17.4	17.2	16.2	16.6	15.1	14.2	13.2	13.4	14.8
90°	17.0	16.0	14.0	13.0	11.0	10.0	8.0	6.0	4.0	2.0	1.0
92.5°	260.5	321.8	327.0	227.8	136.4	81.9	52.7	35.5	23.2	14.8	12.2
95°	865.5	884.5	721.8	446.2	226.6	119.8	74.9	52.9	41.9	33.9	32.9
97.5°	1095.1	944.6	644.5	356.2	195.3	124.6	92.2	72.5	61.5	55.9	54.7
100°	1151.0	901.4	575.0	323.4	193.7	135.8	105.8	86.8	75.9	71.9	69.9
102.5°	1117.5	825.6	522.3	309.9	200.9	149.3	120.2	102.8	91.0	87.8	86.7
105°	1010.3	723.7	471.2	304.5	215.6	171.7	143.8	127.8	117.8	112.8	112.8
107.5°	900.8	653.7	449.6	313.7	237.6	195.1	169.9	153.3	145.1	140.4	138.4
110°	838.5	620.9	443.2	322.4	253.6	212.6	186.7	171.7	162.7	158.7	156.7



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	792.2	601.8	443.2	333.6	268.7	229.4	204.2	189.3	180.3	177.1	175.1
115°	741.7	581.0	446.2	350.4	292.5	255.6	230.6	215.6	206.6	203.6	201.7
117.5°	711.6	570.8	452.8	369.6	316.9	281.9	257.8	240.8	231.8	228.6	225.6
120°	694.8	566.0	459.2	382.3	334.4	299.5	274.5	257.6	248.6	244.6	241.6
122.5°	680.4	562.0	464.8	396.7	351.2	316.3	291.3	272.7	263.7	260.5	258.4
125°	660.9	557.0	474.2	416.3	373.4	340.4	314.5	295.5	286.5	281.5	279.5
127.5°	642.9	554.6	484.8	434.2	394.7	363.0	337.0	316.9	305.5	299.1	296.1
130°	630.9	553.0	491.2	446.2	408.3	377.3	351.4	330.4	317.5	309.5	306.5
132.5°	621.3	553.0	498.3	456.6	421.1	390.1	364.2	342.4	327.8	318.2	314.5
135°	609.9	553.0	508.1	471.2	438.2	407.3	380.3	359.4	343.4	331.4	327.4
137.5°	599.8	554.2	517.1	482.0	450.4	422.3	394.5	374.0	358.0	346.8	343.8
140°	595.0	555.0	521.1	489.2	459.2	430.3	403.3	384.3	368.4	356.4	353.4
142.5°	591.0	555.8	523.5	493.1	464.8	437.4	412.1	393.9	377.9	366.8	364.6
145°	585.0	555.0	526.1	499.1	474.2	448.2	425.3	407.3	393.3	383.3	381.3
147.5°	578.8	552.4	527.1	502.7	480.2	457.4	437.2	421.7	408.7	400.1	398.9
150°	574.0	550.0	527.1	505.1	484.2	462.2	445.2	431.3	418.3	411.3	409.3
152.5°	568.4	546.9	526.3	506.7	488.2	467.8	452.4	439.2	427.9	421.7	420.5
155°	559.0	541.1	524.1	508.1	492.1	475.2	461.2	451.2	441.2	435.2	435.2
157.5°	550.2	535.1	521.5	509.1	495.5	481.0	470.4	461.6	453.0	448.2	448.4
160°	543.1	531.1	519.1	509.1	497.1	484.2	475.2	467.2	460.2	456.2	457.2
162.5°	536.7	526.3	516.7	508.3	498.7	487.4	480.0	473.6	467.4	463.4	464.4
165°	527.1	519.1	513.1	507.1	499.1	491.2	485.2	481.2	476.2	473.2	475.2
167.5°	517.7	512.1	507.5	504.7	499.1	492.5	488.8	486.0	483.2	481.4	482.4
170°	512.1	508.1	505.1	503.1	499.1	494.1	491.2	489.2	487.2	486.2	487.2
172.5°	506.5	503.3	501.9	501.5	498.3	494.1	492.7	491.5	489.6	488.6	490.4
175°	499.1	498.1	498.1	499.1	497.1	494.1	494.1	494.1	493.1	492.1	494.1
177.5°	495.9	495.1	495.1	496.7	495.9	494.3	494.3	495.1	494.3	494.3	495.9
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1598.8	1606.4	1611.2	1620.4	1628.0	1632.3	1636.1	1639.3	1643.1	1646.3	1655.5
5°	1609.1	1626.6	1641.5	1664.4	1685.4	1701.6	1719.1	1734.6	1747.4	1765.7	1779.8
7.5°	1604.6	1635.8	1668.5	1704.0	1740.3	1774.0	1805.1	1834.1	1860.4	1892.3	1920.2
10°	1600.3	1642.8	1684.7	1732.6	1781.9	1823.7	1862.9	1902.7	1931.7	1972.2	2006.6
12.5°	1597.1	1647.1	1697.6	1755.3	1809.4	1868.5	1920.6	1949.7	1993.8	2026.2	2067.1
15°	1583.4	1649.6	1719.1	1783.9	1860.8	1915.5	1961.4	2018.1	2059.3	2100.4	2145.0
17.5°	1559.0	1633.9	1711.7	1796.6	1870.4	1929.1	1988.3	2042.9	2092.1	2147.3	2202.8
20°	1547.7	1622.6	1711.7	1798.7	1871.0	1932.4	1993.1	2053.2	2107.2	2178.1	2242.2
22.5°	1523.9	1614.5	1696.6	1781.5	1855.8	1922.7	1991.5	2059.7	2131.5	2211.5	2291.9
25°	1481.5	1573.3	1660.4	1744.1	1819.0	1902.7	1976.3	2067.4	2159.2	2265.1	2365.0
27.5°	1437.5	1525.4	1605.2	1686.0	1773.4	1868.1	1963.6	2067.0	2187.1	2320.9	2461.8
30°	1401.9	1484.9	1562.5	1645.5	1736.6	1843.3	1947.9	2070.7	2209.8	2360.3	2527.7
32.5°	1360.3	1436.8	1512.3	1600.2	1699.4	1812.0	1933.9	2068.6	2235.7	2406.7	2579.0
35°	1289.2	1353.3	1430.9	1524.7	1636.8	1765.7	1906.7	2066.0	2257.7	2454.1	2599.2
37.5°	1204.8	1264.5	1346.3	1449.1	1566.6	1704.9	1872.3	2061.3	2264.9	2421.5	2468.3
40°	1148.1	1203.4	1288.5	1395.1	1515.3	1661.7	1845.3	2045.1	2242.2	2342.1	2303.6
42.5°	1087.6	1145.7	1228.5	1334.1	1463.4	1622.9	1811.3	2011.1	2176.3	2214.1	2081.1
45°	992.2	1052.2	1133.9	1240.6	1379.6	1552.4	1748.8	1930.4	2025.5	1957.4	1751.5
47.5°	903.5	959.8	1035.5	1145.5	1289.0	1467.7	1656.9	1801.7	1809.3	1646.6	1426.7
50°	843.0	895.0	971.3	1081.3	1223.7	1404.6	1575.3	1689.4	1638.1	1453.8	1242.6
52.5°	783.6	834.5	909.7	1018.6	1159.4	1325.2	1484.1	1564.1	1467.5	1278.4	1097.9
55°	697.9	742.4	816.0	916.6	1050.2	1204.1	1339.1	1366.8	1241.2	1054.9	908.5
57.5°	614.2	655.8	722.7	815.3	937.5	1073.8	1179.4	1173.5	1040.8	880.9	764.7
60°	557.5	598.0	657.4	747.8	859.2	976.7	1067.1	1045.5	913.9	776.2	678.3
62.5°	506.8	542.9	599.1	678.2	779.8	888.6	962.9	931.0	802.1	681.7	604.4
65°	432.0	462.3	510.3	577.8	662.1	751.9	809.3	768.1	658.1	564.3	502.2
67.5°	360.6	384.9	425.1	478.9	550.9	623.0	657.9	616.5	528.5	460.0	414.0
70°	315.2	336.8	367.8	415.8	478.5	539.3	565.6	528.5	452.9	394.2	361.1
72.5°	269.8	287.7	314.9	358.0	408.3	461.0	484.1	448.6	386.5	336.9	306.0
75°	208.6	220.7	239.6	269.3	309.1	351.0	363.8	332.8	292.9	255.8	235.6
77.5°	149.3	159.6	173.9	192.6	220.8	247.4	258.6	240.7	209.9	186.4	169.8
80°	114.7	120.1	132.3	147.8	170.1	187.0	194.4	182.9	161.3	143.8	130.9
82.5°	81.8	87.2	94.5	107.3	121.5	133.0	140.9	133.2	117.6	103.8	96.4
85°	39.8	43.2	47.2	52.6	63.4	70.2	69.5	64.8	58.7	53.3	49.3
87.5°	14.4	15.4	17.4	20.5	22.5	24.9	26.4	25.5	23.7	22.3	20.9
90°	2.0	4.0	6.0	8.0	10.0	11.0	13.0	14.0	16.0	17.0	18.0
92.5°	14.8	23.2	35.5	52.7	81.9	136.4	227.8	327.0	321.8	260.5	176.9
95°	33.9	41.9	52.9	74.9	119.8	226.6	446.2	721.8	884.5	865.5	717.8
97.5°	55.9	61.5	72.5	92.2	124.6	195.3	356.2	644.5	944.6	1095.1	1069.0
100°	71.9	75.9	86.8	105.8	135.8	193.7	323.4	575.0	901.4	1151.0	1227.9
102.5°	87.8	91.0	102.8	120.2	149.3	200.9	309.9	522.3	825.6	1117.5	1281.4
105°	112.8	117.8	127.8	143.8	171.7	215.6	304.5	471.2	723.7	1010.3	1249.8
107.5°	140.4	145.1	153.3	169.9	195.1	237.6	313.7	449.6	653.7	900.8	1137.2
110°	158.7	162.7	171.7	186.7	212.6	253.6	322.4	443.2	620.9	838.5	1054.2



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	177.1	180.3	189.3	204.2	229.4	268.7	333.6	443.2	601.8	792.2	988.7
115°	203.6	206.6	215.6	230.6	255.6	292.5	350.4	446.2	581.0	741.7	906.4
117.5°	228.6	231.8	240.8	257.8	281.9	316.9	369.6	452.8	570.8	711.6	853.3
120°	244.6	248.6	257.6	274.5	299.5	334.4	382.3	459.2	566.0	694.8	824.6
122.5°	260.5	263.7	272.7	291.3	316.3	351.2	396.7	464.8	562.0	680.4	803.0
125°	281.5	286.5	295.5	314.5	340.4	373.4	416.3	474.2	557.0	660.9	771.7
127.5°	299.1	305.5	316.9	337.0	363.0	394.7	434.2	484.8	554.6	642.9	739.7
130°	309.5	317.5	330.4	351.4	377.3	408.3	446.2	491.2	553.0	630.9	719.8
132.5°	318.2	327.8	342.4	364.2	390.1	421.1	456.6	498.3	553.0	621.3	699.8
135°	331.4	343.4	359.4	380.3	407.3	438.2	471.2	508.1	553.0	609.9	673.8
137.5°	346.8	358.0	374.0	394.5	422.3	450.4	482.0	517.1	554.2	599.8	651.9
140°	356.4	368.4	384.3	403.3	430.3	459.2	489.2	521.1	555.0	595.0	639.9
142.5°	366.8	377.9	393.9	412.1	437.4	464.8	493.1	523.5	555.8	591.0	629.5
145°	383.3	393.3	407.3	425.3	448.2	474.2	499.1	526.1	555.0	585.0	615.9
147.5°	400.1	408.7	421.7	437.2	457.4	480.2	502.7	527.1	552.4	578.8	603.2
150°	411.3	418.3	431.3	445.2	462.2	484.2	505.1	527.1	550.0	574.0	596.0
152.5°	421.7	427.9	439.2	452.4	467.8	488.2	506.7	526.3	546.9	568.4	588.0
155°	435.2	441.2	451.2	461.2	475.2	492.1	508.1	524.1	541.1	559.0	576.0
157.5°	448.2	453.0	461.6	470.4	481.0	495.5	509.1	521.5	535.1	550.2	564.0
160°	456.2	460.2	467.2	475.2	484.2	497.1	509.1	519.1	531.1	543.1	556.0
162.5°	463.4	467.4	473.6	480.0	487.4	498.7	508.3	516.7	526.3	536.7	547.3
165°	473.2	476.2	481.2	485.2	491.2	499.1	507.1	513.1	519.1	527.1	535.1
167.5°	481.4	483.2	486.0	488.8	492.5	499.1	504.7	507.5	512.1	517.7	523.5
170°	486.2	487.2	489.2	491.2	494.1	499.1	503.1	505.1	508.1	512.1	517.1
172.5°	488.6	489.6	491.5	492.7	494.1	498.3	501.5	501.9	503.3	506.5	509.9
175°	492.1	493.1	494.1	494.1	494.1	497.1	499.1	498.1	498.1	499.1	502.1
177.5°	494.3	494.3	495.1	494.3	494.3	495.9	496.7	495.1	495.1	495.9	496.7
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1	495.1



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1663.1	1667.4	1676.6	1673.3	1677.7	1679.8	1682.0
5°	1797.4	1819.0	1828.4	1827.1	1841.3	1837.9	1834.5
7.5°	1949.1	1971.8	1984.5	2000.3	2009.5	2010.1	2018.1
10°	2035.0	2064.7	2076.8	2093.7	2104.5	2110.6	2109.9
12.5°	2100.9	2124.1	2151.3	2159.6	2174.2	2181.8	2179.0
15°	2180.1	2217.2	2245.6	2259.7	2278.0	2283.4	2290.8
17.5°	2250.8	2300.6	2333.7	2377.7	2394.3	2404.4	2398.5
20°	2304.3	2369.8	2402.8	2455.5	2484.5	2500.0	2494.6
22.5°	2367.5	2438.3	2499.5	2545.1	2589.2	2610.2	2614.5
25°	2475.7	2572.9	2662.7	2722.8	2777.4	2790.2	2818.6
27.5°	2596.7	2711.3	2807.3	2870.4	2908.5	2922.8	2931.7
30°	2672.8	2786.9	2859.1	2899.6	2911.7	2910.4	2909.0
32.5°	2710.1	2781.5	2795.4	2784.0	2756.2	2732.7	2708.2
35°	2657.3	2604.0	2524.3	2421.7	2346.1	2269.9	2262.4
37.5°	2389.9	2219.4	2086.8	1938.7	1853.3	1800.5	1764.1
40°	2138.2	1944.5	1783.9	1659.0	1572.0	1537.5	1503.8
42.5°	1865.0	1680.0	1537.7	1433.3	1367.9	1329.7	1302.9
45°	1515.3	1351.9	1240.6	1165.0	1113.0	1083.3	1066.4
47.5°	1241.6	1120.8	1026.2	971.7	935.8	912.7	912.8
50°	1094.8	979.4	916.6	873.4	842.3	824.1	827.5
52.5°	964.6	878.4	824.8	788.6	765.7	754.5	754.1
55°	806.6	744.5	709.4	683.1	667.5	654.7	657.4
57.5°	689.9	637.6	614.1	592.2	581.4	576.3	568.8
60°	617.6	577.1	556.8	539.3	528.5	524.4	517.0
62.5°	553.3	521.5	501.8	487.4	477.7	476.4	470.6
65°	465.0	440.7	423.2	416.4	406.3	403.6	403.6
67.5°	383.4	366.0	352.3	346.1	341.7	342.3	339.1
70°	332.1	317.9	309.1	302.4	299.0	299.7	297.0
72.5°	290.5	274.7	267.0	263.0	258.5	260.3	259.2
75°	220.0	211.9	207.9	203.8	201.1	199.8	198.4
77.5°	161.6	154.4	151.3	149.0	149.4	146.2	148.8
80°	124.9	118.8	116.8	113.4	112.7	112.7	112.0
82.5°	91.4	88.0	86.5	83.7	82.5	83.6	81.8
85°	47.2	44.5	43.9	43.9	42.5	41.2	44.5
87.5°	21.1	19.1	19.5	19.0	19.0	18.6	17.6
90°	19.0	20.0	22.0	22.0	22.0	23.0	23.0
92.5°	128.4	96.6	81.9	69.1	66.7	65.3	63.7
95°	566.0	443.2	359.4	288.5	258.6	250.6	234.6
97.5°	962.5	842.9	726.3	664.7	608.7	579.8	567.0
100°	1179.0	1076.1	972.3	903.4	831.6	794.6	778.7
102.5°	1311.5	1262.2	1191.9	1118.3	1067.2	1027.0	1015.0
105°	1386.6	1430.5	1419.5	1387.6	1354.7	1334.7	1322.7
107.5°	1319.7	1432.5	1484.6	1500.8	1500.6	1494.0	1486.0
110°	1243.8	1384.6	1469.5	1514.4	1533.3	1540.3	1540.3



TEST NUMBER: P333279

CATALOG NUMBER: S125DIP-S1090D1035U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1168.8	1311.1	1411.2	1476.8	1509.4	1526.8	1533.9
115°	1061.2	1197.9	1306.7	1384.6	1432.5	1460.5	1473.5
117.5°	986.7	1104.5	1204.3	1282.2	1331.7	1359.4	1367.4
120°	944.4	1054.2	1142.0	1215.9	1263.8	1290.8	1298.8
122.5°	914.0	1011.8	1094.1	1160.0	1203.9	1230.9	1238.1
125°	873.5	960.3	1032.2	1088.1	1129.0	1151.0	1161.0
127.5°	834.8	915.8	983.1	1033.8	1069.9	1090.7	1095.1
130°	807.6	885.5	950.4	1000.3	1033.2	1053.2	1059.2
132.5°	782.0	852.7	915.2	965.1	998.1	1016.4	1023.2
135°	742.7	806.6	863.5	907.4	940.4	958.3	964.3
137.5°	707.6	760.7	809.0	848.3	878.3	894.9	901.4
140°	686.8	732.7	774.7	811.6	837.6	852.5	857.5
142.5°	669.2	708.8	745.1	776.5	798.4	812.6	816.8
145°	646.9	677.8	704.8	728.7	745.7	756.7	760.7
147.5°	628.3	652.1	672.4	691.4	705.0	711.4	713.2
150°	617.9	636.9	654.9	669.8	681.8	685.8	686.8
152.5°	607.5	624.9	638.9	651.5	661.1	665.0	666.0
155°	592.0	606.0	616.9	626.9	633.9	636.9	637.9
157.5°	577.2	588.0	596.6	604.4	610.1	612.9	612.7
160°	566.0	576.0	583.0	590.0	595.0	597.0	596.0
162.5°	556.4	564.8	571.0	576.4	580.6	581.0	580.8
165°	542.1	548.1	553.0	557.0	559.0	559.0	559.0
167.5°	528.1	532.7	536.3	538.3	540.1	539.3	539.1
170°	520.1	523.1	525.1	527.1	528.1	528.1	527.1
172.5°	512.9	515.1	516.3	516.7	518.5	516.9	515.9
175°	502.1	504.1	504.1	504.1	505.1	503.1	502.1
177.5°	497.5	497.5	497.5	496.7	497.5	495.1	495.1
180°	495.1	495.1	495.1	495.1	495.1	495.1	495.1

(END OF REPORT)