

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333294

Luminaire Tested: **S125DIP-S1090D1205U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333294
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1205U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8765.4 lumens
Efficiency: N/A
Efficacy: 134.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333294

CATALOG NUMBER: S125DIP-S1090D1205U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333294

CATALOG NUMBER: S125DIP-S1090D1205U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	50	49	48	43
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36
3	81	72	64	58	75	66	60	55	57	52	48	47	44	41	39	36	34	30
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	23	20	17
8	54	42	34	28	50	39	32	27	33	28	24	29	24	21	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11021	11021	11021
5°	11045	10940	11010
10°	10978	10863	10925
15°	10858	10732	10777
20°	10689	10549	10568
25°	10505	10332	10322
30°	10279	10097	10047
35°	10037	9845	9707
40°	9788	9571	9435
45°	9519	9322	9136
50°	9224	9020	8748
55°	8938	8679	8436
60°	8596	8335	8038
65°	8189	7922	7653
70°	7801	7444	7189
75°	7107	6872	6635
80°	6326	6226	6073
85°	5498	5602	5298



TEST NUMBER: P333294

CATALOG NUMBER: S125DIP-S1090D1205U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.9	1.8
10°-20°	454.5	5.2
20°-30°	671.0	7.7
30°-40°	783.0	8.9
40°-50°	786.4	9.0
50°-60°	690.3	7.9
60°-70°	514.4	5.9
70°-80°	294.1	3.4
80°-90°	88.8	1.0
90°-100°	417.8	4.8
100°-110°	898.0	10.2
110°-120°	842.8	9.6
120°-130°	683.0	7.8
130°-140°	548.1	6.3
140°-150°	413.6	4.7
150°-160°	291.2	3.3
160°-170°	171.6	2.0
170°-180°	55.8	0.6
0°-30°	1286.4	14.7
0°-40°	2069.4	23.6
0°-60°	3546.2	40.5
0°-90°	4443.4	50.7
90°-120°	2158.6	24.6
90°-150°	3803.4	43.4
90°-180°	4322.0	49.3
0°-180°	8765.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1706	1706	1706	1706	1706	
5°	1704	1700	1688	1699	1698	162
15°	1624	1619	1605	1612	1612	458
25°	1474	1467	1450	1452	1448	678
35°	1273	1267	1249	1242	1231	796
45°	1042	1036	1021	1005	1000	803
55°	794	789	771	759	749	708
65°	536	533	518	507	501	532
75°	285	282	275	271	266	304
85°	74	76	76	74	72	83
90°	1	10	19	24	27	6
95°	38	113	1030	467	273	41
105°	131	184	842	1659	1540	138
115°	235	283	676	1458	1715	231
125°	325	381	648	1160	1351	289
135°	381	458	644	972	1122	296
145°	444	508	646	805	885	278
155°	507	545	630	712	742	233
165°	553	568	604	641	651	156
175°	575	575	580	587	584	55
180°	576	576	576	576	576	



TEST NUMBER: P333294

CATALOG NUMBER: S125DIP-S1090D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1710.7	1710.0	1709.2	1708.5	1707.8	1706.2	1703.8	1701.4	1699.0	1696.6	1699.0
5°	1703.7	1703.1	1702.5	1701.9	1701.3	1699.5	1696.5	1693.5	1690.5	1687.5	1690.2
7.5°	1688.0	1687.4	1686.8	1686.2	1685.6	1683.6	1680.3	1677.0	1673.7	1670.4	1673.1
10°	1674.0	1673.4	1672.8	1672.2	1671.6	1669.6	1666.3	1663.0	1659.7	1656.4	1658.8
12.5°	1656.7	1655.6	1654.5	1653.4	1652.4	1650.3	1647.2	1644.2	1641.1	1638.0	1640.0
15°	1624.0	1623.1	1622.2	1621.3	1620.4	1618.3	1615.0	1611.7	1608.4	1605.1	1606.6
17.5°	1586.5	1585.2	1583.8	1582.5	1581.2	1578.8	1575.4	1572.0	1568.6	1565.1	1567.0
20°	1555.2	1554.6	1554.0	1553.4	1552.8	1550.5	1546.6	1542.7	1538.8	1534.9	1537.0
22.5°	1523.8	1522.8	1521.7	1520.6	1519.5	1517.1	1513.5	1509.8	1506.2	1502.5	1503.9
25°	1474.2	1472.7	1471.2	1469.7	1468.2	1465.5	1461.6	1457.7	1453.8	1449.9	1450.5
27.5°	1416.1	1415.2	1414.3	1413.4	1412.5	1410.1	1406.0	1402.0	1398.0	1394.0	1394.1
30°	1378.3	1377.4	1376.5	1375.6	1374.7	1372.0	1367.5	1363.0	1358.5	1354.0	1353.4
32.5°	1337.3	1335.9	1334.5	1333.1	1331.8	1329.1	1325.0	1321.0	1317.0	1313.0	1311.9
35°	1273.0	1271.8	1270.6	1269.4	1268.2	1265.5	1261.3	1257.1	1252.9	1248.7	1247.2
37.5°	1206.3	1204.8	1203.3	1201.8	1200.3	1197.6	1193.6	1189.7	1185.7	1181.8	1179.5
40°	1161.0	1159.5	1158.0	1156.5	1155.0	1152.1	1147.9	1143.7	1139.5	1135.3	1132.6
42.5°	1112.4	1111.1	1109.9	1108.6	1107.3	1104.6	1100.4	1096.2	1092.0	1087.8	1085.3
45°	1042.2	1041.0	1039.8	1038.6	1037.4	1035.0	1031.4	1027.8	1024.2	1020.6	1017.0
47.5°	966.6	966.6	966.7	966.8	966.8	964.7	960.4	956.0	951.7	947.4	943.7
50°	918.0	917.1	916.2	915.3	914.4	912.1	908.5	904.9	901.3	897.7	893.8
52.5°	868.3	867.6	867.0	866.3	865.7	863.4	859.6	855.7	851.9	848.0	844.6
55°	793.8	792.9	792.0	791.1	790.2	787.6	783.4	779.2	775.0	770.8	768.1
57.5°	715.2	714.7	714.3	713.8	713.3	711.3	707.7	704.2	700.7	697.1	693.6
60°	665.5	664.3	663.1	661.9	660.7	658.5	655.2	651.9	648.6	645.3	642.3
62.5°	613.7	612.7	611.8	610.8	609.9	608.0	605.1	602.3	599.5	596.7	593.4
65°	535.9	535.3	534.7	534.1	533.5	531.6	528.3	525.0	521.7	518.4	515.7
67.5°	460.6	459.3	458.1	456.8	455.6	453.7	451.2	448.8	446.3	443.9	441.6
70°	413.1	411.6	410.1	408.6	407.1	405.0	402.3	399.6	396.9	394.2	392.4
72.5°	361.3	360.2	359.2	358.2	357.2	355.8	354.1	352.3	350.6	348.8	346.8
75°	284.8	284.2	283.6	283.0	282.4	281.4	279.9	278.4	276.9	275.4	274.5
77.5°	214.4	214.1	213.9	213.7	213.4	212.9	212.0	211.2	210.4	209.5	209.0
80°	170.1	170.1	170.1	170.1	170.1	169.8	169.2	168.6	168.0	167.4	167.1
82.5°	131.2	130.7	130.3	129.8	129.3	129.0	128.9	128.8	128.6	128.5	128.0
85°	74.2	74.5	74.8	75.1	75.4	75.6	75.6	75.6	75.6	75.6	75.3
87.5°	29.4	29.6	30.1	30.6	31.0	31.4	31.4	31.6	31.6	31.8	32.0
90°	1.2	2.3	4.6	7.0	9.3	11.6	12.8	15.1	16.3	18.6	19.8
92.5°	14.2	17.2	27.0	41.4	61.4	95.3	158.7	265.2	380.7	374.6	303.3
95°	38.3	39.5	48.8	61.6	87.1	139.4	263.8	519.4	840.1	1029.5	1007.4
97.5°	63.7	65.1	71.6	84.4	107.4	145.0	227.3	414.6	750.2	1099.4	1274.7
100°	81.3	83.7	88.3	101.1	123.2	158.0	225.4	376.5	669.3	1049.2	1339.7
102.5°	100.9	102.3	106.0	119.7	139.9	173.8	233.8	360.7	607.9	960.9	1300.7
105°	131.3	131.3	137.1	148.7	167.3	199.9	251.0	354.4	548.4	842.4	1175.9
107.5°	161.0	163.4	168.9	178.5	197.8	227.0	276.5	365.1	523.3	760.8	1048.6
110°	182.4	184.8	189.4	199.9	217.3	247.5	295.1	375.3	515.9	722.7	976.0



TEST NUMBER: P333294

CATALOG NUMBER: S125DIP-S1090D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	203.8	206.1	209.8	220.3	237.7	267.0	312.8	388.3	515.9	700.4	922.1
115°	234.7	237.0	240.5	251.0	268.4	297.5	340.5	407.8	519.4	676.3	863.3
117.5°	262.6	266.1	269.8	280.3	300.0	328.1	368.8	430.2	527.1	664.4	828.2
120°	281.2	284.7	289.3	299.8	319.5	348.6	389.3	445.0	534.5	658.8	808.7
122.5°	300.7	303.3	307.0	317.4	339.1	368.1	408.8	461.8	541.0	654.2	792.0
125°	325.3	327.7	333.5	343.9	366.0	396.2	434.6	484.5	551.9	648.4	769.2
127.5°	344.6	348.1	355.6	368.8	392.3	422.5	459.4	505.5	564.2	645.6	748.3
130°	356.7	360.2	369.5	384.6	409.0	439.2	475.2	519.4	571.7	643.7	734.4
132.5°	366.0	370.4	381.6	398.6	423.9	454.1	490.1	531.5	580.0	643.7	723.2
135°	381.1	385.8	399.7	418.3	442.7	474.1	510.1	548.4	591.4	643.7	710.0
137.5°	400.2	403.7	416.7	435.3	459.2	491.5	524.3	561.0	601.9	645.1	698.1
140°	411.3	414.8	428.8	447.4	469.4	500.8	534.5	569.4	606.5	646.0	692.5
142.5°	424.3	426.9	439.9	458.5	479.7	509.2	541.0	574.0	609.3	647.0	687.9
145°	443.9	446.2	457.8	474.1	495.0	521.7	551.9	581.0	612.4	646.0	680.9
147.5°	464.3	465.7	475.7	490.8	508.9	532.4	558.9	585.2	613.5	643.0	673.7
150°	476.4	478.7	486.9	502.0	518.2	538.0	563.5	588.0	613.5	640.2	668.1
152.5°	489.4	490.8	498.0	511.3	526.6	544.5	568.2	589.8	612.6	636.5	661.6
155°	506.6	506.6	513.6	525.2	536.8	553.1	572.8	591.4	610.0	629.8	650.7
157.5°	522.0	521.7	527.3	537.3	547.5	559.8	576.8	592.6	607.0	622.8	640.5
160°	532.2	531.0	535.7	543.8	553.1	563.5	578.7	592.6	604.2	618.2	632.1
162.5°	540.5	539.4	544.0	551.2	558.7	567.3	580.5	591.7	601.4	612.6	624.7
165°	553.1	550.8	554.3	560.1	564.7	571.7	581.0	590.3	597.2	604.2	613.5
167.5°	561.5	560.3	562.4	565.6	568.9	573.3	581.0	587.5	590.7	596.1	602.6
170°	567.0	565.9	567.0	569.4	571.7	575.2	581.0	585.6	588.0	591.4	596.1
172.5°	570.8	568.7	569.8	572.1	573.5	575.2	580.0	583.8	584.2	585.9	589.6
175°	575.2	572.8	574.0	575.2	575.2	575.2	578.7	581.0	579.8	579.8	581.0
177.5°	577.3	575.4	575.4	576.3	575.4	575.4	577.3	578.2	576.3	576.3	577.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3



TEST NUMBER: P333294

CATALOG NUMBER: S125DIP-S1090D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1701.4	1703.8	1706.2	1707.3	1707.1	1706.8	1706.6	1706.4
5°	1692.9	1695.6	1698.3	1699.5	1699.2	1698.9	1698.6	1698.3
7.5°	1675.7	1678.4	1681.0	1682.2	1681.9	1681.6	1681.3	1681.0
10°	1661.2	1663.6	1666.0	1667.1	1666.8	1666.5	1666.2	1665.9
12.5°	1641.9	1643.8	1645.7	1646.7	1646.6	1646.5	1646.5	1646.4
15°	1608.1	1609.6	1611.1	1611.9	1611.9	1611.9	1611.9	1611.9
17.5°	1568.9	1570.7	1572.6	1572.8	1571.3	1569.8	1568.3	1566.8
20°	1539.1	1541.2	1543.3	1543.6	1542.1	1540.6	1539.1	1537.6
22.5°	1505.3	1506.7	1508.0	1508.2	1507.2	1506.2	1505.2	1504.1
25°	1451.1	1451.7	1452.3	1452.1	1451.2	1450.3	1449.4	1448.5
27.5°	1394.2	1394.3	1394.5	1394.1	1393.2	1392.3	1391.4	1390.5
30°	1352.8	1352.2	1351.6	1350.9	1350.0	1349.1	1348.2	1347.3
32.5°	1310.8	1309.7	1308.7	1307.3	1305.7	1304.1	1302.4	1300.8
35°	1245.7	1244.2	1242.7	1240.8	1238.4	1236.0	1233.6	1231.2
37.5°	1177.3	1175.1	1172.9	1171.1	1169.7	1168.3	1166.9	1165.6
40°	1129.9	1127.2	1124.5	1122.7	1121.8	1120.9	1120.0	1119.1
42.5°	1082.9	1080.4	1078.0	1076.0	1074.7	1073.3	1071.9	1070.5
45°	1013.4	1009.8	1006.2	1003.9	1003.0	1002.1	1001.2	1000.3
47.5°	940.1	936.4	932.8	929.9	927.8	925.7	923.6	921.5
50°	889.9	886.0	882.1	879.1	877.0	874.9	872.8	870.7
52.5°	841.2	837.8	834.4	831.5	829.1	826.8	824.5	822.1
55°	765.4	762.7	760.0	757.6	755.5	753.4	751.3	749.2
57.5°	690.2	686.7	683.2	680.9	679.8	678.6	677.5	676.3
60°	639.3	636.3	633.3	630.7	628.6	626.5	624.4	622.3
62.5°	590.2	587.0	583.7	581.3	579.7	578.1	576.4	574.8
65°	513.0	510.3	507.6	505.6	504.4	503.2	502.0	500.8
67.5°	439.3	437.0	434.7	433.2	432.5	431.8	431.1	430.4
70°	390.6	388.8	387.0	385.5	384.3	383.1	381.9	380.7
72.5°	344.8	342.7	340.7	339.1	337.9	336.7	335.5	334.3
75°	273.6	272.7	271.8	270.7	269.5	268.3	267.1	265.9
77.5°	208.4	207.9	207.4	206.7	205.8	205.0	204.1	203.3
80°	166.8	166.5	166.2	165.7	165.1	164.5	163.9	163.3
82.5°	127.4	126.9	126.4	126.0	125.9	125.8	125.7	125.5
85°	75.0	74.7	74.4	73.9	73.3	72.7	72.1	71.5
87.5°	32.3	32.5	32.7	33.0	32.5	32.0	31.7	31.3
90°	20.9	22.1	23.2	25.6	25.6	25.6	26.7	26.7
92.5°	205.9	149.4	112.5	95.3	80.4	77.6	76.0	74.1
95°	835.4	658.8	515.9	418.3	335.8	300.9	291.7	273.1
97.5°	1244.2	1120.4	981.2	845.4	773.6	708.6	674.9	660.0
100°	1429.2	1372.3	1252.6	1131.7	1051.6	967.9	924.9	906.3
102.5°	1491.5	1526.6	1469.2	1387.4	1301.6	1242.1	1195.4	1181.5
105°	1454.8	1614.0	1665.1	1652.3	1615.1	1576.8	1553.5	1539.6
107.5°	1323.7	1536.1	1667.4	1728.1	1746.9	1746.7	1739.0	1729.7
110°	1227.0	1447.8	1611.6	1710.4	1762.7	1784.8	1792.9	1792.9



TEST NUMBER: P333294

CATALOG NUMBER: S125DIP-S1090D1205U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1150.8	1360.4	1526.1	1642.5	1719.0	1756.9	1777.1	1785.5
115°	1055.1	1235.2	1394.3	1521.0	1611.6	1667.4	1699.9	1715.0
117.5°	993.2	1148.5	1285.6	1401.8	1492.4	1550.1	1582.4	1591.6
120°	959.8	1099.2	1227.0	1329.3	1415.3	1471.0	1502.4	1511.7
122.5°	934.7	1063.9	1177.8	1273.5	1350.2	1401.3	1432.7	1441.1
125°	898.2	1016.7	1117.8	1201.5	1266.5	1314.2	1339.7	1351.4
127.5°	861.0	971.6	1066.0	1144.3	1203.3	1245.4	1269.6	1274.7
130°	837.8	940.0	1030.7	1106.2	1164.3	1202.6	1225.9	1232.8
132.5°	814.5	910.3	992.5	1065.3	1123.4	1161.7	1183.1	1191.0
135°	784.3	864.5	938.9	1005.1	1056.2	1094.6	1115.5	1122.5
137.5°	758.8	823.6	885.4	941.7	987.4	1022.3	1041.6	1049.2
140°	744.8	799.4	852.9	901.7	944.7	974.9	992.3	998.1
142.5°	732.7	779.0	825.0	867.3	903.8	929.3	945.8	950.7
145°	716.9	752.9	789.0	820.3	848.2	868.0	880.8	885.4
147.5°	702.1	731.3	759.0	782.7	804.8	820.6	828.0	830.1
150°	693.7	719.3	741.3	762.2	779.7	793.6	798.3	799.4
152.5°	684.4	707.2	727.4	743.7	758.3	769.4	774.1	775.3
155°	670.4	689.0	705.3	718.1	729.7	737.8	741.3	742.5
157.5°	656.5	671.8	684.4	694.4	703.4	710.2	713.4	713.2
160°	647.2	658.8	670.4	678.6	686.7	692.5	694.9	693.7
162.5°	637.0	647.7	657.4	664.6	670.9	675.8	676.3	676.0
165°	622.8	630.9	637.9	643.7	648.4	650.7	650.7	650.7
167.5°	609.3	614.7	620.0	624.2	626.5	628.6	627.7	627.5
170°	601.9	605.4	608.9	611.2	613.5	614.7	614.7	613.5
172.5°	593.5	597.0	599.6	601.0	601.4	603.5	601.7	600.5
175°	584.5	584.5	586.8	586.8	586.8	588.0	585.6	584.5
177.5°	578.2	579.1	579.1	579.1	578.2	579.1	576.3	576.3
180°	576.3	576.3	576.3	576.3	576.3	576.3	576.3	576.3

(END OF REPORT)