

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333252

Luminaire Tested: **S125DIP-S1090D365U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333252
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D365U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5802.7 lumens
Efficiency: N/A
Efficacy: 133.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81	77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	71	69	66
2	95	88	81	76	91	84	78	74	77	72	68	70	67	64	64	61	59	56
3	87	77	70	64	83	74	67	62	68	62	58	62	58	54	57	54	51	47
4	80	69	61	54	76	66	59	53	61	55	50	56	51	47	51	47	44	41
5	74	62	53	47	70	59	51	46	54	48	43	50	45	41	46	42	38	36
6	68	55	47	41	65	53	46	40	49	43	38	46	40	36	42	37	34	31
7	63	50	42	36	60	48	41	35	45	38	34	41	36	32	38	34	30	28
8	59	46	38	32	56	44	37	31	41	35	30	38	32	28	35	31	27	25
9	55	42	34	29	52	40	33	28	38	31	27	35	30	26	33	28	24	22
10	51	39	31	26	49	37	30	25	35	29	24	32	27	23	30	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10270	10270	10270	10270
5°	11893	10305	9022	10305
10°	13837	10251	7906	10251
15°	15317	10176	7293	10176
20°	17145	10057	6801	10057
25°	20085	9922	6560	9922
30°	21694	9790	6352	9790
35°	17837	9541	6215	9541
40°	12678	9195	6066	9195
45°	9740	8729	5980	8729
50°	8314	8151	5968	8151
55°	7402	7585	6019	7585
60°	6678	6966	6173	6966
65°	6168	6343	6333	6343
70°	5608	5697	6424	5697
75°	4951	5018	6366	5018
80°	4166	4091	5824	4091
85°	3298	2949	4698	2949



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.1	2.6
10°-20°	455.8	7.9
20°-30°	740.1	12.8
30°-40°	902.8	15.6
40°-50°	821.3	14.2
50°-60°	654.2	11.3
60°-70°	455.6	7.9
70°-80°	243.0	4.2
80°-90°	62.3	1.1
90°-100°	127.1	2.2
100°-110°	273.1	4.7
110°-120°	256.3	4.4
120°-130°	207.7	3.6
130°-140°	166.7	2.9
140°-150°	125.8	2.2
150°-160°	88.6	1.5
160°-170°	52.2	0.9
170°-180°	17.0	0.3
0°-30°	1349.0	23.2
0°-40°	2251.8	38.8
0°-60°	3727.3	64.2
0°-90°	4488.2	77.3
90°-120°	656.5	11.3
90°-150°	1156.8	19.9
90°-180°	1315.0	22.7
0°-180°	5802.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1834	1590	1392	1590	1834	185
15°	2291	1522	1091	1522	2291	656
25°	2819	1392	921	1392	2819	1287
35°	2262	1210	788	1210	2262	1385
45°	1066	956	655	956	1066	854
55°	657	674	535	674	657	592
65°	404	415	414	415	404	401
75°	198	201	255	201	198	214
85°	44	40	63	40	44	52
90°	8	0	8	0	8	7
95°	83	12	83	12	83	118
105°	468	40	468	40	468	465
115°	522	71	522	71	522	510
125°	411	99	411	99	411	372
135°	341	116	341	116	341	265
145°	269	135	269	135	269	171
155°	226	154	226	154	226	105
165°	198	168	198	168	198	57
175°	178	175	178	175	178	17
180°	175	175	175	175	175	



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1682.0	1679.8	1677.7	1673.3	1676.6	1667.4	1663.1	1655.5	1646.3	1643.1	1639.3
5°	1834.5	1837.9	1841.3	1827.1	1828.4	1819.0	1797.4	1779.8	1765.7	1747.4	1734.6
7.5°	2018.1	2010.1	2009.5	2000.3	1984.5	1971.8	1949.1	1920.2	1892.3	1860.4	1834.1
10°	2109.9	2110.6	2104.5	2093.7	2076.8	2064.7	2035.0	2006.6	1972.2	1931.7	1902.7
12.5°	2179.0	2181.8	2174.2	2159.6	2151.3	2124.1	2100.9	2067.1	2026.2	1993.8	1949.7
15°	2290.8	2283.4	2278.0	2259.7	2245.6	2217.2	2180.1	2145.0	2100.4	2059.3	2018.1
17.5°	2398.5	2404.4	2394.3	2377.7	2333.7	2300.6	2250.8	2202.8	2147.3	2092.1	2042.9
20°	2494.6	2500.0	2484.5	2455.5	2402.8	2369.8	2304.3	2242.2	2178.1	2107.2	2053.2
22.5°	2614.5	2610.2	2589.2	2545.1	2499.5	2438.3	2367.5	2291.9	2211.5	2131.5	2059.7
25°	2818.6	2790.2	2777.4	2722.8	2662.7	2572.9	2475.7	2365.0	2265.1	2159.2	2067.4
27.5°	2931.7	2922.8	2908.5	2870.4	2807.3	2711.3	2596.7	2461.8	2320.9	2187.1	2067.0
30°	2909.0	2910.4	2911.7	2899.6	2859.1	2786.9	2672.8	2527.7	2360.3	2209.8	2070.7
32.5°	2708.2	2732.7	2756.2	2784.0	2795.4	2781.5	2710.1	2579.0	2406.7	2235.7	2068.6
35°	2262.4	2269.9	2346.1	2421.7	2524.3	2604.0	2657.3	2599.2	2454.1	2257.7	2066.0
37.5°	1764.1	1800.5	1853.3	1938.7	2086.8	2219.4	2389.9	2468.3	2421.5	2264.9	2061.3
40°	1503.8	1537.5	1572.0	1659.0	1783.9	1944.5	2138.2	2303.6	2342.1	2242.2	2045.1
42.5°	1302.9	1329.7	1367.9	1433.3	1537.7	1680.0	1865.0	2081.1	2214.1	2176.3	2011.1
45°	1066.4	1083.3	1113.0	1165.0	1240.6	1351.9	1515.3	1751.5	1957.4	2025.5	1930.4
47.5°	912.8	912.7	935.8	971.7	1026.2	1120.8	1241.6	1426.7	1646.6	1809.3	1801.7
50°	827.5	824.1	842.3	873.4	916.6	979.4	1094.8	1242.6	1453.8	1638.1	1689.4
52.5°	754.1	754.5	765.7	788.6	824.8	878.4	964.6	1097.9	1278.4	1467.5	1564.1
55°	657.4	654.7	667.5	683.1	709.4	744.5	806.6	908.5	1054.9	1241.2	1366.8
57.5°	568.8	576.3	581.4	592.2	614.1	637.6	689.9	764.7	880.9	1040.8	1173.5
60°	517.0	524.4	528.5	539.3	556.8	577.1	617.6	678.3	776.2	913.9	1045.5
62.5°	470.6	476.4	477.7	487.4	501.8	521.5	553.3	604.4	681.7	802.1	931.0
65°	403.6	403.6	406.3	416.4	423.2	440.7	465.0	502.2	564.3	658.1	768.1
67.5°	339.1	342.3	341.7	346.1	352.3	366.0	383.4	414.0	460.0	528.5	616.5
70°	297.0	299.7	299.0	302.4	309.1	317.9	332.1	361.1	394.2	452.9	528.5
72.5°	259.2	260.3	258.5	263.0	267.0	274.7	290.5	306.0	336.9	386.5	448.6
75°	198.4	199.8	201.1	203.8	207.9	211.9	220.0	235.6	255.8	292.9	332.8
77.5°	148.8	146.2	149.4	149.0	151.3	154.4	161.6	169.8	186.4	209.9	240.7
80°	112.0	112.7	112.7	113.4	116.8	118.8	124.9	130.9	143.8	161.3	182.9
82.5°	81.8	83.6	82.5	83.7	86.5	88.0	91.4	96.4	103.8	117.6	133.2
85°	44.5	41.2	42.5	43.9	43.9	44.5	47.2	49.3	53.3	58.7	64.8
87.5°	14.6	15.7	16.1	16.1	16.7	16.5	18.6	18.6	20.1	21.6	23.7
90°	8.1	8.1	7.8	7.8	7.8	7.1	6.7	6.4	6.0	5.7	4.9
92.5°	22.5	23.1	23.6	24.5	29.0	34.2	45.4	62.6	92.2	113.9	115.8
95°	83.1	88.7	91.5	102.1	127.2	156.9	200.4	254.1	306.4	313.1	255.5
97.5°	200.7	205.3	215.5	235.3	257.1	298.4	340.8	378.4	387.7	334.4	228.2
100°	275.7	281.3	294.4	319.8	344.2	381.0	417.4	434.7	407.5	319.1	203.6
102.5°	359.4	363.6	377.8	395.9	422.0	446.9	464.3	453.6	395.6	292.3	184.9
105°	468.3	472.5	479.6	491.2	502.6	506.4	490.9	442.5	357.7	256.2	166.8
107.5°	526.1	528.9	531.3	531.3	525.6	507.1	467.2	402.6	318.9	231.4	159.2
110°	545.3	545.3	542.8	536.1	520.2	490.2	440.4	373.2	296.9	219.8	156.9



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	543.1	540.5	534.4	522.8	499.6	464.2	413.8	350.0	280.5	213.0	156.9
115°	521.6	517.0	507.1	490.2	462.6	424.1	375.7	320.9	262.6	205.7	158.0
117.5°	484.1	481.3	471.5	453.9	426.4	391.0	349.3	302.1	251.9	202.1	160.3
120°	459.8	457.0	447.4	430.5	404.3	373.2	334.3	291.9	246.0	200.4	162.6
122.5°	438.3	435.8	426.2	410.7	387.3	358.2	323.6	284.3	240.9	199.0	164.5
125°	411.0	407.5	399.7	385.2	365.4	340.0	309.2	273.2	234.0	197.2	167.9
127.5°	387.7	386.1	378.8	366.0	348.0	324.2	295.5	261.9	227.6	196.4	171.6
130°	375.0	372.9	365.8	354.1	336.5	313.5	285.9	254.8	223.4	195.8	173.9
132.5°	362.2	359.8	353.3	341.7	324.0	301.9	276.9	247.7	220.0	195.8	176.4
135°	341.4	339.3	332.9	321.3	305.7	285.6	262.9	238.6	215.9	195.8	179.9
137.5°	319.1	316.8	310.9	300.3	286.4	269.3	250.5	230.8	212.3	196.2	183.1
140°	303.6	301.8	296.5	287.3	274.2	259.4	243.1	226.5	210.6	196.5	184.5
142.5°	289.2	287.7	282.7	274.9	263.8	250.9	236.9	222.9	209.2	196.8	185.3
145°	269.3	267.9	264.0	258.0	249.5	240.0	229.0	218.1	207.1	196.5	186.2
147.5°	252.5	251.8	249.6	244.8	238.1	230.9	222.4	213.5	204.9	195.6	186.6
150°	243.1	242.8	241.4	237.1	231.8	225.5	218.8	211.0	203.2	194.7	186.6
152.5°	235.8	235.4	234.0	230.6	226.2	221.2	215.1	208.2	201.2	193.6	186.3
155°	225.8	225.5	224.4	221.9	218.4	214.5	209.6	203.9	197.9	191.6	185.5
157.5°	216.9	217.0	216.0	214.0	211.2	208.2	204.3	199.7	194.8	189.4	184.6
160°	211.0	211.3	210.6	208.9	206.4	203.9	200.4	196.9	192.3	188.0	183.8
162.5°	205.6	205.7	205.5	204.1	202.2	200.0	197.0	193.7	190.0	186.3	182.9
165°	197.9	197.9	197.9	197.2	195.8	194.0	191.9	189.4	186.6	183.8	181.7
167.5°	190.8	190.9	191.2	190.6	189.9	188.6	187.0	185.3	183.3	181.3	179.7
170°	186.6	187.0	187.0	186.6	185.9	185.2	184.1	183.1	181.3	179.9	178.8
172.5°	182.6	183.0	183.6	182.9	182.8	182.4	181.6	180.5	179.3	178.2	177.7
175°	177.8	178.1	178.8	178.5	178.5	178.5	177.8	177.8	176.7	176.4	176.4
177.5°	175.3	175.3	176.1	175.9	176.1	176.1	176.1	175.9	175.6	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1636.1	1632.3	1628.0	1620.4	1611.2	1606.4	1598.8	1594.0	1584.2	1576.1	1567.5
5°	1719.1	1701.6	1685.4	1664.4	1641.5	1626.6	1609.1	1589.5	1569.3	1548.3	1525.4
7.5°	1805.1	1774.0	1740.3	1704.0	1668.5	1635.8	1604.6	1574.0	1545.4	1510.8	1481.5
10°	1862.9	1823.7	1781.9	1732.6	1684.7	1642.8	1600.3	1563.2	1525.4	1484.9	1449.1
12.5°	1920.6	1868.5	1809.4	1755.3	1697.6	1647.1	1597.1	1549.7	1502.2	1457.4	1415.6
15°	1961.4	1915.5	1860.8	1783.9	1719.1	1649.6	1583.4	1522.0	1464.6	1414.7	1362.1
17.5°	1988.3	1929.1	1870.4	1796.6	1711.7	1633.9	1559.0	1488.7	1424.0	1360.7	1309.9
20°	1993.1	1932.4	1871.0	1798.7	1711.7	1622.6	1547.7	1463.3	1393.8	1328.3	1266.2
22.5°	1991.5	1922.7	1855.8	1781.5	1696.6	1614.5	1523.9	1437.9	1362.5	1298.1	1233.3
25°	1976.3	1902.7	1819.0	1744.1	1660.4	1573.3	1481.5	1392.4	1315.5	1241.9	1177.8
27.5°	1963.6	1868.1	1773.4	1686.0	1605.2	1525.4	1437.5	1346.3	1260.9	1186.4	1126.0
30°	1947.9	1843.3	1736.6	1645.5	1562.5	1484.9	1401.9	1312.8	1223.7	1150.8	1086.0
32.5°	1933.9	1812.0	1699.4	1600.2	1512.3	1436.8	1360.3	1275.5	1188.0	1114.1	1049.3
35°	1906.7	1765.7	1636.8	1524.7	1430.9	1353.3	1289.2	1210.2	1129.9	1058.3	996.2
37.5°	1872.3	1704.9	1566.6	1449.1	1346.3	1264.5	1204.8	1144.2	1067.1	998.1	942.0
40°	1845.3	1661.7	1515.3	1395.1	1288.5	1203.4	1148.1	1090.7	1026.6	962.5	903.1
42.5°	1811.3	1622.9	1463.4	1334.1	1228.5	1145.7	1087.6	1038.9	982.3	922.5	867.4
45°	1748.8	1552.4	1379.6	1240.6	1133.9	1052.2	992.2	955.7	913.2	856.5	809.9
47.5°	1656.9	1467.7	1289.0	1145.5	1035.5	959.8	903.5	868.5	838.6	796.4	754.2
50°	1575.3	1404.6	1223.7	1081.3	971.3	895.0	843.0	811.3	785.6	753.2	717.5
52.5°	1484.1	1325.2	1159.4	1018.6	909.7	834.5	783.6	755.7	734.3	711.1	675.9
55°	1339.1	1204.1	1050.2	916.6	816.0	742.4	697.9	673.6	656.1	638.5	616.9
57.5°	1179.4	1073.8	937.5	815.3	722.7	655.8	614.2	590.6	576.9	567.9	555.2
60°	1067.1	976.7	859.2	747.8	657.4	598.0	557.5	539.3	527.8	520.4	510.9
62.5°	962.9	888.6	779.8	678.2	599.1	542.9	506.8	489.1	478.1	474.5	466.7
65°	809.3	751.9	662.1	577.8	510.3	462.3	432.0	415.1	408.3	404.3	405.0
67.5°	657.9	623.0	550.9	478.9	425.1	384.9	360.6	347.6	344.2	338.8	338.7
70°	565.6	539.3	478.5	415.8	367.8	336.8	315.2	301.7	298.3	295.6	295.0
72.5°	484.1	461.0	408.3	358.0	314.9	287.7	269.8	261.7	256.2	254.6	254.5
75°	363.8	351.0	309.1	269.3	239.6	220.7	208.6	201.1	197.1	196.4	197.1
77.5°	258.6	247.4	220.8	192.6	173.9	159.6	149.3	146.7	142.1	142.3	141.6
80°	194.4	187.0	170.1	147.8	132.3	120.1	114.7	110.0	108.7	106.6	108.7
82.5°	140.9	133.0	121.5	107.3	94.5	87.2	81.8	80.3	79.5	78.6	79.0
85°	69.5	70.2	63.4	52.6	47.2	43.2	39.8	39.8	39.1	38.5	39.1
87.5°	24.7	23.5	21.2	19.5	16.6	14.9	14.2	14.6	13.1	12.7	13.4
90°	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	80.6	48.3	29.0	18.7	12.6	8.2	5.2	4.3	5.2	8.2	12.6
95°	158.0	80.2	42.4	26.5	18.7	14.8	12.0	11.7	12.0	14.8	18.7
97.5°	126.1	69.1	44.1	32.7	25.7	21.8	19.8	19.4	19.8	21.8	25.7
100°	114.5	68.6	48.1	37.5	30.7	26.9	25.4	24.7	25.4	26.9	30.7
102.5°	109.7	71.1	52.9	42.6	36.4	32.2	31.1	30.7	31.1	32.2	36.4
105°	107.8	76.3	60.8	50.9	45.2	41.7	39.9	39.9	39.9	41.7	45.2
107.5°	111.0	84.1	69.1	60.2	54.3	51.4	49.7	49.0	49.7	51.4	54.3
110°	114.2	89.8	75.3	66.1	60.8	57.6	56.2	55.5	56.2	57.6	60.8



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	118.1	95.1	81.2	72.3	67.0	63.8	62.7	62.0	62.7	63.8	67.0
115°	124.0	103.6	90.5	81.6	76.3	73.2	72.1	71.4	72.1	73.2	76.3
117.5°	130.8	112.2	99.8	91.3	85.2	82.1	80.9	79.9	80.9	82.1	85.2
120°	135.4	118.4	106.0	97.2	91.2	88.0	86.6	85.5	86.6	88.0	91.2
122.5°	140.4	124.3	112.0	103.1	96.6	93.4	92.2	91.5	92.2	93.4	96.6
125°	147.4	132.2	120.5	111.3	104.6	101.4	99.7	99.0	99.7	101.4	104.6
127.5°	153.7	139.7	128.5	119.3	112.2	108.1	105.9	104.8	105.9	108.1	112.2
130°	158.0	144.5	133.6	124.4	117.0	112.4	109.6	108.5	109.6	112.4	117.0
132.5°	161.7	149.1	138.1	128.9	121.2	116.1	112.7	111.3	112.7	116.1	121.2
135°	166.8	155.1	144.2	134.7	127.2	121.6	117.3	115.9	117.3	121.6	127.2
137.5°	170.6	159.5	149.5	139.7	132.4	126.7	122.8	121.7	122.8	126.7	132.4
140°	173.2	162.6	152.3	142.8	136.1	130.4	126.2	125.1	126.2	130.4	136.1
142.5°	174.6	164.5	154.9	145.9	139.5	133.8	129.8	129.1	129.8	133.8	139.5
145°	176.7	167.9	158.7	150.6	144.2	139.2	135.7	135.0	135.7	139.2	144.2
147.5°	178.0	170.0	161.9	154.8	149.3	144.7	141.6	141.2	141.6	144.7	149.3
150°	178.8	171.4	163.6	157.6	152.7	148.1	145.6	144.9	145.6	148.1	152.7
152.5°	179.4	172.8	165.6	160.2	155.5	151.5	149.3	148.9	149.3	151.5	155.5
155°	179.9	174.2	168.2	163.3	159.7	156.2	154.1	154.1	154.1	156.2	159.7
157.5°	180.2	175.4	170.3	166.5	163.4	160.4	158.7	158.8	158.7	160.4	163.4
160°	180.2	176.0	171.4	168.2	165.4	162.9	161.5	161.9	161.5	162.9	165.4
162.5°	180.0	176.6	172.5	169.9	167.7	165.5	164.1	164.4	164.1	165.5	167.7
165°	179.5	176.7	173.9	171.8	170.3	168.6	167.5	168.2	167.5	168.6	170.3
167.5°	178.7	176.7	174.4	173.0	172.0	171.1	170.4	170.8	170.4	171.1	172.0
170°	178.1	176.7	174.9	173.9	173.2	172.5	172.1	172.5	172.1	172.5	173.2
172.5°	177.6	176.4	174.9	174.4	174.0	173.3	173.0	173.6	173.0	173.3	174.0
175°	176.7	176.0	174.9	174.9	174.9	174.6	174.2	174.9	174.2	174.6	174.9
177.5°	175.9	175.6	175.0	175.0	175.3	175.0	175.0	175.6	175.0	175.0	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1562.6	1556.7	1551.8	1541.0	1535.1	1527.0	1520.5	1527.5	1520.0	1523.2	1518.4
5°	1513.9	1495.0	1481.5	1461.9	1445.1	1429.5	1418.1	1416.0	1410.6	1407.9	1399.8
7.5°	1455.3	1431.7	1408.5	1382.8	1361.2	1339.2	1325.2	1313.6	1305.9	1295.8	1288.9
10°	1420.8	1389.0	1362.1	1331.0	1304.0	1280.4	1261.5	1252.0	1243.3	1230.4	1225.7
12.5°	1378.1	1345.3	1312.4	1279.2	1253.2	1226.9	1210.7	1196.4	1190.3	1175.9	1174.4
15°	1327.0	1277.7	1245.3	1211.5	1175.8	1154.2	1140.7	1125.1	1118.4	1108.3	1100.8
17.5°	1265.9	1221.9	1181.4	1146.5	1115.8	1097.6	1080.9	1070.2	1058.6	1052.0	1039.8
20°	1221.7	1179.8	1139.3	1102.2	1078.6	1057.6	1044.1	1034.0	1021.9	1018.5	1006.4
22.5°	1184.4	1138.2	1099.4	1068.2	1042.4	1018.8	1004.2	997.3	988.9	978.5	976.1
25°	1123.8	1075.9	1042.8	1011.8	988.8	967.2	957.1	948.3	940.2	932.8	930.1
27.5°	1071.4	1028.6	989.3	961.3	941.3	921.6	912.7	902.0	896.1	890.1	882.8
30°	1034.7	990.8	956.4	929.4	907.8	890.3	880.8	873.4	868.0	862.6	858.5
32.5°	996.9	956.3	922.9	896.5	874.9	861.6	853.3	848.0	842.1	835.6	830.5
35°	947.0	902.4	870.0	847.1	830.2	820.1	810.6	805.9	799.1	799.1	793.7
37.5°	890.7	852.2	823.6	802.7	787.5	778.5	768.2	765.0	760.7	757.8	755.9
40°	857.2	821.4	794.4	773.5	757.3	749.9	741.8	736.4	733.7	730.3	728.9
42.5°	822.6	788.5	762.6	743.3	729.2	722.9	715.3	711.5	706.1	701.7	700.9
45°	770.1	737.0	713.4	697.9	685.7	678.3	673.6	665.5	662.8	657.4	656.7
47.5°	720.3	688.6	665.4	652.7	642.0	635.9	628.5	620.4	617.3	614.6	614.3
50°	683.1	654.0	632.4	620.3	610.2	601.4	594.0	588.6	586.5	586.5	587.9
52.5°	645.3	620.5	602.2	587.3	577.8	568.4	561.6	558.3	555.2	558.5	560.9
55°	589.9	564.9	551.4	537.3	527.8	517.0	513.6	512.3	510.3	515.7	518.4
57.5°	531.3	513.8	498.0	483.9	475.4	469.2	464.6	463.8	467.6	470.2	478.9
60°	494.1	473.8	459.6	448.8	438.7	434.7	433.3	432.0	434.7	442.1	453.6
62.5°	453.0	436.6	421.3	413.2	405.8	399.0	398.8	399.6	405.0	413.5	424.9
65°	392.8	378.6	368.5	359.1	353.0	348.9	350.3	353.0	359.1	370.5	383.4
67.5°	331.7	322.0	312.9	305.2	299.4	299.4	300.8	304.8	312.0	325.2	336.9
70°	292.3	281.5	274.0	270.7	265.9	263.2	267.3	274.0	280.1	292.3	302.4
72.5°	252.8	243.7	237.9	235.6	233.5	231.4	232.7	240.0	248.2	260.4	272.1
75°	194.4	191.0	187.0	184.3	182.2	183.6	184.9	191.7	198.4	211.3	224.8
77.5°	141.9	138.4	135.9	135.3	134.2	134.9	138.6	143.6	150.2	159.6	169.8
80°	107.3	106.0	104.6	103.9	103.9	104.6	110.0	113.4	119.5	128.2	136.3
82.5°	78.2	77.3	77.1	76.9	77.5	77.6	80.9	85.3	90.3	96.9	103.9
85°	41.2	39.8	41.8	42.5	41.2	43.2	44.5	47.2	49.3	52.6	56.0
87.5°	14.1	15.3	14.8	15.5	15.6	16.8	16.3	18.6	19.7	20.9	20.5
90°	2.8	3.5	3.9	4.6	4.9	5.7	6.0	6.4	6.7	7.1	7.8
92.5°	18.7	29.0	48.3	80.6	115.8	113.9	92.2	62.6	45.4	34.2	29.0
95°	26.5	42.4	80.2	158.0	255.5	313.1	306.4	254.1	200.4	156.9	127.2
97.5°	32.7	44.1	69.1	126.1	228.2	334.4	387.7	378.4	340.8	298.4	257.1
100°	37.5	48.1	68.6	114.5	203.6	319.1	407.5	434.7	417.4	381.0	344.2
102.5°	42.6	52.9	71.1	109.7	184.9	292.3	395.6	453.6	464.3	446.9	422.0
105°	50.9	60.8	76.3	107.8	166.8	256.2	357.7	442.5	490.9	506.4	502.6
107.5°	60.2	69.1	84.1	111.0	159.2	231.4	318.9	402.6	467.2	507.1	525.6
110°	66.1	75.3	89.8	114.2	156.9	219.8	296.9	373.2	440.4	490.2	520.2



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	72.3	81.2	95.1	118.1	156.9	213.0	280.5	350.0	413.8	464.2	499.6
115°	81.6	90.5	103.6	124.0	158.0	205.7	262.6	320.9	375.7	424.1	462.6
117.5°	91.3	99.8	112.2	130.8	160.3	202.1	251.9	302.1	349.3	391.0	426.4
120°	97.2	106.0	118.4	135.4	162.6	200.4	246.0	291.9	334.3	373.2	404.3
122.5°	103.1	112.0	124.3	140.4	164.5	199.0	240.9	284.3	323.6	358.2	387.3
125°	111.3	120.5	132.2	147.4	167.9	197.2	234.0	273.2	309.2	340.0	365.4
127.5°	119.3	128.5	139.7	153.7	171.6	196.4	227.6	261.9	295.5	324.2	348.0
130°	124.4	133.6	144.5	158.0	173.9	195.8	223.4	254.8	285.9	313.5	336.5
132.5°	128.9	138.1	149.1	161.7	176.4	195.8	220.0	247.7	276.9	301.9	324.0
135°	134.7	144.2	155.1	166.8	179.9	195.8	215.9	238.6	262.9	285.6	305.7
137.5°	139.7	149.5	159.5	170.6	183.1	196.2	212.3	230.8	250.5	269.3	286.4
140°	142.8	152.3	162.6	173.2	184.5	196.5	210.6	226.5	243.1	259.4	274.2
142.5°	145.9	154.9	164.5	174.6	185.3	196.8	209.2	222.9	236.9	250.9	263.8
145°	150.6	158.7	167.9	176.7	186.2	196.5	207.1	218.1	229.0	240.0	249.5
147.5°	154.8	161.9	170.0	178.0	186.6	195.6	204.9	213.5	222.4	230.9	238.1
150°	157.6	163.6	171.4	178.8	186.6	194.7	203.2	211.0	218.8	225.5	231.8
152.5°	160.2	165.6	172.8	179.4	186.3	193.6	201.2	208.2	215.1	221.2	226.2
155°	163.3	168.2	174.2	179.9	185.5	191.6	197.9	203.9	209.6	214.5	218.4
157.5°	166.5	170.3	175.4	180.2	184.6	189.4	194.8	199.7	204.3	208.2	211.2
160°	168.2	171.4	176.0	180.2	183.8	188.0	192.3	196.9	200.4	203.9	206.4
162.5°	169.9	172.5	176.6	180.0	182.9	186.3	190.0	193.7	197.0	200.0	202.2
165°	171.8	173.9	176.7	179.5	181.7	183.8	186.6	189.4	191.9	194.0	195.8
167.5°	173.0	174.4	176.7	178.7	179.7	181.3	183.3	185.3	187.0	188.6	189.9
170°	173.9	174.9	176.7	178.1	178.8	179.9	181.3	183.1	184.1	185.2	185.9
172.5°	174.4	174.9	176.4	177.6	177.7	178.2	179.3	180.5	181.6	182.4	182.8
175°	174.9	174.9	176.0	176.7	176.4	176.4	176.7	177.8	177.8	178.5	178.5
177.5°	175.0	175.0	175.6	175.9	175.3	175.3	175.6	175.9	176.1	176.1	176.1
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1515.1	1518.9	1515.7	1520.0	1515.7	1518.9	1515.1	1518.4	1523.2	1520.0	1527.5
5°	1396.5	1390.4	1394.4	1391.7	1394.4	1390.4	1396.5	1399.8	1407.9	1410.6	1416.0
7.5°	1286.9	1281.1	1274.4	1271.3	1274.4	1281.1	1286.9	1288.9	1295.8	1305.9	1313.6
10°	1218.3	1210.9	1210.2	1205.5	1210.2	1210.9	1218.3	1225.7	1230.4	1243.3	1252.0
12.5°	1168.1	1161.2	1153.5	1151.5	1153.5	1161.2	1168.1	1174.4	1175.9	1190.3	1196.4
15°	1096.8	1091.4	1086.7	1090.7	1086.7	1091.4	1096.8	1100.8	1108.3	1118.4	1125.1
17.5°	1037.5	1033.1	1032.3	1027.3	1032.3	1033.1	1037.5	1039.8	1052.0	1058.6	1070.2
20°	1000.3	996.9	998.3	989.5	998.3	996.9	1000.3	1006.4	1018.5	1021.9	1034.0
22.5°	970.6	964.0	963.2	961.4	963.2	964.0	970.6	976.1	978.5	988.9	997.3
25°	924.0	920.6	917.3	920.6	917.3	920.6	924.0	930.1	932.8	940.2	948.3
27.5°	883.4	879.3	878.4	878.8	878.4	879.3	883.4	882.8	890.1	896.1	902.0
30°	858.5	851.8	852.5	851.8	852.5	851.8	858.5	858.5	862.6	868.0	873.4
32.5°	831.5	826.9	826.0	824.8	826.0	826.9	831.5	830.5	835.6	842.1	848.0
35°	791.7	791.7	788.3	788.3	788.3	791.7	791.7	793.7	799.1	799.1	805.9
37.5°	754.3	753.6	751.6	751.9	751.6	753.6	754.3	755.9	757.8	760.7	765.0
40°	726.2	725.6	723.5	719.5	723.5	725.6	726.2	728.9	730.3	733.7	736.4
42.5°	699.2	697.0	696.0	694.7	696.0	697.0	699.2	700.9	701.7	706.1	711.5
45°	656.7	656.7	655.4	654.7	655.4	656.7	656.7	656.7	657.4	662.8	665.5
47.5°	615.4	616.6	619.2	618.8	619.2	616.6	615.4	614.3	614.6	617.3	620.4
50°	590.6	591.3	593.3	594.0	593.3	591.3	590.6	587.9	586.5	586.5	588.6
52.5°	563.0	567.0	569.5	569.1	569.5	567.0	563.0	560.9	558.5	555.2	558.3
55°	524.4	529.2	533.9	534.6	533.9	529.2	524.4	518.4	515.7	510.3	512.3
57.5°	486.2	492.8	497.8	499.5	497.8	492.8	486.2	478.9	470.2	467.6	463.8
60°	460.3	469.1	475.2	477.9	475.2	469.1	460.3	453.6	442.1	434.7	432.0
62.5°	435.5	445.3	451.4	451.9	451.4	445.3	435.5	424.9	413.5	405.0	399.6
65°	394.8	405.0	410.4	414.4	410.4	405.0	394.8	383.4	370.5	359.1	353.0
67.5°	351.1	361.2	367.2	370.4	367.2	361.2	351.1	336.9	325.2	312.0	304.8
70°	319.3	329.4	337.5	340.2	337.5	329.4	319.3	302.4	292.3	280.1	274.0
72.5°	287.9	297.0	303.5	306.7	303.5	297.0	287.9	272.1	260.4	248.2	240.0
75°	233.5	245.7	251.8	255.1	251.8	245.7	233.5	224.8	211.3	198.4	191.7
77.5°	180.1	191.1	194.8	196.5	194.8	191.1	180.1	169.8	159.6	150.2	143.6
80°	144.4	151.2	155.9	156.6	155.9	151.2	144.4	136.3	128.2	119.5	113.4
82.5°	111.0	116.6	118.1	119.9	118.1	116.6	111.0	103.9	96.9	90.3	85.3
85°	60.7	63.4	64.1	63.4	64.1	63.4	60.7	56.0	52.6	49.3	47.2
87.5°	21.5	21.0	21.1	22.1	21.1	21.0	21.5	20.5	20.9	19.7	18.6
90°	7.8	7.8	8.1	8.1	8.1	7.8	7.8	7.8	7.1	6.7	6.4
92.5°	24.5	23.6	23.1	22.5	23.1	23.6	24.5	29.0	34.2	45.4	62.6
95°	102.1	91.5	88.7	83.1	88.7	91.5	102.1	127.2	156.9	200.4	254.1
97.5°	235.3	215.5	205.3	200.7	205.3	215.5	235.3	257.1	298.4	340.8	378.4
100°	319.8	294.4	281.3	275.7	281.3	294.4	319.8	344.2	381.0	417.4	434.7
102.5°	395.9	377.8	363.6	359.4	363.6	377.8	395.9	422.0	446.9	464.3	453.6
105°	491.2	479.6	472.5	468.3	472.5	479.6	491.2	502.6	506.4	490.9	442.5
107.5°	531.3	531.3	528.9	526.1	528.9	531.3	531.3	525.6	507.1	467.2	402.6
110°	536.1	542.8	545.3	545.3	545.3	542.8	536.1	520.2	490.2	440.4	373.2



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	522.8	534.4	540.5	543.1	540.5	534.4	522.8	499.6	464.2	413.8	350.0
115°	490.2	507.1	517.0	521.6	517.0	507.1	490.2	462.6	424.1	375.7	320.9
117.5°	453.9	471.5	481.3	484.1	481.3	471.5	453.9	426.4	391.0	349.3	302.1
120°	430.5	447.4	457.0	459.8	457.0	447.4	430.5	404.3	373.2	334.3	291.9
122.5°	410.7	426.2	435.8	438.3	435.8	426.2	410.7	387.3	358.2	323.6	284.3
125°	385.2	399.7	407.5	411.0	407.5	399.7	385.2	365.4	340.0	309.2	273.2
127.5°	366.0	378.8	386.1	387.7	386.1	378.8	366.0	348.0	324.2	295.5	261.9
130°	354.1	365.8	372.9	375.0	372.9	365.8	354.1	336.5	313.5	285.9	254.8
132.5°	341.7	353.3	359.8	362.2	359.8	353.3	341.7	324.0	301.9	276.9	247.7
135°	321.3	332.9	339.3	341.4	339.3	332.9	321.3	305.7	285.6	262.9	238.6
137.5°	300.3	310.9	316.8	319.1	316.8	310.9	300.3	286.4	269.3	250.5	230.8
140°	287.3	296.5	301.8	303.6	301.8	296.5	287.3	274.2	259.4	243.1	226.5
142.5°	274.9	282.7	287.7	289.2	287.7	282.7	274.9	263.8	250.9	236.9	222.9
145°	258.0	264.0	267.9	269.3	267.9	264.0	258.0	249.5	240.0	229.0	218.1
147.5°	244.8	249.6	251.8	252.5	251.8	249.6	244.8	238.1	230.9	222.4	213.5
150°	237.1	241.4	242.8	243.1	242.8	241.4	237.1	231.8	225.5	218.8	211.0
152.5°	230.6	234.0	235.4	235.8	235.4	234.0	230.6	226.2	221.2	215.1	208.2
155°	221.9	224.4	225.5	225.8	225.5	224.4	221.9	218.4	214.5	209.6	203.9
157.5°	214.0	216.0	217.0	216.9	217.0	216.0	214.0	211.2	208.2	204.3	199.7
160°	208.9	210.6	211.3	211.0	211.3	210.6	208.9	206.4	203.9	200.4	196.9
162.5°	204.1	205.5	205.7	205.6	205.7	205.5	204.1	202.2	200.0	197.0	193.7
165°	197.2	197.9	197.9	197.9	197.9	197.9	197.2	195.8	194.0	191.9	189.4
167.5°	190.6	191.2	190.9	190.8	190.9	191.2	190.6	189.9	188.6	187.0	185.3
170°	186.6	187.0	187.0	186.6	187.0	187.0	186.6	185.9	185.2	184.1	183.1
172.5°	182.9	183.6	183.0	182.6	183.0	183.6	182.9	182.8	182.4	181.6	180.5
175°	178.5	178.8	178.1	177.8	178.1	178.8	178.5	178.5	178.5	177.8	177.8
177.5°	175.9	176.1	175.3	175.3	175.3	176.1	175.9	176.1	176.1	176.1	175.9
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1520.5	1527.0	1535.1	1541.0	1551.8	1556.7	1562.6	1567.5	1576.1	1584.2	1594.0
5°	1418.1	1429.5	1445.1	1461.9	1481.5	1495.0	1513.9	1525.4	1548.3	1569.3	1589.5
7.5°	1325.2	1339.2	1361.2	1382.8	1408.5	1431.7	1455.3	1481.5	1510.8	1545.4	1574.0
10°	1261.5	1280.4	1304.0	1331.0	1362.1	1389.0	1420.8	1449.1	1484.9	1525.4	1563.2
12.5°	1210.7	1226.9	1253.2	1279.2	1312.4	1345.3	1378.1	1415.6	1457.4	1502.2	1549.7
15°	1140.7	1154.2	1175.8	1211.5	1245.3	1277.7	1327.0	1362.1	1414.7	1464.6	1522.0
17.5°	1080.9	1097.6	1115.8	1146.5	1181.4	1221.9	1265.9	1309.9	1360.7	1424.0	1488.7
20°	1044.1	1057.6	1078.6	1102.2	1139.3	1179.8	1221.7	1266.2	1328.3	1393.8	1463.3
22.5°	1004.2	1018.8	1042.4	1068.2	1099.4	1138.2	1184.4	1233.3	1298.1	1362.5	1437.9
25°	957.1	967.2	988.8	1011.8	1042.8	1075.9	1123.8	1177.8	1241.9	1315.5	1392.4
27.5°	912.7	921.6	941.3	961.3	989.3	1028.6	1071.4	1126.0	1186.4	1260.9	1346.3
30°	880.8	890.3	907.8	929.4	956.4	990.8	1034.7	1086.0	1150.8	1223.7	1312.8
32.5°	853.3	861.6	874.9	896.5	922.9	956.3	996.9	1049.3	1114.1	1188.0	1275.5
35°	810.6	820.1	830.2	847.1	870.0	902.4	947.0	996.2	1058.3	1129.9	1210.2
37.5°	768.2	778.5	787.5	802.7	823.6	852.2	890.7	942.0	998.1	1067.1	1144.2
40°	741.8	749.9	757.3	773.5	794.4	821.4	857.2	903.1	962.5	1026.6	1090.7
42.5°	715.3	722.9	729.2	743.3	762.6	788.5	822.6	867.4	922.5	982.3	1038.9
45°	673.6	678.3	685.7	697.9	713.4	737.0	770.1	809.9	856.5	913.2	955.7
47.5°	628.5	635.9	642.0	652.7	665.4	688.6	720.3	754.2	796.4	838.6	868.5
50°	594.0	601.4	610.2	620.3	632.4	654.0	683.1	717.5	753.2	785.6	811.3
52.5°	561.6	568.4	577.8	587.3	602.2	620.5	645.3	675.9	711.1	734.3	755.7
55°	513.6	517.0	527.8	537.3	551.4	564.9	589.9	616.9	638.5	656.1	673.6
57.5°	464.6	469.2	475.4	483.9	498.0	513.8	531.3	555.2	567.9	576.9	590.6
60°	433.3	434.7	438.7	448.8	459.6	473.8	494.1	510.9	520.4	527.8	539.3
62.5°	398.8	399.0	405.8	413.2	421.3	436.6	453.0	466.7	474.5	478.1	489.1
65°	350.3	348.9	353.0	359.1	368.5	378.6	392.8	405.0	404.3	408.3	415.1
67.5°	300.8	299.4	299.4	305.2	312.9	322.0	331.7	338.7	338.8	344.2	347.6
70°	267.3	263.2	265.9	270.7	274.0	281.5	292.3	295.0	295.6	298.3	301.7
72.5°	232.7	231.4	233.5	235.6	237.9	243.7	252.8	254.5	254.6	256.2	261.7
75°	184.9	183.6	182.2	184.3	187.0	191.0	194.4	197.1	196.4	197.1	201.1
77.5°	138.6	134.9	134.2	135.3	135.9	138.4	141.9	141.6	142.3	142.1	146.7
80°	110.0	104.6	103.9	103.9	104.6	106.0	107.3	108.7	106.6	108.7	110.0
82.5°	80.9	77.6	77.5	76.9	77.1	77.3	78.2	79.0	78.6	79.5	80.3
85°	44.5	43.2	41.2	42.5	41.8	39.8	41.2	39.1	38.5	39.1	39.8
87.5°	16.3	16.8	15.6	15.5	14.8	15.3	14.1	13.4	12.7	13.1	14.6
90°	6.0	5.7	4.9	4.6	3.9	3.5	2.8	2.1	1.4	0.7	0.4
92.5°	92.2	113.9	115.8	80.6	48.3	29.0	18.7	12.6	8.2	5.2	4.3
95°	306.4	313.1	255.5	158.0	80.2	42.4	26.5	18.7	14.8	12.0	11.7
97.5°	387.7	334.4	228.2	126.1	69.1	44.1	32.7	25.7	21.8	19.8	19.4
100°	407.5	319.1	203.6	114.5	68.6	48.1	37.5	30.7	26.9	25.4	24.7
102.5°	395.6	292.3	184.9	109.7	71.1	52.9	42.6	36.4	32.2	31.1	30.7
105°	357.7	256.2	166.8	107.8	76.3	60.8	50.9	45.2	41.7	39.9	39.9
107.5°	318.9	231.4	159.2	111.0	84.1	69.1	60.2	54.3	51.4	49.7	49.0
110°	296.9	219.8	156.9	114.2	89.8	75.3	66.1	60.8	57.6	56.2	55.5



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.5	213.0	156.9	118.1	95.1	81.2	72.3	67.0	63.8	62.7	62.0
115°	262.6	205.7	158.0	124.0	103.6	90.5	81.6	76.3	73.2	72.1	71.4
117.5°	251.9	202.1	160.3	130.8	112.2	99.8	91.3	85.2	82.1	80.9	79.9
120°	246.0	200.4	162.6	135.4	118.4	106.0	97.2	91.2	88.0	86.6	85.5
122.5°	240.9	199.0	164.5	140.4	124.3	112.0	103.1	96.6	93.4	92.2	91.5
125°	234.0	197.2	167.9	147.4	132.2	120.5	111.3	104.6	101.4	99.7	99.0
127.5°	227.6	196.4	171.6	153.7	139.7	128.5	119.3	112.2	108.1	105.9	104.8
130°	223.4	195.8	173.9	158.0	144.5	133.6	124.4	117.0	112.4	109.6	108.5
132.5°	220.0	195.8	176.4	161.7	149.1	138.1	128.9	121.2	116.1	112.7	111.3
135°	215.9	195.8	179.9	166.8	155.1	144.2	134.7	127.2	121.6	117.3	115.9
137.5°	212.3	196.2	183.1	170.6	159.5	149.5	139.7	132.4	126.7	122.8	121.7
140°	210.6	196.5	184.5	173.2	162.6	152.3	142.8	136.1	130.4	126.2	125.1
142.5°	209.2	196.8	185.3	174.6	164.5	154.9	145.9	139.5	133.8	129.8	129.1
145°	207.1	196.5	186.2	176.7	167.9	158.7	150.6	144.2	139.2	135.7	135.0
147.5°	204.9	195.6	186.6	178.0	170.0	161.9	154.8	149.3	144.7	141.6	141.2
150°	203.2	194.7	186.6	178.8	171.4	163.6	157.6	152.7	148.1	145.6	144.9
152.5°	201.2	193.6	186.3	179.4	172.8	165.6	160.2	155.5	151.5	149.3	148.9
155°	197.9	191.6	185.5	179.9	174.2	168.2	163.3	159.7	156.2	154.1	154.1
157.5°	194.8	189.4	184.6	180.2	175.4	170.3	166.5	163.4	160.4	158.7	158.8
160°	192.3	188.0	183.8	180.2	176.0	171.4	168.2	165.4	162.9	161.5	161.9
162.5°	190.0	186.3	182.9	180.0	176.6	172.5	169.9	167.7	165.5	164.1	164.4
165°	186.6	183.8	181.7	179.5	176.7	173.9	171.8	170.3	168.6	167.5	168.2
167.5°	183.3	181.3	179.7	178.7	176.7	174.4	173.0	172.0	171.1	170.4	170.8
170°	181.3	179.9	178.8	178.1	176.7	174.9	173.9	173.2	172.5	172.1	172.5
172.5°	179.3	178.2	177.7	177.6	176.4	174.9	174.4	174.0	173.3	173.0	173.6
175°	176.7	176.4	176.4	176.7	176.0	174.9	174.9	174.9	174.6	174.2	174.9
177.5°	175.6	175.3	175.3	175.9	175.6	175.0	175.0	175.3	175.0	175.0	175.6
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1598.8	1606.4	1611.2	1620.4	1628.0	1632.3	1636.1	1639.3	1643.1	1646.3	1655.5
5°	1609.1	1626.6	1641.5	1664.4	1685.4	1701.6	1719.1	1734.6	1747.4	1765.7	1779.8
7.5°	1604.6	1635.8	1668.5	1704.0	1740.3	1774.0	1805.1	1834.1	1860.4	1892.3	1920.2
10°	1600.3	1642.8	1684.7	1732.6	1781.9	1823.7	1862.9	1902.7	1931.7	1972.2	2006.6
12.5°	1597.1	1647.1	1697.6	1755.3	1809.4	1868.5	1920.6	1949.7	1993.8	2026.2	2067.1
15°	1583.4	1649.6	1719.1	1783.9	1860.8	1915.5	1961.4	2018.1	2059.3	2100.4	2145.0
17.5°	1559.0	1633.9	1711.7	1796.6	1870.4	1929.1	1988.3	2042.9	2092.1	2147.3	2202.8
20°	1547.7	1622.6	1711.7	1798.7	1871.0	1932.4	1993.1	2053.2	2107.2	2178.1	2242.2
22.5°	1523.9	1614.5	1696.6	1781.5	1855.8	1922.7	1991.5	2059.7	2131.5	2211.5	2291.9
25°	1481.5	1573.3	1660.4	1744.1	1819.0	1902.7	1976.3	2067.4	2159.2	2265.1	2365.0
27.5°	1437.5	1525.4	1605.2	1686.0	1773.4	1868.1	1963.6	2067.0	2187.1	2320.9	2461.8
30°	1401.9	1484.9	1562.5	1645.5	1736.6	1843.3	1947.9	2070.7	2209.8	2360.3	2527.7
32.5°	1360.3	1436.8	1512.3	1600.2	1699.4	1812.0	1933.9	2068.6	2235.7	2406.7	2579.0
35°	1289.2	1353.3	1430.9	1524.7	1636.8	1765.7	1906.7	2066.0	2257.7	2454.1	2599.2
37.5°	1204.8	1264.5	1346.3	1449.1	1566.6	1704.9	1872.3	2061.3	2264.9	2421.5	2468.3
40°	1148.1	1203.4	1288.5	1395.1	1515.3	1661.7	1845.3	2045.1	2242.2	2342.1	2303.6
42.5°	1087.6	1145.7	1228.5	1334.1	1463.4	1622.9	1811.3	2011.1	2176.3	2214.1	2081.1
45°	992.2	1052.2	1133.9	1240.6	1379.6	1552.4	1748.8	1930.4	2025.5	1957.4	1751.5
47.5°	903.5	959.8	1035.5	1145.5	1289.0	1467.7	1656.9	1801.7	1809.3	1646.6	1426.7
50°	843.0	895.0	971.3	1081.3	1223.7	1404.6	1575.3	1689.4	1638.1	1453.8	1242.6
52.5°	783.6	834.5	909.7	1018.6	1159.4	1325.2	1484.1	1564.1	1467.5	1278.4	1097.9
55°	697.9	742.4	816.0	916.6	1050.2	1204.1	1339.1	1366.8	1241.2	1054.9	908.5
57.5°	614.2	655.8	722.7	815.3	937.5	1073.8	1179.4	1173.5	1040.8	880.9	764.7
60°	557.5	598.0	657.4	747.8	859.2	976.7	1067.1	1045.5	913.9	776.2	678.3
62.5°	506.8	542.9	599.1	678.2	779.8	888.6	962.9	931.0	802.1	681.7	604.4
65°	432.0	462.3	510.3	577.8	662.1	751.9	809.3	768.1	658.1	564.3	502.2
67.5°	360.6	384.9	425.1	478.9	550.9	623.0	657.9	616.5	528.5	460.0	414.0
70°	315.2	336.8	367.8	415.8	478.5	539.3	565.6	528.5	452.9	394.2	361.1
72.5°	269.8	287.7	314.9	358.0	408.3	461.0	484.1	448.6	386.5	336.9	306.0
75°	208.6	220.7	239.6	269.3	309.1	351.0	363.8	332.8	292.9	255.8	235.6
77.5°	149.3	159.6	173.9	192.6	220.8	247.4	258.6	240.7	209.9	186.4	169.8
80°	114.7	120.1	132.3	147.8	170.1	187.0	194.4	182.9	161.3	143.8	130.9
82.5°	81.8	87.2	94.5	107.3	121.5	133.0	140.9	133.2	117.6	103.8	96.4
85°	39.8	43.2	47.2	52.6	63.4	70.2	69.5	64.8	58.7	53.3	49.3
87.5°	14.2	14.9	16.6	19.5	21.2	23.5	24.7	23.7	21.6	20.1	18.6
90°	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.7	6.0	6.4
92.5°	5.2	8.2	12.6	18.7	29.0	48.3	80.6	115.8	113.9	92.2	62.6
95°	12.0	14.8	18.7	26.5	42.4	80.2	158.0	255.5	313.1	306.4	254.1
97.5°	19.8	21.8	25.7	32.7	44.1	69.1	126.1	228.2	334.4	387.7	378.4
100°	25.4	26.9	30.7	37.5	48.1	68.6	114.5	203.6	319.1	407.5	434.7
102.5°	31.1	32.2	36.4	42.6	52.9	71.1	109.7	184.9	292.3	395.6	453.6
105°	39.9	41.7	45.2	50.9	60.8	76.3	107.8	166.8	256.2	357.7	442.5
107.5°	49.7	51.4	54.3	60.2	69.1	84.1	111.0	159.2	231.4	318.9	402.6
110°	56.2	57.6	60.8	66.1	75.3	89.8	114.2	156.9	219.8	296.9	373.2



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	62.7	63.8	67.0	72.3	81.2	95.1	118.1	156.9	213.0	280.5	350.0
115°	72.1	73.2	76.3	81.6	90.5	103.6	124.0	158.0	205.7	262.6	320.9
117.5°	80.9	82.1	85.2	91.3	99.8	112.2	130.8	160.3	202.1	251.9	302.1
120°	86.6	88.0	91.2	97.2	106.0	118.4	135.4	162.6	200.4	246.0	291.9
122.5°	92.2	93.4	96.6	103.1	112.0	124.3	140.4	164.5	199.0	240.9	284.3
125°	99.7	101.4	104.6	111.3	120.5	132.2	147.4	167.9	197.2	234.0	273.2
127.5°	105.9	108.1	112.2	119.3	128.5	139.7	153.7	171.6	196.4	227.6	261.9
130°	109.6	112.4	117.0	124.4	133.6	144.5	158.0	173.9	195.8	223.4	254.8
132.5°	112.7	116.1	121.2	128.9	138.1	149.1	161.7	176.4	195.8	220.0	247.7
135°	117.3	121.6	127.2	134.7	144.2	155.1	166.8	179.9	195.8	215.9	238.6
137.5°	122.8	126.7	132.4	139.7	149.5	159.5	170.6	183.1	196.2	212.3	230.8
140°	126.2	130.4	136.1	142.8	152.3	162.6	173.2	184.5	196.5	210.6	226.5
142.5°	129.8	133.8	139.5	145.9	154.9	164.5	174.6	185.3	196.8	209.2	222.9
145°	135.7	139.2	144.2	150.6	158.7	167.9	176.7	186.2	196.5	207.1	218.1
147.5°	141.6	144.7	149.3	154.8	161.9	170.0	178.0	186.6	195.6	204.9	213.5
150°	145.6	148.1	152.7	157.6	163.6	171.4	178.8	186.6	194.7	203.2	211.0
152.5°	149.3	151.5	155.5	160.2	165.6	172.8	179.4	186.3	193.6	201.2	208.2
155°	154.1	156.2	159.7	163.3	168.2	174.2	179.9	185.5	191.6	197.9	203.9
157.5°	158.7	160.4	163.4	166.5	170.3	175.4	180.2	184.6	189.4	194.8	199.7
160°	161.5	162.9	165.4	168.2	171.4	176.0	180.2	183.8	188.0	192.3	196.9
162.5°	164.1	165.5	167.7	169.9	172.5	176.6	180.0	182.9	186.3	190.0	193.7
165°	167.5	168.6	170.3	171.8	173.9	176.7	179.5	181.7	183.8	186.6	189.4
167.5°	170.4	171.1	172.0	173.0	174.4	176.7	178.7	179.7	181.3	183.3	185.3
170°	172.1	172.5	173.2	173.9	174.9	176.7	178.1	178.8	179.9	181.3	183.1
172.5°	173.0	173.3	174.0	174.4	174.9	176.4	177.6	177.7	178.2	179.3	180.5
175°	174.2	174.6	174.9	174.9	174.9	176.0	176.7	176.4	176.4	176.7	177.8
177.5°	175.0	175.0	175.3	175.0	175.0	175.6	175.9	175.3	175.3	175.6	175.9
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1663.1	1667.4	1676.6	1673.3	1677.7	1679.8	1682.0
5°	1797.4	1819.0	1828.4	1827.1	1841.3	1837.9	1834.5
7.5°	1949.1	1971.8	1984.5	2000.3	2009.5	2010.1	2018.1
10°	2035.0	2064.7	2076.8	2093.7	2104.5	2110.6	2109.9
12.5°	2100.9	2124.1	2151.3	2159.6	2174.2	2181.8	2179.0
15°	2180.1	2217.2	2245.6	2259.7	2278.0	2283.4	2290.8
17.5°	2250.8	2300.6	2333.7	2377.7	2394.3	2404.4	2398.5
20°	2304.3	2369.8	2402.8	2455.5	2484.5	2500.0	2494.6
22.5°	2367.5	2438.3	2499.5	2545.1	2589.2	2610.2	2614.5
25°	2475.7	2572.9	2662.7	2722.8	2777.4	2790.2	2818.6
27.5°	2596.7	2711.3	2807.3	2870.4	2908.5	2922.8	2931.7
30°	2672.8	2786.9	2859.1	2899.6	2911.7	2910.4	2909.0
32.5°	2710.1	2781.5	2795.4	2784.0	2756.2	2732.7	2708.2
35°	2657.3	2604.0	2524.3	2421.7	2346.1	2269.9	2262.4
37.5°	2389.9	2219.4	2086.8	1938.7	1853.3	1800.5	1764.1
40°	2138.2	1944.5	1783.9	1659.0	1572.0	1537.5	1503.8
42.5°	1865.0	1680.0	1537.7	1433.3	1367.9	1329.7	1302.9
45°	1515.3	1351.9	1240.6	1165.0	1113.0	1083.3	1066.4
47.5°	1241.6	1120.8	1026.2	971.7	935.8	912.7	912.8
50°	1094.8	979.4	916.6	873.4	842.3	824.1	827.5
52.5°	964.6	878.4	824.8	788.6	765.7	754.5	754.1
55°	806.6	744.5	709.4	683.1	667.5	654.7	657.4
57.5°	689.9	637.6	614.1	592.2	581.4	576.3	568.8
60°	617.6	577.1	556.8	539.3	528.5	524.4	517.0
62.5°	553.3	521.5	501.8	487.4	477.7	476.4	470.6
65°	465.0	440.7	423.2	416.4	406.3	403.6	403.6
67.5°	383.4	366.0	352.3	346.1	341.7	342.3	339.1
70°	332.1	317.9	309.1	302.4	299.0	299.7	297.0
72.5°	290.5	274.7	267.0	263.0	258.5	260.3	259.2
75°	220.0	211.9	207.9	203.8	201.1	199.8	198.4
77.5°	161.6	154.4	151.3	149.0	149.4	146.2	148.8
80°	124.9	118.8	116.8	113.4	112.7	112.7	112.0
82.5°	91.4	88.0	86.5	83.7	82.5	83.6	81.8
85°	47.2	44.5	43.9	43.9	42.5	41.2	44.5
87.5°	18.6	16.5	16.7	16.1	16.1	15.7	14.6
90°	6.7	7.1	7.8	7.8	7.8	8.1	8.1
92.5°	45.4	34.2	29.0	24.5	23.6	23.1	22.5
95°	200.4	156.9	127.2	102.1	91.5	88.7	83.1
97.5°	340.8	298.4	257.1	235.3	215.5	205.3	200.7
100°	417.4	381.0	344.2	319.8	294.4	281.3	275.7
102.5°	464.3	446.9	422.0	395.9	377.8	363.6	359.4
105°	490.9	506.4	502.6	491.2	479.6	472.5	468.3
107.5°	467.2	507.1	525.6	531.3	531.3	528.9	526.1
110°	440.4	490.2	520.2	536.1	542.8	545.3	545.3



TEST NUMBER: P333252

CATALOG NUMBER: S125DIP-S1090D365U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	413.8	464.2	499.6	522.8	534.4	540.5	543.1
115°	375.7	424.1	462.6	490.2	507.1	517.0	521.6
117.5°	349.3	391.0	426.4	453.9	471.5	481.3	484.1
120°	334.3	373.2	404.3	430.5	447.4	457.0	459.8
122.5°	323.6	358.2	387.3	410.7	426.2	435.8	438.3
125°	309.2	340.0	365.4	385.2	399.7	407.5	411.0
127.5°	295.5	324.2	348.0	366.0	378.8	386.1	387.7
130°	285.9	313.5	336.5	354.1	365.8	372.9	375.0
132.5°	276.9	301.9	324.0	341.7	353.3	359.8	362.2
135°	262.9	285.6	305.7	321.3	332.9	339.3	341.4
137.5°	250.5	269.3	286.4	300.3	310.9	316.8	319.1
140°	243.1	259.4	274.2	287.3	296.5	301.8	303.6
142.5°	236.9	250.9	263.8	274.9	282.7	287.7	289.2
145°	229.0	240.0	249.5	258.0	264.0	267.9	269.3
147.5°	222.4	230.9	238.1	244.8	249.6	251.8	252.5
150°	218.8	225.5	231.8	237.1	241.4	242.8	243.1
152.5°	215.1	221.2	226.2	230.6	234.0	235.4	235.8
155°	209.6	214.5	218.4	221.9	224.4	225.5	225.8
157.5°	204.3	208.2	211.2	214.0	216.0	217.0	216.9
160°	200.4	203.9	206.4	208.9	210.6	211.3	211.0
162.5°	197.0	200.0	202.2	204.1	205.5	205.7	205.6
165°	191.9	194.0	195.8	197.2	197.9	197.9	197.9
167.5°	187.0	188.6	189.9	190.6	191.2	190.9	190.8
170°	184.1	185.2	185.9	186.6	187.0	187.0	186.6
172.5°	181.6	182.4	182.8	182.9	183.6	183.0	182.6
175°	177.8	178.5	178.5	178.5	178.8	178.1	177.8
177.5°	176.1	176.1	176.1	175.9	176.1	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3

(END OF REPORT)