

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332870-940

Luminaire Tested: **S124RDIP-S350D365U940-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332870-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-S350D365U940-4F0-1E-UDD-F4  
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2441.1 lumens  
Efficiency: N/A  
Efficacy: 120.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332870-940

CATALOG NUMBER: S124RDIP-S350D365U940-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P332870-940

CATALOG NUMBER: S124RDIP-S350D365U940-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	99	94	91	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	58	55	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4451	4451	4451
5°	4460	4406	4433
10°	4432	4353	4353
15°	4381	4262	4229
20°	4312	4141	4064
25°	4222	4000	3899
30°	4135	3852	3691
35°	4039	3698	3482
40°	3923	3523	3256
45°	3817	3350	3027
50°	3695	3149	2783
55°	3564	2940	2519
60°	3421	2713	2249
65°	3289	2428	1983
70°	3099	2110	1683
75°	2857	1753	1369
80°	2492	1334	1255
85°	2112	1213	1130



TEST NUMBER: P332870-940

CATALOG NUMBER: S124RDIP-S350D365U940-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.8	2.1
10°-20°	144.4	5.9
20°-30°	208.5	8.5
30°-40°	236.4	9.7
40°-50°	228.2	9.3
50°-60°	189.8	7.8
60°-70°	131.1	5.4
70°-80°	66.4	2.7
80°-90°	17.9	0.7
90°-100°	115.9	4.7
100°-110°	241.1	9.9
110°-120°	216.0	8.8
120°-130°	181.7	7.4
130°-140°	151.5	6.2
140°-150°	115.7	4.7
150°-160°	81.3	3.3
160°-170°	47.8	2.0
170°-180°	15.6	0.6
0°-30°	404.7	16.6
0°-40°	641.0	26.3
0°-60°	1059.1	43.4
0°-90°	1274.5	52.2
90°-120°	573.0	23.5
90°-150°	1021.9	41.9
90°-180°	1167.0	47.8
0°-180°	2441.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	548	544	548	547	52
15°	524	520	510	509	506	148
25°	474	466	449	442	438	218
35°	410	396	375	361	353	256
45°	334	318	293	273	265	258
55°	253	236	209	188	179	226
65°	172	154	127	110	104	170
75°	92	76	56	47	44	97
85°	23	15	13	12	12	26
90°	0	2	6	6	7	2
95°	10	33	257	127	77	12
105°	37	53	207	445	443	39
115°	65	81	184	354	426	64
125°	90	108	183	301	340	80
135°	108	128	182	268	304	83
145°	124	142	181	226	248	78
155°	141	152	176	199	208	65
165°	154	158	169	178	181	43
175°	160	160	162	164	163	15
180°	160	160	160	160	160	



TEST NUMBER: P332870-940

CATALOG NUMBER: S124RDIP-S350D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	552.6	552.2	552.0	551.7	551.3	550.8	550.0	549.2	548.3	547.5	548.3
5°	550.4	550.0	549.7	549.3	548.8	548.1	547.0	545.9	544.7	543.7	544.6
7.5°	545.4	545.0	544.7	544.2	543.9	542.9	541.4	539.9	538.5	537.1	537.6
10°	540.6	540.2	539.8	539.3	538.8	537.7	536.0	534.3	532.6	531.0	531.4
12.5°	534.6	534.0	533.5	533.0	532.4	531.2	529.1	527.2	525.2	523.2	523.4
15°	524.2	523.3	522.5	521.7	520.8	519.2	516.9	514.5	512.2	509.9	509.7
17.5°	511.7	510.4	509.2	508.0	506.8	504.7	501.9	499.1	496.3	493.5	492.9
20°	501.9	500.6	499.4	498.2	497.0	494.8	491.6	488.4	485.2	482.0	481.3
22.5°	491.1	489.6	488.3	487.0	485.5	483.1	479.7	476.4	473.0	469.5	468.4
25°	474.0	472.3	470.6	469.0	467.3	464.5	460.7	456.8	452.9	449.1	447.5
27.5°	456.1	454.0	451.8	449.8	447.6	444.5	440.4	436.3	432.2	428.1	426.1
30°	443.6	441.2	438.9	436.6	434.3	430.9	426.4	422.0	417.6	413.2	410.9
32.5°	430.4	427.8	425.2	422.5	419.8	416.3	411.7	407.2	402.6	398.1	395.3
35°	409.8	406.8	403.9	400.8	397.8	394.0	389.3	384.6	380.0	375.2	372.0
37.5°	387.8	384.7	381.7	378.5	375.4	371.3	366.0	360.9	355.7	350.5	347.0
40°	372.3	369.2	366.0	363.0	359.9	355.7	350.4	345.0	339.7	334.3	330.4
42.5°	357.4	354.2	350.9	347.7	344.5	340.0	334.5	328.9	323.3	317.7	313.7
45°	334.3	330.8	327.3	323.9	320.4	315.8	310.2	304.6	299.0	293.4	288.7
47.5°	310.4	306.8	303.3	299.6	296.0	291.3	285.5	279.6	273.8	268.0	263.1
50°	294.2	290.5	286.9	283.2	279.6	274.7	268.8	262.7	256.7	250.7	246.0
52.5°	277.7	274.0	270.5	266.9	263.3	258.4	252.3	246.1	240.0	233.8	229.1
55°	253.2	249.5	245.8	242.0	238.3	233.3	227.2	221.1	215.0	208.9	204.0
57.5°	229.1	225.2	221.3	217.4	213.5	208.6	202.5	196.5	190.6	184.5	179.6
60°	211.9	208.1	204.4	200.6	196.9	192.0	186.0	179.9	174.0	168.0	163.1
62.5°	196.4	192.4	188.5	184.7	180.7	175.8	169.6	163.5	157.3	151.1	146.6
65°	172.2	168.2	164.2	160.2	156.0	151.1	145.1	139.0	133.0	127.1	123.1
67.5°	147.1	143.3	139.4	135.5	131.7	127.0	121.4	115.8	110.2	104.7	101.2
70°	131.3	127.3	123.4	119.5	115.5	110.8	105.5	100.1	94.8	89.4	86.4
72.5°	114.4	110.8	107.3	103.7	100.1	95.9	90.8	85.7	80.7	75.6	73.0
75°	91.6	88.1	84.6	81.1	77.7	73.7	69.4	64.9	60.5	56.2	53.9
77.5°	68.5	65.5	62.6	59.7	56.7	53.4	49.8	46.3	42.7	39.1	37.9
80°	53.6	50.9	48.2	45.5	42.7	39.9	37.2	34.3	31.5	28.7	28.4
82.5°	40.8	38.3	35.8	33.3	30.8	28.7	27.1	25.5	23.9	22.3	22.1
85°	22.8	21.0	19.1	17.1	15.2	14.2	13.9	13.6	13.4	13.1	12.9
87.5°	7.8	7.3	7.0	6.4	5.9	5.5	5.8	5.8	5.8	5.9	5.7
90°	0.4	1.0	1.9	2.2	2.5	2.5	4.4	4.4	5.1	5.7	5.4
92.5°	3.6	5.3	8.2	12.0	16.7	23.2	39.2	63.7	87.5	100.0	83.3
95°	10.4	11.3	14.5	18.6	26.1	39.4	66.8	118.5	193.9	256.8	264.1
97.5°	18.6	18.6	21.4	25.1	31.7	42.7	63.8	106.6	181.4	270.5	331.8
100°	24.0	24.0	26.1	30.0	35.9	46.0	64.6	100.2	164.5	253.4	334.0
102.5°	29.0	29.5	31.5	35.0	40.8	50.3	67.1	98.4	153.2	231.9	315.1
105°	36.9	37.8	39.4	43.2	48.9	58.0	73.1	99.2	143.4	206.7	280.8
107.5°	45.6	46.2	47.8	51.8	57.2	66.3	80.1	104.0	141.6	192.6	253.1
110°	51.4	52.0	53.6	57.3	63.0	71.5	85.4	107.5	142.1	187.8	239.2



TEST NUMBER: P332870-940

CATALOG NUMBER: S124RDIP-S350D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	56.9	57.5	59.4	62.9	68.6	77.0	90.4	111.3	143.7	185.6	231.4
115°	64.9	65.9	68.0	71.2	77.2	85.7	98.4	117.3	146.5	184.4	224.1
117.5°	73.2	74.1	76.1	79.5	85.2	94.0	105.9	123.3	149.6	184.0	220.8
120°	78.8	79.5	81.6	85.1	90.4	99.2	111.3	127.6	151.9	184.0	219.0
122.5°	83.8	84.4	86.7	89.9	95.8	104.3	116.3	131.7	154.2	183.8	217.0
125°	90.4	91.7	93.6	97.1	103.1	111.9	123.2	137.7	157.6	183.4	213.7
127.5°	96.3	97.3	99.6	103.5	109.8	118.7	129.7	142.9	160.3	182.7	209.2
130°	99.6	100.9	103.3	108.1	114.0	123.2	133.9	146.2	162.3	182.4	206.4
132.5°	102.9	103.9	107.2	111.6	118.2	126.7	137.5	149.5	164.1	182.3	203.9
135°	107.5	108.7	111.9	117.3	123.9	132.1	142.4	153.8	166.7	181.8	200.1
137.5°	112.1	113.2	116.7	121.8	128.7	136.5	146.2	156.9	168.3	181.8	196.9
140°	115.4	116.3	119.8	125.1	131.7	139.3	148.7	158.8	169.5	181.6	195.1
142.5°	118.9	119.8	123.1	128.1	134.5	141.8	151.1	160.3	170.6	181.6	193.6
145°	123.9	124.8	128.0	132.3	138.4	145.3	153.5	162.0	171.1	180.9	191.0
147.5°	129.5	129.7	132.6	137.1	142.0	148.3	156.0	163.5	171.5	179.8	188.7
150°	133.0	133.3	135.8	139.6	144.4	150.3	157.3	164.2	171.5	179.0	186.9
152.5°	136.3	136.3	138.8	142.4	146.6	152.1	158.3	164.7	170.9	177.7	184.9
155°	140.9	141.2	143.1	146.2	149.7	154.4	159.8	165.1	170.2	175.8	181.8
157.5°	145.3	145.3	147.1	149.5	152.6	156.3	160.9	165.1	169.3	173.9	178.8
160°	148.1	148.1	149.4	151.6	154.1	157.6	161.4	165.1	168.6	172.4	176.5
162.5°	150.6	150.4	151.4	153.4	155.6	158.4	161.8	165.1	167.8	170.9	174.5
165°	153.5	153.5	154.1	155.7	157.3	159.2	162.0	164.5	166.4	168.6	171.1
167.5°	156.3	156.0	156.3	157.5	158.4	159.9	161.9	163.7	164.9	166.3	168.1
170°	157.6	157.3	157.6	158.5	159.2	160.1	161.7	163.3	163.9	164.8	166.1
172.5°	158.8	158.5	158.5	159.3	159.6	160.3	161.4	162.7	162.9	163.3	164.3
175°	160.1	159.8	159.8	160.1	160.4	160.4	161.0	162.0	161.7	161.7	162.3
177.5°	160.7	160.4	160.2	160.4	160.4	160.4	160.7	161.1	160.7	160.7	161.0
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4



TEST NUMBER: P332870-940

CATALOG NUMBER: S124RDIP-S350D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	551.3	551.3	551.3	551.3	551.3	551.3	551.3	551.3
2.5°	549.2	550.0	550.8	551.2	551.1	551.1	551.0	550.9
5°	545.5	546.4	547.4	547.8	547.6	547.4	547.2	547.0
7.5°	538.2	538.9	539.5	539.6	539.3	539.0	538.7	538.4
10°	531.7	532.1	532.4	532.4	532.1	531.7	531.4	531.0
12.5°	523.6	523.9	524.1	524.0	523.4	522.9	522.4	521.8
15°	509.5	509.3	509.1	508.7	508.0	507.4	506.8	506.0
17.5°	492.4	492.0	491.4	490.6	489.6	488.7	487.7	486.7
20°	480.5	479.7	479.0	478.0	476.8	475.5	474.4	473.1
22.5°	467.3	466.1	465.0	464.0	463.0	462.0	461.0	459.9
25°	445.9	444.3	442.7	441.5	440.5	439.5	438.6	437.7
27.5°	424.1	422.1	420.2	418.6	417.1	415.8	414.5	413.1
30°	408.5	406.2	403.9	401.9	400.4	399.0	397.4	395.9
32.5°	392.6	389.9	387.2	385.0	383.6	382.2	380.8	379.3
35°	368.8	365.7	362.5	360.1	358.4	356.7	355.0	353.3
37.5°	343.4	339.8	336.3	333.6	331.9	330.2	328.5	326.8
40°	326.4	322.4	318.5	315.8	314.1	312.4	310.7	309.0
42.5°	309.7	305.7	301.7	298.8	297.0	295.2	293.5	291.8
45°	284.2	279.6	274.9	271.8	270.1	268.4	266.7	265.1
47.5°	258.4	253.6	248.9	245.6	243.7	241.8	240.0	238.2
50°	241.3	236.7	231.9	228.7	226.9	225.2	223.4	221.6
52.5°	224.3	219.5	214.8	211.4	209.6	207.8	205.9	204.0
55°	199.2	194.3	189.4	186.1	184.3	182.5	180.7	179.0
57.5°	174.6	169.7	164.7	161.6	160.2	158.9	157.5	156.1
60°	158.2	153.4	148.5	145.3	143.7	142.3	140.8	139.3
62.5°	142.1	137.6	133.1	130.3	129.0	127.9	126.6	125.5
65°	119.0	114.9	110.9	108.3	107.2	106.1	105.0	103.8
67.5°	97.7	94.3	90.8	88.5	87.2	86.0	84.7	83.5
70°	83.3	80.2	77.1	75.1	74.1	73.2	72.2	71.3
72.5°	70.4	67.7	65.1	63.3	62.4	61.6	60.7	59.8
75°	51.8	49.7	47.5	46.2	45.6	45.0	44.5	43.9
77.5°	36.6	35.4	34.2	33.4	33.3	33.1	32.9	32.7
80°	28.2	27.8	27.6	27.4	27.3	27.2	27.1	27.0
82.5°	21.8	21.7	21.5	21.3	21.2	21.1	21.0	21.0
85°	12.8	12.5	12.3	12.2	12.2	12.2	12.2	12.2
87.5°	5.7	5.7	5.7	5.7	5.8	6.0	6.0	6.1
90°	5.7	6.0	6.3	6.3	6.6	7.0	6.6	6.6
92.5°	61.9	46.5	37.1	30.8	27.0	25.3	24.3	24.3
95°	233.5	184.7	142.4	111.9	96.4	86.7	81.0	76.9
97.5°	345.0	326.9	296.0	263.1	240.5	221.6	212.1	205.5
100°	380.0	386.4	371.0	347.6	320.2	301.0	291.5	289.0
102.5°	378.4	409.6	414.0	404.3	387.5	373.6	363.6	361.6
105°	352.9	407.5	438.7	451.7	452.3	449.7	445.3	443.4
107.5°	317.0	375.1	418.9	447.1	462.6	469.8	473.0	473.8
110°	295.3	349.8	395.6	430.2	452.5	465.8	471.4	474.3





TEST NUMBER: P332870-940

CATALOG NUMBER: S124RDIP-S350D365U940-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	279.4	327.6	370.8	405.5	430.9	446.9	454.9	459.4
115°	263.5	302.2	339.1	369.3	394.2	413.1	423.3	425.8
117.5°	255.7	287.8	316.7	342.4	363.6	379.5	389.7	391.6
120°	252.1	281.4	306.7	329.0	347.0	360.9	369.1	372.6
122.5°	249.1	277.4	300.3	319.9	335.1	347.0	353.9	357.4
125°	244.0	271.0	292.7	310.1	322.7	331.9	337.9	339.7
127.5°	237.6	263.5	285.3	301.7	314.3	322.4	327.5	329.4
130°	232.6	257.5	278.9	295.6	308.5	316.4	321.5	323.3
132.5°	227.3	250.7	271.6	288.3	301.0	309.9	314.7	316.6
135°	220.0	240.5	259.7	275.4	288.0	296.9	301.9	303.8
137.5°	213.4	230.7	246.9	261.1	273.0	281.6	285.8	288.0
140°	209.6	224.4	238.5	251.8	262.9	269.7	274.2	276.7
142.5°	206.1	219.1	231.2	242.7	252.5	259.0	262.9	264.6
145°	201.1	211.8	221.2	230.1	237.9	243.3	246.5	248.0
147.5°	197.0	205.5	213.0	220.0	225.8	230.4	232.7	233.4
150°	194.5	201.7	208.0	213.7	218.7	222.8	224.7	225.0
152.5°	191.7	198.0	203.8	208.4	212.7	216.0	217.1	217.5
155°	187.5	192.5	197.2	201.1	204.2	206.7	207.7	207.7
157.5°	183.1	187.3	191.3	194.3	196.6	198.6	199.1	199.1
160°	180.3	183.7	187.2	189.8	191.6	193.5	193.9	193.9
162.5°	177.5	180.5	183.2	185.5	186.8	188.7	189.0	188.8
165°	173.6	175.6	177.7	179.3	180.6	181.8	181.6	181.2
167.5°	170.0	171.4	173.2	174.1	174.7	175.6	175.5	175.2
170°	167.6	168.6	169.9	170.9	171.5	171.7	171.5	171.5
172.5°	165.7	166.3	167.1	167.8	168.2	168.4	168.2	167.6
175°	162.9	163.3	163.9	163.9	163.9	164.5	163.9	163.3
177.5°	161.1	161.4	161.4	161.7	161.4	161.7	161.1	160.7
180°	160.4	160.4	160.4	160.4	160.4	160.4	160.4	160.4

(END OF REPORT)