

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333265

Luminaire Tested: **S125DIP-S1090D590U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333265
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D590U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6805.3 lumens
Efficiency: N/A
Efficacy: 139.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333265

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333265

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65
1	101	97	93	89	95	91	88	84	80	78	75	71	69	67	62	60	59	55
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	54	52	50	46
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	39
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	39	36	33
5	71	59	50	44	66	55	48	42	50	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	30	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11021	11021	11021
5°	11045	10940	11010
10°	10978	10863	10925
15°	10858	10732	10777
20°	10689	10549	10568
25°	10505	10332	10322
30°	10279	10097	10047
35°	10037	9845	9707
40°	9788	9571	9435
45°	9519	9322	9136
50°	9224	9020	8748
55°	8938	8679	8436
60°	8596	8335	8038
65°	8189	7922	7653
70°	7801	7444	7189
75°	7107	6872	6635
80°	6326	6226	6073
85°	5498	5602	5298



TEST NUMBER: P333265

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.9	2.4
10°-20°	454.5	6.7
20°-30°	671.0	9.9
30°-40°	783.0	11.5
40°-50°	786.4	11.6
50°-60°	690.3	10.1
60°-70°	514.4	7.6
70°-80°	294.1	4.3
80°-90°	87.2	1.3
90°-100°	28.0	0.4
100°-110°	172.4	2.5
110°-120°	312.6	4.6
120°-130°	401.2	5.9
130°-140°	431.5	6.3
140°-150°	405.1	6.0
150°-160°	327.7	4.8
160°-170°	211.9	3.1
170°-180°	73.1	1.1
0°-30°	1286.4	18.9
0°-40°	2069.4	30.4
0°-60°	3546.2	52.1
0°-90°	4441.8	65.3
90°-120°	513.0	7.5
90°-150°	1750.8	25.7
90°-180°	2364.0	34.7
0°-180°	6805.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1706	1706	1706	1706	1706	
5°	1704	1700	1688	1699	1698	162
15°	1624	1619	1605	1612	1612	458
25°	1474	1467	1450	1452	1448	678
35°	1273	1267	1249	1242	1231	796
45°	1042	1036	1021	1005	1000	803
55°	794	789	771	759	749	708
65°	536	533	518	507	501	532
75°	285	282	275	271	266	304
85°	74	76	76	74	72	83
90°	1	5	9	12	14	5
95°	32	30	9	12	12	41
105°	168	170	170	170	169	178
115°	315	318	318	316	313	312
125°	448	452	452	450	448	400
135°	559	562	561	560	556	430
145°	648	649	649	649	646	405
155°	713	710	711	712	708	328
165°	752	749	750	753	748	212
175°	770	766	767	771	766	73
180°	770	770	770	770	770	



TEST NUMBER: P333265

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1710.7	1710.0	1709.2	1708.5	1707.8	1706.2	1703.8	1701.4	1699.0	1696.6	1699.0
5°	1703.7	1703.1	1702.5	1701.9	1701.3	1699.5	1696.5	1693.5	1690.5	1687.5	1690.2
7.5°	1688.0	1687.4	1686.8	1686.2	1685.6	1683.6	1680.3	1677.0	1673.7	1670.4	1673.1
10°	1674.0	1673.4	1672.8	1672.2	1671.6	1669.6	1666.3	1663.0	1659.7	1656.4	1658.8
12.5°	1656.7	1655.6	1654.5	1653.4	1652.4	1650.3	1647.2	1644.2	1641.1	1638.0	1640.0
15°	1624.0	1623.1	1622.2	1621.3	1620.4	1618.3	1615.0	1611.7	1608.4	1605.1	1606.6
17.5°	1586.5	1585.2	1583.8	1582.5	1581.2	1578.8	1575.4	1572.0	1568.6	1565.1	1567.0
20°	1555.2	1554.6	1554.0	1553.4	1552.8	1550.5	1546.6	1542.7	1538.8	1534.9	1537.0
22.5°	1523.8	1522.8	1521.7	1520.6	1519.5	1517.1	1513.5	1509.8	1506.2	1502.5	1503.9
25°	1474.2	1472.7	1471.2	1469.7	1468.2	1465.5	1461.6	1457.7	1453.8	1449.9	1450.5
27.5°	1416.1	1415.2	1414.3	1413.4	1412.5	1410.1	1406.0	1402.0	1398.0	1394.0	1394.1
30°	1378.3	1377.4	1376.5	1375.6	1374.7	1372.0	1367.5	1363.0	1358.5	1354.0	1353.4
32.5°	1337.3	1335.9	1334.5	1333.1	1331.8	1329.1	1325.0	1321.0	1317.0	1313.0	1311.9
35°	1273.0	1271.8	1270.6	1269.4	1268.2	1265.5	1261.3	1257.1	1252.9	1248.7	1247.2
37.5°	1206.3	1204.8	1203.3	1201.8	1200.3	1197.6	1193.6	1189.7	1185.7	1181.8	1179.5
40°	1161.0	1159.5	1158.0	1156.5	1155.0	1152.1	1147.9	1143.7	1139.5	1135.3	1132.6
42.5°	1112.4	1111.1	1109.9	1108.6	1107.3	1104.6	1100.4	1096.2	1092.0	1087.8	1085.3
45°	1042.2	1041.0	1039.8	1038.6	1037.4	1035.0	1031.4	1027.8	1024.2	1020.6	1017.0
47.5°	966.6	966.6	966.7	966.8	966.8	964.7	960.4	956.0	951.7	947.4	943.7
50°	918.0	917.1	916.2	915.3	914.4	912.1	908.5	904.9	901.3	897.7	893.8
52.5°	868.3	867.6	867.0	866.3	865.7	863.4	859.6	855.7	851.9	848.0	844.6
55°	793.8	792.9	792.0	791.1	790.2	787.6	783.4	779.2	775.0	770.8	768.1
57.5°	715.2	714.7	714.3	713.8	713.3	711.3	707.7	704.2	700.7	697.1	693.6
60°	665.5	664.3	663.1	661.9	660.7	658.5	655.2	651.9	648.6	645.3	642.3
62.5°	613.7	612.7	611.8	610.8	609.9	608.0	605.1	602.3	599.5	596.7	593.4
65°	535.9	535.3	534.7	534.1	533.5	531.6	528.3	525.0	521.7	518.4	515.7
67.5°	460.6	459.3	458.1	456.8	455.6	453.7	451.2	448.8	446.3	443.9	441.6
70°	413.1	411.6	410.1	408.6	407.1	405.0	402.3	399.6	396.9	394.2	392.4
72.5°	361.3	360.2	359.2	358.2	357.2	355.8	354.1	352.3	350.6	348.8	346.8
75°	284.8	284.2	283.6	283.0	282.4	281.4	279.9	278.4	276.9	275.4	274.5
77.5°	214.4	214.1	213.9	213.7	213.4	212.9	212.0	211.2	210.4	209.5	209.0
80°	170.1	170.1	170.1	170.1	170.1	169.8	169.2	168.6	168.0	167.4	167.1
82.5°	131.2	130.7	130.3	129.8	129.3	129.0	128.9	128.8	128.6	128.5	128.0
85°	74.2	74.5	74.8	75.1	75.4	75.6	75.6	75.6	75.6	75.6	75.3
87.5°	29.3	29.5	29.7	29.9	30.1	30.2	30.1	30.0	30.0	29.9	30.0
90°	0.6	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8
92.5°	8.8	8.1	7.4	6.7	5.9	6.0	6.8	7.6	8.3	9.1	9.8
95°	32.5	32.1	31.8	31.4	31.0	28.4	23.6	18.8	13.9	9.1	9.8
97.5°	67.9	68.6	69.3	69.9	70.6	66.2	56.7	47.1	37.6	28.1	24.5
100°	95.3	95.7	96.0	96.4	96.8	97.2	97.8	98.3	98.8	99.3	80.4
102.5°	123.1	123.6	124.1	124.6	125.0	125.4	125.7	126.1	126.4	126.7	123.1
105°	167.7	168.2	168.8	169.3	169.8	170.0	170.0	170.0	170.0	170.0	170.0
107.5°	214.1	214.1	214.1	214.1	214.1	214.2	214.4	214.7	215.0	215.2	215.2
110°	244.2	244.2	244.2	244.2	244.2	244.3	244.6	244.8	245.1	245.3	245.0



TEST NUMBER: P333265

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.5	272.8	273.1	273.4	273.7	273.9	274.1	274.2	274.4	274.5	274.1
115°	314.9	315.6	316.2	316.8	317.5	317.9	318.0	318.1	318.2	318.4	317.9
117.5°	358.9	358.8	358.8	358.8	358.8	359.0	359.5	360.0	360.4	360.9	360.3
120°	386.3	386.1	386.0	385.9	385.7	385.9	386.3	386.6	387.0	387.4	387.1
122.5°	410.4	410.9	411.4	411.9	412.4	412.7	412.9	413.1	413.2	413.4	413.2
125°	447.9	448.8	449.6	450.5	451.4	451.9	451.9	451.9	451.9	451.9	451.4
127.5°	483.6	484.2	484.9	485.5	486.1	486.4	486.3	486.3	486.2	486.1	485.8
130°	505.5	506.1	506.8	507.4	508.0	508.4	508.5	508.7	508.8	508.9	508.5
132.5°	527.4	528.1	528.9	529.6	530.3	530.6	530.3	530.0	529.7	529.5	529.4
135°	558.6	559.3	560.1	560.8	561.6	561.9	561.6	561.3	561.1	560.8	560.6
137.5°	587.2	587.9	588.5	589.2	589.8	590.1	589.8	589.6	589.4	589.1	589.2
140°	605.9	606.2	606.4	606.7	606.9	607.0	606.9	606.7	606.6	606.5	606.7
142.5°	622.8	623.0	623.1	623.3	623.4	623.6	623.8	623.9	624.1	624.3	624.3
145°	647.6	647.8	648.1	648.3	648.6	648.7	648.7	648.7	648.7	648.7	648.8
147.5°	669.2	669.2	669.1	669.1	669.0	669.1	669.2	669.4	669.5	669.7	669.9
150°	682.9	682.7	682.4	682.2	681.9	681.9	682.2	682.4	682.7	682.9	683.2
152.5°	696.2	695.6	695.1	694.5	693.9	693.8	694.0	694.3	694.5	694.8	695.1
155°	713.2	712.4	711.7	710.9	710.1	709.9	710.1	710.4	710.6	710.9	711.3
157.5°	726.3	725.8	725.4	724.9	724.5	724.3	724.3	724.3	724.3	724.4	724.8
160°	735.4	734.7	733.9	733.1	732.4	732.1	732.2	732.3	732.4	732.6	733.1
162.5°	742.7	742.0	741.2	740.4	739.7	739.4	739.5	739.6	739.7	739.9	740.6
165°	752.5	751.8	751.0	750.3	749.5	749.2	749.3	749.4	749.6	749.7	750.4
167.5°	759.8	759.1	758.3	757.5	756.7	756.4	756.5	756.6	756.7	756.9	757.8
170°	764.0	763.1	762.2	761.3	760.4	760.0	760.1	760.3	760.4	760.5	761.5
172.5°	766.7	765.8	764.9	764.0	763.1	762.8	763.0	763.3	763.5	763.7	764.6
175°	769.7	768.9	768.1	767.4	766.6	766.3	766.4	766.6	766.7	766.8	767.8
177.5°	771.0	770.4	769.8	769.2	768.6	768.3	768.4	768.5	768.6	768.7	769.5
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7



TEST NUMBER: P333265

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1701.4	1703.8	1706.2	1707.3	1707.1	1706.8	1706.6	1706.4
5°	1692.9	1695.6	1698.3	1699.5	1699.2	1698.9	1698.6	1698.3
7.5°	1675.7	1678.4	1681.0	1682.2	1681.9	1681.6	1681.3	1681.0
10°	1661.2	1663.6	1666.0	1667.1	1666.8	1666.5	1666.2	1665.9
12.5°	1641.9	1643.8	1645.7	1646.7	1646.6	1646.5	1646.5	1646.4
15°	1608.1	1609.6	1611.1	1611.9	1611.9	1611.9	1611.9	1611.9
17.5°	1568.9	1570.7	1572.6	1572.8	1571.3	1569.8	1568.3	1566.8
20°	1539.1	1541.2	1543.3	1543.6	1542.1	1540.6	1539.1	1537.6
22.5°	1505.3	1506.7	1508.0	1508.2	1507.2	1506.2	1505.2	1504.1
25°	1451.1	1451.7	1452.3	1452.1	1451.2	1450.3	1449.4	1448.5
27.5°	1394.2	1394.3	1394.5	1394.1	1393.2	1392.3	1391.4	1390.5
30°	1352.8	1352.2	1351.6	1350.9	1350.0	1349.1	1348.2	1347.3
32.5°	1310.8	1309.7	1308.7	1307.3	1305.7	1304.1	1302.4	1300.8
35°	1245.7	1244.2	1242.7	1240.8	1238.4	1236.0	1233.6	1231.2
37.5°	1177.3	1175.1	1172.9	1171.1	1169.7	1168.3	1166.9	1165.6
40°	1129.9	1127.2	1124.5	1122.7	1121.8	1120.9	1120.0	1119.1
42.5°	1082.9	1080.4	1078.0	1076.0	1074.7	1073.3	1071.9	1070.5
45°	1013.4	1009.8	1006.2	1003.9	1003.0	1002.1	1001.2	1000.3
47.5°	940.1	936.4	932.8	929.9	927.8	925.7	923.6	921.5
50°	889.9	886.0	882.1	879.1	877.0	874.9	872.8	870.7
52.5°	841.2	837.8	834.4	831.5	829.1	826.8	824.5	822.1
55°	765.4	762.7	760.0	757.6	755.5	753.4	751.3	749.2
57.5°	690.2	686.7	683.2	680.9	679.8	678.6	677.5	676.3
60°	639.3	636.3	633.3	630.7	628.6	626.5	624.4	622.3
62.5°	590.2	587.0	583.7	581.3	579.7	578.1	576.4	574.8
65°	513.0	510.3	507.6	505.6	504.4	503.2	502.0	500.8
67.5°	439.3	437.0	434.7	433.2	432.5	431.8	431.1	430.4
70°	390.6	388.8	387.0	385.5	384.3	383.1	381.9	380.7
72.5°	344.8	342.7	340.7	339.1	337.9	336.7	335.5	334.3
75°	273.6	272.7	271.8	270.7	269.5	268.3	267.1	265.9
77.5°	208.4	207.9	207.4	206.7	205.8	205.0	204.1	203.3
80°	166.8	166.5	166.2	165.7	165.1	164.5	163.9	163.3
82.5°	127.4	126.9	126.4	126.0	125.9	125.8	125.7	125.5
85°	75.0	74.7	74.4	73.9	73.3	72.7	72.1	71.5
87.5°	30.2	30.3	30.4	30.3	29.9	29.5	29.1	28.7
90°	10.4	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	10.4	11.0	11.7	12.1	12.2	12.4	12.6	12.8
95°	10.4	11.0	11.7	12.0	12.0	12.0	12.0	12.0
97.5°	20.9	17.3	13.8	12.0	12.0	12.0	12.0	12.0
100°	61.5	42.6	23.7	14.0	13.5	13.0	12.5	12.0
102.5°	119.5	115.9	112.4	106.3	97.6	89.0	80.4	71.8
105°	170.0	170.0	170.0	170.0	169.8	169.7	169.6	169.4
107.5°	215.3	215.3	215.3	215.1	214.8	214.4	214.0	213.6
110°	244.6	244.2	243.8	243.7	243.8	243.9	244.1	244.2



TEST NUMBER: P333265

CATALOG NUMBER: S125DIP-S1090D590U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	273.6	273.1	272.6	272.3	272.1	271.9	271.8	271.6
115°	317.3	316.8	316.3	315.7	314.9	314.2	313.4	312.7
117.5°	359.6	358.9	358.3	357.8	357.5	357.1	356.8	356.5
120°	386.9	386.6	386.4	385.9	385.3	384.7	384.0	383.4
122.5°	412.9	412.7	412.4	411.9	411.2	410.4	409.7	409.0
125°	450.9	450.3	449.8	449.4	449.0	448.6	448.3	447.9
127.5°	485.5	485.3	485.0	484.4	483.4	482.5	481.6	480.6
130°	508.2	507.8	507.4	506.9	506.3	505.6	505.0	504.4
132.5°	529.3	529.2	529.2	528.8	528.2	527.5	526.9	526.3
135°	560.3	560.1	559.8	559.3	558.6	557.8	557.0	556.3
137.5°	589.2	589.3	589.3	589.0	588.4	587.7	587.1	586.4
140°	607.0	607.2	607.5	607.2	606.5	605.7	605.0	604.2
142.5°	624.4	624.4	624.5	624.1	623.4	622.6	621.8	621.1
145°	649.0	649.1	649.2	648.9	648.1	647.4	646.6	645.8
147.5°	670.0	670.2	670.3	669.9	669.0	668.1	667.2	666.3
150°	683.4	683.7	683.9	683.6	682.6	681.5	680.5	679.5
152.5°	695.3	695.6	695.8	695.5	694.6	693.7	692.7	691.8
155°	711.7	712.0	712.4	712.1	711.1	710.1	709.1	708.0
157.5°	725.2	725.6	726.0	725.7	724.7	723.6	722.6	721.6
160°	733.6	734.1	734.6	734.3	733.3	732.3	731.3	730.3
162.5°	741.3	742.0	742.7	742.5	741.4	740.3	739.2	738.0
165°	751.2	752.0	752.7	752.6	751.6	750.6	749.6	748.5
167.5°	758.7	759.6	760.5	760.4	759.3	758.1	757.0	755.8
170°	762.6	763.6	764.6	764.5	763.4	762.2	761.1	760.0
172.5°	765.5	766.5	767.4	767.3	766.1	765.0	763.8	762.7
175°	768.8	769.8	770.9	770.8	769.7	768.5	767.4	766.2
177.5°	770.2	770.9	771.6	771.5	770.7	769.9	769.1	768.3
180°	769.7	769.7	769.7	769.7	769.7	769.7	769.7	769.7

(END OF REPORT)