

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332904-940

Luminaire Tested: **S124RDIP-S575D590U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332904-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D590U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4199.4 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332904-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332904-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	83	81	73	71	69	61	60	58	50	49	48	43
2	89	82	76	71	82	76	71	66	65	61	57	54	51	49	44	42	41	36
3	82	72	65	60	75	67	61	56	57	52	49	48	45	42	39	37	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	27	23
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23	21
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	19	17	15
10	47	36	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P332904-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	2.0
10°-20°	237.4	5.7
20°-30°	342.8	8.2
30°-40°	388.6	9.3
40°-50°	375.2	8.9
50°-60°	312.0	7.4
60°-70°	215.4	5.1
70°-80°	109.2	2.6
80°-90°	30.0	0.7
90°-100°	23.3	0.6
100°-110°	148.3	3.5
110°-120°	283.7	6.8
120°-130°	360.1	8.6
130°-140°	385.3	9.2
140°-150°	360.3	8.6
150°-160°	290.6	6.9
160°-170°	187.4	4.5
170°-180°	64.6	1.5
0°-30°	665.3	15.8
0°-40°	1053.9	25.1
0°-60°	1741.1	41.5
0°-90°	2095.7	49.9
90°-120°	455.3	10.8
90°-150°	1561.1	37.2
90°-180°	2104.0	50.1
0°-180°	4199.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	2	7	11	14	15	3
95°	28	12	11	14	15	36
105°	153	156	159	162	145	160
115°	286	287	287	288	288	281
125°	402	404	403	404	405	359
135°	498	498	500	501	502	384
145°	575	576	576	577	578	359
155°	630	631	629	631	630	290
165°	665	662	662	666	662	188
175°	680	677	678	682	676	65
180°	680	680	680	680	680	



TEST NUMBER: P332904-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	13.1	12.3	11.6	10.9	10.1	9.8	9.8	9.9	10.0	10.0	10.0
90°	1.5	2.8	4.0	5.3	6.5	7.6	8.5	9.4	10.3	11.1	11.9
92.5°	6.4	6.5	6.5	6.6	6.7	7.1	8.1	9.0	9.9	10.8	11.5
95°	28.0	24.2	20.3	16.4	12.6	10.7	10.9	11.0	11.1	11.1	11.9
97.5°	59.4	61.8	64.2	66.6	69.0	63.8	51.3	38.7	26.0	13.5	13.5
100°	83.4	85.4	87.5	89.5	91.6	84.8	69.2	53.6	38.0	22.4	20.4
102.5°	110.3	111.7	113.2	114.8	116.3	116.0	114.0	111.9	109.9	107.8	87.1
105°	153.1	153.8	154.4	155.2	155.8	156.4	157.0	157.6	158.1	158.7	159.7
107.5°	192.9	193.2	193.6	193.9	194.2	194.7	195.6	196.4	197.1	197.9	198.4
110°	219.7	220.1	220.4	220.8	221.1	221.6	222.3	222.9	223.6	224.4	224.5



TEST NUMBER: P332904-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.8	246.4	247.0	247.6	248.3	248.7	249.0	249.3	249.7	249.9	249.9
115°	285.9	286.2	286.5	286.9	287.2	287.3	287.2	287.1	287.0	286.9	287.1
117.5°	322.0	322.4	322.9	323.3	323.8	324.1	324.4	324.7	324.9	325.1	325.1
120°	346.4	346.9	347.3	347.8	348.2	348.4	348.3	348.1	348.0	347.9	348.1
122.5°	369.2	369.4	369.7	370.0	370.2	370.5	370.7	370.8	371.0	371.1	371.2
125°	401.8	402.3	402.8	403.2	403.7	403.8	403.5	403.3	403.1	402.9	403.2
127.5°	432.7	432.8	433.0	433.1	433.2	433.5	434.1	434.5	435.1	435.6	435.5
130°	452.7	452.8	452.9	453.1	453.2	453.3	453.7	454.1	454.4	454.8	454.9
132.5°	471.0	471.2	471.4	471.6	471.8	472.2	472.6	473.0	473.4	473.9	473.9
135°	498.5	498.4	498.3	498.1	498.0	498.2	498.6	499.1	499.5	500.0	500.2
137.5°	522.8	522.8	522.9	522.9	523.0	523.3	523.7	524.2	524.8	525.2	525.5
140°	538.7	538.9	539.1	539.3	539.6	539.8	540.0	540.3	540.5	540.7	541.0
142.5°	552.9	553.3	553.8	554.1	554.6	554.8	554.9	555.1	555.2	555.4	555.6
145°	574.8	575.2	575.4	575.8	576.1	576.3	576.3	576.3	576.3	576.3	576.4
147.5°	592.2	592.8	593.4	594.1	594.7	594.9	594.9	594.8	594.6	594.5	594.6
150°	604.8	605.2	605.7	606.2	606.6	606.8	606.6	606.5	606.5	606.3	606.3
152.5°	615.4	615.7	616.1	616.4	616.8	616.9	616.7	616.5	616.3	616.1	616.3
155°	630.3	630.4	630.4	630.5	630.7	630.5	630.3	629.9	629.5	629.2	629.6
157.5°	642.7	642.7	642.6	642.6	642.5	642.2	641.9	641.5	641.1	640.7	641.3
160°	650.1	649.7	649.3	649.1	648.7	648.5	648.4	648.3	648.1	648.0	648.7
162.5°	656.6	656.1	655.7	655.3	654.9	654.6	654.4	654.3	654.2	654.2	654.8
165°	664.8	664.2	663.7	663.1	662.5	662.3	662.3	662.3	662.3	662.3	663.2
167.5°	671.3	670.7	670.1	669.6	669.0	668.6	668.6	668.5	668.4	668.3	669.4
170°	675.0	674.3	673.6	673.0	672.3	672.0	672.1	672.2	672.3	672.4	673.3
172.5°	677.4	676.7	676.1	675.4	674.8	674.4	674.6	674.7	674.8	674.8	675.8
175°	680.1	679.4	678.7	678.1	677.3	677.1	677.2	677.3	677.4	677.5	678.5
177.5°	681.3	680.6	680.0	679.4	678.8	678.5	678.7	678.9	679.0	679.2	680.0
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1



TEST NUMBER: P332904-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	10.1	10.1	10.1	10.2	10.3	10.5	10.6	10.8
90°	12.6	13.2	13.9	14.4	14.6	14.8	15.1	15.2
92.5°	12.1	12.8	13.5	13.8	13.9	13.9	14.0	14.0
95°	12.6	13.2	13.9	14.3	14.4	14.5	14.6	14.7
97.5°	13.6	13.6	13.7	13.8	13.9	14.0	14.1	14.3
100°	18.5	16.6	14.7	13.8	13.9	14.0	14.1	14.3
102.5°	66.3	45.7	24.9	14.5	14.6	14.6	14.6	14.6
105°	160.8	161.8	162.7	161.2	157.2	153.1	149.0	145.0
107.5°	198.9	199.4	199.8	200.3	200.7	201.2	201.6	202.1
110°	224.8	225.0	225.2	225.5	225.9	226.1	226.5	226.9



TEST NUMBER: P332904-940

CATALOG NUMBER: S124RDIP-S575D590U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	249.9	249.9	249.8	249.9	250.4	250.8	251.3	251.6
115°	287.3	287.6	287.8	287.9	287.9	287.9	287.9	287.9
117.5°	325.0	325.0	324.9	324.9	324.9	324.9	324.8	324.8
120°	348.4	348.6	348.8	348.8	348.6	348.4	348.1	347.9
122.5°	371.4	371.5	371.7	371.6	371.4	371.1	371.0	370.7
125°	403.5	403.9	404.2	404.5	404.6	404.7	404.7	404.9
127.5°	435.5	435.4	435.3	435.2	435.2	435.1	435.0	434.9
130°	455.0	455.0	455.2	455.2	455.2	455.2	455.2	455.2
132.5°	474.1	474.2	474.3	474.3	474.2	474.1	474.0	473.9
135°	500.4	500.7	500.9	501.1	501.3	501.6	501.9	502.0
137.5°	525.8	526.0	526.2	526.3	526.3	526.2	526.1	526.0
140°	541.4	541.7	542.1	542.2	542.4	542.5	542.6	542.7
142.5°	555.8	556.1	556.3	556.5	556.5	556.5	556.5	556.6
145°	576.5	576.7	576.8	576.9	577.1	577.4	577.7	577.8
147.5°	594.7	594.8	594.9	594.9	595.1	595.2	595.3	595.4
150°	606.3	606.3	606.3	606.4	606.5	606.6	606.7	606.8
152.5°	616.4	616.6	616.8	616.9	616.8	616.7	616.6	616.6
155°	630.1	630.5	631.0	631.1	630.7	630.4	630.1	629.7
157.5°	641.9	642.5	643.0	643.0	642.5	641.9	641.3	640.7
160°	649.3	650.1	650.8	650.8	650.1	649.3	648.7	648.0
162.5°	655.5	656.1	656.8	656.8	656.0	655.2	654.5	653.7
165°	664.1	664.9	665.9	665.8	664.8	663.8	662.8	661.7
167.5°	670.4	671.4	672.3	672.3	671.2	670.0	668.9	667.8
170°	674.2	675.1	676.1	675.9	674.8	673.7	672.5	671.5
172.5°	676.7	677.6	678.5	678.3	677.2	675.9	674.7	673.4
175°	679.6	680.6	681.6	681.4	680.1	678.7	677.3	676.0
177.5°	680.7	681.4	682.2	682.0	680.9	679.8	678.7	677.6
180°	680.1	680.1	680.1	680.1	680.1	680.1	680.1	680.1

(END OF REPORT)