

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333269

Luminaire Tested: **S125DIP-S1090D810U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333269  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D810U835-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7293.3 lumens  
Efficiency: N/A  
Efficacy: 134.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	50	48	44
3	84	74	67	61	78	70	64	58	62	57	52	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	45	39	34	39	34	31	34	31	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	28	25	22
8	56	44	36	30	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10270	10270	10270	10270
5°	11893	10305	9022	10305
10°	13837	10251	7906	10251
15°	15317	10176	7293	10176
20°	17145	10057	6801	10057
25°	20085	9922	6560	9922
30°	21694	9790	6352	9790
35°	17837	9541	6215	9541
40°	12678	9195	6066	9195
45°	9740	8729	5980	8729
50°	8314	8151	5968	8151
55°	7402	7585	6019	7585
60°	6678	6966	6173	6966
65°	6168	6343	6333	6343
70°	5608	5697	6424	5697
75°	4951	5018	6366	5018
80°	4166	4091	5824	4091
85°	3298	2949	4698	2949



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	153.1	2.1
10°-20°	455.8	6.2
20°-30°	740.1	10.1
30°-40°	902.8	12.4
40°-50°	821.3	11.3
50°-60°	654.2	9.0
60°-70°	455.6	6.2
70°-80°	243.0	3.3
80°-90°	63.5	0.9
90°-100°	67.3	0.9
100°-110°	198.7	2.7
110°-120°	336.6	4.6
120°-130°	443.0	6.1
130°-140°	496.4	6.8
140°-150°	486.5	6.7
150°-160°	408.6	5.6
160°-170°	271.6	3.7
170°-180°	95.1	1.3
0°-30°	1349.0	18.5
0°-40°	2251.8	30.9
0°-60°	3727.3	51.1
0°-90°	4489.4	61.6
90°-120°	602.7	8.3
90°-150°	2028.6	27.8
90°-180°	2804.0	38.4
0°-180°	7293.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1590	1590	1590	1590	1590	
5°	1834	1590	1392	1590	1834	185
15°	2291	1522	1091	1522	2291	656
25°	2819	1392	921	1392	2819	1287
35°	2262	1210	788	1210	2262	1385
45°	1066	956	655	956	1066	854
55°	657	674	535	674	657	592
65°	404	415	414	415	404	401
75°	198	201	255	201	198	214
85°	44	40	63	40	44	52
90°	19	1	19	1	19	12
95°	67	51	67	51	67	68
105°	194	178	194	178	194	205
115°	340	337	340	337	340	336
125°	495	492	495	492	495	442
135°	642	640	642	640	642	495
145°	778	775	778	775	778	486
155°	887	887	887	887	887	408
165°	962	964	962	964	962	271
175°	999	1002	999	1002	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1682.0	1679.8	1677.7	1673.3	1676.6	1667.4	1663.1	1655.5	1646.3	1643.1	1639.3
5°	1834.5	1837.9	1841.3	1827.1	1828.4	1819.0	1797.4	1779.8	1765.7	1747.4	1734.6
7.5°	2018.1	2010.1	2009.5	2000.3	1984.5	1971.8	1949.1	1920.2	1892.3	1860.4	1834.1
10°	2109.9	2110.6	2104.5	2093.7	2076.8	2064.7	2035.0	2006.6	1972.2	1931.7	1902.7
12.5°	2179.0	2181.8	2174.2	2159.6	2151.3	2124.1	2100.9	2067.1	2026.2	1993.8	1949.7
15°	2290.8	2283.4	2278.0	2259.7	2245.6	2217.2	2180.1	2145.0	2100.4	2059.3	2018.1
17.5°	2398.5	2404.4	2394.3	2377.7	2333.7	2300.6	2250.8	2202.8	2147.3	2092.1	2042.9
20°	2494.6	2500.0	2484.5	2455.5	2402.8	2369.8	2304.3	2242.2	2178.1	2107.2	2053.2
22.5°	2614.5	2610.2	2589.2	2545.1	2499.5	2438.3	2367.5	2291.9	2211.5	2131.5	2059.7
25°	2818.6	2790.2	2777.4	2722.8	2662.7	2572.9	2475.7	2365.0	2265.1	2159.2	2067.4
27.5°	2931.7	2922.8	2908.5	2870.4	2807.3	2711.3	2596.7	2461.8	2320.9	2187.1	2067.0
30°	2909.0	2910.4	2911.7	2899.6	2859.1	2786.9	2672.8	2527.7	2360.3	2209.8	2070.7
32.5°	2708.2	2732.7	2756.2	2784.0	2795.4	2781.5	2710.1	2579.0	2406.7	2235.7	2068.6
35°	2262.4	2269.9	2346.1	2421.7	2524.3	2604.0	2657.3	2599.2	2454.1	2257.7	2066.0
37.5°	1764.1	1800.5	1853.3	1938.7	2086.8	2219.4	2389.9	2468.3	2421.5	2264.9	2061.3
40°	1503.8	1537.5	1572.0	1659.0	1783.9	1944.5	2138.2	2303.6	2342.1	2242.2	2045.1
42.5°	1302.9	1329.7	1367.9	1433.3	1537.7	1680.0	1865.0	2081.1	2214.1	2176.3	2011.1
45°	1066.4	1083.3	1113.0	1165.0	1240.6	1351.9	1515.3	1751.5	1957.4	2025.5	1930.4
47.5°	912.8	912.7	935.8	971.7	1026.2	1120.8	1241.6	1426.7	1646.6	1809.3	1801.7
50°	827.5	824.1	842.3	873.4	916.6	979.4	1094.8	1242.6	1453.8	1638.1	1689.4
52.5°	754.1	754.5	765.7	788.6	824.8	878.4	964.6	1097.9	1278.4	1467.5	1564.1
55°	657.4	654.7	667.5	683.1	709.4	744.5	806.6	908.5	1054.9	1241.2	1366.8
57.5°	568.8	576.3	581.4	592.2	614.1	637.6	689.9	764.7	880.9	1040.8	1173.5
60°	517.0	524.4	528.5	539.3	556.8	577.1	617.6	678.3	776.2	913.9	1045.5
62.5°	470.6	476.4	477.7	487.4	501.8	521.5	553.3	604.4	681.7	802.1	931.0
65°	403.6	403.6	406.3	416.4	423.2	440.7	465.0	502.2	564.3	658.1	768.1
67.5°	339.1	342.3	341.7	346.1	352.3	366.0	383.4	414.0	460.0	528.5	616.5
70°	297.0	299.7	299.0	302.4	309.1	317.9	332.1	361.1	394.2	452.9	528.5
72.5°	259.2	260.3	258.5	263.0	267.0	274.7	290.5	306.0	336.9	386.5	448.6
75°	198.4	199.8	201.1	203.8	207.9	211.9	220.0	235.6	255.8	292.9	332.8
77.5°	148.8	146.2	149.4	149.0	151.3	154.4	161.6	169.8	186.4	209.9	240.7
80°	112.0	112.7	112.7	113.4	116.8	118.8	124.9	130.9	143.8	161.3	182.9
82.5°	81.8	83.6	82.5	83.7	86.5	88.0	91.4	96.4	103.8	117.6	133.2
85°	44.5	41.2	42.5	43.9	43.9	44.5	47.2	49.3	53.3	58.7	64.8
87.5°	16.7	17.7	18.1	18.0	18.5	18.3	20.3	20.1	21.6	23.0	24.9
90°	18.8	18.2	17.7	17.2	16.7	16.0	15.1	14.2	13.4	12.5	11.3
92.5°	36.9	36.5	36.1	35.8	35.4	34.6	33.5	32.3	31.2	30.0	28.5
95°	67.2	66.9	66.6	66.2	65.9	65.1	63.9	62.6	61.4	60.2	58.5
97.5°	102.0	101.8	101.5	101.3	101.1	100.5	99.3	98.2	97.0	95.9	93.5
100°	128.2	127.9	127.5	127.2	126.9	125.9	124.3	122.8	121.2	119.6	117.4
102.5°	154.5	154.0	153.5	153.1	152.6	151.5	149.8	148.1	146.4	144.7	143.5
105°	193.9	193.4	192.9	192.4	191.8	191.1	190.0	189.0	187.9	186.9	185.8
107.5°	234.3	234.3	234.3	234.4	234.4	234.2	233.6	233.1	232.6	232.1	231.3
110°	264.3	264.5	264.6	264.8	265.0	264.8	264.3	263.8	263.3	262.7	262.2



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	293.7	294.0	294.3	294.6	295.0	295.0	294.7	294.5	294.3	294.0	293.4
115°	340.2	340.3	340.5	340.7	340.8	341.0	341.2	341.4	341.5	341.7	341.4
117.5°	385.5	386.2	386.9	387.6	388.3	388.6	388.4	388.3	388.1	388.0	387.7
120°	416.8	417.5	418.2	418.9	419.6	419.9	419.9	419.9	419.9	419.9	419.7
122.5°	448.1	448.6	449.2	449.7	450.3	450.6	450.8	450.9	451.0	451.2	450.7
125°	495.0	495.2	495.3	495.5	495.7	495.9	496.3	496.6	497.0	497.3	497.1
127.5°	540.0	540.4	540.7	541.1	541.4	541.7	541.8	542.0	542.2	542.4	542.2
130°	570.0	570.4	570.7	571.1	571.4	571.7	571.9	572.0	572.2	572.4	572.0
132.5°	598.2	598.7	599.2	599.7	600.1	600.5	600.6	600.8	601.0	601.2	601.2
135°	642.0	642.7	643.4	644.1	644.8	645.1	645.1	645.1	645.1	645.1	644.9
137.5°	684.8	685.7	686.6	687.4	688.3	688.6	688.4	688.2	688.0	687.8	687.4
140°	712.4	713.2	714.1	715.0	715.8	716.1	715.7	715.4	715.1	714.7	714.2
142.5°	738.6	739.5	740.4	741.2	742.1	742.4	742.2	742.0	741.8	741.6	740.9
145°	778.0	778.6	779.1	779.6	780.1	780.4	780.4	780.4	780.4	780.4	779.9
147.5°	811.7	812.9	814.0	815.2	816.4	816.8	816.4	815.9	815.5	815.1	814.7
150°	836.7	837.0	837.4	837.7	838.1	838.3	838.3	838.3	838.3	838.3	837.6
152.5°	857.3	858.0	858.6	859.2	859.8	859.9	859.5	859.1	858.7	858.3	858.0
155°	886.7	887.6	888.5	889.3	890.2	890.3	889.6	888.9	888.2	887.5	887.3
157.5°	911.3	912.4	913.6	914.7	915.9	916.1	915.4	914.7	914.0	913.3	913.1
160°	928.2	929.0	929.9	930.8	931.7	931.7	931.0	930.4	929.7	929.0	928.8
162.5°	942.6	943.6	944.6	945.6	946.6	946.7	945.9	945.0	944.2	943.4	943.3
165°	961.8	962.8	963.9	964.9	966.0	966.1	965.5	964.8	964.1	963.4	963.2
167.5°	977.1	978.2	979.3	980.4	981.4	981.5	980.4	979.4	978.3	977.3	977.3
170°	985.3	986.5	987.7	988.9	990.1	990.2	989.2	988.1	987.1	986.0	986.0
172.5°	992.1	993.2	994.3	995.4	996.5	996.5	995.4	994.4	993.3	992.3	992.3
175°	998.6	999.8	1001.0	1002.2	1003.4	1003.5	1002.5	1001.4	1000.4	999.3	999.3
177.5°	1002.3	1003.3	1004.3	1005.2	1006.2	1006.3	1005.4	1004.6	1003.8	1002.9	1003.1
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1636.1	1632.3	1628.0	1620.4	1611.2	1606.4	1598.8	1594.0	1584.2	1576.1	1567.5
5°	1719.1	1701.6	1685.4	1664.4	1641.5	1626.6	1609.1	1589.5	1569.3	1548.3	1525.4
7.5°	1805.1	1774.0	1740.3	1704.0	1668.5	1635.8	1604.6	1574.0	1545.4	1510.8	1481.5
10°	1862.9	1823.7	1781.9	1732.6	1684.7	1642.8	1600.3	1563.2	1525.4	1484.9	1449.1
12.5°	1920.6	1868.5	1809.4	1755.3	1697.6	1647.1	1597.1	1549.7	1502.2	1457.4	1415.6
15°	1961.4	1915.5	1860.8	1783.9	1719.1	1649.6	1583.4	1522.0	1464.6	1414.7	1362.1
17.5°	1988.3	1929.1	1870.4	1796.6	1711.7	1633.9	1559.0	1488.7	1424.0	1360.7	1309.9
20°	1993.1	1932.4	1871.0	1798.7	1711.7	1622.6	1547.7	1463.3	1393.8	1328.3	1266.2
22.5°	1991.5	1922.7	1855.8	1781.5	1696.6	1614.5	1523.9	1437.9	1362.5	1298.1	1233.3
25°	1976.3	1902.7	1819.0	1744.1	1660.4	1573.3	1481.5	1392.4	1315.5	1241.9	1177.8
27.5°	1963.6	1868.1	1773.4	1686.0	1605.2	1525.4	1437.5	1346.3	1260.9	1186.4	1126.0
30°	1947.9	1843.3	1736.6	1645.5	1562.5	1484.9	1401.9	1312.8	1223.7	1150.8	1086.0
32.5°	1933.9	1812.0	1699.4	1600.2	1512.3	1436.8	1360.3	1275.5	1188.0	1114.1	1049.3
35°	1906.7	1765.7	1636.8	1524.7	1430.9	1353.3	1289.2	1210.2	1129.9	1058.3	996.2
37.5°	1872.3	1704.9	1566.6	1449.1	1346.3	1264.5	1204.8	1144.2	1067.1	998.1	942.0
40°	1845.3	1661.7	1515.3	1395.1	1288.5	1203.4	1148.1	1090.7	1026.6	962.5	903.1
42.5°	1811.3	1622.9	1463.4	1334.1	1228.5	1145.7	1087.6	1038.9	982.3	922.5	867.4
45°	1748.8	1552.4	1379.6	1240.6	1133.9	1052.2	992.2	955.7	913.2	856.5	809.9
47.5°	1656.9	1467.7	1289.0	1145.5	1035.5	959.8	903.5	868.5	838.6	796.4	754.2
50°	1575.3	1404.6	1223.7	1081.3	971.3	895.0	843.0	811.3	785.6	753.2	717.5
52.5°	1484.1	1325.2	1159.4	1018.6	909.7	834.5	783.6	755.7	734.3	711.1	675.9
55°	1339.1	1204.1	1050.2	916.6	816.0	742.4	697.9	673.6	656.1	638.5	616.9
57.5°	1179.4	1073.8	937.5	815.3	722.7	655.8	614.2	590.6	576.9	567.9	555.2
60°	1067.1	976.7	859.2	747.8	657.4	598.0	557.5	539.3	527.8	520.4	510.9
62.5°	962.9	888.6	779.8	678.2	599.1	542.9	506.8	489.1	478.1	474.5	466.7
65°	809.3	751.9	662.1	577.8	510.3	462.3	432.0	415.1	408.3	404.3	405.0
67.5°	657.9	623.0	550.9	478.9	425.1	384.9	360.6	347.6	344.2	338.8	338.7
70°	565.6	539.3	478.5	415.8	367.8	336.8	315.2	301.7	298.3	295.6	295.0
72.5°	484.1	461.0	408.3	358.0	314.9	287.7	269.8	261.7	256.2	254.6	254.5
75°	363.8	351.0	309.1	269.3	239.6	220.7	208.6	201.1	197.1	196.4	197.1
77.5°	258.6	247.4	220.8	192.6	173.9	159.6	149.3	146.7	142.1	142.3	141.6
80°	194.4	187.0	170.1	147.8	132.3	120.1	114.7	110.0	108.7	106.6	108.7
82.5°	140.9	133.0	121.5	107.3	94.5	87.2	81.8	80.3	79.5	78.6	79.0
85°	69.5	70.2	63.4	52.6	47.2	43.2	39.8	39.8	39.1	38.5	39.1
87.5°	25.8	24.5	22.0	20.2	17.2	15.3	14.5	14.7	13.4	13.1	13.9
90°	10.1	8.9	7.6	6.3	5.0	3.6	2.2	0.8	2.2	3.6	5.0
92.5°	27.0	25.5	24.0	22.8	21.8	20.9	19.9	18.9	19.9	20.9	21.8
95°	56.7	55.0	53.3	52.2	51.9	51.5	51.2	50.8	51.2	51.5	51.9
97.5°	91.1	88.7	86.3	85.0	84.9	84.7	84.6	84.5	84.6	84.7	84.9
100°	115.1	112.9	110.6	109.5	109.5	109.5	109.5	109.5	109.5	109.5	109.5
102.5°	142.4	141.2	140.1	139.2	138.5	137.8	137.1	136.4	137.1	137.8	138.5
105°	184.8	183.8	182.7	181.8	180.9	180.0	179.2	178.3	179.2	180.0	180.9
107.5°	230.5	229.7	228.9	228.1	227.2	226.3	225.4	224.6	225.4	226.3	227.2
110°	261.7	261.2	260.7	260.0	259.1	258.2	257.4	256.5	257.4	258.2	259.1





TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	292.7	292.0	291.4	290.8	290.4	289.9	289.5	289.0	289.5	289.9	290.4
115°	341.0	340.7	340.3	339.8	339.1	338.4	337.7	337.0	337.7	338.4	339.1
117.5°	387.4	387.1	386.8	386.4	386.1	385.8	385.5	385.2	385.5	385.8	386.1
120°	419.6	419.4	419.2	418.7	417.8	417.0	416.1	415.2	416.1	417.0	417.8
122.5°	450.3	449.8	449.4	449.0	448.7	448.4	448.1	447.7	448.1	448.4	448.7
125°	497.0	496.8	496.6	496.0	495.0	493.9	492.9	491.8	492.9	493.9	495.0
127.5°	541.9	541.7	541.5	541.1	540.5	539.9	539.4	538.8	539.4	539.9	540.5
130°	571.7	571.3	571.0	570.4	569.5	568.7	567.8	566.9	567.8	568.7	569.5
132.5°	601.3	601.4	601.4	600.8	599.3	597.9	596.5	595.1	596.5	597.9	599.3
135°	644.8	644.6	644.4	643.8	642.8	641.7	640.7	639.6	640.7	641.7	642.8
137.5°	687.0	686.7	686.3	685.6	684.6	683.6	682.6	681.6	682.6	683.6	684.6
140°	713.7	713.1	712.6	711.9	711.1	710.2	709.3	708.5	709.3	710.2	711.1
142.5°	740.3	739.6	739.0	738.3	737.5	736.8	736.1	735.4	736.1	736.8	737.5
145°	779.3	778.8	778.3	777.7	777.0	776.3	775.6	774.9	775.6	776.3	777.0
147.5°	814.3	813.9	813.4	813.0	812.7	812.3	811.9	811.5	811.9	812.3	812.7
150°	836.9	836.2	835.5	835.2	835.4	835.6	835.7	835.9	835.7	835.6	835.4
152.5°	857.7	857.4	857.2	856.9	856.7	856.4	856.2	855.9	856.2	856.4	856.7
155°	887.2	887.0	886.8	886.7	886.7	886.7	886.7	886.7	886.7	886.7	886.7
157.5°	913.0	912.8	912.6	912.7	913.1	913.5	913.9	914.3	913.9	913.5	913.1
160°	928.6	928.4	928.3	928.4	929.0	929.5	930.0	930.5	930.0	929.5	929.0
162.5°	943.3	943.2	943.2	943.4	943.8	944.1	944.5	944.9	944.5	944.1	943.8
165°	963.0	962.8	962.7	962.8	963.1	963.5	963.8	964.2	963.8	963.5	963.1
167.5°	977.3	977.3	977.3	977.6	978.3	979.0	979.7	980.4	979.7	979.0	978.3
170°	986.0	986.0	986.0	986.4	987.1	987.8	988.5	989.2	988.5	987.8	987.1
172.5°	992.3	992.3	992.3	992.6	993.3	994.0	994.7	995.4	994.7	994.0	993.3
175°	999.3	999.3	999.3	999.7	1000.4	1001.1	1001.8	1002.5	1001.8	1001.1	1000.4
177.5°	1003.2	1003.4	1003.5	1003.8	1004.4	1005.0	1005.5	1006.1	1005.5	1005.0	1004.4
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1562.6	1556.7	1551.8	1541.0	1535.1	1527.0	1520.5	1527.5	1520.0	1523.2	1518.4
5°	1513.9	1495.0	1481.5	1461.9	1445.1	1429.5	1418.1	1416.0	1410.6	1407.9	1399.8
7.5°	1455.3	1431.7	1408.5	1382.8	1361.2	1339.2	1325.2	1313.6	1305.9	1295.8	1288.9
10°	1420.8	1389.0	1362.1	1331.0	1304.0	1280.4	1261.5	1252.0	1243.3	1230.4	1225.7
12.5°	1378.1	1345.3	1312.4	1279.2	1253.2	1226.9	1210.7	1196.4	1190.3	1175.9	1174.4
15°	1327.0	1277.7	1245.3	1211.5	1175.8	1154.2	1140.7	1125.1	1118.4	1108.3	1100.8
17.5°	1265.9	1221.9	1181.4	1146.5	1115.8	1097.6	1080.9	1070.2	1058.6	1052.0	1039.8
20°	1221.7	1179.8	1139.3	1102.2	1078.6	1057.6	1044.1	1034.0	1021.9	1018.5	1006.4
22.5°	1184.4	1138.2	1099.4	1068.2	1042.4	1018.8	1004.2	997.3	988.9	978.5	976.1
25°	1123.8	1075.9	1042.8	1011.8	988.8	967.2	957.1	948.3	940.2	932.8	930.1
27.5°	1071.4	1028.6	989.3	961.3	941.3	921.6	912.7	902.0	896.1	890.1	882.8
30°	1034.7	990.8	956.4	929.4	907.8	890.3	880.8	873.4	868.0	862.6	858.5
32.5°	996.9	956.3	922.9	896.5	874.9	861.6	853.3	848.0	842.1	835.6	830.5
35°	947.0	902.4	870.0	847.1	830.2	820.1	810.6	805.9	799.1	799.1	793.7
37.5°	890.7	852.2	823.6	802.7	787.5	778.5	768.2	765.0	760.7	757.8	755.9
40°	857.2	821.4	794.4	773.5	757.3	749.9	741.8	736.4	733.7	730.3	728.9
42.5°	822.6	788.5	762.6	743.3	729.2	722.9	715.3	711.5	706.1	701.7	700.9
45°	770.1	737.0	713.4	697.9	685.7	678.3	673.6	665.5	662.8	657.4	656.7
47.5°	720.3	688.6	665.4	652.7	642.0	635.9	628.5	620.4	617.3	614.6	614.3
50°	683.1	654.0	632.4	620.3	610.2	601.4	594.0	588.6	586.5	586.5	587.9
52.5°	645.3	620.5	602.2	587.3	577.8	568.4	561.6	558.3	555.2	558.5	560.9
55°	589.9	564.9	551.4	537.3	527.8	517.0	513.6	512.3	510.3	515.7	518.4
57.5°	531.3	513.8	498.0	483.9	475.4	469.2	464.6	463.8	467.6	470.2	478.9
60°	494.1	473.8	459.6	448.8	438.7	434.7	433.3	432.0	434.7	442.1	453.6
62.5°	453.0	436.6	421.3	413.2	405.8	399.0	398.8	399.6	405.0	413.5	424.9
65°	392.8	378.6	368.5	359.1	353.0	348.9	350.3	353.0	359.1	370.5	383.4
67.5°	331.7	322.0	312.9	305.2	299.4	299.4	300.8	304.8	312.0	325.2	336.9
70°	292.3	281.5	274.0	270.7	265.9	263.2	267.3	274.0	280.1	292.3	302.4
72.5°	252.8	243.7	237.9	235.6	233.5	231.4	232.7	240.0	248.2	260.4	272.1
75°	194.4	191.0	187.0	184.3	182.2	183.6	184.9	191.7	198.4	211.3	224.8
77.5°	141.9	138.4	135.9	135.3	134.2	134.9	138.6	143.6	150.2	159.6	169.8
80°	107.3	106.0	104.6	103.9	103.9	104.6	110.0	113.4	119.5	128.2	136.3
82.5°	78.2	77.3	77.1	76.9	77.5	77.6	80.9	85.3	90.3	96.9	103.9
85°	41.2	39.8	41.8	42.5	41.2	43.2	44.5	47.2	49.3	52.6	56.0
87.5°	14.8	16.1	15.8	16.6	16.8	18.2	17.8	20.1	21.4	22.6	22.2
90°	6.3	7.6	8.9	10.1	11.3	12.5	13.4	14.2	15.1	16.0	16.7
92.5°	22.8	24.0	25.5	27.0	28.5	30.0	31.2	32.3	33.5	34.6	35.4
95°	52.2	53.3	55.0	56.7	58.5	60.2	61.4	62.6	63.9	65.1	65.9
97.5°	85.0	86.3	88.7	91.1	93.5	95.9	97.0	98.2	99.3	100.5	101.1
100°	109.5	110.6	112.9	115.1	117.4	119.6	121.2	122.8	124.3	125.9	126.9
102.5°	139.2	140.1	141.2	142.4	143.5	144.7	146.4	148.1	149.8	151.5	152.6
105°	181.8	182.7	183.8	184.8	185.8	186.9	187.9	189.0	190.0	191.1	191.8
107.5°	228.1	228.9	229.7	230.5	231.3	232.1	232.6	233.1	233.6	234.2	234.4
110°	260.0	260.7	261.2	261.7	262.2	262.7	263.3	263.8	264.3	264.8	265.0



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	290.8	291.4	292.0	292.7	293.4	294.0	294.3	294.5	294.7	295.0	295.0
115°	339.8	340.3	340.7	341.0	341.4	341.7	341.5	341.4	341.2	341.0	340.8
117.5°	386.4	386.8	387.1	387.4	387.7	388.0	388.1	388.3	388.4	388.6	388.3
120°	418.7	419.2	419.4	419.6	419.7	419.9	419.9	419.9	419.9	419.9	419.6
122.5°	449.0	449.4	449.8	450.3	450.7	451.2	451.0	450.9	450.8	450.6	450.3
125°	496.0	496.6	496.8	497.0	497.1	497.3	497.0	496.6	496.3	495.9	495.7
127.5°	541.1	541.5	541.7	541.9	542.2	542.4	542.2	542.0	541.8	541.7	541.4
130°	570.4	571.0	571.3	571.7	572.0	572.4	572.2	572.0	571.9	571.7	571.4
132.5°	600.8	601.4	601.4	601.3	601.2	601.2	601.0	600.8	600.6	600.5	600.1
135°	643.8	644.4	644.6	644.8	644.9	645.1	645.1	645.1	645.1	645.1	644.8
137.5°	685.6	686.3	686.7	687.0	687.4	687.8	688.0	688.2	688.4	688.6	688.3
140°	711.9	712.6	713.1	713.7	714.2	714.7	715.1	715.4	715.7	716.1	715.8
142.5°	738.3	739.0	739.6	740.3	740.9	741.6	741.8	742.0	742.2	742.4	742.1
145°	777.7	778.3	778.8	779.3	779.9	780.4	780.4	780.4	780.4	780.4	780.1
147.5°	813.0	813.4	813.9	814.3	814.7	815.1	815.5	815.9	816.4	816.8	816.4
150°	835.2	835.5	836.2	836.9	837.6	838.3	838.3	838.3	838.3	838.3	838.1
152.5°	856.9	857.2	857.4	857.7	858.0	858.3	858.7	859.1	859.5	859.9	859.8
155°	886.7	886.8	887.0	887.2	887.3	887.5	888.2	888.9	889.6	890.3	890.2
157.5°	912.7	912.6	912.8	913.0	913.1	913.3	914.0	914.7	915.4	916.1	915.9
160°	928.4	928.3	928.4	928.6	928.8	929.0	929.7	930.4	931.0	931.7	931.7
162.5°	943.4	943.2	943.2	943.3	943.3	943.4	944.2	945.0	945.9	946.7	946.6
165°	962.8	962.7	962.8	963.0	963.2	963.4	964.1	964.8	965.5	966.1	966.0
167.5°	977.6	977.3	977.3	977.3	977.3	977.3	978.3	979.4	980.4	981.5	981.4
170°	986.4	986.0	986.0	986.0	986.0	986.0	987.1	988.1	989.2	990.2	990.1
172.5°	992.6	992.3	992.3	992.3	992.3	992.3	993.3	994.4	995.4	996.5	996.5
175°	999.7	999.3	999.3	999.3	999.3	999.3	1000.4	1001.4	1002.5	1003.5	1003.4
177.5°	1003.8	1003.5	1003.4	1003.2	1003.1	1002.9	1003.8	1004.6	1005.4	1006.3	1006.2
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1515.1	1518.9	1515.7	1520.0	1515.7	1518.9	1515.1	1518.4	1523.2	1520.0	1527.5
5°	1396.5	1390.4	1394.4	1391.7	1394.4	1390.4	1396.5	1399.8	1407.9	1410.6	1416.0
7.5°	1286.9	1281.1	1274.4	1271.3	1274.4	1281.1	1286.9	1288.9	1295.8	1305.9	1313.6
10°	1218.3	1210.9	1210.2	1205.5	1210.2	1210.9	1218.3	1225.7	1230.4	1243.3	1252.0
12.5°	1168.1	1161.2	1153.5	1151.5	1153.5	1161.2	1168.1	1174.4	1175.9	1190.3	1196.4
15°	1096.8	1091.4	1086.7	1090.7	1086.7	1091.4	1096.8	1100.8	1108.3	1118.4	1125.1
17.5°	1037.5	1033.1	1032.3	1027.3	1032.3	1033.1	1037.5	1039.8	1052.0	1058.6	1070.2
20°	1000.3	996.9	998.3	989.5	998.3	996.9	1000.3	1006.4	1018.5	1021.9	1034.0
22.5°	970.6	964.0	963.2	961.4	963.2	964.0	970.6	976.1	978.5	988.9	997.3
25°	924.0	920.6	917.3	920.6	917.3	920.6	924.0	930.1	932.8	940.2	948.3
27.5°	883.4	879.3	878.4	878.8	878.4	879.3	883.4	882.8	890.1	896.1	902.0
30°	858.5	851.8	852.5	851.8	852.5	851.8	858.5	858.5	862.6	868.0	873.4
32.5°	831.5	826.9	826.0	824.8	826.0	826.9	831.5	830.5	835.6	842.1	848.0
35°	791.7	791.7	788.3	788.3	788.3	791.7	791.7	793.7	799.1	799.1	805.9
37.5°	754.3	753.6	751.6	751.9	751.6	753.6	754.3	755.9	757.8	760.7	765.0
40°	726.2	725.6	723.5	719.5	723.5	725.6	726.2	728.9	730.3	733.7	736.4
42.5°	699.2	697.0	696.0	694.7	696.0	697.0	699.2	700.9	701.7	706.1	711.5
45°	656.7	656.7	655.4	654.7	655.4	656.7	656.7	656.7	657.4	662.8	665.5
47.5°	615.4	616.6	619.2	618.8	619.2	616.6	615.4	614.3	614.6	617.3	620.4
50°	590.6	591.3	593.3	594.0	593.3	591.3	590.6	587.9	586.5	586.5	588.6
52.5°	563.0	567.0	569.5	569.1	569.5	567.0	563.0	560.9	558.5	555.2	558.3
55°	524.4	529.2	533.9	534.6	533.9	529.2	524.4	518.4	515.7	510.3	512.3
57.5°	486.2	492.8	497.8	499.5	497.8	492.8	486.2	478.9	470.2	467.6	463.8
60°	460.3	469.1	475.2	477.9	475.2	469.1	460.3	453.6	442.1	434.7	432.0
62.5°	435.5	445.3	451.4	451.9	451.4	445.3	435.5	424.9	413.5	405.0	399.6
65°	394.8	405.0	410.4	414.4	410.4	405.0	394.8	383.4	370.5	359.1	353.0
67.5°	351.1	361.2	367.2	370.4	367.2	361.2	351.1	336.9	325.2	312.0	304.8
70°	319.3	329.4	337.5	340.2	337.5	329.4	319.3	302.4	292.3	280.1	274.0
72.5°	287.9	297.0	303.5	306.7	303.5	297.0	287.9	272.1	260.4	248.2	240.0
75°	233.5	245.7	251.8	255.1	251.8	245.7	233.5	224.8	211.3	198.4	191.7
77.5°	180.1	191.1	194.8	196.5	194.8	191.1	180.1	169.8	159.6	150.2	143.6
80°	144.4	151.2	155.9	156.6	155.9	151.2	144.4	136.3	128.2	119.5	113.4
82.5°	111.0	116.6	118.1	119.9	118.1	116.6	111.0	103.9	96.9	90.3	85.3
85°	60.7	63.4	64.1	63.4	64.1	63.4	60.7	56.0	52.6	49.3	47.2
87.5°	23.4	23.0	23.1	24.3	23.1	23.0	23.4	22.2	22.6	21.4	20.1
90°	17.2	17.7	18.2	18.8	18.2	17.7	17.2	16.7	16.0	15.1	14.2
92.5°	35.8	36.1	36.5	36.9	36.5	36.1	35.8	35.4	34.6	33.5	32.3
95°	66.2	66.6	66.9	67.2	66.9	66.6	66.2	65.9	65.1	63.9	62.6
97.5°	101.3	101.5	101.8	102.0	101.8	101.5	101.3	101.1	100.5	99.3	98.2
100°	127.2	127.5	127.9	128.2	127.9	127.5	127.2	126.9	125.9	124.3	122.8
102.5°	153.1	153.5	154.0	154.5	154.0	153.5	153.1	152.6	151.5	149.8	148.1
105°	192.4	192.9	193.4	193.9	193.4	192.9	192.4	191.8	191.1	190.0	189.0
107.5°	234.4	234.3	234.3	234.3	234.3	234.3	234.4	234.4	234.2	233.6	233.1
110°	264.8	264.6	264.5	264.3	264.5	264.6	264.8	265.0	264.8	264.3	263.8



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	294.6	294.3	294.0	293.7	294.0	294.3	294.6	295.0	295.0	294.7	294.5
115°	340.7	340.5	340.3	340.2	340.3	340.5	340.7	340.8	341.0	341.2	341.4
117.5°	387.6	386.9	386.2	385.5	386.2	386.9	387.6	388.3	388.6	388.4	388.3
120°	418.9	418.2	417.5	416.8	417.5	418.2	418.9	419.6	419.9	419.9	419.9
122.5°	449.7	449.2	448.6	448.1	448.6	449.2	449.7	450.3	450.6	450.8	450.9
125°	495.5	495.3	495.2	495.0	495.2	495.3	495.5	495.7	495.9	496.3	496.6
127.5°	541.1	540.7	540.4	540.0	540.4	540.7	541.1	541.4	541.7	541.8	542.0
130°	571.1	570.7	570.4	570.0	570.4	570.7	571.1	571.4	571.7	571.9	572.0
132.5°	599.7	599.2	598.7	598.2	598.7	599.2	599.7	600.1	600.5	600.6	600.8
135°	644.1	643.4	642.7	642.0	642.7	643.4	644.1	644.8	645.1	645.1	645.1
137.5°	687.4	686.6	685.7	684.8	685.7	686.6	687.4	688.3	688.6	688.4	688.2
140°	715.0	714.1	713.2	712.4	713.2	714.1	715.0	715.8	716.1	715.7	715.4
142.5°	741.2	740.4	739.5	738.6	739.5	740.4	741.2	742.1	742.4	742.2	742.0
145°	779.6	779.1	778.6	778.0	778.6	779.1	779.6	780.1	780.4	780.4	780.4
147.5°	815.2	814.0	812.9	811.7	812.9	814.0	815.2	816.4	816.8	816.4	815.9
150°	837.7	837.4	837.0	836.7	837.0	837.4	837.7	838.1	838.3	838.3	838.3
152.5°	859.2	858.6	858.0	857.3	858.0	858.6	859.2	859.8	859.9	859.5	859.1
155°	889.3	888.5	887.6	886.7	887.6	888.5	889.3	890.2	890.3	889.6	888.9
157.5°	914.7	913.6	912.4	911.3	912.4	913.6	914.7	915.9	916.1	915.4	914.7
160°	930.8	929.9	929.0	928.2	929.0	929.9	930.8	931.7	931.7	931.0	930.4
162.5°	945.6	944.6	943.6	942.6	943.6	944.6	945.6	946.6	946.7	945.9	945.0
165°	964.9	963.9	962.8	961.8	962.8	963.9	964.9	966.0	966.1	965.5	964.8
167.5°	980.4	979.3	978.2	977.1	978.2	979.3	980.4	981.4	981.5	980.4	979.4
170°	988.9	987.7	986.5	985.3	986.5	987.7	988.9	990.1	990.2	989.2	988.1
172.5°	995.4	994.3	993.2	992.1	993.2	994.3	995.4	996.5	996.5	995.4	994.4
175°	1002.2	1001.0	999.8	998.6	999.8	1001.0	1002.2	1003.4	1003.5	1002.5	1001.4
177.5°	1005.2	1004.3	1003.3	1002.3	1003.3	1004.3	1005.2	1006.2	1006.3	1005.4	1004.6
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1520.5	1527.0	1535.1	1541.0	1551.8	1556.7	1562.6	1567.5	1576.1	1584.2	1594.0
5°	1418.1	1429.5	1445.1	1461.9	1481.5	1495.0	1513.9	1525.4	1548.3	1569.3	1589.5
7.5°	1325.2	1339.2	1361.2	1382.8	1408.5	1431.7	1455.3	1481.5	1510.8	1545.4	1574.0
10°	1261.5	1280.4	1304.0	1331.0	1362.1	1389.0	1420.8	1449.1	1484.9	1525.4	1563.2
12.5°	1210.7	1226.9	1253.2	1279.2	1312.4	1345.3	1378.1	1415.6	1457.4	1502.2	1549.7
15°	1140.7	1154.2	1175.8	1211.5	1245.3	1277.7	1327.0	1362.1	1414.7	1464.6	1522.0
17.5°	1080.9	1097.6	1115.8	1146.5	1181.4	1221.9	1265.9	1309.9	1360.7	1424.0	1488.7
20°	1044.1	1057.6	1078.6	1102.2	1139.3	1179.8	1221.7	1266.2	1328.3	1393.8	1463.3
22.5°	1004.2	1018.8	1042.4	1068.2	1099.4	1138.2	1184.4	1233.3	1298.1	1362.5	1437.9
25°	957.1	967.2	988.8	1011.8	1042.8	1075.9	1123.8	1177.8	1241.9	1315.5	1392.4
27.5°	912.7	921.6	941.3	961.3	989.3	1028.6	1071.4	1126.0	1186.4	1260.9	1346.3
30°	880.8	890.3	907.8	929.4	956.4	990.8	1034.7	1086.0	1150.8	1223.7	1312.8
32.5°	853.3	861.6	874.9	896.5	922.9	956.3	996.9	1049.3	1114.1	1188.0	1275.5
35°	810.6	820.1	830.2	847.1	870.0	902.4	947.0	996.2	1058.3	1129.9	1210.2
37.5°	768.2	778.5	787.5	802.7	823.6	852.2	890.7	942.0	998.1	1067.1	1144.2
40°	741.8	749.9	757.3	773.5	794.4	821.4	857.2	903.1	962.5	1026.6	1090.7
42.5°	715.3	722.9	729.2	743.3	762.6	788.5	822.6	867.4	922.5	982.3	1038.9
45°	673.6	678.3	685.7	697.9	713.4	737.0	770.1	809.9	856.5	913.2	955.7
47.5°	628.5	635.9	642.0	652.7	665.4	688.6	720.3	754.2	796.4	838.6	868.5
50°	594.0	601.4	610.2	620.3	632.4	654.0	683.1	717.5	753.2	785.6	811.3
52.5°	561.6	568.4	577.8	587.3	602.2	620.5	645.3	675.9	711.1	734.3	755.7
55°	513.6	517.0	527.8	537.3	551.4	564.9	589.9	616.9	638.5	656.1	673.6
57.5°	464.6	469.2	475.4	483.9	498.0	513.8	531.3	555.2	567.9	576.9	590.6
60°	433.3	434.7	438.7	448.8	459.6	473.8	494.1	510.9	520.4	527.8	539.3
62.5°	398.8	399.0	405.8	413.2	421.3	436.6	453.0	466.7	474.5	478.1	489.1
65°	350.3	348.9	353.0	359.1	368.5	378.6	392.8	405.0	404.3	408.3	415.1
67.5°	300.8	299.4	299.4	305.2	312.9	322.0	331.7	338.7	338.8	344.2	347.6
70°	267.3	263.2	265.9	270.7	274.0	281.5	292.3	295.0	295.6	298.3	301.7
72.5°	232.7	231.4	233.5	235.6	237.9	243.7	252.8	254.5	254.6	256.2	261.7
75°	184.9	183.6	182.2	184.3	187.0	191.0	194.4	197.1	196.4	197.1	201.1
77.5°	138.6	134.9	134.2	135.3	135.9	138.4	141.9	141.6	142.3	142.1	146.7
80°	110.0	104.6	103.9	103.9	104.6	106.0	107.3	108.7	106.6	108.7	110.0
82.5°	80.9	77.6	77.5	76.9	77.1	77.3	78.2	79.0	78.6	79.5	80.3
85°	44.5	43.2	41.2	42.5	41.8	39.8	41.2	39.1	38.5	39.1	39.8
87.5°	17.8	18.2	16.8	16.6	15.8	16.1	14.8	13.9	13.1	13.4	14.7
90°	13.4	12.5	11.3	10.1	8.9	7.6	6.3	5.0	3.6	2.2	0.8
92.5°	31.2	30.0	28.5	27.0	25.5	24.0	22.8	21.8	20.9	19.9	18.9
95°	61.4	60.2	58.5	56.7	55.0	53.3	52.2	51.9	51.5	51.2	50.8
97.5°	97.0	95.9	93.5	91.1	88.7	86.3	85.0	84.9	84.7	84.6	84.5
100°	121.2	119.6	117.4	115.1	112.9	110.6	109.5	109.5	109.5	109.5	109.5
102.5°	146.4	144.7	143.5	142.4	141.2	140.1	139.2	138.5	137.8	137.1	136.4
105°	187.9	186.9	185.8	184.8	183.8	182.7	181.8	180.9	180.0	179.2	178.3
107.5°	232.6	232.1	231.3	230.5	229.7	228.9	228.1	227.2	226.3	225.4	224.6
110°	263.3	262.7	262.2	261.7	261.2	260.7	260.0	259.1	258.2	257.4	256.5



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	294.3	294.0	293.4	292.7	292.0	291.4	290.8	290.4	289.9	289.5	289.0
115°	341.5	341.7	341.4	341.0	340.7	340.3	339.8	339.1	338.4	337.7	337.0
117.5°	388.1	388.0	387.7	387.4	387.1	386.8	386.4	386.1	385.8	385.5	385.2
120°	419.9	419.9	419.7	419.6	419.4	419.2	418.7	417.8	417.0	416.1	415.2
122.5°	451.0	451.2	450.7	450.3	449.8	449.4	449.0	448.7	448.4	448.1	447.7
125°	497.0	497.3	497.1	497.0	496.8	496.6	496.0	495.0	493.9	492.9	491.8
127.5°	542.2	542.4	542.2	541.9	541.7	541.5	541.1	540.5	539.9	539.4	538.8
130°	572.2	572.4	572.0	571.7	571.3	571.0	570.4	569.5	568.7	567.8	566.9
132.5°	601.0	601.2	601.2	601.3	601.4	601.4	600.8	599.3	597.9	596.5	595.1
135°	645.1	645.1	644.9	644.8	644.6	644.4	643.8	642.8	641.7	640.7	639.6
137.5°	688.0	687.8	687.4	687.0	686.7	686.3	685.6	684.6	683.6	682.6	681.6
140°	715.1	714.7	714.2	713.7	713.1	712.6	711.9	711.1	710.2	709.3	708.5
142.5°	741.8	741.6	740.9	740.3	739.6	739.0	738.3	737.5	736.8	736.1	735.4
145°	780.4	780.4	779.9	779.3	778.8	778.3	777.7	777.0	776.3	775.6	774.9
147.5°	815.5	815.1	814.7	814.3	813.9	813.4	813.0	812.7	812.3	811.9	811.5
150°	838.3	838.3	837.6	836.9	836.2	835.5	835.2	835.4	835.6	835.7	835.9
152.5°	858.7	858.3	858.0	857.7	857.4	857.2	856.9	856.7	856.4	856.2	855.9
155°	888.2	887.5	887.3	887.2	887.0	886.8	886.7	886.7	886.7	886.7	886.7
157.5°	914.0	913.3	913.1	913.0	912.8	912.6	912.7	913.1	913.5	913.9	914.3
160°	929.7	929.0	928.8	928.6	928.4	928.3	928.4	929.0	929.5	930.0	930.5
162.5°	944.2	943.4	943.3	943.3	943.2	943.2	943.4	943.8	944.1	944.5	944.9
165°	964.1	963.4	963.2	963.0	962.8	962.7	962.8	963.1	963.5	963.8	964.2
167.5°	978.3	977.3	977.3	977.3	977.3	977.3	977.6	978.3	979.0	979.7	980.4
170°	987.1	986.0	986.0	986.0	986.0	986.0	986.4	987.1	987.8	988.5	989.2
172.5°	993.3	992.3	992.3	992.3	992.3	992.3	992.6	993.3	994.0	994.7	995.4
175°	1000.4	999.3	999.3	999.3	999.3	999.3	999.7	1000.4	1001.1	1001.8	1002.5
177.5°	1003.8	1002.9	1003.1	1003.2	1003.4	1003.5	1003.8	1004.4	1005.0	1005.5	1006.1
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1598.8	1606.4	1611.2	1620.4	1628.0	1632.3	1636.1	1639.3	1643.1	1646.3	1655.5
5°	1609.1	1626.6	1641.5	1664.4	1685.4	1701.6	1719.1	1734.6	1747.4	1765.7	1779.8
7.5°	1604.6	1635.8	1668.5	1704.0	1740.3	1774.0	1805.1	1834.1	1860.4	1892.3	1920.2
10°	1600.3	1642.8	1684.7	1732.6	1781.9	1823.7	1862.9	1902.7	1931.7	1972.2	2006.6
12.5°	1597.1	1647.1	1697.6	1755.3	1809.4	1868.5	1920.6	1949.7	1993.8	2026.2	2067.1
15°	1583.4	1649.6	1719.1	1783.9	1860.8	1915.5	1961.4	2018.1	2059.3	2100.4	2145.0
17.5°	1559.0	1633.9	1711.7	1796.6	1870.4	1929.1	1988.3	2042.9	2092.1	2147.3	2202.8
20°	1547.7	1622.6	1711.7	1798.7	1871.0	1932.4	1993.1	2053.2	2107.2	2178.1	2242.2
22.5°	1523.9	1614.5	1696.6	1781.5	1855.8	1922.7	1991.5	2059.7	2131.5	2211.5	2291.9
25°	1481.5	1573.3	1660.4	1744.1	1819.0	1902.7	1976.3	2067.4	2159.2	2265.1	2365.0
27.5°	1437.5	1525.4	1605.2	1686.0	1773.4	1868.1	1963.6	2067.0	2187.1	2320.9	2461.8
30°	1401.9	1484.9	1562.5	1645.5	1736.6	1843.3	1947.9	2070.7	2209.8	2360.3	2527.7
32.5°	1360.3	1436.8	1512.3	1600.2	1699.4	1812.0	1933.9	2068.6	2235.7	2406.7	2579.0
35°	1289.2	1353.3	1430.9	1524.7	1636.8	1765.7	1906.7	2066.0	2257.7	2454.1	2599.2
37.5°	1204.8	1264.5	1346.3	1449.1	1566.6	1704.9	1872.3	2061.3	2264.9	2421.5	2468.3
40°	1148.1	1203.4	1288.5	1395.1	1515.3	1661.7	1845.3	2045.1	2242.2	2342.1	2303.6
42.5°	1087.6	1145.7	1228.5	1334.1	1463.4	1622.9	1811.3	2011.1	2176.3	2214.1	2081.1
45°	992.2	1052.2	1133.9	1240.6	1379.6	1552.4	1748.8	1930.4	2025.5	1957.4	1751.5
47.5°	903.5	959.8	1035.5	1145.5	1289.0	1467.7	1656.9	1801.7	1809.3	1646.6	1426.7
50°	843.0	895.0	971.3	1081.3	1223.7	1404.6	1575.3	1689.4	1638.1	1453.8	1242.6
52.5°	783.6	834.5	909.7	1018.6	1159.4	1325.2	1484.1	1564.1	1467.5	1278.4	1097.9
55°	697.9	742.4	816.0	916.6	1050.2	1204.1	1339.1	1366.8	1241.2	1054.9	908.5
57.5°	614.2	655.8	722.7	815.3	937.5	1073.8	1179.4	1173.5	1040.8	880.9	764.7
60°	557.5	598.0	657.4	747.8	859.2	976.7	1067.1	1045.5	913.9	776.2	678.3
62.5°	506.8	542.9	599.1	678.2	779.8	888.6	962.9	931.0	802.1	681.7	604.4
65°	432.0	462.3	510.3	577.8	662.1	751.9	809.3	768.1	658.1	564.3	502.2
67.5°	360.6	384.9	425.1	478.9	550.9	623.0	657.9	616.5	528.5	460.0	414.0
70°	315.2	336.8	367.8	415.8	478.5	539.3	565.6	528.5	452.9	394.2	361.1
72.5°	269.8	287.7	314.9	358.0	408.3	461.0	484.1	448.6	386.5	336.9	306.0
75°	208.6	220.7	239.6	269.3	309.1	351.0	363.8	332.8	292.9	255.8	235.6
77.5°	149.3	159.6	173.9	192.6	220.8	247.4	258.6	240.7	209.9	186.4	169.8
80°	114.7	120.1	132.3	147.8	170.1	187.0	194.4	182.9	161.3	143.8	130.9
82.5°	81.8	87.2	94.5	107.3	121.5	133.0	140.9	133.2	117.6	103.8	96.4
85°	39.8	43.2	47.2	52.6	63.4	70.2	69.5	64.8	58.7	53.3	49.3
87.5°	14.5	15.3	17.2	20.2	22.0	24.5	25.8	24.9	23.0	21.6	20.1
90°	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4	14.2
92.5°	19.9	20.9	21.8	22.8	24.0	25.5	27.0	28.5	30.0	31.2	32.3
95°	51.2	51.5	51.9	52.2	53.3	55.0	56.7	58.5	60.2	61.4	62.6
97.5°	84.6	84.7	84.9	85.0	86.3	88.7	91.1	93.5	95.9	97.0	98.2
100°	109.5	109.5	109.5	109.5	110.6	112.9	115.1	117.4	119.6	121.2	122.8
102.5°	137.1	137.8	138.5	139.2	140.1	141.2	142.4	143.5	144.7	146.4	148.1
105°	179.2	180.0	180.9	181.8	182.7	183.8	184.8	185.8	186.9	187.9	189.0
107.5°	225.4	226.3	227.2	228.1	228.9	229.7	230.5	231.3	232.1	232.6	233.1
110°	257.4	258.2	259.1	260.0	260.7	261.2	261.7	262.2	262.7	263.3	263.8





TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	289.5	289.9	290.4	290.8	291.4	292.0	292.7	293.4	294.0	294.3	294.5
115°	337.7	338.4	339.1	339.8	340.3	340.7	341.0	341.4	341.7	341.5	341.4
117.5°	385.5	385.8	386.1	386.4	386.8	387.1	387.4	387.7	388.0	388.1	388.3
120°	416.1	417.0	417.8	418.7	419.2	419.4	419.6	419.7	419.9	419.9	419.9
122.5°	448.1	448.4	448.7	449.0	449.4	449.8	450.3	450.7	451.2	451.0	450.9
125°	492.9	493.9	495.0	496.0	496.6	496.8	497.0	497.1	497.3	497.0	496.6
127.5°	539.4	539.9	540.5	541.1	541.5	541.7	541.9	542.2	542.4	542.2	542.0
130°	567.8	568.7	569.5	570.4	571.0	571.3	571.7	572.0	572.4	572.2	572.0
132.5°	596.5	597.9	599.3	600.8	601.4	601.4	601.3	601.2	601.2	601.0	600.8
135°	640.7	641.7	642.8	643.8	644.4	644.6	644.8	644.9	645.1	645.1	645.1
137.5°	682.6	683.6	684.6	685.6	686.3	686.7	687.0	687.4	687.8	688.0	688.2
140°	709.3	710.2	711.1	711.9	712.6	713.1	713.7	714.2	714.7	715.1	715.4
142.5°	736.1	736.8	737.5	738.3	739.0	739.6	740.3	740.9	741.6	741.8	742.0
145°	775.6	776.3	777.0	777.7	778.3	778.8	779.3	779.9	780.4	780.4	780.4
147.5°	811.9	812.3	812.7	813.0	813.4	813.9	814.3	814.7	815.1	815.5	815.9
150°	835.7	835.6	835.4	835.2	835.5	836.2	836.9	837.6	838.3	838.3	838.3
152.5°	856.2	856.4	856.7	856.9	857.2	857.4	857.7	858.0	858.3	858.7	859.1
155°	886.7	886.7	886.7	886.7	886.8	887.0	887.2	887.3	887.5	888.2	888.9
157.5°	913.9	913.5	913.1	912.7	912.6	912.8	913.0	913.1	913.3	914.0	914.7
160°	930.0	929.5	929.0	928.4	928.3	928.4	928.6	928.8	929.0	929.7	930.4
162.5°	944.5	944.1	943.8	943.4	943.2	943.2	943.3	943.3	943.4	944.2	945.0
165°	963.8	963.5	963.1	962.8	962.7	962.8	963.0	963.2	963.4	964.1	964.8
167.5°	979.7	979.0	978.3	977.6	977.3	977.3	977.3	977.3	977.3	978.3	979.4
170°	988.5	987.8	987.1	986.4	986.0	986.0	986.0	986.0	986.0	987.1	988.1
172.5°	994.7	994.0	993.3	992.6	992.3	992.3	992.3	992.3	992.3	993.3	994.4
175°	1001.8	1001.1	1000.4	999.7	999.3	999.3	999.3	999.3	999.3	1000.4	1001.4
177.5°	1005.5	1005.0	1004.4	1003.8	1003.5	1003.4	1003.2	1003.1	1002.9	1003.8	1004.6
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2	1590.2
2.5°	1663.1	1667.4	1676.6	1673.3	1677.7	1679.8	1682.0
5°	1797.4	1819.0	1828.4	1827.1	1841.3	1837.9	1834.5
7.5°	1949.1	1971.8	1984.5	2000.3	2009.5	2010.1	2018.1
10°	2035.0	2064.7	2076.8	2093.7	2104.5	2110.6	2109.9
12.5°	2100.9	2124.1	2151.3	2159.6	2174.2	2181.8	2179.0
15°	2180.1	2217.2	2245.6	2259.7	2278.0	2283.4	2290.8
17.5°	2250.8	2300.6	2333.7	2377.7	2394.3	2404.4	2398.5
20°	2304.3	2369.8	2402.8	2455.5	2484.5	2500.0	2494.6
22.5°	2367.5	2438.3	2499.5	2545.1	2589.2	2610.2	2614.5
25°	2475.7	2572.9	2662.7	2722.8	2777.4	2790.2	2818.6
27.5°	2596.7	2711.3	2807.3	2870.4	2908.5	2922.8	2931.7
30°	2672.8	2786.9	2859.1	2899.6	2911.7	2910.4	2909.0
32.5°	2710.1	2781.5	2795.4	2784.0	2756.2	2732.7	2708.2
35°	2657.3	2604.0	2524.3	2421.7	2346.1	2269.9	2262.4
37.5°	2389.9	2219.4	2086.8	1938.7	1853.3	1800.5	1764.1
40°	2138.2	1944.5	1783.9	1659.0	1572.0	1537.5	1503.8
42.5°	1865.0	1680.0	1537.7	1433.3	1367.9	1329.7	1302.9
45°	1515.3	1351.9	1240.6	1165.0	1113.0	1083.3	1066.4
47.5°	1241.6	1120.8	1026.2	971.7	935.8	912.7	912.8
50°	1094.8	979.4	916.6	873.4	842.3	824.1	827.5
52.5°	964.6	878.4	824.8	788.6	765.7	754.5	754.1
55°	806.6	744.5	709.4	683.1	667.5	654.7	657.4
57.5°	689.9	637.6	614.1	592.2	581.4	576.3	568.8
60°	617.6	577.1	556.8	539.3	528.5	524.4	517.0
62.5°	553.3	521.5	501.8	487.4	477.7	476.4	470.6
65°	465.0	440.7	423.2	416.4	406.3	403.6	403.6
67.5°	383.4	366.0	352.3	346.1	341.7	342.3	339.1
70°	332.1	317.9	309.1	302.4	299.0	299.7	297.0
72.5°	290.5	274.7	267.0	263.0	258.5	260.3	259.2
75°	220.0	211.9	207.9	203.8	201.1	199.8	198.4
77.5°	161.6	154.4	151.3	149.0	149.4	146.2	148.8
80°	124.9	118.8	116.8	113.4	112.7	112.7	112.0
82.5°	91.4	88.0	86.5	83.7	82.5	83.6	81.8
85°	47.2	44.5	43.9	43.9	42.5	41.2	44.5
87.5°	20.3	18.3	18.5	18.0	18.1	17.7	16.7
90°	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	33.5	34.6	35.4	35.8	36.1	36.5	36.9
95°	63.9	65.1	65.9	66.2	66.6	66.9	67.2
97.5°	99.3	100.5	101.1	101.3	101.5	101.8	102.0
100°	124.3	125.9	126.9	127.2	127.5	127.9	128.2
102.5°	149.8	151.5	152.6	153.1	153.5	154.0	154.5
105°	190.0	191.1	191.8	192.4	192.9	193.4	193.9
107.5°	233.6	234.2	234.4	234.4	234.3	234.3	234.3
110°	264.3	264.8	265.0	264.8	264.6	264.5	264.3



TEST NUMBER: P333269

CATALOG NUMBER: S125DIP-S1090D810U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	294.7	295.0	295.0	294.6	294.3	294.0	293.7
115°	341.2	341.0	340.8	340.7	340.5	340.3	340.2
117.5°	388.4	388.6	388.3	387.6	386.9	386.2	385.5
120°	419.9	419.9	419.6	418.9	418.2	417.5	416.8
122.5°	450.8	450.6	450.3	449.7	449.2	448.6	448.1
125°	496.3	495.9	495.7	495.5	495.3	495.2	495.0
127.5°	541.8	541.7	541.4	541.1	540.7	540.4	540.0
130°	571.9	571.7	571.4	571.1	570.7	570.4	570.0
132.5°	600.6	600.5	600.1	599.7	599.2	598.7	598.2
135°	645.1	645.1	644.8	644.1	643.4	642.7	642.0
137.5°	688.4	688.6	688.3	687.4	686.6	685.7	684.8
140°	715.7	716.1	715.8	715.0	714.1	713.2	712.4
142.5°	742.2	742.4	742.1	741.2	740.4	739.5	738.6
145°	780.4	780.4	780.1	779.6	779.1	778.6	778.0
147.5°	816.4	816.8	816.4	815.2	814.0	812.9	811.7
150°	838.3	838.3	838.1	837.7	837.4	837.0	836.7
152.5°	859.5	859.9	859.8	859.2	858.6	858.0	857.3
155°	889.6	890.3	890.2	889.3	888.5	887.6	886.7
157.5°	915.4	916.1	915.9	914.7	913.6	912.4	911.3
160°	931.0	931.7	931.7	930.8	929.9	929.0	928.2
162.5°	945.9	946.7	946.6	945.6	944.6	943.6	942.6
165°	965.5	966.1	966.0	964.9	963.9	962.8	961.8
167.5°	980.4	981.5	981.4	980.4	979.3	978.2	977.1
170°	989.2	990.2	990.1	988.9	987.7	986.5	985.3
172.5°	995.4	996.5	996.5	995.4	994.3	993.2	992.1
175°	1002.5	1003.5	1003.4	1002.2	1001.0	999.8	998.6
177.5°	1005.4	1006.3	1006.2	1005.2	1004.3	1003.3	1002.3
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8

(END OF REPORT)