

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332911-940

Luminaire Tested: **S124RDIP-S575D810U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332911-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIP-S575D810U940-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4597.3 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332911-940

CATALOG NUMBER: S124RDIP-S575D810U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332911-940

CATALOG NUMBER: S124RDIP-S575D810U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	37	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	35	30	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	31	26	46	35	29	24	30	25	21	26	21	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P332911-940

CATALOG NUMBER: S124RDIP-S575D810U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	1.9
10°-20°	237.4	5.2
20°-30°	342.8	7.5
30°-40°	388.6	8.5
40°-50°	375.2	8.2
50°-60°	312.0	6.8
60°-70°	215.4	4.7
70°-80°	109.2	2.4
80°-90°	30.7	0.7
90°-100°	59.5	1.3
100°-110°	176.1	3.8
110°-120°	298.9	6.5
120°-130°	394.2	8.6
130°-140°	442.7	9.6
140°-150°	435.0	9.5
150°-160°	365.9	8.0
160°-170°	243.4	5.3
170°-180°	85.2	1.9
0°-30°	665.3	14.5
0°-40°	1053.9	22.9
0°-60°	1741.1	37.9
0°-90°	2096.4	45.6
90°-120°	534.5	11.6
90°-150°	1806.3	39.3
90°-180°	2501.0	54.4
0°-180°	4597.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	2	10	15	19	21	4
95°	42	48	53	55	55	47
105°	162	163	166	168	170	172
115°	304	304	303	302	301	300
125°	443	443	442	441	439	394
135°	571	575	575	574	572	442
145°	694	696	697	696	694	434
155°	795	795	794	796	794	366
165°	865	863	862	865	863	244
175°	900	897	896	900	896	85
180°	901	901	901	901	901	



TEST NUMBER: P332911-940

CATALOG NUMBER: S124RDIP-S575D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	13.2	12.6	11.9	11.2	10.6	10.3	10.4	10.6	10.7	10.9	10.9
90°	2.1	3.8	5.5	7.2	8.9	10.3	11.6	12.8	14.1	15.3	16.2
92.5°	14.9	16.9	18.8	20.8	22.7	24.2	25.0	25.9	26.8	27.6	28.2
95°	41.8	43.2	44.6	46.0	47.4	48.7	49.8	50.8	51.9	53.0	53.4
97.5°	73.0	74.2	75.3	76.4	77.5	78.7	80.0	81.2	82.5	83.8	84.4
100°	97.6	98.2	98.8	99.4	100.0	101.1	102.5	103.9	105.2	106.6	107.0
102.5°	123.2	123.5	123.8	124.0	124.2	125.0	126.3	127.5	128.9	130.1	130.5
105°	162.5	162.6	162.7	162.9	163.1	163.5	164.1	164.7	165.3	165.9	166.4
107.5°	203.6	203.8	203.9	204.1	204.3	204.5	204.6	204.6	204.7	204.8	205.3
110°	231.5	231.8	232.0	232.4	232.6	232.7	232.6	232.5	232.3	232.1	231.8



TEST NUMBER: P332911-940

CATALOG NUMBER: S124RDIP-S575D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.5	260.5	260.6	260.6	260.7	260.6	260.3	260.0	259.8	259.5	259.4
115°	304.0	304.0	304.0	304.0	304.0	303.8	303.4	303.2	302.8	302.6	302.4
117.5°	344.9	345.1	345.2	345.3	345.4	345.4	345.2	344.9	344.7	344.6	344.0
120°	372.3	372.9	373.5	374.2	374.8	374.8	374.3	373.9	373.4	373.0	372.2
122.5°	400.7	400.9	401.2	401.4	401.7	401.7	401.5	401.3	401.1	400.8	400.3
125°	442.6	442.6	442.6	442.6	442.6	442.6	442.5	442.3	442.1	442.0	441.7
127.5°	480.7	481.2	481.7	482.1	482.6	482.7	482.4	482.2	482.0	481.7	481.4
130°	507.5	508.0	508.5	508.9	509.3	509.6	509.6	509.6	509.6	509.6	509.3
132.5°	534.8	535.2	535.6	535.8	536.2	536.3	536.2	536.1	535.9	535.8	535.5
135°	571.0	571.9	572.8	573.7	574.7	575.2	575.2	575.2	575.2	575.2	574.8
137.5°	610.3	610.7	611.1	611.5	612.0	612.3	612.6	612.9	613.1	613.3	613.0
140°	636.5	636.8	637.1	637.4	637.8	637.8	637.8	637.8	637.8	637.8	637.8
142.5°	660.5	660.8	661.1	661.4	661.7	661.8	661.6	661.6	661.4	661.3	661.3
145°	693.7	694.3	694.9	695.5	696.2	696.5	696.7	696.8	697.0	697.1	697.0
147.5°	726.6	727.3	728.0	728.8	729.5	729.9	729.7	729.6	729.4	729.3	729.2
150°	746.6	747.3	747.9	748.5	749.1	749.4	749.4	749.4	749.4	749.4	749.4
152.5°	765.6	766.0	766.3	766.7	767.0	767.3	767.4	767.6	767.7	767.9	768.2
155°	794.7	794.7	794.7	794.7	794.7	794.6	794.5	794.3	794.2	794.1	794.6
157.5°	819.3	818.9	818.7	818.4	818.1	818.0	818.0	818.0	817.9	817.9	818.3
160°	833.7	833.6	833.5	833.3	833.1	832.9	832.9	832.7	832.5	832.4	832.9
162.5°	847.1	846.8	846.3	846.0	845.5	845.3	845.1	845.0	844.8	844.6	845.5
165°	865.1	864.7	864.2	863.7	863.3	862.9	862.6	862.3	861.9	861.7	862.6
167.5°	879.0	878.2	877.6	877.0	876.4	876.0	876.0	876.1	876.1	876.1	877.1
170°	886.7	886.0	885.2	884.4	883.7	883.3	883.5	883.7	883.8	884.0	884.8
172.5°	892.3	891.7	891.0	890.4	889.7	889.4	889.5	889.5	889.5	889.6	890.6
175°	900.0	899.2	898.4	897.7	896.9	896.4	896.3	896.1	896.0	895.8	896.9
177.5°	902.5	901.9	901.3	900.6	900.0	899.7	899.7	899.7	899.7	899.7	900.5
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3



TEST NUMBER: P332911-940

CATALOG NUMBER: S124RDIP-S575D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	11.0	11.1	11.1	11.2	11.4	11.6	11.8	11.9
90°	17.2	18.1	19.1	19.7	20.0	20.3	20.6	21.0
92.5°	28.7	29.2	29.9	30.2	30.4	30.6	30.8	30.9
95°	53.9	54.4	54.8	55.1	55.1	55.1	55.1	55.1
97.5°	84.9	85.4	86.1	86.3	86.3	86.3	86.3	86.3
100°	107.3	107.6	107.9	108.1	108.1	108.1	108.1	108.1
102.5°	131.0	131.3	131.8	132.1	132.2	132.3	132.5	132.6
105°	166.8	167.3	167.7	168.3	168.7	169.2	169.6	170.1
107.5°	205.7	206.1	206.5	206.8	206.7	206.7	206.7	206.6
110°	231.5	231.2	230.9	231.0	231.5	231.9	232.4	232.8



TEST NUMBER: P332911-940

CATALOG NUMBER: S124RDIP-S575D810U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	259.3	259.3	259.2	259.2	259.3	259.4	259.5	259.6
115°	302.2	302.1	301.9	301.8	301.7	301.5	301.3	301.1
117.5°	343.5	343.0	342.4	342.0	341.7	341.3	341.1	340.7
120°	371.4	370.6	369.9	369.6	370.0	370.2	370.6	370.9
122.5°	399.8	399.3	398.8	398.2	397.6	397.1	396.5	396.0
125°	441.4	441.0	440.8	440.4	440.1	439.8	439.5	439.2
127.5°	481.1	480.8	480.5	480.2	479.9	479.7	479.5	479.2
130°	509.0	508.6	508.4	507.9	507.3	506.7	506.0	505.4
132.5°	535.2	534.8	534.6	534.3	534.0	533.8	533.5	533.3
135°	574.5	574.2	573.9	573.5	573.0	572.6	572.1	571.7
137.5°	612.5	612.2	611.7	611.5	611.6	611.7	611.8	612.0
140°	637.6	637.4	637.2	637.1	636.9	636.8	636.6	636.5
142.5°	661.2	661.2	661.2	661.1	661.1	661.1	661.0	661.0
145°	696.8	696.7	696.5	696.2	695.7	695.3	694.8	694.4
147.5°	729.1	729.0	728.8	728.7	728.5	728.3	728.3	728.1
150°	749.4	749.4	749.4	749.3	749.2	749.0	748.9	748.7
152.5°	768.6	768.9	769.3	769.3	768.9	768.5	768.1	767.7
155°	795.2	795.9	796.5	796.5	795.9	795.2	794.6	794.1
157.5°	818.8	819.3	819.7	819.7	819.2	818.7	818.1	817.6
160°	833.3	833.7	834.2	834.1	833.3	832.5	831.8	831.0
162.5°	846.3	847.1	848.0	848.0	847.2	846.5	845.7	844.9
165°	863.5	864.4	865.4	865.5	864.9	864.2	863.6	863.1
167.5°	878.0	879.0	879.9	879.9	878.9	877.9	877.0	876.0
170°	885.8	886.7	887.7	887.6	886.5	885.5	884.3	883.2
172.5°	891.6	892.7	893.8	893.8	892.7	891.5	890.5	889.4
175°	898.0	899.0	900.2	900.2	899.0	898.0	896.9	895.8
177.5°	901.4	902.3	903.2	903.1	902.1	901.2	900.2	899.1
180°	901.3	901.3	901.3	901.3	901.3	901.3	901.3	901.3

(END OF REPORT)