

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333311

Luminaire Tested: **S125DIP-S1270D590U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333311
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D590U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7175.3 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333311

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333311

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	71
1	103	98	94	90	97	93	89	86	84	81	78	75	73	71	67	65	64	60
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	50
3	85	75	68	61	80	72	65	59	65	59	54	58	54	50	52	49	46	42
4	78	67	58	52	74	63	56	50	57	51	47	52	47	43	47	43	39	36
5	72	60	51	45	68	57	49	43	51	45	40	47	41	37	42	38	34	32
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30	28
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12727	12727	12727
5°	12756	12635	12716
10°	12679	12545	12618
15°	12541	12395	12447
20°	12344	12183	12205
25°	12133	11932	11921
30°	11872	11662	11604
35°	11591	11371	11211
40°	11304	11054	10897
45°	10993	10766	10552
50°	10652	10417	10104
55°	10323	10025	9743
60°	9928	9627	9285
65°	9459	9149	8839
70°	9009	8597	8303
75°	8210	7938	7663
80°	7305	7189	7018
85°	6358	6469	6121



TEST NUMBER: P333311

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.8	2.6
10°-20°	524.9	7.3
20°-30°	775.0	10.8
30°-40°	904.3	12.6
40°-50°	908.3	12.7
50°-60°	797.3	11.1
60°-70°	594.1	8.3
70°-80°	339.7	4.7
80°-90°	100.4	1.4
90°-100°	49.1	0.7
100°-110°	145.0	2.0
110°-120°	245.6	3.4
120°-130°	323.2	4.5
130°-140°	362.1	5.0
140°-150°	354.9	4.9
150°-160°	298.1	4.2
160°-170°	198.2	2.8
170°-180°	69.4	1.0
0°-30°	1485.7	20.7
0°-40°	2390.0	33.3
0°-60°	4095.6	57.1
0°-90°	5129.8	71.5
90°-120°	439.7	6.1
90°-150°	1479.9	20.6
90°-180°	2046.0	28.5
0°-180°	7175.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1968	1964	1949	1962	1961	187
15°	1876	1870	1854	1861	1862	528
25°	1703	1694	1674	1677	1673	783
35°	1470	1463	1442	1434	1422	919
45°	1204	1197	1179	1161	1155	927
55°	917	911	890	876	865	818
65°	619	615	599	585	578	614
75°	329	326	318	313	307	351
85°	86	87	87	86	83	96
90°	1	5	9	12	14	7
95°	37	38	44	48	49	40
105°	130	133	136	140	142	139
115°	246	248	249	249	248	243
125°	359	362	363	362	361	321
135°	467	470	471	470	468	360
145°	565	568	569	569	568	353
155°	647	647	648	650	647	298
165°	703	702	703	705	702	198
175°	731	729	729	732	728	69
180°	733	733	733	733	733	



TEST NUMBER: P333311

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1975.7	1974.9	1974.1	1973.2	1972.4	1970.6	1967.8	1965.0	1962.3	1959.5	1962.3
5°	1967.6	1966.9	1966.2	1965.5	1964.8	1962.8	1959.3	1955.8	1952.4	1948.9	1952.0
7.5°	1949.5	1948.8	1948.1	1947.4	1946.7	1944.5	1940.7	1936.9	1933.1	1929.3	1932.3
10°	1933.3	1932.6	1931.9	1931.2	1930.5	1928.3	1924.5	1920.7	1916.8	1913.0	1915.8
12.5°	1913.3	1912.1	1910.9	1909.6	1908.4	1906.0	1902.4	1898.9	1895.4	1891.8	1894.1
15°	1875.6	1874.6	1873.5	1872.5	1871.5	1869.0	1865.2	1861.4	1857.6	1853.8	1855.5
17.5°	1832.3	1830.8	1829.2	1827.7	1826.2	1823.4	1819.5	1815.5	1811.6	1807.6	1809.8
20°	1796.1	1795.4	1794.7	1794.0	1793.3	1790.7	1786.2	1781.7	1777.2	1772.7	1775.1
22.5°	1759.9	1758.7	1757.4	1756.2	1754.9	1752.2	1748.0	1743.8	1739.5	1735.3	1736.9
25°	1702.6	1700.8	1699.1	1697.4	1695.6	1692.5	1688.0	1683.5	1679.0	1674.5	1675.2
27.5°	1635.5	1634.5	1633.4	1632.4	1631.4	1628.5	1623.9	1619.2	1614.6	1609.9	1610.1
30°	1591.9	1590.8	1589.8	1588.7	1587.7	1584.6	1579.4	1574.2	1569.0	1563.8	1563.1
32.5°	1544.5	1542.9	1541.3	1539.7	1538.1	1535.0	1530.3	1525.7	1521.0	1516.4	1515.2
35°	1470.2	1468.9	1467.5	1466.1	1464.7	1461.6	1456.7	1451.9	1447.0	1442.2	1440.5
37.5°	1393.2	1391.5	1389.8	1388.0	1386.3	1383.1	1378.6	1374.0	1369.4	1364.9	1362.3
40°	1340.8	1339.1	1337.4	1335.6	1333.9	1330.6	1325.8	1320.9	1316.1	1311.2	1308.1
42.5°	1284.7	1283.3	1281.8	1280.3	1278.9	1275.7	1270.9	1266.0	1261.2	1256.3	1253.5
45°	1203.6	1202.3	1200.9	1199.5	1198.1	1195.3	1191.2	1187.0	1182.9	1178.7	1174.5
47.5°	1116.3	1116.4	1116.5	1116.5	1116.6	1114.1	1109.2	1104.2	1099.2	1094.2	1090.0
50°	1060.2	1059.2	1058.1	1057.1	1056.0	1053.4	1049.3	1045.1	1041.0	1036.8	1032.3
52.5°	1002.8	1002.1	1001.3	1000.5	999.8	997.2	992.7	988.3	983.9	979.4	975.5
55°	916.8	915.7	914.7	913.6	912.6	909.7	904.8	900.0	895.1	890.3	887.1
57.5°	826.0	825.5	824.9	824.4	823.8	821.5	817.4	813.3	809.2	805.1	801.1
60°	768.6	767.3	765.9	764.5	763.1	760.5	756.7	752.9	749.1	745.3	741.8
62.5°	708.8	707.7	706.6	705.4	704.3	702.2	698.9	695.6	692.4	689.1	685.4
65°	619.0	618.3	617.6	616.9	616.2	613.9	610.1	606.3	602.5	598.7	595.6
67.5°	532.0	530.5	529.1	527.6	526.2	524.0	521.2	518.3	515.5	512.6	510.0
70°	477.1	475.4	473.6	471.9	470.2	467.7	464.6	461.5	458.4	455.3	453.2
72.5°	417.2	416.0	414.9	413.7	412.5	410.9	408.9	406.9	404.9	402.9	400.5
75°	329.0	328.3	327.6	326.9	326.2	325.0	323.3	321.5	319.8	318.1	317.0
77.5°	247.6	247.3	247.0	246.8	246.5	245.9	244.9	243.9	242.9	242.0	241.4
80°	196.4	196.4	196.4	196.4	196.4	196.1	195.4	194.7	194.0	193.3	193.0
82.5°	151.5	151.0	150.4	149.9	149.3	149.0	148.8	148.7	148.6	148.4	147.8
85°	85.8	86.1	86.4	86.8	87.1	87.3	87.3	87.3	87.3	87.3	87.0
87.5°	33.8	34.0	34.2	34.4	34.6	34.7	34.6	34.5	34.4	34.3	34.4
90°	0.6	1.6	2.6	3.6	4.6	5.6	6.5	7.4	8.2	9.1	9.8
92.5°	13.8	14.5	15.2	15.9	16.6	17.5	18.6	19.7	20.8	21.9	22.7
95°	37.1	37.3	37.6	37.8	38.1	38.9	40.1	41.4	42.7	43.9	44.8
97.5°	61.6	61.7	61.8	61.9	62.0	62.9	64.7	66.4	68.2	69.9	70.8
100°	79.9	79.9	79.9	79.9	79.9	80.7	82.3	84.0	85.6	87.3	88.4
102.5°	99.5	100.0	100.5	101.0	101.5	102.2	103.0	103.9	104.7	105.5	106.8
105°	130.1	130.7	131.3	132.0	132.6	133.3	134.1	134.8	135.6	136.3	137.1
107.5°	163.8	164.5	165.1	165.7	166.4	167.0	167.6	168.1	168.7	169.3	169.7
110°	187.1	187.7	188.4	189.0	189.7	190.2	190.5	190.9	191.3	191.7	192.1



TEST NUMBER: P333311

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	210.8	211.2	211.5	211.8	212.2	212.6	213.1	213.5	214.0	214.5	214.7
115°	245.9	246.4	246.9	247.4	247.9	248.3	248.5	248.8	249.0	249.3	249.2
117.5°	281.0	281.2	281.5	281.7	281.9	282.2	282.4	282.6	282.8	283.1	283.2
120°	302.9	303.6	304.2	304.8	305.5	305.8	306.0	306.1	306.2	306.3	306.3
122.5°	326.7	326.9	327.1	327.3	327.6	327.8	328.2	328.5	328.8	329.2	329.1
125°	358.8	359.6	360.3	361.1	361.9	362.3	362.4	362.6	362.7	362.8	362.6
127.5°	393.1	393.5	393.9	394.3	394.8	395.1	395.2	395.4	395.5	395.7	395.6
130°	413.6	414.2	414.9	415.5	416.1	416.6	416.8	417.1	417.3	417.6	417.5
132.5°	434.1	435.2	436.2	437.2	438.3	438.8	438.7	438.7	438.6	438.6	438.5
135°	466.6	467.4	468.2	468.9	469.7	470.1	470.3	470.4	470.5	470.6	470.6
137.5°	497.2	498.0	498.7	499.4	500.2	500.7	501.0	501.2	501.5	501.8	501.9
140°	516.8	517.5	518.1	518.7	519.4	519.9	520.3	520.7	521.0	521.4	521.7
142.5°	536.5	537.0	537.5	538.1	538.6	539.1	539.6	540.1	540.6	541.0	541.2
145°	565.3	565.8	566.4	566.9	567.4	567.8	568.2	568.6	569.0	569.3	569.3
147.5°	592.0	592.3	592.6	592.9	593.2	593.4	593.7	594.1	594.4	594.7	595.0
150°	609.8	609.7	609.6	609.5	609.3	609.5	610.0	610.5	611.0	611.5	611.5
152.5°	624.4	624.6	624.8	625.0	625.1	625.3	625.5	625.7	625.9	626.2	626.5
155°	646.9	646.9	646.9	646.9	646.9	647.0	647.1	647.2	647.4	647.5	648.0
157.5°	667.0	666.7	666.4	666.2	665.9	665.8	665.9	666.1	666.2	666.3	666.8
160°	678.9	678.5	678.1	677.7	677.3	677.2	677.3	677.5	677.6	677.7	678.2
162.5°	689.4	689.1	688.8	688.5	688.2	688.1	688.1	688.2	688.2	688.2	688.8
165°	703.4	703.1	702.9	702.6	702.4	702.3	702.4	702.6	702.7	702.8	703.3
167.5°	715.3	714.8	714.2	713.7	713.2	713.0	713.0	713.0	713.0	713.0	713.7
170°	721.6	721.1	720.6	720.1	719.6	719.4	719.4	719.4	719.4	719.4	720.1
172.5°	726.2	725.7	725.2	724.7	724.2	723.9	723.9	723.9	723.9	723.9	724.7
175°	731.3	730.8	730.3	729.8	729.3	729.1	729.1	729.1	729.1	729.1	729.8
177.5°	734.0	733.6	733.2	732.8	732.3	732.1	732.0	731.9	731.8	731.7	732.3
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1



TEST NUMBER: P333311

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1965.0	1967.8	1970.6	1971.8	1971.6	1971.3	1971.0	1970.7
5°	1955.1	1958.3	1961.4	1962.8	1962.4	1962.1	1961.7	1961.4
7.5°	1935.3	1938.4	1941.4	1942.8	1942.5	1942.1	1941.8	1941.4
10°	1918.6	1921.4	1924.1	1925.3	1925.0	1924.6	1924.3	1924.0
12.5°	1896.3	1898.5	1900.7	1901.8	1901.7	1901.6	1901.6	1901.5
15°	1857.3	1859.0	1860.7	1861.6	1861.6	1861.6	1861.6	1861.6
17.5°	1811.9	1814.1	1816.2	1816.4	1814.7	1813.0	1811.2	1809.5
20°	1777.6	1780.0	1782.4	1782.8	1781.0	1779.3	1777.6	1775.8
22.5°	1738.5	1740.1	1741.7	1741.9	1740.7	1739.5	1738.3	1737.2
25°	1675.9	1676.6	1677.3	1677.1	1676.1	1675.0	1674.0	1672.9
27.5°	1610.2	1610.4	1610.5	1610.0	1609.0	1608.0	1606.9	1605.9
30°	1562.4	1561.7	1561.0	1560.2	1559.1	1558.1	1557.0	1556.0
32.5°	1513.9	1512.7	1511.4	1509.8	1508.0	1506.1	1504.2	1502.4
35°	1438.7	1437.0	1435.3	1433.0	1430.2	1427.5	1424.7	1421.9
37.5°	1359.7	1357.2	1354.6	1352.5	1350.9	1349.3	1347.7	1346.1
40°	1305.0	1301.9	1298.7	1296.7	1295.6	1294.6	1293.5	1292.5
42.5°	1250.7	1247.8	1245.0	1242.8	1241.2	1239.6	1238.0	1236.4
45°	1170.4	1166.2	1162.1	1159.5	1158.4	1157.4	1156.3	1155.3
47.5°	1085.7	1081.5	1077.3	1074.0	1071.5	1069.1	1066.7	1064.3
50°	1027.8	1023.3	1018.8	1015.3	1012.9	1010.5	1008.1	1005.6
52.5°	971.5	967.6	963.6	960.3	957.6	954.9	952.2	949.5
55°	884.0	880.9	877.8	875.0	872.6	870.2	867.7	865.3
57.5°	797.1	793.1	789.1	786.4	785.1	783.8	782.4	781.1
60°	738.3	734.9	731.4	728.5	726.0	723.6	721.2	718.8
62.5°	681.6	677.9	674.2	671.4	669.5	667.6	665.7	663.9
65°	592.5	589.3	586.2	584.0	582.6	581.2	579.8	578.4
67.5°	507.4	504.7	502.1	500.4	499.5	498.7	497.9	497.0
70°	451.1	449.0	446.9	445.2	443.8	442.4	441.1	439.7
72.5°	398.2	395.8	393.5	391.6	390.2	388.8	387.4	386.0
75°	316.0	314.9	313.9	312.7	311.3	309.9	308.5	307.1
77.5°	240.7	240.1	239.5	238.7	237.7	236.7	235.8	234.8
80°	192.6	192.3	191.9	191.4	190.7	190.0	189.3	188.7
82.5°	147.2	146.6	145.9	145.6	145.4	145.3	145.1	145.0
85°	86.6	86.3	85.9	85.4	84.7	84.0	83.3	82.6
87.5°	34.5	34.6	34.8	34.6	34.1	33.6	33.2	32.7
90°	10.4	11.0	11.7	12.2	12.6	12.9	13.3	13.7
92.5°	23.6	24.4	25.3	25.8	26.1	26.4	26.6	26.9
95°	45.7	46.6	47.5	48.0	48.3	48.6	48.8	49.1
97.5°	71.6	72.5	73.3	73.8	73.9	74.1	74.2	74.4
100°	89.6	90.7	91.8	92.5	92.8	93.1	93.3	93.6
102.5°	108.0	109.3	110.5	111.3	111.7	112.0	112.4	112.7
105°	137.9	138.6	139.4	140.0	140.3	140.7	141.1	141.5
107.5°	170.1	170.5	170.8	171.0	171.0	171.0	170.9	170.9
110°	192.4	192.8	193.2	193.3	193.2	193.1	192.9	192.8



TEST NUMBER: P333311

CATALOG NUMBER: S125DIP-S1270D590U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	214.9	215.0	215.2	215.2	215.0	214.7	214.5	214.3
115°	249.0	248.9	248.8	248.7	248.5	248.4	248.3	248.2
117.5°	283.3	283.4	283.5	283.3	282.8	282.3	281.8	281.2
120°	306.3	306.3	306.3	306.1	305.6	305.1	304.6	304.1
122.5°	329.0	328.9	328.8	328.5	328.1	327.7	327.3	326.9
125°	362.3	362.1	361.8	361.6	361.5	361.4	361.2	361.1
127.5°	395.4	395.3	395.2	395.0	394.7	394.5	394.2	394.0
130°	417.3	417.2	417.1	416.9	416.6	416.4	416.1	415.9
132.5°	438.3	438.2	438.1	437.8	437.5	437.1	436.8	436.4
135°	470.6	470.6	470.6	470.4	469.9	469.4	468.9	468.4
137.5°	502.1	502.2	502.4	502.2	501.5	500.9	500.3	499.6
140°	521.9	522.2	522.4	522.2	521.6	521.0	520.3	519.7
142.5°	541.3	541.5	541.6	541.4	540.8	540.1	539.5	538.9
145°	569.3	569.3	569.3	569.1	568.8	568.4	568.0	567.6
147.5°	595.3	595.6	595.9	595.6	594.7	593.9	593.0	592.2
150°	611.5	611.5	611.5	611.4	611.2	610.9	610.7	610.4
152.5°	626.8	627.1	627.4	627.3	626.8	626.4	625.9	625.5
155°	648.5	649.0	649.5	649.5	648.8	648.2	647.5	646.9
157.5°	667.3	667.8	668.3	668.2	667.3	666.5	665.7	664.8
160°	678.7	679.2	679.7	679.7	679.1	678.4	677.8	677.2
162.5°	689.4	690.0	690.7	690.6	689.9	689.1	688.4	687.6
165°	703.8	704.3	704.9	704.7	704.0	703.2	702.4	701.7
167.5°	714.5	715.3	716.0	716.0	715.2	714.4	713.6	712.9
170°	720.9	721.6	722.4	722.3	721.5	720.6	719.7	718.8
172.5°	725.5	726.2	727.0	727.0	726.2	725.4	724.6	723.8
175°	730.6	731.3	732.1	732.0	731.2	730.3	729.4	728.5
177.5°	732.9	733.5	734.1	734.1	733.4	732.7	731.9	731.2
180°	733.1	733.1	733.1	733.1	733.1	733.1	733.1	733.1

(END OF REPORT)