

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333313

Luminaire Tested: **S125DIP-S1270D810U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333313  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1270D810U835-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8424.3 lumens  
Efficiency: N/A  
Efficacy: 138.8 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	96	93	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	50	48	44
3	84	74	67	61	78	70	64	58	62	57	52	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	45	38	34	39	34	31	34	31	28	25
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	28	25	22
8	56	44	36	30	52	41	34	29	37	31	27	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11861	11861	11861	11861
5°	13736	11902	10421	11902
10°	15980	11840	9130	11840
15°	17690	11753	8423	11753
20°	19801	11615	7854	11615
25°	23197	11460	7577	11460
30°	25055	11307	7337	11307
35°	20601	11020	7179	11020
40°	14643	10620	7006	10620
45°	11249	10082	6906	10082
50°	9602	9414	6893	9414
55°	8550	8760	6952	8760
60°	7713	8045	7129	8045
65°	7124	7326	7314	7326
70°	6477	6579	7419	6579
75°	5719	5797	7354	5797
80°	4813	4727	6724	4727
85°	3809	3409	5432	3409



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.8	2.1
10°-20°	526.4	6.2
20°-30°	854.8	10.1
30°-40°	1042.7	12.4
40°-50°	948.5	11.3
50°-60°	755.5	9.0
60°-70°	526.2	6.2
70°-80°	280.6	3.3
80°-90°	73.0	0.9
90°-100°	38.3	0.5
100°-110°	236.3	2.8
110°-120°	428.5	5.1
120°-130°	550.0	6.5
130°-140°	591.5	7.0
140°-150°	555.2	6.6
150°-160°	449.1	5.3
160°-170°	290.5	3.4
170°-180°	100.2	1.2
0°-30°	1558.0	18.5
0°-40°	2600.7	30.9
0°-60°	4304.7	51.1
0°-90°	5184.6	61.5
90°-120°	703.1	8.3
90°-150°	2399.9	28.5
90°-180°	3240.0	38.5
0°-180°	8424.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1837	1837	1837	1837	1837	
5°	2119	1836	1607	1836	2119	214
15°	2646	1758	1260	1758	2646	757
25°	3255	1608	1063	1608	3255	1487
35°	2613	1398	910	1398	2613	1599
45°	1232	1104	756	1104	1232	986
55°	759	778	617	778	759	684
65°	466	479	479	479	466	463
75°	229	232	295	232	229	247
85°	51	46	73	46	51	60
90°	19	1	19	1	19	10
95°	16	45	16	45	16	14
105°	232	230	232	230	232	210
115°	429	432	429	432	429	425
125°	614	614	614	614	614	546
135°	762	766	762	766	762	588
145°	885	888	885	888	885	553
155°	970	978	970	978	970	447
165°	1026	1032	1026	1032	1026	290
175°	1050	1055	1050	1055	1050	100
180°	1055	1055	1055	1055	1055	



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1942.6	1940.1	1937.6	1932.6	1936.3	1925.7	1920.7	1912.0	1901.4	1897.7	1893.3
5°	2118.7	2122.6	2126.5	2110.2	2111.7	2100.8	2075.9	2055.6	2039.2	2018.2	2003.4
7.5°	2330.8	2321.6	2320.8	2310.2	2292.0	2277.3	2251.1	2217.7	2185.5	2148.7	2118.3
10°	2436.8	2437.6	2430.6	2418.1	2398.6	2384.6	2350.3	2317.5	2277.8	2231.0	2197.5
12.5°	2516.6	2519.9	2511.0	2494.2	2484.6	2453.2	2426.3	2387.4	2340.1	2302.7	2251.7
15°	2645.7	2637.1	2630.9	2609.8	2593.5	2560.7	2517.9	2477.3	2425.9	2378.3	2330.8
17.5°	2770.1	2777.0	2765.3	2746.1	2695.3	2657.1	2599.6	2544.0	2480.0	2416.2	2359.5
20°	2881.1	2887.4	2869.4	2835.9	2775.1	2736.9	2661.3	2589.6	2515.5	2433.7	2371.3
22.5°	3019.6	3014.6	2990.4	2939.4	2886.7	2816.1	2734.3	2646.9	2554.2	2461.7	2378.8
25°	3255.3	3222.5	3207.7	3144.6	3075.2	2971.5	2859.3	2731.4	2616.1	2493.7	2387.7
27.5°	3385.9	3375.6	3359.1	3315.2	3242.2	3131.3	2999.0	2843.2	2680.5	2526.0	2387.2
30°	3359.7	3361.3	3362.9	3348.8	3302.1	3218.6	3086.9	2919.3	2726.0	2552.2	2391.6
32.5°	3127.8	3156.1	3183.3	3215.4	3228.5	3212.4	3129.9	2978.6	2779.6	2582.1	2389.1
35°	2613.0	2621.5	2709.6	2796.9	2915.4	3007.4	3069.0	3001.9	2834.3	2607.5	2386.1
37.5°	2037.4	2079.5	2140.4	2239.1	2410.1	2563.2	2760.1	2850.7	2796.6	2615.8	2380.7
40°	1736.8	1775.8	1815.5	1916.1	2060.3	2245.8	2469.5	2660.5	2704.9	2589.6	2362.0
42.5°	1504.8	1535.7	1579.8	1655.4	1775.9	1940.2	2154.0	2403.6	2557.1	2513.5	2322.7
45°	1231.6	1251.1	1285.4	1345.5	1432.8	1561.4	1750.0	2022.9	2260.6	2339.3	2229.4
47.5°	1054.2	1054.1	1080.7	1122.2	1185.2	1294.5	1434.0	1647.8	1901.7	2089.6	2080.9
50°	955.7	951.8	972.8	1008.7	1058.6	1131.1	1264.4	1435.1	1679.1	1891.9	1951.1
52.5°	870.9	871.3	884.3	910.8	952.6	1014.5	1114.1	1268.0	1476.4	1694.8	1806.5
55°	759.3	756.1	770.9	788.9	819.3	859.8	931.5	1049.2	1218.4	1433.5	1578.5
57.5°	657.0	665.6	671.5	684.0	709.2	736.3	796.8	883.2	1017.4	1202.0	1355.3
60°	597.1	605.7	610.4	622.8	643.1	666.5	713.3	783.4	896.5	1055.5	1207.5
62.5°	543.5	550.2	551.7	563.0	579.5	602.3	639.1	698.0	787.3	926.4	1075.3
65°	466.2	466.2	469.3	481.0	488.8	509.0	537.1	580.0	651.7	760.0	887.1
67.5°	391.6	395.4	394.6	399.7	406.9	422.7	442.8	478.2	531.3	610.4	712.0
70°	343.0	346.1	345.3	349.2	357.0	367.2	383.5	417.0	455.2	523.1	610.4
72.5°	299.3	300.6	298.6	303.7	308.4	317.3	335.5	353.4	389.1	446.4	518.1
75°	229.2	230.7	232.3	235.4	240.1	244.8	254.1	272.1	295.4	338.3	384.3
77.5°	171.8	168.8	172.6	172.1	174.8	178.4	186.6	196.1	215.3	242.4	278.0
80°	129.4	130.2	130.2	131.0	134.9	137.2	144.2	151.2	166.0	186.3	211.3
82.5°	94.5	96.5	95.3	96.7	99.9	101.6	105.5	111.3	119.9	135.8	153.9
85°	51.4	47.6	49.1	50.7	50.7	51.4	54.6	56.9	61.6	67.8	74.8
87.5°	18.7	19.9	20.4	20.3	20.8	20.7	23.0	22.8	24.5	26.2	28.5
90°	18.8	18.2	17.7	17.2	16.7	16.0	15.1	14.3	13.4	12.5	11.3
92.5°	17.5	17.3	17.0	16.8	16.5	16.0	15.1	14.3	13.4	12.5	11.4
95°	16.4	16.4	16.4	16.4	16.4	16.0	15.1	14.3	13.4	12.5	19.1
97.5°	16.4	16.4	16.4	16.4	16.4	18.9	23.8	28.7	33.6	38.5	51.5
100°	16.4	17.1	17.8	18.5	19.2	32.5	58.4	84.3	110.2	136.1	135.4
102.5°	98.4	110.2	122.0	133.8	145.7	154.0	158.9	163.8	168.7	173.6	173.2
105°	232.3	232.4	232.6	232.8	233.0	233.0	233.0	233.0	233.0	233.0	233.0
107.5°	292.8	293.3	293.8	294.4	294.9	295.1	295.1	295.1	295.0	295.0	294.6
110°	334.7	334.5	334.4	334.2	334.0	334.2	334.7	335.2	335.8	336.3	335.9



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	372.3	372.5	372.7	373.0	373.2	373.7	374.3	375.0	375.7	376.3	376.1
115°	428.6	429.6	430.6	431.7	432.7	433.6	434.3	435.0	435.7	436.4	436.2
117.5°	488.6	489.1	489.5	490.0	490.4	491.1	492.0	492.9	493.8	494.7	494.1
120°	525.5	526.4	527.3	528.1	529.0	529.6	530.0	530.3	530.7	531.0	530.5
122.5°	560.6	561.6	562.6	563.6	564.6	565.3	565.6	566.0	566.3	566.7	566.4
125°	613.9	614.4	614.9	615.5	616.0	616.6	617.3	618.0	618.7	619.4	619.4
127.5°	658.8	660.1	661.4	662.7	663.9	664.8	665.2	665.5	665.9	666.3	666.4
130°	691.3	692.2	693.1	693.9	694.8	695.5	696.0	696.5	697.1	697.6	697.4
132.5°	721.4	722.2	723.1	724.0	724.8	725.3	725.4	725.5	725.6	725.7	726.1
135°	762.5	763.5	764.6	765.6	766.7	767.4	767.7	768.1	768.4	768.8	769.1
137.5°	803.8	804.7	805.6	806.5	807.4	807.8	807.7	807.7	807.6	807.5	807.9
140°	828.2	829.2	830.3	831.3	832.4	832.7	832.4	832.0	831.7	831.3	831.5
142.5°	851.3	852.4	853.4	854.5	855.5	856.0	855.9	855.9	855.8	855.7	855.5
145°	885.3	886.3	887.4	888.4	889.4	889.9	889.7	889.5	889.4	889.2	889.2
147.5°	913.3	914.5	915.8	917.0	918.3	918.8	918.6	918.4	918.2	918.0	917.8
150°	931.4	932.8	934.2	935.6	937.0	937.5	937.2	936.8	936.5	936.1	935.8
152.5°	948.3	949.6	950.8	952.1	953.3	953.8	953.4	953.1	952.7	952.4	952.0
155°	970.5	971.9	973.3	974.7	976.1	976.5	976.0	975.5	974.9	974.4	974.1
157.5°	989.1	990.5	991.9	993.3	994.7	995.1	994.6	994.0	993.4	992.9	992.8
160°	1001.0	1002.4	1003.8	1005.2	1006.6	1006.9	1006.2	1005.5	1004.8	1004.1	1004.0
162.5°	1011.7	1013.2	1014.7	1016.2	1017.8	1018.0	1017.1	1016.1	1015.1	1014.2	1014.0
165°	1026.0	1027.4	1028.8	1030.2	1031.6	1031.8	1030.7	1029.7	1028.7	1027.6	1027.4
167.5°	1036.1	1037.6	1039.2	1040.7	1042.3	1042.5	1041.2	1040.0	1038.7	1037.5	1037.3
170°	1041.7	1043.2	1044.8	1046.4	1047.9	1048.0	1046.6	1045.2	1043.9	1042.5	1042.3
172.5°	1045.4	1047.0	1048.6	1050.1	1051.7	1051.9	1050.6	1049.3	1048.1	1046.8	1046.5
175°	1050.3	1051.9	1053.4	1055.0	1056.5	1056.6	1055.2	1053.8	1052.5	1051.1	1050.9
177.5°	1053.1	1054.2	1055.3	1056.4	1057.6	1057.6	1056.6	1055.7	1054.7	1053.7	1053.6
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1889.6	1885.2	1880.2	1871.5	1860.9	1855.3	1846.5	1840.9	1829.7	1820.3	1810.4
5°	1985.4	1965.2	1946.5	1922.3	1895.8	1878.6	1858.4	1835.8	1812.4	1788.2	1761.7
7.5°	2084.8	2048.9	2009.9	1968.0	1927.0	1889.2	1853.2	1817.8	1784.8	1744.9	1711.1
10°	2151.5	2106.3	2057.9	2001.0	1945.7	1897.4	1848.2	1805.4	1761.7	1714.9	1673.6
12.5°	2218.2	2158.0	2089.7	2027.2	1960.7	1902.3	1844.5	1789.8	1734.9	1683.1	1635.0
15°	2265.3	2212.3	2149.1	2060.3	1985.4	1905.2	1828.8	1757.8	1691.6	1633.9	1573.1
17.5°	2296.3	2228.0	2160.2	2074.9	1976.9	1887.1	1800.5	1719.3	1644.6	1571.5	1512.9
20°	2301.9	2231.8	2160.8	2077.4	1976.9	1874.0	1787.4	1690.0	1609.7	1534.1	1462.4
22.5°	2300.1	2220.5	2143.4	2057.5	1959.4	1864.6	1760.0	1660.7	1573.5	1499.2	1424.3
25°	2282.4	2197.5	2100.8	2014.3	1917.6	1817.1	1711.1	1608.2	1519.3	1434.3	1360.3
27.5°	2267.8	2157.6	2048.1	1947.2	1853.9	1761.7	1660.2	1554.8	1456.3	1370.2	1300.4
30°	2249.7	2128.9	2005.7	1900.5	1804.6	1714.9	1619.1	1516.2	1413.3	1329.1	1254.3
32.5°	2233.5	2092.7	1962.7	1848.1	1746.6	1659.4	1571.0	1473.1	1372.1	1286.7	1211.8
35°	2202.2	2039.2	1890.3	1760.9	1652.6	1562.9	1488.9	1397.7	1304.9	1222.3	1150.6
37.5°	2162.4	1969.1	1809.3	1673.6	1554.8	1460.4	1391.4	1321.4	1232.4	1152.8	1087.9
40°	2131.2	1919.2	1750.0	1611.3	1488.1	1389.9	1326.0	1259.7	1185.7	1111.6	1043.0
42.5°	2091.9	1874.3	1690.2	1540.8	1418.9	1323.2	1256.1	1199.8	1134.5	1065.5	1001.8
45°	2019.7	1792.9	1593.3	1432.8	1309.6	1215.3	1145.9	1103.8	1054.7	989.2	935.4
47.5°	1913.6	1695.1	1488.7	1323.0	1195.9	1108.5	1043.5	1003.1	968.5	919.8	871.0
50°	1819.4	1622.2	1413.3	1248.8	1121.7	1033.6	973.6	937.0	907.4	869.9	828.6
52.5°	1714.0	1530.5	1339.1	1176.5	1050.6	963.8	905.0	872.8	848.1	821.3	780.6
55°	1546.6	1390.7	1212.9	1058.6	942.4	857.5	806.0	778.0	757.7	737.4	712.5
57.5°	1362.1	1240.2	1082.8	941.7	834.7	757.4	709.4	682.1	666.3	655.9	641.2
60°	1232.4	1128.0	992.3	863.7	759.3	690.7	643.9	622.8	609.6	601.0	590.1
62.5°	1112.1	1026.3	900.7	783.3	691.9	627.0	585.3	564.8	552.2	548.0	539.0
65°	934.6	868.4	764.7	667.3	589.3	534.0	498.9	479.4	471.6	466.9	467.7
67.5°	759.9	719.5	636.2	553.1	490.9	444.5	416.4	401.5	397.6	391.3	391.2
70°	653.2	622.8	552.7	480.2	424.8	389.0	364.0	348.4	344.5	341.4	340.7
72.5°	559.1	532.4	471.6	413.5	363.7	332.2	311.7	302.3	295.9	294.0	293.9
75°	420.2	405.4	357.0	311.0	276.7	254.9	240.9	232.3	227.6	226.8	227.6
77.5°	298.7	285.8	255.1	222.5	200.8	184.3	172.4	169.5	164.2	164.3	163.5
80°	224.5	215.9	196.4	170.7	152.8	138.8	132.5	127.1	125.5	123.2	125.5
82.5°	162.8	153.6	140.3	123.9	109.1	100.7	94.5	92.8	91.8	90.7	91.2
85°	80.3	81.1	73.3	60.8	54.6	49.9	46.0	46.0	45.2	44.4	45.2
87.5°	29.5	28.0	25.2	23.1	19.7	17.6	16.6	17.0	15.4	15.1	16.0
90°	10.1	8.9	7.6	6.3	5.0	3.6	2.2	0.8	2.2	3.6	5.0
92.5°	10.4	9.3	8.2	8.2	9.1	10.1	11.1	12.0	11.1	10.1	9.1
95°	25.7	32.3	38.9	42.5	43.0	43.5	44.1	44.6	44.1	43.5	43.0
97.5°	64.6	77.7	90.8	96.8	95.9	94.9	94.0	93.1	94.0	94.9	95.9
100°	134.7	134.0	133.3	132.7	132.2	131.6	131.1	130.6	131.1	131.6	132.2
102.5°	172.8	172.4	171.9	171.4	170.7	170.1	169.4	168.8	169.4	170.1	170.7
105°	233.0	233.0	233.0	232.7	232.0	231.3	230.6	229.9	230.6	231.3	232.0
107.5°	294.3	293.9	293.6	293.4	293.4	293.4	293.4	293.4	293.4	293.4	293.4
110°	335.6	335.2	334.9	334.7	334.7	334.7	334.7	334.7	334.7	334.7	334.7





TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	375.9	375.7	375.5	375.2	374.8	374.3	373.9	373.5	373.9	374.3	374.8
115°	436.0	435.9	435.7	435.2	434.3	433.4	432.6	431.7	432.6	433.4	434.3
117.5°	493.4	492.7	492.1	491.8	491.8	491.8	491.9	491.9	491.9	491.8	491.8
120°	530.0	529.4	528.9	528.7	528.9	529.1	529.3	529.4	529.3	529.1	528.9
122.5°	566.2	565.9	565.7	565.2	564.6	563.9	563.3	562.6	563.3	563.9	564.6
125°	619.4	619.4	619.4	618.8	617.6	616.3	615.1	613.9	615.1	616.3	617.6
127.5°	666.5	666.6	666.7	666.3	665.5	664.6	663.7	662.9	663.7	664.6	665.5
130°	697.2	697.1	696.9	696.4	695.5	694.6	693.8	692.9	693.8	694.6	695.5
132.5°	726.5	726.9	727.3	727.0	725.9	724.9	723.9	722.9	723.9	724.9	725.9
135°	769.4	769.8	770.1	769.8	768.8	767.7	766.7	765.6	766.7	767.7	768.8
137.5°	808.2	808.5	808.8	808.5	807.6	806.7	805.8	804.9	805.8	806.7	807.6
140°	831.7	831.8	832.0	831.9	831.6	831.2	830.9	830.5	830.9	831.2	831.6
142.5°	855.2	855.0	854.7	854.5	854.3	854.1	853.9	853.7	853.9	854.1	854.3
145°	889.2	889.2	889.2	889.0	888.7	888.3	888.0	887.6	888.0	888.3	888.7
147.5°	917.5	917.3	917.1	917.1	917.1	917.2	917.3	917.3	917.3	917.2	917.1
150°	935.4	935.1	934.7	934.7	935.1	935.4	935.8	936.1	935.8	935.4	935.1
152.5°	951.7	951.3	951.0	951.2	952.0	952.7	953.5	954.3	953.5	952.7	952.0
155°	973.7	973.4	973.0	973.4	974.4	975.5	976.5	977.6	976.5	975.5	974.4
157.5°	992.8	992.8	992.7	993.0	993.7	994.3	994.9	995.5	994.9	994.3	993.7
160°	1003.8	1003.6	1003.5	1003.9	1004.9	1006.0	1007.0	1008.1	1007.0	1006.0	1004.9
162.5°	1013.8	1013.6	1013.5	1013.9	1014.9	1016.0	1017.0	1018.1	1017.0	1016.0	1014.9
165°	1027.3	1027.1	1026.9	1027.3	1028.4	1029.4	1030.5	1031.5	1030.5	1029.4	1028.4
167.5°	1037.1	1036.9	1036.8	1037.2	1038.3	1039.4	1040.5	1041.5	1040.5	1039.4	1038.3
170°	1042.1	1041.9	1041.8	1042.3	1043.5	1044.7	1045.9	1047.2	1045.9	1044.7	1043.5
172.5°	1046.2	1045.9	1045.6	1046.0	1047.3	1048.5	1049.7	1050.9	1049.7	1048.5	1047.3
175°	1050.7	1050.5	1050.4	1050.8	1051.9	1052.9	1053.9	1055.0	1053.9	1052.9	1051.9
177.5°	1053.4	1053.3	1053.2	1053.5	1054.4	1055.2	1056.0	1056.9	1056.0	1055.2	1054.4
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1804.7	1797.9	1792.3	1779.8	1772.9	1763.6	1756.1	1764.2	1755.5	1759.2	1753.6
5°	1748.5	1726.6	1711.1	1688.4	1669.0	1651.0	1637.8	1635.4	1629.2	1626.1	1616.7
7.5°	1680.8	1653.5	1626.7	1597.1	1572.1	1546.7	1530.5	1517.1	1508.2	1496.5	1488.6
10°	1640.9	1604.3	1573.1	1537.2	1506.0	1478.8	1456.9	1446.0	1435.9	1421.1	1415.6
12.5°	1591.6	1553.7	1515.7	1477.4	1447.4	1417.0	1398.3	1381.8	1374.8	1358.1	1356.4
15°	1532.5	1475.6	1438.2	1399.2	1357.9	1333.0	1317.4	1299.5	1291.7	1280.0	1271.4
17.5°	1462.1	1411.2	1364.5	1324.1	1288.7	1267.7	1248.3	1236.0	1222.6	1215.0	1200.9
20°	1410.9	1362.6	1315.8	1273.0	1245.7	1221.5	1205.9	1194.2	1180.2	1176.3	1162.3
22.5°	1367.9	1314.6	1269.7	1233.7	1203.9	1176.6	1159.8	1151.8	1142.2	1130.2	1127.3
25°	1297.9	1242.6	1204.4	1168.5	1142.0	1117.1	1105.4	1095.2	1085.9	1077.3	1074.2
27.5°	1237.4	1188.0	1142.6	1110.2	1087.1	1064.4	1054.1	1041.8	1034.9	1028.0	1019.6
30°	1195.0	1144.3	1104.6	1073.4	1048.5	1028.2	1017.3	1008.7	1002.5	996.2	991.6
32.5°	1151.4	1104.4	1065.9	1035.4	1010.4	995.1	985.5	979.4	972.5	965.0	959.1
35°	1093.7	1042.2	1004.8	978.3	958.8	947.1	936.2	930.7	923.0	923.0	916.7
37.5°	1028.7	984.2	951.2	927.0	909.5	899.1	887.3	883.5	878.5	875.2	873.1
40°	990.0	948.7	917.5	893.3	874.6	866.0	856.7	850.5	847.3	843.4	841.9
42.5°	950.1	910.6	880.7	858.4	842.2	834.9	826.1	821.8	815.5	810.4	809.5
45°	889.4	851.2	824.0	806.0	792.0	783.4	778.0	768.6	765.5	759.3	758.5
47.5°	831.9	795.3	768.5	753.8	741.5	734.5	725.9	716.5	713.0	709.8	709.5
50°	788.9	755.4	730.4	716.4	704.7	694.6	686.0	679.7	677.4	677.4	679.0
52.5°	745.2	716.7	695.5	678.3	667.3	656.5	648.6	644.8	641.2	645.0	647.8
55°	681.3	652.5	636.9	620.5	609.6	597.1	593.2	591.7	589.3	595.6	598.7
57.5°	613.6	593.4	575.1	558.9	549.1	541.9	536.6	535.7	540.1	543.0	553.1
60°	570.6	547.2	530.9	518.4	506.7	502.0	500.5	498.9	502.0	510.6	523.8
62.5°	523.2	504.2	486.6	477.2	468.6	460.9	460.5	461.5	467.7	477.5	490.8
65°	453.7	437.3	425.6	414.7	407.7	403.0	404.6	407.7	414.7	428.0	442.8
67.5°	383.1	371.8	361.4	352.5	345.8	345.8	347.4	352.0	360.3	375.6	389.1
70°	337.5	325.1	316.5	312.6	307.1	304.0	308.7	316.5	323.5	337.5	349.2
72.5°	292.0	281.4	274.7	272.1	269.7	267.2	268.8	277.2	286.7	300.7	314.3
75°	224.5	220.6	215.9	212.8	210.5	212.0	213.6	221.4	229.2	244.0	259.6
77.5°	163.9	159.8	157.0	156.2	155.0	155.7	160.1	165.9	173.5	184.3	196.1
80°	123.9	122.4	120.8	120.0	120.0	120.8	127.1	131.0	138.0	148.1	157.5
82.5°	90.3	89.3	89.0	88.9	89.5	89.6	93.4	98.5	104.3	111.9	120.0
85°	47.6	46.0	48.3	49.1	47.6	49.9	51.4	54.6	56.9	60.8	64.7
87.5°	16.9	18.4	18.0	18.9	19.1	20.6	20.1	22.8	24.2	25.6	25.2
90°	6.3	7.6	8.9	10.1	11.3	12.5	13.4	14.3	15.1	16.0	16.7
92.5°	8.2	8.2	9.3	10.4	11.4	12.5	13.4	14.3	15.1	16.0	16.5
95°	42.5	38.9	32.3	25.7	19.1	12.5	13.4	14.3	15.1	16.0	16.4
97.5°	96.8	90.8	77.7	64.6	51.5	38.5	33.6	28.7	23.8	18.9	16.4
100°	132.7	133.3	134.0	134.7	135.4	136.1	110.2	84.3	58.4	32.5	19.2
102.5°	171.4	171.9	172.4	172.8	173.2	173.6	168.7	163.8	158.9	154.0	145.7
105°	232.7	233.0	233.0	233.0	233.0	233.0	233.0	233.0	233.0	233.0	233.0
107.5°	293.4	293.6	293.9	294.3	294.6	295.0	295.0	295.1	295.1	295.1	294.9
110°	334.7	334.9	335.2	335.6	335.9	336.3	335.8	335.2	334.7	334.2	334.0



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	375.2	375.5	375.7	375.9	376.1	376.3	375.7	375.0	374.3	373.7	373.2
115°	435.2	435.7	435.9	436.0	436.2	436.4	435.7	435.0	434.3	433.6	432.7
117.5°	491.8	492.1	492.7	493.4	494.1	494.7	493.8	492.9	492.0	491.1	490.4
120°	528.7	528.9	529.4	530.0	530.5	531.0	530.7	530.3	530.0	529.6	529.0
122.5°	565.2	565.7	565.9	566.2	566.4	566.7	566.3	566.0	565.6	565.3	564.6
125°	618.8	619.4	619.4	619.4	619.4	619.4	618.7	618.0	617.3	616.6	616.0
127.5°	666.3	666.7	666.6	666.5	666.4	666.3	665.9	665.5	665.2	664.8	663.9
130°	696.4	696.9	697.1	697.2	697.4	697.6	697.1	696.5	696.0	695.5	694.8
132.5°	727.0	727.3	726.9	726.5	726.1	725.7	725.6	725.5	725.4	725.3	724.8
135°	769.8	770.1	769.8	769.4	769.1	768.8	768.4	768.1	767.7	767.4	766.7
137.5°	808.5	808.8	808.5	808.2	807.9	807.5	807.6	807.7	807.7	807.8	807.4
140°	831.9	832.0	831.8	831.7	831.5	831.3	831.7	832.0	832.4	832.7	832.4
142.5°	854.5	854.7	855.0	855.2	855.5	855.7	855.8	855.9	855.9	856.0	855.5
145°	889.0	889.2	889.2	889.2	889.2	889.2	889.4	889.5	889.7	889.9	889.4
147.5°	917.1	917.1	917.3	917.5	917.8	918.0	918.2	918.4	918.6	918.8	918.3
150°	934.7	934.7	935.1	935.4	935.8	936.1	936.5	936.8	937.2	937.5	937.0
152.5°	951.2	951.0	951.3	951.7	952.0	952.4	952.7	953.1	953.4	953.8	953.3
155°	973.4	973.0	973.4	973.7	974.1	974.4	974.9	975.5	976.0	976.5	976.1
157.5°	993.0	992.7	992.8	992.8	992.8	992.9	993.4	994.0	994.6	995.1	994.7
160°	1003.9	1003.5	1003.6	1003.8	1004.0	1004.1	1004.8	1005.5	1006.2	1006.9	1006.6
162.5°	1013.9	1013.5	1013.6	1013.8	1014.0	1014.2	1015.1	1016.1	1017.1	1018.0	1017.8
165°	1027.3	1026.9	1027.1	1027.3	1027.4	1027.6	1028.7	1029.7	1030.7	1031.8	1031.6
167.5°	1037.2	1036.8	1036.9	1037.1	1037.3	1037.5	1038.7	1040.0	1041.2	1042.5	1042.3
170°	1042.3	1041.8	1041.9	1042.1	1042.3	1042.5	1043.9	1045.2	1046.6	1048.0	1047.9
172.5°	1046.0	1045.6	1045.9	1046.2	1046.5	1046.8	1048.1	1049.3	1050.6	1051.9	1051.7
175°	1050.8	1050.4	1050.5	1050.7	1050.9	1051.1	1052.5	1053.8	1055.2	1056.6	1056.5
177.5°	1053.5	1053.2	1053.3	1053.4	1053.6	1053.7	1054.7	1055.7	1056.6	1057.6	1057.6
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1749.9	1754.2	1750.5	1755.5	1750.5	1754.2	1749.9	1753.6	1759.2	1755.5	1764.2
5°	1612.8	1605.8	1610.5	1607.4	1610.5	1605.8	1612.8	1616.7	1626.1	1629.2	1635.4
7.5°	1486.2	1479.5	1471.9	1468.3	1471.9	1479.5	1486.2	1488.6	1496.5	1508.2	1517.1
10°	1407.0	1398.5	1397.7	1392.2	1397.7	1398.5	1407.0	1415.6	1421.1	1435.9	1446.0
12.5°	1349.0	1341.1	1332.2	1329.9	1332.2	1341.1	1349.0	1356.4	1358.1	1374.8	1381.8
15°	1266.7	1260.5	1255.0	1259.7	1255.0	1260.5	1266.7	1271.4	1280.0	1291.7	1299.5
17.5°	1198.3	1193.1	1192.2	1186.4	1192.2	1193.1	1198.3	1200.9	1215.0	1222.6	1236.0
20°	1155.3	1151.4	1152.9	1142.8	1152.9	1151.4	1155.3	1162.3	1176.3	1180.2	1194.2
22.5°	1121.0	1113.3	1112.4	1110.4	1112.4	1113.3	1121.0	1127.3	1130.2	1142.2	1151.8
25°	1067.2	1063.3	1059.4	1063.3	1059.4	1063.3	1067.2	1074.2	1077.3	1085.9	1095.2
27.5°	1020.2	1015.6	1014.5	1014.9	1014.5	1015.6	1020.2	1019.6	1028.0	1034.9	1041.8
30°	991.6	983.8	984.5	983.8	984.5	983.8	991.6	991.6	996.2	1002.5	1008.7
32.5°	960.4	955.1	954.0	952.6	954.0	955.1	960.4	959.1	965.0	972.5	979.4
35°	914.4	914.4	910.5	910.5	910.5	914.4	914.4	916.7	923.0	923.0	930.7
37.5°	871.2	870.4	868.1	868.4	868.1	870.4	871.2	873.1	875.2	878.5	883.5
40°	838.8	838.0	835.6	831.0	835.6	838.0	838.8	841.9	843.4	847.3	850.5
42.5°	807.6	804.9	803.8	802.3	803.8	804.9	807.6	809.5	810.4	815.5	821.8
45°	758.5	758.5	756.9	756.1	756.9	758.5	758.5	758.5	759.3	765.5	768.6
47.5°	710.8	712.2	715.1	714.7	715.1	712.2	710.8	709.5	709.8	713.0	716.5
50°	682.1	682.9	685.2	686.0	685.2	682.9	682.1	679.0	677.4	677.4	679.7
52.5°	650.3	654.8	657.8	657.3	657.8	654.8	650.3	647.8	645.0	641.2	644.8
55°	605.7	611.1	616.6	617.4	616.6	611.1	605.7	598.7	595.6	589.3	591.7
57.5°	561.6	569.2	575.0	576.8	575.0	569.2	561.6	553.1	543.0	540.1	535.7
60°	531.6	541.8	548.8	551.9	548.8	541.8	531.6	523.8	510.6	502.0	498.9
62.5°	502.9	514.3	521.3	522.0	521.3	514.3	502.9	490.8	477.5	467.7	461.5
65°	456.0	467.7	473.9	478.6	473.9	467.7	456.0	442.8	428.0	414.7	407.7
67.5°	405.5	417.2	424.1	427.8	424.1	417.2	405.5	389.1	375.6	360.3	352.0
70°	368.7	380.4	389.8	392.9	389.8	380.4	368.7	349.2	337.5	323.5	316.5
72.5°	332.5	343.0	350.5	354.2	350.5	343.0	332.5	314.3	300.7	286.7	277.2
75°	269.7	283.7	290.8	294.7	290.8	283.7	269.7	259.6	244.0	229.2	221.4
77.5°	208.0	220.8	225.0	227.0	225.0	220.8	208.0	196.1	184.3	173.5	165.9
80°	166.8	174.6	180.1	180.8	180.1	174.6	166.8	157.5	148.1	138.0	131.0
82.5°	128.2	134.7	136.4	138.4	136.4	134.7	128.2	120.0	111.9	104.3	98.5
85°	70.2	73.3	74.1	73.3	74.1	73.3	70.2	64.7	60.8	56.9	54.6
87.5°	26.5	26.0	26.1	27.5	26.1	26.0	26.5	25.2	25.6	24.2	22.8
90°	17.2	17.7	18.2	18.8	18.2	17.7	17.2	16.7	16.0	15.1	14.3
92.5°	16.8	17.0	17.3	17.5	17.3	17.0	16.8	16.5	16.0	15.1	14.3
95°	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.0	15.1	14.3
97.5°	16.4	16.4	16.4	16.4	16.4	16.4	16.4	16.4	18.9	23.8	28.7
100°	18.5	17.8	17.1	16.4	17.1	17.8	18.5	19.2	32.5	58.4	84.3
102.5°	133.8	122.0	110.2	98.4	110.2	122.0	133.8	145.7	154.0	158.9	163.8
105°	232.8	232.6	232.4	232.3	232.4	232.6	232.8	233.0	233.0	233.0	233.0
107.5°	294.4	293.8	293.3	292.8	293.3	293.8	294.4	294.9	295.1	295.1	295.1
110°	334.2	334.4	334.5	334.7	334.5	334.4	334.2	334.0	334.2	334.7	335.2



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	373.0	372.7	372.5	372.3	372.5	372.7	373.0	373.2	373.7	374.3	375.0
115°	431.7	430.6	429.6	428.6	429.6	430.6	431.7	432.7	433.6	434.3	435.0
117.5°	490.0	489.5	489.1	488.6	489.1	489.5	490.0	490.4	491.1	492.0	492.9
120°	528.1	527.3	526.4	525.5	526.4	527.3	528.1	529.0	529.6	530.0	530.3
122.5°	563.6	562.6	561.6	560.6	561.6	562.6	563.6	564.6	565.3	565.6	566.0
125°	615.5	614.9	614.4	613.9	614.4	614.9	615.5	616.0	616.6	617.3	618.0
127.5°	662.7	661.4	660.1	658.8	660.1	661.4	662.7	663.9	664.8	665.2	665.5
130°	693.9	693.1	692.2	691.3	692.2	693.1	693.9	694.8	695.5	696.0	696.5
132.5°	724.0	723.1	722.2	721.4	722.2	723.1	724.0	724.8	725.3	725.4	725.5
135°	765.6	764.6	763.5	762.5	763.5	764.6	765.6	766.7	767.4	767.7	768.1
137.5°	806.5	805.6	804.7	803.8	804.7	805.6	806.5	807.4	807.8	807.7	807.7
140°	831.3	830.3	829.2	828.2	829.2	830.3	831.3	832.4	832.7	832.4	832.0
142.5°	854.5	853.4	852.4	851.3	852.4	853.4	854.5	855.5	856.0	855.9	855.9
145°	888.4	887.4	886.3	885.3	886.3	887.4	888.4	889.4	889.9	889.7	889.5
147.5°	917.0	915.8	914.5	913.3	914.5	915.8	917.0	918.3	918.8	918.6	918.4
150°	935.6	934.2	932.8	931.4	932.8	934.2	935.6	937.0	937.5	937.2	936.8
152.5°	952.1	950.8	949.6	948.3	949.6	950.8	952.1	953.3	953.8	953.4	953.1
155°	974.7	973.3	971.9	970.5	971.9	973.3	974.7	976.1	976.5	976.0	975.5
157.5°	993.3	991.9	990.5	989.1	990.5	991.9	993.3	994.7	995.1	994.6	994.0
160°	1005.2	1003.8	1002.4	1001.0	1002.4	1003.8	1005.2	1006.6	1006.9	1006.2	1005.5
162.5°	1016.2	1014.7	1013.2	1011.7	1013.2	1014.7	1016.2	1017.8	1018.0	1017.1	1016.1
165°	1030.2	1028.8	1027.4	1026.0	1027.4	1028.8	1030.2	1031.6	1031.8	1030.7	1029.7
167.5°	1040.7	1039.2	1037.6	1036.1	1037.6	1039.2	1040.7	1042.3	1042.5	1041.2	1040.0
170°	1046.4	1044.8	1043.2	1041.7	1043.2	1044.8	1046.4	1047.9	1048.0	1046.6	1045.2
172.5°	1050.1	1048.6	1047.0	1045.4	1047.0	1048.6	1050.1	1051.7	1051.9	1050.6	1049.3
175°	1055.0	1053.4	1051.9	1050.3	1051.9	1053.4	1055.0	1056.5	1056.6	1055.2	1053.8
177.5°	1056.4	1055.3	1054.2	1053.1	1054.2	1055.3	1056.4	1057.6	1057.6	1056.6	1055.7
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1756.1	1763.6	1772.9	1779.8	1792.3	1797.9	1804.7	1810.4	1820.3	1829.7	1840.9
5°	1637.8	1651.0	1669.0	1688.4	1711.1	1726.6	1748.5	1761.7	1788.2	1812.4	1835.8
7.5°	1530.5	1546.7	1572.1	1597.1	1626.7	1653.5	1680.8	1711.1	1744.9	1784.8	1817.8
10°	1456.9	1478.8	1506.0	1537.2	1573.1	1604.3	1640.9	1673.6	1714.9	1761.7	1805.4
12.5°	1398.3	1417.0	1447.4	1477.4	1515.7	1553.7	1591.6	1635.0	1683.1	1734.9	1789.8
15°	1317.4	1333.0	1357.9	1399.2	1438.2	1475.6	1532.5	1573.1	1633.9	1691.6	1757.8
17.5°	1248.3	1267.7	1288.7	1324.1	1364.5	1411.2	1462.1	1512.9	1571.5	1644.6	1719.3
20°	1205.9	1221.5	1245.7	1273.0	1315.8	1362.6	1410.9	1462.4	1534.1	1609.7	1690.0
22.5°	1159.8	1176.6	1203.9	1233.7	1269.7	1314.6	1367.9	1424.3	1499.2	1573.5	1660.7
25°	1105.4	1117.1	1142.0	1168.5	1204.4	1242.6	1297.9	1360.3	1434.3	1519.3	1608.2
27.5°	1054.1	1064.4	1087.1	1110.2	1142.6	1188.0	1237.4	1300.4	1370.2	1456.3	1554.8
30°	1017.3	1028.2	1048.5	1073.4	1104.6	1144.3	1195.0	1254.3	1329.1	1413.3	1516.2
32.5°	985.5	995.1	1010.4	1035.4	1065.9	1104.4	1151.4	1211.8	1286.7	1372.1	1473.1
35°	936.2	947.1	958.8	978.3	1004.8	1042.2	1093.7	1150.6	1222.3	1304.9	1397.7
37.5°	887.3	899.1	909.5	927.0	951.2	984.2	1028.7	1087.9	1152.8	1232.4	1321.4
40°	856.7	866.0	874.6	893.3	917.5	948.7	990.0	1043.0	1111.6	1185.7	1259.7
42.5°	826.1	834.9	842.2	858.4	880.7	910.6	950.1	1001.8	1065.5	1134.5	1199.8
45°	778.0	783.4	792.0	806.0	824.0	851.2	889.4	935.4	989.2	1054.7	1103.8
47.5°	725.9	734.5	741.5	753.8	768.5	795.3	831.9	871.0	919.8	968.5	1003.1
50°	686.0	694.6	704.7	716.4	730.4	755.4	788.9	828.6	869.9	907.4	937.0
52.5°	648.6	656.5	667.3	678.3	695.5	716.7	745.2	780.6	821.3	848.1	872.8
55°	593.2	597.1	609.6	620.5	636.9	652.5	681.3	712.5	737.4	757.7	778.0
57.5°	536.6	541.9	549.1	558.9	575.1	593.4	613.6	641.2	655.9	666.3	682.1
60°	500.5	502.0	506.7	518.4	530.9	547.2	570.6	590.1	601.0	609.6	622.8
62.5°	460.5	460.9	468.6	477.2	486.6	504.2	523.2	539.0	548.0	552.2	564.8
65°	404.6	403.0	407.7	414.7	425.6	437.3	453.7	467.7	466.9	471.6	479.4
67.5°	347.4	345.8	345.8	352.5	361.4	371.8	383.1	391.2	391.3	397.6	401.5
70°	308.7	304.0	307.1	312.6	316.5	325.1	337.5	340.7	341.4	344.5	348.4
72.5°	268.8	267.2	269.7	272.1	274.7	281.4	292.0	293.9	294.0	295.9	302.3
75°	213.6	212.0	210.5	212.8	215.9	220.6	224.5	227.6	226.8	227.6	232.3
77.5°	160.1	155.7	155.0	156.2	157.0	159.8	163.9	163.5	164.3	164.2	169.5
80°	127.1	120.8	120.0	120.0	120.8	122.4	123.9	125.5	123.2	125.5	127.1
82.5°	93.4	89.6	89.5	88.9	89.0	89.3	90.3	91.2	90.7	91.8	92.8
85°	51.4	49.9	47.6	49.1	48.3	46.0	47.6	45.2	44.4	45.2	46.0
87.5°	20.1	20.6	19.1	18.9	18.0	18.4	16.9	16.0	15.1	15.4	17.0
90°	13.4	12.5	11.3	10.1	8.9	7.6	6.3	5.0	3.6	2.2	0.8
92.5°	13.4	12.5	11.4	10.4	9.3	8.2	8.2	9.1	10.1	11.1	12.0
95°	13.4	12.5	19.1	25.7	32.3	38.9	42.5	43.0	43.5	44.1	44.6
97.5°	33.6	38.5	51.5	64.6	77.7	90.8	96.8	95.9	94.9	94.0	93.1
100°	110.2	136.1	135.4	134.7	134.0	133.3	132.7	132.2	131.6	131.1	130.6
102.5°	168.7	173.6	173.2	172.8	172.4	171.9	171.4	170.7	170.1	169.4	168.8
105°	233.0	233.0	233.0	233.0	233.0	233.0	232.7	232.0	231.3	230.6	229.9
107.5°	295.0	295.0	294.6	294.3	293.9	293.6	293.4	293.4	293.4	293.4	293.4
110°	335.8	336.3	335.9	335.6	335.2	334.9	334.7	334.7	334.7	334.7	334.7



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	375.7	376.3	376.1	375.9	375.7	375.5	375.2	374.8	374.3	373.9	373.5
115°	435.7	436.4	436.2	436.0	435.9	435.7	435.2	434.3	433.4	432.6	431.7
117.5°	493.8	494.7	494.1	493.4	492.7	492.1	491.8	491.8	491.8	491.9	491.9
120°	530.7	531.0	530.5	530.0	529.4	528.9	528.7	528.9	529.1	529.3	529.4
122.5°	566.3	566.7	566.4	566.2	565.9	565.7	565.2	564.6	563.9	563.3	562.6
125°	618.7	619.4	619.4	619.4	619.4	619.4	618.8	617.6	616.3	615.1	613.9
127.5°	665.9	666.3	666.4	666.5	666.6	666.7	666.3	665.5	664.6	663.7	662.9
130°	697.1	697.6	697.4	697.2	697.1	696.9	696.4	695.5	694.6	693.8	692.9
132.5°	725.6	725.7	726.1	726.5	726.9	727.3	727.0	725.9	724.9	723.9	722.9
135°	768.4	768.8	769.1	769.4	769.8	770.1	769.8	768.8	767.7	766.7	765.6
137.5°	807.6	807.5	807.9	808.2	808.5	808.8	808.5	807.6	806.7	805.8	804.9
140°	831.7	831.3	831.5	831.7	831.8	832.0	831.9	831.6	831.2	830.9	830.5
142.5°	855.8	855.7	855.5	855.2	855.0	854.7	854.5	854.3	854.1	853.9	853.7
145°	889.4	889.2	889.2	889.2	889.2	889.2	889.0	888.7	888.3	888.0	887.6
147.5°	918.2	918.0	917.8	917.5	917.3	917.1	917.1	917.1	917.2	917.3	917.3
150°	936.5	936.1	935.8	935.4	935.1	934.7	934.7	935.1	935.4	935.8	936.1
152.5°	952.7	952.4	952.0	951.7	951.3	951.0	951.2	952.0	952.7	953.5	954.3
155°	974.9	974.4	974.1	973.7	973.4	973.0	973.4	974.4	975.5	976.5	977.6
157.5°	993.4	992.9	992.8	992.8	992.8	992.7	993.0	993.7	994.3	994.9	995.5
160°	1004.8	1004.1	1004.0	1003.8	1003.6	1003.5	1003.9	1004.9	1006.0	1007.0	1008.1
162.5°	1015.1	1014.2	1014.0	1013.8	1013.6	1013.5	1013.9	1014.9	1016.0	1017.0	1018.1
165°	1028.7	1027.6	1027.4	1027.3	1027.1	1026.9	1027.3	1028.4	1029.4	1030.5	1031.5
167.5°	1038.7	1037.5	1037.3	1037.1	1036.9	1036.8	1037.2	1038.3	1039.4	1040.5	1041.5
170°	1043.9	1042.5	1042.3	1042.1	1041.9	1041.8	1042.3	1043.5	1044.7	1045.9	1047.2
172.5°	1048.1	1046.8	1046.5	1046.2	1045.9	1045.6	1046.0	1047.3	1048.5	1049.7	1050.9
175°	1052.5	1051.1	1050.9	1050.7	1050.5	1050.4	1050.8	1051.9	1052.9	1053.9	1055.0
177.5°	1054.7	1053.7	1053.6	1053.4	1053.3	1053.2	1053.5	1054.4	1055.2	1056.0	1056.9
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1846.5	1855.3	1860.9	1871.5	1880.2	1885.2	1889.6	1893.3	1897.7	1901.4	1912.0
5°	1858.4	1878.6	1895.8	1922.3	1946.5	1965.2	1985.4	2003.4	2018.2	2039.2	2055.6
7.5°	1853.2	1889.2	1927.0	1968.0	2009.9	2048.9	2084.8	2118.3	2148.7	2185.5	2217.7
10°	1848.2	1897.4	1945.7	2001.0	2057.9	2106.3	2151.5	2197.5	2231.0	2277.8	2317.5
12.5°	1844.5	1902.3	1960.7	2027.2	2089.7	2158.0	2218.2	2251.7	2302.7	2340.1	2387.4
15°	1828.8	1905.2	1985.4	2060.3	2149.1	2212.3	2265.3	2330.8	2378.3	2425.9	2477.3
17.5°	1800.5	1887.1	1976.9	2074.9	2160.2	2228.0	2296.3	2359.5	2416.2	2480.0	2544.0
20°	1787.4	1874.0	1976.9	2077.4	2160.8	2231.8	2301.9	2371.3	2433.7	2515.5	2589.6
22.5°	1760.0	1864.6	1959.4	2057.5	2143.4	2220.5	2300.1	2378.8	2461.7	2554.2	2646.9
25°	1711.1	1817.1	1917.6	2014.3	2100.8	2197.5	2282.4	2387.7	2493.7	2616.1	2731.4
27.5°	1660.2	1761.7	1853.9	1947.2	2048.1	2157.6	2267.8	2387.2	2526.0	2680.5	2843.2
30°	1619.1	1714.9	1804.6	1900.5	2005.7	2128.9	2249.7	2391.6	2552.2	2726.0	2919.3
32.5°	1571.0	1659.4	1746.6	1848.1	1962.7	2092.7	2233.5	2389.1	2582.1	2779.6	2978.6
35°	1488.9	1562.9	1652.6	1760.9	1890.3	2039.2	2202.2	2386.1	2607.5	2834.3	3001.9
37.5°	1391.4	1460.4	1554.8	1673.6	1809.3	1969.1	2162.4	2380.7	2615.8	2796.6	2850.7
40°	1326.0	1389.9	1488.1	1611.3	1750.0	1919.2	2131.2	2362.0	2589.6	2704.9	2660.5
42.5°	1256.1	1323.2	1418.9	1540.8	1690.2	1874.3	2091.9	2322.7	2513.5	2557.1	2403.6
45°	1145.9	1215.3	1309.6	1432.8	1593.3	1792.9	2019.7	2229.4	2339.3	2260.6	2022.9
47.5°	1043.5	1108.5	1195.9	1323.0	1488.7	1695.1	1913.6	2080.9	2089.6	1901.7	1647.8
50°	973.6	1033.6	1121.7	1248.8	1413.3	1622.2	1819.4	1951.1	1891.9	1679.1	1435.1
52.5°	905.0	963.8	1050.6	1176.5	1339.1	1530.5	1714.0	1806.5	1694.8	1476.4	1268.0
55°	806.0	857.5	942.4	1058.6	1212.9	1390.7	1546.6	1578.5	1433.5	1218.4	1049.2
57.5°	709.4	757.4	834.7	941.7	1082.8	1240.2	1362.1	1355.3	1202.0	1017.4	883.2
60°	643.9	690.7	759.3	863.7	992.3	1128.0	1232.4	1207.5	1055.5	896.5	783.4
62.5°	585.3	627.0	691.9	783.3	900.7	1026.3	1112.1	1075.3	926.4	787.3	698.0
65°	498.9	534.0	589.3	667.3	764.7	868.4	934.6	887.1	760.0	651.7	580.0
67.5°	416.4	444.5	490.9	553.1	636.2	719.5	759.9	712.0	610.4	531.3	478.2
70°	364.0	389.0	424.8	480.2	552.7	622.8	653.2	610.4	523.1	455.2	417.0
72.5°	311.7	332.2	363.7	413.5	471.6	532.4	559.1	518.1	446.4	389.1	353.4
75°	240.9	254.9	276.7	311.0	357.0	405.4	420.2	384.3	338.3	295.4	272.1
77.5°	172.4	184.3	200.8	222.5	255.1	285.8	298.7	278.0	242.4	215.3	196.1
80°	132.5	138.8	152.8	170.7	196.4	215.9	224.5	211.3	186.3	166.0	151.2
82.5°	94.5	100.7	109.1	123.9	140.3	153.6	162.8	153.9	135.8	119.9	111.3
85°	46.0	49.9	54.6	60.8	73.3	81.1	80.3	74.8	67.8	61.6	56.9
87.5°	16.6	17.6	19.7	23.1	25.2	28.0	29.5	28.5	26.2	24.5	22.8
90°	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4	14.3
92.5°	11.1	10.1	9.1	8.2	8.2	9.3	10.4	11.4	12.5	13.4	14.3
95°	44.1	43.5	43.0	42.5	38.9	32.3	25.7	19.1	12.5	13.4	14.3
97.5°	94.0	94.9	95.9	96.8	90.8	77.7	64.6	51.5	38.5	33.6	28.7
100°	131.1	131.6	132.2	132.7	133.3	134.0	134.7	135.4	136.1	110.2	84.3
102.5°	169.4	170.1	170.7	171.4	171.9	172.4	172.8	173.2	173.6	168.7	163.8
105°	230.6	231.3	232.0	232.7	233.0	233.0	233.0	233.0	233.0	233.0	233.0
107.5°	293.4	293.4	293.4	293.4	293.6	293.9	294.3	294.6	295.0	295.0	295.1
110°	334.7	334.7	334.7	334.7	334.9	335.2	335.6	335.9	336.3	335.8	335.2





TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	373.9	374.3	374.8	375.2	375.5	375.7	375.9	376.1	376.3	375.7	375.0
115°	432.6	433.4	434.3	435.2	435.7	435.9	436.0	436.2	436.4	435.7	435.0
117.5°	491.9	491.8	491.8	491.8	492.1	492.7	493.4	494.1	494.7	493.8	492.9
120°	529.3	529.1	528.9	528.7	528.9	529.4	530.0	530.5	531.0	530.7	530.3
122.5°	563.3	563.9	564.6	565.2	565.7	565.9	566.2	566.4	566.7	566.3	566.0
125°	615.1	616.3	617.6	618.8	619.4	619.4	619.4	619.4	619.4	618.7	618.0
127.5°	663.7	664.6	665.5	666.3	666.7	666.6	666.5	666.4	666.3	665.9	665.5
130°	693.8	694.6	695.5	696.4	696.9	697.1	697.2	697.4	697.6	697.1	696.5
132.5°	723.9	724.9	725.9	727.0	727.3	726.9	726.5	726.1	725.7	725.6	725.5
135°	766.7	767.7	768.8	769.8	770.1	769.8	769.4	769.1	768.8	768.4	768.1
137.5°	805.8	806.7	807.6	808.5	808.8	808.5	808.2	807.9	807.5	807.6	807.7
140°	830.9	831.2	831.6	831.9	832.0	831.8	831.7	831.5	831.3	831.7	832.0
142.5°	853.9	854.1	854.3	854.5	854.7	855.0	855.2	855.5	855.7	855.8	855.9
145°	888.0	888.3	888.7	889.0	889.2	889.2	889.2	889.2	889.2	889.4	889.5
147.5°	917.3	917.2	917.1	917.1	917.1	917.3	917.5	917.8	918.0	918.2	918.4
150°	935.8	935.4	935.1	934.7	934.7	935.1	935.4	935.8	936.1	936.5	936.8
152.5°	953.5	952.7	952.0	951.2	951.0	951.3	951.7	952.0	952.4	952.7	953.1
155°	976.5	975.5	974.4	973.4	973.0	973.4	973.7	974.1	974.4	974.9	975.5
157.5°	994.9	994.3	993.7	993.0	992.7	992.8	992.8	992.8	992.9	993.4	994.0
160°	1007.0	1006.0	1004.9	1003.9	1003.5	1003.6	1003.8	1004.0	1004.1	1004.8	1005.5
162.5°	1017.0	1016.0	1014.9	1013.9	1013.5	1013.6	1013.8	1014.0	1014.2	1015.1	1016.1
165°	1030.5	1029.4	1028.4	1027.3	1026.9	1027.1	1027.3	1027.4	1027.6	1028.7	1029.7
167.5°	1040.5	1039.4	1038.3	1037.2	1036.8	1036.9	1037.1	1037.3	1037.5	1038.7	1040.0
170°	1045.9	1044.7	1043.5	1042.3	1041.8	1041.9	1042.1	1042.3	1042.5	1043.9	1045.2
172.5°	1049.7	1048.5	1047.3	1046.0	1045.6	1045.9	1046.2	1046.5	1046.8	1048.1	1049.3
175°	1053.9	1052.9	1051.9	1050.8	1050.4	1050.5	1050.7	1050.9	1051.1	1052.5	1053.8
177.5°	1056.0	1055.2	1054.4	1053.5	1053.2	1053.3	1053.4	1053.6	1053.7	1054.7	1055.7
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1920.7	1925.7	1936.3	1932.6	1937.6	1940.1	1942.6
5°	2075.9	2100.8	2111.7	2110.2	2126.5	2122.6	2118.7
7.5°	2251.1	2277.3	2292.0	2310.2	2320.8	2321.6	2330.8
10°	2350.3	2384.6	2398.6	2418.1	2430.6	2437.6	2436.8
12.5°	2426.3	2453.2	2484.6	2494.2	2511.0	2519.9	2516.6
15°	2517.9	2560.7	2593.5	2609.8	2630.9	2637.1	2645.7
17.5°	2599.6	2657.1	2695.3	2746.1	2765.3	2777.0	2770.1
20°	2661.3	2736.9	2775.1	2835.9	2869.4	2887.4	2881.1
22.5°	2734.3	2816.1	2886.7	2939.4	2990.4	3014.6	3019.6
25°	2859.3	2971.5	3075.2	3144.6	3207.7	3222.5	3255.3
27.5°	2999.0	3131.3	3242.2	3315.2	3359.1	3375.6	3385.9
30°	3086.9	3218.6	3302.1	3348.8	3362.9	3361.3	3359.7
32.5°	3129.9	3212.4	3228.5	3215.4	3183.3	3156.1	3127.8
35°	3069.0	3007.4	2915.4	2796.9	2709.6	2621.5	2613.0
37.5°	2760.1	2563.2	2410.1	2239.1	2140.4	2079.5	2037.4
40°	2469.5	2245.8	2060.3	1916.1	1815.5	1775.8	1736.8
42.5°	2154.0	1940.2	1775.9	1655.4	1579.8	1535.7	1504.8
45°	1750.0	1561.4	1432.8	1345.5	1285.4	1251.1	1231.6
47.5°	1434.0	1294.5	1185.2	1122.2	1080.7	1054.1	1054.2
50°	1264.4	1131.1	1058.6	1008.7	972.8	951.8	955.7
52.5°	1114.1	1014.5	952.6	910.8	884.3	871.3	870.9
55°	931.5	859.8	819.3	788.9	770.9	756.1	759.3
57.5°	796.8	736.3	709.2	684.0	671.5	665.6	657.0
60°	713.3	666.5	643.1	622.8	610.4	605.7	597.1
62.5°	639.1	602.3	579.5	563.0	551.7	550.2	543.5
65°	537.1	509.0	488.8	481.0	469.3	466.2	466.2
67.5°	442.8	422.7	406.9	399.7	394.6	395.4	391.6
70°	383.5	367.2	357.0	349.2	345.3	346.1	343.0
72.5°	335.5	317.3	308.4	303.7	298.6	300.6	299.3
75°	254.1	244.8	240.1	235.4	232.3	230.7	229.2
77.5°	186.6	178.4	174.8	172.1	172.6	168.8	171.8
80°	144.2	137.2	134.9	131.0	130.2	130.2	129.4
82.5°	105.5	101.6	99.9	96.7	95.3	96.5	94.5
85°	54.6	51.4	50.7	50.7	49.1	47.6	51.4
87.5°	23.0	20.7	20.8	20.3	20.4	19.9	18.7
90°	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	15.1	16.0	16.5	16.8	17.0	17.3	17.5
95°	15.1	16.0	16.4	16.4	16.4	16.4	16.4
97.5°	23.8	18.9	16.4	16.4	16.4	16.4	16.4
100°	58.4	32.5	19.2	18.5	17.8	17.1	16.4
102.5°	158.9	154.0	145.7	133.8	122.0	110.2	98.4
105°	233.0	233.0	233.0	232.8	232.6	232.4	232.3
107.5°	295.1	295.1	294.9	294.4	293.8	293.3	292.8
110°	334.7	334.2	334.0	334.2	334.4	334.5	334.7



TEST NUMBER: P333313

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	374.3	373.7	373.2	373.0	372.7	372.5	372.3
115°	434.3	433.6	432.7	431.7	430.6	429.6	428.6
117.5°	492.0	491.1	490.4	490.0	489.5	489.1	488.6
120°	530.0	529.6	529.0	528.1	527.3	526.4	525.5
122.5°	565.6	565.3	564.6	563.6	562.6	561.6	560.6
125°	617.3	616.6	616.0	615.5	614.9	614.4	613.9
127.5°	665.2	664.8	663.9	662.7	661.4	660.1	658.8
130°	696.0	695.5	694.8	693.9	693.1	692.2	691.3
132.5°	725.4	725.3	724.8	724.0	723.1	722.2	721.4
135°	767.7	767.4	766.7	765.6	764.6	763.5	762.5
137.5°	807.7	807.8	807.4	806.5	805.6	804.7	803.8
140°	832.4	832.7	832.4	831.3	830.3	829.2	828.2
142.5°	855.9	856.0	855.5	854.5	853.4	852.4	851.3
145°	889.7	889.9	889.4	888.4	887.4	886.3	885.3
147.5°	918.6	918.8	918.3	917.0	915.8	914.5	913.3
150°	937.2	937.5	937.0	935.6	934.2	932.8	931.4
152.5°	953.4	953.8	953.3	952.1	950.8	949.6	948.3
155°	976.0	976.5	976.1	974.7	973.3	971.9	970.5
157.5°	994.6	995.1	994.7	993.3	991.9	990.5	989.1
160°	1006.2	1006.9	1006.6	1005.2	1003.8	1002.4	1001.0
162.5°	1017.1	1018.0	1017.8	1016.2	1014.7	1013.2	1011.7
165°	1030.7	1031.8	1031.6	1030.2	1028.8	1027.4	1026.0
167.5°	1041.2	1042.5	1042.3	1040.7	1039.2	1037.6	1036.1
170°	1046.6	1048.0	1047.9	1046.4	1044.8	1043.2	1041.7
172.5°	1050.6	1051.9	1051.7	1050.1	1048.6	1047.0	1045.4
175°	1055.2	1056.6	1056.5	1055.0	1053.4	1051.9	1050.3
177.5°	1056.6	1057.6	1057.6	1056.4	1055.3	1054.2	1053.1
180°	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0	1055.0

(END OF REPORT)