

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333320

Luminaire Tested: **S125DIP-S1270D810U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333320
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D810U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7934.2 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333320

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333320

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	101	97	93	89	95	91	87	84	80	78	75	70	68	67	61	60	59	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	52	49	45
3	84	74	67	60	78	70	63	58	62	57	52	55	50	47	48	45	42	38
4	77	66	57	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12727	12727	12727
5°	12756	12635	12716
10°	12679	12545	12618
15°	12541	12395	12447
20°	12344	12183	12205
25°	12133	11932	11921
30°	11872	11662	11604
35°	11591	11371	11211
40°	11304	11054	10897
45°	10993	10766	10552
50°	10652	10417	10104
55°	10323	10025	9743
60°	9928	9627	9285
65°	9459	9149	8839
70°	9009	8597	8303
75°	8210	7938	7663
80°	7305	7189	7018
85°	6358	6469	6121



TEST NUMBER: P333320

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.8	2.3
10°-20°	524.9	6.6
20°-30°	775.0	9.8
30°-40°	904.3	11.4
40°-50°	908.3	11.4
50°-60°	797.3	10.0
60°-70°	594.1	7.5
70°-80°	339.7	4.3
80°-90°	101.0	1.3
90°-100°	67.3	0.8
100°-110°	198.7	2.5
110°-120°	336.6	4.2
120°-130°	443.0	5.6
130°-140°	496.4	6.3
140°-150°	486.5	6.1
150°-160°	408.6	5.2
160°-170°	271.6	3.4
170°-180°	95.1	1.2
0°-30°	1485.7	18.7
0°-40°	2390.0	30.1
0°-60°	4095.6	51.6
0°-90°	5130.4	64.7
90°-120°	602.7	7.6
90°-150°	2028.6	25.6
90°-180°	2804.0	35.3
0°-180°	7934.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1968	1964	1949	1962	1961	187
15°	1876	1870	1854	1861	1862	528
25°	1703	1694	1674	1677	1673	783
35°	1470	1463	1442	1434	1422	919
45°	1204	1197	1179	1161	1155	927
55°	917	911	890	876	865	818
65°	619	615	599	585	578	614
75°	329	326	318	313	307	351
85°	86	87	87	86	83	96
90°	1	7	12	16	19	7
95°	51	53	60	66	67	54
105°	178	182	187	191	194	190
115°	337	340	342	341	340	333
125°	492	496	497	496	495	440
135°	640	644	645	645	642	493
145°	775	778	780	780	778	484
155°	887	887	888	890	887	408
165°	964	963	963	966	962	272
175°	1002	1000	999	1003	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P333320

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1975.7	1974.9	1974.1	1973.2	1972.4	1970.6	1967.8	1965.0	1962.3	1959.5	1962.3
5°	1967.6	1966.9	1966.2	1965.5	1964.8	1962.8	1959.3	1955.8	1952.4	1948.9	1952.0
7.5°	1949.5	1948.8	1948.1	1947.4	1946.7	1944.5	1940.7	1936.9	1933.1	1929.3	1932.3
10°	1933.3	1932.6	1931.9	1931.2	1930.5	1928.3	1924.5	1920.7	1916.8	1913.0	1915.8
12.5°	1913.3	1912.1	1910.9	1909.6	1908.4	1906.0	1902.4	1898.9	1895.4	1891.8	1894.1
15°	1875.6	1874.6	1873.5	1872.5	1871.5	1869.0	1865.2	1861.4	1857.6	1853.8	1855.5
17.5°	1832.3	1830.8	1829.2	1827.7	1826.2	1823.4	1819.5	1815.5	1811.6	1807.6	1809.8
20°	1796.1	1795.4	1794.7	1794.0	1793.3	1790.7	1786.2	1781.7	1777.2	1772.7	1775.1
22.5°	1759.9	1758.7	1757.4	1756.2	1754.9	1752.2	1748.0	1743.8	1739.5	1735.3	1736.9
25°	1702.6	1700.8	1699.1	1697.4	1695.6	1692.5	1688.0	1683.5	1679.0	1674.5	1675.2
27.5°	1635.5	1634.5	1633.4	1632.4	1631.4	1628.5	1623.9	1619.2	1614.6	1609.9	1610.1
30°	1591.9	1590.8	1589.8	1588.7	1587.7	1584.6	1579.4	1574.2	1569.0	1563.8	1563.1
32.5°	1544.5	1542.9	1541.3	1539.7	1538.1	1535.0	1530.3	1525.7	1521.0	1516.4	1515.2
35°	1470.2	1468.9	1467.5	1466.1	1464.7	1461.6	1456.7	1451.9	1447.0	1442.2	1440.5
37.5°	1393.2	1391.5	1389.8	1388.0	1386.3	1383.1	1378.6	1374.0	1369.4	1364.9	1362.3
40°	1340.8	1339.1	1337.4	1335.6	1333.9	1330.6	1325.8	1320.9	1316.1	1311.2	1308.1
42.5°	1284.7	1283.3	1281.8	1280.3	1278.9	1275.7	1270.9	1266.0	1261.2	1256.3	1253.5
45°	1203.6	1202.3	1200.9	1199.5	1198.1	1195.3	1191.2	1187.0	1182.9	1178.7	1174.5
47.5°	1116.3	1116.4	1116.5	1116.5	1116.6	1114.1	1109.2	1104.2	1099.2	1094.2	1090.0
50°	1060.2	1059.2	1058.1	1057.1	1056.0	1053.4	1049.3	1045.1	1041.0	1036.8	1032.3
52.5°	1002.8	1002.1	1001.3	1000.5	999.8	997.2	992.7	988.3	983.9	979.4	975.5
55°	916.8	915.7	914.7	913.6	912.6	909.7	904.8	900.0	895.1	890.3	887.1
57.5°	826.0	825.5	824.9	824.4	823.8	821.5	817.4	813.3	809.2	805.1	801.1
60°	768.6	767.3	765.9	764.5	763.1	760.5	756.7	752.9	749.1	745.3	741.8
62.5°	708.8	707.7	706.6	705.4	704.3	702.2	698.9	695.6	692.4	689.1	685.4
65°	619.0	618.3	617.6	616.9	616.2	613.9	610.1	606.3	602.5	598.7	595.6
67.5°	532.0	530.5	529.1	527.6	526.2	524.0	521.2	518.3	515.5	512.6	510.0
70°	477.1	475.4	473.6	471.9	470.2	467.7	464.6	461.5	458.4	455.3	453.2
72.5°	417.2	416.0	414.9	413.7	412.5	410.9	408.9	406.9	404.9	402.9	400.5
75°	329.0	328.3	327.6	326.9	326.2	325.0	323.3	321.5	319.8	318.1	317.0
77.5°	247.6	247.3	247.0	246.8	246.5	245.9	244.9	243.9	242.9	242.0	241.4
80°	196.4	196.4	196.4	196.4	196.4	196.1	195.4	194.7	194.0	193.3	193.0
82.5°	151.5	151.0	150.4	149.9	149.3	149.0	148.8	148.7	148.6	148.4	147.8
85°	85.8	86.1	86.4	86.8	87.1	87.3	87.3	87.3	87.3	87.3	87.0
87.5°	33.8	34.1	34.4	34.7	34.9	35.1	35.0	35.0	35.0	34.9	35.1
90°	0.8	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4
92.5°	18.9	19.9	20.9	21.8	22.8	24.0	25.5	27.0	28.5	30.0	31.2
95°	50.8	51.2	51.5	51.9	52.2	53.3	55.0	56.7	58.5	60.2	61.4
97.5°	84.5	84.6	84.7	84.9	85.0	86.3	88.7	91.1	93.5	95.9	97.0
100°	109.5	109.5	109.5	109.5	109.5	110.6	112.9	115.1	117.4	119.6	121.2
102.5°	136.4	137.1	137.8	138.5	139.2	140.1	141.2	142.4	143.5	144.7	146.4
105°	178.3	179.2	180.0	180.9	181.8	182.7	183.8	184.8	185.8	186.9	187.9
107.5°	224.6	225.4	226.3	227.2	228.1	228.9	229.7	230.5	231.3	232.1	232.6
110°	256.5	257.4	258.2	259.1	260.0	260.7	261.2	261.7	262.2	262.7	263.3



TEST NUMBER: P333320

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	289.0	289.5	289.9	290.4	290.8	291.4	292.0	292.7	293.4	294.0	294.3
115°	337.0	337.7	338.4	339.1	339.8	340.3	340.7	341.0	341.4	341.7	341.5
117.5°	385.2	385.5	385.8	386.1	386.4	386.8	387.1	387.4	387.7	388.0	388.1
120°	415.2	416.1	417.0	417.8	418.7	419.2	419.4	419.6	419.7	419.9	419.9
122.5°	447.7	448.1	448.4	448.7	449.0	449.4	449.8	450.3	450.7	451.2	451.0
125°	491.8	492.9	493.9	495.0	496.0	496.6	496.8	497.0	497.1	497.3	497.0
127.5°	538.8	539.4	539.9	540.5	541.1	541.5	541.7	541.9	542.2	542.4	542.2
130°	566.9	567.8	568.7	569.5	570.4	571.0	571.3	571.7	572.0	572.4	572.2
132.5°	595.1	596.5	597.9	599.3	600.8	601.4	601.4	601.3	601.2	601.2	601.0
135°	639.6	640.7	641.7	642.8	643.8	644.4	644.6	644.8	644.9	645.1	645.1
137.5°	681.6	682.6	683.6	684.6	685.6	686.3	686.7	687.0	687.4	687.8	688.0
140°	708.5	709.3	710.2	711.1	711.9	712.6	713.1	713.7	714.2	714.7	715.1
142.5°	735.4	736.1	736.8	737.5	738.3	739.0	739.6	740.3	740.9	741.6	741.8
145°	774.9	775.6	776.3	777.0	777.7	778.3	778.8	779.3	779.9	780.4	780.4
147.5°	811.5	811.9	812.3	812.7	813.0	813.4	813.9	814.3	814.7	815.1	815.5
150°	835.9	835.7	835.6	835.4	835.2	835.5	836.2	836.9	837.6	838.3	838.3
152.5°	855.9	856.2	856.4	856.7	856.9	857.2	857.4	857.7	858.0	858.3	858.7
155°	886.7	886.7	886.7	886.7	886.7	886.8	887.0	887.2	887.3	887.5	888.2
157.5°	914.3	913.9	913.5	913.1	912.7	912.6	912.8	913.0	913.1	913.3	914.0
160°	930.5	930.0	929.5	929.0	928.4	928.3	928.4	928.6	928.8	929.0	929.7
162.5°	944.9	944.5	944.1	943.8	943.4	943.2	943.2	943.3	943.3	943.4	944.2
165°	964.2	963.8	963.5	963.1	962.8	962.7	962.8	963.0	963.2	963.4	964.1
167.5°	980.4	979.7	979.0	978.3	977.6	977.3	977.3	977.3	977.3	977.3	978.3
170°	989.2	988.5	987.8	987.1	986.4	986.0	986.0	986.0	986.0	986.0	987.1
172.5°	995.4	994.7	994.0	993.3	992.6	992.3	992.3	992.3	992.3	992.3	993.3
175°	1002.5	1001.8	1001.1	1000.4	999.7	999.3	999.3	999.3	999.3	999.3	1000.4
177.5°	1006.1	1005.5	1005.0	1004.4	1003.8	1003.5	1003.4	1003.2	1003.1	1002.9	1003.8
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333320

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1965.0	1967.8	1970.6	1971.8	1971.6	1971.3	1971.0	1970.7
5°	1955.1	1958.3	1961.4	1962.8	1962.4	1962.1	1961.7	1961.4
7.5°	1935.3	1938.4	1941.4	1942.8	1942.5	1942.1	1941.8	1941.4
10°	1918.6	1921.4	1924.1	1925.3	1925.0	1924.6	1924.3	1924.0
12.5°	1896.3	1898.5	1900.7	1901.8	1901.7	1901.6	1901.6	1901.5
15°	1857.3	1859.0	1860.7	1861.6	1861.6	1861.6	1861.6	1861.6
17.5°	1811.9	1814.1	1816.2	1816.4	1814.7	1813.0	1811.2	1809.5
20°	1777.6	1780.0	1782.4	1782.8	1781.0	1779.3	1777.6	1775.8
22.5°	1738.5	1740.1	1741.7	1741.9	1740.7	1739.5	1738.3	1737.2
25°	1675.9	1676.6	1677.3	1677.1	1676.1	1675.0	1674.0	1672.9
27.5°	1610.2	1610.4	1610.5	1610.0	1609.0	1608.0	1606.9	1605.9
30°	1562.4	1561.7	1561.0	1560.2	1559.1	1558.1	1557.0	1556.0
32.5°	1513.9	1512.7	1511.4	1509.8	1508.0	1506.1	1504.2	1502.4
35°	1438.7	1437.0	1435.3	1433.0	1430.2	1427.5	1424.7	1421.9
37.5°	1359.7	1357.2	1354.6	1352.5	1350.9	1349.3	1347.7	1346.1
40°	1305.0	1301.9	1298.7	1296.7	1295.6	1294.6	1293.5	1292.5
42.5°	1250.7	1247.8	1245.0	1242.8	1241.2	1239.6	1238.0	1236.4
45°	1170.4	1166.2	1162.1	1159.5	1158.4	1157.4	1156.3	1155.3
47.5°	1085.7	1081.5	1077.3	1074.0	1071.5	1069.1	1066.7	1064.3
50°	1027.8	1023.3	1018.8	1015.3	1012.9	1010.5	1008.1	1005.6
52.5°	971.5	967.6	963.6	960.3	957.6	954.9	952.2	949.5
55°	884.0	880.9	877.8	875.0	872.6	870.2	867.7	865.3
57.5°	797.1	793.1	789.1	786.4	785.1	783.8	782.4	781.1
60°	738.3	734.9	731.4	728.5	726.0	723.6	721.2	718.8
62.5°	681.6	677.9	674.2	671.4	669.5	667.6	665.7	663.9
65°	592.5	589.3	586.2	584.0	582.6	581.2	579.8	578.4
67.5°	507.4	504.7	502.1	500.4	499.5	498.7	497.9	497.0
70°	451.1	449.0	446.9	445.2	443.8	442.4	441.1	439.7
72.5°	398.2	395.8	393.5	391.6	390.2	388.8	387.4	386.0
75°	316.0	314.9	313.9	312.7	311.3	309.9	308.5	307.1
77.5°	240.7	240.1	239.5	238.7	237.7	236.7	235.8	234.8
80°	192.6	192.3	191.9	191.4	190.7	190.0	189.3	188.7
82.5°	147.2	146.6	145.9	145.6	145.4	145.3	145.1	145.0
85°	86.6	86.3	85.9	85.4	84.7	84.0	83.3	82.6
87.5°	35.3	35.5	35.6	35.5	35.0	34.6	34.1	33.7
90°	14.2	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	32.3	33.5	34.6	35.4	35.8	36.1	36.5	36.9
95°	62.6	63.9	65.1	65.9	66.2	66.6	66.9	67.2
97.5°	98.2	99.3	100.5	101.1	101.3	101.5	101.8	102.0
100°	122.8	124.3	125.9	126.9	127.2	127.5	127.9	128.2
102.5°	148.1	149.8	151.5	152.6	153.1	153.5	154.0	154.5
105°	189.0	190.0	191.1	191.8	192.4	192.9	193.4	193.9
107.5°	233.1	233.6	234.2	234.4	234.4	234.3	234.3	234.3
110°	263.8	264.3	264.8	265.0	264.8	264.6	264.5	264.3



TEST NUMBER: P333320

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.5	294.7	295.0	295.0	294.6	294.3	294.0	293.7
115°	341.4	341.2	341.0	340.8	340.7	340.5	340.3	340.2
117.5°	388.3	388.4	388.6	388.3	387.6	386.9	386.2	385.5
120°	419.9	419.9	419.9	419.6	418.9	418.2	417.5	416.8
122.5°	450.9	450.8	450.6	450.3	449.7	449.2	448.6	448.1
125°	496.6	496.3	495.9	495.7	495.5	495.3	495.2	495.0
127.5°	542.0	541.8	541.7	541.4	541.1	540.7	540.4	540.0
130°	572.0	571.9	571.7	571.4	571.1	570.7	570.4	570.0
132.5°	600.8	600.6	600.5	600.1	599.7	599.2	598.7	598.2
135°	645.1	645.1	645.1	644.8	644.1	643.4	642.7	642.0
137.5°	688.2	688.4	688.6	688.3	687.4	686.6	685.7	684.8
140°	715.4	715.7	716.1	715.8	715.0	714.1	713.2	712.4
142.5°	742.0	742.2	742.4	742.1	741.2	740.4	739.5	738.6
145°	780.4	780.4	780.4	780.1	779.6	779.1	778.6	778.0
147.5°	815.9	816.4	816.8	816.4	815.2	814.0	812.9	811.7
150°	838.3	838.3	838.3	838.1	837.7	837.4	837.0	836.7
152.5°	859.1	859.5	859.9	859.8	859.2	858.6	858.0	857.3
155°	888.9	889.6	890.3	890.2	889.3	888.5	887.6	886.7
157.5°	914.7	915.4	916.1	915.9	914.7	913.6	912.4	911.3
160°	930.4	931.0	931.7	931.7	930.8	929.9	929.0	928.2
162.5°	945.0	945.9	946.7	946.6	945.6	944.6	943.6	942.6
165°	964.8	965.5	966.1	966.0	964.9	963.9	962.8	961.8
167.5°	979.4	980.4	981.5	981.4	980.4	979.3	978.2	977.1
170°	988.1	989.2	990.2	990.1	988.9	987.7	986.5	985.3
172.5°	994.4	995.4	996.5	996.5	995.4	994.3	993.2	992.1
175°	1001.4	1002.5	1003.5	1003.4	1002.2	1001.0	999.8	998.6
177.5°	1004.6	1005.4	1006.3	1006.2	1005.2	1004.3	1003.3	1002.3
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8

(END OF REPORT)