

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333321

Luminaire Tested: **S125DIP-S1270D810U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333321
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D810U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8038.6 lumens
Efficiency: N/A
Efficacy: 132.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333321

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333321

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	64
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	54
2	92	84	78	72	86	79	74	69	70	66	62	61	58	55	53	51	49	45
3	84	74	66	60	78	70	63	58	62	56	52	54	50	47	47	44	41	38
4	77	65	57	51	72	62	54	49	55	49	44	48	44	40	42	39	36	33
5	70	58	50	44	66	55	48	42	49	43	38	43	39	35	38	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	35	31	27	25
7	60	47	39	34	56	45	38	32	40	34	30	36	31	27	32	28	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	39	32	27	49	38	30	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12727	12727	12727
5°	12756	12635	12716
10°	12679	12545	12618
15°	12541	12395	12447
20°	12344	12183	12205
25°	12133	11932	11921
30°	11872	11662	11604
35°	11591	11371	11211
40°	11304	11054	10897
45°	10993	10766	10552
50°	10652	10417	10104
55°	10323	10025	9743
60°	9928	9627	9285
65°	9459	9149	8839
70°	9009	8597	8303
75°	8210	7938	7663
80°	7305	7189	7018
85°	6358	6469	6121



TEST NUMBER: P333321

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.8	2.3
10°-20°	524.9	6.5
20°-30°	775.0	9.6
30°-40°	904.3	11.2
40°-50°	908.3	11.3
50°-60°	797.3	9.9
60°-70°	594.1	7.4
70°-80°	339.7	4.2
80°-90°	101.0	1.3
90°-100°	281.1	3.5
100°-110°	604.3	7.5
110°-120°	567.1	7.1
120°-130°	459.6	5.7
130°-140°	368.8	4.6
140°-150°	278.3	3.5
150°-160°	195.9	2.4
160°-170°	115.5	1.4
170°-180°	37.6	0.5
0°-30°	1485.7	18.5
0°-40°	2390.0	29.7
0°-60°	4095.6	50.9
0°-90°	5130.3	63.8
90°-120°	1452.5	18.1
90°-150°	2559.3	31.8
90°-180°	2908.0	36.2
0°-180°	8038.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1968	1964	1949	1962	1961	187
15°	1876	1870	1854	1861	1862	528
25°	1703	1694	1674	1677	1673	783
35°	1470	1463	1442	1434	1422	919
45°	1204	1197	1179	1161	1155	927
55°	917	911	890	876	865	818
65°	619	615	599	585	578	614
75°	329	326	318	313	307	351
85°	86	87	87	86	83	96
90°	1	7	12	16	18	6
95°	26	76	693	314	184	27
105°	88	124	567	1116	1036	93
115°	158	190	455	981	1154	155
125°	219	256	436	780	909	194
135°	256	308	433	654	755	199
145°	299	342	435	541	596	187
155°	341	367	424	479	500	157
165°	372	382	407	431	438	105
175°	387	387	390	395	393	37
180°	388	388	388	388	388	



TEST NUMBER: P333321

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1975.7	1974.9	1974.1	1973.2	1972.4	1970.6	1967.8	1965.0	1962.3	1959.5	1962.3
5°	1967.6	1966.9	1966.2	1965.5	1964.8	1962.8	1959.3	1955.8	1952.4	1948.9	1952.0
7.5°	1949.5	1948.8	1948.1	1947.4	1946.7	1944.5	1940.7	1936.9	1933.1	1929.3	1932.3
10°	1933.3	1932.6	1931.9	1931.2	1930.5	1928.3	1924.5	1920.7	1916.8	1913.0	1915.8
12.5°	1913.3	1912.1	1910.9	1909.6	1908.4	1906.0	1902.4	1898.9	1895.4	1891.8	1894.1
15°	1875.6	1874.6	1873.5	1872.5	1871.5	1869.0	1865.2	1861.4	1857.6	1853.8	1855.5
17.5°	1832.3	1830.8	1829.2	1827.7	1826.2	1823.4	1819.5	1815.5	1811.6	1807.6	1809.8
20°	1796.1	1795.4	1794.7	1794.0	1793.3	1790.7	1786.2	1781.7	1777.2	1772.7	1775.1
22.5°	1759.9	1758.7	1757.4	1756.2	1754.9	1752.2	1748.0	1743.8	1739.5	1735.3	1736.9
25°	1702.6	1700.8	1699.1	1697.4	1695.6	1692.5	1688.0	1683.5	1679.0	1674.5	1675.2
27.5°	1635.5	1634.5	1633.4	1632.4	1631.4	1628.5	1623.9	1619.2	1614.6	1609.9	1610.1
30°	1591.9	1590.8	1589.8	1588.7	1587.7	1584.6	1579.4	1574.2	1569.0	1563.8	1563.1
32.5°	1544.5	1542.9	1541.3	1539.7	1538.1	1535.0	1530.3	1525.7	1521.0	1516.4	1515.2
35°	1470.2	1468.9	1467.5	1466.1	1464.7	1461.6	1456.7	1451.9	1447.0	1442.2	1440.5
37.5°	1393.2	1391.5	1389.8	1388.0	1386.3	1383.1	1378.6	1374.0	1369.4	1364.9	1362.3
40°	1340.8	1339.1	1337.4	1335.6	1333.9	1330.6	1325.8	1320.9	1316.1	1311.2	1308.1
42.5°	1284.7	1283.3	1281.8	1280.3	1278.9	1275.7	1270.9	1266.0	1261.2	1256.3	1253.5
45°	1203.6	1202.3	1200.9	1199.5	1198.1	1195.3	1191.2	1187.0	1182.9	1178.7	1174.5
47.5°	1116.3	1116.4	1116.5	1116.5	1116.6	1114.1	1109.2	1104.2	1099.2	1094.2	1090.0
50°	1060.2	1059.2	1058.1	1057.1	1056.0	1053.4	1049.3	1045.1	1041.0	1036.8	1032.3
52.5°	1002.8	1002.1	1001.3	1000.5	999.8	997.2	992.7	988.3	983.9	979.4	975.5
55°	916.8	915.7	914.7	913.6	912.6	909.7	904.8	900.0	895.1	890.3	887.1
57.5°	826.0	825.5	824.9	824.4	823.8	821.5	817.4	813.3	809.2	805.1	801.1
60°	768.6	767.3	765.9	764.5	763.1	760.5	756.7	752.9	749.1	745.3	741.8
62.5°	708.8	707.7	706.6	705.4	704.3	702.2	698.9	695.6	692.4	689.1	685.4
65°	619.0	618.3	617.6	616.9	616.2	613.9	610.1	606.3	602.5	598.7	595.6
67.5°	532.0	530.5	529.1	527.6	526.2	524.0	521.2	518.3	515.5	512.6	510.0
70°	477.1	475.4	473.6	471.9	470.2	467.7	464.6	461.5	458.4	455.3	453.2
72.5°	417.2	416.0	414.9	413.7	412.5	410.9	408.9	406.9	404.9	402.9	400.5
75°	329.0	328.3	327.6	326.9	326.2	325.0	323.3	321.5	319.8	318.1	317.0
77.5°	247.6	247.3	247.0	246.8	246.5	245.9	244.9	243.9	242.9	242.0	241.4
80°	196.4	196.4	196.4	196.4	196.4	196.1	195.4	194.7	194.0	193.3	193.0
82.5°	151.5	151.0	150.4	149.9	149.3	149.0	148.8	148.7	148.6	148.4	147.8
85°	85.8	86.1	86.4	86.8	87.1	87.3	87.3	87.3	87.3	87.3	87.0
87.5°	33.8	34.0	34.3	34.6	34.9	35.1	35.0	35.0	34.9	34.9	35.1
90°	0.8	1.6	3.1	4.7	6.3	7.8	8.6	10.2	10.9	12.5	13.3
92.5°	9.5	11.6	18.1	27.8	41.3	64.1	106.8	178.4	256.1	252.1	204.1
95°	25.8	26.6	32.8	41.4	58.6	93.8	177.5	349.5	565.3	692.8	677.9
97.5°	42.8	43.8	48.2	56.8	72.2	97.6	152.9	279.0	504.8	739.8	857.7
100°	54.7	56.3	59.4	68.0	82.9	106.3	151.7	253.3	450.4	706.1	901.5
102.5°	67.9	68.8	71.3	80.5	94.1	117.0	157.3	242.7	409.1	646.6	875.3
105°	88.4	88.4	92.3	100.1	112.6	134.5	168.9	238.5	369.1	566.9	791.3
107.5°	108.4	109.9	113.7	120.1	133.1	152.8	186.1	245.7	352.2	512.0	705.6
110°	122.8	124.3	127.4	134.5	146.2	166.5	198.6	252.6	347.2	486.3	656.8



TEST NUMBER: P333321

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	137.1	138.7	141.2	148.2	160.0	179.7	210.5	261.3	347.2	471.3	620.5
115°	157.9	159.5	161.9	168.9	180.6	200.2	229.1	274.4	349.5	455.1	580.9
117.5°	176.7	179.1	181.6	188.6	201.9	220.8	248.2	289.5	354.7	447.1	557.3
120°	189.2	191.6	194.7	201.7	215.0	234.6	261.9	299.5	359.7	443.3	544.2
122.5°	202.4	204.1	206.6	213.6	228.2	247.7	275.1	310.7	364.0	440.2	532.9
125°	218.9	220.5	224.4	231.4	246.3	266.6	292.4	326.0	371.4	436.3	517.6
127.5°	231.9	234.3	239.3	248.2	264.0	284.3	309.2	340.1	379.7	434.4	503.5
130°	240.0	242.4	248.6	258.8	275.2	295.6	319.8	349.5	384.7	433.2	494.2
132.5°	246.3	249.3	256.8	268.2	285.2	305.6	329.8	357.6	390.3	433.2	486.7
135°	256.5	259.6	269.0	281.5	297.9	319.0	343.3	369.1	398.0	433.2	477.7
137.5°	269.3	271.6	280.4	292.9	309.0	330.7	352.8	377.5	405.0	434.1	469.8
140°	276.8	279.1	288.5	301.0	315.9	337.0	359.7	383.1	408.1	434.7	466.0
142.5°	285.5	287.3	296.0	308.5	322.8	342.6	364.0	386.3	410.0	435.4	462.9
145°	298.7	300.2	308.1	319.0	333.1	351.1	371.4	390.9	412.1	434.7	458.2
147.5°	312.4	313.4	320.1	330.3	342.5	358.3	376.1	393.8	412.8	432.7	453.3
150°	320.6	322.1	327.6	337.8	348.7	362.0	379.2	395.6	412.8	430.8	449.6
152.5°	329.3	330.3	335.1	344.0	354.4	366.4	382.3	396.9	412.2	428.3	445.2
155°	340.9	340.9	345.6	353.4	361.2	372.2	385.5	398.0	410.5	423.8	437.9
157.5°	351.2	351.1	354.8	361.5	368.4	376.7	388.1	398.8	408.5	419.1	431.0
160°	358.1	357.3	360.5	365.9	372.2	379.2	389.4	398.8	406.6	416.0	425.4
162.5°	363.7	363.0	366.1	370.9	375.9	381.7	390.6	398.1	404.7	412.2	420.3
165°	372.2	370.6	373.0	376.9	380.0	384.7	390.9	397.2	401.9	406.6	412.8
167.5°	377.8	377.0	378.4	380.6	382.8	385.8	390.9	395.3	397.5	401.1	405.5
170°	381.6	380.8	381.6	383.1	384.7	387.0	390.9	394.1	395.6	398.0	401.1
172.5°	384.1	382.7	383.4	385.0	385.9	387.0	390.3	392.8	393.1	394.2	396.7
175°	387.0	385.5	386.3	387.0	387.0	387.0	389.4	390.9	390.2	390.2	390.9
177.5°	388.4	387.2	387.2	387.8	387.2	387.2	388.4	389.1	387.8	387.8	388.4
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333321

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1965.0	1967.8	1970.6	1971.8	1971.6	1971.3	1971.0	1970.7
5°	1955.1	1958.3	1961.4	1962.8	1962.4	1962.1	1961.7	1961.4
7.5°	1935.3	1938.4	1941.4	1942.8	1942.5	1942.1	1941.8	1941.4
10°	1918.6	1921.4	1924.1	1925.3	1925.0	1924.6	1924.3	1924.0
12.5°	1896.3	1898.5	1900.7	1901.8	1901.7	1901.6	1901.6	1901.5
15°	1857.3	1859.0	1860.7	1861.6	1861.6	1861.6	1861.6	1861.6
17.5°	1811.9	1814.1	1816.2	1816.4	1814.7	1813.0	1811.2	1809.5
20°	1777.6	1780.0	1782.4	1782.8	1781.0	1779.3	1777.6	1775.8
22.5°	1738.5	1740.1	1741.7	1741.9	1740.7	1739.5	1738.3	1737.2
25°	1675.9	1676.6	1677.3	1677.1	1676.1	1675.0	1674.0	1672.9
27.5°	1610.2	1610.4	1610.5	1610.0	1609.0	1608.0	1606.9	1605.9
30°	1562.4	1561.7	1561.0	1560.2	1559.1	1558.1	1557.0	1556.0
32.5°	1513.9	1512.7	1511.4	1509.8	1508.0	1506.1	1504.2	1502.4
35°	1438.7	1437.0	1435.3	1433.0	1430.2	1427.5	1424.7	1421.9
37.5°	1359.7	1357.2	1354.6	1352.5	1350.9	1349.3	1347.7	1346.1
40°	1305.0	1301.9	1298.7	1296.7	1295.6	1294.6	1293.5	1292.5
42.5°	1250.7	1247.8	1245.0	1242.8	1241.2	1239.6	1238.0	1236.4
45°	1170.4	1166.2	1162.1	1159.5	1158.4	1157.4	1156.3	1155.3
47.5°	1085.7	1081.5	1077.3	1074.0	1071.5	1069.1	1066.7	1064.3
50°	1027.8	1023.3	1018.8	1015.3	1012.9	1010.5	1008.1	1005.6
52.5°	971.5	967.6	963.6	960.3	957.6	954.9	952.2	949.5
55°	884.0	880.9	877.8	875.0	872.6	870.2	867.7	865.3
57.5°	797.1	793.1	789.1	786.4	785.1	783.8	782.4	781.1
60°	738.3	734.9	731.4	728.5	726.0	723.6	721.2	718.8
62.5°	681.6	677.9	674.2	671.4	669.5	667.6	665.7	663.9
65°	592.5	589.3	586.2	584.0	582.6	581.2	579.8	578.4
67.5°	507.4	504.7	502.1	500.4	499.5	498.7	497.9	497.0
70°	451.1	449.0	446.9	445.2	443.8	442.4	441.1	439.7
72.5°	398.2	395.8	393.5	391.6	390.2	388.8	387.4	386.0
75°	316.0	314.9	313.9	312.7	311.3	309.9	308.5	307.1
77.5°	240.7	240.1	239.5	238.7	237.7	236.7	235.8	234.8
80°	192.6	192.3	191.9	191.4	190.7	190.0	189.3	188.7
82.5°	147.2	146.6	145.9	145.6	145.4	145.3	145.1	145.0
85°	86.6	86.3	85.9	85.4	84.7	84.0	83.3	82.6
87.5°	35.2	35.4	35.6	35.6	35.0	34.5	34.1	33.5
90°	14.1	14.9	15.6	17.2	17.2	17.2	18.0	18.0
92.5°	138.6	100.6	75.7	64.1	54.1	52.2	51.1	49.9
95°	562.2	443.3	347.2	281.5	226.0	202.5	196.3	183.7
97.5°	837.3	753.9	660.2	568.9	520.6	476.8	454.1	444.1
100°	961.7	923.4	842.9	761.6	707.6	651.3	622.4	609.9
102.5°	1003.6	1027.3	988.6	933.6	875.9	835.8	804.4	795.0
105°	978.9	1086.1	1120.5	1111.9	1086.8	1061.0	1045.4	1036.0
107.5°	890.7	1033.7	1122.0	1162.8	1175.5	1175.3	1170.2	1163.9
110°	825.7	974.2	1084.5	1150.9	1186.1	1201.0	1206.5	1206.5



TEST NUMBER: P333321

CATALOG NUMBER: S125DIP-S1270D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	774.4	915.4	1026.9	1105.3	1156.7	1182.2	1195.8	1201.5
115°	710.0	831.2	938.3	1023.5	1084.5	1122.0	1143.9	1154.1
117.5°	668.4	772.8	865.1	943.3	1004.3	1043.0	1064.8	1071.0
120°	645.8	739.7	825.7	894.5	952.3	989.9	1011.0	1017.2
122.5°	629.0	715.9	792.5	857.0	908.6	943.0	964.1	969.7
125°	604.4	684.2	752.2	808.5	852.3	884.3	901.5	909.3
127.5°	579.4	653.8	717.3	770.0	809.7	838.0	854.3	857.7
130°	563.7	632.6	693.5	744.4	783.5	809.3	824.9	829.6
132.5°	548.1	612.5	667.9	716.8	755.9	781.7	796.1	801.4
135°	527.8	581.7	631.8	676.3	710.7	736.5	750.6	755.3
137.5°	510.6	554.2	595.8	633.6	664.5	687.9	700.9	706.1
140°	501.2	537.9	573.9	606.7	635.7	656.0	667.7	671.6
142.5°	493.1	524.2	555.1	583.6	608.2	625.4	636.5	639.7
145°	482.4	506.7	530.9	552.0	570.8	584.1	592.7	595.8
147.5°	472.4	492.1	510.7	526.7	541.5	552.2	557.2	558.6
150°	466.8	484.0	498.8	512.9	524.7	534.0	537.2	537.9
152.5°	460.5	475.9	489.5	500.4	510.3	517.8	520.9	521.7
155°	451.2	463.7	474.6	483.2	491.0	496.5	498.8	499.6
157.5°	441.8	452.1	460.5	467.3	473.4	477.9	480.1	479.9
160°	435.5	443.3	451.2	456.6	462.1	466.0	467.6	466.8
162.5°	428.6	435.8	442.4	447.2	451.5	454.7	455.1	454.9
165°	419.1	424.6	429.3	433.2	436.3	437.9	437.9	437.9
167.5°	410.0	413.6	417.2	420.0	421.6	423.0	422.4	422.2
170°	405.0	407.4	409.7	411.3	412.8	413.6	413.6	412.8
172.5°	399.4	401.7	403.5	404.4	404.7	406.1	404.9	404.1
175°	393.3	393.3	394.9	394.9	394.9	395.6	394.1	393.3
177.5°	389.1	389.7	389.7	389.7	389.1	389.7	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)