

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P334796

Luminaire Tested: **S124IP-S590U835-4F0-1E-UDD-4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P334796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124IP-S590U835-4F0-1E-UDD-4
Description: DEFINE 4 INDIRECT LED LUMINAIRE, BATWING OPTIC
PENDANT MOUNT, 590 LUMENS PER FOOT
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2115.9 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect


Input Watts (W): 18.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P334796

CATALOG NUMBER: S124IP-S590U835-4F0-1E-UDD-4

Luminous Intensity Polar Plot





TEST NUMBER: P334796

CATALOG NUMBER: S124IP-S590U835-4F0-1E-UDD-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0



TEST NUMBER: P334796

CATALOG NUMBER: S124IP-S590U835-4F0-1E-UDD-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.1	0.1
90°-100°	210.4	9.9
100°-110°	439.4	20.8
110°-120°	390.5	18.5
120°-130°	328.8	15.5
130°-140°	274.3	13.0
140°-150°	209.4	9.9
150°-160°	147.2	7.0
160°-170°	86.6	4.1
170°-180°	28.2	1.3
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.1	0.1
90°-120°	1040.3	49.2
90°-150°	1852.8	87.6
90°-180°	2115.0	100.0
0°-180°	2115.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	5	10	11	12	1
95°	19	59	465	230	139	21
105°	67	97	374	806	803	71
115°	118	148	334	641	771	117
125°	164	194	332	546	615	146
135°	194	232	329	484	550	150
145°	224	257	327	408	449	141
155°	255	275	318	360	376	118
165°	278	286	305	323	328	78
175°	290	290	293	297	296	28
180°	290	290	290	290	290	



TEST NUMBER: P334796

CATALOG NUMBER: S124IP-S590U835-4F0-1E-UDD-4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.6	1.7	3.4	4.0	4.6	4.6	8.0	8.0	9.1	10.3	9.7
92.5°	8.0	11.4	17.7	26.2	36.5	51.3	86.7	142.0	195.7	223.6	186.0
95°	18.8	20.5	26.2	33.7	47.3	71.3	120.9	214.5	350.8	464.9	478.0
97.5°	31.4	31.4	36.5	43.4	55.3	75.9	115.2	195.7	336.0	497.4	599.5
100°	43.4	43.4	47.3	54.2	65.0	83.3	116.9	181.4	297.8	458.6	604.7
102.5°	54.8	55.9	59.3	65.6	75.9	93.0	122.6	177.4	272.1	410.2	561.9
105°	66.7	68.5	71.3	78.2	88.4	105.0	132.3	179.7	259.6	374.2	508.3
107.5°	79.9	81.0	83.9	91.3	101.0	117.5	142.6	186.5	256.1	350.8	464.3
110°	93.0	94.1	97.0	103.8	114.1	129.5	154.6	194.5	257.3	340.0	433.0



TEST NUMBER: P334796

CATALOG NUMBER: S124IP-S590U835-4F0-1E-UDD-4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	105.5	106.7	110.1	116.4	126.6	142.0	166.0	203.1	260.7	334.9	415.3
115°	117.5	119.2	123.2	128.9	139.8	155.2	178.0	212.2	265.3	333.7	405.6
117.5°	130.1	131.8	135.2	141.5	151.7	167.7	189.4	221.3	269.8	333.1	400.5
120°	142.6	143.8	147.7	154.0	163.7	179.7	201.4	231.0	275.0	333.1	396.5
122.5°	154.0	155.2	159.2	164.9	175.7	191.1	212.8	240.2	280.1	332.6	391.9
125°	163.7	166.0	169.4	175.7	186.5	202.5	223.0	249.3	285.2	332.0	386.8
127.5°	172.8	174.6	178.6	185.4	196.8	212.8	232.7	257.3	289.2	330.9	379.9
130°	180.3	182.5	187.1	195.7	206.5	223.0	242.4	264.7	293.8	330.3	373.6
132.5°	187.7	189.4	195.7	203.7	215.6	231.0	250.4	272.1	297.8	329.7	367.9
135°	194.5	196.8	202.5	212.2	224.2	239.0	257.8	278.4	301.8	329.1	362.2
137.5°	201.4	203.7	209.9	219.1	231.6	245.9	263.5	282.9	304.0	329.1	357.1
140°	208.8	210.5	216.8	226.5	238.4	252.1	269.3	287.5	306.9	328.6	353.1
142.5°	216.8	218.5	224.2	233.3	244.7	257.8	274.4	290.9	309.2	328.6	349.7
145°	224.2	225.9	231.6	239.6	250.4	263.0	277.8	293.2	309.8	327.4	345.7
147.5°	232.7	233.3	238.4	247.0	256.1	267.5	281.8	295.5	310.3	325.7	342.3
150°	240.7	241.3	245.9	252.7	261.3	272.1	284.7	297.2	310.3	324.0	338.3
152.5°	248.1	248.1	252.7	259.0	266.4	276.1	286.9	298.3	309.2	321.2	333.7
155°	255.0	255.6	259.0	264.7	271.0	279.5	289.2	298.9	308.0	318.3	329.1
157.5°	261.8	261.8	265.3	269.8	275.5	282.4	290.9	298.9	306.9	315.5	324.6
160°	268.1	268.1	270.4	274.4	278.9	285.2	292.1	298.9	305.2	312.0	319.5
162.5°	273.8	273.2	275.0	278.4	282.4	286.9	293.2	298.9	303.5	308.6	314.9
165°	277.8	277.8	278.9	281.8	284.7	288.1	293.2	297.8	301.2	305.2	309.8
167.5°	282.4	281.8	282.4	284.7	286.4	289.2	293.2	296.6	298.9	301.8	305.2
170°	285.2	284.7	285.2	286.9	288.1	289.8	292.6	295.5	296.6	298.3	300.6
172.5°	288.1	287.5	287.5	288.6	289.2	290.4	292.1	294.4	294.4	294.9	296.6
175°	289.8	289.2	289.2	289.8	290.4	290.4	291.5	293.2	292.6	292.6	293.8
177.5°	290.9	290.4	289.8	290.4	290.4	290.4	290.9	292.1	290.9	290.9	291.5
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4



TEST NUMBER: P334796

CATALOG NUMBER: S124IP-S590U835-4F0-1E-UDD-4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	10.3	10.8	11.4	11.4	12.0	12.5	12.0	12.0
92.5°	137.5	102.7	81.0	66.7	58.2	54.2	51.9	51.9
95°	422.7	334.3	257.8	202.5	174.6	156.9	146.6	139.2
97.5°	608.7	564.7	502.0	438.1	399.3	365.1	348.0	334.3
100°	688.0	699.4	671.4	629.2	579.6	544.8	527.7	523.1
102.5°	684.0	751.9	769.0	757.6	731.9	709.1	690.8	687.4
105°	638.9	737.6	794.1	817.5	818.6	814.0	806.0	802.6
107.5°	583.6	690.2	769.0	816.9	842.0	852.3	856.8	857.4
110°	534.5	633.2	715.9	778.7	819.2	843.1	853.4	858.5



TEST NUMBER: P334796

CATALOG NUMBER: S124IP-S590U835-4F0-1E-UDD-4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	498.6	583.0	660.0	722.8	770.1	800.3	815.7	824.9
115°	476.9	547.1	613.8	668.6	713.6	747.9	766.1	770.7
117.5°	464.3	523.7	577.9	625.8	665.7	695.4	714.8	717.6
120°	456.4	509.4	555.0	595.5	628.1	653.2	668.0	674.3
122.5°	449.5	500.3	540.8	575.0	601.3	621.8	633.8	640.0
125°	441.5	490.6	529.9	561.3	584.1	600.7	611.5	614.9
127.5°	432.4	479.7	519.1	548.8	571.6	586.4	595.5	599.0
130°	421.0	466.1	504.8	535.1	558.5	572.7	581.9	585.3
132.5°	409.0	450.7	488.3	518.5	541.4	557.9	566.5	569.9
135°	398.2	435.3	470.0	498.6	521.4	537.4	546.5	549.9
137.5°	387.9	420.4	450.7	476.9	498.6	515.1	522.5	526.5
140°	379.3	406.2	431.8	455.8	475.8	488.3	496.3	500.9
142.5°	371.4	394.2	415.3	435.3	452.4	463.8	470.6	473.5
145°	363.9	383.3	400.5	416.4	430.7	440.4	446.1	448.9
147.5°	357.7	373.6	387.9	401.0	411.9	420.4	425.0	426.1
150°	352.0	365.1	376.5	386.8	395.9	403.3	406.7	407.3
152.5°	345.7	356.5	366.8	374.8	382.2	387.9	389.6	390.2
155°	339.4	348.5	357.1	363.9	369.7	374.2	375.9	375.9
157.5°	332.6	340.6	348.0	353.7	358.2	361.7	362.8	362.8
160°	326.3	332.6	338.8	343.4	346.8	350.3	350.8	350.8
162.5°	320.0	325.2	329.7	333.7	336.0	339.4	340.0	339.4
165°	314.3	317.7	321.7	324.6	326.9	329.1	328.6	328.0
167.5°	308.6	311.5	314.9	316.6	317.7	319.5	319.5	318.9
170°	303.5	305.2	307.5	309.2	310.3	310.9	310.3	310.3
172.5°	298.9	300.1	301.2	302.3	302.9	303.5	302.9	301.8
175°	294.9	295.5	296.6	296.6	296.6	297.8	296.6	295.5
177.5°	292.1	292.6	292.6	293.2	292.6	293.2	292.1	290.9
180°	290.4	290.4	290.4	290.4	290.4	290.4	290.4	290.4

(END OF REPORT)