

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333121

Luminaire Tested: **S125DIP-S375D365U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333121  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D365U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2985.4 lumens  
Efficiency: N/A  
Efficacy: 147.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333121

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333121

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	30
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	18
8	54	42	34	28	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3773	3773	3773
5°	3781	3745	3769
10°	3758	3719	3740
15°	3718	3674	3689
20°	3659	3612	3618
25°	3596	3537	3534
30°	3519	3457	3439
35°	3436	3370	3323
40°	3351	3277	3230
45°	3259	3191	3128
50°	3158	3088	2995
55°	3059	2971	2888
60°	2942	2853	2753
65°	2804	2713	2621
70°	2670	2549	2460
75°	2433	2353	2271
80°	2165	2131	2079
85°	1882	1919	1815



TEST NUMBER: P333121

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.1	1.8
10°-20°	155.6	5.2
20°-30°	229.7	7.7
30°-40°	268.1	9.0
40°-50°	269.2	9.0
50°-60°	236.3	7.9
60°-70°	176.1	5.9
70°-80°	100.7	3.4
80°-90°	30.3	1.0
90°-100°	17.3	0.6
100°-110°	106.8	3.6
110°-120°	193.7	6.5
120°-130°	248.6	8.3
130°-140°	267.4	9.0
140°-150°	251.0	8.4
150°-160°	203.0	6.8
160°-170°	131.3	4.4
170°-180°	45.3	1.5
0°-30°	440.4	14.8
0°-40°	708.5	23.7
0°-60°	1214.0	40.7
0°-90°	1521.1	51.0
90°-120°	317.8	10.6
90°-150°	1084.7	36.3
90°-180°	1464.0	49.0
0°-180°	2985.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	584	584	584	584	584	
5°	583	582	578	582	581	55
15°	556	554	550	552	552	157
25°	505	502	496	497	496	232
35°	436	434	428	425	422	272
45°	357	355	349	344	342	275
55°	272	270	264	260	256	243
65°	184	182	178	173	172	182
75°	98	96	94	93	91	104
85°	25	26	26	25	24	28
90°	0	3	6	7	8	2
95°	20	18	6	7	7	26
105°	104	105	105	105	105	110
115°	195	197	197	196	194	193
125°	278	280	280	279	278	248
135°	346	348	348	347	345	267
145°	401	402	402	402	400	251
155°	442	440	440	441	439	203
165°	466	464	464	466	464	132
175°	477	475	475	478	475	45
180°	477	477	477	477	477	



TEST NUMBER: P333121

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
2.5°	585.6	585.4	585.2	584.9	584.7	584.1	583.3	582.5	581.7	580.8	581.7
5°	583.2	583.0	582.8	582.6	582.4	581.8	580.8	579.8	578.7	577.7	578.6
7.5°	577.9	577.7	577.5	577.3	577.1	576.4	575.3	574.1	573.0	571.9	572.8
10°	573.1	572.9	572.7	572.5	572.3	571.6	570.5	569.3	568.2	567.1	567.9
12.5°	567.2	566.8	566.4	566.1	565.7	565.0	563.9	562.9	561.8	560.8	561.4
15°	556.0	555.7	555.4	555.1	554.7	554.0	552.9	551.8	550.6	549.5	550.0
17.5°	543.1	542.7	542.2	541.8	541.3	540.5	539.3	538.2	537.0	535.8	536.5
20°	532.4	532.2	532.0	531.8	531.6	530.8	529.5	528.1	526.8	525.5	526.2
22.5°	521.7	521.3	520.9	520.6	520.2	519.4	518.1	516.9	515.6	514.4	514.9
25°	504.7	504.2	503.6	503.1	502.6	501.7	500.4	499.0	497.7	496.4	496.6
27.5°	484.8	484.5	484.2	483.9	483.6	482.7	481.4	480.0	478.6	477.2	477.3
30°	471.9	471.6	471.2	470.9	470.6	469.7	468.2	466.6	465.1	463.5	463.3
32.5°	457.8	457.3	456.9	456.4	455.9	455.0	453.6	452.2	450.9	449.5	449.1
35°	435.8	435.4	435.0	434.6	434.2	433.2	431.8	430.4	428.9	427.5	427.0
37.5°	413.0	412.5	412.0	411.4	410.9	410.0	408.6	407.3	405.9	404.6	403.8
40°	397.5	396.9	396.4	395.9	395.4	394.4	393.0	391.6	390.1	388.7	387.8
42.5°	380.8	380.4	380.0	379.5	379.1	378.2	376.7	375.3	373.8	372.4	371.6
45°	356.8	356.4	356.0	355.6	355.1	354.3	353.1	351.9	350.6	349.4	348.2
47.5°	330.9	330.9	330.9	331.0	331.0	330.3	328.8	327.3	325.8	324.3	323.1
50°	314.3	314.0	313.7	313.3	313.0	312.3	311.0	309.8	308.6	307.3	306.0
52.5°	297.3	297.0	296.8	296.6	296.4	295.6	294.3	293.0	291.6	290.3	289.2
55°	271.7	271.4	271.1	270.8	270.5	269.6	268.2	266.8	265.3	263.9	263.0
57.5°	244.9	244.7	244.5	244.4	244.2	243.5	242.3	241.1	239.9	238.7	237.5
60°	227.8	227.4	227.0	226.6	226.2	225.4	224.3	223.2	222.0	220.9	219.9
62.5°	210.1	209.8	209.4	209.1	208.8	208.1	207.2	206.2	205.2	204.3	203.2
65°	183.5	183.3	183.1	182.9	182.7	182.0	180.9	179.7	178.6	177.5	176.5
67.5°	157.7	157.3	156.8	156.4	156.0	155.3	154.5	153.6	152.8	152.0	151.2
70°	141.4	140.9	140.4	139.9	139.4	138.6	137.7	136.8	135.9	135.0	134.3
72.5°	123.7	123.3	123.0	122.6	122.3	121.8	121.2	120.6	120.0	119.4	118.7
75°	97.5	97.3	97.1	96.9	96.7	96.3	95.8	95.3	94.8	94.3	94.0
77.5°	73.4	73.3	73.2	73.1	73.1	72.9	72.6	72.3	72.0	71.7	71.5
80°	58.2	58.2	58.2	58.2	58.2	58.1	57.9	57.7	57.5	57.3	57.2
82.5°	44.9	44.8	44.6	44.4	44.3	44.2	44.1	44.1	44.0	44.0	43.8
85°	25.4	25.5	25.6	25.7	25.8	25.9	25.9	25.9	25.9	25.9	25.8
87.5°	10.1	10.2	10.3	10.4	10.6	10.6	10.7	10.7	10.7	10.7	10.8
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.1	5.7	6.0
92.5°	5.4	5.0	4.6	4.1	3.7	3.7	4.2	4.7	5.2	5.7	6.0
95°	20.1	19.9	19.7	19.4	19.2	17.6	14.6	11.6	8.6	5.7	6.0
97.5°	42.1	42.5	42.9	43.3	43.8	41.0	35.1	29.2	23.3	17.4	15.2
100°	59.0	59.3	59.5	59.7	60.0	60.2	60.6	60.9	61.2	61.5	49.8
102.5°	76.3	76.6	76.9	77.2	77.5	77.7	77.9	78.1	78.3	78.5	76.3
105°	103.9	104.2	104.6	104.9	105.2	105.3	105.3	105.3	105.3	105.3	105.3
107.5°	132.6	132.6	132.6	132.6	132.6	132.7	132.9	133.0	133.2	133.3	133.3
110°	151.3	151.3	151.3	151.3	151.3	151.4	151.5	151.7	151.8	152.0	151.8



TEST NUMBER: P333121

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.8	169.0	169.2	169.4	169.6	169.7	169.8	169.9	170.0	170.1	169.8
115°	195.1	195.5	195.9	196.3	196.7	196.9	197.0	197.1	197.2	197.2	196.9
117.5°	222.3	222.3	222.3	222.3	222.3	222.4	222.7	223.0	223.3	223.6	223.2
120°	239.3	239.2	239.2	239.1	239.0	239.1	239.3	239.5	239.8	240.0	239.9
122.5°	254.3	254.6	254.9	255.2	255.5	255.7	255.8	255.9	256.0	256.1	256.0
125°	277.5	278.0	278.6	279.1	279.7	280.0	280.0	280.0	280.0	280.0	279.6
127.5°	299.6	300.0	300.4	300.8	301.2	301.4	301.3	301.3	301.2	301.2	301.0
130°	313.2	313.6	314.0	314.4	314.8	315.0	315.1	315.1	315.2	315.3	315.1
132.5°	326.8	327.2	327.7	328.1	328.6	328.7	328.6	328.4	328.2	328.0	328.0
135°	346.1	346.5	347.0	347.5	347.9	348.1	347.9	347.8	347.6	347.5	347.3
137.5°	363.8	364.2	364.6	365.0	365.4	365.6	365.4	365.3	365.1	365.0	365.0
140°	375.4	375.6	375.7	375.9	376.0	376.1	376.0	375.9	375.8	375.8	375.9
142.5°	385.9	386.0	386.1	386.1	386.2	386.3	386.5	386.6	386.7	386.8	386.8
145°	401.2	401.4	401.5	401.7	401.8	401.9	401.9	401.9	401.9	401.9	402.0
147.5°	414.6	414.6	414.6	414.5	414.5	414.5	414.6	414.7	414.8	414.9	415.0
150°	423.1	423.0	422.8	422.6	422.5	422.5	422.6	422.8	423.0	423.1	423.3
152.5°	431.3	431.0	430.6	430.3	429.9	429.8	430.0	430.2	430.3	430.5	430.6
155°	441.9	441.4	440.9	440.4	440.0	439.8	440.0	440.1	440.3	440.4	440.7
157.5°	450.0	449.7	449.4	449.1	448.9	448.7	448.7	448.8	448.8	448.8	449.0
160°	455.6	455.2	454.7	454.2	453.8	453.6	453.6	453.7	453.8	453.9	454.2
162.5°	460.2	459.7	459.2	458.7	458.3	458.1	458.2	458.2	458.3	458.4	458.8
165°	466.2	465.8	465.3	464.8	464.4	464.2	464.2	464.3	464.4	464.5	464.9
167.5°	470.8	470.3	469.8	469.3	468.8	468.6	468.7	468.8	468.9	468.9	469.5
170°	473.3	472.8	472.2	471.7	471.1	470.9	471.0	471.0	471.1	471.2	471.8
172.5°	475.0	474.5	473.9	473.4	472.8	472.6	472.7	472.9	473.0	473.2	473.7
175°	476.8	476.4	475.9	475.4	475.0	474.8	474.8	474.9	475.0	475.1	475.7
177.5°	477.7	477.3	476.9	476.6	476.2	476.0	476.1	476.2	476.2	476.3	476.7
180°	476.8	476.8	476.8	476.8	476.8	476.8	476.8	476.8	476.8	476.8	476.8



TEST NUMBER: P333121

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
2.5°	582.5	583.3	584.1	584.5	584.4	584.3	584.3	584.2
5°	579.5	580.5	581.4	581.8	581.7	581.6	581.5	581.4
7.5°	573.7	574.6	575.5	575.9	575.8	575.7	575.6	575.5
10°	568.7	569.5	570.4	570.7	570.6	570.5	570.4	570.3
12.5°	562.1	562.8	563.4	563.7	563.7	563.7	563.7	563.6
15°	550.5	551.0	551.6	551.8	551.8	551.8	551.8	551.8
17.5°	537.1	537.7	538.4	538.4	537.9	537.4	536.9	536.4
20°	526.9	527.6	528.3	528.5	527.9	527.4	526.9	526.4
22.5°	515.3	515.8	516.3	516.3	516.0	515.6	515.3	514.9
25°	496.8	497.0	497.2	497.1	496.8	496.5	496.2	495.9
27.5°	477.3	477.3	477.4	477.3	476.9	476.6	476.3	476.0
30°	463.1	462.9	462.7	462.5	462.2	461.9	461.5	461.2
32.5°	448.8	448.4	448.0	447.6	447.0	446.4	445.9	445.3
35°	426.5	426.0	425.4	424.8	424.0	423.1	422.3	421.5
37.5°	403.1	402.3	401.5	400.9	400.4	400.0	399.5	399.0
40°	386.8	385.9	385.0	384.4	384.1	383.7	383.4	383.1
42.5°	370.7	369.9	369.0	368.4	367.9	367.4	367.0	366.5
45°	346.9	345.7	344.5	343.7	343.4	343.1	342.8	342.5
47.5°	321.8	320.6	319.3	318.3	317.6	316.9	316.2	315.5
50°	304.7	303.3	302.0	301.0	300.2	299.5	298.8	298.1
52.5°	288.0	286.8	285.6	284.7	283.9	283.1	282.3	281.5
55°	262.0	261.1	260.2	259.4	258.7	257.9	257.2	256.5
57.5°	236.3	235.1	233.9	233.1	232.7	232.3	231.9	231.5
60°	218.9	217.8	216.8	215.9	215.2	214.5	213.8	213.1
62.5°	202.1	200.9	199.8	199.0	198.5	197.9	197.3	196.8
65°	175.6	174.7	173.8	173.1	172.7	172.3	171.9	171.5
67.5°	150.4	149.6	148.8	148.3	148.1	147.8	147.6	147.3
70°	133.7	133.1	132.5	132.0	131.6	131.2	130.7	130.3
72.5°	118.0	117.3	116.6	116.1	115.7	115.3	114.8	114.4
75°	93.7	93.4	93.0	92.7	92.3	91.9	91.5	91.0
77.5°	71.4	71.2	71.0	70.8	70.5	70.2	69.9	69.6
80°	57.1	57.0	56.9	56.7	56.5	56.3	56.1	55.9
82.5°	43.6	43.4	43.3	43.1	43.1	43.1	43.0	43.0
85°	25.7	25.6	25.5	25.3	25.1	24.9	24.7	24.5
87.5°	10.9	11.0	11.1	11.0	10.9	10.8	10.7	10.6
90°	6.4	6.8	7.2	7.5	7.8	8.0	8.2	8.5
92.5°	6.4	6.8	7.2	7.5	7.6	7.7	7.8	7.9
95°	6.4	6.8	7.2	7.4	7.4	7.4	7.4	7.4
97.5°	13.0	10.7	8.5	7.4	7.4	7.4	7.4	7.4
100°	38.1	26.4	14.7	8.7	8.4	8.1	7.7	7.4
102.5°	74.0	71.8	69.6	65.8	60.5	55.2	49.8	44.5
105°	105.3	105.3	105.3	105.3	105.2	105.1	105.1	105.0
107.5°	133.4	133.4	133.4	133.3	133.1	132.8	132.6	132.3
110°	151.5	151.3	151.1	151.0	151.1	151.1	151.2	151.3





TEST NUMBER: P333121

CATALOG NUMBER: S125DIP-S375D365U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	169.5	169.2	168.9	168.7	168.6	168.5	168.4	168.3
115°	196.6	196.3	196.0	195.6	195.1	194.7	194.2	193.7
117.5°	222.8	222.4	222.0	221.7	221.5	221.3	221.1	220.9
120°	239.7	239.5	239.4	239.1	238.7	238.3	237.9	237.5
122.5°	255.8	255.7	255.5	255.2	254.7	254.3	253.8	253.4
125°	279.3	279.0	278.7	278.4	278.2	278.0	277.7	277.5
127.5°	300.8	300.6	300.5	300.1	299.5	298.9	298.4	297.8
130°	314.8	314.6	314.4	314.0	313.7	313.3	312.9	312.5
132.5°	327.9	327.9	327.8	327.6	327.2	326.8	326.4	326.1
135°	347.2	347.0	346.8	346.5	346.1	345.6	345.1	344.6
137.5°	365.1	365.1	365.1	364.9	364.5	364.1	363.7	363.3
140°	376.1	376.2	376.4	376.2	375.8	375.3	374.8	374.3
142.5°	386.8	386.9	386.9	386.7	386.2	385.7	385.3	384.8
145°	402.1	402.1	402.2	402.0	401.6	401.1	400.6	400.1
147.5°	415.1	415.2	415.3	415.1	414.5	413.9	413.4	412.8
150°	423.4	423.6	423.7	423.5	422.9	422.3	421.6	421.0
152.5°	430.8	430.9	431.1	430.9	430.3	429.8	429.2	428.6
155°	440.9	441.1	441.4	441.2	440.6	439.9	439.3	438.7
157.5°	449.3	449.5	449.8	449.6	449.0	448.3	447.7	447.1
160°	454.5	454.8	455.1	455.0	454.3	453.7	453.1	452.5
162.5°	459.3	459.7	460.2	460.0	459.3	458.6	458.0	457.3
165°	465.4	465.9	466.4	466.3	465.7	465.0	464.4	463.8
167.5°	470.1	470.6	471.2	471.1	470.4	469.7	469.0	468.3
170°	472.4	473.1	473.7	473.7	473.0	472.3	471.5	470.8
172.5°	474.3	474.9	475.4	475.4	474.7	473.9	473.2	472.5
175°	476.3	477.0	477.6	477.6	476.8	476.1	475.4	474.7
177.5°	477.2	477.6	478.0	478.0	477.5	477.0	476.5	476.0
180°	476.8	476.8	476.8	476.8	476.8	476.8	476.8	476.8

(END OF REPORT)