

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333288-927

Luminaire Tested: **S125DIP-S1090D1205U927-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333288-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1205U927-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6981.0 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49	43
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41	37
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	64	56	50	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	24	21
7	59	46	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18
8	54	42	34	29	50	39	32	28	34	29	25	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	25	31	26	22	27	23	19	23	19	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8136	8136	8136	8136
5°	9422	8163	7148	8163
10°	10961	8121	6263	8121
15°	12133	8062	5777	8062
20°	13582	7967	5388	7967
25°	15911	7860	5197	7860
30°	17186	7756	5032	7756
35°	14130	7559	4924	7559
40°	10044	7284	4806	7284
45°	7716	6915	4737	6915
50°	6586	6457	4728	6457
55°	5864	6008	4769	6008
60°	5291	5518	4890	5518
65°	4886	5025	5017	5025
70°	4443	4513	5089	4513
75°	3923	3975	5043	3975
80°	3299	3239	4616	3239
85°	2616	2334	3720	2334



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	1.7
10°-20°	361.1	5.2
20°-30°	586.3	8.4
30°-40°	715.2	10.2
40°-50°	650.6	9.3
50°-60°	518.2	7.4
60°-70°	361.0	5.2
70°-80°	192.5	2.8
80°-90°	51.1	0.7
90°-100°	330.9	4.7
100°-110°	711.4	10.2
110°-120°	667.6	9.6
120°-130°	541.1	7.8
130°-140°	434.2	6.2
140°-150°	327.7	4.7
150°-160°	230.6	3.3
160°-170°	136.0	1.9
170°-180°	44.2	0.6
0°-30°	1068.7	15.3
0°-40°	1783.8	25.6
0°-60°	2952.7	42.3
0°-90°	3557.2	51.0
90°-120°	1710.0	24.5
90°-150°	3013.0	43.2
90°-180°	3424.0	49.0
0°-180°	6981.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1260	1260	1260	1260	1260	
5°	1453	1259	1102	1259	1453	146
15°	1815	1206	864	1206	1815	519
25°	2233	1103	729	1103	2233	1020
35°	1792	959	624	959	1792	1097
45°	845	757	519	757	845	676
55°	521	534	424	534	521	469
65°	320	329	328	329	320	317
75°	157	159	202	159	157	169
85°	35	32	50	32	35	41
90°	21	1	21	1	21	16
95°	216	30	216	30	216	306
105°	1220	104	1220	104	1220	1212
115°	1359	186	1359	186	1359	1327
125°	1071	258	1071	258	1071	969
135°	889	302	889	302	889	689
145°	701	352	701	352	701	446
155°	588	401	588	401	588	274
165°	516	438	516	438	516	147
175°	463	456	463	456	463	45
180°	456	456	456	456	456	



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1332.5	1330.7	1329.0	1325.6	1328.2	1320.9	1317.5	1311.5	1304.2	1301.6	1298.6
5°	1453.3	1456.0	1458.6	1447.4	1448.4	1441.0	1423.9	1409.9	1398.8	1384.3	1374.1
7.5°	1598.7	1592.4	1591.9	1584.6	1572.1	1562.0	1544.0	1521.1	1499.0	1473.8	1452.9
10°	1671.4	1672.0	1667.1	1658.6	1645.2	1635.6	1612.1	1589.6	1562.3	1530.3	1507.3
12.5°	1726.2	1728.4	1722.4	1710.8	1704.2	1682.7	1664.3	1637.5	1605.1	1579.5	1544.5
15°	1814.7	1808.9	1804.6	1790.1	1778.9	1756.4	1727.0	1699.2	1663.9	1631.3	1598.7
17.5°	1900.0	1904.7	1896.7	1883.6	1848.7	1822.5	1783.0	1745.0	1701.1	1657.3	1618.3
20°	1976.2	1980.5	1968.2	1945.2	1903.5	1877.3	1825.4	1776.2	1725.5	1669.3	1626.5
22.5°	2071.2	2067.8	2051.1	2016.2	1980.1	1931.6	1875.5	1815.6	1751.9	1688.5	1631.7
25°	2232.8	2210.3	2200.2	2157.0	2109.3	2038.2	1961.2	1873.5	1794.4	1710.5	1637.8
27.5°	2322.4	2315.4	2304.1	2273.9	2223.9	2147.8	2057.1	1950.2	1838.6	1732.6	1637.4
30°	2304.5	2305.6	2306.6	2297.0	2264.9	2207.7	2117.3	2002.4	1869.8	1750.6	1640.4
32.5°	2145.4	2164.8	2183.4	2205.4	2214.5	2203.5	2146.9	2043.0	1906.5	1771.1	1638.7
35°	1792.2	1798.2	1858.5	1918.4	1999.7	2062.8	2105.1	2059.0	1944.1	1788.5	1636.6
37.5°	1397.5	1426.3	1468.2	1535.8	1653.1	1758.2	1893.2	1955.3	1918.3	1794.2	1632.9
40°	1191.3	1218.0	1245.3	1314.2	1413.2	1540.4	1693.8	1824.9	1855.4	1776.2	1620.1
42.5°	1032.1	1053.4	1083.6	1135.4	1218.1	1330.9	1477.4	1648.6	1754.0	1724.0	1593.2
45°	844.8	858.2	881.7	922.9	982.8	1071.0	1200.4	1387.5	1550.6	1604.6	1529.2
47.5°	723.1	723.0	741.3	769.8	812.9	887.9	983.6	1130.2	1304.4	1433.3	1427.3
50°	655.5	652.8	667.3	691.9	726.1	775.9	867.3	984.4	1151.7	1297.7	1338.3
52.5°	597.4	597.7	606.6	624.7	653.4	695.9	764.1	869.7	1012.7	1162.5	1239.1
55°	520.8	518.6	528.8	541.1	562.0	589.8	639.0	719.7	835.7	983.3	1082.8
57.5°	450.6	456.5	460.6	469.1	486.5	505.1	546.5	605.8	697.8	824.5	929.6
60°	409.6	415.4	418.7	427.2	441.1	457.2	489.3	537.3	614.9	724.0	828.2
62.5°	372.8	377.4	378.4	386.1	397.5	413.1	438.3	478.8	540.0	635.4	737.5
65°	319.7	319.7	321.9	329.9	335.3	349.1	368.4	397.8	447.0	521.3	608.5
67.5°	268.6	271.2	270.7	274.2	279.1	289.9	303.7	328.0	364.4	418.7	488.4
70°	235.3	237.4	236.9	239.6	244.9	251.8	263.1	286.1	312.3	358.8	418.7
72.5°	205.3	206.2	204.8	208.3	211.5	217.6	230.1	242.4	266.9	306.2	355.4
75°	157.2	158.3	159.3	161.4	164.7	167.9	174.3	186.6	202.6	232.0	263.6
77.5°	117.9	115.8	118.4	118.0	119.9	122.3	128.0	134.5	147.7	166.3	190.7
80°	88.7	89.3	89.3	89.8	92.5	94.1	98.9	103.7	113.9	127.8	144.9
82.5°	64.8	66.2	65.4	66.3	68.5	69.7	72.4	76.4	82.2	93.2	105.5
85°	35.3	32.6	33.7	34.8	34.8	35.3	37.4	39.1	42.2	46.5	51.3
87.5°	14.5	15.4	15.6	15.6	16.0	15.7	17.2	17.0	18.1	19.2	20.5
90°	21.2	21.2	20.3	20.3	20.3	18.4	17.5	16.6	15.7	14.7	12.9
92.5°	58.7	60.2	61.5	63.7	75.5	89.1	118.4	163.1	240.3	296.8	301.6
95°	216.3	231.1	238.4	266.0	331.4	408.7	521.9	661.8	798.0	815.6	665.5
97.5°	522.8	534.6	561.3	612.8	669.7	777.3	887.6	985.6	1009.8	870.9	594.3
100°	718.0	732.7	766.8	833.1	896.5	992.3	1087.1	1132.2	1061.3	831.2	530.2
102.5°	936.0	947.0	984.0	1031.1	1099.1	1163.9	1209.3	1181.5	1030.4	761.2	481.6
105°	1219.6	1230.7	1249.1	1279.5	1308.9	1319.1	1278.6	1152.5	931.5	667.3	434.4
107.5°	1370.2	1377.6	1383.7	1383.9	1369.0	1320.9	1216.9	1048.6	830.7	602.7	414.5
110°	1420.3	1420.3	1413.9	1396.4	1354.9	1276.7	1146.9	972.0	773.2	572.5	408.7



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1414.4	1407.8	1391.8	1361.8	1301.2	1208.9	1077.7	911.6	730.5	554.8	408.7
115°	1358.6	1346.6	1320.9	1276.7	1204.9	1104.5	978.5	835.8	683.9	535.8	411.5
117.5°	1260.8	1253.5	1228.0	1182.3	1110.5	1018.4	909.8	786.8	656.1	526.3	417.6
120°	1197.5	1190.2	1165.3	1121.2	1053.0	972.0	870.8	760.3	640.6	521.9	423.4
122.5°	1141.6	1135.0	1110.1	1069.6	1008.8	933.0	842.8	740.5	627.4	518.2	428.6
125°	1070.6	1061.3	1041.1	1003.3	951.8	885.5	805.4	711.5	609.3	513.7	437.2
127.5°	1009.8	1005.8	986.6	953.2	906.5	844.5	769.7	682.1	592.8	511.4	446.9
130°	976.6	971.1	952.7	922.3	876.3	816.5	744.7	663.7	581.8	509.9	452.9
132.5°	943.5	937.2	920.3	889.9	843.9	786.2	721.1	645.2	572.9	509.9	459.5
135°	889.2	883.7	867.1	836.7	796.2	743.8	684.8	621.3	562.4	509.9	468.5
137.5°	831.2	825.1	809.8	782.2	746.0	701.4	652.4	601.1	553.0	511.0	476.8
140°	790.7	786.1	772.3	748.4	714.3	675.7	633.3	590.0	548.6	511.7	480.5
142.5°	753.1	749.2	736.2	716.0	687.1	653.6	617.1	580.4	544.9	512.5	482.7
145°	701.4	697.8	687.6	671.9	649.8	625.0	596.4	567.9	539.4	511.7	485.1
147.5°	657.6	655.9	650.1	637.5	620.0	601.3	579.3	556.2	533.7	509.4	486.0
150°	633.3	632.4	628.7	617.7	603.8	587.2	569.8	549.5	529.3	507.2	486.0
152.5°	614.2	613.2	609.5	600.7	589.1	576.2	560.2	542.2	524.1	504.2	485.3
155°	588.2	587.2	584.5	578.1	568.9	558.7	545.8	531.1	515.5	498.9	483.2
157.5°	565.0	565.1	562.6	557.2	550.1	542.2	532.2	520.1	507.4	493.4	480.9
160°	549.5	550.5	548.6	544.0	537.6	531.1	521.9	512.7	500.7	489.7	478.6
162.5°	535.5	535.8	535.4	531.5	526.5	520.8	513.1	504.6	494.9	485.3	476.4
165°	515.5	515.5	515.5	513.7	509.9	505.3	499.8	493.4	486.0	478.6	473.1
167.5°	497.1	497.3	498.0	496.3	494.5	491.2	487.0	482.7	477.4	472.2	467.9
170°	486.0	487.0	487.0	486.0	484.2	482.4	479.6	476.8	472.2	468.5	465.8
172.5°	475.7	476.7	478.1	476.4	476.1	475.0	472.9	470.2	467.1	464.1	462.8
175°	463.0	463.9	465.8	464.9	464.9	464.9	463.0	463.0	460.3	459.3	459.3
177.5°	456.5	456.5	458.8	458.0	458.8	458.8	458.8	458.0	457.3	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1296.1	1293.1	1289.7	1283.7	1276.4	1272.6	1266.5	1262.7	1255.0	1248.6	1241.7
5°	1361.8	1348.0	1335.1	1318.5	1300.4	1288.6	1274.7	1259.2	1243.2	1226.5	1208.4
7.5°	1430.0	1405.3	1378.6	1349.9	1321.8	1295.9	1271.1	1246.9	1224.2	1196.8	1173.6
10°	1475.8	1444.7	1411.6	1372.5	1334.6	1301.4	1267.7	1238.3	1208.4	1176.3	1148.0
12.5°	1521.5	1480.2	1433.4	1390.5	1344.8	1304.8	1265.2	1227.6	1190.0	1154.5	1121.4
15°	1553.8	1517.4	1474.1	1413.2	1361.8	1306.8	1254.3	1205.7	1160.2	1120.7	1079.0
17.5°	1575.1	1528.2	1481.7	1423.2	1356.0	1294.3	1235.0	1179.3	1128.1	1077.9	1037.7
20°	1578.9	1530.8	1482.2	1424.9	1356.0	1285.4	1226.1	1159.2	1104.1	1052.3	1003.1
22.5°	1577.6	1523.1	1470.1	1411.3	1344.0	1279.0	1207.2	1139.1	1079.3	1028.3	977.0
25°	1565.6	1507.3	1441.0	1381.6	1315.3	1246.3	1173.6	1103.0	1042.1	983.8	933.0
27.5°	1555.5	1479.9	1404.9	1335.6	1271.6	1208.4	1138.8	1066.5	998.9	939.8	892.0
30°	1543.1	1460.2	1375.7	1303.5	1237.8	1176.3	1110.6	1040.0	969.4	911.6	860.3
32.5°	1532.0	1435.4	1346.2	1267.7	1198.0	1138.2	1077.6	1010.4	941.1	882.6	831.2
35°	1510.5	1398.8	1296.6	1207.8	1133.5	1072.1	1021.3	958.7	895.1	838.4	789.2
37.5°	1483.2	1350.6	1241.0	1148.0	1066.5	1001.7	954.4	906.4	845.3	790.7	746.2
40°	1461.8	1316.4	1200.4	1105.2	1020.7	953.3	909.5	864.0	813.3	762.5	715.4
42.5°	1434.9	1285.6	1159.3	1056.9	973.2	907.6	861.6	823.0	778.2	730.8	687.1
45°	1385.4	1229.8	1092.9	982.8	898.3	833.5	786.0	757.1	723.4	678.5	641.6
47.5°	1312.6	1162.7	1021.1	907.4	820.3	760.3	715.7	688.0	664.3	630.9	597.5
50°	1247.9	1112.7	969.4	856.6	769.4	709.0	667.8	642.7	622.3	596.7	568.4
52.5°	1175.7	1049.8	918.5	806.9	720.6	661.1	620.8	598.7	581.7	563.3	535.4
55°	1060.8	953.9	831.9	726.1	646.4	588.1	552.9	533.6	519.8	505.8	488.7
57.5°	934.3	850.6	742.7	645.9	572.5	519.5	486.6	467.9	457.0	449.9	439.8
60°	845.3	773.7	680.6	592.4	520.8	473.7	441.6	427.2	418.1	412.3	404.7
62.5°	762.8	703.9	617.7	537.3	474.6	430.1	401.5	387.5	378.7	375.9	369.7
65°	641.1	595.6	524.5	457.7	404.3	366.2	342.2	328.8	323.4	320.3	320.8
67.5°	521.2	493.5	436.4	379.4	336.8	304.9	285.7	275.4	272.7	268.4	268.3
70°	448.1	427.2	379.1	329.4	291.4	266.8	249.7	239.0	236.3	234.2	233.7
72.5°	383.5	365.2	323.4	283.6	249.5	227.9	213.7	207.3	203.0	201.7	201.6
75°	288.2	278.1	244.9	213.3	189.8	174.8	165.2	159.3	156.1	155.6	156.1
77.5°	204.9	196.0	174.9	152.6	137.8	126.4	118.3	116.2	112.6	112.7	112.2
80°	154.0	148.1	134.8	117.1	104.8	95.1	90.9	87.1	86.1	84.4	86.1
82.5°	111.6	105.4	96.3	85.0	74.9	69.1	64.8	63.6	63.0	62.3	62.6
85°	55.1	55.6	50.2	41.7	37.4	34.2	31.5	31.5	31.0	30.5	31.0
87.5°	21.2	20.0	18.1	16.5	13.9	12.3	11.5	11.7	10.6	10.5	11.4
90°	12.0	10.1	9.2	7.4	5.5	3.6	1.8	1.0	1.8	3.6	5.5
92.5°	210.1	125.7	75.5	48.6	32.8	21.4	13.6	11.2	13.6	21.4	32.8
95°	411.5	209.0	110.4	69.0	48.8	38.7	31.3	30.3	31.3	38.7	48.8
97.5°	328.4	180.1	114.9	85.1	66.9	56.7	51.6	50.5	51.6	56.7	66.9
100°	298.3	178.6	125.2	97.6	80.1	69.9	66.3	64.4	66.3	69.9	80.1
102.5°	285.7	185.2	137.7	110.8	94.8	84.0	81.0	79.9	81.0	84.0	94.8
105°	280.7	198.8	158.4	132.5	117.8	108.6	104.0	104.0	104.0	108.6	117.8
107.5°	289.2	219.0	179.8	156.7	141.4	133.8	129.4	127.5	129.4	133.8	141.4
110°	297.3	233.8	196.1	172.1	158.4	150.0	146.4	144.5	146.4	150.0	158.4



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	307.6	247.8	211.5	188.3	174.5	166.2	163.3	161.4	163.3	166.2	174.5
115°	323.1	269.7	235.7	212.6	198.8	190.5	187.7	185.9	187.7	190.5	198.8
117.5°	340.8	292.2	259.9	237.7	222.0	213.7	210.8	208.0	210.8	213.7	222.0
120°	352.5	308.4	276.2	253.1	237.5	229.2	225.5	222.8	225.5	229.2	237.5
122.5°	365.8	323.8	291.6	268.6	251.4	243.2	240.3	238.2	240.3	243.2	251.4
125°	383.8	344.3	313.9	289.9	272.4	264.2	259.6	257.7	259.6	264.2	272.4
127.5°	400.4	363.9	334.7	310.8	292.2	281.7	275.8	273.0	275.8	281.7	292.2
130°	411.5	376.4	347.9	324.0	304.7	292.7	285.3	282.6	285.3	292.7	304.7
132.5°	421.0	388.2	359.7	335.8	315.8	302.3	293.4	289.9	293.4	302.3	315.8
135°	434.4	404.1	375.6	350.7	331.4	316.6	305.6	301.9	305.6	316.6	331.4
137.5°	444.4	415.3	389.4	363.8	344.8	330.1	319.8	317.0	319.8	330.1	344.8
140°	451.1	423.4	396.7	371.9	354.4	339.7	328.6	325.8	328.6	339.7	354.4
142.5°	454.7	428.6	403.4	380.0	363.2	348.5	338.2	336.1	338.2	348.5	363.2
145°	460.3	437.2	413.3	392.1	375.6	362.7	353.5	351.6	353.5	362.7	375.6
147.5°	463.6	442.8	421.8	403.1	388.8	376.8	368.9	367.8	368.9	376.8	388.8
150°	465.8	446.4	426.2	410.5	397.7	385.7	379.2	377.4	379.2	385.7	397.7
152.5°	467.2	450.1	431.3	417.2	405.0	394.5	388.8	387.7	388.8	394.5	405.0
155°	468.5	453.8	438.2	425.2	416.1	406.9	401.3	401.3	401.3	406.9	416.1
157.5°	469.4	456.9	443.5	433.7	425.6	417.7	413.3	413.5	413.3	417.7	425.6
160°	469.4	458.4	446.4	438.2	430.8	424.4	420.6	421.6	420.6	424.4	430.8
162.5°	468.7	459.9	449.4	442.6	436.7	430.9	427.3	428.2	427.3	430.9	436.7
165°	467.6	460.3	452.9	447.3	443.7	439.1	436.3	438.2	436.3	439.1	443.7
167.5°	465.4	460.3	454.2	450.7	448.1	445.5	443.9	444.8	443.9	445.5	448.1
170°	463.9	460.3	455.7	452.9	451.1	449.2	448.3	449.2	448.3	449.2	451.1
172.5°	462.5	459.5	455.7	454.3	453.2	451.4	450.5	452.2	450.5	451.4	453.2
175°	460.3	458.4	455.7	455.7	455.7	454.7	453.8	455.7	453.8	454.7	455.7
177.5°	458.0	457.3	455.8	455.8	456.5	455.8	455.8	457.3	455.8	455.8	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1237.9	1233.2	1229.3	1220.8	1216.1	1209.7	1204.5	1210.1	1204.1	1206.7	1202.8
5°	1199.3	1184.3	1173.6	1158.1	1144.8	1132.4	1123.4	1121.7	1117.5	1115.3	1108.9
7.5°	1152.9	1134.2	1115.8	1095.4	1078.3	1060.9	1049.8	1040.6	1034.5	1026.5	1021.0
10°	1125.5	1100.3	1079.0	1054.4	1033.0	1014.3	999.3	991.8	984.9	974.7	971.0
12.5°	1091.7	1065.7	1039.7	1013.4	992.8	971.9	959.1	947.8	942.9	931.5	930.3
15°	1051.2	1012.2	986.5	959.7	931.4	914.3	903.6	891.3	886.0	878.0	872.0
17.5°	1002.8	968.0	935.9	908.2	883.9	869.5	856.3	847.8	838.6	833.4	823.7
20°	967.8	934.6	902.5	873.1	854.4	837.8	827.1	819.1	809.5	806.8	797.3
22.5°	938.3	901.7	870.9	846.2	825.8	807.1	795.5	790.0	783.4	775.2	773.2
25°	890.3	852.3	826.1	801.5	783.3	766.2	758.2	751.2	744.8	738.9	736.8
27.5°	848.7	814.8	783.7	761.5	745.7	730.1	723.0	714.5	709.9	705.1	699.3
30°	819.7	784.9	757.6	736.3	719.1	705.3	697.8	691.9	687.6	683.3	680.1
32.5°	789.7	757.6	731.1	710.2	693.1	682.5	676.0	671.8	667.1	661.9	657.9
35°	750.2	714.9	689.2	671.1	657.7	649.7	642.1	638.4	633.0	633.0	628.8
37.5°	705.6	675.1	652.4	635.9	623.8	616.7	608.6	606.0	602.6	600.3	598.8
40°	679.1	650.7	629.3	612.8	599.9	594.1	587.6	583.4	581.2	578.5	577.4
42.5°	651.6	624.6	604.1	588.8	577.7	572.7	566.6	563.6	559.4	555.9	555.2
45°	610.1	583.8	565.1	552.9	543.2	537.3	533.6	527.2	525.1	520.8	520.2
47.5°	570.6	545.5	527.1	517.1	508.6	503.7	497.9	491.5	489.0	486.9	486.6
50°	541.1	518.1	501.0	491.4	483.4	476.4	470.6	466.3	464.6	464.6	465.7
52.5°	511.2	491.5	477.1	465.2	457.7	450.3	444.9	442.3	439.8	442.4	444.3
55°	467.3	447.5	436.8	425.6	418.1	409.6	406.9	405.8	404.3	408.5	410.7
57.5°	420.9	407.0	394.5	383.3	376.6	371.7	368.0	367.4	370.4	372.5	379.4
60°	391.4	375.3	364.1	355.5	347.5	344.4	343.3	342.2	344.4	350.2	359.3
62.5°	358.9	345.9	333.7	327.3	321.5	316.1	315.9	316.6	320.8	327.6	336.6
65°	311.2	299.9	291.9	284.5	279.6	276.4	277.5	279.6	284.5	293.5	303.7
67.5°	262.8	255.1	247.9	241.8	237.2	237.2	238.3	241.5	247.2	257.6	266.9
70°	231.6	223.0	217.1	214.4	210.6	208.5	211.8	217.1	221.9	231.6	239.6
72.5°	200.3	193.1	188.5	186.6	185.0	183.3	184.3	190.1	196.6	206.3	215.6
75°	154.0	151.3	148.1	146.0	144.3	145.4	146.5	151.9	157.2	167.4	178.1
77.5°	112.4	109.6	107.7	107.2	106.3	106.9	109.8	113.8	119.0	126.4	134.5
80°	85.0	84.0	82.9	82.3	82.3	82.9	87.1	89.8	94.7	101.6	108.0
82.5°	61.9	61.2	61.1	60.9	61.4	61.5	64.1	67.6	71.5	76.8	82.3
85°	32.6	31.5	33.1	33.7	32.6	34.2	35.3	37.4	39.1	41.7	44.4
87.5°	12.2	13.4	13.2	13.9	14.1	15.4	15.1	17.0	18.1	19.1	19.0
90°	7.4	9.2	10.1	12.0	12.9	14.7	15.7	16.6	17.5	18.4	20.3
92.5°	48.6	75.5	125.7	210.1	301.6	296.8	240.3	163.1	118.4	89.1	75.5
95°	69.0	110.4	209.0	411.5	665.5	815.6	798.0	661.8	521.9	408.7	331.4
97.5°	85.1	114.9	180.1	328.4	594.3	870.9	1009.8	985.6	887.6	777.3	669.7
100°	97.6	125.2	178.6	298.3	530.2	831.2	1061.3	1132.2	1087.1	992.3	896.5
102.5°	110.8	137.7	185.2	285.7	481.6	761.2	1030.4	1181.5	1209.3	1163.9	1099.1
105°	132.5	158.4	198.8	280.7	434.4	667.3	931.5	1152.5	1278.6	1319.1	1308.9
107.5°	156.7	179.8	219.0	289.2	414.5	602.7	830.7	1048.6	1216.9	1320.9	1369.0
110°	172.1	196.1	233.8	297.3	408.7	572.5	773.2	972.0	1146.9	1276.7	1354.9



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	188.3	211.5	247.8	307.6	408.7	554.8	730.5	911.6	1077.7	1208.9	1301.2
115°	212.6	235.7	269.7	323.1	411.5	535.8	683.9	835.8	978.5	1104.5	1204.9
117.5°	237.7	259.9	292.2	340.8	417.6	526.3	656.1	786.8	909.8	1018.4	1110.5
120°	253.1	276.2	308.4	352.5	423.4	521.9	640.6	760.3	870.8	972.0	1053.0
122.5°	268.6	291.6	323.8	365.8	428.6	518.2	627.4	740.5	842.8	933.0	1008.8
125°	289.9	313.9	344.3	383.8	437.2	513.7	609.3	711.5	805.4	885.5	951.8
127.5°	310.8	334.7	363.9	400.4	446.9	511.4	592.8	682.1	769.7	844.5	906.5
130°	324.0	347.9	376.4	411.5	452.9	509.9	581.8	663.7	744.7	816.5	876.3
132.5°	335.8	359.7	388.2	421.0	459.5	509.9	572.9	645.2	721.1	786.2	843.9
135°	350.7	375.6	404.1	434.4	468.5	509.9	562.4	621.3	684.8	743.8	796.2
137.5°	363.8	389.4	415.3	444.4	476.8	511.0	553.0	601.1	652.4	701.4	746.0
140°	371.9	396.7	423.4	451.1	480.5	511.7	548.6	590.0	633.3	675.7	714.3
142.5°	380.0	403.4	428.6	454.7	482.7	512.5	544.9	580.4	617.1	653.6	687.1
145°	392.1	413.3	437.2	460.3	485.1	511.7	539.4	567.9	596.4	625.0	649.8
147.5°	403.1	421.8	442.8	463.6	486.0	509.4	533.7	556.2	579.3	601.3	620.0
150°	410.5	426.2	446.4	465.8	486.0	507.2	529.3	549.5	569.8	587.2	603.8
152.5°	417.2	431.3	450.1	467.2	485.3	504.2	524.1	542.2	560.2	576.2	589.1
155°	425.2	438.2	453.8	468.5	483.2	498.9	515.5	531.1	545.8	558.7	568.9
157.5°	433.7	443.5	456.9	469.4	480.9	493.4	507.4	520.1	532.2	542.2	550.1
160°	438.2	446.4	458.4	469.4	478.6	489.7	500.7	512.7	521.9	531.1	537.6
162.5°	442.6	449.4	459.9	468.7	476.4	485.3	494.9	504.6	513.1	520.8	526.5
165°	447.3	452.9	460.3	467.6	473.1	478.6	486.0	493.4	499.8	505.3	509.9
167.5°	450.7	454.2	460.3	465.4	467.9	472.2	477.4	482.7	487.0	491.2	494.5
170°	452.9	455.7	460.3	463.9	465.8	468.5	472.2	476.8	479.6	482.4	484.2
172.5°	454.3	455.7	459.5	462.5	462.8	464.1	467.1	470.2	472.9	475.0	476.1
175°	455.7	455.7	458.4	460.3	459.3	459.3	460.3	463.0	463.0	464.9	464.9
177.5°	455.8	455.8	457.3	458.0	456.5	456.5	457.3	458.0	458.8	458.8	458.8
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1200.2	1203.2	1200.7	1204.1	1200.7	1203.2	1200.2	1202.8	1206.7	1204.1	1210.1
5°	1106.3	1101.5	1104.6	1102.5	1104.6	1101.5	1106.3	1108.9	1115.3	1117.5	1121.7
7.5°	1019.5	1014.9	1009.6	1007.1	1009.6	1014.9	1019.5	1021.0	1026.5	1034.5	1040.6
10°	965.1	959.3	958.7	955.0	958.7	959.3	965.1	971.0	974.7	984.9	991.8
12.5°	925.3	919.9	913.8	912.2	913.8	919.9	925.3	930.3	931.5	942.9	947.8
15°	868.9	864.6	860.9	864.0	860.9	864.6	868.9	872.0	878.0	886.0	891.3
17.5°	821.9	818.4	817.8	813.8	817.8	818.4	821.9	823.7	833.4	838.6	847.8
20°	792.4	789.7	790.8	783.9	790.8	789.7	792.4	797.3	806.8	809.5	819.1
22.5°	768.9	763.7	763.0	761.6	763.0	763.7	768.9	773.2	775.2	783.4	790.0
25°	732.0	729.3	726.7	729.3	726.7	729.3	732.0	736.8	738.9	744.8	751.2
27.5°	699.8	696.6	695.9	696.2	695.9	696.6	699.8	699.3	705.1	709.9	714.5
30°	680.1	674.8	675.3	674.8	675.3	674.8	680.1	680.1	683.3	687.6	691.9
32.5°	658.7	655.1	654.3	653.4	654.3	655.1	658.7	657.9	661.9	667.1	671.8
35°	627.2	627.2	624.5	624.5	624.5	627.2	627.2	628.8	633.0	633.0	638.4
37.5°	597.5	597.0	595.4	595.6	595.4	597.0	597.5	598.8	600.3	602.6	606.0
40°	575.3	574.8	573.1	570.0	573.1	574.8	575.3	577.4	578.5	581.2	583.4
42.5°	553.9	552.2	551.4	550.3	551.4	552.2	553.9	555.2	555.9	559.4	563.6
45°	520.2	520.2	519.2	518.6	519.2	520.2	520.2	520.2	520.8	525.1	527.2
47.5°	487.5	488.5	490.5	490.2	490.5	488.5	487.5	486.6	486.9	489.0	491.5
50°	467.9	468.4	470.0	470.6	470.0	468.4	467.9	465.7	464.6	464.6	466.3
52.5°	446.0	449.2	451.1	450.8	451.1	449.2	446.0	444.3	442.4	439.8	442.3
55°	415.4	419.2	422.9	423.5	422.9	419.2	415.4	410.7	408.5	404.3	405.8
57.5°	385.2	390.4	394.3	395.7	394.3	390.4	385.2	379.4	372.5	370.4	367.4
60°	364.6	371.6	376.4	378.6	376.4	371.6	364.6	359.3	350.2	344.4	342.2
62.5°	345.0	352.8	357.6	358.0	357.6	352.8	345.0	336.6	327.6	320.8	316.6
65°	312.8	320.8	325.1	328.3	325.1	320.8	312.8	303.7	293.5	284.5	279.6
67.5°	278.1	286.1	290.9	293.4	290.9	286.1	278.1	266.9	257.6	247.2	241.5
70°	252.9	260.9	267.4	269.5	267.4	260.9	252.9	239.6	231.6	221.9	217.1
72.5°	228.1	235.3	240.4	243.0	240.4	235.3	228.1	215.6	206.3	196.6	190.1
75°	185.0	194.6	199.5	202.1	199.5	194.6	185.0	178.1	167.4	157.2	151.9
77.5°	142.7	151.4	154.3	155.7	154.3	151.4	142.7	134.5	126.4	119.0	113.8
80°	114.4	119.8	123.5	124.1	123.5	119.8	114.4	108.0	101.6	94.7	89.8
82.5°	87.9	92.4	93.6	95.0	93.6	92.4	87.9	82.3	76.8	71.5	67.6
85°	48.1	50.2	50.8	50.2	50.8	50.2	48.1	44.4	41.7	39.1	37.4
87.5°	19.9	19.5	19.6	20.5	19.6	19.5	19.9	19.0	19.1	18.1	17.0
90°	20.3	20.3	21.2	21.2	21.2	20.3	20.3	20.3	18.4	17.5	16.6
92.5°	63.7	61.5	60.2	58.7	60.2	61.5	63.7	75.5	89.1	118.4	163.1
95°	266.0	238.4	231.1	216.3	231.1	238.4	266.0	331.4	408.7	521.9	661.8
97.5°	612.8	561.3	534.6	522.8	534.6	561.3	612.8	669.7	777.3	887.6	985.6
100°	833.1	766.8	732.7	718.0	732.7	766.8	833.1	896.5	992.3	1087.1	1132.2
102.5°	1031.1	984.0	947.0	936.0	947.0	984.0	1031.1	1099.1	1163.9	1209.3	1181.5
105°	1279.5	1249.1	1230.7	1219.6	1230.7	1249.1	1279.5	1308.9	1319.1	1278.6	1152.5
107.5°	1383.9	1383.7	1377.6	1370.2	1377.6	1383.7	1383.9	1369.0	1320.9	1216.9	1048.6
110°	1396.4	1413.9	1420.3	1420.3	1420.3	1413.9	1396.4	1354.9	1276.7	1146.9	972.0



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1361.8	1391.8	1407.8	1414.4	1407.8	1391.8	1361.8	1301.2	1208.9	1077.7	911.6
115°	1276.7	1320.9	1346.6	1358.6	1346.6	1320.9	1276.7	1204.9	1104.5	978.5	835.8
117.5°	1182.3	1228.0	1253.5	1260.8	1253.5	1228.0	1182.3	1110.5	1018.4	909.8	786.8
120°	1121.2	1165.3	1190.2	1197.5	1190.2	1165.3	1121.2	1053.0	972.0	870.8	760.3
122.5°	1069.6	1110.1	1135.0	1141.6	1135.0	1110.1	1069.6	1008.8	933.0	842.8	740.5
125°	1003.3	1041.1	1061.3	1070.6	1061.3	1041.1	1003.3	951.8	885.5	805.4	711.5
127.5°	953.2	986.6	1005.8	1009.8	1005.8	986.6	953.2	906.5	844.5	769.7	682.1
130°	922.3	952.7	971.1	976.6	971.1	952.7	922.3	876.3	816.5	744.7	663.7
132.5°	889.9	920.3	937.2	943.5	937.2	920.3	889.9	843.9	786.2	721.1	645.2
135°	836.7	867.1	883.7	889.2	883.7	867.1	836.7	796.2	743.8	684.8	621.3
137.5°	782.2	809.8	825.1	831.2	825.1	809.8	782.2	746.0	701.4	652.4	601.1
140°	748.4	772.3	786.1	790.7	786.1	772.3	748.4	714.3	675.7	633.3	590.0
142.5°	716.0	736.2	749.2	753.1	749.2	736.2	716.0	687.1	653.6	617.1	580.4
145°	671.9	687.6	697.8	701.4	697.8	687.6	671.9	649.8	625.0	596.4	567.9
147.5°	637.5	650.1	655.9	657.6	655.9	650.1	637.5	620.0	601.3	579.3	556.2
150°	617.7	628.7	632.4	633.3	632.4	628.7	617.7	603.8	587.2	569.8	549.5
152.5°	600.7	609.5	613.2	614.2	613.2	609.5	600.7	589.1	576.2	560.2	542.2
155°	578.1	584.5	587.2	588.2	587.2	584.5	578.1	568.9	558.7	545.8	531.1
157.5°	557.2	562.6	565.1	565.0	565.1	562.6	557.2	550.1	542.2	532.2	520.1
160°	544.0	548.6	550.5	549.5	550.5	548.6	544.0	537.6	531.1	521.9	512.7
162.5°	531.5	535.4	535.8	535.5	535.8	535.4	531.5	526.5	520.8	513.1	504.6
165°	513.7	515.5	515.5	515.5	515.5	515.5	513.7	509.9	505.3	499.8	493.4
167.5°	496.3	498.0	497.3	497.1	497.3	498.0	496.3	494.5	491.2	487.0	482.7
170°	486.0	487.0	487.0	486.0	487.0	487.0	486.0	484.2	482.4	479.6	476.8
172.5°	476.4	478.1	476.7	475.7	476.7	478.1	476.4	476.1	475.0	472.9	470.2
175°	464.9	465.8	463.9	463.0	463.9	465.8	464.9	464.9	464.9	463.0	463.0
177.5°	458.0	458.8	456.5	456.5	456.5	458.8	458.0	458.8	458.8	458.8	458.0
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1204.5	1209.7	1216.1	1220.8	1229.3	1233.2	1237.9	1241.7	1248.6	1255.0	1262.7
5°	1123.4	1132.4	1144.8	1158.1	1173.6	1184.3	1199.3	1208.4	1226.5	1243.2	1259.2
7.5°	1049.8	1060.9	1078.3	1095.4	1115.8	1134.2	1152.9	1173.6	1196.8	1224.2	1246.9
10°	999.3	1014.3	1033.0	1054.4	1079.0	1100.3	1125.5	1148.0	1176.3	1208.4	1238.3
12.5°	959.1	971.9	992.8	1013.4	1039.7	1065.7	1091.7	1121.4	1154.5	1190.0	1227.6
15°	903.6	914.3	931.4	959.7	986.5	1012.2	1051.2	1079.0	1120.7	1160.2	1205.7
17.5°	856.3	869.5	883.9	908.2	935.9	968.0	1002.8	1037.7	1077.9	1128.1	1179.3
20°	827.1	837.8	854.4	873.1	902.5	934.6	967.8	1003.1	1052.3	1104.1	1159.2
22.5°	795.5	807.1	825.8	846.2	870.9	901.7	938.3	977.0	1028.3	1079.3	1139.1
25°	758.2	766.2	783.3	801.5	826.1	852.3	890.3	933.0	983.8	1042.1	1103.0
27.5°	723.0	730.1	745.7	761.5	783.7	814.8	848.7	892.0	939.8	998.9	1066.5
30°	697.8	705.3	719.1	736.3	757.6	784.9	819.7	860.3	911.6	969.4	1040.0
32.5°	676.0	682.5	693.1	710.2	731.1	757.6	789.7	831.2	882.6	941.1	1010.4
35°	642.1	649.7	657.7	671.1	689.2	714.9	750.2	789.2	838.4	895.1	958.7
37.5°	608.6	616.7	623.8	635.9	652.4	675.1	705.6	746.2	790.7	845.3	906.4
40°	587.6	594.1	599.9	612.8	629.3	650.7	679.1	715.4	762.5	813.3	864.0
42.5°	566.6	572.7	577.7	588.8	604.1	624.6	651.6	687.1	730.8	778.2	823.0
45°	533.6	537.3	543.2	552.9	565.1	583.8	610.1	641.6	678.5	723.4	757.1
47.5°	497.9	503.7	508.6	517.1	527.1	545.5	570.6	597.5	630.9	664.3	688.0
50°	470.6	476.4	483.4	491.4	501.0	518.1	541.1	568.4	596.7	622.3	642.7
52.5°	444.9	450.3	457.7	465.2	477.1	491.5	511.2	535.4	563.3	581.7	598.7
55°	406.9	409.6	418.1	425.6	436.8	447.5	467.3	488.7	505.8	519.8	533.6
57.5°	368.0	371.7	376.6	383.3	394.5	407.0	420.9	439.8	449.9	457.0	467.9
60°	343.3	344.4	347.5	355.5	364.1	375.3	391.4	404.7	412.3	418.1	427.2
62.5°	315.9	316.1	321.5	327.3	333.7	345.9	358.9	369.7	375.9	378.7	387.5
65°	277.5	276.4	279.6	284.5	291.9	299.9	311.2	320.8	320.3	323.4	328.8
67.5°	238.3	237.2	237.2	241.8	247.9	255.1	262.8	268.3	268.4	272.7	275.4
70°	211.8	208.5	210.6	214.4	217.1	223.0	231.6	233.7	234.2	236.3	239.0
72.5°	184.3	183.3	185.0	186.6	188.5	193.1	200.3	201.6	201.7	203.0	207.3
75°	146.5	145.4	144.3	146.0	148.1	151.3	154.0	156.1	155.6	156.1	159.3
77.5°	109.8	106.9	106.3	107.2	107.7	109.6	112.4	112.2	112.7	112.6	116.2
80°	87.1	82.9	82.3	82.3	82.9	84.0	85.0	86.1	84.4	86.1	87.1
82.5°	64.1	61.5	61.4	60.9	61.1	61.2	61.9	62.6	62.3	63.0	63.6
85°	35.3	34.2	32.6	33.7	33.1	31.5	32.6	31.0	30.5	31.0	31.5
87.5°	15.1	15.4	14.1	13.9	13.2	13.4	12.2	11.4	10.5	10.6	11.7
90°	15.7	14.7	12.9	12.0	10.1	9.2	7.4	5.5	3.6	1.8	1.0
92.5°	240.3	296.8	301.6	210.1	125.7	75.5	48.6	32.8	21.4	13.6	11.2
95°	798.0	815.6	665.5	411.5	209.0	110.4	69.0	48.8	38.7	31.3	30.3
97.5°	1009.8	870.9	594.3	328.4	180.1	114.9	85.1	66.9	56.7	51.6	50.5
100°	1061.3	831.2	530.2	298.3	178.6	125.2	97.6	80.1	69.9	66.3	64.4
102.5°	1030.4	761.2	481.6	285.7	185.2	137.7	110.8	94.8	84.0	81.0	79.9
105°	931.5	667.3	434.4	280.7	198.8	158.4	132.5	117.8	108.6	104.0	104.0
107.5°	830.7	602.7	414.5	289.2	219.0	179.8	156.7	141.4	133.8	129.4	127.5
110°	773.2	572.5	408.7	297.3	233.8	196.1	172.1	158.4	150.0	146.4	144.5



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	730.5	554.8	408.7	307.6	247.8	211.5	188.3	174.5	166.2	163.3	161.4
115°	683.9	535.8	411.5	323.1	269.7	235.7	212.6	198.8	190.5	187.7	185.9
117.5°	656.1	526.3	417.6	340.8	292.2	259.9	237.7	222.0	213.7	210.8	208.0
120°	640.6	521.9	423.4	352.5	308.4	276.2	253.1	237.5	229.2	225.5	222.8
122.5°	627.4	518.2	428.6	365.8	323.8	291.6	268.6	251.4	243.2	240.3	238.2
125°	609.3	513.7	437.2	383.8	344.3	313.9	289.9	272.4	264.2	259.6	257.7
127.5°	592.8	511.4	446.9	400.4	363.9	334.7	310.8	292.2	281.7	275.8	273.0
130°	581.8	509.9	452.9	411.5	376.4	347.9	324.0	304.7	292.7	285.3	282.6
132.5°	572.9	509.9	459.5	421.0	388.2	359.7	335.8	315.8	302.3	293.4	289.9
135°	562.4	509.9	468.5	434.4	404.1	375.6	350.7	331.4	316.6	305.6	301.9
137.5°	553.0	511.0	476.8	444.4	415.3	389.4	363.8	344.8	330.1	319.8	317.0
140°	548.6	511.7	480.5	451.1	423.4	396.7	371.9	354.4	339.7	328.6	325.8
142.5°	544.9	512.5	482.7	454.7	428.6	403.4	380.0	363.2	348.5	338.2	336.1
145°	539.4	511.7	485.1	460.3	437.2	413.3	392.1	375.6	362.7	353.5	351.6
147.5°	533.7	509.4	486.0	463.6	442.8	421.8	403.1	388.8	376.8	368.9	367.8
150°	529.3	507.2	486.0	465.8	446.4	426.2	410.5	397.7	385.7	379.2	377.4
152.5°	524.1	504.2	485.3	467.2	450.1	431.3	417.2	405.0	394.5	388.8	387.7
155°	515.5	498.9	483.2	468.5	453.8	438.2	425.2	416.1	406.9	401.3	401.3
157.5°	507.4	493.4	480.9	469.4	456.9	443.5	433.7	425.6	417.7	413.3	413.5
160°	500.7	489.7	478.6	469.4	458.4	446.4	438.2	430.8	424.4	420.6	421.6
162.5°	494.9	485.3	476.4	468.7	459.9	449.4	442.6	436.7	430.9	427.3	428.2
165°	486.0	478.6	473.1	467.6	460.3	452.9	447.3	443.7	439.1	436.3	438.2
167.5°	477.4	472.2	467.9	465.4	460.3	454.2	450.7	448.1	445.5	443.9	444.8
170°	472.2	468.5	465.8	463.9	460.3	455.7	452.9	451.1	449.2	448.3	449.2
172.5°	467.1	464.1	462.8	462.5	459.5	455.7	454.3	453.2	451.4	450.5	452.2
175°	460.3	459.3	459.3	460.3	458.4	455.7	455.7	455.7	454.7	453.8	455.7
177.5°	457.3	456.5	456.5	458.0	457.3	455.8	455.8	456.5	455.8	455.8	457.3
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1266.5	1272.6	1276.4	1283.7	1289.7	1293.1	1296.1	1298.6	1301.6	1304.2	1311.5
5°	1274.7	1288.6	1300.4	1318.5	1335.1	1348.0	1361.8	1374.1	1384.3	1398.8	1409.9
7.5°	1271.1	1295.9	1321.8	1349.9	1378.6	1405.3	1430.0	1452.9	1473.8	1499.0	1521.1
10°	1267.7	1301.4	1334.6	1372.5	1411.6	1444.7	1475.8	1507.3	1530.3	1562.3	1589.6
12.5°	1265.2	1304.8	1344.8	1390.5	1433.4	1480.2	1521.5	1544.5	1579.5	1605.1	1637.5
15°	1254.3	1306.8	1361.8	1413.2	1474.1	1517.4	1553.8	1598.7	1631.3	1663.9	1699.2
17.5°	1235.0	1294.3	1356.0	1423.2	1481.7	1528.2	1575.1	1618.3	1657.3	1701.1	1745.0
20°	1226.1	1285.4	1356.0	1424.9	1482.2	1530.8	1578.9	1626.5	1669.3	1725.5	1776.2
22.5°	1207.2	1279.0	1344.0	1411.3	1470.1	1523.1	1577.6	1631.7	1688.5	1751.9	1815.6
25°	1173.6	1246.3	1315.3	1381.6	1441.0	1507.3	1565.6	1637.8	1710.5	1794.4	1873.5
27.5°	1138.8	1208.4	1271.6	1335.6	1404.9	1479.9	1555.5	1637.4	1732.6	1838.6	1950.2
30°	1110.6	1176.3	1237.8	1303.5	1375.7	1460.2	1543.1	1640.4	1750.6	1869.8	2002.4
32.5°	1077.6	1138.2	1198.0	1267.7	1346.2	1435.4	1532.0	1638.7	1771.1	1906.5	2043.0
35°	1021.3	1072.1	1133.5	1207.8	1296.6	1398.8	1510.5	1636.6	1788.5	1944.1	2059.0
37.5°	954.4	1001.7	1066.5	1148.0	1241.0	1350.6	1483.2	1632.9	1794.2	1918.3	1955.3
40°	909.5	953.3	1020.7	1105.2	1200.4	1316.4	1461.8	1620.1	1776.2	1855.4	1824.9
42.5°	861.6	907.6	973.2	1056.9	1159.3	1285.6	1434.9	1593.2	1724.0	1754.0	1648.6
45°	786.0	833.5	898.3	982.8	1092.9	1229.8	1385.4	1529.2	1604.6	1550.6	1387.5
47.5°	715.7	760.3	820.3	907.4	1021.1	1162.7	1312.6	1427.3	1433.3	1304.4	1130.2
50°	667.8	709.0	769.4	856.6	969.4	1112.7	1247.9	1338.3	1297.7	1151.7	984.4
52.5°	620.8	661.1	720.6	806.9	918.5	1049.8	1175.7	1239.1	1162.5	1012.7	869.7
55°	552.9	588.1	646.4	726.1	831.9	953.9	1060.8	1082.8	983.3	835.7	719.7
57.5°	486.6	519.5	572.5	645.9	742.7	850.6	934.3	929.6	824.5	697.8	605.8
60°	441.6	473.7	520.8	592.4	680.6	773.7	845.3	828.2	724.0	614.9	537.3
62.5°	401.5	430.1	474.6	537.3	617.7	703.9	762.8	737.5	635.4	540.0	478.8
65°	342.2	366.2	404.3	457.7	524.5	595.6	641.1	608.5	521.3	447.0	397.8
67.5°	285.7	304.9	336.8	379.4	436.4	493.5	521.2	488.4	418.7	364.4	328.0
70°	249.7	266.8	291.4	329.4	379.1	427.2	448.1	418.7	358.8	312.3	286.1
72.5°	213.7	227.9	249.5	283.6	323.4	365.2	383.5	355.4	306.2	266.9	242.4
75°	165.2	174.8	189.8	213.3	244.9	278.1	288.2	263.6	232.0	202.6	186.6
77.5°	118.3	126.4	137.8	152.6	174.9	196.0	204.9	190.7	166.3	147.7	134.5
80°	90.9	95.1	104.8	117.1	134.8	148.1	154.0	144.9	127.8	113.9	103.7
82.5°	64.8	69.1	74.9	85.0	96.3	105.4	111.6	105.5	93.2	82.2	76.4
85°	31.5	34.2	37.4	41.7	50.2	55.6	55.1	51.3	46.5	42.2	39.1
87.5°	11.5	12.3	13.9	16.5	18.1	20.0	21.2	20.5	19.2	18.1	17.0
90°	1.8	3.6	5.5	7.4	9.2	10.1	12.0	12.9	14.7	15.7	16.6
92.5°	13.6	21.4	32.8	48.6	75.5	125.7	210.1	301.6	296.8	240.3	163.1
95°	31.3	38.7	48.8	69.0	110.4	209.0	411.5	665.5	815.6	798.0	661.8
97.5°	51.6	56.7	66.9	85.1	114.9	180.1	328.4	594.3	870.9	1009.8	985.6
100°	66.3	69.9	80.1	97.6	125.2	178.6	298.3	530.2	831.2	1061.3	1132.2
102.5°	81.0	84.0	94.8	110.8	137.7	185.2	285.7	481.6	761.2	1030.4	1181.5
105°	104.0	108.6	117.8	132.5	158.4	198.8	280.7	434.4	667.3	931.5	1152.5
107.5°	129.4	133.8	141.4	156.7	179.8	219.0	289.2	414.5	602.7	830.7	1048.6
110°	146.4	150.0	158.4	172.1	196.1	233.8	297.3	408.7	572.5	773.2	972.0



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	163.3	166.2	174.5	188.3	211.5	247.8	307.6	408.7	554.8	730.5	911.6
115°	187.7	190.5	198.8	212.6	235.7	269.7	323.1	411.5	535.8	683.9	835.8
117.5°	210.8	213.7	222.0	237.7	259.9	292.2	340.8	417.6	526.3	656.1	786.8
120°	225.5	229.2	237.5	253.1	276.2	308.4	352.5	423.4	521.9	640.6	760.3
122.5°	240.3	243.2	251.4	268.6	291.6	323.8	365.8	428.6	518.2	627.4	740.5
125°	259.6	264.2	272.4	289.9	313.9	344.3	383.8	437.2	513.7	609.3	711.5
127.5°	275.8	281.7	292.2	310.8	334.7	363.9	400.4	446.9	511.4	592.8	682.1
130°	285.3	292.7	304.7	324.0	347.9	376.4	411.5	452.9	509.9	581.8	663.7
132.5°	293.4	302.3	315.8	335.8	359.7	388.2	421.0	459.5	509.9	572.9	645.2
135°	305.6	316.6	331.4	350.7	375.6	404.1	434.4	468.5	509.9	562.4	621.3
137.5°	319.8	330.1	344.8	363.8	389.4	415.3	444.4	476.8	511.0	553.0	601.1
140°	328.6	339.7	354.4	371.9	396.7	423.4	451.1	480.5	511.7	548.6	590.0
142.5°	338.2	348.5	363.2	380.0	403.4	428.6	454.7	482.7	512.5	544.9	580.4
145°	353.5	362.7	375.6	392.1	413.3	437.2	460.3	485.1	511.7	539.4	567.9
147.5°	368.9	376.8	388.8	403.1	421.8	442.8	463.6	486.0	509.4	533.7	556.2
150°	379.2	385.7	397.7	410.5	426.2	446.4	465.8	486.0	507.2	529.3	549.5
152.5°	388.8	394.5	405.0	417.2	431.3	450.1	467.2	485.3	504.2	524.1	542.2
155°	401.3	406.9	416.1	425.2	438.2	453.8	468.5	483.2	498.9	515.5	531.1
157.5°	413.3	417.7	425.6	433.7	443.5	456.9	469.4	480.9	493.4	507.4	520.1
160°	420.6	424.4	430.8	438.2	446.4	458.4	469.4	478.6	489.7	500.7	512.7
162.5°	427.3	430.9	436.7	442.6	449.4	459.9	468.7	476.4	485.3	494.9	504.6
165°	436.3	439.1	443.7	447.3	452.9	460.3	467.6	473.1	478.6	486.0	493.4
167.5°	443.9	445.5	448.1	450.7	454.2	460.3	465.4	467.9	472.2	477.4	482.7
170°	448.3	449.2	451.1	452.9	455.7	460.3	463.9	465.8	468.5	472.2	476.8
172.5°	450.5	451.4	453.2	454.3	455.7	459.5	462.5	462.8	464.1	467.1	470.2
175°	453.8	454.7	455.7	455.7	455.7	458.4	460.3	459.3	459.3	460.3	463.0
177.5°	455.8	455.8	456.5	455.8	455.8	457.3	458.0	456.5	456.5	457.3	458.0
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7	1259.7
2.5°	1317.5	1320.9	1328.2	1325.6	1329.0	1330.7	1332.5
5°	1423.9	1441.0	1448.4	1447.4	1458.6	1456.0	1453.3
7.5°	1544.0	1562.0	1572.1	1584.6	1591.9	1592.4	1598.7
10°	1612.1	1635.6	1645.2	1658.6	1667.1	1672.0	1671.4
12.5°	1664.3	1682.7	1704.2	1710.8	1722.4	1728.4	1726.2
15°	1727.0	1756.4	1778.9	1790.1	1804.6	1808.9	1814.7
17.5°	1783.0	1822.5	1848.7	1883.6	1896.7	1904.7	1900.0
20°	1825.4	1877.3	1903.5	1945.2	1968.2	1980.5	1976.2
22.5°	1875.5	1931.6	1980.1	2016.2	2051.1	2067.8	2071.2
25°	1961.2	2038.2	2109.3	2157.0	2200.2	2210.3	2232.8
27.5°	2057.1	2147.8	2223.9	2273.9	2304.1	2315.4	2322.4
30°	2117.3	2207.7	2264.9	2297.0	2306.6	2305.6	2304.5
32.5°	2146.9	2203.5	2214.5	2205.4	2183.4	2164.8	2145.4
35°	2105.1	2062.8	1999.7	1918.4	1858.5	1798.2	1792.2
37.5°	1893.2	1758.2	1653.1	1535.8	1468.2	1426.3	1397.5
40°	1693.8	1540.4	1413.2	1314.2	1245.3	1218.0	1191.3
42.5°	1477.4	1330.9	1218.1	1135.4	1083.6	1053.4	1032.1
45°	1200.4	1071.0	982.8	922.9	881.7	858.2	844.8
47.5°	983.6	887.9	812.9	769.8	741.3	723.0	723.1
50°	867.3	775.9	726.1	691.9	667.3	652.8	655.5
52.5°	764.1	695.9	653.4	624.7	606.6	597.7	597.4
55°	639.0	589.8	562.0	541.1	528.8	518.6	520.8
57.5°	546.5	505.1	486.5	469.1	460.6	456.5	450.6
60°	489.3	457.2	441.1	427.2	418.7	415.4	409.6
62.5°	438.3	413.1	397.5	386.1	378.4	377.4	372.8
65°	368.4	349.1	335.3	329.9	321.9	319.7	319.7
67.5°	303.7	289.9	279.1	274.2	270.7	271.2	268.6
70°	263.1	251.8	244.9	239.6	236.9	237.4	235.3
72.5°	230.1	217.6	211.5	208.3	204.8	206.2	205.3
75°	174.3	167.9	164.7	161.4	159.3	158.3	157.2
77.5°	128.0	122.3	119.9	118.0	118.4	115.8	117.9
80°	98.9	94.1	92.5	89.8	89.3	89.3	88.7
82.5°	72.4	69.7	68.5	66.3	65.4	66.2	64.8
85°	37.4	35.3	34.8	34.8	33.7	32.6	35.3
87.5°	17.2	15.7	16.0	15.6	15.6	15.4	14.5
90°	17.5	18.4	20.3	20.3	20.3	21.2	21.2
92.5°	118.4	89.1	75.5	63.7	61.5	60.2	58.7
95°	521.9	408.7	331.4	266.0	238.4	231.1	216.3
97.5°	887.6	777.3	669.7	612.8	561.3	534.6	522.8
100°	1087.1	992.3	896.5	833.1	766.8	732.7	718.0
102.5°	1209.3	1163.9	1099.1	1031.1	984.0	947.0	936.0
105°	1278.6	1319.1	1308.9	1279.5	1249.1	1230.7	1219.6
107.5°	1216.9	1320.9	1369.0	1383.9	1383.7	1377.6	1370.2
110°	1146.9	1276.7	1354.9	1396.4	1413.9	1420.3	1420.3



TEST NUMBER: P333288-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1077.7	1208.9	1301.2	1361.8	1391.8	1407.8	1414.4
115°	978.5	1104.5	1204.9	1276.7	1320.9	1346.6	1358.6
117.5°	909.8	1018.4	1110.5	1182.3	1228.0	1253.5	1260.8
120°	870.8	972.0	1053.0	1121.2	1165.3	1190.2	1197.5
122.5°	842.8	933.0	1008.8	1069.6	1110.1	1135.0	1141.6
125°	805.4	885.5	951.8	1003.3	1041.1	1061.3	1070.6
127.5°	769.7	844.5	906.5	953.2	986.6	1005.8	1009.8
130°	744.7	816.5	876.3	922.3	952.7	971.1	976.6
132.5°	721.1	786.2	843.9	889.9	920.3	937.2	943.5
135°	684.8	743.8	796.2	836.7	867.1	883.7	889.2
137.5°	652.4	701.4	746.0	782.2	809.8	825.1	831.2
140°	633.3	675.7	714.3	748.4	772.3	786.1	790.7
142.5°	617.1	653.6	687.1	716.0	736.2	749.2	753.1
145°	596.4	625.0	649.8	671.9	687.6	697.8	701.4
147.5°	579.3	601.3	620.0	637.5	650.1	655.9	657.6
150°	569.8	587.2	603.8	617.7	628.7	632.4	633.3
152.5°	560.2	576.2	589.1	600.7	609.5	613.2	614.2
155°	545.8	558.7	568.9	578.1	584.5	587.2	588.2
157.5°	532.2	542.2	550.1	557.2	562.6	565.1	565.0
160°	521.9	531.1	537.6	544.0	548.6	550.5	549.5
162.5°	513.1	520.8	526.5	531.5	535.4	535.8	535.5
165°	499.8	505.3	509.9	513.7	515.5	515.5	515.5
167.5°	487.0	491.2	494.5	496.3	498.0	497.3	497.1
170°	479.6	482.4	484.2	486.0	487.0	487.0	486.0
172.5°	472.9	475.0	476.1	476.4	478.1	476.7	475.7
175°	463.0	464.9	464.9	464.9	465.8	463.9	463.0
177.5°	458.8	458.8	458.8	458.0	458.8	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5

(END OF REPORT)