

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333167

Luminaire Tested: **S125DIP-S610D365U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333167
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D365U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3767.4 lumens
Efficiency: N/A
Efficacy: 137.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333167

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333167

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56
2	92	85	78	73	87	80	74	69	71	67	63	63	59	56	55	53	50	47
3	84	74	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43	39
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	36	39	35	32	29
6	65	53	44	38	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	33	28	25	23
8	56	43	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6203	6203	6203
5°	6217	6157	6196
10°	6178	6114	6149
15°	6111	6040	6066
20°	6016	5937	5948
25°	5912	5815	5810
30°	5785	5683	5655
35°	5649	5541	5463
40°	5509	5387	5311
45°	5358	5246	5142
50°	5191	5077	4924
55°	5031	4884	4748
60°	4839	4691	4525
65°	4609	4459	4308
70°	4390	4190	4047
75°	4000	3868	3735
80°	3559	3503	3418
85°	3097	3149	2986



TEST NUMBER: P333167

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	2.4
10°-20°	255.8	6.8
20°-30°	377.7	10.0
30°-40°	440.7	11.7
40°-50°	442.6	11.7
50°-60°	388.5	10.3
60°-70°	289.5	7.7
70°-80°	165.5	4.4
80°-90°	49.1	1.3
90°-100°	30.4	0.8
100°-110°	89.8	2.4
110°-120°	152.1	4.0
120°-130°	200.2	5.3
130°-140°	224.4	6.0
140°-150°	219.9	5.8
150°-160°	184.7	4.9
160°-170°	122.8	3.3
170°-180°	43.0	1.1
0°-30°	724.0	19.2
0°-40°	1164.7	30.9
0°-60°	1995.9	53.0
0°-90°	2500.0	66.4
90°-120°	272.4	7.2
90°-150°	916.9	24.3
90°-180°	1267.0	33.6
0°-180°	3767.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	960	960	960	960	960	
5°	959	957	950	956	956	91
15°	914	911	903	907	907	257
25°	830	826	816	817	815	382
35°	716	713	703	699	693	448
45°	587	583	574	566	563	452
55°	447	444	434	427	422	399
65°	302	300	292	285	282	299
75°	160	159	155	153	150	171
85°	42	42	42	42	40	47
90°	0	3	6	7	8	4
95°	23	24	27	30	30	25
105°	81	82	84	87	88	86
115°	152	154	154	154	154	151
125°	222	224	225	224	224	199
135°	289	291	292	292	290	223
145°	350	352	353	353	352	219
155°	401	401	401	402	401	185
165°	436	435	435	437	435	123
175°	453	452	452	454	451	43
180°	454	454	454	454	454	



TEST NUMBER: P333167

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	962.8	962.4	962.0	961.6	961.2	960.3	959.0	957.6	956.3	954.9	956.3
5°	958.9	958.5	958.2	957.8	957.5	956.5	954.8	953.1	951.4	949.7	951.3
7.5°	950.0	949.7	949.4	949.0	948.7	947.6	945.7	943.9	942.0	940.2	941.6
10°	942.1	941.8	941.5	941.1	940.8	939.7	937.8	936.0	934.1	932.3	933.6
12.5°	932.4	931.8	931.2	930.6	930.0	928.8	927.1	925.4	923.6	921.9	923.0
15°	914.0	913.5	913.0	912.5	912.0	910.8	909.0	907.1	905.2	903.4	904.2
17.5°	892.9	892.2	891.4	890.7	889.9	888.6	886.7	884.7	882.8	880.9	881.9
20°	875.3	874.9	874.6	874.3	873.9	872.7	870.5	868.3	866.1	863.9	865.1
22.5°	857.6	857.0	856.4	855.8	855.2	853.9	851.8	849.8	847.7	845.6	846.4
25°	829.7	828.8	828.0	827.2	826.3	824.8	822.6	820.4	818.2	816.0	816.4
27.5°	797.0	796.5	796.0	795.5	795.0	793.6	791.3	789.1	786.8	784.6	784.6
30°	775.7	775.2	774.7	774.2	773.7	772.2	769.7	767.1	764.6	762.1	761.7
32.5°	752.6	751.9	751.1	750.3	749.5	748.0	745.8	743.5	741.2	739.0	738.4
35°	716.5	715.8	715.1	714.5	713.8	712.3	709.9	707.5	705.2	702.8	702.0
37.5°	678.9	678.1	677.3	676.4	675.6	674.0	671.8	669.6	667.3	665.1	663.9
40°	653.4	652.6	651.7	650.9	650.0	648.4	646.1	643.7	641.3	639.0	637.5
42.5°	626.1	625.4	624.6	623.9	623.2	621.7	619.3	617.0	614.6	612.2	610.9
45°	586.6	585.9	585.2	584.5	583.9	582.5	580.5	578.5	576.4	574.4	572.4
47.5°	544.0	544.0	544.1	544.1	544.1	542.9	540.5	538.1	535.7	533.2	531.2
50°	516.7	516.1	515.6	515.1	514.6	513.4	511.3	509.3	507.3	505.3	503.1
52.5°	488.7	488.3	488.0	487.6	487.2	485.9	483.8	481.6	479.5	477.3	475.4
55°	446.8	446.2	445.7	445.2	444.7	443.3	440.9	438.6	436.2	433.8	432.3
57.5°	402.5	402.3	402.0	401.7	401.5	400.3	398.3	396.3	394.3	392.4	390.4
60°	374.6	373.9	373.2	372.5	371.9	370.6	368.8	366.9	365.0	363.2	361.5
62.5°	345.4	344.9	344.3	343.8	343.2	342.2	340.6	339.0	337.4	335.8	334.0
65°	301.6	301.3	301.0	300.6	300.3	299.2	297.3	295.5	293.6	291.8	290.2
67.5°	259.2	258.5	257.8	257.1	256.4	255.4	254.0	252.6	251.2	249.8	248.5
70°	232.5	231.7	230.8	230.0	229.1	227.9	226.4	224.9	223.4	221.9	220.8
72.5°	203.3	202.7	202.2	201.6	201.0	200.2	199.3	198.3	197.3	196.3	195.2
75°	160.3	160.0	159.6	159.3	159.0	158.4	157.5	156.7	155.8	155.0	154.5
77.5°	120.7	120.5	120.4	120.2	120.1	119.8	119.3	118.9	118.4	117.9	117.6
80°	95.7	95.7	95.7	95.7	95.7	95.6	95.2	94.9	94.6	94.2	94.0
82.5°	73.9	73.6	73.3	73.0	72.8	72.6	72.5	72.5	72.4	72.3	72.0
85°	41.8	42.0	42.1	42.3	42.5	42.5	42.5	42.5	42.5	42.5	42.4
87.5°	16.5	16.6	16.7	16.9	17.0	17.0	17.0	17.0	17.0	16.9	17.0
90°	0.4	1.0	1.6	2.2	2.9	3.5	4.0	4.6	5.1	5.7	6.0
92.5°	8.6	9.0	9.4	9.9	10.3	10.9	11.5	12.2	12.9	13.6	14.1
95°	23.0	23.1	23.3	23.4	23.6	24.1	24.9	25.6	26.4	27.2	27.8
97.5°	38.2	38.2	38.3	38.4	38.4	39.0	40.1	41.2	42.2	43.3	43.9
100°	49.5	49.5	49.5	49.5	49.5	50.0	51.0	52.0	53.1	54.1	54.8
102.5°	61.6	62.0	62.3	62.6	62.9	63.3	63.8	64.3	64.9	65.4	66.2
105°	80.6	81.0	81.4	81.8	82.2	82.6	83.1	83.5	84.0	84.5	84.9
107.5°	101.5	101.9	102.3	102.7	103.1	103.5	103.8	104.2	104.5	104.9	105.1
110°	115.9	116.3	116.7	117.1	117.5	117.8	118.0	118.3	118.5	118.8	119.0



TEST NUMBER: P333167

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	130.6	130.8	131.0	131.2	131.4	131.7	132.0	132.3	132.6	132.9	133.0
115°	152.3	152.6	153.0	153.3	153.6	153.8	154.0	154.1	154.3	154.5	154.4
117.5°	174.1	174.2	174.4	174.5	174.7	174.8	175.0	175.1	175.2	175.4	175.4
120°	187.7	188.1	188.5	188.9	189.2	189.5	189.6	189.6	189.7	189.8	189.8
122.5°	202.4	202.5	202.7	202.8	202.9	203.1	203.3	203.5	203.7	203.9	203.9
125°	222.3	222.8	223.3	223.7	224.2	224.5	224.6	224.6	224.7	224.8	224.6
127.5°	243.5	243.8	244.1	244.3	244.6	244.8	244.9	245.0	245.1	245.1	245.1
130°	256.2	256.6	257.0	257.4	257.8	258.1	258.2	258.4	258.6	258.7	258.6
132.5°	269.0	269.6	270.3	270.9	271.5	271.9	271.8	271.8	271.8	271.7	271.6
135°	289.1	289.6	290.1	290.5	291.0	291.3	291.4	291.4	291.5	291.6	291.6
137.5°	308.1	308.5	309.0	309.4	309.9	310.2	310.4	310.5	310.7	310.9	311.0
140°	320.2	320.6	321.0	321.4	321.8	322.1	322.3	322.6	322.8	323.0	323.2
142.5°	332.4	332.7	333.0	333.4	333.7	334.0	334.3	334.6	334.9	335.2	335.3
145°	350.3	350.6	350.9	351.2	351.5	351.8	352.0	352.3	352.5	352.7	352.7
147.5°	366.8	367.0	367.1	367.3	367.5	367.7	367.9	368.1	368.2	368.4	368.6
150°	377.8	377.8	377.7	377.6	377.5	377.6	377.9	378.3	378.6	378.9	378.9
152.5°	386.9	387.0	387.1	387.2	387.3	387.4	387.6	387.7	387.8	387.9	388.1
155°	400.8	400.8	400.8	400.8	400.8	400.8	400.9	401.0	401.1	401.2	401.5
157.5°	413.2	413.1	412.9	412.7	412.6	412.5	412.6	412.7	412.7	412.8	413.1
160°	420.6	420.4	420.1	419.9	419.7	419.6	419.7	419.7	419.8	419.9	420.2
162.5°	427.1	426.9	426.8	426.6	426.4	426.3	426.3	426.4	426.4	426.4	426.8
165°	435.8	435.6	435.5	435.3	435.2	435.1	435.2	435.3	435.4	435.4	435.8
167.5°	443.1	442.8	442.5	442.2	441.9	441.7	441.7	441.7	441.7	441.7	442.2
170°	447.1	446.8	446.5	446.2	445.8	445.7	445.7	445.7	445.7	445.7	446.2
172.5°	449.9	449.6	449.3	449.0	448.7	448.5	448.5	448.5	448.5	448.5	449.0
175°	453.1	452.8	452.5	452.2	451.9	451.7	451.7	451.7	451.7	451.7	452.2
177.5°	454.7	454.5	454.2	454.0	453.7	453.6	453.5	453.5	453.4	453.3	453.7
180°	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2



TEST NUMBER: P333167

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	957.6	959.0	960.3	960.9	960.8	960.6	960.5	960.4
5°	952.8	954.3	955.8	956.5	956.3	956.2	956.0	955.8
7.5°	943.1	944.6	946.1	946.8	946.6	946.4	946.3	946.1
10°	935.0	936.3	937.7	938.3	938.1	937.9	937.7	937.6
12.5°	924.1	925.2	926.2	926.8	926.7	926.7	926.7	926.6
15°	905.1	905.9	906.8	907.2	907.2	907.2	907.2	907.2
17.5°	883.0	884.0	885.1	885.2	884.3	883.5	882.7	881.8
20°	866.2	867.4	868.6	868.8	867.9	867.1	866.2	865.4
22.5°	847.2	848.0	848.8	848.9	848.3	847.7	847.1	846.6
25°	816.7	817.0	817.4	817.3	816.8	816.3	815.8	815.3
27.5°	784.7	784.8	784.8	784.6	784.1	783.6	783.1	782.6
30°	761.4	761.1	760.7	760.3	759.8	759.3	758.8	758.3
32.5°	737.8	737.1	736.5	735.8	734.9	734.0	733.0	732.1
35°	701.1	700.3	699.4	698.3	697.0	695.6	694.3	692.9
37.5°	662.6	661.4	660.1	659.1	658.3	657.6	656.8	656.0
40°	635.9	634.4	632.9	631.9	631.4	630.9	630.4	629.9
42.5°	609.5	608.1	606.7	605.6	604.8	604.1	603.3	602.5
45°	570.3	568.3	566.3	565.0	564.5	564.0	563.5	563.0
47.5°	529.1	527.0	525.0	523.4	522.2	521.0	519.8	518.6
50°	500.9	498.7	496.5	494.8	493.6	492.4	491.2	490.1
52.5°	473.4	471.5	469.6	468.0	466.7	465.3	464.0	462.7
55°	430.8	429.3	427.8	426.4	425.2	424.0	422.9	421.7
57.5°	388.4	386.5	384.5	383.2	382.6	381.9	381.3	380.7
60°	359.8	358.1	356.4	355.0	353.8	352.6	351.4	350.3
62.5°	332.2	330.4	328.5	327.2	326.3	325.3	324.4	323.5
65°	288.7	287.2	285.7	284.6	283.9	283.2	282.6	281.9
67.5°	247.3	246.0	244.7	243.8	243.4	243.0	242.6	242.2
70°	219.8	218.8	217.8	217.0	216.3	215.6	214.9	214.3
72.5°	194.0	192.9	191.7	190.8	190.1	189.5	188.8	188.1
75°	154.0	153.5	153.0	152.4	151.7	151.0	150.4	149.7
77.5°	117.3	117.0	116.7	116.3	115.8	115.4	114.9	114.4
80°	93.9	93.7	93.5	93.3	92.9	92.6	92.3	91.9
82.5°	71.7	71.4	71.1	70.9	70.9	70.8	70.7	70.7
85°	42.2	42.0	41.9	41.6	41.3	40.9	40.6	40.3
87.5°	17.1	17.2	17.2	17.2	17.0	16.7	16.5	16.3
90°	6.4	6.8	7.2	7.5	7.8	8.0	8.2	8.5
92.5°	14.6	15.1	15.6	16.0	16.2	16.3	16.5	16.7
95°	28.3	28.9	29.4	29.8	29.9	30.1	30.2	30.4
97.5°	44.4	44.9	45.4	45.7	45.8	45.9	46.0	46.1
100°	55.5	56.2	56.9	57.3	57.5	57.7	57.8	58.0
102.5°	66.9	67.7	68.5	69.0	69.2	69.4	69.6	69.8
105°	85.4	85.9	86.4	86.7	86.9	87.2	87.4	87.7
107.5°	105.4	105.6	105.8	106.0	105.9	105.9	105.9	105.9
110°	119.2	119.5	119.7	119.8	119.7	119.6	119.5	119.5



TEST NUMBER: P333167

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	133.1	133.2	133.3	133.3	133.2	133.0	132.9	132.8
115°	154.3	154.2	154.1	154.1	154.0	153.9	153.8	153.7
117.5°	175.5	175.6	175.6	175.5	175.2	174.9	174.6	174.2
120°	189.8	189.8	189.8	189.6	189.3	189.0	188.7	188.4
122.5°	203.8	203.7	203.7	203.5	203.3	203.0	202.8	202.5
125°	224.5	224.3	224.2	224.0	224.0	223.9	223.8	223.7
127.5°	245.0	244.9	244.8	244.7	244.6	244.4	244.2	244.1
130°	258.6	258.5	258.4	258.3	258.1	258.0	257.8	257.7
132.5°	271.6	271.5	271.4	271.3	271.0	270.8	270.6	270.4
135°	291.6	291.6	291.6	291.4	291.1	290.8	290.5	290.2
137.5°	311.1	311.2	311.3	311.1	310.7	310.3	309.9	309.5
140°	323.4	323.5	323.7	323.6	323.2	322.8	322.4	322.0
142.5°	335.4	335.5	335.6	335.4	335.0	334.6	334.3	333.9
145°	352.7	352.7	352.7	352.6	352.4	352.1	351.9	351.7
147.5°	368.8	369.0	369.2	369.0	368.5	367.9	367.4	366.9
150°	378.9	378.9	378.9	378.8	378.7	378.5	378.3	378.2
152.5°	388.3	388.5	388.7	388.6	388.4	388.1	387.8	387.5
155°	401.8	402.1	402.4	402.4	402.0	401.6	401.2	400.8
157.5°	413.4	413.8	414.1	414.0	413.5	412.9	412.4	411.9
160°	420.5	420.8	421.1	421.1	420.7	420.3	419.9	419.5
162.5°	427.1	427.5	427.9	427.9	427.4	426.9	426.5	426.0
165°	436.1	436.4	436.7	436.6	436.1	435.7	435.2	434.7
167.5°	442.7	443.1	443.6	443.6	443.1	442.6	442.1	441.7
170°	446.6	447.1	447.6	447.5	447.0	446.4	445.9	445.3
172.5°	449.5	449.9	450.4	450.4	449.9	449.4	448.9	448.4
175°	452.6	453.1	453.6	453.5	453.0	452.4	451.9	451.3
177.5°	454.1	454.5	454.8	454.8	454.4	453.9	453.5	453.0
180°	454.2	454.2	454.2	454.2	454.2	454.2	454.2	454.2

(END OF REPORT)