

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333294-927

Luminaire Tested: **S125DIP-S1090D1205U927-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333294-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1090D1205U927-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6943.8 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333294-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333294-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	50	49	48	43
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36
3	81	72	64	58	75	66	60	55	57	52	48	47	44	41	39	36	34	30
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	22
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	28	25	23	20
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	23	20	17
8	54	42	34	28	50	39	32	27	33	28	24	29	24	21	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8730	8730	8730
5°	8749	8666	8722
10°	8697	8605	8655
15°	8602	8501	8538
20°	8467	8357	8372
25°	8322	8185	8177
30°	8143	7999	7959
35°	7950	7799	7689
40°	7754	7583	7474
45°	7541	7384	7237
50°	7306	7145	6931
55°	7080	6875	6683
60°	6810	6603	6368
65°	6487	6276	6062
70°	6180	5897	5695
75°	5629	5445	5255
80°	5013	4932	4813
85°	4357	4439	4194



TEST NUMBER: P333294-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.5	1.8
10°-20°	360.0	5.2
20°-30°	531.6	7.7
30°-40°	620.3	8.9
40°-50°	623.0	9.0
50°-60°	546.9	7.9
60°-70°	407.5	5.9
70°-80°	233.0	3.4
80°-90°	70.3	1.0
90°-100°	330.9	4.8
100°-110°	711.4	10.2
110°-120°	667.6	9.6
120°-130°	541.1	7.8
130°-140°	434.2	6.3
140°-150°	327.7	4.7
150°-160°	230.6	3.3
160°-170°	136.0	2.0
170°-180°	44.2	0.6
0°-30°	1019.1	14.7
0°-40°	1639.4	23.6
0°-60°	2809.2	40.5
0°-90°	3520.0	50.7
90°-120°	1710.0	24.6
90°-150°	3013.0	43.4
90°-180°	3424.0	49.3
0°-180°	6943.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1352	1352	1352	1352	1352	
5°	1350	1347	1337	1346	1345	128
15°	1286	1283	1272	1277	1277	362
25°	1168	1162	1149	1150	1148	537
35°	1008	1004	989	984	975	631
45°	826	821	808	796	792	636
55°	629	625	611	601	594	561
65°	424	422	411	401	397	421
75°	226	223	218	215	211	241
85°	59	60	60	59	57	66
90°	1	8	15	19	21	5
95°	30	90	816	370	216	32
105°	104	145	667	1314	1220	110
115°	186	224	536	1155	1359	183
125°	258	302	514	919	1071	229
135°	302	363	510	770	889	234
145°	352	403	512	637	701	220
155°	401	432	499	564	588	185
165°	438	450	479	508	516	123
175°	456	456	459	465	463	43
180°	456	456	456	456	456	



TEST NUMBER: P333294-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8
2.5°	1355.2	1354.6	1354.0	1353.4	1352.9	1351.6	1349.7	1347.8	1345.9	1344.0	1345.9
5°	1349.6	1349.2	1348.7	1348.2	1347.7	1346.3	1343.9	1341.6	1339.2	1336.8	1338.9
7.5°	1337.2	1336.7	1336.3	1335.8	1335.3	1333.7	1331.1	1328.5	1325.9	1323.3	1325.4
10°	1326.1	1325.6	1325.2	1324.7	1324.2	1322.6	1320.0	1317.4	1314.8	1312.2	1314.1
12.5°	1312.4	1311.5	1310.7	1309.8	1309.0	1307.3	1304.9	1302.5	1300.1	1297.6	1299.2
15°	1286.5	1285.8	1285.1	1284.4	1283.7	1282.0	1279.4	1276.8	1274.1	1271.5	1272.7
17.5°	1256.8	1255.8	1254.7	1253.6	1252.6	1250.7	1248.0	1245.3	1242.6	1239.8	1241.3
20°	1232.0	1231.5	1231.1	1230.6	1230.1	1228.3	1225.2	1222.1	1219.0	1215.9	1217.6
22.5°	1207.1	1206.3	1205.5	1204.6	1203.7	1201.8	1199.0	1196.0	1193.2	1190.3	1191.4
25°	1167.8	1166.6	1165.5	1164.3	1163.1	1160.9	1157.9	1154.8	1151.7	1148.6	1149.1
27.5°	1121.8	1121.1	1120.4	1119.7	1119.0	1117.1	1113.8	1110.6	1107.5	1104.3	1104.4
30°	1091.9	1091.2	1090.4	1089.7	1089.0	1086.9	1083.3	1079.7	1076.2	1072.6	1072.1
32.5°	1059.4	1058.3	1057.2	1056.1	1055.0	1052.9	1049.6	1046.5	1043.3	1040.1	1039.3
35°	1008.4	1007.5	1006.5	1005.6	1004.6	1002.5	999.2	995.9	992.5	989.2	988.0
37.5°	955.6	954.4	953.2	952.0	950.9	948.7	945.5	942.5	939.3	936.2	934.4
40°	919.7	918.5	917.3	916.2	915.0	912.7	909.3	906.0	902.7	899.4	897.2
42.5°	881.2	880.2	879.2	878.2	877.2	875.0	871.7	868.4	865.1	861.7	859.8
45°	825.6	824.7	823.7	822.8	821.8	819.9	817.1	814.2	811.4	808.5	805.6
47.5°	765.7	765.7	765.8	765.9	765.9	764.2	760.8	757.3	753.9	750.5	747.6
50°	727.2	726.5	725.8	725.1	724.4	722.5	719.7	716.8	714.0	711.1	708.1
52.5°	687.9	687.3	686.8	686.3	685.8	684.0	681.0	677.9	674.9	671.8	669.1
55°	628.8	628.1	627.4	626.7	626.0	623.9	620.6	617.3	613.9	610.6	608.5
57.5°	566.6	566.2	565.9	565.5	565.1	563.5	560.6	557.9	555.1	552.2	549.5
60°	527.2	526.2	525.3	524.3	523.4	521.7	519.0	516.4	513.8	511.2	508.8
62.5°	486.2	485.4	484.7	483.9	483.2	481.6	479.3	477.1	474.9	472.7	470.1
65°	424.5	424.1	423.6	423.1	422.6	421.1	418.5	415.9	413.3	410.7	408.5
67.5°	364.9	363.8	362.9	361.9	360.9	359.4	357.4	355.5	353.6	351.6	349.8
70°	327.3	326.1	324.9	323.7	322.5	320.8	318.7	316.6	314.4	312.3	310.9
72.5°	286.2	285.3	284.6	283.8	283.0	281.9	280.5	279.1	277.7	276.3	274.7
75°	225.6	225.1	224.7	224.2	223.7	222.9	221.7	220.5	219.4	218.2	217.5
77.5°	169.8	169.6	169.4	169.3	169.1	168.7	167.9	167.3	166.7	166.0	165.6
80°	134.8	134.8	134.8	134.8	134.8	134.5	134.0	133.6	133.1	132.6	132.4
82.5°	103.9	103.5	103.2	102.8	102.4	102.2	102.1	102.0	101.9	101.8	101.4
85°	58.8	59.0	59.3	59.5	59.7	59.9	59.9	59.9	59.9	59.9	59.7
87.5°	23.3	23.4	23.8	24.2	24.6	24.9	24.9	25.0	25.0	25.2	25.3
90°	1.0	1.8	3.6	5.5	7.4	9.2	10.1	12.0	12.9	14.7	15.7
92.5°	11.2	13.6	21.4	32.8	48.6	75.5	125.7	210.1	301.6	296.8	240.3
95°	30.3	31.3	38.7	48.8	69.0	110.4	209.0	411.5	665.5	815.6	798.0
97.5°	50.5	51.6	56.7	66.9	85.1	114.9	180.1	328.4	594.3	870.9	1009.8
100°	64.4	66.3	69.9	80.1	97.6	125.2	178.6	298.3	530.2	831.2	1061.3
102.5°	79.9	81.0	84.0	94.8	110.8	137.7	185.2	285.7	481.6	761.2	1030.4
105°	104.0	104.0	108.6	117.8	132.5	158.4	198.8	280.7	434.4	667.3	931.5
107.5°	127.5	129.4	133.8	141.4	156.7	179.8	219.0	289.2	414.5	602.7	830.7
110°	144.5	146.4	150.0	158.4	172.1	196.1	233.8	297.3	408.7	572.5	773.2



TEST NUMBER: P333294-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.4	163.3	166.2	174.5	188.3	211.5	247.8	307.6	408.7	554.8	730.5
115°	185.9	187.7	190.5	198.8	212.6	235.7	269.7	323.1	411.5	535.8	683.9
117.5°	208.0	210.8	213.7	222.0	237.7	259.9	292.2	340.8	417.6	526.3	656.1
120°	222.8	225.5	229.2	237.5	253.1	276.2	308.4	352.5	423.4	521.9	640.6
122.5°	238.2	240.3	243.2	251.4	268.6	291.6	323.8	365.8	428.6	518.2	627.4
125°	257.7	259.6	264.2	272.4	289.9	313.9	344.3	383.8	437.2	513.7	609.3
127.5°	273.0	275.8	281.7	292.2	310.8	334.7	363.9	400.4	446.9	511.4	592.8
130°	282.6	285.3	292.7	304.7	324.0	347.9	376.4	411.5	452.9	509.9	581.8
132.5°	289.9	293.4	302.3	315.8	335.8	359.7	388.2	421.0	459.5	509.9	572.9
135°	301.9	305.6	316.6	331.4	350.7	375.6	404.1	434.4	468.5	509.9	562.4
137.5°	317.0	319.8	330.1	344.8	363.8	389.4	415.3	444.4	476.8	511.0	553.0
140°	325.8	328.6	339.7	354.4	371.9	396.7	423.4	451.1	480.5	511.7	548.6
142.5°	336.1	338.2	348.5	363.2	380.0	403.4	428.6	454.7	482.7	512.5	544.9
145°	351.6	353.5	362.7	375.6	392.1	413.3	437.2	460.3	485.1	511.7	539.4
147.5°	367.8	368.9	376.8	388.8	403.1	421.8	442.8	463.6	486.0	509.4	533.7
150°	377.4	379.2	385.7	397.7	410.5	426.2	446.4	465.8	486.0	507.2	529.3
152.5°	387.7	388.8	394.5	405.0	417.2	431.3	450.1	467.2	485.3	504.2	524.1
155°	401.3	401.3	406.9	416.1	425.2	438.2	453.8	468.5	483.2	498.9	515.5
157.5°	413.5	413.3	417.7	425.6	433.7	443.5	456.9	469.4	480.9	493.4	507.4
160°	421.6	420.6	424.4	430.8	438.2	446.4	458.4	469.4	478.6	489.7	500.7
162.5°	428.2	427.3	430.9	436.7	442.6	449.4	459.9	468.7	476.4	485.3	494.9
165°	438.2	436.3	439.1	443.7	447.3	452.9	460.3	467.6	473.1	478.6	486.0
167.5°	444.8	443.9	445.5	448.1	450.7	454.2	460.3	465.4	467.9	472.2	477.4
170°	449.2	448.3	449.2	451.1	452.9	455.7	460.3	463.9	465.8	468.5	472.2
172.5°	452.2	450.5	451.4	453.2	454.3	455.7	459.5	462.5	462.8	464.1	467.1
175°	455.7	453.8	454.7	455.7	455.7	455.7	458.4	460.3	459.3	459.3	460.3
177.5°	457.3	455.8	455.8	456.5	455.8	455.8	457.3	458.0	456.5	456.5	457.3
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5



TEST NUMBER: P333294-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8	1351.8
2.5°	1347.8	1349.7	1351.6	1352.5	1352.3	1352.1	1351.9	1351.8
5°	1341.1	1343.2	1345.4	1346.3	1346.1	1345.8	1345.6	1345.4
7.5°	1327.5	1329.6	1331.7	1332.6	1332.4	1332.1	1331.9	1331.7
10°	1316.0	1317.9	1319.8	1320.6	1320.4	1320.2	1319.9	1319.7
12.5°	1300.7	1302.2	1303.7	1304.5	1304.4	1304.3	1304.3	1304.2
15°	1273.9	1275.1	1276.3	1276.9	1276.9	1276.9	1276.9	1276.9
17.5°	1242.9	1244.3	1245.8	1245.9	1244.8	1243.6	1242.4	1241.2
20°	1219.2	1220.9	1222.6	1222.8	1221.6	1220.4	1219.2	1218.1
22.5°	1192.5	1193.6	1194.6	1194.8	1194.0	1193.2	1192.4	1191.5
25°	1149.5	1150.0	1150.5	1150.3	1149.6	1148.9	1148.2	1147.5
27.5°	1104.5	1104.5	1104.7	1104.4	1103.7	1103.0	1102.2	1101.5
30°	1071.7	1071.2	1070.7	1070.2	1069.4	1068.7	1068.0	1067.3
32.5°	1038.4	1037.5	1036.7	1035.6	1034.4	1033.1	1031.7	1030.5
35°	986.8	985.6	984.4	982.9	981.0	979.1	977.2	975.3
37.5°	932.6	930.9	929.2	927.7	926.6	925.5	924.4	923.4
40°	895.1	892.9	890.8	889.4	888.7	888.0	887.2	886.5
42.5°	857.9	855.9	854.0	852.4	851.4	850.2	849.1	848.0
45°	802.8	799.9	797.1	795.3	794.6	793.8	793.1	792.4
47.5°	744.7	741.8	738.9	736.7	735.0	733.3	731.7	730.0
50°	705.0	701.9	698.8	696.4	694.7	693.1	691.4	689.8
52.5°	666.4	663.7	661.0	658.7	656.8	655.0	653.2	651.3
55°	606.3	604.2	602.1	600.2	598.5	596.8	595.2	593.5
57.5°	546.8	544.0	541.2	539.4	538.5	537.6	536.7	535.8
60°	506.4	504.1	501.7	499.6	498.0	496.3	494.6	493.0
62.5°	467.5	465.0	462.4	460.5	459.2	458.0	456.6	455.3
65°	406.4	404.3	402.1	400.5	399.6	398.6	397.7	396.7
67.5°	348.0	346.2	344.4	343.2	342.6	342.1	341.5	341.0
70°	309.4	308.0	306.6	305.4	304.4	303.5	302.5	301.6
72.5°	273.1	271.5	269.9	268.6	267.7	266.7	265.8	264.8
75°	216.7	216.0	215.3	214.4	213.5	212.5	211.6	210.6
77.5°	165.1	164.7	164.3	163.7	163.0	162.4	161.7	161.1
80°	132.1	131.9	131.7	131.3	130.8	130.3	129.8	129.4
82.5°	100.9	100.5	100.1	99.8	99.7	99.7	99.6	99.4
85°	59.4	59.2	58.9	58.5	58.1	57.6	57.1	56.6
87.5°	25.6	25.7	25.9	26.1	25.7	25.3	25.1	24.8
90°	16.6	17.5	18.4	20.3	20.3	20.3	21.2	21.2
92.5°	163.1	118.4	89.1	75.5	63.7	61.5	60.2	58.7
95°	661.8	521.9	408.7	331.4	266.0	238.4	231.1	216.3
97.5°	985.6	887.6	777.3	669.7	612.8	561.3	534.6	522.8
100°	1132.2	1087.1	992.3	896.5	833.1	766.8	732.7	718.0
102.5°	1181.5	1209.3	1163.9	1099.1	1031.1	984.0	947.0	936.0
105°	1152.5	1278.6	1319.1	1308.9	1279.5	1249.1	1230.7	1219.6
107.5°	1048.6	1216.9	1320.9	1369.0	1383.9	1383.7	1377.6	1370.2
110°	972.0	1146.9	1276.7	1354.9	1396.4	1413.9	1420.3	1420.3



TEST NUMBER: P333294-927

CATALOG NUMBER: S125DIP-S1090D1205U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	911.6	1077.7	1208.9	1301.2	1361.8	1391.8	1407.8	1414.4
115°	835.8	978.5	1104.5	1204.9	1276.7	1320.9	1346.6	1358.6
117.5°	786.8	909.8	1018.4	1110.5	1182.3	1228.0	1253.5	1260.8
120°	760.3	870.8	972.0	1053.0	1121.2	1165.3	1190.2	1197.5
122.5°	740.5	842.8	933.0	1008.8	1069.6	1110.1	1135.0	1141.6
125°	711.5	805.4	885.5	951.8	1003.3	1041.1	1061.3	1070.6
127.5°	682.1	769.7	844.5	906.5	953.2	986.6	1005.8	1009.8
130°	663.7	744.7	816.5	876.3	922.3	952.7	971.1	976.6
132.5°	645.2	721.1	786.2	843.9	889.9	920.3	937.2	943.5
135°	621.3	684.8	743.8	796.2	836.7	867.1	883.7	889.2
137.5°	601.1	652.4	701.4	746.0	782.2	809.8	825.1	831.2
140°	590.0	633.3	675.7	714.3	748.4	772.3	786.1	790.7
142.5°	580.4	617.1	653.6	687.1	716.0	736.2	749.2	753.1
145°	567.9	596.4	625.0	649.8	671.9	687.6	697.8	701.4
147.5°	556.2	579.3	601.3	620.0	637.5	650.1	655.9	657.6
150°	549.5	569.8	587.2	603.8	617.7	628.7	632.4	633.3
152.5°	542.2	560.2	576.2	589.1	600.7	609.5	613.2	614.2
155°	531.1	545.8	558.7	568.9	578.1	584.5	587.2	588.2
157.5°	520.1	532.2	542.2	550.1	557.2	562.6	565.1	565.0
160°	512.7	521.9	531.1	537.6	544.0	548.6	550.5	549.5
162.5°	504.6	513.1	520.8	526.5	531.5	535.4	535.8	535.5
165°	493.4	499.8	505.3	509.9	513.7	515.5	515.5	515.5
167.5°	482.7	487.0	491.2	494.5	496.3	498.0	497.3	497.1
170°	476.8	479.6	482.4	484.2	486.0	487.0	487.0	486.0
172.5°	470.2	472.9	475.0	476.1	476.4	478.1	476.7	475.7
175°	463.0	463.0	464.9	464.9	464.9	465.8	463.9	463.0
177.5°	458.0	458.8	458.8	458.8	458.0	458.8	456.5	456.5
180°	456.5	456.5	456.5	456.5	456.5	456.5	456.5	456.5

(END OF REPORT)