

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333168

Luminaire Tested: **S125DIP-S610D365U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333168
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D365U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3814.6 lumens
Efficiency: N/A
Efficacy: 138.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333168

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333168

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66
1	101	97	93	89	95	91	88	84	81	78	76	71	69	67	62	61	59	55
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	40	37	33
5	71	59	50	44	66	56	48	42	50	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	25
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6203	6203	6203
5°	6217	6157	6196
10°	6178	6114	6149
15°	6111	6040	6066
20°	6016	5937	5948
25°	5912	5815	5810
30°	5785	5683	5655
35°	5649	5541	5463
40°	5509	5387	5311
45°	5358	5246	5142
50°	5191	5077	4924
55°	5031	4884	4748
60°	4839	4691	4525
65°	4609	4459	4308
70°	4390	4190	4047
75°	4000	3868	3735
80°	3559	3503	3418
85°	3097	3149	2986



TEST NUMBER: P333168

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	2.4
10°-20°	255.8	6.7
20°-30°	377.7	9.9
30°-40°	440.7	11.6
40°-50°	442.6	11.6
50°-60°	388.5	10.2
60°-70°	289.5	7.6
70°-80°	165.5	4.3
80°-90°	49.1	1.3
90°-100°	127.1	3.3
100°-110°	273.1	7.2
110°-120°	256.3	6.7
120°-130°	207.7	5.4
130°-140°	166.7	4.4
140°-150°	125.8	3.3
150°-160°	88.6	2.3
160°-170°	52.2	1.4
170°-180°	17.0	0.4
0°-30°	724.0	19.0
0°-40°	1164.7	30.5
0°-60°	1995.9	52.3
0°-90°	2500.0	65.5
90°-120°	656.5	17.2
90°-150°	1156.8	30.3
90°-180°	1315.0	34.5
0°-180°	3814.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	960	960	960	960	960	
5°	959	957	950	956	956	91
15°	914	911	903	907	907	257
25°	830	826	816	817	815	382
35°	716	713	703	699	693	448
45°	587	583	574	566	563	452
55°	447	444	434	427	422	399
65°	302	300	292	285	282	299
75°	160	159	155	153	150	171
85°	42	42	42	42	40	47
90°	0	3	6	7	8	3
95°	12	34	313	142	83	12
105°	40	56	256	504	468	42
115°	71	86	206	443	522	70
125°	99	116	197	353	411	88
135°	116	139	196	296	341	90
145°	135	155	196	245	269	85
155°	154	166	192	216	226	71
165°	168	173	184	195	198	47
175°	175	175	176	178	178	17
180°	175	175	175	175	175	



TEST NUMBER: P333168

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	962.8	962.4	962.0	961.6	961.2	960.3	959.0	957.6	956.3	954.9	956.3
5°	958.9	958.5	958.2	957.8	957.5	956.5	954.8	953.1	951.4	949.7	951.3
7.5°	950.0	949.7	949.4	949.0	948.7	947.6	945.7	943.9	942.0	940.2	941.6
10°	942.1	941.8	941.5	941.1	940.8	939.7	937.8	936.0	934.1	932.3	933.6
12.5°	932.4	931.8	931.2	930.6	930.0	928.8	927.1	925.4	923.6	921.9	923.0
15°	914.0	913.5	913.0	912.5	912.0	910.8	909.0	907.1	905.2	903.4	904.2
17.5°	892.9	892.2	891.4	890.7	889.9	888.6	886.7	884.7	882.8	880.9	881.9
20°	875.3	874.9	874.6	874.3	873.9	872.7	870.5	868.3	866.1	863.9	865.1
22.5°	857.6	857.0	856.4	855.8	855.2	853.9	851.8	849.8	847.7	845.6	846.4
25°	829.7	828.8	828.0	827.2	826.3	824.8	822.6	820.4	818.2	816.0	816.4
27.5°	797.0	796.5	796.0	795.5	795.0	793.6	791.3	789.1	786.8	784.6	784.6
30°	775.7	775.2	774.7	774.2	773.7	772.2	769.7	767.1	764.6	762.1	761.7
32.5°	752.6	751.9	751.1	750.3	749.5	748.0	745.8	743.5	741.2	739.0	738.4
35°	716.5	715.8	715.1	714.5	713.8	712.3	709.9	707.5	705.2	702.8	702.0
37.5°	678.9	678.1	677.3	676.4	675.6	674.0	671.8	669.6	667.3	665.1	663.9
40°	653.4	652.6	651.7	650.9	650.0	648.4	646.1	643.7	641.3	639.0	637.5
42.5°	626.1	625.4	624.6	623.9	623.2	621.7	619.3	617.0	614.6	612.2	610.9
45°	586.6	585.9	585.2	584.5	583.9	582.5	580.5	578.5	576.4	574.4	572.4
47.5°	544.0	544.0	544.1	544.1	544.1	542.9	540.5	538.1	535.7	533.2	531.2
50°	516.7	516.1	515.6	515.1	514.6	513.4	511.3	509.3	507.3	505.3	503.1
52.5°	488.7	488.3	488.0	487.6	487.2	485.9	483.8	481.6	479.5	477.3	475.4
55°	446.8	446.2	445.7	445.2	444.7	443.3	440.9	438.6	436.2	433.8	432.3
57.5°	402.5	402.3	402.0	401.7	401.5	400.3	398.3	396.3	394.3	392.4	390.4
60°	374.6	373.9	373.2	372.5	371.9	370.6	368.8	366.9	365.0	363.2	361.5
62.5°	345.4	344.9	344.3	343.8	343.2	342.2	340.6	339.0	337.4	335.8	334.0
65°	301.6	301.3	301.0	300.6	300.3	299.2	297.3	295.5	293.6	291.8	290.2
67.5°	259.2	258.5	257.8	257.1	256.4	255.4	254.0	252.6	251.2	249.8	248.5
70°	232.5	231.7	230.8	230.0	229.1	227.9	226.4	224.9	223.4	221.9	220.8
72.5°	203.3	202.7	202.2	201.6	201.0	200.2	199.3	198.3	197.3	196.3	195.2
75°	160.3	160.0	159.6	159.3	159.0	158.4	157.5	156.7	155.8	155.0	154.5
77.5°	120.7	120.5	120.4	120.2	120.1	119.8	119.3	118.9	118.4	117.9	117.6
80°	95.7	95.7	95.7	95.7	95.7	95.6	95.2	94.9	94.6	94.2	94.0
82.5°	73.9	73.6	73.3	73.0	72.8	72.6	72.5	72.5	72.4	72.3	72.0
85°	41.8	42.0	42.1	42.3	42.5	42.5	42.5	42.5	42.5	42.5	42.4
87.5°	16.5	16.6	16.7	16.8	17.0	17.1	17.0	17.0	16.9	16.9	17.0
90°	0.4	0.7	1.4	2.1	2.8	3.5	3.9	4.6	4.9	5.7	6.0
92.5°	4.3	5.2	8.2	12.6	18.7	29.0	48.3	80.6	115.8	113.9	92.2
95°	11.7	12.0	14.8	18.7	26.5	42.4	80.2	158.0	255.5	313.1	306.4
97.5°	19.4	19.8	21.8	25.7	32.7	44.1	69.1	126.1	228.2	334.4	387.7
100°	24.7	25.4	26.9	30.7	37.5	48.1	68.6	114.5	203.6	319.1	407.5
102.5°	30.7	31.1	32.2	36.4	42.6	52.9	71.1	109.7	184.9	292.3	395.6
105°	39.9	39.9	41.7	45.2	50.9	60.8	76.3	107.8	166.8	256.2	357.7
107.5°	49.0	49.7	51.4	54.3	60.2	69.1	84.1	111.0	159.2	231.4	318.9
110°	55.5	56.2	57.6	60.8	66.1	75.3	89.8	114.2	156.9	219.8	296.9



TEST NUMBER: P333168

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.0	62.7	63.8	67.0	72.3	81.2	95.1	118.1	156.9	213.0	280.5
115°	71.4	72.1	73.2	76.3	81.6	90.5	103.6	124.0	158.0	205.7	262.6
117.5°	79.9	80.9	82.1	85.2	91.3	99.8	112.2	130.8	160.3	202.1	251.9
120°	85.5	86.6	88.0	91.2	97.2	106.0	118.4	135.4	162.6	200.4	246.0
122.5°	91.5	92.2	93.4	96.6	103.1	112.0	124.3	140.4	164.5	199.0	240.9
125°	99.0	99.7	101.4	104.6	111.3	120.5	132.2	147.4	167.9	197.2	234.0
127.5°	104.8	105.9	108.1	112.2	119.3	128.5	139.7	153.7	171.6	196.4	227.6
130°	108.5	109.6	112.4	117.0	124.4	133.6	144.5	158.0	173.9	195.8	223.4
132.5°	111.3	112.7	116.1	121.2	128.9	138.1	149.1	161.7	176.4	195.8	220.0
135°	115.9	117.3	121.6	127.2	134.7	144.2	155.1	166.8	179.9	195.8	215.9
137.5°	121.7	122.8	126.7	132.4	139.7	149.5	159.5	170.6	183.1	196.2	212.3
140°	125.1	126.2	130.4	136.1	142.8	152.3	162.6	173.2	184.5	196.5	210.6
142.5°	129.1	129.8	133.8	139.5	145.9	154.9	164.5	174.6	185.3	196.8	209.2
145°	135.0	135.7	139.2	144.2	150.6	158.7	167.9	176.7	186.2	196.5	207.1
147.5°	141.2	141.6	144.7	149.3	154.8	161.9	170.0	178.0	186.6	195.6	204.9
150°	144.9	145.6	148.1	152.7	157.6	163.6	171.4	178.8	186.6	194.7	203.2
152.5°	148.9	149.3	151.5	155.5	160.2	165.6	172.8	179.4	186.3	193.6	201.2
155°	154.1	154.1	156.2	159.7	163.3	168.2	174.2	179.9	185.5	191.6	197.9
157.5°	158.8	158.7	160.4	163.4	166.5	170.3	175.4	180.2	184.6	189.4	194.8
160°	161.9	161.5	162.9	165.4	168.2	171.4	176.0	180.2	183.8	188.0	192.3
162.5°	164.4	164.1	165.5	167.7	169.9	172.5	176.6	180.0	182.9	186.3	190.0
165°	168.2	167.5	168.6	170.3	171.8	173.9	176.7	179.5	181.7	183.8	186.6
167.5°	170.8	170.4	171.1	172.0	173.0	174.4	176.7	178.7	179.7	181.3	183.3
170°	172.5	172.1	172.5	173.2	173.9	174.9	176.7	178.1	178.8	179.9	181.3
172.5°	173.6	173.0	173.3	174.0	174.4	174.9	176.4	177.6	177.7	178.2	179.3
175°	174.9	174.2	174.6	174.9	174.9	174.9	176.0	176.7	176.4	176.4	176.7
177.5°	175.6	175.0	175.0	175.3	175.0	175.0	175.6	175.9	175.3	175.3	175.6
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3



TEST NUMBER: P333168

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	957.6	959.0	960.3	960.9	960.8	960.6	960.5	960.4
5°	952.8	954.3	955.8	956.5	956.3	956.2	956.0	955.8
7.5°	943.1	944.6	946.1	946.8	946.6	946.4	946.3	946.1
10°	935.0	936.3	937.7	938.3	938.1	937.9	937.7	937.6
12.5°	924.1	925.2	926.2	926.8	926.7	926.7	926.7	926.6
15°	905.1	905.9	906.8	907.2	907.2	907.2	907.2	907.2
17.5°	883.0	884.0	885.1	885.2	884.3	883.5	882.7	881.8
20°	866.2	867.4	868.6	868.8	867.9	867.1	866.2	865.4
22.5°	847.2	848.0	848.8	848.9	848.3	847.7	847.1	846.6
25°	816.7	817.0	817.4	817.3	816.8	816.3	815.8	815.3
27.5°	784.7	784.8	784.8	784.6	784.1	783.6	783.1	782.6
30°	761.4	761.1	760.7	760.3	759.8	759.3	758.8	758.3
32.5°	737.8	737.1	736.5	735.8	734.9	734.0	733.0	732.1
35°	701.1	700.3	699.4	698.3	697.0	695.6	694.3	692.9
37.5°	662.6	661.4	660.1	659.1	658.3	657.6	656.8	656.0
40°	635.9	634.4	632.9	631.9	631.4	630.9	630.4	629.9
42.5°	609.5	608.1	606.7	605.6	604.8	604.1	603.3	602.5
45°	570.3	568.3	566.3	565.0	564.5	564.0	563.5	563.0
47.5°	529.1	527.0	525.0	523.4	522.2	521.0	519.8	518.6
50°	500.9	498.7	496.5	494.8	493.6	492.4	491.2	490.1
52.5°	473.4	471.5	469.6	468.0	466.7	465.3	464.0	462.7
55°	430.8	429.3	427.8	426.4	425.2	424.0	422.9	421.7
57.5°	388.4	386.5	384.5	383.2	382.6	381.9	381.3	380.7
60°	359.8	358.1	356.4	355.0	353.8	352.6	351.4	350.3
62.5°	332.2	330.4	328.5	327.2	326.3	325.3	324.4	323.5
65°	288.7	287.2	285.7	284.6	283.9	283.2	282.6	281.9
67.5°	247.3	246.0	244.7	243.8	243.4	243.0	242.6	242.2
70°	219.8	218.8	217.8	217.0	216.3	215.6	214.9	214.3
72.5°	194.0	192.9	191.7	190.8	190.1	189.5	188.8	188.1
75°	154.0	153.5	153.0	152.4	151.7	151.0	150.4	149.7
77.5°	117.3	117.0	116.7	116.3	115.8	115.4	114.9	114.4
80°	93.9	93.7	93.5	93.3	92.9	92.6	92.3	91.9
82.5°	71.7	71.4	71.1	70.9	70.9	70.8	70.7	70.7
85°	42.2	42.0	41.9	41.6	41.3	40.9	40.6	40.3
87.5°	17.1	17.1	17.2	17.2	17.0	16.7	16.5	16.2
90°	6.4	6.7	7.1	7.8	7.8	7.8	8.1	8.1
92.5°	62.6	45.4	34.2	29.0	24.5	23.6	23.1	22.5
95°	254.1	200.4	156.9	127.2	102.1	91.5	88.7	83.1
97.5°	378.4	340.8	298.4	257.1	235.3	215.5	205.3	200.7
100°	434.7	417.4	381.0	344.2	319.8	294.4	281.3	275.7
102.5°	453.6	464.3	446.9	422.0	395.9	377.8	363.6	359.4
105°	442.5	490.9	506.4	502.6	491.2	479.6	472.5	468.3
107.5°	402.6	467.2	507.1	525.6	531.3	531.3	528.9	526.1
110°	373.2	440.4	490.2	520.2	536.1	542.8	545.3	545.3



TEST NUMBER: P333168

CATALOG NUMBER: S125DIP-S610D365U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	350.0	413.8	464.2	499.6	522.8	534.4	540.5	543.1
115°	320.9	375.7	424.1	462.6	490.2	507.1	517.0	521.6
117.5°	302.1	349.3	391.0	426.4	453.9	471.5	481.3	484.1
120°	291.9	334.3	373.2	404.3	430.5	447.4	457.0	459.8
122.5°	284.3	323.6	358.2	387.3	410.7	426.2	435.8	438.3
125°	273.2	309.2	340.0	365.4	385.2	399.7	407.5	411.0
127.5°	261.9	295.5	324.2	348.0	366.0	378.8	386.1	387.7
130°	254.8	285.9	313.5	336.5	354.1	365.8	372.9	375.0
132.5°	247.7	276.9	301.9	324.0	341.7	353.3	359.8	362.2
135°	238.6	262.9	285.6	305.7	321.3	332.9	339.3	341.4
137.5°	230.8	250.5	269.3	286.4	300.3	310.9	316.8	319.1
140°	226.5	243.1	259.4	274.2	287.3	296.5	301.8	303.6
142.5°	222.9	236.9	250.9	263.8	274.9	282.7	287.7	289.2
145°	218.1	229.0	240.0	249.5	258.0	264.0	267.9	269.3
147.5°	213.5	222.4	230.9	238.1	244.8	249.6	251.8	252.5
150°	211.0	218.8	225.5	231.8	237.1	241.4	242.8	243.1
152.5°	208.2	215.1	221.2	226.2	230.6	234.0	235.4	235.8
155°	203.9	209.6	214.5	218.4	221.9	224.4	225.5	225.8
157.5°	199.7	204.3	208.2	211.2	214.0	216.0	217.0	216.9
160°	196.9	200.4	203.9	206.4	208.9	210.6	211.3	211.0
162.5°	193.7	197.0	200.0	202.2	204.1	205.5	205.7	205.6
165°	189.4	191.9	194.0	195.8	197.2	197.9	197.9	197.9
167.5°	185.3	187.0	188.6	189.9	190.6	191.2	190.9	190.8
170°	183.1	184.1	185.2	185.9	186.6	187.0	187.0	186.6
172.5°	180.5	181.6	182.4	182.8	182.9	183.6	183.0	182.6
175°	177.8	177.8	178.5	178.5	178.5	178.8	178.1	177.8
177.5°	175.9	176.1	176.1	176.1	175.9	176.1	175.3	175.3
180°	175.3	175.3	175.3	175.3	175.3	175.3	175.3	175.3

(END OF REPORT)