

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333179

Luminaire Tested: **S125DIP-S610D810U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333179
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5331.6 lumens
Efficiency: N/A
Efficacy: 138.8 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47					47			
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46					40				
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39					34				
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33					29				
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29					25				
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25					22				
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22					19				
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20					17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18					15				
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16					14				
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14					12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5780	5780	5780	5780
5°	6694	5800	5078	5800
10°	7788	5770	4450	5770
15°	8620	5727	4105	5727
20°	9649	5660	3827	5660
25°	11305	5585	3693	5585
30°	12210	5510	3575	5510
35°	10039	5370	3498	5370
40°	7136	5176	3414	5176
45°	5482	4913	3366	4913
50°	4679	4588	3359	4588
55°	4166	4269	3388	4269
60°	3759	3920	3475	3920
65°	3472	3570	3564	3570
70°	3155	3206	3616	3206
75°	2787	2825	3583	2825
80°	2347	2302	3277	2302
85°	1860	1660	2645	1660



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.2	1.6
10°-20°	256.5	4.8
20°-30°	416.6	7.8
30°-40°	508.1	9.5
40°-50°	462.2	8.7
50°-60°	368.2	6.9
60°-70°	256.4	4.8
70°-80°	136.8	2.6
80°-90°	36.7	0.7
90°-100°	67.3	1.3
100°-110°	198.7	3.7
110°-120°	336.6	6.3
120°-130°	443.0	8.3
130°-140°	496.4	9.3
140°-150°	486.5	9.1
150°-160°	408.6	7.7
160°-170°	271.6	5.1
170°-180°	95.1	1.8
0°-30°	759.2	14.2
0°-40°	1267.4	23.8
0°-60°	2097.8	39.3
0°-90°	2527.7	47.4
90°-120°	602.7	11.3
90°-150°	2028.6	38.0
90°-180°	2804.0	52.6
0°-180°	5331.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	1032	895	783	895	1032	104
15°	1289	857	614	857	1289	369
25°	1586	784	518	784	1586	725
35°	1273	681	444	681	1273	779
45°	600	538	368	538	600	480
55°	370	379	301	379	370	333
65°	227	234	233	234	227	225
75°	112	113	144	113	112	120
85°	25	22	36	22	25	29
90°	19	1	19	1	19	12
95°	67	51	67	51	67	68
105°	194	178	194	178	194	205
115°	340	337	340	337	340	336
125°	495	492	495	492	495	442
135°	642	640	642	640	642	495
145°	778	775	778	775	778	486
155°	887	887	887	887	887	408
165°	962	964	962	964	962	271
175°	999	1002	999	1002	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	946.7	945.4	944.2	941.8	943.6	938.4	936.0	931.8	926.6	924.8	922.6
5°	1032.5	1034.4	1036.3	1028.3	1029.1	1023.8	1011.6	1001.7	993.8	983.5	976.3
7.5°	1135.8	1131.3	1131.0	1125.8	1116.9	1109.8	1097.0	1080.7	1065.0	1047.1	1032.3
10°	1187.5	1187.9	1184.5	1178.4	1168.9	1162.0	1145.3	1129.4	1110.0	1087.2	1070.9
12.5°	1226.4	1228.0	1223.7	1215.5	1210.8	1195.5	1182.4	1163.4	1140.4	1122.2	1097.3
15°	1289.3	1285.1	1282.1	1271.8	1263.8	1247.9	1227.0	1207.2	1182.2	1159.0	1135.8
17.5°	1349.9	1353.3	1347.6	1338.2	1313.5	1294.8	1266.8	1239.8	1208.5	1177.5	1149.8
20°	1404.0	1407.1	1398.3	1382.0	1352.4	1333.7	1296.9	1261.9	1225.9	1186.0	1155.6
22.5°	1471.5	1469.1	1457.3	1432.4	1406.8	1372.3	1332.5	1289.9	1244.7	1199.6	1159.2
25°	1586.4	1570.4	1563.2	1532.4	1498.6	1448.1	1393.4	1331.1	1274.9	1215.2	1163.6
27.5°	1650.0	1645.0	1637.0	1615.5	1580.0	1526.0	1461.5	1385.6	1306.2	1231.0	1163.3
30°	1637.3	1638.0	1638.8	1631.9	1609.2	1568.5	1504.3	1422.6	1328.4	1243.7	1165.5
32.5°	1524.2	1538.0	1551.3	1566.9	1573.3	1565.5	1525.3	1451.5	1354.6	1258.3	1164.2
35°	1273.3	1277.5	1320.5	1363.0	1420.7	1465.6	1495.6	1462.9	1381.2	1270.7	1162.8
37.5°	992.8	1013.4	1043.1	1091.2	1174.5	1249.1	1345.1	1389.2	1362.8	1274.7	1160.1
40°	846.4	865.4	884.7	933.7	1004.0	1094.4	1203.4	1296.5	1318.2	1261.9	1151.0
42.5°	733.3	748.4	769.9	806.7	865.4	945.5	1049.7	1171.3	1246.1	1224.9	1131.9
45°	600.2	609.7	626.4	655.7	698.2	760.9	852.8	985.8	1101.6	1140.0	1086.4
47.5°	513.7	513.7	526.7	546.9	577.6	630.8	698.8	803.0	926.7	1018.3	1014.0
50°	465.7	463.8	474.1	491.6	515.9	551.2	616.2	699.4	818.3	922.0	950.8
52.5°	424.4	424.6	430.9	443.8	464.2	494.4	542.9	617.9	719.5	825.9	880.3
55°	370.0	368.5	375.7	384.4	399.3	419.0	454.0	511.3	593.7	698.6	769.2
57.5°	320.2	324.3	327.2	333.3	345.6	358.8	388.3	430.4	495.8	585.8	660.5
60°	291.0	295.2	297.4	303.5	313.4	324.8	347.6	381.8	436.9	514.4	588.4
62.5°	264.8	268.1	268.9	274.3	282.4	293.5	311.4	340.1	383.7	451.4	524.0
65°	227.2	227.2	228.7	234.4	238.2	248.1	261.7	282.6	317.6	370.4	432.3
67.5°	190.8	192.7	192.3	194.8	198.3	206.0	215.8	233.0	258.9	297.4	347.0
70°	167.1	168.7	168.3	170.2	174.0	178.9	186.9	203.2	221.8	254.9	297.4
72.5°	145.9	146.5	145.5	148.0	150.3	154.6	163.5	172.2	189.6	217.5	252.5
75°	111.7	112.4	113.2	114.7	117.0	119.3	123.8	132.6	144.0	164.9	187.3
77.5°	83.7	82.3	84.1	83.9	85.2	86.9	90.9	95.6	104.9	118.1	135.5
80°	63.1	63.4	63.4	63.8	65.7	66.9	70.3	73.7	80.9	90.8	102.9
82.5°	46.0	47.0	46.4	47.1	48.7	49.5	51.4	54.2	58.4	66.2	75.0
85°	25.1	23.2	23.9	24.7	24.7	25.1	26.6	27.7	30.0	33.0	36.5
87.5°	11.0	11.6	11.8	11.6	11.8	11.7	12.7	12.6	13.3	14.1	15.0
90°	18.8	18.2	17.7	17.2	16.7	16.0	15.1	14.2	13.4	12.5	11.3
92.5°	36.9	36.5	36.1	35.8	35.4	34.6	33.5	32.3	31.2	30.0	28.5
95°	67.2	66.9	66.6	66.2	65.9	65.1	63.9	62.6	61.4	60.2	58.5
97.5°	102.0	101.8	101.5	101.3	101.1	100.5	99.3	98.2	97.0	95.9	93.5
100°	128.2	127.9	127.5	127.2	126.9	125.9	124.3	122.8	121.2	119.6	117.4
102.5°	154.5	154.0	153.5	153.1	152.6	151.5	149.8	148.1	146.4	144.7	143.5
105°	193.9	193.4	192.9	192.4	191.8	191.1	190.0	189.0	187.9	186.9	185.8
107.5°	234.3	234.3	234.3	234.4	234.4	234.2	233.6	233.1	232.6	232.1	231.3
110°	264.3	264.5	264.6	264.8	265.0	264.8	264.3	263.8	263.3	262.7	262.2



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	293.7	294.0	294.3	294.6	295.0	295.0	294.7	294.5	294.3	294.0	293.4
115°	340.2	340.3	340.5	340.7	340.8	341.0	341.2	341.4	341.5	341.7	341.4
117.5°	385.5	386.2	386.9	387.6	388.3	388.6	388.4	388.3	388.1	388.0	387.7
120°	416.8	417.5	418.2	418.9	419.6	419.9	419.9	419.9	419.9	419.9	419.7
122.5°	448.1	448.6	449.2	449.7	450.3	450.6	450.8	450.9	451.0	451.2	450.7
125°	495.0	495.2	495.3	495.5	495.7	495.9	496.3	496.6	497.0	497.3	497.1
127.5°	540.0	540.4	540.7	541.1	541.4	541.7	541.8	542.0	542.2	542.4	542.2
130°	570.0	570.4	570.7	571.1	571.4	571.7	571.9	572.0	572.2	572.4	572.0
132.5°	598.2	598.7	599.2	599.7	600.1	600.5	600.6	600.8	601.0	601.2	601.2
135°	642.0	642.7	643.4	644.1	644.8	645.1	645.1	645.1	645.1	645.1	644.9
137.5°	684.8	685.7	686.6	687.4	688.3	688.6	688.4	688.2	688.0	687.8	687.4
140°	712.4	713.2	714.1	715.0	715.8	716.1	715.7	715.4	715.1	714.7	714.2
142.5°	738.6	739.5	740.4	741.2	742.1	742.4	742.2	742.0	741.8	741.6	740.9
145°	778.0	778.6	779.1	779.6	780.1	780.4	780.4	780.4	780.4	780.4	779.9
147.5°	811.7	812.9	814.0	815.2	816.4	816.8	816.4	815.9	815.5	815.1	814.7
150°	836.7	837.0	837.4	837.7	838.1	838.3	838.3	838.3	838.3	838.3	837.6
152.5°	857.3	858.0	858.6	859.2	859.8	859.9	859.5	859.1	858.7	858.3	858.0
155°	886.7	887.6	888.5	889.3	890.2	890.3	889.6	888.9	888.2	887.5	887.3
157.5°	911.3	912.4	913.6	914.7	915.9	916.1	915.4	914.7	914.0	913.3	913.1
160°	928.2	929.0	929.9	930.8	931.7	931.7	931.0	930.4	929.7	929.0	928.8
162.5°	942.6	943.6	944.6	945.6	946.6	946.7	945.9	945.0	944.2	943.4	943.3
165°	961.8	962.8	963.9	964.9	966.0	966.1	965.5	964.8	964.1	963.4	963.2
167.5°	977.1	978.2	979.3	980.4	981.4	981.5	980.4	979.4	978.3	977.3	977.3
170°	985.3	986.5	987.7	988.9	990.1	990.2	989.2	988.1	987.1	986.0	986.0
172.5°	992.1	993.2	994.3	995.4	996.5	996.5	995.4	994.4	993.3	992.3	992.3
175°	998.6	999.8	1001.0	1002.2	1003.4	1003.5	1002.5	1001.4	1000.4	999.3	999.3
177.5°	1002.3	1003.3	1004.3	1005.2	1006.2	1006.3	1005.4	1004.6	1003.8	1002.9	1003.1
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	920.8	918.7	916.3	912.0	906.8	904.1	899.9	897.1	891.6	887.1	882.2
5°	967.5	957.7	948.6	936.8	923.9	915.5	905.6	894.6	883.2	871.4	858.5
7.5°	1015.9	998.5	979.5	959.0	939.1	920.7	903.1	885.9	869.8	850.3	833.8
10°	1048.5	1026.4	1002.9	975.1	948.2	924.6	900.7	879.8	858.5	835.7	815.6
12.5°	1081.0	1051.6	1018.4	987.9	955.5	927.1	898.9	872.2	845.5	820.2	796.8
15°	1103.9	1078.1	1047.3	1004.0	967.5	928.4	891.2	856.6	824.3	796.2	766.6
17.5°	1119.0	1085.8	1052.7	1011.2	963.4	919.6	877.4	837.9	801.5	765.8	737.3
20°	1121.8	1087.6	1053.0	1012.4	963.4	913.2	871.1	823.6	784.4	747.6	712.6
22.5°	1120.9	1082.1	1044.5	1002.6	954.9	908.7	857.7	809.3	766.8	730.6	694.1
25°	1112.3	1070.9	1023.8	981.6	934.5	885.5	833.8	783.7	740.4	699.0	662.9
27.5°	1105.1	1051.4	998.1	948.9	903.4	858.5	809.1	757.7	709.7	667.7	633.7
30°	1096.3	1037.4	977.4	926.1	879.4	835.7	789.0	738.9	688.7	647.7	611.2
32.5°	1088.4	1019.8	956.5	900.6	851.2	808.7	765.6	717.9	668.7	627.0	590.6
35°	1073.2	993.8	921.2	858.1	805.3	761.7	725.6	681.1	635.9	595.6	560.7
37.5°	1053.8	959.6	881.7	815.6	757.7	711.7	678.1	644.0	600.6	561.8	530.2
40°	1038.6	935.3	852.8	785.2	725.2	677.3	646.2	613.9	577.8	541.7	508.3
42.5°	1019.4	913.4	823.6	750.9	691.5	644.8	612.1	584.7	552.9	519.2	488.2
45°	984.3	873.7	776.5	698.2	638.2	592.2	558.4	537.9	514.0	482.1	455.9
47.5°	932.5	826.1	725.5	644.7	582.8	540.2	508.5	488.8	472.0	448.3	424.5
50°	886.6	790.5	688.7	608.6	546.6	503.7	474.5	456.6	442.2	423.9	403.8
52.5°	835.3	745.8	652.6	573.3	512.0	469.7	441.0	425.3	413.3	400.2	380.4
55°	753.7	677.7	591.1	515.9	459.3	417.9	392.8	379.1	369.2	359.4	347.2
57.5°	663.8	604.4	527.6	458.9	406.8	369.1	345.7	332.4	324.7	319.6	312.5
60°	600.6	549.7	483.6	420.9	370.0	336.6	313.8	303.5	297.1	292.9	287.6
62.5°	541.9	500.1	438.9	381.7	337.2	305.6	285.2	275.3	269.1	267.1	262.6
65°	455.5	423.2	372.7	325.2	287.2	260.2	243.1	233.6	229.8	227.5	227.9
67.5°	370.3	350.6	310.1	269.6	239.2	216.6	202.9	195.6	193.7	190.7	190.6
70°	318.3	303.5	269.3	234.0	207.0	189.6	177.4	169.8	167.9	166.4	166.0
72.5°	272.4	259.5	229.8	201.5	177.3	161.9	151.9	147.3	144.2	143.3	143.2
75°	204.8	197.5	174.0	151.6	134.9	124.2	117.4	113.2	110.9	110.5	110.9
77.5°	145.6	139.3	124.3	108.4	97.9	89.8	84.0	82.6	80.0	80.1	79.7
80°	109.4	105.2	95.7	83.2	74.5	67.6	64.6	61.9	61.2	60.0	61.2
82.5°	79.3	74.8	68.4	60.4	53.2	49.1	46.0	45.2	44.7	44.2	44.4
85°	39.1	39.5	35.7	29.6	26.6	24.3	22.4	22.4	22.0	21.7	22.0
87.5°	15.4	14.5	13.1	11.9	10.1	8.9	8.3	8.4	7.7	7.7	8.3
90°	10.1	8.9	7.6	6.3	5.0	3.6	2.2	0.8	2.2	3.6	5.0
92.5°	27.0	25.5	24.0	22.8	21.8	20.9	19.9	18.9	19.9	20.9	21.8
95°	56.7	55.0	53.3	52.2	51.9	51.5	51.2	50.8	51.2	51.5	51.9
97.5°	91.1	88.7	86.3	85.0	84.9	84.7	84.6	84.5	84.6	84.7	84.9
100°	115.1	112.9	110.6	109.5	109.5	109.5	109.5	109.5	109.5	109.5	109.5
102.5°	142.4	141.2	140.1	139.2	138.5	137.8	137.1	136.4	137.1	137.8	138.5
105°	184.8	183.8	182.7	181.8	180.9	180.0	179.2	178.3	179.2	180.0	180.9
107.5°	230.5	229.7	228.9	228.1	227.2	226.3	225.4	224.6	225.4	226.3	227.2
110°	261.7	261.2	260.7	260.0	259.1	258.2	257.4	256.5	257.4	258.2	259.1



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	292.7	292.0	291.4	290.8	290.4	289.9	289.5	289.0	289.5	289.9	290.4
115°	341.0	340.7	340.3	339.8	339.1	338.4	337.7	337.0	337.7	338.4	339.1
117.5°	387.4	387.1	386.8	386.4	386.1	385.8	385.5	385.2	385.5	385.8	386.1
120°	419.6	419.4	419.2	418.7	417.8	417.0	416.1	415.2	416.1	417.0	417.8
122.5°	450.3	449.8	449.4	449.0	448.7	448.4	448.1	447.7	448.1	448.4	448.7
125°	497.0	496.8	496.6	496.0	495.0	493.9	492.9	491.8	492.9	493.9	495.0
127.5°	541.9	541.7	541.5	541.1	540.5	539.9	539.4	538.8	539.4	539.9	540.5
130°	571.7	571.3	571.0	570.4	569.5	568.7	567.8	566.9	567.8	568.7	569.5
132.5°	601.3	601.4	601.4	600.8	599.3	597.9	596.5	595.1	596.5	597.9	599.3
135°	644.8	644.6	644.4	643.8	642.8	641.7	640.7	639.6	640.7	641.7	642.8
137.5°	687.0	686.7	686.3	685.6	684.6	683.6	682.6	681.6	682.6	683.6	684.6
140°	713.7	713.1	712.6	711.9	711.1	710.2	709.3	708.5	709.3	710.2	711.1
142.5°	740.3	739.6	739.0	738.3	737.5	736.8	736.1	735.4	736.1	736.8	737.5
145°	779.3	778.8	778.3	777.7	777.0	776.3	775.6	774.9	775.6	776.3	777.0
147.5°	814.3	813.9	813.4	813.0	812.7	812.3	811.9	811.5	811.9	812.3	812.7
150°	836.9	836.2	835.5	835.2	835.4	835.6	835.7	835.9	835.7	835.6	835.4
152.5°	857.7	857.4	857.2	856.9	856.7	856.4	856.2	855.9	856.2	856.4	856.7
155°	887.2	887.0	886.8	886.7	886.7	886.7	886.7	886.7	886.7	886.7	886.7
157.5°	913.0	912.8	912.6	912.7	913.1	913.5	913.9	914.3	913.9	913.5	913.1
160°	928.6	928.4	928.3	928.4	929.0	929.5	930.0	930.5	930.0	929.5	929.0
162.5°	943.3	943.2	943.2	943.4	943.8	944.1	944.5	944.9	944.5	944.1	943.8
165°	963.0	962.8	962.7	962.8	963.1	963.5	963.8	964.2	963.8	963.5	963.1
167.5°	977.3	977.3	977.3	977.6	978.3	979.0	979.7	980.4	979.7	979.0	978.3
170°	986.0	986.0	986.0	986.4	987.1	987.8	988.5	989.2	988.5	987.8	987.1
172.5°	992.3	992.3	992.3	992.6	993.3	994.0	994.7	995.4	994.7	994.0	993.3
175°	999.3	999.3	999.3	999.7	1000.4	1001.1	1001.8	1002.5	1001.8	1001.1	1000.4
177.5°	1003.2	1003.4	1003.5	1003.8	1004.4	1005.0	1005.5	1006.1	1005.5	1005.0	1004.4
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	879.5	876.1	873.4	867.3	864.0	859.4	855.8	859.7	855.5	857.3	854.6
5°	852.1	841.4	833.8	822.8	813.3	804.6	798.1	797.0	793.9	792.4	787.9
7.5°	819.1	805.8	792.7	778.3	766.1	753.8	745.8	739.3	735.0	729.3	725.4
10°	799.6	781.8	766.6	749.1	733.9	720.6	710.0	704.7	699.7	692.5	689.9
12.5°	775.6	757.2	738.6	719.9	705.4	690.5	681.4	673.4	670.0	661.8	661.0
15°	746.8	719.1	700.9	681.9	661.7	649.6	642.0	633.3	629.5	623.8	619.6
17.5°	712.5	687.7	664.9	645.3	628.0	617.8	608.3	602.3	595.8	592.1	585.2
20°	687.6	664.0	641.2	620.3	607.0	595.3	587.7	582.0	575.1	573.2	566.4
22.5°	666.6	640.6	618.7	601.2	586.7	573.4	565.2	561.3	556.6	550.7	549.4
25°	632.5	605.5	586.9	569.4	556.5	544.4	538.7	533.7	529.2	525.0	523.5
27.5°	603.0	578.9	556.8	541.0	529.8	518.7	513.7	507.7	504.3	501.0	496.9
30°	582.4	557.7	538.3	523.1	510.9	501.1	495.7	491.6	488.5	485.5	483.2
32.5°	561.1	538.2	519.4	504.6	492.4	485.0	480.2	477.3	473.9	470.3	467.4
35°	533.0	507.9	489.7	476.7	467.2	461.5	456.2	453.6	449.8	449.8	446.7
37.5°	501.3	479.6	463.5	451.7	443.2	438.1	432.4	430.6	428.1	426.5	425.5
40°	482.4	462.3	447.1	435.3	426.2	422.0	417.5	414.4	412.9	411.0	410.3
42.5°	463.0	443.8	429.2	418.3	410.4	406.8	402.6	400.5	397.4	394.9	394.5
45°	433.4	414.8	401.5	392.8	386.0	381.8	379.1	374.6	373.0	370.0	369.6
47.5°	405.4	387.5	374.5	367.3	361.3	357.9	353.7	349.2	347.4	345.9	345.8
50°	384.4	368.1	355.9	349.1	343.4	338.5	334.3	331.3	330.1	330.1	330.9
52.5°	363.2	349.3	338.9	330.6	325.2	319.9	316.1	314.2	312.5	314.3	315.7
55°	332.0	318.0	310.4	302.4	297.1	291.0	289.1	288.3	287.2	290.2	291.7
57.5°	299.0	289.2	280.3	272.4	267.6	264.1	261.5	261.1	263.2	264.6	269.6
60°	278.1	266.7	258.7	252.6	246.9	244.6	243.9	243.1	244.6	248.8	255.3
62.5°	255.0	245.7	237.1	232.6	228.4	224.6	224.4	224.9	227.9	232.7	239.2
65°	221.1	213.1	207.4	202.1	198.7	196.4	197.2	198.7	202.1	208.6	215.8
67.5°	186.7	181.2	176.1	171.8	168.5	168.5	169.3	171.6	175.6	183.0	189.6
70°	164.5	158.4	154.2	152.3	149.7	148.2	150.4	154.2	157.6	164.5	170.2
72.5°	142.3	137.1	133.9	132.6	131.4	130.2	131.0	135.1	139.7	146.6	153.2
75°	109.4	107.5	105.2	103.7	102.6	103.3	104.1	107.9	111.7	118.9	126.5
77.5°	79.9	77.9	76.5	76.1	75.5	75.9	78.0	80.8	84.6	89.8	95.6
80°	60.4	59.6	58.9	58.5	58.5	58.9	61.9	63.8	67.2	72.2	76.7
82.5°	44.0	43.5	43.4	43.3	43.6	43.7	45.5	48.0	50.8	54.6	58.5
85°	23.2	22.4	23.6	23.9	23.2	24.3	25.1	26.6	27.7	29.6	31.5
87.5°	8.9	9.7	9.7	10.2	10.5	11.3	11.2	12.6	13.4	14.1	14.0
90°	6.3	7.6	8.9	10.1	11.3	12.5	13.4	14.2	15.1	16.0	16.7
92.5°	22.8	24.0	25.5	27.0	28.5	30.0	31.2	32.3	33.5	34.6	35.4
95°	52.2	53.3	55.0	56.7	58.5	60.2	61.4	62.6	63.9	65.1	65.9
97.5°	85.0	86.3	88.7	91.1	93.5	95.9	97.0	98.2	99.3	100.5	101.1
100°	109.5	110.6	112.9	115.1	117.4	119.6	121.2	122.8	124.3	125.9	126.9
102.5°	139.2	140.1	141.2	142.4	143.5	144.7	146.4	148.1	149.8	151.5	152.6
105°	181.8	182.7	183.8	184.8	185.8	186.9	187.9	189.0	190.0	191.1	191.8
107.5°	228.1	228.9	229.7	230.5	231.3	232.1	232.6	233.1	233.6	234.2	234.4
110°	260.0	260.7	261.2	261.7	262.2	262.7	263.3	263.8	264.3	264.8	265.0



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	290.8	291.4	292.0	292.7	293.4	294.0	294.3	294.5	294.7	295.0	295.0
115°	339.8	340.3	340.7	341.0	341.4	341.7	341.5	341.4	341.2	341.0	340.8
117.5°	386.4	386.8	387.1	387.4	387.7	388.0	388.1	388.3	388.4	388.6	388.3
120°	418.7	419.2	419.4	419.6	419.7	419.9	419.9	419.9	419.9	419.9	419.6
122.5°	449.0	449.4	449.8	450.3	450.7	451.2	451.0	450.9	450.8	450.6	450.3
125°	496.0	496.6	496.8	497.0	497.1	497.3	497.0	496.6	496.3	495.9	495.7
127.5°	541.1	541.5	541.7	541.9	542.2	542.4	542.2	542.0	541.8	541.7	541.4
130°	570.4	571.0	571.3	571.7	572.0	572.4	572.2	572.0	571.9	571.7	571.4
132.5°	600.8	601.4	601.4	601.3	601.2	601.2	601.0	600.8	600.6	600.5	600.1
135°	643.8	644.4	644.6	644.8	644.9	645.1	645.1	645.1	645.1	645.1	644.8
137.5°	685.6	686.3	686.7	687.0	687.4	687.8	688.0	688.2	688.4	688.6	688.3
140°	711.9	712.6	713.1	713.7	714.2	714.7	715.1	715.4	715.7	716.1	715.8
142.5°	738.3	739.0	739.6	740.3	740.9	741.6	741.8	742.0	742.2	742.4	742.1
145°	777.7	778.3	778.8	779.3	779.9	780.4	780.4	780.4	780.4	780.4	780.1
147.5°	813.0	813.4	813.9	814.3	814.7	815.1	815.5	815.9	816.4	816.8	816.4
150°	835.2	835.5	836.2	836.9	837.6	838.3	838.3	838.3	838.3	838.3	838.1
152.5°	856.9	857.2	857.4	857.7	858.0	858.3	858.7	859.1	859.5	859.9	859.8
155°	886.7	886.8	887.0	887.2	887.3	887.5	888.2	888.9	889.6	890.3	890.2
157.5°	912.7	912.6	912.8	913.0	913.1	913.3	914.0	914.7	915.4	916.1	915.9
160°	928.4	928.3	928.4	928.6	928.8	929.0	929.7	930.4	931.0	931.7	931.7
162.5°	943.4	943.2	943.2	943.3	943.3	943.4	944.2	945.0	945.9	946.7	946.6
165°	962.8	962.7	962.8	963.0	963.2	963.4	964.1	964.8	965.5	966.1	966.0
167.5°	977.6	977.3	977.3	977.3	977.3	977.3	978.3	979.4	980.4	981.5	981.4
170°	986.4	986.0	986.0	986.0	986.0	986.0	987.1	988.1	989.2	990.2	990.1
172.5°	992.6	992.3	992.3	992.3	992.3	992.3	993.3	994.4	995.4	996.5	996.5
175°	999.7	999.3	999.3	999.3	999.3	999.3	1000.4	1001.4	1002.5	1003.5	1003.4
177.5°	1003.8	1003.5	1003.4	1003.2	1003.1	1002.9	1003.8	1004.6	1005.4	1006.3	1006.2
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	852.7	854.9	853.1	855.5	853.1	854.9	852.7	854.6	857.3	855.5	859.7
5°	786.0	782.5	784.8	783.3	784.8	782.5	786.0	787.9	792.4	793.9	797.0
7.5°	724.3	721.0	717.3	715.5	717.3	721.0	724.3	725.4	729.3	735.0	739.3
10°	685.7	681.5	681.1	678.5	681.1	681.5	685.7	689.9	692.5	699.7	704.7
12.5°	657.4	653.5	649.2	648.1	649.2	653.5	657.4	661.0	661.8	670.0	673.4
15°	617.3	614.3	611.6	613.9	611.6	614.3	617.3	619.6	623.8	629.5	633.3
17.5°	583.9	581.4	581.0	578.2	581.0	581.4	583.9	585.2	592.1	595.8	602.3
20°	563.0	561.1	561.8	556.9	561.8	561.1	563.0	566.4	573.2	575.1	582.0
22.5°	546.3	542.5	542.1	541.1	542.1	542.5	546.3	549.4	550.7	556.6	561.3
25°	520.1	518.2	516.3	518.2	516.3	518.2	520.1	523.5	525.0	529.2	533.7
27.5°	497.2	494.9	494.4	494.6	494.4	494.9	497.2	496.9	501.0	504.3	507.7
30°	483.2	479.4	479.8	479.4	479.8	479.4	483.2	483.2	485.5	488.5	491.6
32.5°	468.0	465.4	464.9	464.2	464.9	465.4	468.0	467.4	470.3	473.9	477.3
35°	445.6	445.6	443.7	443.7	443.7	445.6	445.6	446.7	449.8	449.8	453.6
37.5°	424.5	424.2	423.0	423.2	423.0	424.2	424.5	425.5	426.5	428.1	430.6
40°	408.7	408.4	407.2	404.9	407.2	408.4	408.7	410.3	411.0	412.9	414.4
42.5°	393.6	392.3	391.7	391.0	391.7	392.3	393.6	394.5	394.9	397.4	400.5
45°	369.6	369.6	368.9	368.5	368.9	369.6	369.6	369.6	370.0	373.0	374.6
47.5°	346.4	347.1	348.5	348.3	348.5	347.1	346.4	345.8	345.9	347.4	349.2
50°	332.4	332.8	333.9	334.3	333.9	332.8	332.4	330.9	330.1	330.1	331.3
52.5°	316.9	319.1	320.5	320.3	320.5	319.1	316.9	315.7	314.3	312.5	314.2
55°	295.2	297.8	300.5	300.9	300.5	297.8	295.2	291.7	290.2	287.2	288.3
57.5°	273.7	277.4	280.2	281.1	280.2	277.4	273.7	269.6	264.6	263.2	261.1
60°	259.1	264.0	267.4	269.0	267.4	264.0	259.1	255.3	248.8	244.6	243.1
62.5°	245.1	250.6	254.1	254.4	254.1	250.6	245.1	239.2	232.7	227.9	224.9
65°	222.2	227.9	231.0	233.2	231.0	227.9	222.2	215.8	208.6	202.1	198.7
67.5°	197.6	203.3	206.7	208.5	206.7	203.3	197.6	189.6	183.0	175.6	171.6
70°	179.7	185.4	189.9	191.5	189.9	185.4	179.7	170.2	164.5	157.6	154.2
72.5°	162.1	167.1	170.8	172.6	170.8	167.1	162.1	153.2	146.6	139.7	135.1
75°	131.4	138.3	141.7	143.6	141.7	138.3	131.4	126.5	118.9	111.7	107.9
77.5°	101.4	107.6	109.6	110.6	109.6	107.6	101.4	95.6	89.8	84.6	80.8
80°	81.3	85.1	87.8	88.1	87.8	85.1	81.3	76.7	72.2	67.2	63.8
82.5°	62.5	65.6	66.5	67.5	66.5	65.6	62.5	58.5	54.6	50.8	48.0
85°	34.2	35.7	36.1	35.7	36.1	35.7	34.2	31.5	29.6	27.7	26.6
87.5°	14.7	14.5	14.6	15.3	14.6	14.5	14.7	14.0	14.1	13.4	12.6
90°	17.2	17.7	18.2	18.8	18.2	17.7	17.2	16.7	16.0	15.1	14.2
92.5°	35.8	36.1	36.5	36.9	36.5	36.1	35.8	35.4	34.6	33.5	32.3
95°	66.2	66.6	66.9	67.2	66.9	66.6	66.2	65.9	65.1	63.9	62.6
97.5°	101.3	101.5	101.8	102.0	101.8	101.5	101.3	101.1	100.5	99.3	98.2
100°	127.2	127.5	127.9	128.2	127.9	127.5	127.2	126.9	125.9	124.3	122.8
102.5°	153.1	153.5	154.0	154.5	154.0	153.5	153.1	152.6	151.5	149.8	148.1
105°	192.4	192.9	193.4	193.9	193.4	192.9	192.4	191.8	191.1	190.0	189.0
107.5°	234.4	234.3	234.3	234.3	234.3	234.3	234.4	234.4	234.2	233.6	233.1
110°	264.8	264.6	264.5	264.3	264.5	264.6	264.8	265.0	264.8	264.3	263.8



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	294.6	294.3	294.0	293.7	294.0	294.3	294.6	295.0	295.0	294.7	294.5
115°	340.7	340.5	340.3	340.2	340.3	340.5	340.7	340.8	341.0	341.2	341.4
117.5°	387.6	386.9	386.2	385.5	386.2	386.9	387.6	388.3	388.6	388.4	388.3
120°	418.9	418.2	417.5	416.8	417.5	418.2	418.9	419.6	419.9	419.9	419.9
122.5°	449.7	449.2	448.6	448.1	448.6	449.2	449.7	450.3	450.6	450.8	450.9
125°	495.5	495.3	495.2	495.0	495.2	495.3	495.5	495.7	495.9	496.3	496.6
127.5°	541.1	540.7	540.4	540.0	540.4	540.7	541.1	541.4	541.7	541.8	542.0
130°	571.1	570.7	570.4	570.0	570.4	570.7	571.1	571.4	571.7	571.9	572.0
132.5°	599.7	599.2	598.7	598.2	598.7	599.2	599.7	600.1	600.5	600.6	600.8
135°	644.1	643.4	642.7	642.0	642.7	643.4	644.1	644.8	645.1	645.1	645.1
137.5°	687.4	686.6	685.7	684.8	685.7	686.6	687.4	688.3	688.6	688.4	688.2
140°	715.0	714.1	713.2	712.4	713.2	714.1	715.0	715.8	716.1	715.7	715.4
142.5°	741.2	740.4	739.5	738.6	739.5	740.4	741.2	742.1	742.4	742.2	742.0
145°	779.6	779.1	778.6	778.0	778.6	779.1	779.6	780.1	780.4	780.4	780.4
147.5°	815.2	814.0	812.9	811.7	812.9	814.0	815.2	816.4	816.8	816.4	815.9
150°	837.7	837.4	837.0	836.7	837.0	837.4	837.7	838.1	838.3	838.3	838.3
152.5°	859.2	858.6	858.0	857.3	858.0	858.6	859.2	859.8	859.9	859.5	859.1
155°	889.3	888.5	887.6	886.7	887.6	888.5	889.3	890.2	890.3	889.6	888.9
157.5°	914.7	913.6	912.4	911.3	912.4	913.6	914.7	915.9	916.1	915.4	914.7
160°	930.8	929.9	929.0	928.2	929.0	929.9	930.8	931.7	931.7	931.0	930.4
162.5°	945.6	944.6	943.6	942.6	943.6	944.6	945.6	946.6	946.7	945.9	945.0
165°	964.9	963.9	962.8	961.8	962.8	963.9	964.9	966.0	966.1	965.5	964.8
167.5°	980.4	979.3	978.2	977.1	978.2	979.3	980.4	981.4	981.5	980.4	979.4
170°	988.9	987.7	986.5	985.3	986.5	987.7	988.9	990.1	990.2	989.2	988.1
172.5°	995.4	994.3	993.2	992.1	993.2	994.3	995.4	996.5	996.5	995.4	994.4
175°	1002.2	1001.0	999.8	998.6	999.8	1001.0	1002.2	1003.4	1003.5	1002.5	1001.4
177.5°	1005.2	1004.3	1003.3	1002.3	1003.3	1004.3	1005.2	1006.2	1006.3	1005.4	1004.6
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	855.8	859.4	864.0	867.3	873.4	876.1	879.5	882.2	887.1	891.6	897.1
5°	798.1	804.6	813.3	822.8	833.8	841.4	852.1	858.5	871.4	883.2	894.6
7.5°	745.8	753.8	766.1	778.3	792.7	805.8	819.1	833.8	850.3	869.8	885.9
10°	710.0	720.6	733.9	749.1	766.6	781.8	799.6	815.6	835.7	858.5	879.8
12.5°	681.4	690.5	705.4	719.9	738.6	757.2	775.6	796.8	820.2	845.5	872.2
15°	642.0	649.6	661.7	681.9	700.9	719.1	746.8	766.6	796.2	824.3	856.6
17.5°	608.3	617.8	628.0	645.3	664.9	687.7	712.5	737.3	765.8	801.5	837.9
20°	587.7	595.3	607.0	620.3	641.2	664.0	687.6	712.6	747.6	784.4	823.6
22.5°	565.2	573.4	586.7	601.2	618.7	640.6	666.6	694.1	730.6	766.8	809.3
25°	538.7	544.4	556.5	569.4	586.9	605.5	632.5	662.9	699.0	740.4	783.7
27.5°	513.7	518.7	529.8	541.0	556.8	578.9	603.0	633.7	667.7	709.7	757.7
30°	495.7	501.1	510.9	523.1	538.3	557.7	582.4	611.2	647.7	688.7	738.9
32.5°	480.2	485.0	492.4	504.6	519.4	538.2	561.1	590.6	627.0	668.7	717.9
35°	456.2	461.5	467.2	476.7	489.7	507.9	533.0	560.7	595.6	635.9	681.1
37.5°	432.4	438.1	443.2	451.7	463.5	479.6	501.3	530.2	561.8	600.6	644.0
40°	417.5	422.0	426.2	435.3	447.1	462.3	482.4	508.3	541.7	577.8	613.9
42.5°	402.6	406.8	410.4	418.3	429.2	443.8	463.0	488.2	519.2	552.9	584.7
45°	379.1	381.8	386.0	392.8	401.5	414.8	433.4	455.9	482.1	514.0	537.9
47.5°	353.7	357.9	361.3	367.3	374.5	387.5	405.4	424.5	448.3	472.0	488.8
50°	334.3	338.5	343.4	349.1	355.9	368.1	384.4	403.8	423.9	442.2	456.6
52.5°	316.1	319.9	325.2	330.6	338.9	349.3	363.2	380.4	400.2	413.3	425.3
55°	289.1	291.0	297.1	302.4	310.4	318.0	332.0	347.2	359.4	369.2	379.1
57.5°	261.5	264.1	267.6	272.4	280.3	289.2	299.0	312.5	319.6	324.7	332.4
60°	243.9	244.6	246.9	252.6	258.7	266.7	278.1	287.6	292.9	297.1	303.5
62.5°	224.4	224.6	228.4	232.6	237.1	245.7	255.0	262.6	267.1	269.1	275.3
65°	197.2	196.4	198.7	202.1	207.4	213.1	221.1	227.9	227.5	229.8	233.6
67.5°	169.3	168.5	168.5	171.8	176.1	181.2	186.7	190.6	190.7	193.7	195.6
70°	150.4	148.2	149.7	152.3	154.2	158.4	164.5	166.0	166.4	167.9	169.8
72.5°	131.0	130.2	131.4	132.6	133.9	137.1	142.3	143.2	143.3	144.2	147.3
75°	104.1	103.3	102.6	103.7	105.2	107.5	109.4	110.9	110.5	110.9	113.2
77.5°	78.0	75.9	75.5	76.1	76.5	77.9	79.9	79.7	80.1	80.0	82.6
80°	61.9	58.9	58.5	58.5	58.9	59.6	60.4	61.2	60.0	61.2	61.9
82.5°	45.5	43.7	43.6	43.3	43.4	43.5	44.0	44.4	44.2	44.7	45.2
85°	25.1	24.3	23.2	23.9	23.6	22.4	23.2	22.0	21.7	22.0	22.4
87.5°	11.2	11.3	10.5	10.2	9.7	9.7	8.9	8.3	7.7	7.7	8.4
90°	13.4	12.5	11.3	10.1	8.9	7.6	6.3	5.0	3.6	2.2	0.8
92.5°	31.2	30.0	28.5	27.0	25.5	24.0	22.8	21.8	20.9	19.9	18.9
95°	61.4	60.2	58.5	56.7	55.0	53.3	52.2	51.9	51.5	51.2	50.8
97.5°	97.0	95.9	93.5	91.1	88.7	86.3	85.0	84.9	84.7	84.6	84.5
100°	121.2	119.6	117.4	115.1	112.9	110.6	109.5	109.5	109.5	109.5	109.5
102.5°	146.4	144.7	143.5	142.4	141.2	140.1	139.2	138.5	137.8	137.1	136.4
105°	187.9	186.9	185.8	184.8	183.8	182.7	181.8	180.9	180.0	179.2	178.3
107.5°	232.6	232.1	231.3	230.5	229.7	228.9	228.1	227.2	226.3	225.4	224.6
110°	263.3	262.7	262.2	261.7	261.2	260.7	260.0	259.1	258.2	257.4	256.5



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	294.3	294.0	293.4	292.7	292.0	291.4	290.8	290.4	289.9	289.5	289.0
115°	341.5	341.7	341.4	341.0	340.7	340.3	339.8	339.1	338.4	337.7	337.0
117.5°	388.1	388.0	387.7	387.4	387.1	386.8	386.4	386.1	385.8	385.5	385.2
120°	419.9	419.9	419.7	419.6	419.4	419.2	418.7	417.8	417.0	416.1	415.2
122.5°	451.0	451.2	450.7	450.3	449.8	449.4	449.0	448.7	448.4	448.1	447.7
125°	497.0	497.3	497.1	497.0	496.8	496.6	496.0	495.0	493.9	492.9	491.8
127.5°	542.2	542.4	542.2	541.9	541.7	541.5	541.1	540.5	539.9	539.4	538.8
130°	572.2	572.4	572.0	571.7	571.3	571.0	570.4	569.5	568.7	567.8	566.9
132.5°	601.0	601.2	601.2	601.3	601.4	601.4	600.8	599.3	597.9	596.5	595.1
135°	645.1	645.1	644.9	644.8	644.6	644.4	643.8	642.8	641.7	640.7	639.6
137.5°	688.0	687.8	687.4	687.0	686.7	686.3	685.6	684.6	683.6	682.6	681.6
140°	715.1	714.7	714.2	713.7	713.1	712.6	711.9	711.1	710.2	709.3	708.5
142.5°	741.8	741.6	740.9	740.3	739.6	739.0	738.3	737.5	736.8	736.1	735.4
145°	780.4	780.4	779.9	779.3	778.8	778.3	777.7	777.0	776.3	775.6	774.9
147.5°	815.5	815.1	814.7	814.3	813.9	813.4	813.0	812.7	812.3	811.9	811.5
150°	838.3	838.3	837.6	836.9	836.2	835.5	835.2	835.4	835.6	835.7	835.9
152.5°	858.7	858.3	858.0	857.7	857.4	857.2	856.9	856.7	856.4	856.2	855.9
155°	888.2	887.5	887.3	887.2	887.0	886.8	886.7	886.7	886.7	886.7	886.7
157.5°	914.0	913.3	913.1	913.0	912.8	912.6	912.7	913.1	913.5	913.9	914.3
160°	929.7	929.0	928.8	928.6	928.4	928.3	928.4	929.0	929.5	930.0	930.5
162.5°	944.2	943.4	943.3	943.3	943.2	943.2	943.4	943.8	944.1	944.5	944.9
165°	964.1	963.4	963.2	963.0	962.8	962.7	962.8	963.1	963.5	963.8	964.2
167.5°	978.3	977.3	977.3	977.3	977.3	977.3	977.6	978.3	979.0	979.7	980.4
170°	987.1	986.0	986.0	986.0	986.0	986.0	986.4	987.1	987.8	988.5	989.2
172.5°	993.3	992.3	992.3	992.3	992.3	992.3	992.6	993.3	994.0	994.7	995.4
175°	1000.4	999.3	999.3	999.3	999.3	999.3	999.7	1000.4	1001.1	1001.8	1002.5
177.5°	1003.8	1002.9	1003.1	1003.2	1003.4	1003.5	1003.8	1004.4	1005.0	1005.5	1006.1
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	899.9	904.1	906.8	912.0	916.3	918.7	920.8	922.6	924.8	926.6	931.8
5°	905.6	915.5	923.9	936.8	948.6	957.7	967.5	976.3	983.5	993.8	1001.7
7.5°	903.1	920.7	939.1	959.0	979.5	998.5	1015.9	1032.3	1047.1	1065.0	1080.7
10°	900.7	924.6	948.2	975.1	1002.9	1026.4	1048.5	1070.9	1087.2	1110.0	1129.4
12.5°	898.9	927.1	955.5	987.9	1018.4	1051.6	1081.0	1097.3	1122.2	1140.4	1163.4
15°	891.2	928.4	967.5	1004.0	1047.3	1078.1	1103.9	1135.8	1159.0	1182.2	1207.2
17.5°	877.4	919.6	963.4	1011.2	1052.7	1085.8	1119.0	1149.8	1177.5	1208.5	1239.8
20°	871.1	913.2	963.4	1012.4	1053.0	1087.6	1121.8	1155.6	1186.0	1225.9	1261.9
22.5°	857.7	908.7	954.9	1002.6	1044.5	1082.1	1120.9	1159.2	1199.6	1244.7	1289.9
25°	833.8	885.5	934.5	981.6	1023.8	1070.9	1112.3	1163.6	1215.2	1274.9	1331.1
27.5°	809.1	858.5	903.4	948.9	998.1	1051.4	1105.1	1163.3	1231.0	1306.2	1385.6
30°	789.0	835.7	879.4	926.1	977.4	1037.4	1096.3	1165.5	1243.7	1328.4	1422.6
32.5°	765.6	808.7	851.2	900.6	956.5	1019.8	1088.4	1164.2	1258.3	1354.6	1451.5
35°	725.6	761.7	805.3	858.1	921.2	993.8	1073.2	1162.8	1270.7	1381.2	1462.9
37.5°	678.1	711.7	757.7	815.6	881.7	959.6	1053.8	1160.1	1274.7	1362.8	1389.2
40°	646.2	677.3	725.2	785.2	852.8	935.3	1038.6	1151.0	1261.9	1318.2	1296.5
42.5°	612.1	644.8	691.5	750.9	823.6	913.4	1019.4	1131.9	1224.9	1246.1	1171.3
45°	558.4	592.2	638.2	698.2	776.5	873.7	984.3	1086.4	1140.0	1101.6	985.8
47.5°	508.5	540.2	582.8	644.7	725.5	826.1	932.5	1014.0	1018.3	926.7	803.0
50°	474.5	503.7	546.6	608.6	688.7	790.5	886.6	950.8	922.0	818.3	699.4
52.5°	441.0	469.7	512.0	573.3	652.6	745.8	835.3	880.3	825.9	719.5	617.9
55°	392.8	417.9	459.3	515.9	591.1	677.7	753.7	769.2	698.6	593.7	511.3
57.5°	345.7	369.1	406.8	458.9	527.6	604.4	663.8	660.5	585.8	495.8	430.4
60°	313.8	336.6	370.0	420.9	483.6	549.7	600.6	588.4	514.4	436.9	381.8
62.5°	285.2	305.6	337.2	381.7	438.9	500.1	541.9	524.0	451.4	383.7	340.1
65°	243.1	260.2	287.2	325.2	372.7	423.2	455.5	432.3	370.4	317.6	282.6
67.5°	202.9	216.6	239.2	269.6	310.1	350.6	370.3	347.0	297.4	258.9	233.0
70°	177.4	189.6	207.0	234.0	269.3	303.5	318.3	297.4	254.9	221.8	203.2
72.5°	151.9	161.9	177.3	201.5	229.8	259.5	272.4	252.5	217.5	189.6	172.2
75°	117.4	124.2	134.9	151.6	174.0	197.5	204.8	187.3	164.9	144.0	132.6
77.5°	84.0	89.8	97.9	108.4	124.3	139.3	145.6	135.5	118.1	104.9	95.6
80°	64.6	67.6	74.5	83.2	95.7	105.2	109.4	102.9	90.8	80.9	73.7
82.5°	46.0	49.1	53.2	60.4	68.4	74.8	79.3	75.0	66.2	58.4	54.2
85°	22.4	24.3	26.6	29.6	35.7	39.5	39.1	36.5	33.0	30.0	27.7
87.5°	8.3	8.9	10.1	11.9	13.1	14.5	15.4	15.0	14.1	13.3	12.6
90°	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4	14.2
92.5°	19.9	20.9	21.8	22.8	24.0	25.5	27.0	28.5	30.0	31.2	32.3
95°	51.2	51.5	51.9	52.2	53.3	55.0	56.7	58.5	60.2	61.4	62.6
97.5°	84.6	84.7	84.9	85.0	86.3	88.7	91.1	93.5	95.9	97.0	98.2
100°	109.5	109.5	109.5	109.5	110.6	112.9	115.1	117.4	119.6	121.2	122.8
102.5°	137.1	137.8	138.5	139.2	140.1	141.2	142.4	143.5	144.7	146.4	148.1
105°	179.2	180.0	180.9	181.8	182.7	183.8	184.8	185.8	186.9	187.9	189.0
107.5°	225.4	226.3	227.2	228.1	228.9	229.7	230.5	231.3	232.1	232.6	233.1
110°	257.4	258.2	259.1	260.0	260.7	261.2	261.7	262.2	262.7	263.3	263.8



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	289.5	289.9	290.4	290.8	291.4	292.0	292.7	293.4	294.0	294.3	294.5
115°	337.7	338.4	339.1	339.8	340.3	340.7	341.0	341.4	341.7	341.5	341.4
117.5°	385.5	385.8	386.1	386.4	386.8	387.1	387.4	387.7	388.0	388.1	388.3
120°	416.1	417.0	417.8	418.7	419.2	419.4	419.6	419.7	419.9	419.9	419.9
122.5°	448.1	448.4	448.7	449.0	449.4	449.8	450.3	450.7	451.2	451.0	450.9
125°	492.9	493.9	495.0	496.0	496.6	496.8	497.0	497.1	497.3	497.0	496.6
127.5°	539.4	539.9	540.5	541.1	541.5	541.7	541.9	542.2	542.4	542.2	542.0
130°	567.8	568.7	569.5	570.4	571.0	571.3	571.7	572.0	572.4	572.2	572.0
132.5°	596.5	597.9	599.3	600.8	601.4	601.4	601.3	601.2	601.2	601.0	600.8
135°	640.7	641.7	642.8	643.8	644.4	644.6	644.8	644.9	645.1	645.1	645.1
137.5°	682.6	683.6	684.6	685.6	686.3	686.7	687.0	687.4	687.8	688.0	688.2
140°	709.3	710.2	711.1	711.9	712.6	713.1	713.7	714.2	714.7	715.1	715.4
142.5°	736.1	736.8	737.5	738.3	739.0	739.6	740.3	740.9	741.6	741.8	742.0
145°	775.6	776.3	777.0	777.7	778.3	778.8	779.3	779.9	780.4	780.4	780.4
147.5°	811.9	812.3	812.7	813.0	813.4	813.9	814.3	814.7	815.1	815.5	815.9
150°	835.7	835.6	835.4	835.2	835.5	836.2	836.9	837.6	838.3	838.3	838.3
152.5°	856.2	856.4	856.7	856.9	857.2	857.4	857.7	858.0	858.3	858.7	859.1
155°	886.7	886.7	886.7	886.7	886.8	887.0	887.2	887.3	887.5	888.2	888.9
157.5°	913.9	913.5	913.1	912.7	912.6	912.8	913.0	913.1	913.3	914.0	914.7
160°	930.0	929.5	929.0	928.4	928.3	928.4	928.6	928.8	929.0	929.7	930.4
162.5°	944.5	944.1	943.8	943.4	943.2	943.2	943.3	943.3	943.4	944.2	945.0
165°	963.8	963.5	963.1	962.8	962.7	962.8	963.0	963.2	963.4	964.1	964.8
167.5°	979.7	979.0	978.3	977.6	977.3	977.3	977.3	977.3	977.3	978.3	979.4
170°	988.5	987.8	987.1	986.4	986.0	986.0	986.0	986.0	986.0	987.1	988.1
172.5°	994.7	994.0	993.3	992.6	992.3	992.3	992.3	992.3	992.3	993.3	994.4
175°	1001.8	1001.1	1000.4	999.7	999.3	999.3	999.3	999.3	999.3	1000.4	1001.4
177.5°	1005.5	1005.0	1004.4	1003.8	1003.5	1003.4	1003.2	1003.1	1002.9	1003.8	1004.6
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	895.0	895.0	895.0	895.0	895.0	895.0	895.0
2.5°	936.0	938.4	943.6	941.8	944.2	945.4	946.7
5°	1011.6	1023.8	1029.1	1028.3	1036.3	1034.4	1032.5
7.5°	1097.0	1109.8	1116.9	1125.8	1131.0	1131.3	1135.8
10°	1145.3	1162.0	1168.9	1178.4	1184.5	1187.9	1187.5
12.5°	1182.4	1195.5	1210.8	1215.5	1223.7	1228.0	1226.4
15°	1227.0	1247.9	1263.8	1271.8	1282.1	1285.1	1289.3
17.5°	1266.8	1294.8	1313.5	1338.2	1347.6	1353.3	1349.9
20°	1296.9	1333.7	1352.4	1382.0	1398.3	1407.1	1404.0
22.5°	1332.5	1372.3	1406.8	1432.4	1457.3	1469.1	1471.5
25°	1393.4	1448.1	1498.6	1532.4	1563.2	1570.4	1586.4
27.5°	1461.5	1526.0	1580.0	1615.5	1637.0	1645.0	1650.0
30°	1504.3	1568.5	1609.2	1631.9	1638.8	1638.0	1637.3
32.5°	1525.3	1565.5	1573.3	1566.9	1551.3	1538.0	1524.2
35°	1495.6	1465.6	1420.7	1363.0	1320.5	1277.5	1273.3
37.5°	1345.1	1249.1	1174.5	1091.2	1043.1	1013.4	992.8
40°	1203.4	1094.4	1004.0	933.7	884.7	865.4	846.4
42.5°	1049.7	945.5	865.4	806.7	769.9	748.4	733.3
45°	852.8	760.9	698.2	655.7	626.4	609.7	600.2
47.5°	698.8	630.8	577.6	546.9	526.7	513.7	513.7
50°	616.2	551.2	515.9	491.6	474.1	463.8	465.7
52.5°	542.9	494.4	464.2	443.8	430.9	424.6	424.4
55°	454.0	419.0	399.3	384.4	375.7	368.5	370.0
57.5°	388.3	358.8	345.6	333.3	327.2	324.3	320.2
60°	347.6	324.8	313.4	303.5	297.4	295.2	291.0
62.5°	311.4	293.5	282.4	274.3	268.9	268.1	264.8
65°	261.7	248.1	238.2	234.4	228.7	227.2	227.2
67.5°	215.8	206.0	198.3	194.8	192.3	192.7	190.8
70°	186.9	178.9	174.0	170.2	168.3	168.7	167.1
72.5°	163.5	154.6	150.3	148.0	145.5	146.5	145.9
75°	123.8	119.3	117.0	114.7	113.2	112.4	111.7
77.5°	90.9	86.9	85.2	83.9	84.1	82.3	83.7
80°	70.3	66.9	65.7	63.8	63.4	63.4	63.1
82.5°	51.4	49.5	48.7	47.1	46.4	47.0	46.0
85°	26.6	25.1	24.7	24.7	23.9	23.2	25.1
87.5°	12.7	11.7	11.8	11.6	11.8	11.6	11.0
90°	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	33.5	34.6	35.4	35.8	36.1	36.5	36.9
95°	63.9	65.1	65.9	66.2	66.6	66.9	67.2
97.5°	99.3	100.5	101.1	101.3	101.5	101.8	102.0
100°	124.3	125.9	126.9	127.2	127.5	127.9	128.2
102.5°	149.8	151.5	152.6	153.1	153.5	154.0	154.5
105°	190.0	191.1	191.8	192.4	192.9	193.4	193.9
107.5°	233.6	234.2	234.4	234.4	234.3	234.3	234.3
110°	264.3	264.8	265.0	264.8	264.6	264.5	264.3



TEST NUMBER: P333179

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	294.7	295.0	295.0	294.6	294.3	294.0	293.7
115°	341.2	341.0	340.8	340.7	340.5	340.3	340.2
117.5°	388.4	388.6	388.3	387.6	386.9	386.2	385.5
120°	419.9	419.9	419.6	418.9	418.2	417.5	416.8
122.5°	450.8	450.6	450.3	449.7	449.2	448.6	448.1
125°	496.3	495.9	495.7	495.5	495.3	495.2	495.0
127.5°	541.8	541.7	541.4	541.1	540.7	540.4	540.0
130°	571.9	571.7	571.4	571.1	570.7	570.4	570.0
132.5°	600.6	600.5	600.1	599.7	599.2	598.7	598.2
135°	645.1	645.1	644.8	644.1	643.4	642.7	642.0
137.5°	688.4	688.6	688.3	687.4	686.6	685.7	684.8
140°	715.7	716.1	715.8	715.0	714.1	713.2	712.4
142.5°	742.2	742.4	742.1	741.2	740.4	739.5	738.6
145°	780.4	780.4	780.1	779.6	779.1	778.6	778.0
147.5°	816.4	816.8	816.4	815.2	814.0	812.9	811.7
150°	838.3	838.3	838.1	837.7	837.4	837.0	836.7
152.5°	859.5	859.9	859.8	859.2	858.6	858.0	857.3
155°	889.6	890.3	890.2	889.3	888.5	887.6	886.7
157.5°	915.4	916.1	915.9	914.7	913.6	912.4	911.3
160°	931.0	931.7	931.7	930.8	929.9	929.0	928.2
162.5°	945.9	946.7	946.6	945.6	944.6	943.6	942.6
165°	965.5	966.1	966.0	964.9	963.9	962.8	961.8
167.5°	980.4	981.5	981.4	980.4	979.3	978.2	977.1
170°	989.2	990.2	990.1	988.9	987.7	986.5	985.3
172.5°	995.4	996.5	996.5	995.4	994.3	993.2	992.1
175°	1002.5	1003.5	1003.4	1002.2	1001.0	999.8	998.6
177.5°	1005.4	1006.3	1006.2	1005.2	1004.3	1003.3	1002.3
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8

(END OF REPORT)