

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333185

Luminaire Tested: **S125DIP-S610D810U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333185  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S610D810U835-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5305.1 lumens  
Efficiency: N/A  
Efficacy: 138.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333185

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333185

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47	47	47	47	47	47	47		
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40	40	40	40	40	40	40		
2	88	81	75	70	81	75	69	65	63	59	55	52	49	46	41	40	38	33	33	33	33	33	33	33		
3	81	71	64	58	74	66	59	54	55	50	47	46	42	39	37	34	32	28	28	28	28	28	28	28		
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24	24	24	24	24		
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	30	27	24	21	21	21	21	21	21	21		
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21	18	18	18	18	18	18	18		
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16	16	16	16	16	16	16		
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	15	15	15	15	15	15	15		
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13	13	13	13	13		
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12	12	12	12	12	12	12		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6203	6203	6203
5°	6217	6157	6196
10°	6178	6114	6149
15°	6111	6040	6066
20°	6016	5937	5948
25°	5912	5815	5810
30°	5785	5683	5655
35°	5649	5541	5463
40°	5509	5387	5311
45°	5358	5246	5142
50°	5191	5077	4924
55°	5031	4884	4748
60°	4839	4691	4525
65°	4609	4459	4308
70°	4390	4190	4047
75°	4000	3868	3735
80°	3559	3503	3418
85°	3097	3149	2986



TEST NUMBER: P333185

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.6	1.7
10°-20°	255.8	4.8
20°-30°	377.7	7.1
30°-40°	440.7	8.3
40°-50°	442.6	8.3
50°-60°	388.5	7.3
60°-70°	289.5	5.5
70°-80°	165.5	3.1
80°-90°	50.3	0.9
90°-100°	67.3	1.3
100°-110°	198.7	3.7
110°-120°	336.6	6.3
120°-130°	443.0	8.4
130°-140°	496.4	9.4
140°-150°	486.5	9.2
150°-160°	408.6	7.7
160°-170°	271.6	5.1
170°-180°	95.1	1.8
0°-30°	724.0	13.6
0°-40°	1164.7	22.0
0°-60°	1995.9	37.6
0°-90°	2501.2	47.1
90°-120°	602.7	11.4
90°-150°	2028.6	38.2
90°-180°	2804.0	52.9
0°-180°	5305.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	960	960	960	960	960	
5°	959	957	950	956	956	91
15°	914	911	903	907	907	257
25°	830	826	816	817	815	382
35°	716	713	703	699	693	448
45°	587	583	574	566	563	452
55°	447	444	434	427	422	399
65°	302	300	292	285	282	299
75°	160	159	155	153	150	171
85°	42	42	42	42	40	47
90°	1	7	12	16	19	5
95°	51	53	60	66	67	54
105°	178	182	187	191	194	190
115°	337	340	342	341	340	333
125°	492	496	497	496	495	440
135°	640	644	645	645	642	493
145°	775	778	780	780	778	484
155°	887	887	888	890	887	408
165°	964	963	963	966	962	272
175°	1002	1000	999	1003	999	95
180°	1005	1005	1005	1005	1005	



TEST NUMBER: P333185

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	962.8	962.4	962.0	961.6	961.2	960.3	959.0	957.6	956.3	954.9	956.3
5°	958.9	958.5	958.2	957.8	957.5	956.5	954.8	953.1	951.4	949.7	951.3
7.5°	950.0	949.7	949.4	949.0	948.7	947.6	945.7	943.9	942.0	940.2	941.6
10°	942.1	941.8	941.5	941.1	940.8	939.7	937.8	936.0	934.1	932.3	933.6
12.5°	932.4	931.8	931.2	930.6	930.0	928.8	927.1	925.4	923.6	921.9	923.0
15°	914.0	913.5	913.0	912.5	912.0	910.8	909.0	907.1	905.2	903.4	904.2
17.5°	892.9	892.2	891.4	890.7	889.9	888.6	886.7	884.7	882.8	880.9	881.9
20°	875.3	874.9	874.6	874.3	873.9	872.7	870.5	868.3	866.1	863.9	865.1
22.5°	857.6	857.0	856.4	855.8	855.2	853.9	851.8	849.8	847.7	845.6	846.4
25°	829.7	828.8	828.0	827.2	826.3	824.8	822.6	820.4	818.2	816.0	816.4
27.5°	797.0	796.5	796.0	795.5	795.0	793.6	791.3	789.1	786.8	784.6	784.6
30°	775.7	775.2	774.7	774.2	773.7	772.2	769.7	767.1	764.6	762.1	761.7
32.5°	752.6	751.9	751.1	750.3	749.5	748.0	745.8	743.5	741.2	739.0	738.4
35°	716.5	715.8	715.1	714.5	713.8	712.3	709.9	707.5	705.2	702.8	702.0
37.5°	678.9	678.1	677.3	676.4	675.6	674.0	671.8	669.6	667.3	665.1	663.9
40°	653.4	652.6	651.7	650.9	650.0	648.4	646.1	643.7	641.3	639.0	637.5
42.5°	626.1	625.4	624.6	623.9	623.2	621.7	619.3	617.0	614.6	612.2	610.9
45°	586.6	585.9	585.2	584.5	583.9	582.5	580.5	578.5	576.4	574.4	572.4
47.5°	544.0	544.0	544.1	544.1	544.1	542.9	540.5	538.1	535.7	533.2	531.2
50°	516.7	516.1	515.6	515.1	514.6	513.4	511.3	509.3	507.3	505.3	503.1
52.5°	488.7	488.3	488.0	487.6	487.2	485.9	483.8	481.6	479.5	477.3	475.4
55°	446.8	446.2	445.7	445.2	444.7	443.3	440.9	438.6	436.2	433.8	432.3
57.5°	402.5	402.3	402.0	401.7	401.5	400.3	398.3	396.3	394.3	392.4	390.4
60°	374.6	373.9	373.2	372.5	371.9	370.6	368.8	366.9	365.0	363.2	361.5
62.5°	345.4	344.9	344.3	343.8	343.2	342.2	340.6	339.0	337.4	335.8	334.0
65°	301.6	301.3	301.0	300.6	300.3	299.2	297.3	295.5	293.6	291.8	290.2
67.5°	259.2	258.5	257.8	257.1	256.4	255.4	254.0	252.6	251.2	249.8	248.5
70°	232.5	231.7	230.8	230.0	229.1	227.9	226.4	224.9	223.4	221.9	220.8
72.5°	203.3	202.7	202.2	201.6	201.0	200.2	199.3	198.3	197.3	196.3	195.2
75°	160.3	160.0	159.6	159.3	159.0	158.4	157.5	156.7	155.8	155.0	154.5
77.5°	120.7	120.5	120.4	120.2	120.1	119.8	119.3	118.9	118.4	117.9	117.6
80°	95.7	95.7	95.7	95.7	95.7	95.6	95.2	94.9	94.6	94.2	94.0
82.5°	73.9	73.6	73.3	73.0	72.8	72.6	72.5	72.5	72.4	72.3	72.0
85°	41.8	42.0	42.1	42.3	42.5	42.5	42.5	42.5	42.5	42.5	42.4
87.5°	16.6	16.8	17.1	17.4	17.7	17.9	18.0	18.1	18.2	18.3	18.5
90°	0.8	2.2	3.6	5.0	6.3	7.6	8.9	10.1	11.3	12.5	13.4
92.5°	18.9	19.9	20.9	21.8	22.8	24.0	25.5	27.0	28.5	30.0	31.2
95°	50.8	51.2	51.5	51.9	52.2	53.3	55.0	56.7	58.5	60.2	61.4
97.5°	84.5	84.6	84.7	84.9	85.0	86.3	88.7	91.1	93.5	95.9	97.0
100°	109.5	109.5	109.5	109.5	109.5	110.6	112.9	115.1	117.4	119.6	121.2
102.5°	136.4	137.1	137.8	138.5	139.2	140.1	141.2	142.4	143.5	144.7	146.4
105°	178.3	179.2	180.0	180.9	181.8	182.7	183.8	184.8	185.8	186.9	187.9
107.5°	224.6	225.4	226.3	227.2	228.1	228.9	229.7	230.5	231.3	232.1	232.6
110°	256.5	257.4	258.2	259.1	260.0	260.7	261.2	261.7	262.2	262.7	263.3



TEST NUMBER: P333185

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	289.0	289.5	289.9	290.4	290.8	291.4	292.0	292.7	293.4	294.0	294.3
115°	337.0	337.7	338.4	339.1	339.8	340.3	340.7	341.0	341.4	341.7	341.5
117.5°	385.2	385.5	385.8	386.1	386.4	386.8	387.1	387.4	387.7	388.0	388.1
120°	415.2	416.1	417.0	417.8	418.7	419.2	419.4	419.6	419.7	419.9	419.9
122.5°	447.7	448.1	448.4	448.7	449.0	449.4	449.8	450.3	450.7	451.2	451.0
125°	491.8	492.9	493.9	495.0	496.0	496.6	496.8	497.0	497.1	497.3	497.0
127.5°	538.8	539.4	539.9	540.5	541.1	541.5	541.7	541.9	542.2	542.4	542.2
130°	566.9	567.8	568.7	569.5	570.4	571.0	571.3	571.7	572.0	572.4	572.2
132.5°	595.1	596.5	597.9	599.3	600.8	601.4	601.4	601.3	601.2	601.2	601.0
135°	639.6	640.7	641.7	642.8	643.8	644.4	644.6	644.8	644.9	645.1	645.1
137.5°	681.6	682.6	683.6	684.6	685.6	686.3	686.7	687.0	687.4	687.8	688.0
140°	708.5	709.3	710.2	711.1	711.9	712.6	713.1	713.7	714.2	714.7	715.1
142.5°	735.4	736.1	736.8	737.5	738.3	739.0	739.6	740.3	740.9	741.6	741.8
145°	774.9	775.6	776.3	777.0	777.7	778.3	778.8	779.3	779.9	780.4	780.4
147.5°	811.5	811.9	812.3	812.7	813.0	813.4	813.9	814.3	814.7	815.1	815.5
150°	835.9	835.7	835.6	835.4	835.2	835.5	836.2	836.9	837.6	838.3	838.3
152.5°	855.9	856.2	856.4	856.7	856.9	857.2	857.4	857.7	858.0	858.3	858.7
155°	886.7	886.7	886.7	886.7	886.7	886.8	887.0	887.2	887.3	887.5	888.2
157.5°	914.3	913.9	913.5	913.1	912.7	912.6	912.8	913.0	913.1	913.3	914.0
160°	930.5	930.0	929.5	929.0	928.4	928.3	928.4	928.6	928.8	929.0	929.7
162.5°	944.9	944.5	944.1	943.8	943.4	943.2	943.2	943.3	943.3	943.4	944.2
165°	964.2	963.8	963.5	963.1	962.8	962.7	962.8	963.0	963.2	963.4	964.1
167.5°	980.4	979.7	979.0	978.3	977.6	977.3	977.3	977.3	977.3	977.3	978.3
170°	989.2	988.5	987.8	987.1	986.4	986.0	986.0	986.0	986.0	986.0	987.1
172.5°	995.4	994.7	994.0	993.3	992.6	992.3	992.3	992.3	992.3	992.3	993.3
175°	1002.5	1001.8	1001.1	1000.4	999.7	999.3	999.3	999.3	999.3	999.3	1000.4
177.5°	1006.1	1005.5	1005.0	1004.4	1003.8	1003.5	1003.4	1003.2	1003.1	1002.9	1003.8
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8



TEST NUMBER: P333185

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	957.6	959.0	960.3	960.9	960.8	960.6	960.5	960.4
5°	952.8	954.3	955.8	956.5	956.3	956.2	956.0	955.8
7.5°	943.1	944.6	946.1	946.8	946.6	946.4	946.3	946.1
10°	935.0	936.3	937.7	938.3	938.1	937.9	937.7	937.6
12.5°	924.1	925.2	926.2	926.8	926.7	926.7	926.7	926.6
15°	905.1	905.9	906.8	907.2	907.2	907.2	907.2	907.2
17.5°	883.0	884.0	885.1	885.2	884.3	883.5	882.7	881.8
20°	866.2	867.4	868.6	868.8	867.9	867.1	866.2	865.4
22.5°	847.2	848.0	848.8	848.9	848.3	847.7	847.1	846.6
25°	816.7	817.0	817.4	817.3	816.8	816.3	815.8	815.3
27.5°	784.7	784.8	784.8	784.6	784.1	783.6	783.1	782.6
30°	761.4	761.1	760.7	760.3	759.8	759.3	758.8	758.3
32.5°	737.8	737.1	736.5	735.8	734.9	734.0	733.0	732.1
35°	701.1	700.3	699.4	698.3	697.0	695.6	694.3	692.9
37.5°	662.6	661.4	660.1	659.1	658.3	657.6	656.8	656.0
40°	635.9	634.4	632.9	631.9	631.4	630.9	630.4	629.9
42.5°	609.5	608.1	606.7	605.6	604.8	604.1	603.3	602.5
45°	570.3	568.3	566.3	565.0	564.5	564.0	563.5	563.0
47.5°	529.1	527.0	525.0	523.4	522.2	521.0	519.8	518.6
50°	500.9	498.7	496.5	494.8	493.6	492.4	491.2	490.1
52.5°	473.4	471.5	469.6	468.0	466.7	465.3	464.0	462.7
55°	430.8	429.3	427.8	426.4	425.2	424.0	422.9	421.7
57.5°	388.4	386.5	384.5	383.2	382.6	381.9	381.3	380.7
60°	359.8	358.1	356.4	355.0	353.8	352.6	351.4	350.3
62.5°	332.2	330.4	328.5	327.2	326.3	325.3	324.4	323.5
65°	288.7	287.2	285.7	284.6	283.9	283.2	282.6	281.9
67.5°	247.3	246.0	244.7	243.8	243.4	243.0	242.6	242.2
70°	219.8	218.8	217.8	217.0	216.3	215.6	214.9	214.3
72.5°	194.0	192.9	191.7	190.8	190.1	189.5	188.8	188.1
75°	154.0	153.5	153.0	152.4	151.7	151.0	150.4	149.7
77.5°	117.3	117.0	116.7	116.3	115.8	115.4	114.9	114.4
80°	93.9	93.7	93.5	93.3	92.9	92.6	92.3	91.9
82.5°	71.7	71.4	71.1	70.9	70.9	70.8	70.7	70.7
85°	42.2	42.0	41.9	41.6	41.3	40.9	40.6	40.3
87.5°	18.7	18.8	19.0	19.0	18.8	18.7	18.5	18.3
90°	14.2	15.1	16.0	16.7	17.2	17.7	18.2	18.8
92.5°	32.3	33.5	34.6	35.4	35.8	36.1	36.5	36.9
95°	62.6	63.9	65.1	65.9	66.2	66.6	66.9	67.2
97.5°	98.2	99.3	100.5	101.1	101.3	101.5	101.8	102.0
100°	122.8	124.3	125.9	126.9	127.2	127.5	127.9	128.2
102.5°	148.1	149.8	151.5	152.6	153.1	153.5	154.0	154.5
105°	189.0	190.0	191.1	191.8	192.4	192.9	193.4	193.9
107.5°	233.1	233.6	234.2	234.4	234.4	234.3	234.3	234.3
110°	263.8	264.3	264.8	265.0	264.8	264.6	264.5	264.3





TEST NUMBER: P333185

CATALOG NUMBER: S125DIP-S610D810U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.5	294.7	295.0	295.0	294.6	294.3	294.0	293.7
115°	341.4	341.2	341.0	340.8	340.7	340.5	340.3	340.2
117.5°	388.3	388.4	388.6	388.3	387.6	386.9	386.2	385.5
120°	419.9	419.9	419.9	419.6	418.9	418.2	417.5	416.8
122.5°	450.9	450.8	450.6	450.3	449.7	449.2	448.6	448.1
125°	496.6	496.3	495.9	495.7	495.5	495.3	495.2	495.0
127.5°	542.0	541.8	541.7	541.4	541.1	540.7	540.4	540.0
130°	572.0	571.9	571.7	571.4	571.1	570.7	570.4	570.0
132.5°	600.8	600.6	600.5	600.1	599.7	599.2	598.7	598.2
135°	645.1	645.1	645.1	644.8	644.1	643.4	642.7	642.0
137.5°	688.2	688.4	688.6	688.3	687.4	686.6	685.7	684.8
140°	715.4	715.7	716.1	715.8	715.0	714.1	713.2	712.4
142.5°	742.0	742.2	742.4	742.1	741.2	740.4	739.5	738.6
145°	780.4	780.4	780.4	780.1	779.6	779.1	778.6	778.0
147.5°	815.9	816.4	816.8	816.4	815.2	814.0	812.9	811.7
150°	838.3	838.3	838.3	838.1	837.7	837.4	837.0	836.7
152.5°	859.1	859.5	859.9	859.8	859.2	858.6	858.0	857.3
155°	888.9	889.6	890.3	890.2	889.3	888.5	887.6	886.7
157.5°	914.7	915.4	916.1	915.9	914.7	913.6	912.4	911.3
160°	930.4	931.0	931.7	931.7	930.8	929.9	929.0	928.2
162.5°	945.0	945.9	946.7	946.6	945.6	944.6	943.6	942.6
165°	964.8	965.5	966.1	966.0	964.9	963.9	962.8	961.8
167.5°	979.4	980.4	981.5	981.4	980.4	979.3	978.2	977.1
170°	988.1	989.2	990.2	990.1	988.9	987.7	986.5	985.3
172.5°	994.4	995.4	996.5	996.5	995.4	994.3	993.2	992.1
175°	1001.4	1002.5	1003.5	1003.4	1002.2	1001.0	999.8	998.6
177.5°	1004.6	1005.4	1006.3	1006.2	1005.2	1004.3	1003.3	1002.3
180°	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8	1004.8

(END OF REPORT)