

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333233

Luminaire Tested: **S125DIP-S850D1035U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333233
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D1035U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7034.7 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49																				
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42																				
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	44	42	40	35																				
3	81	72	65	59	75	67	61	55	57	52	48	47	44	41	39	36	34	30																				
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26																				
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23																				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20																				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18																				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16																				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14																				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7901	7901	7901	7901
5°	9149	7927	6941	7927
10°	10645	7887	6082	7887
15°	11784	7829	5610	7829
20°	13190	7737	5232	7737
25°	15452	7633	5047	7633
30°	16690	7532	4887	7532
35°	13722	7340	4782	7340
40°	9754	7074	4666	7074
45°	7493	6716	4601	6716
50°	6396	6271	4591	6271
55°	5695	5835	4631	5835
60°	5137	5359	4748	5359
65°	4745	4879	4872	4879
70°	4315	4383	4942	4383
75°	3810	3860	4898	3860
80°	3206	3146	4482	3146
85°	2542	2267	3616	2267



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	1.7
10°-20°	350.7	5.0
20°-30°	569.4	8.1
30°-40°	694.5	9.9
40°-50°	631.8	9.0
50°-60°	503.3	7.2
60°-70°	350.5	5.0
70°-80°	186.9	2.7
80°-90°	50.0	0.7
90°-100°	85.9	1.2
100°-110°	253.7	3.6
110°-120°	429.8	6.1
120°-130°	565.6	8.0
130°-140°	633.8	9.0
140°-150°	621.1	8.8
150°-160°	521.7	7.4
160°-170°	346.8	4.9
170°-180°	121.4	1.7
0°-30°	1037.8	14.8
0°-40°	1732.4	24.6
0°-60°	2867.5	40.8
0°-90°	3454.9	49.1
90°-120°	769.4	10.9
90°-150°	2589.9	36.8
90°-180°	3580.0	50.9
0°-180°	7034.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1411	1223	1071	1223	1411	142
15°	1762	1171	839	1171	1762	504
25°	2168	1071	708	1071	2168	990
35°	1740	931	606	931	1740	1065
45°	820	735	504	735	820	657
55°	506	518	411	518	506	455
65°	310	319	319	319	310	308
75°	153	155	196	155	153	164
85°	34	31	49	31	34	40
90°	24	1	24	1	24	15
95°	86	65	86	65	86	87
105°	248	228	248	228	248	262
115°	434	430	434	430	434	430
125°	632	628	632	628	632	564
135°	820	817	820	817	820	632
145°	993	989	993	989	993	620
155°	1132	1132	1132	1132	1132	521
165°	1228	1231	1228	1231	1228	346
175°	1275	1280	1275	1280	1275	121
180°	1283	1283	1283	1283	1283	



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1294.0	1292.3	1290.7	1287.3	1289.8	1282.8	1279.4	1273.6	1266.6	1264.1	1261.2
5°	1411.3	1413.9	1416.5	1405.6	1406.7	1399.4	1382.8	1369.3	1358.4	1344.4	1334.5
7.5°	1552.6	1546.4	1545.9	1538.9	1526.7	1517.0	1499.5	1477.3	1455.8	1431.3	1411.0
10°	1623.2	1623.7	1619.0	1610.7	1597.8	1588.4	1565.6	1543.7	1517.3	1486.1	1463.8
12.5°	1676.4	1678.5	1672.6	1661.4	1655.1	1634.1	1616.2	1590.3	1558.8	1533.9	1499.9
15°	1762.4	1756.6	1752.5	1738.5	1727.6	1705.8	1677.2	1650.2	1615.9	1584.2	1552.6
17.5°	1845.2	1849.8	1842.0	1829.2	1795.4	1769.9	1731.6	1694.6	1652.0	1609.5	1571.7
20°	1919.2	1923.3	1911.4	1889.1	1848.6	1823.1	1772.7	1725.0	1675.6	1621.1	1579.6
22.5°	2011.4	2008.1	1992.0	1958.0	1922.9	1875.9	1821.3	1763.2	1701.4	1639.8	1584.6
25°	2168.4	2146.6	2136.7	2094.7	2048.5	1979.4	1904.6	1819.5	1742.6	1661.1	1590.5
27.5°	2255.4	2248.6	2237.6	2208.3	2159.7	2085.9	1997.7	1893.9	1785.5	1682.6	1590.2
30°	2238.0	2239.0	2240.1	2230.7	2199.6	2144.0	2056.3	1944.6	1815.8	1700.0	1593.1
32.5°	2083.5	2102.4	2120.4	2141.8	2150.5	2139.9	2084.9	1984.1	1851.6	1720.0	1591.4
35°	1740.5	1746.3	1804.9	1863.1	1942.0	2003.3	2044.3	1999.7	1888.0	1736.9	1589.4
37.5°	1357.1	1385.2	1425.8	1491.5	1605.4	1707.4	1838.6	1898.9	1862.9	1742.4	1585.8
40°	1156.9	1182.9	1209.3	1276.3	1372.4	1496.0	1645.0	1772.2	1801.8	1725.0	1573.3
42.5°	1002.4	1022.9	1052.3	1102.7	1183.0	1292.4	1434.8	1601.1	1703.4	1674.3	1547.2
45°	820.4	833.4	856.3	896.2	954.4	1040.1	1165.7	1347.5	1505.8	1558.3	1485.1
47.5°	702.2	702.1	719.9	747.5	789.5	862.3	955.2	1097.6	1266.8	1391.9	1386.1
50°	636.6	634.0	648.0	671.9	705.1	753.4	842.2	955.9	1118.5	1260.2	1299.7
52.5°	580.1	580.4	589.0	606.7	634.5	675.8	742.1	844.6	983.5	1129.0	1203.3
55°	505.8	503.7	513.5	525.5	545.7	572.7	620.5	698.9	811.6	954.9	1051.5
57.5°	437.6	443.3	447.3	455.6	472.4	490.5	530.8	588.3	677.7	800.7	902.8
60°	397.7	403.5	406.6	414.9	428.4	444.0	475.1	521.9	597.1	703.1	804.3
62.5°	362.0	366.5	367.5	375.0	386.0	401.2	425.7	464.9	524.4	617.1	716.3
65°	310.5	310.5	312.6	320.4	325.6	339.1	357.8	386.3	434.1	506.3	590.9
67.5°	260.9	263.4	262.8	266.3	271.1	281.5	294.9	318.5	353.9	406.6	474.3
70°	228.5	230.5	230.0	232.6	237.8	244.6	255.5	277.8	303.2	348.4	406.6
72.5°	199.4	200.2	198.9	202.3	205.4	211.3	223.5	235.4	259.2	297.3	345.1
75°	152.7	153.7	154.7	156.8	159.9	163.0	169.3	181.2	196.8	225.4	256.0
77.5°	114.4	112.5	115.0	114.7	116.4	118.8	124.3	130.6	143.4	161.5	185.2
80°	86.2	86.7	86.7	87.2	89.8	91.4	96.1	100.7	110.6	124.1	140.7
82.5°	62.9	64.3	63.5	64.4	66.6	67.7	70.3	74.1	79.9	90.5	102.5
85°	34.3	31.7	32.7	33.8	33.8	34.3	36.3	37.9	41.0	45.2	49.8
87.5°	14.8	15.5	15.7	15.6	15.9	15.7	17.2	16.9	18.0	19.0	20.3
90°	24.0	23.3	22.6	22.0	21.3	20.4	19.3	18.2	17.1	16.0	14.4
92.5°	47.1	46.6	46.1	45.7	45.2	44.2	42.7	41.3	39.8	38.3	36.4
95°	85.9	85.4	85.0	84.5	84.1	83.1	81.5	80.0	78.4	76.9	74.7
97.5°	130.2	129.9	129.7	129.4	129.1	128.3	126.8	125.3	123.9	122.4	119.3
100°	163.7	163.3	162.8	162.4	162.0	160.7	158.7	156.7	154.7	152.7	149.9
102.5°	197.3	196.7	196.0	195.4	194.8	193.4	191.2	189.0	186.9	184.7	183.2
105°	247.6	246.9	246.3	245.6	244.9	243.9	242.6	241.3	239.9	238.6	237.3
107.5°	299.1	299.2	299.2	299.2	299.3	299.0	298.3	297.6	297.0	296.3	295.3
110°	337.4	337.7	337.9	338.1	338.3	338.1	337.4	336.8	336.1	335.4	334.8



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.0	375.4	375.8	376.2	376.6	376.6	376.3	376.0	375.7	375.4	374.5
115°	434.3	434.5	434.7	434.9	435.2	435.4	435.6	435.8	436.1	436.3	435.8
117.5°	492.2	493.1	494.0	494.8	495.7	496.1	495.9	495.7	495.6	495.4	495.0
120°	532.1	533.0	533.9	534.8	535.7	536.1	536.1	536.1	536.1	536.1	535.9
122.5°	572.1	572.8	573.5	574.2	574.9	575.3	575.5	575.7	575.9	576.0	575.5
125°	632.0	632.2	632.4	632.6	632.8	633.2	633.6	634.1	634.5	635.0	634.7
127.5°	689.5	689.9	690.3	690.8	691.2	691.6	691.8	692.0	692.2	692.5	692.2
130°	727.8	728.2	728.7	729.1	729.6	729.9	730.1	730.3	730.6	730.8	730.3
132.5°	763.7	764.4	765.0	765.6	766.2	766.6	766.9	767.1	767.3	767.5	767.6
135°	819.6	820.5	821.4	822.3	823.2	823.6	823.6	823.6	823.6	823.6	823.4
137.5°	874.4	875.5	876.6	877.7	878.8	879.2	878.9	878.7	878.4	878.1	877.7
140°	909.5	910.6	911.7	912.8	913.9	914.3	913.8	913.4	912.9	912.5	911.8
142.5°	943.0	944.2	945.3	946.4	947.5	947.9	947.6	947.4	947.1	946.8	946.0
145°	993.4	994.0	994.7	995.4	996.0	996.4	996.4	996.4	996.4	996.4	995.7
147.5°	1036.3	1037.8	1039.3	1040.8	1042.3	1042.8	1042.3	1041.7	1041.2	1040.7	1040.1
150°	1068.2	1068.7	1069.1	1069.6	1070.0	1070.2	1070.2	1070.2	1070.2	1070.2	1069.3
152.5°	1094.6	1095.4	1096.2	1097.0	1097.8	1097.9	1097.4	1096.9	1096.3	1095.8	1095.4
155°	1132.1	1133.2	1134.3	1135.5	1136.6	1136.7	1135.8	1134.9	1134.0	1133.1	1132.9
157.5°	1163.5	1164.9	1166.4	1167.9	1169.3	1169.6	1168.7	1167.8	1167.0	1166.1	1165.9
160°	1185.0	1186.2	1187.3	1188.4	1189.5	1189.6	1188.7	1187.8	1186.9	1186.0	1185.8
162.5°	1203.4	1204.7	1206.0	1207.3	1208.6	1208.7	1207.6	1206.5	1205.5	1204.4	1204.4
165°	1228.0	1229.3	1230.6	1232.0	1233.3	1233.5	1232.6	1231.7	1230.9	1230.0	1229.7
167.5°	1247.5	1248.9	1250.3	1251.7	1253.0	1253.1	1251.7	1250.4	1249.1	1247.7	1247.7
170°	1257.9	1259.5	1261.0	1262.6	1264.1	1264.2	1262.9	1261.6	1260.3	1258.9	1258.9
172.5°	1266.7	1268.1	1269.5	1270.8	1272.2	1272.2	1270.9	1269.6	1268.2	1266.9	1266.9
175°	1274.9	1276.4	1278.0	1279.6	1281.1	1281.2	1279.9	1278.6	1277.2	1275.9	1275.9
177.5°	1279.7	1280.9	1282.2	1283.4	1284.7	1284.7	1283.7	1282.6	1281.6	1280.5	1280.7
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1258.7	1255.8	1252.4	1246.6	1239.6	1235.8	1230.0	1226.3	1218.8	1212.6	1205.9
5°	1322.5	1309.0	1296.6	1280.5	1262.8	1251.4	1237.9	1222.8	1207.3	1191.2	1173.5
7.5°	1388.7	1364.8	1338.8	1310.9	1283.6	1258.5	1234.5	1210.9	1188.9	1162.3	1139.8
10°	1433.1	1403.0	1370.8	1332.9	1296.1	1263.9	1231.2	1202.6	1173.5	1142.4	1114.8
12.5°	1477.6	1437.5	1392.0	1350.4	1306.0	1267.2	1228.7	1192.2	1155.7	1121.2	1089.1
15°	1509.0	1473.6	1431.6	1372.4	1322.5	1269.1	1218.2	1170.9	1126.8	1088.4	1047.9
17.5°	1529.6	1484.1	1439.0	1382.2	1316.8	1257.0	1199.4	1145.3	1095.5	1046.8	1007.8
20°	1533.4	1486.6	1439.4	1383.8	1316.8	1248.3	1190.7	1125.7	1072.3	1021.9	974.1
22.5°	1532.1	1479.2	1427.7	1370.5	1305.2	1242.1	1172.4	1106.2	1048.2	998.6	948.8
25°	1520.4	1463.8	1399.4	1341.8	1277.4	1210.4	1139.8	1071.2	1012.0	955.4	906.1
27.5°	1510.6	1437.2	1364.3	1297.1	1234.9	1173.5	1105.9	1035.7	970.1	912.7	866.2
30°	1498.6	1418.1	1336.0	1265.9	1202.1	1142.4	1078.5	1010.0	941.4	885.3	835.5
32.5°	1487.8	1394.0	1307.4	1231.1	1163.4	1105.4	1046.5	981.3	914.0	857.1	807.2
35°	1466.9	1358.4	1259.2	1173.0	1100.8	1041.1	991.8	931.0	869.2	814.2	766.4
37.5°	1440.4	1311.6	1205.2	1114.8	1035.7	972.8	926.9	880.2	820.9	767.9	724.7
40°	1419.6	1278.4	1165.7	1073.3	991.3	925.8	883.3	839.1	789.8	740.5	694.8
42.5°	1393.5	1248.5	1125.9	1026.4	945.1	881.4	836.7	799.2	755.7	709.7	667.3
45°	1345.4	1194.3	1061.4	954.4	872.3	809.5	763.3	735.3	702.6	658.9	623.1
47.5°	1274.7	1129.2	991.7	881.3	796.6	738.4	695.1	668.2	645.1	612.7	580.2
50°	1211.9	1080.6	941.4	831.8	747.2	688.5	648.6	624.1	604.4	579.5	552.0
52.5°	1141.7	1019.5	892.0	783.7	699.9	642.0	602.9	581.4	565.0	547.1	520.0
55°	1030.2	926.4	808.0	705.1	627.8	571.2	536.9	518.2	504.7	491.2	474.6
57.5°	907.3	826.1	721.2	627.3	556.0	504.5	472.5	454.3	443.9	436.9	427.1
60°	820.9	751.4	661.0	575.3	505.8	460.1	428.9	414.9	406.1	400.3	393.1
62.5°	740.8	683.7	599.9	521.7	460.9	417.7	389.9	376.3	367.8	365.0	359.0
65°	622.6	578.5	509.4	444.5	392.6	355.7	332.3	319.3	314.1	311.0	311.6
67.5°	506.2	479.3	423.8	368.5	327.0	296.1	277.4	267.4	264.8	260.7	260.6
70°	435.1	414.9	368.2	319.9	283.0	259.1	242.5	232.1	229.5	227.4	226.9
72.5°	372.4	354.7	314.1	275.4	242.3	221.3	207.6	201.4	197.1	195.9	195.8
75°	279.9	270.0	237.8	207.2	184.3	169.8	160.5	154.7	151.6	151.1	151.6
77.5°	199.0	190.4	169.9	148.2	133.8	122.8	114.9	112.9	109.4	109.5	108.9
80°	149.5	143.8	130.9	113.7	101.8	92.4	88.3	84.6	83.6	82.0	83.6
82.5°	108.4	102.3	93.5	82.6	72.7	67.1	62.9	61.8	61.2	60.4	60.8
85°	53.5	54.0	48.8	40.5	36.3	33.2	30.6	30.6	30.1	29.6	30.1
87.5°	20.9	19.7	17.7	16.2	13.7	12.1	11.4	11.4	10.5	10.5	11.2
90°	12.9	11.3	9.8	8.1	6.3	4.5	2.8	1.0	2.8	4.5	6.3
92.5°	34.5	32.6	30.7	29.1	27.9	26.6	25.4	24.2	25.4	26.6	27.9
95°	72.4	70.2	68.0	66.7	66.2	65.8	65.3	64.9	65.3	65.8	66.2
97.5°	116.3	113.2	110.2	108.5	108.4	108.2	108.0	107.8	108.0	108.2	108.4
100°	147.0	144.1	141.2	139.8	139.8	139.8	139.8	139.8	139.8	139.8	139.8
102.5°	181.8	180.3	178.8	177.7	176.8	175.9	175.0	174.1	175.0	175.9	176.8
105°	235.9	234.6	233.3	232.1	231.0	229.8	228.7	227.6	228.7	229.8	231.0
107.5°	294.3	293.2	292.2	291.2	290.1	288.9	287.8	286.7	287.8	288.9	290.1
110°	334.1	333.4	332.8	331.9	330.8	329.7	328.6	327.5	328.6	329.7	330.8



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	373.7	372.9	372.0	371.3	370.7	370.1	369.6	369.0	369.6	370.1	370.7
115°	435.4	434.9	434.5	433.8	433.0	432.1	431.2	430.3	431.2	432.1	433.0
117.5°	494.6	494.2	493.8	493.4	493.0	492.6	492.2	491.8	492.2	492.6	493.0
120°	535.7	535.4	535.2	534.6	533.5	532.3	531.2	530.1	531.2	532.3	533.5
122.5°	574.9	574.3	573.7	573.3	572.9	572.5	572.1	571.7	572.1	572.5	572.9
125°	634.5	634.3	634.1	633.3	632.0	630.6	629.3	628.0	629.3	630.6	632.0
127.5°	691.9	691.7	691.4	690.9	690.1	689.4	688.6	687.9	688.6	689.4	690.1
130°	729.9	729.5	729.0	728.2	727.1	726.0	724.9	723.8	724.9	726.0	727.1
132.5°	767.7	767.8	767.9	767.0	765.2	763.4	761.6	759.7	761.6	763.4	765.2
135°	823.2	823.0	822.8	822.0	820.6	819.3	818.0	816.7	818.0	819.3	820.6
137.5°	877.2	876.7	876.2	875.3	874.0	872.7	871.4	870.2	871.4	872.7	874.0
140°	911.2	910.5	909.8	908.9	907.8	906.7	905.6	904.5	905.6	906.7	907.8
142.5°	945.2	944.3	943.5	942.6	941.6	940.7	939.8	938.8	939.8	940.7	941.6
145°	995.0	994.4	993.7	992.9	992.0	991.1	990.3	989.4	990.3	991.1	992.0
147.5°	1039.6	1039.1	1038.6	1038.0	1037.6	1037.1	1036.6	1036.1	1036.6	1037.1	1037.6
150°	1068.5	1067.6	1066.7	1066.4	1066.6	1066.8	1067.0	1067.2	1067.0	1066.8	1066.6
152.5°	1095.1	1094.7	1094.4	1094.0	1093.7	1093.4	1093.1	1092.8	1093.1	1093.4	1093.7
155°	1132.7	1132.5	1132.2	1132.1	1132.1	1132.1	1132.1	1132.1	1132.1	1132.1	1132.1
157.5°	1165.6	1165.4	1165.2	1165.3	1165.8	1166.3	1166.8	1167.3	1166.8	1166.3	1165.8
160°	1185.6	1185.4	1185.2	1185.4	1186.0	1186.7	1187.4	1188.0	1187.4	1186.7	1186.0
162.5°	1204.3	1204.3	1204.2	1204.5	1204.9	1205.4	1205.9	1206.4	1205.9	1205.4	1204.9
165°	1229.5	1229.3	1229.1	1229.2	1229.6	1230.1	1230.5	1231.0	1230.5	1230.1	1229.6
167.5°	1247.7	1247.7	1247.7	1248.2	1249.1	1250.0	1250.8	1251.7	1250.8	1250.0	1249.1
170°	1258.9	1258.9	1258.9	1259.4	1260.3	1261.1	1262.0	1262.9	1262.0	1261.1	1260.3
172.5°	1266.9	1266.9	1266.9	1267.4	1268.2	1269.1	1270.0	1270.9	1270.0	1269.1	1268.2
175°	1275.9	1275.9	1275.9	1276.3	1277.2	1278.1	1279.0	1279.9	1279.0	1278.1	1277.2
177.5°	1280.8	1281.0	1281.2	1281.6	1282.3	1283.1	1283.8	1284.5	1283.8	1283.1	1282.3
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1202.2	1197.6	1193.9	1185.6	1181.0	1174.8	1169.8	1175.2	1169.4	1171.9	1168.1
5°	1164.7	1150.2	1139.8	1124.7	1111.7	1099.8	1091.0	1089.4	1085.2	1083.2	1076.9
7.5°	1119.6	1101.4	1083.6	1063.9	1047.2	1030.3	1019.5	1010.6	1004.7	996.9	991.6
10°	1093.0	1068.6	1047.9	1024.0	1003.2	985.0	970.5	963.2	956.5	946.6	943.0
12.5°	1060.2	1035.0	1009.6	984.1	964.2	943.9	931.4	920.4	915.8	904.6	903.5
15°	1020.9	983.0	958.0	932.1	904.5	887.9	877.5	865.6	860.4	852.6	846.9
17.5°	973.9	940.1	908.9	882.0	858.4	844.4	831.5	823.3	814.4	809.3	800.0
20°	939.9	907.7	876.5	847.9	829.8	813.7	803.3	795.5	786.2	783.6	774.2
22.5°	911.2	875.7	845.8	821.8	801.9	783.8	772.5	767.3	760.8	752.8	750.9
25°	864.6	827.7	802.3	778.4	760.7	744.1	736.3	729.6	723.3	717.6	715.5
27.5°	824.3	791.3	761.1	739.5	724.2	709.0	702.1	693.9	689.4	684.8	679.2
30°	796.0	762.3	735.8	715.0	698.4	684.9	677.6	671.9	667.8	663.6	660.5
32.5°	766.9	735.7	710.0	689.7	673.1	662.9	656.4	652.4	647.8	642.8	638.9
35°	728.5	694.2	669.3	651.7	638.7	630.9	623.6	620.0	614.8	614.8	610.6
37.5°	685.2	655.6	633.6	617.5	605.9	598.9	591.0	588.5	585.2	583.0	581.6
40°	659.5	631.9	611.2	595.1	582.6	576.9	570.7	566.5	564.4	561.8	560.8
42.5°	632.9	606.6	586.7	571.8	561.0	556.1	550.3	547.4	543.2	539.8	539.2
45°	592.5	567.0	548.9	536.9	527.6	521.9	518.2	512.0	509.9	505.8	505.2
47.5°	554.1	529.7	511.9	502.1	493.9	489.2	483.5	477.3	474.9	472.8	472.6
50°	525.5	503.2	486.5	477.2	469.4	462.7	456.9	452.8	451.2	451.2	452.3
52.5°	496.4	477.4	463.3	451.9	444.5	437.3	432.0	429.5	427.1	429.6	431.5
55°	453.8	434.6	424.2	413.3	406.1	397.7	395.2	394.1	392.6	396.7	398.8
57.5°	408.8	395.3	383.1	372.3	365.8	361.0	357.5	356.8	359.7	361.7	368.5
60°	380.1	364.5	353.6	345.3	337.5	334.4	333.4	332.3	334.4	340.1	348.9
62.5°	348.5	335.9	324.1	317.9	312.2	307.0	306.8	307.4	311.6	318.1	326.9
65°	302.2	291.3	283.5	276.2	271.6	268.5	269.5	271.6	276.2	285.1	294.9
67.5°	255.2	247.7	240.7	234.8	230.3	230.3	231.4	234.5	240.0	250.2	259.2
70°	224.8	216.5	210.8	208.2	204.6	202.5	205.6	210.8	215.5	224.8	232.6
72.5°	194.5	187.5	183.0	181.2	179.7	178.0	179.0	184.6	191.0	200.3	209.4
75°	149.5	146.9	143.8	141.8	140.2	141.2	142.3	147.5	152.7	162.5	172.9
77.5°	109.1	106.4	104.6	104.1	103.2	103.7	106.7	110.5	115.6	122.8	130.6
80°	82.6	81.5	80.5	80.0	80.0	80.5	84.6	87.2	91.9	98.7	104.9
82.5°	60.1	59.5	59.3	59.2	59.6	59.7	62.2	65.6	69.5	74.6	80.0
85°	31.7	30.6	32.2	32.7	31.7	33.2	34.3	36.3	37.9	40.5	43.1
87.5°	12.0	13.2	13.1	13.8	14.1	15.2	15.0	16.9	18.0	19.0	18.8
90°	8.1	9.8	11.3	12.9	14.4	16.0	17.1	18.2	19.3	20.4	21.3
92.5°	29.1	30.7	32.6	34.5	36.4	38.3	39.8	41.3	42.7	44.2	45.2
95°	66.7	68.0	70.2	72.4	74.7	76.9	78.4	80.0	81.5	83.1	84.1
97.5°	108.5	110.2	113.2	116.3	119.3	122.4	123.9	125.3	126.8	128.3	129.1
100°	139.8	141.2	144.1	147.0	149.9	152.7	154.7	156.7	158.7	160.7	162.0
102.5°	177.7	178.8	180.3	181.8	183.2	184.7	186.9	189.0	191.2	193.4	194.8
105°	232.1	233.3	234.6	235.9	237.3	238.6	239.9	241.3	242.6	243.9	244.9
107.5°	291.2	292.2	293.2	294.3	295.3	296.3	297.0	297.6	298.3	299.0	299.3
110°	331.9	332.8	333.4	334.1	334.8	335.4	336.1	336.8	337.4	338.1	338.3



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	371.3	372.0	372.9	373.7	374.5	375.4	375.7	376.0	376.3	376.6	376.6
115°	433.8	434.5	434.9	435.4	435.8	436.3	436.1	435.8	435.6	435.4	435.2
117.5°	493.4	493.8	494.2	494.6	495.0	495.4	495.6	495.7	495.9	496.1	495.7
120°	534.6	535.2	535.4	535.7	535.9	536.1	536.1	536.1	536.1	536.1	535.7
122.5°	573.3	573.7	574.3	574.9	575.5	576.0	575.9	575.7	575.5	575.3	574.9
125°	633.3	634.1	634.3	634.5	634.7	635.0	634.5	634.1	633.6	633.2	632.8
127.5°	690.9	691.4	691.7	691.9	692.2	692.5	692.2	692.0	691.8	691.6	691.2
130°	728.2	729.0	729.5	729.9	730.3	730.8	730.6	730.3	730.1	729.9	729.6
132.5°	767.0	767.9	767.8	767.7	767.6	767.5	767.3	767.1	766.9	766.6	766.2
135°	822.0	822.8	823.0	823.2	823.4	823.6	823.6	823.6	823.6	823.6	823.2
137.5°	875.3	876.2	876.7	877.2	877.7	878.1	878.4	878.7	878.9	879.2	878.8
140°	908.9	909.8	910.5	911.2	911.8	912.5	912.9	913.4	913.8	914.3	913.9
142.5°	942.6	943.5	944.3	945.2	946.0	946.8	947.1	947.4	947.6	947.9	947.5
145°	992.9	993.7	994.4	995.0	995.7	996.4	996.4	996.4	996.4	996.4	996.0
147.5°	1038.0	1038.6	1039.1	1039.6	1040.1	1040.7	1041.2	1041.7	1042.3	1042.8	1042.3
150°	1066.4	1066.7	1067.6	1068.5	1069.3	1070.2	1070.2	1070.2	1070.2	1070.2	1070.0
152.5°	1094.0	1094.4	1094.7	1095.1	1095.4	1095.8	1096.3	1096.9	1097.4	1097.9	1097.8
155°	1132.1	1132.2	1132.5	1132.7	1132.9	1133.1	1134.0	1134.9	1135.8	1136.7	1136.6
157.5°	1165.3	1165.2	1165.4	1165.6	1165.9	1166.1	1167.0	1167.8	1168.7	1169.6	1169.3
160°	1185.4	1185.2	1185.4	1185.6	1185.8	1186.0	1186.9	1187.8	1188.7	1189.6	1189.5
162.5°	1204.5	1204.2	1204.3	1204.3	1204.4	1204.4	1205.5	1206.5	1207.6	1208.7	1208.6
165°	1229.2	1229.1	1229.3	1229.5	1229.7	1230.0	1230.9	1231.7	1232.6	1233.5	1233.3
167.5°	1248.2	1247.7	1247.7	1247.7	1247.7	1247.7	1249.1	1250.4	1251.7	1253.1	1253.0
170°	1259.4	1258.9	1258.9	1258.9	1258.9	1258.9	1260.3	1261.6	1262.9	1264.2	1264.1
172.5°	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.2	1269.6	1270.9	1272.2	1272.2
175°	1276.3	1275.9	1275.9	1275.9	1275.9	1275.9	1277.2	1278.6	1279.9	1281.2	1281.1
177.5°	1281.6	1281.2	1281.0	1280.8	1280.7	1280.5	1281.6	1282.6	1283.7	1284.7	1284.7
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1165.6	1168.5	1166.0	1169.4	1166.0	1168.5	1165.6	1168.1	1171.9	1169.4	1175.2
5°	1074.3	1069.7	1072.8	1070.7	1072.8	1069.7	1074.3	1076.9	1083.2	1085.2	1089.4
7.5°	990.0	985.5	980.5	978.1	980.5	985.5	990.0	991.6	996.9	1004.7	1010.6
10°	937.3	931.5	931.0	927.4	931.0	931.5	937.3	943.0	946.6	956.5	963.2
12.5°	898.6	893.3	887.4	885.9	887.4	893.3	898.6	903.5	904.6	915.8	920.4
15°	843.8	839.6	836.0	839.1	836.0	839.6	843.8	846.9	852.6	860.4	865.6
17.5°	798.2	794.8	794.1	790.3	794.1	794.8	798.2	800.0	809.3	814.4	823.3
20°	769.5	766.9	768.0	761.2	768.0	766.9	769.5	774.2	783.6	786.2	795.5
22.5°	746.7	741.6	741.0	739.6	741.0	741.6	746.7	750.9	752.8	760.8	767.3
25°	710.9	708.3	705.7	708.3	705.7	708.3	710.9	715.5	717.6	723.3	729.6
27.5°	679.6	676.5	675.8	676.1	675.8	676.5	679.6	679.2	684.8	689.4	693.9
30°	660.5	655.3	655.8	655.3	655.8	655.3	660.5	660.5	663.6	667.8	671.9
32.5°	639.7	636.2	635.5	634.5	635.5	636.2	639.7	638.9	642.8	647.8	652.4
35°	609.1	609.1	606.5	606.5	606.5	609.1	609.1	610.6	614.8	614.8	620.0
37.5°	580.3	579.8	578.2	578.5	578.2	579.8	580.3	581.6	583.0	585.2	588.5
40°	558.7	558.2	556.6	553.5	556.6	558.2	558.7	560.8	561.8	564.4	566.5
42.5°	537.9	536.2	535.5	534.4	535.5	536.2	537.9	539.2	539.8	543.2	547.4
45°	505.2	505.2	504.2	503.7	504.2	505.2	505.2	505.2	505.8	509.9	512.0
47.5°	473.5	474.4	476.4	476.1	476.4	474.4	473.5	472.6	472.8	474.9	477.3
50°	454.3	454.9	456.4	456.9	456.4	454.9	454.3	452.3	451.2	451.2	452.8
52.5°	433.2	436.2	438.1	437.8	438.1	436.2	433.2	431.5	429.6	427.1	429.5
55°	403.5	407.1	410.7	411.3	410.7	407.1	403.5	398.8	396.7	392.6	394.1
57.5°	374.1	379.2	383.0	384.2	383.0	379.2	374.1	368.5	361.7	359.7	356.8
60°	354.1	360.9	365.6	367.6	365.6	360.9	354.1	348.9	340.1	334.4	332.3
62.5°	335.0	342.6	347.3	347.7	347.3	342.6	335.0	326.9	318.1	311.6	307.4
65°	303.8	311.6	315.7	318.8	315.7	311.6	303.8	294.9	285.1	276.2	271.6
67.5°	270.1	277.9	282.5	285.0	282.5	277.9	270.1	259.2	250.2	240.0	234.5
70°	245.6	253.4	259.6	261.7	259.6	253.4	245.6	232.6	224.8	215.5	210.8
72.5°	221.5	228.5	233.5	235.9	233.5	228.5	221.5	209.4	200.3	191.0	184.6
75°	179.7	189.0	193.7	196.3	193.7	189.0	179.7	172.9	162.5	152.7	147.5
77.5°	138.5	147.1	149.9	151.2	149.9	147.1	138.5	130.6	122.8	115.6	110.5
80°	111.1	116.3	119.9	120.5	119.9	116.3	111.1	104.9	98.7	91.9	87.2
82.5°	85.4	89.7	90.9	92.2	90.9	89.7	85.4	80.0	74.6	69.5	65.6
85°	46.7	48.8	49.3	48.8	49.3	48.8	46.7	43.1	40.5	37.9	36.3
87.5°	19.8	19.5	19.6	20.6	19.6	19.5	19.8	18.8	19.0	18.0	16.9
90°	22.0	22.6	23.3	24.0	23.3	22.6	22.0	21.3	20.4	19.3	18.2
92.5°	45.7	46.1	46.6	47.1	46.6	46.1	45.7	45.2	44.2	42.7	41.3
95°	84.5	85.0	85.4	85.9	85.4	85.0	84.5	84.1	83.1	81.5	80.0
97.5°	129.4	129.7	129.9	130.2	129.9	129.7	129.4	129.1	128.3	126.8	125.3
100°	162.4	162.8	163.3	163.7	163.3	162.8	162.4	162.0	160.7	158.7	156.7
102.5°	195.4	196.0	196.7	197.3	196.7	196.0	195.4	194.8	193.4	191.2	189.0
105°	245.6	246.3	246.9	247.6	246.9	246.3	245.6	244.9	243.9	242.6	241.3
107.5°	299.2	299.2	299.2	299.1	299.2	299.2	299.2	299.3	299.0	298.3	297.6
110°	338.1	337.9	337.7	337.4	337.7	337.9	338.1	338.3	338.1	337.4	336.8



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	376.2	375.8	375.4	375.0	375.4	375.8	376.2	376.6	376.6	376.3	376.0
115°	434.9	434.7	434.5	434.3	434.5	434.7	434.9	435.2	435.4	435.6	435.8
117.5°	494.8	494.0	493.1	492.2	493.1	494.0	494.8	495.7	496.1	495.9	495.7
120°	534.8	533.9	533.0	532.1	533.0	533.9	534.8	535.7	536.1	536.1	536.1
122.5°	574.2	573.5	572.8	572.1	572.8	573.5	574.2	574.9	575.3	575.5	575.7
125°	632.6	632.4	632.2	632.0	632.2	632.4	632.6	632.8	633.2	633.6	634.1
127.5°	690.8	690.3	689.9	689.5	689.9	690.3	690.8	691.2	691.6	691.8	692.0
130°	729.1	728.7	728.2	727.8	728.2	728.7	729.1	729.6	729.9	730.1	730.3
132.5°	765.6	765.0	764.4	763.7	764.4	765.0	765.6	766.2	766.6	766.9	767.1
135°	822.3	821.4	820.5	819.6	820.5	821.4	822.3	823.2	823.6	823.6	823.6
137.5°	877.7	876.6	875.5	874.4	875.5	876.6	877.7	878.8	879.2	878.9	878.7
140°	912.8	911.7	910.6	909.5	910.6	911.7	912.8	913.9	914.3	913.8	913.4
142.5°	946.4	945.3	944.2	943.0	944.2	945.3	946.4	947.5	947.9	947.6	947.4
145°	995.4	994.7	994.0	993.4	994.0	994.7	995.4	996.0	996.4	996.4	996.4
147.5°	1040.8	1039.3	1037.8	1036.3	1037.8	1039.3	1040.8	1042.3	1042.8	1042.3	1041.7
150°	1069.6	1069.1	1068.7	1068.2	1068.7	1069.1	1069.6	1070.0	1070.2	1070.2	1070.2
152.5°	1097.0	1096.2	1095.4	1094.6	1095.4	1096.2	1097.0	1097.8	1097.9	1097.4	1096.9
155°	1135.5	1134.3	1133.2	1132.1	1133.2	1134.3	1135.5	1136.6	1136.7	1135.8	1134.9
157.5°	1167.9	1166.4	1164.9	1163.5	1164.9	1166.4	1167.9	1169.3	1169.6	1168.7	1167.8
160°	1188.4	1187.3	1186.2	1185.0	1186.2	1187.3	1188.4	1189.5	1189.6	1188.7	1187.8
162.5°	1207.3	1206.0	1204.7	1203.4	1204.7	1206.0	1207.3	1208.6	1208.7	1207.6	1206.5
165°	1232.0	1230.6	1229.3	1228.0	1229.3	1230.6	1232.0	1233.3	1233.5	1232.6	1231.7
167.5°	1251.7	1250.3	1248.9	1247.5	1248.9	1250.3	1251.7	1253.0	1253.1	1251.7	1250.4
170°	1262.6	1261.0	1259.5	1257.9	1259.5	1261.0	1262.6	1264.1	1264.2	1262.9	1261.6
172.5°	1270.8	1269.5	1268.1	1266.7	1268.1	1269.5	1270.8	1272.2	1272.2	1270.9	1269.6
175°	1279.6	1278.0	1276.4	1274.9	1276.4	1278.0	1279.6	1281.1	1281.2	1279.9	1278.6
177.5°	1283.4	1282.2	1280.9	1279.7	1280.9	1282.2	1283.4	1284.7	1284.7	1283.7	1282.6
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1169.8	1174.8	1181.0	1185.6	1193.9	1197.6	1202.2	1205.9	1212.6	1218.8	1226.3
5°	1091.0	1099.8	1111.7	1124.7	1139.8	1150.2	1164.7	1173.5	1191.2	1207.3	1222.8
7.5°	1019.5	1030.3	1047.2	1063.9	1083.6	1101.4	1119.6	1139.8	1162.3	1188.9	1210.9
10°	970.5	985.0	1003.2	1024.0	1047.9	1068.6	1093.0	1114.8	1142.4	1173.5	1202.6
12.5°	931.4	943.9	964.2	984.1	1009.6	1035.0	1060.2	1089.1	1121.2	1155.7	1192.2
15°	877.5	887.9	904.5	932.1	958.0	983.0	1020.9	1047.9	1088.4	1126.8	1170.9
17.5°	831.5	844.4	858.4	882.0	908.9	940.1	973.9	1007.8	1046.8	1095.5	1145.3
20°	803.3	813.7	829.8	847.9	876.5	907.7	939.9	974.1	1021.9	1072.3	1125.7
22.5°	772.5	783.8	801.9	821.8	845.8	875.7	911.2	948.8	998.6	1048.2	1106.2
25°	736.3	744.1	760.7	778.4	802.3	827.7	864.6	906.1	955.4	1012.0	1071.2
27.5°	702.1	709.0	724.2	739.5	761.1	791.3	824.3	866.2	912.7	970.1	1035.7
30°	677.6	684.9	698.4	715.0	735.8	762.3	796.0	835.5	885.3	941.4	1010.0
32.5°	656.4	662.9	673.1	689.7	710.0	735.7	766.9	807.2	857.1	914.0	981.3
35°	623.6	630.9	638.7	651.7	669.3	694.2	728.5	766.4	814.2	869.2	931.0
37.5°	591.0	598.9	605.9	617.5	633.6	655.6	685.2	724.7	767.9	820.9	880.2
40°	570.7	576.9	582.6	595.1	611.2	631.9	659.5	694.8	740.5	789.8	839.1
42.5°	550.3	556.1	561.0	571.8	586.7	606.6	632.9	667.3	709.7	755.7	799.2
45°	518.2	521.9	527.6	536.9	548.9	567.0	592.5	623.1	658.9	702.6	735.3
47.5°	483.5	489.2	493.9	502.1	511.9	529.7	554.1	580.2	612.7	645.1	668.2
50°	456.9	462.7	469.4	477.2	486.5	503.2	525.5	552.0	579.5	604.4	624.1
52.5°	432.0	437.3	444.5	451.9	463.3	477.4	496.4	520.0	547.1	565.0	581.4
55°	395.2	397.7	406.1	413.3	424.2	434.6	453.8	474.6	491.2	504.7	518.2
57.5°	357.5	361.0	365.8	372.3	383.1	395.3	408.8	427.1	436.9	443.9	454.3
60°	333.4	334.4	337.5	345.3	353.6	364.5	380.1	393.1	400.3	406.1	414.9
62.5°	306.8	307.0	312.2	317.9	324.1	335.9	348.5	359.0	365.0	367.8	376.3
65°	269.5	268.5	271.6	276.2	283.5	291.3	302.2	311.6	311.0	314.1	319.3
67.5°	231.4	230.3	230.3	234.8	240.7	247.7	255.2	260.6	260.7	264.8	267.4
70°	205.6	202.5	204.6	208.2	210.8	216.5	224.8	226.9	227.4	229.5	232.1
72.5°	179.0	178.0	179.7	181.2	183.0	187.5	194.5	195.8	195.9	197.1	201.4
75°	142.3	141.2	140.2	141.8	143.8	146.9	149.5	151.6	151.1	151.6	154.7
77.5°	106.7	103.7	103.2	104.1	104.6	106.4	109.1	108.9	109.5	109.4	112.9
80°	84.6	80.5	80.0	80.0	80.5	81.5	82.6	83.6	82.0	83.6	84.6
82.5°	62.2	59.7	59.6	59.2	59.3	59.5	60.1	60.8	60.4	61.2	61.8
85°	34.3	33.2	31.7	32.7	32.2	30.6	31.7	30.1	29.6	30.1	30.6
87.5°	15.0	15.2	14.1	13.8	13.1	13.2	12.0	11.2	10.5	10.5	11.4
90°	17.1	16.0	14.4	12.9	11.3	9.8	8.1	6.3	4.5	2.8	1.0
92.5°	39.8	38.3	36.4	34.5	32.6	30.7	29.1	27.9	26.6	25.4	24.2
95°	78.4	76.9	74.7	72.4	70.2	68.0	66.7	66.2	65.8	65.3	64.9
97.5°	123.9	122.4	119.3	116.3	113.2	110.2	108.5	108.4	108.2	108.0	107.8
100°	154.7	152.7	149.9	147.0	144.1	141.2	139.8	139.8	139.8	139.8	139.8
102.5°	186.9	184.7	183.2	181.8	180.3	178.8	177.7	176.8	175.9	175.0	174.1
105°	239.9	238.6	237.3	235.9	234.6	233.3	232.1	231.0	229.8	228.7	227.6
107.5°	297.0	296.3	295.3	294.3	293.2	292.2	291.2	290.1	288.9	287.8	286.7
110°	336.1	335.4	334.8	334.1	333.4	332.8	331.9	330.8	329.7	328.6	327.5



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	375.7	375.4	374.5	373.7	372.9	372.0	371.3	370.7	370.1	369.6	369.0
115°	436.1	436.3	435.8	435.4	434.9	434.5	433.8	433.0	432.1	431.2	430.3
117.5°	495.6	495.4	495.0	494.6	494.2	493.8	493.4	493.0	492.6	492.2	491.8
120°	536.1	536.1	535.9	535.7	535.4	535.2	534.6	533.5	532.3	531.2	530.1
122.5°	575.9	576.0	575.5	574.9	574.3	573.7	573.3	572.9	572.5	572.1	571.7
125°	634.5	635.0	634.7	634.5	634.3	634.1	633.3	632.0	630.6	629.3	628.0
127.5°	692.2	692.5	692.2	691.9	691.7	691.4	690.9	690.1	689.4	688.6	687.9
130°	730.6	730.8	730.3	729.9	729.5	729.0	728.2	727.1	726.0	724.9	723.8
132.5°	767.3	767.5	767.6	767.7	767.8	767.9	767.0	765.2	763.4	761.6	759.7
135°	823.6	823.6	823.4	823.2	823.0	822.8	822.0	820.6	819.3	818.0	816.7
137.5°	878.4	878.1	877.7	877.2	876.7	876.2	875.3	874.0	872.7	871.4	870.2
140°	912.9	912.5	911.8	911.2	910.5	909.8	908.9	907.8	906.7	905.6	904.5
142.5°	947.1	946.8	946.0	945.2	944.3	943.5	942.6	941.6	940.7	939.8	938.8
145°	996.4	996.4	995.7	995.0	994.4	993.7	992.9	992.0	991.1	990.3	989.4
147.5°	1041.2	1040.7	1040.1	1039.6	1039.1	1038.6	1038.0	1037.6	1037.1	1036.6	1036.1
150°	1070.2	1070.2	1069.3	1068.5	1067.6	1066.7	1066.4	1066.6	1066.8	1067.0	1067.2
152.5°	1096.3	1095.8	1095.4	1095.1	1094.7	1094.4	1094.0	1093.7	1093.4	1093.1	1092.8
155°	1134.0	1133.1	1132.9	1132.7	1132.5	1132.2	1132.1	1132.1	1132.1	1132.1	1132.1
157.5°	1167.0	1166.1	1165.9	1165.6	1165.4	1165.2	1165.3	1165.8	1166.3	1166.8	1167.3
160°	1186.9	1186.0	1185.8	1185.6	1185.4	1185.2	1185.4	1186.0	1186.7	1187.4	1188.0
162.5°	1205.5	1204.4	1204.4	1204.3	1204.3	1204.2	1204.5	1204.9	1205.4	1205.9	1206.4
165°	1230.9	1230.0	1229.7	1229.5	1229.3	1229.1	1229.2	1229.6	1230.1	1230.5	1231.0
167.5°	1249.1	1247.7	1247.7	1247.7	1247.7	1247.7	1248.2	1249.1	1250.0	1250.8	1251.7
170°	1260.3	1258.9	1258.9	1258.9	1258.9	1258.9	1259.4	1260.3	1261.1	1262.0	1262.9
172.5°	1268.2	1266.9	1266.9	1266.9	1266.9	1266.9	1267.4	1268.2	1269.1	1270.0	1270.9
175°	1277.2	1275.9	1275.9	1275.9	1275.9	1275.9	1276.3	1277.2	1278.1	1279.0	1279.9
177.5°	1281.6	1280.5	1280.7	1280.8	1281.0	1281.2	1281.6	1282.3	1283.1	1283.8	1284.5
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1230.0	1235.8	1239.6	1246.6	1252.4	1255.8	1258.7	1261.2	1264.1	1266.6	1273.6
5°	1237.9	1251.4	1262.8	1280.5	1296.6	1309.0	1322.5	1334.5	1344.4	1358.4	1369.3
7.5°	1234.5	1258.5	1283.6	1310.9	1338.8	1364.8	1388.7	1411.0	1431.3	1455.8	1477.3
10°	1231.2	1263.9	1296.1	1332.9	1370.8	1403.0	1433.1	1463.8	1486.1	1517.3	1543.7
12.5°	1228.7	1267.2	1306.0	1350.4	1392.0	1437.5	1477.6	1499.9	1533.9	1558.8	1590.3
15°	1218.2	1269.1	1322.5	1372.4	1431.6	1473.6	1509.0	1552.6	1584.2	1615.9	1650.2
17.5°	1199.4	1257.0	1316.8	1382.2	1439.0	1484.1	1529.6	1571.7	1609.5	1652.0	1694.6
20°	1190.7	1248.3	1316.8	1383.8	1439.4	1486.6	1533.4	1579.6	1621.1	1675.6	1725.0
22.5°	1172.4	1242.1	1305.2	1370.5	1427.7	1479.2	1532.1	1584.6	1639.8	1701.4	1763.2
25°	1139.8	1210.4	1277.4	1341.8	1399.4	1463.8	1520.4	1590.5	1661.1	1742.6	1819.5
27.5°	1105.9	1173.5	1234.9	1297.1	1364.3	1437.2	1510.6	1590.2	1682.6	1785.5	1893.9
30°	1078.5	1142.4	1202.1	1265.9	1336.0	1418.1	1498.6	1593.1	1700.0	1815.8	1944.6
32.5°	1046.5	1105.4	1163.4	1231.1	1307.4	1394.0	1487.8	1591.4	1720.0	1851.6	1984.1
35°	991.8	1041.1	1100.8	1173.0	1259.2	1358.4	1466.9	1589.4	1736.9	1888.0	1999.7
37.5°	926.9	972.8	1035.7	1114.8	1205.2	1311.6	1440.4	1585.8	1742.4	1862.9	1898.9
40°	883.3	925.8	991.3	1073.3	1165.7	1278.4	1419.6	1573.3	1725.0	1801.8	1772.2
42.5°	836.7	881.4	945.1	1026.4	1125.9	1248.5	1393.5	1547.2	1674.3	1703.4	1601.1
45°	763.3	809.5	872.3	954.4	1061.4	1194.3	1345.4	1485.1	1558.3	1505.8	1347.5
47.5°	695.1	738.4	796.6	881.3	991.7	1129.2	1274.7	1386.1	1391.9	1266.8	1097.6
50°	648.6	688.5	747.2	831.8	941.4	1080.6	1211.9	1299.7	1260.2	1118.5	955.9
52.5°	602.9	642.0	699.9	783.7	892.0	1019.5	1141.7	1203.3	1129.0	983.5	844.6
55°	536.9	571.2	627.8	705.1	808.0	926.4	1030.2	1051.5	954.9	811.6	698.9
57.5°	472.5	504.5	556.0	627.3	721.2	826.1	907.3	902.8	800.7	677.7	588.3
60°	428.9	460.1	505.8	575.3	661.0	751.4	820.9	804.3	703.1	597.1	521.9
62.5°	389.9	417.7	460.9	521.7	599.9	683.7	740.8	716.3	617.1	524.4	464.9
65°	332.3	355.7	392.6	444.5	509.4	578.5	622.6	590.9	506.3	434.1	386.3
67.5°	277.4	296.1	327.0	368.5	423.8	479.3	506.2	474.3	406.6	353.9	318.5
70°	242.5	259.1	283.0	319.9	368.2	414.9	435.1	406.6	348.4	303.2	277.8
72.5°	207.6	221.3	242.3	275.4	314.1	354.7	372.4	345.1	297.3	259.2	235.4
75°	160.5	169.8	184.3	207.2	237.8	270.0	279.9	256.0	225.4	196.8	181.2
77.5°	114.9	122.8	133.8	148.2	169.9	190.4	199.0	185.2	161.5	143.4	130.6
80°	88.3	92.4	101.8	113.7	130.9	143.8	149.5	140.7	124.1	110.6	100.7
82.5°	62.9	67.1	72.7	82.6	93.5	102.3	108.4	102.5	90.5	79.9	74.1
85°	30.6	33.2	36.3	40.5	48.8	54.0	53.5	49.8	45.2	41.0	37.9
87.5°	11.4	12.1	13.7	16.2	17.7	19.7	20.9	20.3	19.0	18.0	16.9
90°	2.8	4.5	6.3	8.1	9.8	11.3	12.9	14.4	16.0	17.1	18.2
92.5°	25.4	26.6	27.9	29.1	30.7	32.6	34.5	36.4	38.3	39.8	41.3
95°	65.3	65.8	66.2	66.7	68.0	70.2	72.4	74.7	76.9	78.4	80.0
97.5°	108.0	108.2	108.4	108.5	110.2	113.2	116.3	119.3	122.4	123.9	125.3
100°	139.8	139.8	139.8	139.8	141.2	144.1	147.0	149.9	152.7	154.7	156.7
102.5°	175.0	175.9	176.8	177.7	178.8	180.3	181.8	183.2	184.7	186.9	189.0
105°	228.7	229.8	231.0	232.1	233.3	234.6	235.9	237.3	238.6	239.9	241.3
107.5°	287.8	288.9	290.1	291.2	292.2	293.2	294.3	295.3	296.3	297.0	297.6
110°	328.6	329.7	330.8	331.9	332.8	333.4	334.1	334.8	335.4	336.1	336.8



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	369.6	370.1	370.7	371.3	372.0	372.9	373.7	374.5	375.4	375.7	376.0
115°	431.2	432.1	433.0	433.8	434.5	434.9	435.4	435.8	436.3	436.1	435.8
117.5°	492.2	492.6	493.0	493.4	493.8	494.2	494.6	495.0	495.4	495.6	495.7
120°	531.2	532.3	533.5	534.6	535.2	535.4	535.7	535.9	536.1	536.1	536.1
122.5°	572.1	572.5	572.9	573.3	573.7	574.3	574.9	575.5	576.0	575.9	575.7
125°	629.3	630.6	632.0	633.3	634.1	634.3	634.5	634.7	635.0	634.5	634.1
127.5°	688.6	689.4	690.1	690.9	691.4	691.7	691.9	692.2	692.5	692.2	692.0
130°	724.9	726.0	727.1	728.2	729.0	729.5	729.9	730.3	730.8	730.6	730.3
132.5°	761.6	763.4	765.2	767.0	767.9	767.8	767.7	767.6	767.5	767.3	767.1
135°	818.0	819.3	820.6	822.0	822.8	823.0	823.2	823.4	823.6	823.6	823.6
137.5°	871.4	872.7	874.0	875.3	876.2	876.7	877.2	877.7	878.1	878.4	878.7
140°	905.6	906.7	907.8	908.9	909.8	910.5	911.2	911.8	912.5	912.9	913.4
142.5°	939.8	940.7	941.6	942.6	943.5	944.3	945.2	946.0	946.8	947.1	947.4
145°	990.3	991.1	992.0	992.9	993.7	994.4	995.0	995.7	996.4	996.4	996.4
147.5°	1036.6	1037.1	1037.6	1038.0	1038.6	1039.1	1039.6	1040.1	1040.7	1041.2	1041.7
150°	1067.0	1066.8	1066.6	1066.4	1066.7	1067.6	1068.5	1069.3	1070.2	1070.2	1070.2
152.5°	1093.1	1093.4	1093.7	1094.0	1094.4	1094.7	1095.1	1095.4	1095.8	1096.3	1096.9
155°	1132.1	1132.1	1132.1	1132.1	1132.2	1132.5	1132.7	1132.9	1133.1	1134.0	1134.9
157.5°	1166.8	1166.3	1165.8	1165.3	1165.2	1165.4	1165.6	1165.9	1166.1	1167.0	1167.8
160°	1187.4	1186.7	1186.0	1185.4	1185.2	1185.4	1185.6	1185.8	1186.0	1186.9	1187.8
162.5°	1205.9	1205.4	1204.9	1204.5	1204.2	1204.3	1204.3	1204.4	1204.4	1205.5	1206.5
165°	1230.5	1230.1	1229.6	1229.2	1229.1	1229.3	1229.5	1229.7	1230.0	1230.9	1231.7
167.5°	1250.8	1250.0	1249.1	1248.2	1247.7	1247.7	1247.7	1247.7	1247.7	1249.1	1250.4
170°	1262.0	1261.1	1260.3	1259.4	1258.9	1258.9	1258.9	1258.9	1258.9	1260.3	1261.6
172.5°	1270.0	1269.1	1268.2	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.2	1269.6
175°	1279.0	1278.1	1277.2	1276.3	1275.9	1275.9	1275.9	1275.9	1275.9	1277.2	1278.6
177.5°	1283.8	1283.1	1282.3	1281.6	1281.2	1281.0	1280.8	1280.7	1280.5	1281.6	1282.6
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1279.4	1282.8	1289.8	1287.3	1290.7	1292.3	1294.0
5°	1382.8	1399.4	1406.7	1405.6	1416.5	1413.9	1411.3
7.5°	1499.5	1517.0	1526.7	1538.9	1545.9	1546.4	1552.6
10°	1565.6	1588.4	1597.8	1610.7	1619.0	1623.7	1623.2
12.5°	1616.2	1634.1	1655.1	1661.4	1672.6	1678.5	1676.4
15°	1677.2	1705.8	1727.6	1738.5	1752.5	1756.6	1762.4
17.5°	1731.6	1769.9	1795.4	1829.2	1842.0	1849.8	1845.2
20°	1772.7	1823.1	1848.6	1889.1	1911.4	1923.3	1919.2
22.5°	1821.3	1875.9	1922.9	1958.0	1992.0	2008.1	2011.4
25°	1904.6	1979.4	2048.5	2094.7	2136.7	2146.6	2168.4
27.5°	1997.7	2085.9	2159.7	2208.3	2237.6	2248.6	2255.4
30°	2056.3	2144.0	2199.6	2230.7	2240.1	2239.0	2238.0
32.5°	2084.9	2139.9	2150.5	2141.8	2120.4	2102.4	2083.5
35°	2044.3	2003.3	1942.0	1863.1	1804.9	1746.3	1740.5
37.5°	1838.6	1707.4	1605.4	1491.5	1425.8	1385.2	1357.1
40°	1645.0	1496.0	1372.4	1276.3	1209.3	1182.9	1156.9
42.5°	1434.8	1292.4	1183.0	1102.7	1052.3	1022.9	1002.4
45°	1165.7	1040.1	954.4	896.2	856.3	833.4	820.4
47.5°	955.2	862.3	789.5	747.5	719.9	702.1	702.2
50°	842.2	753.4	705.1	671.9	648.0	634.0	636.6
52.5°	742.1	675.8	634.5	606.7	589.0	580.4	580.1
55°	620.5	572.7	545.7	525.5	513.5	503.7	505.8
57.5°	530.8	490.5	472.4	455.6	447.3	443.3	437.6
60°	475.1	444.0	428.4	414.9	406.6	403.5	397.7
62.5°	425.7	401.2	386.0	375.0	367.5	366.5	362.0
65°	357.8	339.1	325.6	320.4	312.6	310.5	310.5
67.5°	294.9	281.5	271.1	266.3	262.8	263.4	260.9
70°	255.5	244.6	237.8	232.6	230.0	230.5	228.5
72.5°	223.5	211.3	205.4	202.3	198.9	200.2	199.4
75°	169.3	163.0	159.9	156.8	154.7	153.7	152.7
77.5°	124.3	118.8	116.4	114.7	115.0	112.5	114.4
80°	96.1	91.4	89.8	87.2	86.7	86.7	86.2
82.5°	70.3	67.7	66.6	64.4	63.5	64.3	62.9
85°	36.3	34.3	33.8	33.8	32.7	31.7	34.3
87.5°	17.2	15.7	15.9	15.6	15.7	15.5	14.8
90°	19.3	20.4	21.3	22.0	22.6	23.3	24.0
92.5°	42.7	44.2	45.2	45.7	46.1	46.6	47.1
95°	81.5	83.1	84.1	84.5	85.0	85.4	85.9
97.5°	126.8	128.3	129.1	129.4	129.7	129.9	130.2
100°	158.7	160.7	162.0	162.4	162.8	163.3	163.7
102.5°	191.2	193.4	194.8	195.4	196.0	196.7	197.3
105°	242.6	243.9	244.9	245.6	246.3	246.9	247.6
107.5°	298.3	299.0	299.3	299.2	299.2	299.2	299.1
110°	337.4	338.1	338.3	338.1	337.9	337.7	337.4



TEST NUMBER: P333233

CATALOG NUMBER: S125DIP-S850D1035U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	376.3	376.6	376.6	376.2	375.8	375.4	375.0
115°	435.6	435.4	435.2	434.9	434.7	434.5	434.3
117.5°	495.9	496.1	495.7	494.8	494.0	493.1	492.2
120°	536.1	536.1	535.7	534.8	533.9	533.0	532.1
122.5°	575.5	575.3	574.9	574.2	573.5	572.8	572.1
125°	633.6	633.2	632.8	632.6	632.4	632.2	632.0
127.5°	691.8	691.6	691.2	690.8	690.3	689.9	689.5
130°	730.1	729.9	729.6	729.1	728.7	728.2	727.8
132.5°	766.9	766.6	766.2	765.6	765.0	764.4	763.7
135°	823.6	823.6	823.2	822.3	821.4	820.5	819.6
137.5°	878.9	879.2	878.8	877.7	876.6	875.5	874.4
140°	913.8	914.3	913.9	912.8	911.7	910.6	909.5
142.5°	947.6	947.9	947.5	946.4	945.3	944.2	943.0
145°	996.4	996.4	996.0	995.4	994.7	994.0	993.4
147.5°	1042.3	1042.8	1042.3	1040.8	1039.3	1037.8	1036.3
150°	1070.2	1070.2	1070.0	1069.6	1069.1	1068.7	1068.2
152.5°	1097.4	1097.9	1097.8	1097.0	1096.2	1095.4	1094.6
155°	1135.8	1136.7	1136.6	1135.5	1134.3	1133.2	1132.1
157.5°	1168.7	1169.6	1169.3	1167.9	1166.4	1164.9	1163.5
160°	1188.7	1189.6	1189.5	1188.4	1187.3	1186.2	1185.0
162.5°	1207.6	1208.7	1208.6	1207.3	1206.0	1204.7	1203.4
165°	1232.6	1233.5	1233.3	1232.0	1230.6	1229.3	1228.0
167.5°	1251.7	1253.1	1253.0	1251.7	1250.3	1248.9	1247.5
170°	1262.9	1264.2	1264.1	1262.6	1261.0	1259.5	1257.9
172.5°	1270.9	1272.2	1272.2	1270.8	1269.5	1268.1	1266.7
175°	1279.9	1281.2	1281.1	1279.6	1278.0	1276.4	1274.9
177.5°	1283.7	1284.7	1284.7	1283.4	1282.2	1280.9	1279.7
180°	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9	1282.9

(END OF REPORT)