

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333222

Luminaire Tested: **S125DIP-S850D590U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333222
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D590U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5539.3 lumens
Efficiency: N/A
Efficacy: 137.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333222

CATALOG NUMBER: S125DIP-S850D590U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333222

CATALOG NUMBER: S125DIP-S850D590U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	86	83	79	76	74	68	67	65	59	58	56	52
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	50	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	37
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	38	35	31
5	70	58	50	44	65	55	47	42	48	42	38	43	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8478	8478	8478
5°	8497	8416	8470
10°	8445	8357	8405
15°	8354	8256	8291
20°	8223	8115	8130
25°	8082	7948	7941
30°	7908	7768	7730
35°	7722	7574	7468
40°	7530	7363	7259
45°	7323	7172	7029
50°	7095	6939	6731
55°	6876	6677	6490
60°	6613	6412	6185
65°	6301	6094	5888
70°	6001	5727	5531
75°	5467	5288	5105
80°	4868	4790	4675
85°	4231	4313	4076



TEST NUMBER: P333222

CATALOG NUMBER: S125DIP-S850D590U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	2.2
10°-20°	349.6	6.3
20°-30°	516.2	9.3
30°-40°	602.4	10.9
40°-50°	605.0	10.9
50°-60°	531.1	9.6
60°-70°	395.7	7.1
70°-80°	226.3	4.1
80°-90°	67.4	1.2
90°-100°	205.1	3.7
100°-110°	440.9	8.0
110°-120°	413.8	7.5
120°-130°	335.3	6.1
130°-140°	269.1	4.9
140°-150°	203.1	3.7
150°-160°	142.9	2.6
160°-170°	84.3	1.5
170°-180°	27.4	0.5
0°-30°	989.7	17.9
0°-40°	1592.1	28.7
0°-60°	2728.2	49.3
0°-90°	3417.6	61.7
90°-120°	1059.7	19.1
90°-150°	1867.2	33.7
90°-180°	2122.0	38.3
0°-180°	5539.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1313	1313	1313	1313	1313	
5°	1311	1308	1298	1307	1306	124
15°	1249	1246	1235	1240	1240	352
25°	1134	1128	1115	1117	1114	522
35°	979	975	961	955	947	612
45°	802	797	785	773	770	618
55°	611	607	593	584	576	545
65°	412	410	399	390	385	409
75°	219	217	212	209	205	234
85°	57	58	58	57	55	64
90°	1	5	9	12	13	4
95°	19	56	505	229	134	20
105°	64	90	414	814	756	68
115°	115	139	332	716	842	113
125°	160	187	318	569	663	142
135°	187	225	316	477	551	145
145°	218	250	317	395	435	137
155°	249	268	309	349	364	114
165°	272	279	297	315	319	76
175°	282	282	285	288	287	27
180°	283	283	283	283	283	



TEST NUMBER: P333222

CATALOG NUMBER: S125DIP-S850D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1316.1	1315.5	1315.0	1314.4	1313.8	1312.6	1310.8	1309.0	1307.1	1305.3	1307.1
5°	1310.7	1310.2	1309.7	1309.3	1308.8	1307.4	1305.1	1302.8	1300.5	1298.2	1300.3
7.5°	1298.6	1298.2	1297.7	1297.2	1296.8	1295.3	1292.7	1290.2	1287.7	1285.1	1287.1
10°	1287.8	1287.4	1286.9	1286.4	1286.0	1284.5	1281.9	1279.4	1276.9	1274.3	1276.2
12.5°	1274.5	1273.7	1272.9	1272.0	1271.2	1269.6	1267.3	1264.9	1262.5	1260.2	1261.7
15°	1249.4	1248.7	1248.0	1247.3	1246.6	1245.0	1242.5	1239.9	1237.4	1234.8	1236.0
17.5°	1220.5	1219.5	1218.5	1217.5	1216.5	1214.6	1212.0	1209.4	1206.7	1204.1	1205.5
20°	1196.4	1196.0	1195.5	1195.0	1194.6	1192.8	1189.8	1186.8	1183.8	1180.8	1182.5
22.5°	1172.3	1171.5	1170.7	1169.8	1169.0	1167.2	1164.4	1161.5	1158.7	1155.9	1157.0
25°	1134.1	1133.0	1131.8	1130.6	1129.5	1127.4	1124.4	1121.4	1118.4	1115.4	1115.9
27.5°	1089.4	1088.8	1088.1	1087.4	1086.7	1084.8	1081.7	1078.6	1075.5	1072.4	1072.5
30°	1060.4	1059.7	1059.0	1058.3	1057.6	1055.5	1052.1	1048.6	1045.1	1041.7	1041.2
32.5°	1028.8	1027.7	1026.7	1025.6	1024.6	1022.5	1019.4	1016.3	1013.2	1010.1	1009.3
35°	979.4	978.4	977.5	976.6	975.7	973.6	970.4	967.1	963.9	960.7	959.5
37.5°	928.1	926.9	925.7	924.6	923.4	921.3	918.3	915.2	912.2	909.2	907.4
40°	893.2	892.0	890.9	889.7	888.5	886.4	883.1	879.9	876.7	873.4	871.4
42.5°	855.8	854.8	853.8	852.9	851.9	849.8	846.6	843.3	840.1	836.9	835.0
45°	801.8	800.8	799.9	799.0	798.1	796.2	793.5	790.7	787.9	785.2	782.4
47.5°	743.6	743.7	743.7	743.7	743.8	742.2	738.8	735.5	732.2	728.9	726.0
50°	706.2	705.5	704.8	704.1	703.5	701.7	699.0	696.2	693.4	690.6	687.6
52.5°	668.0	667.5	667.0	666.5	666.0	664.2	661.3	658.3	655.4	652.4	649.8
55°	610.7	610.0	609.3	608.6	607.9	605.9	602.7	599.5	596.2	593.0	590.9
57.5°	550.2	549.9	549.5	549.1	548.8	547.2	544.5	541.8	539.0	536.3	533.6
60°	512.0	511.1	510.2	509.2	508.3	506.6	504.0	501.5	499.0	496.4	494.1
62.5°	472.1	471.4	470.7	469.9	469.2	467.7	465.6	463.4	461.2	459.0	456.6
65°	412.3	411.8	411.4	410.9	410.5	409.0	406.4	403.9	401.3	398.8	396.7
67.5°	354.4	353.4	352.4	351.4	350.5	349.0	347.2	345.3	343.4	341.5	339.7
70°	317.8	316.6	315.5	314.3	313.2	311.6	309.5	307.4	305.3	303.3	301.9
72.5°	277.9	277.1	276.3	275.6	274.8	273.7	272.4	271.0	269.7	268.4	266.8
75°	219.1	218.7	218.2	217.8	217.3	216.5	215.3	214.2	213.0	211.9	211.2
77.5°	164.9	164.7	164.6	164.4	164.2	163.8	163.1	162.5	161.8	161.2	160.8
80°	130.9	130.9	130.9	130.9	130.9	130.6	130.2	129.7	129.2	128.8	128.6
82.5°	100.9	100.6	100.2	99.8	99.5	99.2	99.1	99.1	99.0	98.9	98.5
85°	57.1	57.4	57.6	57.8	58.0	58.2	58.2	58.2	58.2	58.2	57.9
87.5°	22.5	22.7	22.9	23.1	23.3	23.5	23.4	23.5	23.4	23.4	23.5
90°	0.6	1.1	2.3	3.4	4.6	5.7	6.3	7.4	8.0	9.1	9.7
92.5°	7.0	8.4	13.2	20.3	30.1	46.8	77.9	130.2	186.9	183.9	148.9
95°	18.8	19.4	24.0	30.2	42.8	68.5	129.5	255.0	412.4	505.4	494.6
97.5°	31.3	31.9	35.1	41.4	52.7	71.2	111.6	203.5	368.3	539.7	625.8
100°	39.9	41.1	43.4	49.6	60.5	77.6	110.7	184.8	328.6	515.1	657.7
102.5°	49.5	50.2	52.0	58.8	68.7	85.3	114.8	177.1	298.4	471.7	638.5
105°	64.5	64.5	67.3	73.0	82.1	98.1	123.2	174.0	269.2	413.6	577.3
107.5°	79.1	80.2	82.9	87.6	97.1	111.5	135.8	179.2	256.9	373.5	514.8
110°	89.6	90.7	93.0	98.1	106.7	121.5	144.9	184.2	253.3	354.8	479.2



TEST NUMBER: P333222

CATALOG NUMBER: S125DIP-S850D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	100.1	101.2	103.0	108.2	116.7	131.1	153.6	190.6	253.3	343.9	452.7
115°	115.2	116.4	118.1	123.2	131.8	146.0	167.1	200.2	255.0	332.0	423.8
117.5°	128.9	130.6	132.5	137.6	147.3	161.1	181.1	211.2	258.7	326.2	406.6
120°	138.0	139.8	142.0	147.2	156.9	171.1	191.1	218.5	262.4	323.4	397.0
122.5°	147.6	148.9	150.7	155.8	166.5	180.7	200.7	226.7	265.6	321.2	388.8
125°	159.7	160.9	163.7	168.8	179.7	194.5	213.3	237.9	271.0	318.3	377.6
127.5°	169.2	170.9	174.6	181.1	192.6	207.4	225.5	248.1	277.0	316.9	367.4
130°	175.1	176.8	181.4	188.8	200.8	215.6	233.3	255.0	280.7	316.0	360.5
132.5°	179.7	181.9	187.3	195.7	208.1	222.9	240.6	260.9	284.8	316.0	355.0
135°	187.1	189.4	196.2	205.4	217.3	232.7	250.4	269.2	290.3	316.0	348.5
137.5°	196.5	198.2	204.6	213.7	225.4	241.3	257.4	275.4	295.5	316.7	342.7
140°	201.9	203.6	210.5	219.6	230.5	245.9	262.4	279.5	297.8	317.2	340.0
142.5°	208.3	209.6	216.0	225.1	235.5	250.0	265.6	281.8	299.1	317.6	337.7
145°	217.9	219.0	224.7	232.7	243.0	256.1	271.0	285.2	300.6	317.2	334.3
147.5°	227.9	228.6	233.5	240.9	249.8	261.4	274.4	287.3	301.2	315.7	330.7
150°	233.9	235.0	239.0	246.4	254.4	264.1	276.7	288.6	301.2	314.3	328.0
152.5°	240.3	240.9	244.5	251.0	258.5	267.3	278.9	289.5	300.7	312.5	324.8
155°	248.7	248.7	252.1	257.8	263.5	271.5	281.2	290.3	299.5	309.2	319.4
157.5°	256.2	256.1	258.9	263.8	268.8	274.8	283.2	290.9	298.0	305.7	314.4
160°	261.3	260.7	263.0	267.0	271.5	276.7	284.1	290.9	296.6	303.5	310.3
162.5°	265.4	264.8	267.1	270.6	274.3	278.5	285.0	290.5	295.3	300.7	306.7
165°	271.5	270.4	272.1	274.9	277.2	280.7	285.2	289.8	293.2	296.6	301.2
167.5°	275.6	275.1	276.1	277.7	279.3	281.4	285.2	288.4	290.0	292.6	295.8
170°	278.4	277.8	278.4	279.5	280.7	282.4	285.2	287.5	288.6	290.3	292.6
172.5°	280.2	279.2	279.7	280.9	281.6	282.4	284.8	286.6	286.8	287.6	289.4
175°	282.4	281.2	281.8	282.4	282.4	282.4	284.1	285.2	284.6	284.6	285.2
177.5°	283.4	282.5	282.5	282.9	282.5	282.5	283.4	283.8	282.9	282.9	283.4
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9



TEST NUMBER: P333222

CATALOG NUMBER: S125DIP-S850D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1309.0	1310.8	1312.6	1313.5	1313.3	1313.1	1312.9	1312.7
5°	1302.4	1304.4	1306.5	1307.4	1307.2	1307.0	1306.7	1306.5
7.5°	1289.2	1291.2	1293.2	1294.1	1293.9	1293.7	1293.4	1293.2
10°	1278.0	1279.9	1281.7	1282.5	1282.3	1282.0	1281.8	1281.6
12.5°	1263.1	1264.6	1266.1	1266.8	1266.8	1266.7	1266.7	1266.6
15°	1237.2	1238.3	1239.5	1240.0	1240.0	1240.0	1240.0	1240.0
17.5°	1207.0	1208.4	1209.8	1210.0	1208.8	1207.7	1206.5	1205.4
20°	1184.1	1185.7	1187.3	1187.5	1186.4	1185.2	1184.1	1182.9
22.5°	1158.0	1159.1	1160.2	1160.3	1159.5	1158.7	1157.9	1157.2
25°	1116.3	1116.8	1117.3	1117.1	1116.5	1115.8	1115.1	1114.4
27.5°	1072.6	1072.7	1072.8	1072.5	1071.8	1071.1	1070.4	1069.7
30°	1040.8	1040.3	1039.8	1039.3	1038.6	1037.9	1037.2	1036.5
32.5°	1008.4	1007.6	1006.8	1005.7	1004.5	1003.2	1002.0	1000.8
35°	958.4	957.2	956.1	954.6	952.7	950.9	949.0	947.2
37.5°	905.7	904.0	902.3	900.9	899.9	898.8	897.8	896.7
40°	869.3	867.2	865.1	863.7	863.0	862.4	861.7	861.0
42.5°	833.1	831.2	829.3	827.8	826.8	825.7	824.6	823.6
45°	779.6	776.8	774.1	772.3	771.7	771.0	770.3	769.6
47.5°	723.2	720.4	717.6	715.4	713.8	712.2	710.5	708.9
50°	684.6	681.6	678.6	676.3	674.7	673.1	671.5	669.9
52.5°	647.2	644.5	641.9	639.7	637.9	636.1	634.3	632.5
55°	588.9	586.8	584.7	582.9	581.2	579.6	578.0	576.4
57.5°	531.0	528.3	525.6	523.8	522.9	522.1	521.2	520.3
60°	491.8	489.5	487.2	485.2	483.6	482.0	480.4	478.8
62.5°	454.1	451.6	449.1	447.2	446.0	444.7	443.5	442.2
65°	394.7	392.6	390.5	389.0	388.1	387.2	386.2	385.3
67.5°	338.0	336.2	334.5	333.3	332.8	332.2	331.6	331.1
70°	300.5	299.1	297.7	296.6	295.6	294.7	293.8	292.9
72.5°	265.2	263.7	262.1	260.8	259.9	259.0	258.1	257.1
75°	210.5	209.8	209.1	208.3	207.4	206.4	205.5	204.6
77.5°	160.4	159.9	159.5	159.0	158.3	157.7	157.1	156.4
80°	128.3	128.1	127.9	127.5	127.1	126.6	126.1	125.7
82.5°	98.0	97.6	97.2	97.0	96.9	96.8	96.7	96.6
85°	57.7	57.5	57.2	56.9	56.4	56.0	55.5	55.0
87.5°	23.7	23.8	23.9	23.9	23.6	23.2	22.9	22.6
90°	10.3	10.8	11.4	12.5	12.5	12.5	13.1	13.1
92.5°	101.1	73.4	55.2	46.8	39.5	38.1	37.3	36.4
95°	410.1	323.4	253.3	205.4	164.9	147.7	143.2	134.1
97.5°	610.8	550.0	481.7	415.0	379.8	347.8	331.3	324.0
100°	701.6	673.7	614.9	555.6	516.2	475.2	454.1	444.9
102.5°	732.2	749.4	721.2	681.1	639.0	609.8	586.9	580.0
105°	714.2	792.3	817.4	811.1	792.9	774.1	762.7	755.8
107.5°	649.8	754.1	818.6	848.3	857.6	857.5	853.7	849.1
110°	602.4	710.8	791.2	839.7	865.3	876.2	880.2	880.2



TEST NUMBER: P333222

CATALOG NUMBER: S125DIP-S850D590U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	565.0	667.9	749.2	806.4	843.9	862.5	872.4	876.5
115°	517.9	606.4	684.5	746.7	791.2	818.6	834.5	842.0
117.5°	487.6	563.8	631.1	688.2	732.7	761.0	776.8	781.4
120°	471.2	539.6	602.4	652.6	694.8	722.2	737.6	742.1
122.5°	458.9	522.3	578.2	625.2	662.8	687.9	703.3	707.4
125°	440.9	499.1	548.8	589.8	621.8	645.2	657.7	663.4
127.5°	422.7	477.0	523.3	561.8	590.7	611.4	623.2	625.8
130°	411.3	461.5	506.0	543.0	571.6	590.4	601.8	605.2
132.5°	399.9	446.9	487.3	523.0	551.5	570.3	580.8	584.7
135°	385.0	424.4	460.9	493.4	518.5	537.3	547.6	551.0
137.5°	372.5	404.3	434.7	462.3	484.7	501.9	511.3	515.1
140°	365.6	392.5	418.7	442.7	463.8	478.6	487.1	490.0
142.5°	359.7	382.4	405.0	425.8	443.7	456.2	464.3	466.7
145°	352.0	369.6	387.3	402.7	416.4	426.1	432.4	434.7
147.5°	344.7	359.0	372.6	384.2	395.1	402.8	406.5	407.5
150°	340.5	353.1	363.9	374.2	382.8	389.6	391.9	392.5
152.5°	336.0	347.2	357.1	365.1	372.3	377.7	380.0	380.6
155°	329.1	338.3	346.2	352.5	358.2	362.2	363.9	364.5
157.5°	322.3	329.8	336.0	340.9	345.3	348.6	350.2	350.1
160°	317.7	323.4	329.1	333.1	337.1	340.0	341.1	340.5
162.5°	312.7	318.0	322.7	326.3	329.4	331.8	332.0	331.9
165°	305.7	309.7	313.2	316.0	318.3	319.4	319.4	319.4
167.5°	299.1	301.8	304.4	306.4	307.6	308.6	308.1	308.0
170°	295.5	297.2	298.9	300.0	301.2	301.8	301.8	301.2
172.5°	291.4	293.1	294.3	295.0	295.3	296.3	295.4	294.8
175°	286.9	286.9	288.1	288.1	288.1	288.6	287.5	286.9
177.5°	283.8	284.3	284.3	284.3	283.8	284.3	282.9	282.9
180°	282.9	282.9	282.9	282.9	282.9	282.9	282.9	282.9

(END OF REPORT)