

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333225

Luminaire Tested: **S125DIP-S850D810U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333225
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U835-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6362.6 lumens
Efficiency: N/A
Efficacy: 138.6 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	67	66	63	59	57	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	31	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7901	7901	7901	7901
5°	9149	7927	6941	7927
10°	10645	7887	6082	7887
15°	11784	7829	5610	7829
20°	13190	7737	5232	7737
25°	15452	7633	5047	7633
30°	16690	7532	4887	7532
35°	13722	7340	4782	7340
40°	9754	7074	4666	7074
45°	7493	6716	4601	6716
50°	6396	6271	4591	6271
55°	5695	5835	4631	5835
60°	5137	5359	4748	5359
65°	4745	4879	4872	4879
70°	4315	4383	4942	4383
75°	3810	3860	4898	3860
80°	3206	3146	4482	3146
85°	2542	2267	3616	2267



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	1.9
10°-20°	350.7	5.5
20°-30°	569.4	8.9
30°-40°	694.5	10.9
40°-50°	631.8	9.9
50°-60°	503.3	7.9
60°-70°	350.5	5.5
70°-80°	186.9	2.9
80°-90°	49.3	0.8
90°-100°	281.1	4.4
100°-110°	604.3	9.5
110°-120°	567.1	8.9
120°-130°	459.6	7.2
130°-140°	368.8	5.8
140°-150°	278.3	4.4
150°-160°	195.9	3.1
160°-170°	115.5	1.8
170°-180°	37.6	0.6
0°-30°	1037.8	16.3
0°-40°	1732.4	27.2
0°-60°	2867.5	45.1
0°-90°	3454.3	54.3
90°-120°	1452.5	22.8
90°-150°	2559.3	40.2
90°-180°	2908.0	45.7
0°-180°	6362.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1411	1223	1071	1223	1411	142
15°	1762	1171	839	1171	1762	504
25°	2168	1071	708	1071	2168	990
35°	1740	931	606	931	1740	1065
45°	820	735	504	735	820	657
55°	506	518	411	518	506	455
65°	310	319	319	319	310	308
75°	153	155	196	155	153	164
85°	34	31	49	31	34	40
90°	18	1	18	1	18	14
95°	184	26	184	26	184	260
105°	1036	88	1036	88	1036	1030
115°	1154	158	1154	158	1154	1128
125°	909	219	909	219	909	823
135°	755	256	755	256	755	585
145°	596	299	596	299	596	379
155°	500	341	500	341	500	233
165°	438	372	438	372	438	125
175°	393	387	393	387	393	38
180°	388	388	388	388	388	



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1294.0	1292.3	1290.7	1287.3	1289.8	1282.8	1279.4	1273.6	1266.6	1264.1	1261.2
5°	1411.3	1413.9	1416.5	1405.6	1406.7	1399.4	1382.8	1369.3	1358.4	1344.4	1334.5
7.5°	1552.6	1546.4	1545.9	1538.9	1526.7	1517.0	1499.5	1477.3	1455.8	1431.3	1411.0
10°	1623.2	1623.7	1619.0	1610.7	1597.8	1588.4	1565.6	1543.7	1517.3	1486.1	1463.8
12.5°	1676.4	1678.5	1672.6	1661.4	1655.1	1634.1	1616.2	1590.3	1558.8	1533.9	1499.9
15°	1762.4	1756.6	1752.5	1738.5	1727.6	1705.8	1677.2	1650.2	1615.9	1584.2	1552.6
17.5°	1845.2	1849.8	1842.0	1829.2	1795.4	1769.9	1731.6	1694.6	1652.0	1609.5	1571.7
20°	1919.2	1923.3	1911.4	1889.1	1848.6	1823.1	1772.7	1725.0	1675.6	1621.1	1579.6
22.5°	2011.4	2008.1	1992.0	1958.0	1922.9	1875.9	1821.3	1763.2	1701.4	1639.8	1584.6
25°	2168.4	2146.6	2136.7	2094.7	2048.5	1979.4	1904.6	1819.5	1742.6	1661.1	1590.5
27.5°	2255.4	2248.6	2237.6	2208.3	2159.7	2085.9	1997.7	1893.9	1785.5	1682.6	1590.2
30°	2238.0	2239.0	2240.1	2230.7	2199.6	2144.0	2056.3	1944.6	1815.8	1700.0	1593.1
32.5°	2083.5	2102.4	2120.4	2141.8	2150.5	2139.9	2084.9	1984.1	1851.6	1720.0	1591.4
35°	1740.5	1746.3	1804.9	1863.1	1942.0	2003.3	2044.3	1999.7	1888.0	1736.9	1589.4
37.5°	1357.1	1385.2	1425.8	1491.5	1605.4	1707.4	1838.6	1898.9	1862.9	1742.4	1585.8
40°	1156.9	1182.9	1209.3	1276.3	1372.4	1496.0	1645.0	1772.2	1801.8	1725.0	1573.3
42.5°	1002.4	1022.9	1052.3	1102.7	1183.0	1292.4	1434.8	1601.1	1703.4	1674.3	1547.2
45°	820.4	833.4	856.3	896.2	954.4	1040.1	1165.7	1347.5	1505.8	1558.3	1485.1
47.5°	702.2	702.1	719.9	747.5	789.5	862.3	955.2	1097.6	1266.8	1391.9	1386.1
50°	636.6	634.0	648.0	671.9	705.1	753.4	842.2	955.9	1118.5	1260.2	1299.7
52.5°	580.1	580.4	589.0	606.7	634.5	675.8	742.1	844.6	983.5	1129.0	1203.3
55°	505.8	503.7	513.5	525.5	545.7	572.7	620.5	698.9	811.6	954.9	1051.5
57.5°	437.6	443.3	447.3	455.6	472.4	490.5	530.8	588.3	677.7	800.7	902.8
60°	397.7	403.5	406.6	414.9	428.4	444.0	475.1	521.9	597.1	703.1	804.3
62.5°	362.0	366.5	367.5	375.0	386.0	401.2	425.7	464.9	524.4	617.1	716.3
65°	310.5	310.5	312.6	320.4	325.6	339.1	357.8	386.3	434.1	506.3	590.9
67.5°	260.9	263.4	262.8	266.3	271.1	281.5	294.9	318.5	353.9	406.6	474.3
70°	228.5	230.5	230.0	232.6	237.8	244.6	255.5	277.8	303.2	348.4	406.6
72.5°	199.4	200.2	198.9	202.3	205.4	211.3	223.5	235.4	259.2	297.3	345.1
75°	152.7	153.7	154.7	156.8	159.9	163.0	169.3	181.2	196.8	225.4	256.0
77.5°	114.4	112.5	115.0	114.7	116.4	118.8	124.3	130.6	143.4	161.5	185.2
80°	86.2	86.7	86.7	87.2	89.8	91.4	96.1	100.7	110.6	124.1	140.7
82.5°	62.9	64.3	63.5	64.4	66.6	67.7	70.3	74.1	79.9	90.5	102.5
85°	34.3	31.7	32.7	33.8	33.8	34.3	36.3	37.9	41.0	45.2	49.8
87.5°	13.6	14.4	14.7	14.7	15.1	14.8	16.3	16.1	17.2	18.3	19.6
90°	18.0	18.0	17.2	17.2	17.2	15.6	14.9	14.1	13.3	12.5	10.9
92.5°	49.9	51.1	52.2	54.1	64.1	75.7	100.6	138.6	204.1	252.1	256.1
95°	183.7	196.3	202.5	226.0	281.5	347.2	443.3	562.2	677.9	692.8	565.3
97.5°	444.1	454.1	476.8	520.6	568.9	660.2	753.9	837.3	857.7	739.8	504.8
100°	609.9	622.4	651.3	707.6	761.6	842.9	923.4	961.7	901.5	706.1	450.4
102.5°	795.0	804.4	835.8	875.9	933.6	988.6	1027.3	1003.6	875.3	646.6	409.1
105°	1036.0	1045.4	1061.0	1086.8	1111.9	1120.5	1086.1	978.9	791.3	566.9	369.1
107.5°	1163.9	1170.2	1175.3	1175.5	1162.8	1122.0	1033.7	890.7	705.6	512.0	352.2
110°	1206.5	1206.5	1201.0	1186.1	1150.9	1084.5	974.2	825.7	656.8	486.3	347.2



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1201.5	1195.8	1182.2	1156.7	1105.3	1026.9	915.4	774.4	620.5	471.3	347.2
115°	1154.1	1143.9	1122.0	1084.5	1023.5	938.3	831.2	710.0	580.9	455.1	349.5
117.5°	1071.0	1064.8	1043.0	1004.3	943.3	865.1	772.8	668.4	557.3	447.1	354.7
120°	1017.2	1011.0	989.9	952.3	894.5	825.7	739.7	645.8	544.2	443.3	359.7
122.5°	969.7	964.1	943.0	908.6	857.0	792.5	715.9	629.0	532.9	440.2	364.0
125°	909.3	901.5	884.3	852.3	808.5	752.2	684.2	604.4	517.6	436.3	371.4
127.5°	857.7	854.3	838.0	809.7	770.0	717.3	653.8	579.4	503.5	434.4	379.7
130°	829.6	824.9	809.3	783.5	744.4	693.5	632.6	563.7	494.2	433.2	384.7
132.5°	801.4	796.1	781.7	755.9	716.8	667.9	612.5	548.1	486.7	433.2	390.3
135°	755.3	750.6	736.5	710.7	676.3	631.8	581.7	527.8	477.7	433.2	398.0
137.5°	706.1	700.9	687.9	664.5	633.6	595.8	554.2	510.6	469.8	434.1	405.0
140°	671.6	667.7	656.0	635.7	606.7	573.9	537.9	501.2	466.0	434.7	408.1
142.5°	639.7	636.5	625.4	608.2	583.6	555.1	524.2	493.1	462.9	435.4	410.0
145°	595.8	592.7	584.1	570.8	552.0	530.9	506.7	482.4	458.2	434.7	412.1
147.5°	558.6	557.2	552.2	541.5	526.7	510.7	492.1	472.4	453.3	432.7	412.8
150°	537.9	537.2	534.0	524.7	512.9	498.8	484.0	466.8	449.6	430.8	412.8
152.5°	521.7	520.9	517.8	510.3	500.4	489.5	475.9	460.5	445.2	428.3	412.2
155°	499.6	498.8	496.5	491.0	483.2	474.6	463.7	451.2	437.9	423.8	410.5
157.5°	479.9	480.1	477.9	473.4	467.3	460.5	452.1	441.8	431.0	419.1	408.5
160°	466.8	467.6	466.0	462.1	456.6	451.2	443.3	435.5	425.4	416.0	406.6
162.5°	454.9	455.1	454.7	451.5	447.2	442.4	435.8	428.6	420.3	412.2	404.7
165°	437.9	437.9	437.9	436.3	433.2	429.3	424.6	419.1	412.8	406.6	401.9
167.5°	422.2	422.4	423.0	421.6	420.0	417.2	413.6	410.0	405.5	401.1	397.5
170°	412.8	413.6	413.6	412.8	411.3	409.7	407.4	405.0	401.1	398.0	395.6
172.5°	404.1	404.9	406.1	404.7	404.4	403.5	401.7	399.4	396.7	394.2	393.1
175°	393.3	394.1	395.6	394.9	394.9	394.9	393.3	393.3	390.9	390.2	390.2
177.5°	387.8	387.8	389.7	389.1	389.7	389.7	389.7	389.1	388.4	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1258.7	1255.8	1252.4	1246.6	1239.6	1235.8	1230.0	1226.3	1218.8	1212.6	1205.9
5°	1322.5	1309.0	1296.6	1280.5	1262.8	1251.4	1237.9	1222.8	1207.3	1191.2	1173.5
7.5°	1388.7	1364.8	1338.8	1310.9	1283.6	1258.5	1234.5	1210.9	1188.9	1162.3	1139.8
10°	1433.1	1403.0	1370.8	1332.9	1296.1	1263.9	1231.2	1202.6	1173.5	1142.4	1114.8
12.5°	1477.6	1437.5	1392.0	1350.4	1306.0	1267.2	1228.7	1192.2	1155.7	1121.2	1089.1
15°	1509.0	1473.6	1431.6	1372.4	1322.5	1269.1	1218.2	1170.9	1126.8	1088.4	1047.9
17.5°	1529.6	1484.1	1439.0	1382.2	1316.8	1257.0	1199.4	1145.3	1095.5	1046.8	1007.8
20°	1533.4	1486.6	1439.4	1383.8	1316.8	1248.3	1190.7	1125.7	1072.3	1021.9	974.1
22.5°	1532.1	1479.2	1427.7	1370.5	1305.2	1242.1	1172.4	1106.2	1048.2	998.6	948.8
25°	1520.4	1463.8	1399.4	1341.8	1277.4	1210.4	1139.8	1071.2	1012.0	955.4	906.1
27.5°	1510.6	1437.2	1364.3	1297.1	1234.9	1173.5	1105.9	1035.7	970.1	912.7	866.2
30°	1498.6	1418.1	1336.0	1265.9	1202.1	1142.4	1078.5	1010.0	941.4	885.3	835.5
32.5°	1487.8	1394.0	1307.4	1231.1	1163.4	1105.4	1046.5	981.3	914.0	857.1	807.2
35°	1466.9	1358.4	1259.2	1173.0	1100.8	1041.1	991.8	931.0	869.2	814.2	766.4
37.5°	1440.4	1311.6	1205.2	1114.8	1035.7	972.8	926.9	880.2	820.9	767.9	724.7
40°	1419.6	1278.4	1165.7	1073.3	991.3	925.8	883.3	839.1	789.8	740.5	694.8
42.5°	1393.5	1248.5	1125.9	1026.4	945.1	881.4	836.7	799.2	755.7	709.7	667.3
45°	1345.4	1194.3	1061.4	954.4	872.3	809.5	763.3	735.3	702.6	658.9	623.1
47.5°	1274.7	1129.2	991.7	881.3	796.6	738.4	695.1	668.2	645.1	612.7	580.2
50°	1211.9	1080.6	941.4	831.8	747.2	688.5	648.6	624.1	604.4	579.5	552.0
52.5°	1141.7	1019.5	892.0	783.7	699.9	642.0	602.9	581.4	565.0	547.1	520.0
55°	1030.2	926.4	808.0	705.1	627.8	571.2	536.9	518.2	504.7	491.2	474.6
57.5°	907.3	826.1	721.2	627.3	556.0	504.5	472.5	454.3	443.9	436.9	427.1
60°	820.9	751.4	661.0	575.3	505.8	460.1	428.9	414.9	406.1	400.3	393.1
62.5°	740.8	683.7	599.9	521.7	460.9	417.7	389.9	376.3	367.8	365.0	359.0
65°	622.6	578.5	509.4	444.5	392.6	355.7	332.3	319.3	314.1	311.0	311.6
67.5°	506.2	479.3	423.8	368.5	327.0	296.1	277.4	267.4	264.8	260.7	260.6
70°	435.1	414.9	368.2	319.9	283.0	259.1	242.5	232.1	229.5	227.4	226.9
72.5°	372.4	354.7	314.1	275.4	242.3	221.3	207.6	201.4	197.1	195.9	195.8
75°	279.9	270.0	237.8	207.2	184.3	169.8	160.5	154.7	151.6	151.1	151.6
77.5°	199.0	190.4	169.9	148.2	133.8	122.8	114.9	112.9	109.4	109.5	108.9
80°	149.5	143.8	130.9	113.7	101.8	92.4	88.3	84.6	83.6	82.0	83.6
82.5°	108.4	102.3	93.5	82.6	72.7	67.1	62.9	61.8	61.2	60.4	60.8
85°	53.5	54.0	48.8	40.5	36.3	33.2	30.6	30.6	30.1	29.6	30.1
87.5°	20.3	19.2	17.3	15.8	13.4	11.8	11.1	11.4	10.3	10.2	10.9
90°	10.2	8.6	7.8	6.3	4.7	3.1	1.6	0.8	1.6	3.1	4.7
92.5°	178.4	106.8	64.1	41.3	27.8	18.1	11.6	9.5	11.6	18.1	27.8
95°	349.5	177.5	93.8	58.6	41.4	32.8	26.6	25.8	26.6	32.8	41.4
97.5°	279.0	152.9	97.6	72.2	56.8	48.2	43.8	42.8	43.8	48.2	56.8
100°	253.3	151.7	106.3	82.9	68.0	59.4	56.3	54.7	56.3	59.4	68.0
102.5°	242.7	157.3	117.0	94.1	80.5	71.3	68.8	67.9	68.8	71.3	80.5
105°	238.5	168.9	134.5	112.6	100.1	92.3	88.4	88.4	88.4	92.3	100.1
107.5°	245.7	186.1	152.8	133.1	120.1	113.7	109.9	108.4	109.9	113.7	120.1
110°	252.6	198.6	166.5	146.2	134.5	127.4	124.3	122.8	124.3	127.4	134.5



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	261.3	210.5	179.7	160.0	148.2	141.2	138.7	137.1	138.7	141.2	148.2
115°	274.4	229.1	200.2	180.6	168.9	161.9	159.5	157.9	159.5	161.9	168.9
117.5°	289.5	248.2	220.8	201.9	188.6	181.6	179.1	176.7	179.1	181.6	188.6
120°	299.5	261.9	234.6	215.0	201.7	194.7	191.6	189.2	191.6	194.7	201.7
122.5°	310.7	275.1	247.7	228.2	213.6	206.6	204.1	202.4	204.1	206.6	213.6
125°	326.0	292.4	266.6	246.3	231.4	224.4	220.5	218.9	220.5	224.4	231.4
127.5°	340.1	309.2	284.3	264.0	248.2	239.3	234.3	231.9	234.3	239.3	248.2
130°	349.5	319.8	295.6	275.2	258.8	248.6	242.4	240.0	242.4	248.6	258.8
132.5°	357.6	329.8	305.6	285.2	268.2	256.8	249.3	246.3	249.3	256.8	268.2
135°	369.1	343.3	319.0	297.9	281.5	269.0	259.6	256.5	259.6	269.0	281.5
137.5°	377.5	352.8	330.7	309.0	292.9	280.4	271.6	269.3	271.6	280.4	292.9
140°	383.1	359.7	337.0	315.9	301.0	288.5	279.1	276.8	279.1	288.5	301.0
142.5°	386.3	364.0	342.6	322.8	308.5	296.0	287.3	285.5	287.3	296.0	308.5
145°	390.9	371.4	351.1	333.1	319.0	308.1	300.2	298.7	300.2	308.1	319.0
147.5°	393.8	376.1	358.3	342.5	330.3	320.1	313.4	312.4	313.4	320.1	330.3
150°	395.6	379.2	362.0	348.7	337.8	327.6	322.1	320.6	322.1	327.6	337.8
152.5°	396.9	382.3	366.4	354.4	344.0	335.1	330.3	329.3	330.3	335.1	344.0
155°	398.0	385.5	372.2	361.2	353.4	345.6	340.9	340.9	340.9	345.6	353.4
157.5°	398.8	388.1	376.7	368.4	361.5	354.8	351.1	351.2	351.1	354.8	361.5
160°	398.8	389.4	379.2	372.2	365.9	360.5	357.3	358.1	357.3	360.5	365.9
162.5°	398.1	390.6	381.7	375.9	370.9	366.1	363.0	363.7	363.0	366.1	370.9
165°	397.2	390.9	384.7	380.0	376.9	373.0	370.6	372.2	370.6	373.0	376.9
167.5°	395.3	390.9	385.8	382.8	380.6	378.4	377.0	377.8	377.0	378.4	380.6
170°	394.1	390.9	387.0	384.7	383.1	381.6	380.8	381.6	380.8	381.6	383.1
172.5°	392.8	390.3	387.0	385.9	385.0	383.4	382.7	384.1	382.7	383.4	385.0
175°	390.9	389.4	387.0	387.0	387.0	386.3	385.5	387.0	385.5	386.3	387.0
177.5°	389.1	388.4	387.2	387.2	387.8	387.2	387.2	388.4	387.2	387.2	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1202.2	1197.6	1193.9	1185.6	1181.0	1174.8	1169.8	1175.2	1169.4	1171.9	1168.1
5°	1164.7	1150.2	1139.8	1124.7	1111.7	1099.8	1091.0	1089.4	1085.2	1083.2	1076.9
7.5°	1119.6	1101.4	1083.6	1063.9	1047.2	1030.3	1019.5	1010.6	1004.7	996.9	991.6
10°	1093.0	1068.6	1047.9	1024.0	1003.2	985.0	970.5	963.2	956.5	946.6	943.0
12.5°	1060.2	1035.0	1009.6	984.1	964.2	943.9	931.4	920.4	915.8	904.6	903.5
15°	1020.9	983.0	958.0	932.1	904.5	887.9	877.5	865.6	860.4	852.6	846.9
17.5°	973.9	940.1	908.9	882.0	858.4	844.4	831.5	823.3	814.4	809.3	800.0
20°	939.9	907.7	876.5	847.9	829.8	813.7	803.3	795.5	786.2	783.6	774.2
22.5°	911.2	875.7	845.8	821.8	801.9	783.8	772.5	767.3	760.8	752.8	750.9
25°	864.6	827.7	802.3	778.4	760.7	744.1	736.3	729.6	723.3	717.6	715.5
27.5°	824.3	791.3	761.1	739.5	724.2	709.0	702.1	693.9	689.4	684.8	679.2
30°	796.0	762.3	735.8	715.0	698.4	684.9	677.6	671.9	667.8	663.6	660.5
32.5°	766.9	735.7	710.0	689.7	673.1	662.9	656.4	652.4	647.8	642.8	638.9
35°	728.5	694.2	669.3	651.7	638.7	630.9	623.6	620.0	614.8	614.8	610.6
37.5°	685.2	655.6	633.6	617.5	605.9	598.9	591.0	588.5	585.2	583.0	581.6
40°	659.5	631.9	611.2	595.1	582.6	576.9	570.7	566.5	564.4	561.8	560.8
42.5°	632.9	606.6	586.7	571.8	561.0	556.1	550.3	547.4	543.2	539.8	539.2
45°	592.5	567.0	548.9	536.9	527.6	521.9	518.2	512.0	509.9	505.8	505.2
47.5°	554.1	529.7	511.9	502.1	493.9	489.2	483.5	477.3	474.9	472.8	472.6
50°	525.5	503.2	486.5	477.2	469.4	462.7	456.9	452.8	451.2	451.2	452.3
52.5°	496.4	477.4	463.3	451.9	444.5	437.3	432.0	429.5	427.1	429.6	431.5
55°	453.8	434.6	424.2	413.3	406.1	397.7	395.2	394.1	392.6	396.7	398.8
57.5°	408.8	395.3	383.1	372.3	365.8	361.0	357.5	356.8	359.7	361.7	368.5
60°	380.1	364.5	353.6	345.3	337.5	334.4	333.4	332.3	334.4	340.1	348.9
62.5°	348.5	335.9	324.1	317.9	312.2	307.0	306.8	307.4	311.6	318.1	326.9
65°	302.2	291.3	283.5	276.2	271.6	268.5	269.5	271.6	276.2	285.1	294.9
67.5°	255.2	247.7	240.7	234.8	230.3	230.3	231.4	234.5	240.0	250.2	259.2
70°	224.8	216.5	210.8	208.2	204.6	202.5	205.6	210.8	215.5	224.8	232.6
72.5°	194.5	187.5	183.0	181.2	179.7	178.0	179.0	184.6	191.0	200.3	209.4
75°	149.5	146.9	143.8	141.8	140.2	141.2	142.3	147.5	152.7	162.5	172.9
77.5°	109.1	106.4	104.6	104.1	103.2	103.7	106.7	110.5	115.6	122.8	130.6
80°	82.6	81.5	80.5	80.0	80.0	80.5	84.6	87.2	91.9	98.7	104.9
82.5°	60.1	59.5	59.3	59.2	59.6	59.7	62.2	65.6	69.5	74.6	80.0
85°	31.7	30.6	32.2	32.7	31.7	33.2	34.3	36.3	37.9	40.5	43.1
87.5°	11.6	12.8	12.5	13.2	13.4	14.5	14.3	16.1	17.1	18.1	18.0
90°	6.3	7.8	8.6	10.2	10.9	12.5	13.3	14.1	14.9	15.6	17.2
92.5°	41.3	64.1	106.8	178.4	256.1	252.1	204.1	138.6	100.6	75.7	64.1
95°	58.6	93.8	177.5	349.5	565.3	692.8	677.9	562.2	443.3	347.2	281.5
97.5°	72.2	97.6	152.9	279.0	504.8	739.8	857.7	837.3	753.9	660.2	568.9
100°	82.9	106.3	151.7	253.3	450.4	706.1	901.5	961.7	923.4	842.9	761.6
102.5°	94.1	117.0	157.3	242.7	409.1	646.6	875.3	1003.6	1027.3	988.6	933.6
105°	112.6	134.5	168.9	238.5	369.1	566.9	791.3	978.9	1086.1	1120.5	1111.9
107.5°	133.1	152.8	186.1	245.7	352.2	512.0	705.6	890.7	1033.7	1122.0	1162.8
110°	146.2	166.5	198.6	252.6	347.2	486.3	656.8	825.7	974.2	1084.5	1150.9



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	160.0	179.7	210.5	261.3	347.2	471.3	620.5	774.4	915.4	1026.9	1105.3
115°	180.6	200.2	229.1	274.4	349.5	455.1	580.9	710.0	831.2	938.3	1023.5
117.5°	201.9	220.8	248.2	289.5	354.7	447.1	557.3	668.4	772.8	865.1	943.3
120°	215.0	234.6	261.9	299.5	359.7	443.3	544.2	645.8	739.7	825.7	894.5
122.5°	228.2	247.7	275.1	310.7	364.0	440.2	532.9	629.0	715.9	792.5	857.0
125°	246.3	266.6	292.4	326.0	371.4	436.3	517.6	604.4	684.2	752.2	808.5
127.5°	264.0	284.3	309.2	340.1	379.7	434.4	503.5	579.4	653.8	717.3	770.0
130°	275.2	295.6	319.8	349.5	384.7	433.2	494.2	563.7	632.6	693.5	744.4
132.5°	285.2	305.6	329.8	357.6	390.3	433.2	486.7	548.1	612.5	667.9	716.8
135°	297.9	319.0	343.3	369.1	398.0	433.2	477.7	527.8	581.7	631.8	676.3
137.5°	309.0	330.7	352.8	377.5	405.0	434.1	469.8	510.6	554.2	595.8	633.6
140°	315.9	337.0	359.7	383.1	408.1	434.7	466.0	501.2	537.9	573.9	606.7
142.5°	322.8	342.6	364.0	386.3	410.0	435.4	462.9	493.1	524.2	555.1	583.6
145°	333.1	351.1	371.4	390.9	412.1	434.7	458.2	482.4	506.7	530.9	552.0
147.5°	342.5	358.3	376.1	393.8	412.8	432.7	453.3	472.4	492.1	510.7	526.7
150°	348.7	362.0	379.2	395.6	412.8	430.8	449.6	466.8	484.0	498.8	512.9
152.5°	354.4	366.4	382.3	396.9	412.2	428.3	445.2	460.5	475.9	489.5	500.4
155°	361.2	372.2	385.5	398.0	410.5	423.8	437.9	451.2	463.7	474.6	483.2
157.5°	368.4	376.7	388.1	398.8	408.5	419.1	431.0	441.8	452.1	460.5	467.3
160°	372.2	379.2	389.4	398.8	406.6	416.0	425.4	435.5	443.3	451.2	456.6
162.5°	375.9	381.7	390.6	398.1	404.7	412.2	420.3	428.6	435.8	442.4	447.2
165°	380.0	384.7	390.9	397.2	401.9	406.6	412.8	419.1	424.6	429.3	433.2
167.5°	382.8	385.8	390.9	395.3	397.5	401.1	405.5	410.0	413.6	417.2	420.0
170°	384.7	387.0	390.9	394.1	395.6	398.0	401.1	405.0	407.4	409.7	411.3
172.5°	385.9	387.0	390.3	392.8	393.1	394.2	396.7	399.4	401.7	403.5	404.4
175°	387.0	387.0	389.4	390.9	390.2	390.2	390.9	393.3	393.3	394.9	394.9
177.5°	387.2	387.2	388.4	389.1	387.8	387.8	388.4	389.1	389.7	389.7	389.7
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1165.6	1168.5	1166.0	1169.4	1166.0	1168.5	1165.6	1168.1	1171.9	1169.4	1175.2
5°	1074.3	1069.7	1072.8	1070.7	1072.8	1069.7	1074.3	1076.9	1083.2	1085.2	1089.4
7.5°	990.0	985.5	980.5	978.1	980.5	985.5	990.0	991.6	996.9	1004.7	1010.6
10°	937.3	931.5	931.0	927.4	931.0	931.5	937.3	943.0	946.6	956.5	963.2
12.5°	898.6	893.3	887.4	885.9	887.4	893.3	898.6	903.5	904.6	915.8	920.4
15°	843.8	839.6	836.0	839.1	836.0	839.6	843.8	846.9	852.6	860.4	865.6
17.5°	798.2	794.8	794.1	790.3	794.1	794.8	798.2	800.0	809.3	814.4	823.3
20°	769.5	766.9	768.0	761.2	768.0	766.9	769.5	774.2	783.6	786.2	795.5
22.5°	746.7	741.6	741.0	739.6	741.0	741.6	746.7	750.9	752.8	760.8	767.3
25°	710.9	708.3	705.7	708.3	705.7	708.3	710.9	715.5	717.6	723.3	729.6
27.5°	679.6	676.5	675.8	676.1	675.8	676.5	679.6	679.2	684.8	689.4	693.9
30°	660.5	655.3	655.8	655.3	655.8	655.3	660.5	660.5	663.6	667.8	671.9
32.5°	639.7	636.2	635.5	634.5	635.5	636.2	639.7	638.9	642.8	647.8	652.4
35°	609.1	609.1	606.5	606.5	606.5	609.1	609.1	610.6	614.8	614.8	620.0
37.5°	580.3	579.8	578.2	578.5	578.2	579.8	580.3	581.6	583.0	585.2	588.5
40°	558.7	558.2	556.6	553.5	556.6	558.2	558.7	560.8	561.8	564.4	566.5
42.5°	537.9	536.2	535.5	534.4	535.5	536.2	537.9	539.2	539.8	543.2	547.4
45°	505.2	505.2	504.2	503.7	504.2	505.2	505.2	505.2	505.8	509.9	512.0
47.5°	473.5	474.4	476.4	476.1	476.4	474.4	473.5	472.6	472.8	474.9	477.3
50°	454.3	454.9	456.4	456.9	456.4	454.9	454.3	452.3	451.2	451.2	452.8
52.5°	433.2	436.2	438.1	437.8	438.1	436.2	433.2	431.5	429.6	427.1	429.5
55°	403.5	407.1	410.7	411.3	410.7	407.1	403.5	398.8	396.7	392.6	394.1
57.5°	374.1	379.2	383.0	384.2	383.0	379.2	374.1	368.5	361.7	359.7	356.8
60°	354.1	360.9	365.6	367.6	365.6	360.9	354.1	348.9	340.1	334.4	332.3
62.5°	335.0	342.6	347.3	347.7	347.3	342.6	335.0	326.9	318.1	311.6	307.4
65°	303.8	311.6	315.7	318.8	315.7	311.6	303.8	294.9	285.1	276.2	271.6
67.5°	270.1	277.9	282.5	285.0	282.5	277.9	270.1	259.2	250.2	240.0	234.5
70°	245.6	253.4	259.6	261.7	259.6	253.4	245.6	232.6	224.8	215.5	210.8
72.5°	221.5	228.5	233.5	235.9	233.5	228.5	221.5	209.4	200.3	191.0	184.6
75°	179.7	189.0	193.7	196.3	193.7	189.0	179.7	172.9	162.5	152.7	147.5
77.5°	138.5	147.1	149.9	151.2	149.9	147.1	138.5	130.6	122.8	115.6	110.5
80°	111.1	116.3	119.9	120.5	119.9	116.3	111.1	104.9	98.7	91.9	87.2
82.5°	85.4	89.7	90.9	92.2	90.9	89.7	85.4	80.0	74.6	69.5	65.6
85°	46.7	48.8	49.3	48.8	49.3	48.8	46.7	43.1	40.5	37.9	36.3
87.5°	18.8	18.4	18.6	19.4	18.6	18.4	18.8	18.0	18.1	17.1	16.1
90°	17.2	17.2	18.0	18.0	18.0	17.2	17.2	17.2	15.6	14.9	14.1
92.5°	54.1	52.2	51.1	49.9	51.1	52.2	54.1	64.1	75.7	100.6	138.6
95°	226.0	202.5	196.3	183.7	196.3	202.5	226.0	281.5	347.2	443.3	562.2
97.5°	520.6	476.8	454.1	444.1	454.1	476.8	520.6	568.9	660.2	753.9	837.3
100°	707.6	651.3	622.4	609.9	622.4	651.3	707.6	761.6	842.9	923.4	961.7
102.5°	875.9	835.8	804.4	795.0	804.4	835.8	875.9	933.6	988.6	1027.3	1003.6
105°	1086.8	1061.0	1045.4	1036.0	1045.4	1061.0	1086.8	1111.9	1120.5	1086.1	978.9
107.5°	1175.5	1175.3	1170.2	1163.9	1170.2	1175.3	1175.5	1162.8	1122.0	1033.7	890.7
110°	1186.1	1201.0	1206.5	1206.5	1206.5	1201.0	1186.1	1150.9	1084.5	974.2	825.7



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1156.7	1182.2	1195.8	1201.5	1195.8	1182.2	1156.7	1105.3	1026.9	915.4	774.4
115°	1084.5	1122.0	1143.9	1154.1	1143.9	1122.0	1084.5	1023.5	938.3	831.2	710.0
117.5°	1004.3	1043.0	1064.8	1071.0	1064.8	1043.0	1004.3	943.3	865.1	772.8	668.4
120°	952.3	989.9	1011.0	1017.2	1011.0	989.9	952.3	894.5	825.7	739.7	645.8
122.5°	908.6	943.0	964.1	969.7	964.1	943.0	908.6	857.0	792.5	715.9	629.0
125°	852.3	884.3	901.5	909.3	901.5	884.3	852.3	808.5	752.2	684.2	604.4
127.5°	809.7	838.0	854.3	857.7	854.3	838.0	809.7	770.0	717.3	653.8	579.4
130°	783.5	809.3	824.9	829.6	824.9	809.3	783.5	744.4	693.5	632.6	563.7
132.5°	755.9	781.7	796.1	801.4	796.1	781.7	755.9	716.8	667.9	612.5	548.1
135°	710.7	736.5	750.6	755.3	750.6	736.5	710.7	676.3	631.8	581.7	527.8
137.5°	664.5	687.9	700.9	706.1	700.9	687.9	664.5	633.6	595.8	554.2	510.6
140°	635.7	656.0	667.7	671.6	667.7	656.0	635.7	606.7	573.9	537.9	501.2
142.5°	608.2	625.4	636.5	639.7	636.5	625.4	608.2	583.6	555.1	524.2	493.1
145°	570.8	584.1	592.7	595.8	592.7	584.1	570.8	552.0	530.9	506.7	482.4
147.5°	541.5	552.2	557.2	558.6	557.2	552.2	541.5	526.7	510.7	492.1	472.4
150°	524.7	534.0	537.2	537.9	537.2	534.0	524.7	512.9	498.8	484.0	466.8
152.5°	510.3	517.8	520.9	521.7	520.9	517.8	510.3	500.4	489.5	475.9	460.5
155°	491.0	496.5	498.8	499.6	498.8	496.5	491.0	483.2	474.6	463.7	451.2
157.5°	473.4	477.9	480.1	479.9	480.1	477.9	473.4	467.3	460.5	452.1	441.8
160°	462.1	466.0	467.6	466.8	467.6	466.0	462.1	456.6	451.2	443.3	435.5
162.5°	451.5	454.7	455.1	454.9	455.1	454.7	451.5	447.2	442.4	435.8	428.6
165°	436.3	437.9	437.9	437.9	437.9	437.9	436.3	433.2	429.3	424.6	419.1
167.5°	421.6	423.0	422.4	422.2	422.4	423.0	421.6	420.0	417.2	413.6	410.0
170°	412.8	413.6	413.6	412.8	413.6	413.6	412.8	411.3	409.7	407.4	405.0
172.5°	404.7	406.1	404.9	404.1	404.9	406.1	404.7	404.4	403.5	401.7	399.4
175°	394.9	395.6	394.1	393.3	394.1	395.6	394.9	394.9	394.9	393.3	393.3
177.5°	389.1	389.7	387.8	387.8	387.8	389.7	389.1	389.7	389.7	389.7	389.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1169.8	1174.8	1181.0	1185.6	1193.9	1197.6	1202.2	1205.9	1212.6	1218.8	1226.3
5°	1091.0	1099.8	1111.7	1124.7	1139.8	1150.2	1164.7	1173.5	1191.2	1207.3	1222.8
7.5°	1019.5	1030.3	1047.2	1063.9	1083.6	1101.4	1119.6	1139.8	1162.3	1188.9	1210.9
10°	970.5	985.0	1003.2	1024.0	1047.9	1068.6	1093.0	1114.8	1142.4	1173.5	1202.6
12.5°	931.4	943.9	964.2	984.1	1009.6	1035.0	1060.2	1089.1	1121.2	1155.7	1192.2
15°	877.5	887.9	904.5	932.1	958.0	983.0	1020.9	1047.9	1088.4	1126.8	1170.9
17.5°	831.5	844.4	858.4	882.0	908.9	940.1	973.9	1007.8	1046.8	1095.5	1145.3
20°	803.3	813.7	829.8	847.9	876.5	907.7	939.9	974.1	1021.9	1072.3	1125.7
22.5°	772.5	783.8	801.9	821.8	845.8	875.7	911.2	948.8	998.6	1048.2	1106.2
25°	736.3	744.1	760.7	778.4	802.3	827.7	864.6	906.1	955.4	1012.0	1071.2
27.5°	702.1	709.0	724.2	739.5	761.1	791.3	824.3	866.2	912.7	970.1	1035.7
30°	677.6	684.9	698.4	715.0	735.8	762.3	796.0	835.5	885.3	941.4	1010.0
32.5°	656.4	662.9	673.1	689.7	710.0	735.7	766.9	807.2	857.1	914.0	981.3
35°	623.6	630.9	638.7	651.7	669.3	694.2	728.5	766.4	814.2	869.2	931.0
37.5°	591.0	598.9	605.9	617.5	633.6	655.6	685.2	724.7	767.9	820.9	880.2
40°	570.7	576.9	582.6	595.1	611.2	631.9	659.5	694.8	740.5	789.8	839.1
42.5°	550.3	556.1	561.0	571.8	586.7	606.6	632.9	667.3	709.7	755.7	799.2
45°	518.2	521.9	527.6	536.9	548.9	567.0	592.5	623.1	658.9	702.6	735.3
47.5°	483.5	489.2	493.9	502.1	511.9	529.7	554.1	580.2	612.7	645.1	668.2
50°	456.9	462.7	469.4	477.2	486.5	503.2	525.5	552.0	579.5	604.4	624.1
52.5°	432.0	437.3	444.5	451.9	463.3	477.4	496.4	520.0	547.1	565.0	581.4
55°	395.2	397.7	406.1	413.3	424.2	434.6	453.8	474.6	491.2	504.7	518.2
57.5°	357.5	361.0	365.8	372.3	383.1	395.3	408.8	427.1	436.9	443.9	454.3
60°	333.4	334.4	337.5	345.3	353.6	364.5	380.1	393.1	400.3	406.1	414.9
62.5°	306.8	307.0	312.2	317.9	324.1	335.9	348.5	359.0	365.0	367.8	376.3
65°	269.5	268.5	271.6	276.2	283.5	291.3	302.2	311.6	311.0	314.1	319.3
67.5°	231.4	230.3	230.3	234.8	240.7	247.7	255.2	260.6	260.7	264.8	267.4
70°	205.6	202.5	204.6	208.2	210.8	216.5	224.8	226.9	227.4	229.5	232.1
72.5°	179.0	178.0	179.7	181.2	183.0	187.5	194.5	195.8	195.9	197.1	201.4
75°	142.3	141.2	140.2	141.8	143.8	146.9	149.5	151.6	151.1	151.6	154.7
77.5°	106.7	103.7	103.2	104.1	104.6	106.4	109.1	108.9	109.5	109.4	112.9
80°	84.6	80.5	80.0	80.0	80.5	81.5	82.6	83.6	82.0	83.6	84.6
82.5°	62.2	59.7	59.6	59.2	59.3	59.5	60.1	60.8	60.4	61.2	61.8
85°	34.3	33.2	31.7	32.7	32.2	30.6	31.7	30.1	29.6	30.1	30.6
87.5°	14.3	14.5	13.4	13.2	12.5	12.8	11.6	10.9	10.2	10.3	11.4
90°	13.3	12.5	10.9	10.2	8.6	7.8	6.3	4.7	3.1	1.6	0.8
92.5°	204.1	252.1	256.1	178.4	106.8	64.1	41.3	27.8	18.1	11.6	9.5
95°	677.9	692.8	565.3	349.5	177.5	93.8	58.6	41.4	32.8	26.6	25.8
97.5°	857.7	739.8	504.8	279.0	152.9	97.6	72.2	56.8	48.2	43.8	42.8
100°	901.5	706.1	450.4	253.3	151.7	106.3	82.9	68.0	59.4	56.3	54.7
102.5°	875.3	646.6	409.1	242.7	157.3	117.0	94.1	80.5	71.3	68.8	67.9
105°	791.3	566.9	369.1	238.5	168.9	134.5	112.6	100.1	92.3	88.4	88.4
107.5°	705.6	512.0	352.2	245.7	186.1	152.8	133.1	120.1	113.7	109.9	108.4
110°	656.8	486.3	347.2	252.6	198.6	166.5	146.2	134.5	127.4	124.3	122.8



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	620.5	471.3	347.2	261.3	210.5	179.7	160.0	148.2	141.2	138.7	137.1
115°	580.9	455.1	349.5	274.4	229.1	200.2	180.6	168.9	161.9	159.5	157.9
117.5°	557.3	447.1	354.7	289.5	248.2	220.8	201.9	188.6	181.6	179.1	176.7
120°	544.2	443.3	359.7	299.5	261.9	234.6	215.0	201.7	194.7	191.6	189.2
122.5°	532.9	440.2	364.0	310.7	275.1	247.7	228.2	213.6	206.6	204.1	202.4
125°	517.6	436.3	371.4	326.0	292.4	266.6	246.3	231.4	224.4	220.5	218.9
127.5°	503.5	434.4	379.7	340.1	309.2	284.3	264.0	248.2	239.3	234.3	231.9
130°	494.2	433.2	384.7	349.5	319.8	295.6	275.2	258.8	248.6	242.4	240.0
132.5°	486.7	433.2	390.3	357.6	329.8	305.6	285.2	268.2	256.8	249.3	246.3
135°	477.7	433.2	398.0	369.1	343.3	319.0	297.9	281.5	269.0	259.6	256.5
137.5°	469.8	434.1	405.0	377.5	352.8	330.7	309.0	292.9	280.4	271.6	269.3
140°	466.0	434.7	408.1	383.1	359.7	337.0	315.9	301.0	288.5	279.1	276.8
142.5°	462.9	435.4	410.0	386.3	364.0	342.6	322.8	308.5	296.0	287.3	285.5
145°	458.2	434.7	412.1	390.9	371.4	351.1	333.1	319.0	308.1	300.2	298.7
147.5°	453.3	432.7	412.8	393.8	376.1	358.3	342.5	330.3	320.1	313.4	312.4
150°	449.6	430.8	412.8	395.6	379.2	362.0	348.7	337.8	327.6	322.1	320.6
152.5°	445.2	428.3	412.2	396.9	382.3	366.4	354.4	344.0	335.1	330.3	329.3
155°	437.9	423.8	410.5	398.0	385.5	372.2	361.2	353.4	345.6	340.9	340.9
157.5°	431.0	419.1	408.5	398.8	388.1	376.7	368.4	361.5	354.8	351.1	351.2
160°	425.4	416.0	406.6	398.8	389.4	379.2	372.2	365.9	360.5	357.3	358.1
162.5°	420.3	412.2	404.7	398.1	390.6	381.7	375.9	370.9	366.1	363.0	363.7
165°	412.8	406.6	401.9	397.2	390.9	384.7	380.0	376.9	373.0	370.6	372.2
167.5°	405.5	401.1	397.5	395.3	390.9	385.8	382.8	380.6	378.4	377.0	377.8
170°	401.1	398.0	395.6	394.1	390.9	387.0	384.7	383.1	381.6	380.8	381.6
172.5°	396.7	394.2	393.1	392.8	390.3	387.0	385.9	385.0	383.4	382.7	384.1
175°	390.9	390.2	390.2	390.9	389.4	387.0	387.0	387.0	386.3	385.5	387.0
177.5°	388.4	387.8	387.8	389.1	388.4	387.2	387.2	387.8	387.2	387.2	388.4
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1230.0	1235.8	1239.6	1246.6	1252.4	1255.8	1258.7	1261.2	1264.1	1266.6	1273.6
5°	1237.9	1251.4	1262.8	1280.5	1296.6	1309.0	1322.5	1334.5	1344.4	1358.4	1369.3
7.5°	1234.5	1258.5	1283.6	1310.9	1338.8	1364.8	1388.7	1411.0	1431.3	1455.8	1477.3
10°	1231.2	1263.9	1296.1	1332.9	1370.8	1403.0	1433.1	1463.8	1486.1	1517.3	1543.7
12.5°	1228.7	1267.2	1306.0	1350.4	1392.0	1437.5	1477.6	1499.9	1533.9	1558.8	1590.3
15°	1218.2	1269.1	1322.5	1372.4	1431.6	1473.6	1509.0	1552.6	1584.2	1615.9	1650.2
17.5°	1199.4	1257.0	1316.8	1382.2	1439.0	1484.1	1529.6	1571.7	1609.5	1652.0	1694.6
20°	1190.7	1248.3	1316.8	1383.8	1439.4	1486.6	1533.4	1579.6	1621.1	1675.6	1725.0
22.5°	1172.4	1242.1	1305.2	1370.5	1427.7	1479.2	1532.1	1584.6	1639.8	1701.4	1763.2
25°	1139.8	1210.4	1277.4	1341.8	1399.4	1463.8	1520.4	1590.5	1661.1	1742.6	1819.5
27.5°	1105.9	1173.5	1234.9	1297.1	1364.3	1437.2	1510.6	1590.2	1682.6	1785.5	1893.9
30°	1078.5	1142.4	1202.1	1265.9	1336.0	1418.1	1498.6	1593.1	1700.0	1815.8	1944.6
32.5°	1046.5	1105.4	1163.4	1231.1	1307.4	1394.0	1487.8	1591.4	1720.0	1851.6	1984.1
35°	991.8	1041.1	1100.8	1173.0	1259.2	1358.4	1466.9	1589.4	1736.9	1888.0	1999.7
37.5°	926.9	972.8	1035.7	1114.8	1205.2	1311.6	1440.4	1585.8	1742.4	1862.9	1898.9
40°	883.3	925.8	991.3	1073.3	1165.7	1278.4	1419.6	1573.3	1725.0	1801.8	1772.2
42.5°	836.7	881.4	945.1	1026.4	1125.9	1248.5	1393.5	1547.2	1674.3	1703.4	1601.1
45°	763.3	809.5	872.3	954.4	1061.4	1194.3	1345.4	1485.1	1558.3	1505.8	1347.5
47.5°	695.1	738.4	796.6	881.3	991.7	1129.2	1274.7	1386.1	1391.9	1266.8	1097.6
50°	648.6	688.5	747.2	831.8	941.4	1080.6	1211.9	1299.7	1260.2	1118.5	955.9
52.5°	602.9	642.0	699.9	783.7	892.0	1019.5	1141.7	1203.3	1129.0	983.5	844.6
55°	536.9	571.2	627.8	705.1	808.0	926.4	1030.2	1051.5	954.9	811.6	698.9
57.5°	472.5	504.5	556.0	627.3	721.2	826.1	907.3	902.8	800.7	677.7	588.3
60°	428.9	460.1	505.8	575.3	661.0	751.4	820.9	804.3	703.1	597.1	521.9
62.5°	389.9	417.7	460.9	521.7	599.9	683.7	740.8	716.3	617.1	524.4	464.9
65°	332.3	355.7	392.6	444.5	509.4	578.5	622.6	590.9	506.3	434.1	386.3
67.5°	277.4	296.1	327.0	368.5	423.8	479.3	506.2	474.3	406.6	353.9	318.5
70°	242.5	259.1	283.0	319.9	368.2	414.9	435.1	406.6	348.4	303.2	277.8
72.5°	207.6	221.3	242.3	275.4	314.1	354.7	372.4	345.1	297.3	259.2	235.4
75°	160.5	169.8	184.3	207.2	237.8	270.0	279.9	256.0	225.4	196.8	181.2
77.5°	114.9	122.8	133.8	148.2	169.9	190.4	199.0	185.2	161.5	143.4	130.6
80°	88.3	92.4	101.8	113.7	130.9	143.8	149.5	140.7	124.1	110.6	100.7
82.5°	62.9	67.1	72.7	82.6	93.5	102.3	108.4	102.5	90.5	79.9	74.1
85°	30.6	33.2	36.3	40.5	48.8	54.0	53.5	49.8	45.2	41.0	37.9
87.5°	11.1	11.8	13.4	15.8	17.3	19.2	20.3	19.6	18.3	17.2	16.1
90°	1.6	3.1	4.7	6.3	7.8	8.6	10.2	10.9	12.5	13.3	14.1
92.5°	11.6	18.1	27.8	41.3	64.1	106.8	178.4	256.1	252.1	204.1	138.6
95°	26.6	32.8	41.4	58.6	93.8	177.5	349.5	565.3	692.8	677.9	562.2
97.5°	43.8	48.2	56.8	72.2	97.6	152.9	279.0	504.8	739.8	857.7	837.3
100°	56.3	59.4	68.0	82.9	106.3	151.7	253.3	450.4	706.1	901.5	961.7
102.5°	68.8	71.3	80.5	94.1	117.0	157.3	242.7	409.1	646.6	875.3	1003.6
105°	88.4	92.3	100.1	112.6	134.5	168.9	238.5	369.1	566.9	791.3	978.9
107.5°	109.9	113.7	120.1	133.1	152.8	186.1	245.7	352.2	512.0	705.6	890.7
110°	124.3	127.4	134.5	146.2	166.5	198.6	252.6	347.2	486.3	656.8	825.7



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	138.7	141.2	148.2	160.0	179.7	210.5	261.3	347.2	471.3	620.5	774.4
115°	159.5	161.9	168.9	180.6	200.2	229.1	274.4	349.5	455.1	580.9	710.0
117.5°	179.1	181.6	188.6	201.9	220.8	248.2	289.5	354.7	447.1	557.3	668.4
120°	191.6	194.7	201.7	215.0	234.6	261.9	299.5	359.7	443.3	544.2	645.8
122.5°	204.1	206.6	213.6	228.2	247.7	275.1	310.7	364.0	440.2	532.9	629.0
125°	220.5	224.4	231.4	246.3	266.6	292.4	326.0	371.4	436.3	517.6	604.4
127.5°	234.3	239.3	248.2	264.0	284.3	309.2	340.1	379.7	434.4	503.5	579.4
130°	242.4	248.6	258.8	275.2	295.6	319.8	349.5	384.7	433.2	494.2	563.7
132.5°	249.3	256.8	268.2	285.2	305.6	329.8	357.6	390.3	433.2	486.7	548.1
135°	259.6	269.0	281.5	297.9	319.0	343.3	369.1	398.0	433.2	477.7	527.8
137.5°	271.6	280.4	292.9	309.0	330.7	352.8	377.5	405.0	434.1	469.8	510.6
140°	279.1	288.5	301.0	315.9	337.0	359.7	383.1	408.1	434.7	466.0	501.2
142.5°	287.3	296.0	308.5	322.8	342.6	364.0	386.3	410.0	435.4	462.9	493.1
145°	300.2	308.1	319.0	333.1	351.1	371.4	390.9	412.1	434.7	458.2	482.4
147.5°	313.4	320.1	330.3	342.5	358.3	376.1	393.8	412.8	432.7	453.3	472.4
150°	322.1	327.6	337.8	348.7	362.0	379.2	395.6	412.8	430.8	449.6	466.8
152.5°	330.3	335.1	344.0	354.4	366.4	382.3	396.9	412.2	428.3	445.2	460.5
155°	340.9	345.6	353.4	361.2	372.2	385.5	398.0	410.5	423.8	437.9	451.2
157.5°	351.1	354.8	361.5	368.4	376.7	388.1	398.8	408.5	419.1	431.0	441.8
160°	357.3	360.5	365.9	372.2	379.2	389.4	398.8	406.6	416.0	425.4	435.5
162.5°	363.0	366.1	370.9	375.9	381.7	390.6	398.1	404.7	412.2	420.3	428.6
165°	370.6	373.0	376.9	380.0	384.7	390.9	397.2	401.9	406.6	412.8	419.1
167.5°	377.0	378.4	380.6	382.8	385.8	390.9	395.3	397.5	401.1	405.5	410.0
170°	380.8	381.6	383.1	384.7	387.0	390.9	394.1	395.6	398.0	401.1	405.0
172.5°	382.7	383.4	385.0	385.9	387.0	390.3	392.8	393.1	394.2	396.7	399.4
175°	385.5	386.3	387.0	387.0	387.0	389.4	390.9	390.2	390.2	390.9	393.3
177.5°	387.2	387.2	387.8	387.2	387.2	388.4	389.1	387.8	387.8	388.4	389.1
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1279.4	1282.8	1289.8	1287.3	1290.7	1292.3	1294.0
5°	1382.8	1399.4	1406.7	1405.6	1416.5	1413.9	1411.3
7.5°	1499.5	1517.0	1526.7	1538.9	1545.9	1546.4	1552.6
10°	1565.6	1588.4	1597.8	1610.7	1619.0	1623.7	1623.2
12.5°	1616.2	1634.1	1655.1	1661.4	1672.6	1678.5	1676.4
15°	1677.2	1705.8	1727.6	1738.5	1752.5	1756.6	1762.4
17.5°	1731.6	1769.9	1795.4	1829.2	1842.0	1849.8	1845.2
20°	1772.7	1823.1	1848.6	1889.1	1911.4	1923.3	1919.2
22.5°	1821.3	1875.9	1922.9	1958.0	1992.0	2008.1	2011.4
25°	1904.6	1979.4	2048.5	2094.7	2136.7	2146.6	2168.4
27.5°	1997.7	2085.9	2159.7	2208.3	2237.6	2248.6	2255.4
30°	2056.3	2144.0	2199.6	2230.7	2240.1	2239.0	2238.0
32.5°	2084.9	2139.9	2150.5	2141.8	2120.4	2102.4	2083.5
35°	2044.3	2003.3	1942.0	1863.1	1804.9	1746.3	1740.5
37.5°	1838.6	1707.4	1605.4	1491.5	1425.8	1385.2	1357.1
40°	1645.0	1496.0	1372.4	1276.3	1209.3	1182.9	1156.9
42.5°	1434.8	1292.4	1183.0	1102.7	1052.3	1022.9	1002.4
45°	1165.7	1040.1	954.4	896.2	856.3	833.4	820.4
47.5°	955.2	862.3	789.5	747.5	719.9	702.1	702.2
50°	842.2	753.4	705.1	671.9	648.0	634.0	636.6
52.5°	742.1	675.8	634.5	606.7	589.0	580.4	580.1
55°	620.5	572.7	545.7	525.5	513.5	503.7	505.8
57.5°	530.8	490.5	472.4	455.6	447.3	443.3	437.6
60°	475.1	444.0	428.4	414.9	406.6	403.5	397.7
62.5°	425.7	401.2	386.0	375.0	367.5	366.5	362.0
65°	357.8	339.1	325.6	320.4	312.6	310.5	310.5
67.5°	294.9	281.5	271.1	266.3	262.8	263.4	260.9
70°	255.5	244.6	237.8	232.6	230.0	230.5	228.5
72.5°	223.5	211.3	205.4	202.3	198.9	200.2	199.4
75°	169.3	163.0	159.9	156.8	154.7	153.7	152.7
77.5°	124.3	118.8	116.4	114.7	115.0	112.5	114.4
80°	96.1	91.4	89.8	87.2	86.7	86.7	86.2
82.5°	70.3	67.7	66.6	64.4	63.5	64.3	62.9
85°	36.3	34.3	33.8	33.8	32.7	31.7	34.3
87.5°	16.3	14.8	15.1	14.7	14.7	14.4	13.6
90°	14.9	15.6	17.2	17.2	17.2	18.0	18.0
92.5°	100.6	75.7	64.1	54.1	52.2	51.1	49.9
95°	443.3	347.2	281.5	226.0	202.5	196.3	183.7
97.5°	753.9	660.2	568.9	520.6	476.8	454.1	444.1
100°	923.4	842.9	761.6	707.6	651.3	622.4	609.9
102.5°	1027.3	988.6	933.6	875.9	835.8	804.4	795.0
105°	1086.1	1120.5	1111.9	1086.8	1061.0	1045.4	1036.0
107.5°	1033.7	1122.0	1162.8	1175.5	1175.3	1170.2	1163.9
110°	974.2	1084.5	1150.9	1186.1	1201.0	1206.5	1206.5



TEST NUMBER: P333225

CATALOG NUMBER: S125DIP-S850D810U835-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	915.4	1026.9	1105.3	1156.7	1182.2	1195.8	1201.5
115°	831.2	938.3	1023.5	1084.5	1122.0	1143.9	1154.1
117.5°	772.8	865.1	943.3	1004.3	1043.0	1064.8	1071.0
120°	739.7	825.7	894.5	952.3	989.9	1011.0	1017.2
122.5°	715.9	792.5	857.0	908.6	943.0	964.1	969.7
125°	684.2	752.2	808.5	852.3	884.3	901.5	909.3
127.5°	653.8	717.3	770.0	809.7	838.0	854.3	857.7
130°	632.6	693.5	744.4	783.5	809.3	824.9	829.6
132.5°	612.5	667.9	716.8	755.9	781.7	796.1	801.4
135°	581.7	631.8	676.3	710.7	736.5	750.6	755.3
137.5°	554.2	595.8	633.6	664.5	687.9	700.9	706.1
140°	537.9	573.9	606.7	635.7	656.0	667.7	671.6
142.5°	524.2	555.1	583.6	608.2	625.4	636.5	639.7
145°	506.7	530.9	552.0	570.8	584.1	592.7	595.8
147.5°	492.1	510.7	526.7	541.5	552.2	557.2	558.6
150°	484.0	498.8	512.9	524.7	534.0	537.2	537.9
152.5°	475.9	489.5	500.4	510.3	517.8	520.9	521.7
155°	463.7	474.6	483.2	491.0	496.5	498.8	499.6
157.5°	452.1	460.5	467.3	473.4	477.9	480.1	479.9
160°	443.3	451.2	456.6	462.1	466.0	467.6	466.8
162.5°	435.8	442.4	447.2	451.5	454.7	455.1	454.9
165°	424.6	429.3	433.2	436.3	437.9	437.9	437.9
167.5°	413.6	417.2	420.0	421.6	423.0	422.4	422.2
170°	407.4	409.7	411.3	412.8	413.6	413.6	412.8
172.5°	401.7	403.5	404.4	404.7	406.1	404.9	404.1
175°	393.3	394.9	394.9	394.9	395.6	394.1	393.3
177.5°	389.7	389.7	389.7	389.1	389.7	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)