

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333131-927

Luminaire Tested: **S125DIP-S375D590U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333131-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D590U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2825.9 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333131-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333131-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	44	43	42	36
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	37	35	30
3	80	70	63	57	73	65	58	53	54	49	45	43	40	37	34	32	30	25
4	73	62	54	48	66	57	50	45	47	42	38	39	35	32	30	28	26	22
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22	19
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	23	20	17	15
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	21	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2989	2989	2989
5°	2995	2967	2986
10°	2977	2946	2963
15°	2945	2910	2923
20°	2899	2861	2866
25°	2849	2802	2799
30°	2788	2738	2725
35°	2722	2670	2633
40°	2655	2596	2559
45°	2582	2528	2478
50°	2502	2446	2372
55°	2423	2354	2288
60°	2331	2260	2180
65°	2222	2149	2077
70°	2115	2019	1949
75°	1926	1864	1799
80°	1715	1689	1648
85°	1489	1519	1438



TEST NUMBER: P333131-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	1.5
10°-20°	123.3	4.4
20°-30°	182.0	6.4
30°-40°	212.4	7.5
40°-50°	213.3	7.5
50°-60°	187.2	6.6
60°-70°	139.5	4.9
70°-80°	79.8	2.8
80°-90°	24.5	0.9
90°-100°	38.9	1.4
100°-110°	114.9	4.1
110°-120°	194.5	6.9
120°-130°	256.0	9.1
130°-140°	286.9	10.2
140°-150°	281.2	9.9
150°-160°	236.2	8.4
160°-170°	157.0	5.6
170°-180°	54.9	1.9
0°-30°	348.9	12.3
0°-40°	561.2	19.9
0°-60°	961.7	34.0
0°-90°	1205.5	42.7
90°-120°	348.3	12.3
90°-150°	1172.4	41.5
90°-180°	1620.0	57.3
0°-180°	2825.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	463	463	463	463	463	
5°	462	461	458	461	461	44
15°	440	439	435	437	437	124
25°	400	398	393	394	393	184
35°	345	344	339	337	334	216
45°	283	281	277	273	271	218
55°	215	214	209	206	203	192
65°	145	144	141	137	136	144
75°	77	76	75	74	72	82
85°	20	20	20	20	19	23
90°	0	4	7	10	11	3
95°	29	30	35	38	39	31
105°	103	105	108	111	112	110
115°	195	197	198	197	197	193
125°	284	287	287	287	286	254
135°	370	372	373	373	371	285
145°	448	450	451	451	450	280
155°	512	512	513	514	512	236
165°	557	556	557	558	556	157
175°	579	578	578	580	577	55
180°	581	581	581	581	581	



TEST NUMBER: P333131-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	463.9	463.7	463.6	463.3	463.2	462.7	462.1	461.4	460.8	460.1	460.8
5°	462.0	461.8	461.7	461.5	461.4	460.9	460.1	459.3	458.4	457.6	458.4
7.5°	457.8	457.6	457.5	457.3	457.2	456.6	455.7	454.8	453.9	453.0	453.8
10°	454.0	453.8	453.7	453.5	453.4	452.8	451.9	451.0	450.1	449.2	449.9
12.5°	449.3	449.0	448.7	448.5	448.1	447.6	446.7	445.9	445.0	444.3	444.7
15°	440.5	440.2	440.0	439.7	439.4	438.9	438.0	437.1	436.2	435.3	435.7
17.5°	430.2	429.9	429.5	429.2	428.8	428.2	427.2	426.4	425.4	424.5	425.0
20°	421.8	421.6	421.4	421.3	421.1	420.5	419.5	418.4	417.3	416.3	416.8
22.5°	413.3	413.0	412.6	412.4	412.1	411.5	410.4	409.5	408.4	407.5	407.9
25°	399.8	399.4	398.9	398.5	398.2	397.4	396.4	395.3	394.3	393.2	393.4
27.5°	384.0	383.8	383.6	383.3	383.1	382.4	381.4	380.2	379.1	378.0	378.1
30°	373.8	373.6	373.3	373.0	372.8	372.1	370.9	369.6	368.4	367.2	367.0
32.5°	362.7	362.3	361.9	361.6	361.2	360.4	359.3	358.2	357.2	356.1	355.8
35°	345.2	344.9	344.6	344.3	344.0	343.2	342.1	341.0	339.8	338.7	338.3
37.5°	327.2	326.8	326.4	325.9	325.5	324.8	323.7	322.7	321.5	320.5	319.9
40°	314.9	314.4	314.0	313.6	313.2	312.4	311.3	310.2	309.0	307.9	307.2
42.5°	301.7	301.3	301.0	300.6	300.3	299.6	298.4	297.3	296.1	295.0	294.4
45°	282.7	282.3	282.0	281.7	281.3	280.7	279.7	278.8	277.7	276.8	275.8
47.5°	262.1	262.1	262.1	262.2	262.2	261.7	260.5	259.3	258.1	256.9	256.0
50°	249.0	248.7	248.5	248.2	248.0	247.4	246.4	245.4	244.5	243.4	242.4
52.5°	235.5	235.3	235.1	235.0	234.8	234.2	233.1	232.1	231.0	230.0	229.1
55°	215.2	215.0	214.8	214.5	214.3	213.6	212.5	211.4	210.2	209.1	208.3
57.5°	194.0	193.8	193.7	193.6	193.5	192.9	191.9	191.0	190.0	189.1	188.1
60°	180.5	180.1	179.8	179.5	179.2	178.6	177.7	176.8	175.9	175.0	174.2
62.5°	166.4	166.2	165.9	165.6	165.4	164.9	164.1	163.3	162.6	161.8	161.0
65°	145.4	145.2	145.0	144.9	144.7	144.2	143.3	142.4	141.5	140.6	139.8
67.5°	124.9	124.6	124.2	123.9	123.6	123.0	122.4	121.7	121.0	120.4	119.8
70°	112.0	111.6	111.2	110.8	110.4	109.8	109.1	108.4	107.7	106.9	106.4
72.5°	98.0	97.7	97.4	97.1	96.9	96.5	96.0	95.5	95.1	94.6	94.0
75°	77.2	77.1	76.9	76.8	76.6	76.3	75.9	75.5	75.1	74.7	74.5
77.5°	58.1	58.1	58.0	57.9	57.9	57.8	57.5	57.3	57.0	56.8	56.6
80°	46.1	46.1	46.1	46.1	46.1	46.0	45.9	45.7	45.6	45.4	45.3
82.5°	35.6	35.5	35.3	35.2	35.1	35.0	34.9	34.9	34.9	34.9	34.7
85°	20.1	20.2	20.3	20.4	20.4	20.5	20.5	20.5	20.5	20.5	20.4
87.5°	8.0	8.2	8.3	8.5	8.6	8.8	8.9	8.9	9.0	9.0	9.2
90°	0.5	1.3	2.1	2.9	3.6	4.4	5.1	5.9	6.5	7.2	7.8
92.5°	10.9	11.5	12.0	12.6	13.2	13.9	14.7	15.6	16.5	17.3	18.0
95°	29.4	29.5	29.8	29.9	30.2	30.8	31.8	32.8	33.8	34.8	35.5
97.5°	48.8	48.9	49.0	49.0	49.1	49.8	51.3	52.6	54.0	55.4	56.1
100°	63.3	63.3	63.3	63.3	63.3	63.9	65.2	66.5	67.8	69.2	70.0
102.5°	78.8	79.2	79.6	80.0	80.4	81.0	81.6	82.3	82.9	83.6	84.6
105°	103.1	103.5	104.0	104.6	105.0	105.6	106.2	106.8	107.4	108.0	108.6
107.5°	129.8	130.3	130.8	131.3	131.8	132.3	132.8	133.2	133.6	134.1	134.4
110°	148.2	148.7	149.2	149.7	150.3	150.7	150.9	151.2	151.5	151.9	152.2



TEST NUMBER: P333131-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.0	167.3	167.5	167.8	168.1	168.4	168.8	169.1	169.5	169.9	170.1
115°	194.8	195.2	195.6	196.0	196.4	196.7	196.9	197.1	197.3	197.5	197.4
117.5°	222.6	222.8	223.0	223.2	223.3	223.6	223.7	223.9	224.0	224.3	224.3
120°	240.0	240.5	241.0	241.5	242.0	242.2	242.4	242.5	242.6	242.6	242.6
122.5°	258.8	259.0	259.1	259.3	259.5	259.7	260.0	260.2	260.5	260.8	260.7
125°	284.2	284.9	285.4	286.1	286.7	287.0	287.1	287.2	287.3	287.4	287.2
127.5°	311.4	311.7	312.0	312.4	312.8	313.0	313.1	313.2	313.3	313.5	313.4
130°	327.6	328.1	328.7	329.2	329.6	330.0	330.2	330.4	330.6	330.8	330.7
132.5°	343.9	344.8	345.5	346.3	347.2	347.6	347.5	347.5	347.5	347.5	347.4
135°	369.6	370.3	370.9	371.5	372.1	372.4	372.6	372.6	372.7	372.8	372.8
137.5°	393.9	394.5	395.1	395.6	396.2	396.6	396.9	397.0	397.3	397.5	397.6
140°	409.4	410.0	410.4	410.9	411.5	411.9	412.2	412.5	412.7	413.0	413.3
142.5°	425.0	425.4	425.8	426.3	426.7	427.1	427.5	427.9	428.3	428.6	428.7
145°	447.8	448.2	448.7	449.1	449.5	449.8	450.1	450.4	450.8	451.0	451.0
147.5°	469.0	469.2	469.4	469.7	469.9	470.1	470.3	470.6	470.9	471.1	471.3
150°	483.1	483.0	482.9	482.8	482.7	482.8	483.2	483.6	484.0	484.4	484.4
152.5°	494.6	494.8	495.0	495.1	495.2	495.4	495.5	495.7	495.8	496.1	496.3
155°	512.5	512.5	512.5	512.5	512.5	512.5	512.6	512.7	512.9	512.9	513.3
157.5°	528.4	528.1	527.9	527.8	527.5	527.4	527.5	527.7	527.8	527.8	528.2
160°	537.8	537.5	537.2	536.9	536.5	536.5	536.5	536.7	536.8	536.9	537.3
162.5°	546.1	545.9	545.7	545.4	545.2	545.1	545.1	545.2	545.2	545.2	545.7
165°	557.2	557.0	556.8	556.6	556.4	556.3	556.4	556.6	556.7	556.7	557.1
167.5°	566.6	566.3	565.8	565.4	565.0	564.8	564.8	564.8	564.8	564.8	565.4
170°	571.6	571.2	570.8	570.5	570.1	569.9	569.9	569.9	569.9	569.9	570.5
172.5°	575.3	574.9	574.5	574.1	573.7	573.5	573.5	573.5	573.5	573.5	574.1
175°	579.3	578.9	578.5	578.1	577.7	577.6	577.6	577.6	577.6	577.6	578.1
177.5°	581.5	581.1	580.8	580.5	580.1	580.0	579.9	579.8	579.7	579.6	580.1
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7



TEST NUMBER: P333131-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	461.4	462.1	462.7	463.0	463.0	462.9	462.9	462.8
5°	459.1	459.9	460.6	460.9	460.8	460.7	460.7	460.6
7.5°	454.5	455.2	455.9	456.2	456.1	456.1	456.0	455.9
10°	450.5	451.1	451.9	452.1	452.0	451.9	451.9	451.8
12.5°	445.3	445.8	446.3	446.6	446.6	446.6	446.6	446.5
15°	436.1	436.5	437.0	437.1	437.1	437.1	437.1	437.1
17.5°	425.5	426.0	426.5	426.5	426.1	425.7	425.3	424.9
20°	417.4	418.0	418.5	418.7	418.2	417.8	417.4	417.0
22.5°	408.2	408.6	409.0	409.0	408.8	408.4	408.2	407.9
25°	393.6	393.7	393.9	393.8	393.6	393.3	393.1	392.8
27.5°	378.1	378.1	378.2	378.1	377.8	377.6	377.3	377.1
30°	366.9	366.7	366.5	366.4	366.1	365.9	365.6	365.4
32.5°	355.5	355.2	354.9	354.6	354.1	353.6	353.2	352.8
35°	337.9	337.5	337.0	336.5	335.9	335.2	334.5	333.9
37.5°	319.3	318.7	318.1	317.6	317.2	316.9	316.5	316.1
40°	306.4	305.7	305.0	304.5	304.3	304.0	303.7	303.5
42.5°	293.7	293.0	292.3	291.8	291.4	291.0	290.7	290.3
45°	274.8	273.9	272.9	272.3	272.0	271.8	271.6	271.3
47.5°	254.9	254.0	252.9	252.2	251.6	251.0	250.5	249.9
50°	241.4	240.3	239.2	238.4	237.8	237.3	236.7	236.1
52.5°	228.1	227.2	226.2	225.5	224.9	224.3	223.6	223.0
55°	207.6	206.8	206.1	205.5	204.9	204.3	203.7	203.2
57.5°	187.2	186.2	185.3	184.7	184.3	184.0	183.7	183.4
60°	173.4	172.5	171.7	171.0	170.5	169.9	169.4	168.8
62.5°	160.1	159.1	158.3	157.6	157.2	156.8	156.3	155.9
65°	139.1	138.4	137.7	137.1	136.8	136.5	136.2	135.9
67.5°	119.1	118.5	117.9	117.5	117.3	117.1	116.9	116.7
70°	105.9	105.4	105.0	104.6	104.3	103.9	103.5	103.2
72.5°	93.5	92.9	92.4	92.0	91.7	91.3	90.9	90.6
75°	74.2	74.0	73.7	73.4	73.1	72.8	72.5	72.1
77.5°	56.6	56.4	56.2	56.1	55.8	55.6	55.4	55.1
80°	45.2	45.2	45.1	44.9	44.8	44.6	44.4	44.3
82.5°	34.5	34.4	34.3	34.1	34.1	34.1	34.1	34.1
85°	20.4	20.3	20.2	20.0	19.9	19.7	19.6	19.4
87.5°	9.3	9.3	9.4	9.5	9.4	9.3	9.3	9.2
90°	8.2	8.7	9.3	9.7	10.0	10.2	10.5	10.9
92.5°	18.7	19.3	20.0	20.4	20.7	20.9	21.1	21.3
95°	36.2	36.9	37.6	38.0	38.3	38.5	38.7	38.9
97.5°	56.7	57.4	58.1	58.5	58.5	58.7	58.8	58.9
100°	71.0	71.9	72.7	73.3	73.5	73.8	73.9	74.1
102.5°	85.6	86.6	87.5	88.2	88.5	88.7	89.0	89.3
105°	109.2	109.8	110.4	110.9	111.1	111.5	111.8	112.1
107.5°	134.8	135.1	135.3	135.5	135.5	135.5	135.4	135.4
110°	152.4	152.7	153.0	153.1	153.0	153.0	152.8	152.7



TEST NUMBER: P333131-927

CATALOG NUMBER: S125DIP-S375D590U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.2	170.3	170.5	170.5	170.3	170.1	169.9	169.8
115°	197.3	197.2	197.1	197.0	196.9	196.8	196.7	196.6
117.5°	224.4	224.5	224.6	224.4	224.0	223.6	223.2	222.8
120°	242.6	242.6	242.6	242.5	242.1	241.7	241.3	240.9
122.5°	260.6	260.5	260.5	260.2	259.9	259.6	259.3	259.0
125°	287.0	286.8	286.6	286.5	286.4	286.3	286.1	286.1
127.5°	313.2	313.1	313.1	312.9	312.7	312.5	312.3	312.1
130°	330.6	330.5	330.4	330.3	330.0	329.9	329.6	329.5
132.5°	347.2	347.1	347.1	346.8	346.6	346.3	346.0	345.7
135°	372.8	372.8	372.8	372.6	372.2	371.9	371.5	371.1
137.5°	397.8	397.8	398.0	397.8	397.3	396.8	396.3	395.8
140°	413.4	413.7	413.8	413.7	413.2	412.7	412.2	411.7
142.5°	428.8	429.0	429.0	428.9	428.4	427.9	427.4	426.9
145°	451.0	451.0	451.0	450.8	450.6	450.3	450.0	449.6
147.5°	471.6	471.8	472.1	471.8	471.1	470.5	469.8	469.1
150°	484.4	484.4	484.4	484.3	484.2	483.9	483.8	483.5
152.5°	496.5	496.8	497.0	496.9	496.5	496.2	495.8	495.5
155°	513.7	514.1	514.5	514.5	514.0	513.5	512.9	512.5
157.5°	528.6	529.0	529.4	529.3	528.6	528.0	527.4	526.6
160°	537.7	538.1	538.4	538.4	538.0	537.4	536.9	536.5
162.5°	546.1	546.6	547.2	547.1	546.5	545.9	545.3	544.7
165°	557.5	557.9	558.4	558.3	557.7	557.1	556.4	555.9
167.5°	566.0	566.6	567.2	567.2	566.6	565.9	565.3	564.7
170°	571.1	571.6	572.3	572.2	571.6	570.8	570.1	569.4
172.5°	574.7	575.3	575.9	575.9	575.3	574.6	574.0	573.4
175°	578.8	579.3	580.0	579.9	579.2	578.5	577.8	577.1
177.5°	580.6	581.1	581.5	581.5	581.0	580.4	579.8	579.2
180°	580.7	580.7	580.7	580.7	580.7	580.7	580.7	580.7

(END OF REPORT)