

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333601

Luminaire Tested: **S125RDIP-S1090D1035U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333601
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1035U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8361.5 lumens
Efficiency: N/A
Efficacy: 138.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333601

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333601

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	87	90	87	84	81	74	71	69	62	60	58	50	49	48	43
2	90	82	76	71	82	76	71	66	65	61	58	54	52	49	45	43	41	36
3	82	72	65	59	75	67	61	56	57	53	49	48	45	42	40	37	35	31
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	32	29	27	23
6	63	51	43	38	58	48	41	36	41	36	31	35	31	27	29	26	23	21
7	59	47	39	33	54	43	36	31	37	32	28	32	28	24	27	23	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	16
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11544	11544	11544
5°	11570	11439	11509
10°	11482	11332	11332
15°	11346	11102	11012
20°	11171	10781	10652
25°	10967	10467	10236
30°	10712	10097	9775
35°	10452	9717	9260
40°	10209	9321	8752
45°	9913	8878	8199
50°	9616	8396	7623
55°	9272	7935	7007
60°	8928	7375	6347
65°	8520	6725	5590
70°	8055	5914	4817
75°	7411	4986	4007
80°	6527	3916	3362
85°	5498	3201	3001



TEST NUMBER: P333601

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.1	2.0
10°-20°	469.7	5.6
20°-30°	681.1	8.1
30°-40°	776.2	9.3
40°-50°	756.6	9.0
50°-60°	636.9	7.6
60°-70°	446.5	5.3
70°-80°	229.5	2.7
80°-90°	60.8	0.7
90°-100°	49.0	0.6
100°-110°	301.7	3.6
110°-120°	547.1	6.5
120°-130°	702.2	8.4
130°-140°	755.2	9.0
140°-150°	708.9	8.5
150°-160°	573.4	6.9
160°-170°	370.9	4.4
170°-180°	127.9	1.5
0°-30°	1318.9	15.8
0°-40°	2095.1	25.1
0°-60°	3488.6	41.7
0°-90°	4225.3	50.5
90°-120°	897.7	10.7
90°-150°	3064.0	36.6
90°-180°	4136.0	49.5
0°-180°	8361.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1787	1787	1787	1787	1787	
5°	1785	1779	1764	1777	1775	169
15°	1697	1688	1660	1659	1647	478
25°	1539	1517	1469	1451	1436	708
35°	1326	1292	1232	1194	1174	830
45°	1085	1044	972	920	898	837
55°	824	778	705	646	622	736
65°	558	510	440	388	366	552
75°	297	256	200	171	161	314
85°	74	51	43	42	40	83
90°	1	9	16	21	24	6
95°	57	52	16	21	21	73
105°	294	297	298	297	296	311
115°	551	556	557	553	547	546
125°	784	790	791	787	784	700
135°	978	983	982	979	974	753
145°	1133	1135	1135	1136	1130	708
155°	1248	1243	1244	1246	1239	575
165°	1317	1311	1312	1317	1310	372
175°	1347	1341	1342	1349	1341	128
180°	1347	1347	1347	1347	1347	



TEST NUMBER: P333601

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1790.6	1789.9	1789.2	1788.4	1787.7	1786.2	1783.8	1781.4	1779.0	1776.6	1779.0
5°	1784.7	1783.5	1782.3	1781.1	1779.9	1777.6	1774.3	1771.0	1767.7	1764.4	1767.4
7.5°	1767.1	1766.0	1764.8	1763.7	1762.5	1760.0	1756.0	1752.1	1748.1	1744.2	1746.3
10°	1750.9	1750.0	1749.1	1748.2	1747.3	1744.8	1740.6	1736.4	1732.2	1728.0	1728.9
12.5°	1732.5	1731.4	1730.3	1729.1	1728.0	1724.6	1719.0	1713.3	1707.7	1702.0	1702.7
15°	1696.9	1695.1	1693.3	1691.5	1689.7	1685.7	1679.4	1673.1	1666.8	1660.5	1660.2
17.5°	1656.7	1653.9	1651.2	1648.4	1645.6	1640.3	1632.4	1624.5	1616.5	1608.6	1607.1
20°	1625.4	1622.4	1619.4	1616.4	1613.4	1607.1	1597.5	1587.9	1578.3	1568.7	1567.2
22.5°	1590.8	1587.8	1584.8	1581.8	1578.8	1572.3	1562.2	1552.1	1542.0	1531.9	1529.0
25°	1539.0	1534.5	1530.0	1525.5	1521.0	1513.2	1502.1	1491.0	1479.9	1468.8	1464.9
27.5°	1479.6	1474.1	1468.6	1463.2	1457.7	1449.1	1437.2	1425.3	1413.4	1401.5	1396.1
30°	1436.4	1430.7	1425.0	1419.3	1413.6	1404.4	1391.8	1379.2	1366.6	1354.0	1347.1
32.5°	1394.2	1387.6	1380.9	1374.3	1367.6	1357.9	1345.0	1332.2	1319.3	1306.5	1298.9
35°	1325.7	1318.5	1311.3	1304.1	1296.9	1286.5	1273.0	1259.5	1246.0	1232.5	1223.8
37.5°	1258.4	1249.7	1240.9	1232.2	1223.4	1212.1	1198.1	1184.2	1170.3	1156.4	1145.9
40°	1210.9	1201.9	1192.9	1183.9	1174.9	1163.2	1148.8	1134.4	1120.0	1105.6	1094.2
42.5°	1161.2	1152.0	1142.8	1133.5	1124.3	1112.2	1097.3	1082.5	1067.6	1052.7	1041.8
45°	1085.4	1076.7	1068.0	1059.3	1050.6	1038.0	1021.5	1005.0	988.5	972.0	960.0
47.5°	1006.8	997.6	988.4	979.3	970.1	957.2	940.6	923.9	907.3	890.7	878.3
50°	957.1	947.2	937.3	927.4	917.5	904.0	886.9	869.8	852.7	835.6	823.0
52.5°	903.1	893.0	882.8	872.7	862.6	849.4	833.3	817.1	801.0	784.9	771.3
55°	823.5	813.9	804.3	794.7	785.1	771.9	755.1	738.3	721.5	704.7	691.2
57.5°	743.0	732.8	722.5	712.2	702.0	688.8	672.6	656.4	640.2	624.0	610.8
60°	691.2	680.7	670.2	659.7	649.2	635.8	619.6	603.4	587.2	571.0	557.8
62.5°	636.1	626.1	616.1	606.0	596.0	582.8	566.4	549.9	533.5	517.0	504.8
65°	557.5	547.3	537.1	526.9	516.7	503.7	487.8	471.9	456.0	440.1	428.1
67.5°	479.5	469.3	459.1	448.9	438.7	426.0	410.7	395.5	380.3	365.0	354.1
70°	426.6	416.4	406.2	396.0	385.8	373.2	358.2	343.2	328.2	313.2	303.9
72.5°	374.8	364.8	354.8	344.9	334.9	322.9	308.9	294.8	280.8	266.8	258.2
75°	297.0	288.0	279.0	270.0	261.0	250.2	237.6	225.0	212.4	199.8	193.2
77.5°	219.8	212.6	205.4	198.2	191.0	182.3	172.3	162.2	152.1	142.0	137.4
80°	175.5	168.3	161.1	153.9	146.7	138.9	130.5	122.1	113.7	105.3	102.6
82.5°	132.3	125.8	119.3	112.9	106.4	100.3	94.5	88.7	83.0	77.2	76.0
85°	74.2	68.8	63.4	58.0	52.6	49.2	47.7	46.2	44.7	43.2	42.9
87.5°	25.0	23.7	22.4	21.1	19.7	19.1	19.2	19.3	19.3	19.4	19.6
90°	1.0	2.8	4.5	6.3	8.1	9.8	11.3	12.9	14.4	16.0	17.1
92.5°	15.4	14.1	12.9	11.6	10.4	10.5	11.8	13.2	14.6	16.0	17.1
95°	56.9	56.2	55.6	54.9	54.3	49.7	41.3	32.8	24.4	16.0	17.1
97.5°	118.8	120.0	121.2	122.4	123.6	115.9	99.2	82.5	65.8	49.1	42.9
100°	166.7	167.4	168.1	168.7	169.4	170.2	171.1	172.0	172.8	173.7	140.7
102.5°	215.5	216.3	217.2	218.0	218.8	219.5	220.1	220.6	221.1	221.7	215.4
105°	293.5	294.4	295.3	296.2	297.1	297.5	297.5	297.5	297.5	297.5	297.5
107.5°	374.6	374.6	374.6	374.6	374.6	374.8	375.3	375.7	376.2	376.6	376.7
110°	427.3	427.3	427.3	427.3	427.3	427.6	428.0	428.5	428.9	429.3	428.7



TEST NUMBER: P333601

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	476.9	477.4	477.9	478.5	479.0	479.4	479.7	479.9	480.2	480.5	479.6
115°	551.2	552.3	553.4	554.5	555.6	556.3	556.5	556.7	556.9	557.1	556.3
117.5°	628.0	628.0	627.9	627.9	627.9	628.3	629.1	629.9	630.8	631.6	630.5
120°	676.0	675.7	675.5	675.3	675.1	675.3	676.0	676.6	677.3	678.0	677.5
122.5°	718.3	719.1	720.0	720.8	721.7	722.2	722.6	722.9	723.2	723.5	723.0
125°	783.8	785.3	786.9	788.5	790.0	790.8	790.8	790.8	790.8	790.8	789.9
127.5°	846.3	847.4	848.5	849.6	850.7	851.2	851.1	851.0	850.8	850.7	850.2
130°	884.6	885.8	886.9	888.0	889.1	889.7	890.0	890.2	890.4	890.6	890.0
132.5°	923.0	924.3	925.6	926.8	928.1	928.5	928.0	927.6	927.1	926.6	926.4
135°	977.5	978.8	980.2	981.5	982.8	983.3	982.8	982.4	981.9	981.5	981.0
137.5°	1027.6	1028.8	1029.9	1031.1	1032.2	1032.6	1032.2	1031.8	1031.4	1031.0	1031.1
140°	1060.4	1060.8	1061.3	1061.7	1062.1	1062.3	1062.0	1061.8	1061.6	1061.4	1061.8
142.5°	1089.9	1090.2	1090.5	1090.7	1091.0	1091.3	1091.6	1091.9	1092.2	1092.5	1092.6
145°	1133.3	1133.7	1134.1	1134.6	1135.0	1135.3	1135.3	1135.3	1135.3	1135.3	1135.5
147.5°	1171.2	1171.1	1171.0	1170.9	1170.8	1170.9	1171.2	1171.5	1171.7	1172.0	1172.3
150°	1195.2	1194.7	1194.3	1193.8	1193.4	1193.4	1193.8	1194.3	1194.7	1195.2	1195.6
152.5°	1218.3	1217.4	1216.4	1215.4	1214.4	1214.2	1214.6	1215.0	1215.5	1215.9	1216.4
155°	1248.1	1246.8	1245.4	1244.1	1242.8	1242.3	1242.8	1243.2	1243.6	1244.1	1244.8
157.5°	1271.0	1270.2	1269.5	1268.7	1267.9	1267.5	1267.5	1267.6	1267.6	1267.7	1268.4
160°	1287.0	1285.7	1284.4	1283.0	1281.7	1281.1	1281.4	1281.6	1281.8	1282.0	1282.9
162.5°	1299.8	1298.5	1297.1	1295.8	1294.5	1293.9	1294.1	1294.4	1294.6	1294.8	1296.1
165°	1317.0	1315.6	1314.3	1313.0	1311.7	1311.1	1311.3	1311.5	1311.8	1312.0	1313.3
167.5°	1329.8	1328.4	1327.0	1325.6	1324.3	1323.7	1323.9	1324.1	1324.3	1324.6	1326.2
170°	1336.9	1335.4	1333.8	1332.3	1330.7	1330.1	1330.3	1330.5	1330.7	1331.0	1332.7
172.5°	1341.7	1340.2	1338.6	1337.1	1335.5	1335.0	1335.3	1335.7	1336.1	1336.5	1338.1
175°	1346.9	1345.6	1344.3	1342.9	1341.6	1341.1	1341.3	1341.5	1341.7	1341.9	1343.7
177.5°	1349.3	1348.3	1347.2	1346.1	1345.1	1344.6	1344.8	1345.0	1345.2	1345.3	1346.6
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9



TEST NUMBER: P333601

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1781.4	1783.8	1786.2	1787.2	1787.0	1786.8	1786.5	1786.3
5°	1770.4	1773.4	1776.4	1777.6	1777.0	1776.4	1775.8	1775.2
7.5°	1748.4	1750.5	1752.6	1753.3	1752.6	1752.0	1751.3	1750.6
10°	1729.8	1730.7	1731.6	1731.6	1730.7	1729.8	1728.9	1728.0
12.5°	1703.4	1704.0	1704.7	1704.3	1702.9	1701.6	1700.2	1698.8
15°	1659.9	1659.6	1659.3	1657.8	1655.1	1652.4	1649.7	1647.0
17.5°	1605.6	1604.1	1602.6	1600.8	1598.5	1596.3	1594.1	1591.9
20°	1565.7	1564.2	1562.7	1560.6	1557.9	1555.2	1552.5	1549.8
22.5°	1526.1	1523.1	1520.2	1517.6	1515.4	1513.2	1510.9	1508.7
25°	1461.0	1457.1	1453.2	1449.6	1446.3	1443.0	1439.7	1436.4
27.5°	1390.6	1385.2	1379.7	1375.4	1372.2	1369.0	1365.8	1362.7
30°	1340.2	1333.3	1326.4	1321.6	1318.9	1316.2	1313.5	1310.8
32.5°	1291.3	1283.6	1276.0	1270.5	1267.1	1263.7	1260.2	1256.8
35°	1215.1	1206.4	1197.7	1191.3	1187.1	1182.9	1178.7	1174.5
37.5°	1135.5	1125.1	1114.6	1107.4	1103.3	1099.2	1095.1	1091.0
40°	1082.8	1071.4	1060.0	1052.5	1048.9	1045.3	1041.7	1038.1
42.5°	1030.9	1019.9	1009.0	1000.9	995.6	990.4	985.1	979.8
45°	948.0	936.0	924.0	915.7	911.2	906.7	902.2	897.7
47.5°	866.0	853.6	841.3	832.6	827.6	822.6	817.7	812.7
50°	810.4	797.8	785.2	776.7	772.2	767.7	763.2	758.7
52.5°	757.8	744.2	730.6	721.6	717.1	712.6	708.1	703.6
55°	677.7	664.2	650.7	641.5	636.7	631.9	627.1	622.3
57.5°	597.6	584.4	571.2	562.4	558.2	553.9	549.6	545.4
60°	544.6	531.4	518.2	509.4	504.9	500.4	495.9	491.4
62.5°	492.6	480.3	468.1	459.7	455.2	450.7	446.2	441.7
65°	416.1	404.1	392.1	383.8	379.3	374.8	370.3	365.8
67.5°	343.1	332.1	321.1	313.8	310.2	306.6	303.0	299.4
70°	294.6	285.3	276.0	269.5	265.9	262.3	258.7	255.1
72.5°	249.6	241.0	232.4	226.9	224.5	222.1	219.7	217.3
75°	186.6	180.0	173.4	169.0	166.9	164.8	162.7	160.6
77.5°	132.8	128.2	123.5	120.4	118.9	117.3	115.8	114.2
80°	99.9	97.2	94.5	92.8	92.2	91.6	91.0	90.4
82.5°	74.7	73.4	72.2	71.4	71.0	70.6	70.3	69.9
85°	42.6	42.3	42.0	41.7	41.4	41.1	40.8	40.5
87.5°	19.8	20.1	20.3	20.3	20.2	20.1	20.0	19.9
90°	18.2	19.3	20.4	21.3	22.0	22.6	23.3	24.0
92.5°	18.2	19.3	20.4	21.1	21.4	21.7	22.1	22.4
95°	18.2	19.3	20.4	21.0	21.0	21.0	21.0	21.0
97.5°	36.6	30.4	24.1	21.0	21.0	21.0	21.0	21.0
100°	107.6	74.6	41.5	24.5	23.6	22.7	21.9	21.0
102.5°	209.1	202.9	196.6	186.0	170.9	155.8	140.7	125.6
105°	297.5	297.5	297.5	297.4	297.2	297.0	296.8	296.5
107.5°	376.7	376.8	376.8	376.5	375.8	375.2	374.5	373.8
110°	428.0	427.3	426.7	426.5	426.7	426.9	427.1	427.3



TEST NUMBER: P333601

CATALOG NUMBER: S125RDIP-S1090D1035U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	478.8	477.9	477.1	476.5	476.2	475.9	475.6	475.3
115°	555.4	554.5	553.6	552.5	551.2	549.8	548.5	547.2
117.5°	629.3	628.2	627.0	626.1	625.6	625.0	624.4	623.8
120°	677.1	676.6	676.2	675.4	674.3	673.2	672.1	671.0
122.5°	722.6	722.2	721.7	720.8	719.6	718.3	717.0	715.7
125°	789.0	788.1	787.2	786.5	785.8	785.1	784.5	783.8
127.5°	849.7	849.2	848.7	847.7	846.0	844.4	842.8	841.1
130°	889.3	888.6	888.0	887.1	886.0	884.9	883.8	882.6
132.5°	926.3	926.2	926.0	925.4	924.3	923.2	922.1	921.0
135°	980.6	980.2	979.7	978.8	977.5	976.2	974.8	973.5
137.5°	1031.2	1031.3	1031.4	1030.8	1029.7	1028.5	1027.4	1026.2
140°	1062.3	1062.7	1063.1	1062.7	1061.4	1060.0	1058.7	1057.4
142.5°	1092.7	1092.8	1092.9	1092.3	1090.9	1089.6	1088.3	1086.9
145°	1135.7	1135.9	1136.1	1135.6	1134.3	1132.9	1131.6	1130.3
147.5°	1172.5	1172.8	1173.1	1172.4	1170.8	1169.2	1167.6	1166.0
150°	1196.1	1196.5	1196.9	1196.3	1194.5	1192.7	1190.9	1189.2
152.5°	1216.8	1217.3	1217.7	1217.1	1215.5	1213.9	1212.3	1210.7
155°	1245.4	1246.1	1246.8	1246.2	1244.4	1242.6	1240.9	1239.1
157.5°	1269.1	1269.8	1270.5	1270.0	1268.2	1266.4	1264.6	1262.9
160°	1283.8	1284.7	1285.6	1285.1	1283.4	1281.6	1279.8	1278.0
162.5°	1297.3	1298.5	1299.8	1299.4	1297.5	1295.5	1293.6	1291.6
165°	1314.6	1316.0	1317.3	1317.1	1315.3	1313.5	1311.8	1310.0
167.5°	1327.8	1329.4	1331.0	1330.8	1328.8	1326.8	1324.8	1322.8
170°	1334.5	1336.3	1338.1	1337.9	1335.9	1334.0	1332.0	1330.0
172.5°	1339.7	1341.3	1342.9	1342.7	1340.7	1338.7	1336.7	1334.8
175°	1345.5	1347.3	1349.0	1348.9	1346.9	1344.9	1342.9	1340.9
177.5°	1347.8	1349.1	1350.3	1350.2	1348.8	1347.4	1346.0	1344.5
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9

(END OF REPORT)