

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333604

Luminaire Tested: **S125RDIP-S1090D1205U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333604  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D1205U835-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9077.4 lumens  
Efficiency: N/A  
Efficacy: 138.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47					47			
1	98	93	90	86	90	86	83	80	72	70	68	59	58	57	48	47	46					40				
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39					34				
3	81	72	65	60	75	67	61	56	56	52	48	47	44	41	38	36	34					30				
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	31	29					26				
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26					22				
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23					20				
7	58	46	39	33	54	43	36	31	37	31	28	31	27	24	26	23	20					18				
8	54	42	35	29	50	39	32	28	34	28	24	28	24	21	24	20	18					16				
9	51	38	31	26	46	36	29	25	31	26	22	26	22	19	22	19	16					14				
10	47	35	28	23	43	33	27	22	28	23	20	24	20	17	20	17	15					13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10619	10619	10619	10619
5°	12217	10633	9390	10633
10°	14014	10579	8286	10579
15°	15136	10470	7365	10470
20°	16690	10344	6801	10344
25°	19316	10177	6310	10177
30°	21020	10001	5990	10001
35°	17731	9797	5694	9797
40°	12382	9429	5440	9429
45°	9186	8933	5191	8933
50°	7324	8416	4977	8416
55°	6217	7775	4788	7775
60°	5371	7201	4481	7201
65°	4786	6580	3857	6580
70°	4205	6027	3518	6027
75°	3638	5220	3301	5220
80°	2760	4392	2760	4392
85°	2297	3453	2601	3453



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.7	1.7
10°-20°	462.1	5.1
20°-30°	732.6	8.1
30°-40°	883.5	9.7
40°-50°	789.0	8.7
50°-60°	605.0	6.7
60°-70°	393.2	4.3
70°-80°	191.2	2.1
80°-90°	48.9	0.5
90°-100°	57.0	0.6
100°-110°	351.1	3.9
110°-120°	636.8	7.0
120°-130°	817.3	9.0
130°-140°	879.1	9.7
140°-150°	825.1	9.1
150°-160°	667.5	7.4
160°-170°	431.7	4.8
170°-180°	148.9	1.6
0°-30°	1352.3	14.9
0°-40°	2235.8	24.6
0°-60°	3629.8	40.0
0°-90°	4263.0	47.0
90°-120°	1044.9	11.5
90°-150°	3566.4	39.3
90°-180°	4814.0	53.0
0°-180°	9077.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1884	1640	1448	1640	1884	188
15°	2264	1566	1102	1566	2264	649
25°	2711	1428	886	1428	2711	1245
35°	2249	1243	722	1243	2249	1358
45°	1006	978	568	978	1006	802
55°	552	690	425	690	552	501
65°	313	431	252	431	313	312
75°	146	209	132	209	146	155
85°	31	47	35	47	31	36
90°	28	1	28	1	28	14
95°	24	66	24	66	24	20
105°	345	342	345	342	345	312
115°	637	642	637	642	637	632
125°	912	912	912	912	912	812
135°	1133	1138	1133	1138	1133	874
145°	1316	1319	1316	1319	1316	822
155°	1442	1453	1442	1453	1442	665
165°	1525	1533	1525	1533	1525	430
175°	1561	1568	1561	1568	1561	149
180°	1568	1568	1568	1568	1568	



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1729.5	1728.4	1730.6	1724.6	1725.2	1716.0	1716.0	1709.0	1699.8	1692.8	1689.5
5°	1884.4	1885.8	1883.1	1873.0	1866.2	1856.1	1844.6	1824.4	1807.5	1791.3	1778.5
7.5°	2044.0	2044.9	2036.0	2032.9	2015.9	2003.5	1978.0	1950.4	1926.0	1895.0	1871.2
10°	2136.9	2136.2	2126.7	2119.3	2104.5	2085.6	2060.6	2028.2	1997.8	1964.1	1931.7
12.5°	2190.9	2189.1	2186.1	2177.1	2163.3	2146.6	2125.4	2093.5	2056.1	2019.2	1981.4
15°	2263.8	2259.0	2250.3	2238.8	2219.2	2199.6	2176.0	2147.7	2111.9	2070.0	2035.0
17.5°	2353.9	2354.1	2340.6	2324.6	2298.0	2263.5	2227.0	2181.3	2132.7	2086.7	2049.3
20°	2428.4	2426.4	2412.9	2381.9	2351.5	2308.3	2266.5	2210.4	2151.0	2091.0	2044.4
22.5°	2535.4	2530.1	2516.0	2475.3	2428.2	2372.6	2308.6	2240.1	2168.3	2100.1	2039.0
25°	2710.6	2706.5	2678.8	2631.6	2565.5	2479.7	2396.0	2302.2	2199.0	2109.2	2035.0
27.5°	2830.4	2826.0	2805.5	2766.2	2705.2	2615.0	2501.7	2376.3	2247.4	2123.9	2016.9
30°	2818.6	2828.7	2826.0	2807.8	2761.9	2680.9	2576.3	2435.2	2282.0	2136.9	2009.3
32.5°	2649.0	2658.1	2681.8	2717.6	2720.3	2687.9	2609.7	2479.5	2320.9	2155.8	2003.4
35°	2248.9	2261.1	2307.0	2379.2	2473.7	2552.6	2568.8	2498.6	2356.2	2178.7	1994.5
37.5°	1728.9	1795.3	1834.0	1910.0	2052.8	2198.0	2337.7	2389.2	2328.5	2169.3	1980.0
40°	1468.7	1484.9	1553.7	1639.4	1759.6	1910.8	2109.9	2253.6	2258.4	2147.7	1957.3
42.5°	1257.0	1277.5	1324.8	1393.2	1496.1	1647.3	1852.9	2042.5	2130.4	2088.3	1927.6
45°	1005.7	1021.2	1055.6	1108.3	1187.2	1312.1	1488.9	1708.3	1882.4	1950.6	1848.0
47.5°	826.1	834.5	864.5	904.6	963.0	1054.0	1190.9	1381.3	1590.2	1736.6	1722.2
50°	728.9	738.4	761.3	791.7	841.0	917.9	1027.3	1185.9	1401.2	1580.0	1615.8
52.5°	653.3	661.2	675.5	704.2	744.9	804.0	892.3	1035.8	1229.5	1419.7	1502.4
55°	552.1	557.5	569.0	585.2	617.6	660.1	736.4	835.6	992.2	1183.8	1305.3
57.5°	468.7	471.4	478.7	493.7	516.1	547.1	602.2	686.3	798.6	971.2	1105.3
60°	415.8	418.5	427.9	438.0	455.6	483.9	527.1	585.8	693.8	836.3	971.9
62.5°	373.6	375.3	379.3	389.4	404.8	426.7	460.7	508.6	594.5	719.6	847.7
65°	313.2	313.8	315.2	323.3	332.7	348.9	371.2	405.0	469.8	564.3	677.6
67.5°	255.1	256.1	260.8	263.6	273.5	282.0	295.1	320.9	366.5	430.2	518.4
70°	222.7	222.1	226.8	230.2	233.5	243.7	252.4	273.4	301.7	350.3	423.9
72.5°	192.5	190.7	192.8	194.0	198.4	205.3	214.1	226.9	248.8	282.3	338.6
75°	145.8	146.5	146.5	147.8	151.2	153.9	156.6	163.3	175.5	197.8	228.1
77.5°	102.3	101.2	104.1	104.5	106.5	109.5	111.8	114.5	119.5	128.6	144.3
80°	74.2	74.2	74.9	76.9	76.3	77.6	81.0	83.7	89.8	95.2	100.6
82.5°	57.0	56.4	57.1	57.5	57.4	58.7	59.9	60.5	62.8	65.5	69.2
85°	31.0	31.0	31.7	31.7	32.4	32.4	33.1	33.1	33.1	33.7	34.4
87.5°	17.5	16.8	16.1	15.9	16.3	17.2	16.4	15.6	15.3	15.1	15.2
90°	27.9	27.1	26.3	25.6	24.8	23.8	22.5	21.2	19.9	18.6	16.8
92.5°	26.0	25.7	25.3	24.9	24.6	23.8	22.5	21.2	19.9	18.6	17.0
95°	24.4	24.4	24.4	24.4	24.4	23.8	22.5	21.2	19.9	18.6	28.4
97.5°	24.4	24.4	24.4	24.4	24.4	28.0	35.3	42.6	49.9	57.2	76.6
100°	24.4	25.4	26.5	27.5	28.5	48.3	86.8	125.3	163.7	202.2	201.2
102.5°	146.2	163.8	181.3	198.9	216.5	228.9	236.2	243.4	250.7	258.0	257.4
105°	345.2	345.4	345.7	345.9	346.2	346.3	346.3	346.3	346.3	346.3	346.3
107.5°	435.1	435.9	436.7	437.4	438.2	438.6	438.5	438.5	438.4	438.4	437.9
110°	497.4	497.2	496.9	496.6	496.4	496.6	497.4	498.2	499.0	499.7	499.2



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	553.2	553.6	553.9	554.3	554.6	555.3	556.3	557.3	558.3	559.2	558.9
115°	636.9	638.4	640.0	641.5	643.1	644.4	645.4	646.4	647.5	648.5	648.2
117.5°	726.1	726.8	727.5	728.1	728.8	729.8	731.2	732.5	733.9	735.2	734.2
120°	781.0	782.3	783.6	784.9	786.2	787.1	787.6	788.1	788.6	789.1	788.3
122.5°	833.1	834.6	836.0	837.5	839.0	840.1	840.6	841.1	841.6	842.1	841.8
125°	912.3	913.1	913.9	914.6	915.4	916.3	917.3	918.4	919.4	920.4	920.4
127.5°	979.0	980.9	982.8	984.8	986.7	987.9	988.5	989.0	989.6	990.2	990.3
130°	1027.4	1028.7	1030.0	1031.2	1032.5	1033.6	1034.3	1035.1	1035.9	1036.7	1036.4
132.5°	1072.0	1073.3	1074.6	1075.9	1077.2	1077.9	1078.0	1078.2	1078.4	1078.5	1079.1
135°	1133.1	1134.7	1136.2	1137.8	1139.3	1140.4	1140.9	1141.4	1141.9	1142.4	1142.9
137.5°	1194.5	1195.8	1197.2	1198.5	1199.9	1200.5	1200.4	1200.3	1200.2	1200.1	1200.5
140°	1230.8	1232.3	1233.9	1235.4	1236.9	1237.5	1236.9	1236.4	1235.9	1235.4	1235.7
142.5°	1265.2	1266.7	1268.3	1269.8	1271.4	1272.1	1272.0	1271.9	1271.8	1271.7	1271.3
145°	1315.6	1317.1	1318.7	1320.2	1321.8	1322.4	1322.2	1321.9	1321.7	1321.4	1321.4
147.5°	1357.2	1359.1	1360.9	1362.8	1364.6	1365.4	1365.1	1364.8	1364.5	1364.2	1363.9
150°	1384.2	1386.2	1388.3	1390.4	1392.4	1393.2	1392.7	1392.2	1391.6	1391.1	1390.6
152.5°	1409.3	1411.1	1413.0	1414.8	1416.7	1417.4	1416.9	1416.3	1415.8	1415.3	1414.8
155°	1442.3	1444.3	1446.4	1448.5	1450.5	1451.2	1450.4	1449.6	1448.9	1448.1	1447.6
157.5°	1469.9	1472.0	1474.1	1476.1	1478.2	1478.8	1478.0	1477.2	1476.3	1475.5	1475.5
160°	1487.6	1489.7	1491.7	1493.8	1495.9	1496.4	1495.3	1494.3	1493.3	1492.2	1492.0
162.5°	1503.4	1505.7	1507.9	1510.2	1512.5	1512.9	1511.5	1510.0	1508.6	1507.1	1506.9
165°	1524.8	1526.8	1528.9	1531.0	1533.0	1533.3	1531.8	1530.2	1528.7	1527.1	1526.8
167.5°	1539.7	1542.0	1544.3	1546.6	1549.0	1549.2	1547.3	1545.5	1543.6	1541.8	1541.5
170°	1548.0	1550.4	1552.7	1555.0	1557.3	1557.5	1555.4	1553.3	1551.3	1549.2	1548.9
172.5°	1553.6	1555.9	1558.3	1560.6	1562.9	1563.1	1561.3	1559.4	1557.6	1555.7	1555.2
175°	1560.8	1563.1	1565.5	1567.8	1570.1	1570.2	1568.2	1566.1	1564.0	1562.0	1561.7
177.5°	1565.0	1566.6	1568.3	1570.0	1571.6	1571.7	1570.3	1568.8	1567.4	1565.9	1565.7
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1689.5	1685.7	1678.7	1672.2	1664.1	1657.1	1652.3	1646.3	1638.8	1629.6	1622.0
5°	1764.3	1749.4	1729.9	1713.0	1691.4	1674.5	1657.0	1640.1	1623.2	1601.6	1582.7
7.5°	1847.2	1816.5	1786.7	1749.2	1715.2	1684.8	1655.6	1626.1	1597.2	1566.5	1537.0
10°	1897.9	1860.8	1819.6	1772.4	1729.2	1688.0	1650.2	1613.1	1574.0	1539.5	1502.4
12.5°	1945.5	1897.5	1850.4	1790.8	1738.9	1688.6	1640.5	1594.2	1552.4	1507.7	1467.9
15°	1988.4	1941.1	1888.5	1815.6	1743.4	1682.6	1625.9	1565.9	1513.9	1463.9	1419.4
17.5°	2005.0	1955.4	1894.3	1824.2	1745.3	1668.9	1595.8	1530.0	1468.8	1410.6	1360.5
20°	1998.5	1950.6	1887.8	1821.0	1736.6	1657.0	1578.0	1505.1	1437.0	1375.5	1322.2
22.5°	1982.8	1933.3	1872.7	1802.1	1722.0	1637.5	1553.2	1475.4	1404.0	1340.4	1282.3
25°	1959.4	1891.9	1829.8	1760.9	1684.7	1601.0	1513.9	1428.2	1351.9	1287.1	1223.7
27.5°	1934.9	1850.7	1771.7	1703.3	1622.7	1548.0	1464.1	1376.2	1296.0	1230.0	1164.9
30°	1912.8	1818.3	1731.2	1653.6	1577.3	1506.5	1426.8	1341.1	1258.8	1190.6	1124.5
32.5°	1885.2	1784.8	1689.1	1599.6	1526.0	1455.7	1383.6	1301.7	1221.5	1151.2	1084.0
35°	1850.7	1722.5	1618.5	1523.3	1441.7	1373.5	1308.7	1242.6	1162.3	1089.4	1023.9
37.5°	1805.3	1659.8	1539.5	1435.9	1349.7	1281.3	1230.1	1169.7	1096.4	1026.6	965.8
40°	1777.8	1614.5	1482.8	1380.3	1289.8	1217.6	1169.7	1118.4	1051.6	986.1	925.3
42.5°	1741.1	1572.9	1425.6	1318.7	1227.7	1158.2	1109.7	1064.9	1008.9	947.2	882.1
45°	1669.1	1492.3	1337.7	1223.0	1131.2	1063.0	1017.8	978.0	935.5	878.8	822.1
47.5°	1575.4	1408.2	1246.5	1121.2	1031.3	968.0	924.1	892.7	862.3	814.1	759.0
50°	1500.4	1339.1	1181.1	1059.7	963.8	903.7	862.6	837.6	809.9	766.1	720.2
52.5°	1411.8	1267.8	1113.1	988.9	898.5	842.2	802.6	777.7	754.9	719.1	675.3
55°	1272.3	1146.1	1004.3	891.6	808.6	751.9	714.1	690.5	677.0	646.6	612.2
57.5°	1111.2	1020.8	895.8	787.1	713.7	657.7	630.0	609.9	594.6	573.2	548.9
60°	998.9	935.5	823.4	720.2	652.7	599.3	574.4	557.5	543.3	525.1	506.2
62.5°	885.0	838.8	741.4	652.7	590.6	545.9	522.5	507.3	491.0	478.7	460.3
65°	732.3	691.1	623.6	554.1	496.8	461.0	444.1	430.6	420.5	407.0	394.2
67.5°	569.7	552.9	506.3	458.4	417.2	385.4	370.8	361.4	349.2	341.1	332.3
70°	469.8	461.7	428.6	396.9	358.4	336.8	323.3	319.2	304.4	296.3	290.2
72.5°	381.2	377.4	358.4	336.4	309.3	290.4	277.9	273.4	263.9	257.4	253.5
75°	261.2	262.6	259.2	245.0	234.9	222.7	211.9	209.2	202.5	197.1	193.7
77.5°	165.2	172.1	172.4	171.7	167.7	160.2	155.8	153.8	147.1	145.1	144.3
80°	113.4	120.8	127.6	126.9	125.5	123.5	120.1	118.1	114.7	112.7	111.4
82.5°	75.6	82.5	88.1	91.8	91.5	89.5	87.2	86.3	85.6	84.1	83.8
85°	35.8	37.1	39.1	43.9	47.2	47.9	47.2	46.6	44.5	45.2	45.9
87.5°	15.4	15.1	15.2	14.8	13.9	16.2	17.4	17.5	16.8	16.2	15.5
90°	15.0	13.2	11.4	9.4	7.4	5.3	3.2	1.2	3.2	5.3	7.4
92.5°	15.4	13.8	12.2	12.1	13.6	15.0	16.5	17.9	16.5	15.0	13.6
95°	38.2	48.0	57.9	63.1	63.9	64.7	65.5	66.2	65.5	64.7	63.9
97.5°	96.0	115.4	134.9	143.9	142.5	141.1	139.7	138.3	139.7	141.1	142.5
100°	200.2	199.1	198.1	197.2	196.4	195.6	194.9	194.1	194.9	195.6	196.4
102.5°	256.8	256.1	255.5	254.7	253.7	252.8	251.8	250.8	251.8	252.8	253.7
105°	346.3	346.3	346.3	345.8	344.8	343.7	342.7	341.7	342.7	343.7	344.8
107.5°	437.3	436.8	436.3	436.1	436.1	436.1	436.1	436.1	436.1	436.1	436.1
110°	498.7	498.2	497.7	497.4	497.4	497.4	497.4	497.4	497.4	497.4	497.4





TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	558.6	558.3	558.0	557.5	556.9	556.3	555.7	555.1	555.7	556.3	556.9
115°	648.0	647.7	647.5	646.7	645.4	644.1	642.8	641.5	642.8	644.1	645.4
117.5°	733.2	732.3	731.3	730.8	730.9	730.9	731.0	731.0	731.0	730.9	730.9
120°	787.6	786.8	786.0	785.8	786.0	786.3	786.5	786.8	786.5	786.3	786.0
122.5°	841.4	841.0	840.7	840.0	839.0	838.0	837.1	836.1	837.1	838.0	839.0
125°	920.4	920.4	920.4	919.5	917.7	915.9	914.1	912.3	914.1	915.9	917.7
127.5°	990.5	990.6	990.8	990.2	988.9	987.6	986.4	985.1	986.4	987.6	988.9
130°	1036.2	1035.9	1035.6	1034.9	1033.6	1032.3	1031.0	1029.7	1031.0	1032.3	1033.6
132.5°	1079.6	1080.2	1080.8	1080.3	1078.8	1077.3	1075.8	1074.3	1075.8	1077.3	1078.8
135°	1143.5	1144.0	1144.5	1144.0	1142.4	1140.9	1139.3	1137.8	1139.3	1140.9	1142.4
137.5°	1201.0	1201.5	1201.9	1201.5	1200.1	1198.8	1197.5	1196.1	1197.5	1198.8	1200.1
140°	1235.9	1236.2	1236.4	1236.3	1235.8	1235.3	1234.8	1234.2	1234.8	1235.3	1235.8
142.5°	1270.9	1270.6	1270.2	1269.9	1269.6	1269.3	1268.9	1268.6	1268.9	1269.3	1269.6
145°	1321.4	1321.4	1321.4	1321.1	1320.6	1320.1	1319.6	1319.1	1319.6	1320.1	1320.6
147.5°	1363.5	1363.2	1362.9	1362.8	1362.9	1363.0	1363.1	1363.2	1363.1	1363.0	1362.9
150°	1390.1	1389.6	1389.1	1389.1	1389.6	1390.1	1390.6	1391.1	1390.6	1390.1	1389.6
152.5°	1414.3	1413.8	1413.2	1413.5	1414.7	1415.8	1417.0	1418.1	1417.0	1415.8	1414.7
155°	1447.0	1446.5	1446.0	1446.5	1448.1	1449.6	1451.2	1452.7	1451.2	1449.6	1448.1
157.5°	1475.4	1475.4	1475.3	1475.7	1476.7	1477.6	1478.5	1479.5	1478.5	1477.6	1476.7
160°	1491.7	1491.5	1491.2	1491.9	1493.4	1495.0	1496.5	1498.1	1496.5	1495.0	1493.4
162.5°	1506.6	1506.3	1506.1	1506.7	1508.3	1509.8	1511.4	1512.9	1511.4	1509.8	1508.3
165°	1526.6	1526.3	1526.1	1526.7	1528.3	1529.8	1531.4	1532.9	1531.4	1529.8	1528.3
167.5°	1541.2	1541.0	1540.7	1541.4	1543.0	1544.6	1546.2	1547.8	1546.2	1544.6	1543.0
170°	1548.7	1548.4	1548.2	1548.9	1550.7	1552.5	1554.4	1556.2	1554.4	1552.5	1550.7
172.5°	1554.8	1554.3	1553.8	1554.5	1556.3	1558.1	1559.9	1561.7	1559.9	1558.1	1556.3
175°	1561.5	1561.2	1560.9	1561.6	1563.1	1564.7	1566.2	1567.8	1566.2	1564.7	1563.1
177.5°	1565.5	1565.3	1565.1	1565.6	1566.9	1568.1	1569.3	1570.6	1569.3	1568.1	1566.9
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1616.6	1609.1	1603.7	1592.9	1585.3	1582.1	1576.1	1574.5	1580.4	1576.1	1575.6
5°	1568.6	1549.0	1533.5	1517.9	1501.1	1490.3	1474.1	1471.4	1467.3	1461.2	1459.9
7.5°	1510.9	1485.4	1465.4	1439.8	1417.5	1399.6	1379.3	1369.7	1364.5	1356.6	1346.1
10°	1472.0	1441.7	1414.7	1389.0	1361.4	1339.1	1318.8	1303.3	1293.2	1283.7	1279.7
12.5°	1433.7	1402.8	1368.2	1337.2	1306.3	1281.3	1258.9	1248.8	1237.6	1226.5	1217.1
15°	1374.2	1333.0	1295.2	1259.4	1233.1	1206.1	1184.5	1169.7	1152.8	1148.1	1129.9
17.5°	1311.0	1270.6	1226.4	1188.7	1158.2	1128.5	1104.7	1087.9	1075.2	1057.8	1049.4
20°	1271.6	1223.7	1180.5	1146.1	1112.3	1077.2	1052.9	1038.7	1026.6	1012.4	1005.7
22.5°	1229.5	1182.6	1138.4	1098.0	1063.7	1029.2	1011.9	997.2	983.4	970.3	961.4
25°	1167.6	1120.4	1073.8	1032.0	996.2	971.2	951.0	934.1	926.7	913.9	904.4
27.5°	1106.5	1056.3	1008.0	966.2	938.2	913.5	896.9	883.5	870.1	858.9	850.7
30°	1067.1	1015.8	963.1	930.1	900.4	876.7	858.5	845.7	835.6	825.5	819.4
32.5°	1027.7	974.8	928.0	892.3	864.2	843.8	825.0	812.8	802.1	790.9	783.7
35°	964.5	910.5	872.7	837.6	809.9	791.0	778.2	760.7	751.9	743.8	736.4
37.5°	905.8	855.6	814.7	783.9	759.8	741.1	724.5	715.0	704.2	696.9	690.7
40°	862.6	816.7	779.6	747.2	729.6	708.7	693.2	681.0	672.9	663.5	656.7
42.5°	823.7	781.0	745.0	715.8	694.0	676.3	661.3	649.2	638.9	632.2	626.5
45°	768.8	726.2	691.1	664.1	643.9	627.0	611.5	605.4	591.9	583.8	581.1
47.5°	711.9	673.9	640.0	615.1	594.4	578.4	563.8	551.4	544.0	536.0	531.7
50°	673.6	637.1	605.4	581.1	560.9	543.3	529.8	521.7	511.6	504.2	498.8
52.5°	635.3	601.5	569.8	546.6	529.0	511.5	496.4	488.3	478.7	473.9	470.2
55°	580.5	544.7	517.7	494.7	476.5	460.3	446.1	438.0	432.0	427.2	425.9
57.5°	518.4	490.0	464.9	444.2	425.3	410.1	397.7	390.0	384.6	383.9	379.9
60°	477.9	452.2	429.3	407.0	390.8	376.6	365.8	357.0	351.6	351.0	349.6
62.5°	437.4	412.8	391.5	371.9	357.3	343.7	333.4	323.6	320.3	317.0	314.0
65°	377.3	355.0	337.5	321.9	306.4	294.9	284.8	278.8	271.3	267.3	259.9
67.5°	318.3	301.0	284.2	271.1	258.9	248.0	239.6	230.6	225.6	222.3	216.9
70°	279.4	265.9	249.1	234.9	225.4	216.7	209.9	199.8	196.4	193.7	191.0
72.5°	242.7	230.8	216.7	205.2	195.7	187.5	179.7	174.9	171.6	168.9	167.3
75°	191.0	179.5	167.4	159.3	152.5	145.8	141.7	138.4	137.0	136.3	133.6
77.5°	140.3	134.2	124.5	118.0	113.5	110.8	107.2	105.4	105.3	102.3	101.4
80°	107.3	103.9	95.8	93.1	89.8	87.1	85.0	81.7	78.3	76.9	74.9
82.5°	79.8	76.4	73.2	68.8	66.0	64.4	62.4	61.1	61.6	59.7	58.7
85°	42.5	39.1	37.8	37.1	35.8	37.1	36.4	35.8	35.1	34.4	35.1
87.5°	15.4	15.8	15.6	17.0	15.8	16.7	16.9	16.7	16.9	17.2	16.8
90°	9.4	11.4	13.2	15.0	16.8	18.6	19.9	21.2	22.5	23.8	24.8
92.5°	12.1	12.2	13.8	15.4	17.0	18.6	19.9	21.2	22.5	23.8	24.6
95°	63.1	57.9	48.0	38.2	28.4	18.6	19.9	21.2	22.5	23.8	24.4
97.5°	143.9	134.9	115.4	96.0	76.6	57.2	49.9	42.6	35.3	28.0	24.4
100°	197.2	198.1	199.1	200.2	201.2	202.2	163.7	125.3	86.8	48.3	28.5
102.5°	254.7	255.5	256.1	256.8	257.4	258.0	250.7	243.4	236.2	228.9	216.5
105°	345.8	346.3	346.3	346.3	346.3	346.3	346.3	346.3	346.3	346.3	346.2
107.5°	436.1	436.3	436.8	437.3	437.9	438.4	438.4	438.5	438.5	438.6	438.2
110°	497.4	497.7	498.2	498.7	499.2	499.7	499.0	498.2	497.4	496.6	496.4



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	557.5	558.0	558.3	558.6	558.9	559.2	558.3	557.3	556.3	555.3	554.6
115°	646.7	647.5	647.7	648.0	648.2	648.5	647.5	646.4	645.4	644.4	643.1
117.5°	730.8	731.3	732.3	733.2	734.2	735.2	733.9	732.5	731.2	729.8	728.8
120°	785.8	786.0	786.8	787.6	788.3	789.1	788.6	788.1	787.6	787.1	786.2
122.5°	840.0	840.7	841.0	841.4	841.8	842.1	841.6	841.1	840.6	840.1	839.0
125°	919.5	920.4	920.4	920.4	920.4	920.4	919.4	918.4	917.3	916.3	915.4
127.5°	990.2	990.8	990.6	990.5	990.3	990.2	989.6	989.0	988.5	987.9	986.7
130°	1034.9	1035.6	1035.9	1036.2	1036.4	1036.7	1035.9	1035.1	1034.3	1033.6	1032.5
132.5°	1080.3	1080.8	1080.2	1079.6	1079.1	1078.5	1078.4	1078.2	1078.0	1077.9	1077.2
135°	1144.0	1144.5	1144.0	1143.5	1142.9	1142.4	1141.9	1141.4	1140.9	1140.4	1139.3
137.5°	1201.5	1201.9	1201.5	1201.0	1200.5	1200.1	1200.2	1200.3	1200.4	1200.5	1199.9
140°	1236.3	1236.4	1236.2	1235.9	1235.7	1235.4	1235.9	1236.4	1236.9	1237.5	1236.9
142.5°	1269.9	1270.2	1270.6	1270.9	1271.3	1271.7	1271.8	1271.9	1272.0	1272.1	1271.4
145°	1321.1	1321.4	1321.4	1321.4	1321.4	1321.4	1321.7	1321.9	1322.2	1322.4	1321.8
147.5°	1362.8	1362.9	1363.2	1363.5	1363.9	1364.2	1364.5	1364.8	1365.1	1365.4	1364.6
150°	1389.1	1389.1	1389.6	1390.1	1390.6	1391.1	1391.6	1392.2	1392.7	1393.2	1392.4
152.5°	1413.5	1413.2	1413.8	1414.3	1414.8	1415.3	1415.8	1416.3	1416.9	1417.4	1416.7
155°	1446.5	1446.0	1446.5	1447.0	1447.6	1448.1	1448.9	1449.6	1450.4	1451.2	1450.5
157.5°	1475.7	1475.3	1475.4	1475.4	1475.5	1475.5	1476.3	1477.2	1478.0	1478.8	1478.2
160°	1491.9	1491.2	1491.5	1491.7	1492.0	1492.2	1493.3	1494.3	1495.3	1496.4	1495.9
162.5°	1506.7	1506.1	1506.3	1506.6	1506.9	1507.1	1508.6	1510.0	1511.5	1512.9	1512.5
165°	1526.7	1526.1	1526.3	1526.6	1526.8	1527.1	1528.7	1530.2	1531.8	1533.3	1533.0
167.5°	1541.4	1540.7	1541.0	1541.2	1541.5	1541.8	1543.6	1545.5	1547.3	1549.2	1549.0
170°	1548.9	1548.2	1548.4	1548.7	1548.9	1549.2	1551.3	1553.3	1555.4	1557.5	1557.3
172.5°	1554.5	1553.8	1554.3	1554.8	1555.2	1555.7	1557.6	1559.4	1561.3	1563.1	1562.9
175°	1561.6	1560.9	1561.2	1561.5	1561.7	1562.0	1564.0	1566.1	1568.2	1570.2	1570.1
177.5°	1565.6	1565.1	1565.3	1565.5	1565.7	1565.9	1567.4	1568.8	1570.3	1571.7	1571.6
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1575.0	1569.1	1567.5	1569.6	1567.5	1569.1	1575.0	1575.6	1576.1	1580.4	1574.5
5°	1453.2	1446.4	1449.8	1448.4	1449.8	1446.4	1453.2	1459.9	1461.2	1467.3	1471.4
7.5°	1346.0	1337.6	1328.7	1331.5	1328.7	1337.6	1346.0	1346.1	1356.6	1364.5	1369.7
10°	1270.9	1264.2	1260.1	1263.5	1260.1	1264.2	1270.9	1279.7	1283.7	1293.2	1303.3
12.5°	1207.7	1203.7	1200.2	1198.7	1200.2	1203.7	1207.7	1217.1	1226.5	1237.6	1248.8
15°	1121.8	1113.7	1110.3	1101.5	1110.3	1113.7	1121.8	1129.9	1148.1	1152.8	1169.7
17.5°	1042.5	1039.8	1031.0	1027.3	1031.0	1039.8	1042.5	1049.4	1057.8	1075.2	1087.9
20°	995.5	992.8	984.1	989.5	984.1	992.8	995.5	1005.7	1012.4	1026.6	1038.7
22.5°	956.7	950.7	947.9	946.3	947.9	950.7	956.7	961.4	970.3	983.4	997.2
25°	901.7	892.9	889.6	885.5	889.6	892.9	901.7	904.4	913.9	926.7	934.1
27.5°	846.9	842.2	837.7	836.7	837.7	842.2	846.9	850.7	858.9	870.1	883.5
30°	811.3	806.6	803.2	803.2	803.2	806.6	811.3	819.4	825.5	835.6	845.7
32.5°	779.4	775.8	772.4	771.9	772.4	775.8	779.4	783.7	790.9	802.1	812.8
35°	733.0	727.6	726.2	722.2	726.2	727.6	733.0	736.4	743.8	751.9	760.7
37.5°	684.8	680.3	680.2	679.8	680.2	680.3	684.8	690.7	696.9	704.2	715.0
40°	654.0	650.6	650.0	645.2	650.0	650.6	654.0	656.7	663.5	672.9	681.0
42.5°	621.1	619.3	617.0	615.0	617.0	619.3	621.1	626.5	632.2	638.9	649.2
45°	576.4	571.7	571.7	568.3	571.7	571.7	576.4	581.1	583.8	591.9	605.4
47.5°	530.2	526.6	527.0	523.5	527.0	526.6	530.2	531.7	536.0	544.0	551.4
50°	499.5	497.4	496.8	495.4	496.8	497.4	499.5	498.8	504.2	511.6	521.7
52.5°	468.7	467.7	470.3	467.3	470.3	467.7	468.7	470.2	473.9	478.7	488.3
55°	427.2	425.2	429.3	425.2	429.3	425.2	427.2	425.9	427.2	432.0	438.0
57.5°	379.6	377.7	381.3	379.3	381.3	377.7	379.6	379.9	383.9	384.6	390.0
60°	348.3	344.2	346.2	346.9	346.2	344.2	348.3	349.6	351.0	351.6	357.0
62.5°	311.0	308.6	310.1	307.0	310.1	308.6	311.0	314.0	317.0	320.3	323.6
65°	258.5	256.5	253.8	252.4	253.8	256.5	258.5	259.9	267.3	271.3	278.8
67.5°	217.2	212.3	212.2	213.3	212.2	212.3	217.2	216.9	222.3	225.6	230.6
70°	187.0	187.0	186.3	186.3	186.3	187.0	187.0	191.0	193.7	196.4	199.8
72.5°	165.9	165.4	164.1	163.6	164.1	165.4	165.9	167.3	168.9	171.6	174.9
75°	133.6	134.3	133.0	132.3	133.0	134.3	133.6	133.6	136.3	137.0	138.4
77.5°	98.7	95.8	97.3	95.8	97.3	95.8	98.7	101.4	102.3	105.3	105.4
80°	74.9	74.2	76.3	74.2	76.3	74.2	74.9	74.9	76.9	78.3	81.7
82.5°	59.3	58.6	59.5	58.0	59.5	58.6	59.3	58.7	59.7	61.6	61.1
85°	35.8	35.1	34.4	35.1	34.4	35.1	35.8	35.1	34.4	35.1	35.8
87.5°	17.5	17.1	17.3	17.5	17.3	17.1	17.5	16.8	17.2	16.9	16.7
90°	25.6	26.3	27.1	27.9	27.1	26.3	25.6	24.8	23.8	22.5	21.2
92.5°	24.9	25.3	25.7	26.0	25.7	25.3	24.9	24.6	23.8	22.5	21.2
95°	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	23.8	22.5	21.2
97.5°	24.4	24.4	24.4	24.4	24.4	24.4	24.4	24.4	28.0	35.3	42.6
100°	27.5	26.5	25.4	24.4	25.4	26.5	27.5	28.5	48.3	86.8	125.3
102.5°	198.9	181.3	163.8	146.2	163.8	181.3	198.9	216.5	228.9	236.2	243.4
105°	345.9	345.7	345.4	345.2	345.4	345.7	345.9	346.2	346.3	346.3	346.3
107.5°	437.4	436.7	435.9	435.1	435.9	436.7	437.4	438.2	438.6	438.5	438.5
110°	496.6	496.9	497.2	497.4	497.2	496.9	496.6	496.4	496.6	497.4	498.2



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	554.3	553.9	553.6	553.2	553.6	553.9	554.3	554.6	555.3	556.3	557.3
115°	641.5	640.0	638.4	636.9	638.4	640.0	641.5	643.1	644.4	645.4	646.4
117.5°	728.1	727.5	726.8	726.1	726.8	727.5	728.1	728.8	729.8	731.2	732.5
120°	784.9	783.6	782.3	781.0	782.3	783.6	784.9	786.2	787.1	787.6	788.1
122.5°	837.5	836.0	834.6	833.1	834.6	836.0	837.5	839.0	840.1	840.6	841.1
125°	914.6	913.9	913.1	912.3	913.1	913.9	914.6	915.4	916.3	917.3	918.4
127.5°	984.8	982.8	980.9	979.0	980.9	982.8	984.8	986.7	987.9	988.5	989.0
130°	1031.2	1030.0	1028.7	1027.4	1028.7	1030.0	1031.2	1032.5	1033.6	1034.3	1035.1
132.5°	1075.9	1074.6	1073.3	1072.0	1073.3	1074.6	1075.9	1077.2	1077.9	1078.0	1078.2
135°	1137.8	1136.2	1134.7	1133.1	1134.7	1136.2	1137.8	1139.3	1140.4	1140.9	1141.4
137.5°	1198.5	1197.2	1195.8	1194.5	1195.8	1197.2	1198.5	1199.9	1200.5	1200.4	1200.3
140°	1235.4	1233.9	1232.3	1230.8	1232.3	1233.9	1235.4	1236.9	1237.5	1236.9	1236.4
142.5°	1269.8	1268.3	1266.7	1265.2	1266.7	1268.3	1269.8	1271.4	1272.1	1272.0	1271.9
145°	1320.2	1318.7	1317.1	1315.6	1317.1	1318.7	1320.2	1321.8	1322.4	1322.2	1321.9
147.5°	1362.8	1360.9	1359.1	1357.2	1359.1	1360.9	1362.8	1364.6	1365.4	1365.1	1364.8
150°	1390.4	1388.3	1386.2	1384.2	1386.2	1388.3	1390.4	1392.4	1393.2	1392.7	1392.2
152.5°	1414.8	1413.0	1411.1	1409.3	1411.1	1413.0	1414.8	1416.7	1417.4	1416.9	1416.3
155°	1448.5	1446.4	1444.3	1442.3	1444.3	1446.4	1448.5	1450.5	1451.2	1450.4	1449.6
157.5°	1476.1	1474.1	1472.0	1469.9	1472.0	1474.1	1476.1	1478.2	1478.8	1478.0	1477.2
160°	1493.8	1491.7	1489.7	1487.6	1489.7	1491.7	1493.8	1495.9	1496.4	1495.3	1494.3
162.5°	1510.2	1507.9	1505.7	1503.4	1505.7	1507.9	1510.2	1512.5	1512.9	1511.5	1510.0
165°	1531.0	1528.9	1526.8	1524.8	1526.8	1528.9	1531.0	1533.0	1533.3	1531.8	1530.2
167.5°	1546.6	1544.3	1542.0	1539.7	1542.0	1544.3	1546.6	1549.0	1549.2	1547.3	1545.5
170°	1555.0	1552.7	1550.4	1548.0	1550.4	1552.7	1555.0	1557.3	1557.5	1555.4	1553.3
172.5°	1560.6	1558.3	1555.9	1553.6	1555.9	1558.3	1560.6	1562.9	1563.1	1561.3	1559.4
175°	1567.8	1565.5	1563.1	1560.8	1563.1	1565.5	1567.8	1570.1	1570.2	1568.2	1566.1
177.5°	1570.0	1568.3	1566.6	1565.0	1566.6	1568.3	1570.0	1571.6	1571.7	1570.3	1568.8
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1576.1	1582.1	1585.3	1592.9	1603.7	1609.1	1616.6	1622.0	1629.6	1638.8	1646.3
5°	1474.1	1490.3	1501.1	1517.9	1533.5	1549.0	1568.6	1582.7	1601.6	1623.2	1640.1
7.5°	1379.3	1399.6	1417.5	1439.8	1465.4	1485.4	1510.9	1537.0	1566.5	1597.2	1626.1
10°	1318.8	1339.1	1361.4	1389.0	1414.7	1441.7	1472.0	1502.4	1539.5	1574.0	1613.1
12.5°	1258.9	1281.3	1306.3	1337.2	1368.2	1402.8	1433.7	1467.9	1507.7	1552.4	1594.2
15°	1184.5	1206.1	1233.1	1259.4	1295.2	1333.0	1374.2	1419.4	1463.9	1513.9	1565.9
17.5°	1104.7	1128.5	1158.2	1188.7	1226.4	1270.6	1311.0	1360.5	1410.6	1468.8	1530.0
20°	1052.9	1077.2	1112.3	1146.1	1180.5	1223.7	1271.6	1322.2	1375.5	1437.0	1505.1
22.5°	1011.9	1029.2	1063.7	1098.0	1138.4	1182.6	1229.5	1282.3	1340.4	1404.0	1475.4
25°	951.0	971.2	996.2	1032.0	1073.8	1120.4	1167.6	1223.7	1287.1	1351.9	1428.2
27.5°	896.9	913.5	938.2	966.2	1008.0	1056.3	1106.5	1164.9	1230.0	1296.0	1376.2
30°	858.5	876.7	900.4	930.1	963.1	1015.8	1067.1	1124.5	1190.6	1258.8	1341.1
32.5°	825.0	843.8	864.2	892.3	928.0	974.8	1027.7	1084.0	1151.2	1221.5	1301.7
35°	778.2	791.0	809.9	837.6	872.7	910.5	964.5	1023.9	1089.4	1162.3	1242.6
37.5°	724.5	741.1	759.8	783.9	814.7	855.6	905.8	965.8	1026.6	1096.4	1169.7
40°	693.2	708.7	729.6	747.2	779.6	816.7	862.6	925.3	986.1	1051.6	1118.4
42.5°	661.3	676.3	694.0	715.8	745.0	781.0	823.7	882.1	947.2	1008.9	1064.9
45°	611.5	627.0	643.9	664.1	691.1	726.2	768.8	822.1	878.8	935.5	978.0
47.5°	563.8	578.4	594.4	615.1	640.0	673.9	711.9	759.0	814.1	862.3	892.7
50°	529.8	543.3	560.9	581.1	605.4	637.1	673.6	720.2	766.1	809.9	837.6
52.5°	496.4	511.5	529.0	546.6	569.8	601.5	635.3	675.3	719.1	754.9	777.7
55°	446.1	460.3	476.5	494.7	517.7	544.7	580.5	612.2	646.6	677.0	690.5
57.5°	397.7	410.1	425.3	444.2	464.9	490.0	518.4	548.9	573.2	594.6	609.9
60°	365.8	376.6	390.8	407.0	429.3	452.2	477.9	506.2	525.1	543.3	557.5
62.5°	333.4	343.7	357.3	371.9	391.5	412.8	437.4	460.3	478.7	491.0	507.3
65°	284.8	294.9	306.4	321.9	337.5	355.0	377.3	394.2	407.0	420.5	430.6
67.5°	239.6	248.0	258.9	271.1	284.2	301.0	318.3	332.3	341.1	349.2	361.4
70°	209.9	216.7	225.4	234.9	249.1	265.9	279.4	290.2	296.3	304.4	319.2
72.5°	179.7	187.5	195.7	205.2	216.7	230.8	242.7	253.5	257.4	263.9	273.4
75°	141.7	145.8	152.5	159.3	167.4	179.5	191.0	193.7	197.1	202.5	209.2
77.5°	107.2	110.8	113.5	118.0	124.5	134.2	140.3	144.3	145.1	147.1	153.8
80°	85.0	87.1	89.8	93.1	95.8	103.9	107.3	111.4	112.7	114.7	118.1
82.5°	62.4	64.4	66.0	68.8	73.2	76.4	79.8	83.8	84.1	85.6	86.3
85°	36.4	37.1	35.8	37.1	37.8	39.1	42.5	45.9	45.2	44.5	46.6
87.5°	16.9	16.7	15.8	17.0	15.6	15.8	15.4	15.5	16.2	16.8	17.5
90°	19.9	18.6	16.8	15.0	13.2	11.4	9.4	7.4	5.3	3.2	1.2
92.5°	19.9	18.6	17.0	15.4	13.8	12.2	12.1	13.6	15.0	16.5	17.9
95°	19.9	18.6	28.4	38.2	48.0	57.9	63.1	63.9	64.7	65.5	66.2
97.5°	49.9	57.2	76.6	96.0	115.4	134.9	143.9	142.5	141.1	139.7	138.3
100°	163.7	202.2	201.2	200.2	199.1	198.1	197.2	196.4	195.6	194.9	194.1
102.5°	250.7	258.0	257.4	256.8	256.1	255.5	254.7	253.7	252.8	251.8	250.8
105°	346.3	346.3	346.3	346.3	346.3	346.3	345.8	344.8	343.7	342.7	341.7
107.5°	438.4	438.4	437.9	437.3	436.8	436.3	436.1	436.1	436.1	436.1	436.1
110°	499.0	499.7	499.2	498.7	498.2	497.7	497.4	497.4	497.4	497.4	497.4



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	558.3	559.2	558.9	558.6	558.3	558.0	557.5	556.9	556.3	555.7	555.1
115°	647.5	648.5	648.2	648.0	647.7	647.5	646.7	645.4	644.1	642.8	641.5
117.5°	733.9	735.2	734.2	733.2	732.3	731.3	730.8	730.9	730.9	731.0	731.0
120°	788.6	789.1	788.3	787.6	786.8	786.0	785.8	786.0	786.3	786.5	786.8
122.5°	841.6	842.1	841.8	841.4	841.0	840.7	840.0	839.0	838.0	837.1	836.1
125°	919.4	920.4	920.4	920.4	920.4	920.4	919.5	917.7	915.9	914.1	912.3
127.5°	989.6	990.2	990.3	990.5	990.6	990.8	990.2	988.9	987.6	986.4	985.1
130°	1035.9	1036.7	1036.4	1036.2	1035.9	1035.6	1034.9	1033.6	1032.3	1031.0	1029.7
132.5°	1078.4	1078.5	1079.1	1079.6	1080.2	1080.8	1080.3	1078.8	1077.3	1075.8	1074.3
135°	1141.9	1142.4	1142.9	1143.5	1144.0	1144.5	1144.0	1142.4	1140.9	1139.3	1137.8
137.5°	1200.2	1200.1	1200.5	1201.0	1201.5	1201.9	1201.5	1200.1	1198.8	1197.5	1196.1
140°	1235.9	1235.4	1235.7	1235.9	1236.2	1236.4	1236.3	1235.8	1235.3	1234.8	1234.2
142.5°	1271.8	1271.7	1271.3	1270.9	1270.6	1270.2	1269.9	1269.6	1269.3	1268.9	1268.6
145°	1321.7	1321.4	1321.4	1321.4	1321.4	1321.4	1321.1	1320.6	1320.1	1319.6	1319.1
147.5°	1364.5	1364.2	1363.9	1363.5	1363.2	1362.9	1362.8	1362.9	1363.0	1363.1	1363.2
150°	1391.6	1391.1	1390.6	1390.1	1389.6	1389.1	1389.1	1389.6	1390.1	1390.6	1391.1
152.5°	1415.8	1415.3	1414.8	1414.3	1413.8	1413.2	1413.5	1414.7	1415.8	1417.0	1418.1
155°	1448.9	1448.1	1447.6	1447.0	1446.5	1446.0	1446.5	1448.1	1449.6	1451.2	1452.7
157.5°	1476.3	1475.5	1475.5	1475.4	1475.4	1475.3	1475.7	1476.7	1477.6	1478.5	1479.5
160°	1493.3	1492.2	1492.0	1491.7	1491.5	1491.2	1491.9	1493.4	1495.0	1496.5	1498.1
162.5°	1508.6	1507.1	1506.9	1506.6	1506.3	1506.1	1506.7	1508.3	1509.8	1511.4	1512.9
165°	1528.7	1527.1	1526.8	1526.6	1526.3	1526.1	1526.7	1528.3	1529.8	1531.4	1532.9
167.5°	1543.6	1541.8	1541.5	1541.2	1541.0	1540.7	1541.4	1543.0	1544.6	1546.2	1547.8
170°	1551.3	1549.2	1548.9	1548.7	1548.4	1548.2	1548.9	1550.7	1552.5	1554.4	1556.2
172.5°	1557.6	1555.7	1555.2	1554.8	1554.3	1553.8	1554.5	1556.3	1558.1	1559.9	1561.7
175°	1564.0	1562.0	1561.7	1561.5	1561.2	1560.9	1561.6	1563.1	1564.7	1566.2	1567.8
177.5°	1567.4	1565.9	1565.7	1565.5	1565.3	1565.1	1565.6	1566.9	1568.1	1569.3	1570.6
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1652.3	1657.1	1664.1	1672.2	1678.7	1685.7	1689.5	1689.5	1692.8	1699.8	1709.0
5°	1657.0	1674.5	1691.4	1713.0	1729.9	1749.4	1764.3	1778.5	1791.3	1807.5	1824.4
7.5°	1655.6	1684.8	1715.2	1749.2	1786.7	1816.5	1847.2	1871.2	1895.0	1926.0	1950.4
10°	1650.2	1688.0	1729.2	1772.4	1819.6	1860.8	1897.9	1931.7	1964.1	1997.8	2028.2
12.5°	1640.5	1688.6	1738.9	1790.8	1850.4	1897.5	1945.5	1981.4	2019.2	2056.1	2093.5
15°	1625.9	1682.6	1743.4	1815.6	1888.5	1941.1	1988.4	2035.0	2070.0	2111.9	2147.7
17.5°	1595.8	1668.9	1745.3	1824.2	1894.3	1955.4	2005.0	2049.3	2086.7	2132.7	2181.3
20°	1578.0	1657.0	1736.6	1821.0	1887.8	1950.6	1998.5	2044.4	2091.0	2151.0	2210.4
22.5°	1553.2	1637.5	1722.0	1802.1	1872.7	1933.3	1982.8	2039.0	2100.1	2168.3	2240.1
25°	1513.9	1601.0	1684.7	1760.9	1829.8	1891.9	1959.4	2035.0	2109.2	2199.0	2302.2
27.5°	1464.1	1548.0	1622.7	1703.3	1771.7	1850.7	1934.9	2016.9	2123.9	2247.4	2376.3
30°	1426.8	1506.5	1577.3	1653.6	1731.2	1818.3	1912.8	2009.3	2136.9	2282.0	2435.2
32.5°	1383.6	1455.7	1526.0	1599.6	1689.1	1784.8	1885.2	2003.4	2155.8	2320.9	2479.5
35°	1308.7	1373.5	1441.7	1523.3	1618.5	1722.5	1850.7	1994.5	2178.7	2356.2	2498.6
37.5°	1230.1	1281.3	1349.7	1435.9	1539.5	1659.8	1805.3	1980.0	2169.3	2328.5	2389.2
40°	1169.7	1217.6	1289.8	1380.3	1482.8	1614.5	1777.8	1957.3	2147.7	2258.4	2253.6
42.5°	1109.7	1158.2	1227.7	1318.7	1425.6	1572.9	1741.1	1927.6	2088.3	2130.4	2042.5
45°	1017.8	1063.0	1131.2	1223.0	1337.7	1492.3	1669.1	1848.0	1950.6	1882.4	1708.3
47.5°	924.1	968.0	1031.3	1121.2	1246.5	1408.2	1575.4	1722.2	1736.6	1590.2	1381.3
50°	862.6	903.7	963.8	1059.7	1181.1	1339.1	1500.4	1615.8	1580.0	1401.2	1185.9
52.5°	802.6	842.2	898.5	988.9	1113.1	1267.8	1411.8	1502.4	1419.7	1229.5	1035.8
55°	714.1	751.9	808.6	891.6	1004.3	1146.1	1272.3	1305.3	1183.8	992.2	835.6
57.5°	630.0	657.7	713.7	787.1	895.8	1020.8	1111.2	1105.3	971.2	798.6	686.3
60°	574.4	599.3	652.7	720.2	823.4	935.5	998.9	971.9	836.3	693.8	585.8
62.5°	522.5	545.9	590.6	652.7	741.4	838.8	885.0	847.7	719.6	594.5	508.6
65°	444.1	461.0	496.8	554.1	623.6	691.1	732.3	677.6	564.3	469.8	405.0
67.5°	370.8	385.4	417.2	458.4	506.3	552.9	569.7	518.4	430.2	366.5	320.9
70°	323.3	336.8	358.4	396.9	428.6	461.7	469.8	423.9	350.3	301.7	273.4
72.5°	277.9	290.4	309.3	336.4	358.4	377.4	381.2	338.6	282.3	248.8	226.9
75°	211.9	222.7	234.9	245.0	259.2	262.6	261.2	228.1	197.8	175.5	163.3
77.5°	155.8	160.2	167.7	171.7	172.4	172.1	165.2	144.3	128.6	119.5	114.5
80°	120.1	123.5	125.5	126.9	127.6	120.8	113.4	100.6	95.2	89.8	83.7
82.5°	87.2	89.5	91.5	91.8	88.1	82.5	75.6	69.2	65.5	62.8	60.5
85°	47.2	47.9	47.2	43.9	39.1	37.1	35.8	34.4	33.7	33.1	33.1
87.5°	17.4	16.2	13.9	14.8	15.2	15.1	15.4	15.2	15.1	15.3	15.6
90°	3.2	5.3	7.4	9.4	11.4	13.2	15.0	16.8	18.6	19.9	21.2
92.5°	16.5	15.0	13.6	12.1	12.2	13.8	15.4	17.0	18.6	19.9	21.2
95°	65.5	64.7	63.9	63.1	57.9	48.0	38.2	28.4	18.6	19.9	21.2
97.5°	139.7	141.1	142.5	143.9	134.9	115.4	96.0	76.6	57.2	49.9	42.6
100°	194.9	195.6	196.4	197.2	198.1	199.1	200.2	201.2	202.2	163.7	125.3
102.5°	251.8	252.8	253.7	254.7	255.5	256.1	256.8	257.4	258.0	250.7	243.4
105°	342.7	343.7	344.8	345.8	346.3	346.3	346.3	346.3	346.3	346.3	346.3
107.5°	436.1	436.1	436.1	436.1	436.3	436.8	437.3	437.9	438.4	438.4	438.5
110°	497.4	497.4	497.4	497.4	497.7	498.2	498.7	499.2	499.7	499.0	498.2





TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	555.7	556.3	556.9	557.5	558.0	558.3	558.6	558.9	559.2	558.3	557.3
115°	642.8	644.1	645.4	646.7	647.5	647.7	648.0	648.2	648.5	647.5	646.4
117.5°	731.0	730.9	730.9	730.8	731.3	732.3	733.2	734.2	735.2	733.9	732.5
120°	786.5	786.3	786.0	785.8	786.0	786.8	787.6	788.3	789.1	788.6	788.1
122.5°	837.1	838.0	839.0	840.0	840.7	841.0	841.4	841.8	842.1	841.6	841.1
125°	914.1	915.9	917.7	919.5	920.4	920.4	920.4	920.4	920.4	919.4	918.4
127.5°	986.4	987.6	988.9	990.2	990.8	990.6	990.5	990.3	990.2	989.6	989.0
130°	1031.0	1032.3	1033.6	1034.9	1035.6	1035.9	1036.2	1036.4	1036.7	1035.9	1035.1
132.5°	1075.8	1077.3	1078.8	1080.3	1080.8	1080.2	1079.6	1079.1	1078.5	1078.4	1078.2
135°	1139.3	1140.9	1142.4	1144.0	1144.5	1144.0	1143.5	1142.9	1142.4	1141.9	1141.4
137.5°	1197.5	1198.8	1200.1	1201.5	1201.9	1201.5	1201.0	1200.5	1200.1	1200.2	1200.3
140°	1234.8	1235.3	1235.8	1236.3	1236.4	1236.2	1235.9	1235.7	1235.4	1235.9	1236.4
142.5°	1268.9	1269.3	1269.6	1269.9	1270.2	1270.6	1270.9	1271.3	1271.7	1271.8	1271.9
145°	1319.6	1320.1	1320.6	1321.1	1321.4	1321.4	1321.4	1321.4	1321.4	1321.7	1321.9
147.5°	1363.1	1363.0	1362.9	1362.8	1362.9	1363.2	1363.5	1363.9	1364.2	1364.5	1364.8
150°	1390.6	1390.1	1389.6	1389.1	1389.1	1389.6	1390.1	1390.6	1391.1	1391.6	1392.2
152.5°	1417.0	1415.8	1414.7	1413.5	1413.2	1413.8	1414.3	1414.8	1415.3	1415.8	1416.3
155°	1451.2	1449.6	1448.1	1446.5	1446.0	1446.5	1447.0	1447.6	1448.1	1448.9	1449.6
157.5°	1478.5	1477.6	1476.7	1475.7	1475.3	1475.4	1475.4	1475.5	1475.5	1476.3	1477.2
160°	1496.5	1495.0	1493.4	1491.9	1491.2	1491.5	1491.7	1492.0	1492.2	1493.3	1494.3
162.5°	1511.4	1509.8	1508.3	1506.7	1506.1	1506.3	1506.6	1506.9	1507.1	1508.6	1510.0
165°	1531.4	1529.8	1528.3	1526.7	1526.1	1526.3	1526.6	1526.8	1527.1	1528.7	1530.2
167.5°	1546.2	1544.6	1543.0	1541.4	1540.7	1541.0	1541.2	1541.5	1541.8	1543.6	1545.5
170°	1554.4	1552.5	1550.7	1548.9	1548.2	1548.4	1548.7	1548.9	1549.2	1551.3	1553.3
172.5°	1559.9	1558.1	1556.3	1554.5	1553.8	1554.3	1554.8	1555.2	1555.7	1557.6	1559.4
175°	1566.2	1564.7	1563.1	1561.6	1560.9	1561.2	1561.5	1561.7	1562.0	1564.0	1566.1
177.5°	1569.3	1568.1	1566.9	1565.6	1565.1	1565.3	1565.5	1565.7	1565.9	1567.4	1568.8
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1716.0	1716.0	1725.2	1724.6	1730.6	1728.4	1729.5
5°	1844.6	1856.1	1866.2	1873.0	1883.1	1885.8	1884.4
7.5°	1978.0	2003.5	2015.9	2032.9	2036.0	2044.9	2044.0
10°	2060.6	2085.6	2104.5	2119.3	2126.7	2136.2	2136.9
12.5°	2125.4	2146.6	2163.3	2177.1	2186.1	2189.1	2190.9
15°	2176.0	2199.6	2219.2	2238.8	2250.3	2259.0	2263.8
17.5°	2227.0	2263.5	2298.0	2324.6	2340.6	2354.1	2353.9
20°	2266.5	2308.3	2351.5	2381.9	2412.9	2426.4	2428.4
22.5°	2308.6	2372.6	2428.2	2475.3	2516.0	2530.1	2535.4
25°	2396.0	2479.7	2565.5	2631.6	2678.8	2706.5	2710.6
27.5°	2501.7	2615.0	2705.2	2766.2	2805.5	2826.0	2830.4
30°	2576.3	2680.9	2761.9	2807.8	2826.0	2828.7	2818.6
32.5°	2609.7	2687.9	2720.3	2717.6	2681.8	2658.1	2649.0
35°	2568.8	2552.6	2473.7	2379.2	2307.0	2261.1	2248.9
37.5°	2337.7	2198.0	2052.8	1910.0	1834.0	1795.3	1728.9
40°	2109.9	1910.8	1759.6	1639.4	1553.7	1484.9	1468.7
42.5°	1852.9	1647.3	1496.1	1393.2	1324.8	1277.5	1257.0
45°	1488.9	1312.1	1187.2	1108.3	1055.6	1021.2	1005.7
47.5°	1190.9	1054.0	963.0	904.6	864.5	834.5	826.1
50°	1027.3	917.9	841.0	791.7	761.3	738.4	728.9
52.5°	892.3	804.0	744.9	704.2	675.5	661.2	653.3
55°	736.4	660.1	617.6	585.2	569.0	557.5	552.1
57.5°	602.2	547.1	516.1	493.7	478.7	471.4	468.7
60°	527.1	483.9	455.6	438.0	427.9	418.5	415.8
62.5°	460.7	426.7	404.8	389.4	379.3	375.3	373.6
65°	371.2	348.9	332.7	323.3	315.2	313.8	313.2
67.5°	295.1	282.0	273.5	263.6	260.8	256.1	255.1
70°	252.4	243.7	233.5	230.2	226.8	222.1	222.7
72.5°	214.1	205.3	198.4	194.0	192.8	190.7	192.5
75°	156.6	153.9	151.2	147.8	146.5	146.5	145.8
77.5°	111.8	109.5	106.5	104.5	104.1	101.2	102.3
80°	81.0	77.6	76.3	76.9	74.9	74.2	74.2
82.5°	59.9	58.7	57.4	57.5	57.1	56.4	57.0
85°	33.1	32.4	32.4	31.7	31.7	31.0	31.0
87.5°	16.4	17.2	16.3	15.9	16.1	16.8	17.5
90°	22.5	23.8	24.8	25.6	26.3	27.1	27.9
92.5°	22.5	23.8	24.6	24.9	25.3	25.7	26.0
95°	22.5	23.8	24.4	24.4	24.4	24.4	24.4
97.5°	35.3	28.0	24.4	24.4	24.4	24.4	24.4
100°	86.8	48.3	28.5	27.5	26.5	25.4	24.4
102.5°	236.2	228.9	216.5	198.9	181.3	163.8	146.2
105°	346.3	346.3	346.2	345.9	345.7	345.4	345.2
107.5°	438.5	438.6	438.2	437.4	436.7	435.9	435.1
110°	497.4	496.6	496.4	496.6	496.9	497.2	497.4



TEST NUMBER: P333604

CATALOG NUMBER: S125RDIP-S1090D1205U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	556.3	555.3	554.6	554.3	553.9	553.6	553.2
115°	645.4	644.4	643.1	641.5	640.0	638.4	636.9
117.5°	731.2	729.8	728.8	728.1	727.5	726.8	726.1
120°	787.6	787.1	786.2	784.9	783.6	782.3	781.0
122.5°	840.6	840.1	839.0	837.5	836.0	834.6	833.1
125°	917.3	916.3	915.4	914.6	913.9	913.1	912.3
127.5°	988.5	987.9	986.7	984.8	982.8	980.9	979.0
130°	1034.3	1033.6	1032.5	1031.2	1030.0	1028.7	1027.4
132.5°	1078.0	1077.9	1077.2	1075.9	1074.6	1073.3	1072.0
135°	1140.9	1140.4	1139.3	1137.8	1136.2	1134.7	1133.1
137.5°	1200.4	1200.5	1199.9	1198.5	1197.2	1195.8	1194.5
140°	1236.9	1237.5	1236.9	1235.4	1233.9	1232.3	1230.8
142.5°	1272.0	1272.1	1271.4	1269.8	1268.3	1266.7	1265.2
145°	1322.2	1322.4	1321.8	1320.2	1318.7	1317.1	1315.6
147.5°	1365.1	1365.4	1364.6	1362.8	1360.9	1359.1	1357.2
150°	1392.7	1393.2	1392.4	1390.4	1388.3	1386.2	1384.2
152.5°	1416.9	1417.4	1416.7	1414.8	1413.0	1411.1	1409.3
155°	1450.4	1451.2	1450.5	1448.5	1446.4	1444.3	1442.3
157.5°	1478.0	1478.8	1478.2	1476.1	1474.1	1472.0	1469.9
160°	1495.3	1496.4	1495.9	1493.8	1491.7	1489.7	1487.6
162.5°	1511.5	1512.9	1512.5	1510.2	1507.9	1505.7	1503.4
165°	1531.8	1533.3	1533.0	1531.0	1528.9	1526.8	1524.8
167.5°	1547.3	1549.2	1549.0	1546.6	1544.3	1542.0	1539.7
170°	1555.4	1557.5	1557.3	1555.0	1552.7	1550.4	1548.0
172.5°	1561.3	1563.1	1562.9	1560.6	1558.3	1555.9	1553.6
175°	1568.2	1570.2	1570.1	1567.8	1565.5	1563.1	1560.8
177.5°	1570.3	1571.7	1571.6	1570.0	1568.3	1566.6	1565.0
180°	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8	1567.8

(END OF REPORT)