

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333197-927

Luminaire Tested: **S125DIP-S610D1205U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333197-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D1205U927-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5304.1 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	67	63	59	56	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	72	62	54	49	66	57	50	45	46	42	38	37	33	31	28	26	24	20
5	66	55	47	42	60	50	44	38	41	36	32	33	29	27	25	23	21	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	57	45	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	17	15	12
9	49	37	29	25	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4579	4579	4579	4579
5°	5302	4595	4023	4595
10°	6169	4571	3525	4571
15°	6829	4537	3251	4537
20°	7644	4484	3032	4484
25°	8955	4424	2925	4424
30°	9672	4365	2832	4365
35°	7953	4254	2771	4254
40°	5653	4100	2705	4100
45°	4343	3892	2666	3892
50°	3706	3634	2661	3634
55°	3300	3381	2684	3381
60°	2977	3105	2753	3105
65°	2751	2829	2823	2829
70°	2500	2540	2865	2540
75°	2208	2238	2840	2238
80°	1860	1822	2596	1822
85°	1475	1312	2097	1312



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.3	1.3
10°-20°	203.2	3.8
20°-30°	330.0	6.2
30°-40°	402.5	7.6
40°-50°	366.2	6.9
50°-60°	291.7	5.5
60°-70°	203.2	3.8
70°-80°	108.3	2.0
80°-90°	29.9	0.6
90°-100°	79.2	1.5
100°-110°	234.0	4.4
110°-120°	396.3	7.5
120°-130°	521.5	9.8
130°-140°	584.4	11.0
140°-150°	572.7	10.8
150°-160°	481.1	9.1
160°-170°	319.8	6.0
170°-180°	111.9	2.1
0°-30°	601.5	11.3
0°-40°	1004.0	18.9
0°-60°	1661.8	31.3
0°-90°	2003.2	37.8
90°-120°	709.5	13.4
90°-150°	2388.1	45.0
90°-180°	3301.0	62.2
0°-180°	5304.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	709	709	709	709	709	
5°	818	709	620	709	818	82
15°	1021	679	486	679	1021	292
25°	1257	621	410	621	1257	574
35°	1009	540	352	540	1009	617
45°	476	426	292	426	476	381
55°	293	300	238	300	293	264
65°	180	185	185	185	180	179
75°	88	90	114	90	88	95
85°	20	18	28	18	20	23
90°	22	1	22	1	22	13
95°	79	60	79	60	79	81
105°	228	210	228	210	228	242
115°	400	397	400	397	400	396
125°	583	579	583	579	583	520
135°	756	753	756	753	756	583
145°	916	912	916	912	916	572
155°	1044	1044	1044	1044	1044	480
165°	1132	1135	1132	1135	1132	319
175°	1176	1180	1176	1180	1176	112
180°	1183	1183	1183	1183	1183	



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	750.0	748.9	748.0	746.1	747.5	743.4	741.5	738.2	734.0	732.6	730.9
5°	817.9	819.4	820.9	814.6	815.2	811.0	801.4	793.5	787.3	779.1	773.4
7.5°	899.8	896.2	896.0	891.8	884.8	879.2	869.0	856.1	843.7	829.5	817.8
10°	940.7	941.0	938.3	933.5	926.0	920.5	907.3	894.7	879.3	861.3	848.3
12.5°	971.5	972.8	969.4	962.9	959.2	947.1	936.7	921.6	903.4	889.0	869.3
15°	1021.4	1018.0	1015.7	1007.5	1001.2	988.6	972.0	956.3	936.5	918.1	899.8
17.5°	1069.4	1072.1	1067.5	1060.1	1040.5	1025.7	1003.5	982.1	957.4	932.8	910.9
20°	1112.2	1114.7	1107.7	1094.8	1071.3	1056.5	1027.4	999.7	971.1	939.5	915.4
22.5°	1165.7	1163.8	1154.4	1134.7	1114.4	1087.1	1055.6	1021.8	986.0	950.3	918.3
25°	1256.7	1244.0	1238.3	1213.9	1187.2	1147.2	1103.8	1054.5	1010.0	962.7	921.8
27.5°	1307.1	1303.1	1296.8	1279.8	1251.6	1208.9	1157.8	1097.6	1034.7	975.2	921.5
30°	1297.0	1297.6	1298.2	1292.8	1274.8	1242.5	1191.7	1127.0	1052.3	985.2	923.3
32.5°	1207.4	1218.4	1228.9	1241.3	1246.3	1240.2	1208.3	1149.9	1073.1	996.8	922.3
35°	1008.7	1012.0	1046.1	1079.7	1125.5	1161.0	1184.8	1158.9	1094.2	1006.6	921.1
37.5°	786.5	802.8	826.3	864.4	930.4	989.5	1065.6	1100.5	1079.6	1009.8	919.0
40°	670.5	685.6	700.8	739.7	795.4	867.0	953.3	1027.1	1044.3	999.7	911.8
42.5°	580.9	592.9	609.9	639.1	685.6	749.0	831.6	927.9	987.1	970.3	896.7
45°	475.5	483.0	496.2	519.4	553.1	602.8	675.6	780.9	872.7	903.1	860.6
47.5°	406.9	406.9	417.2	433.2	457.6	499.7	553.6	636.1	734.1	806.7	803.3
50°	368.9	367.4	375.6	389.4	408.7	436.7	488.1	554.1	648.2	730.4	753.2
52.5°	336.2	336.4	341.4	351.6	367.7	391.7	430.1	489.5	570.0	654.3	697.4
55°	293.1	291.9	297.6	304.5	316.3	331.9	359.7	405.0	470.3	553.4	609.3
57.5°	253.7	256.9	259.2	264.0	273.8	284.2	307.6	341.0	392.8	464.1	523.2
60°	230.5	233.9	235.6	240.4	248.3	257.3	275.4	302.5	346.1	407.5	466.1
62.5°	209.8	212.4	213.0	217.3	223.7	232.5	246.7	269.4	304.0	357.6	415.1
65°	180.0	180.0	181.2	185.7	188.7	196.5	207.3	223.9	251.6	293.4	342.5
67.5°	151.1	152.7	152.3	154.3	157.1	163.2	171.0	184.6	205.1	235.6	274.9
70°	132.4	133.6	133.3	134.8	137.8	141.7	148.1	161.0	175.7	201.9	235.6
72.5°	115.6	116.1	115.3	117.2	119.1	122.5	129.5	136.4	150.2	172.3	200.0
75°	88.5	89.0	89.7	90.9	92.7	94.5	98.1	105.0	114.1	130.6	148.4
77.5°	66.3	65.2	66.6	66.5	67.5	68.8	72.0	75.7	83.1	93.6	107.3
80°	50.0	50.2	50.2	50.5	52.0	53.0	55.7	58.4	64.1	71.9	81.5
82.5°	36.4	37.2	36.8	37.3	38.6	39.2	40.7	42.9	46.3	52.4	59.4
85°	19.9	18.4	18.9	19.6	19.6	19.9	21.1	21.9	23.8	26.1	28.9
87.5°	10.2	10.5	10.7	10.5	10.7	10.5	11.2	11.1	11.6	12.1	12.8
90°	22.1	21.5	20.8	20.3	19.6	18.9	17.8	16.8	15.8	14.7	13.3
92.5°	43.4	43.0	42.5	42.1	41.7	40.7	39.4	38.0	36.7	35.3	33.6
95°	79.1	78.7	78.3	78.0	77.6	76.6	75.2	73.8	72.3	70.9	68.8
97.5°	120.0	119.8	119.5	119.3	119.1	118.3	116.9	115.6	114.2	112.9	110.0
100°	151.0	150.6	150.1	149.7	149.3	148.2	146.4	144.5	142.7	140.9	138.2
102.5°	181.9	181.3	180.8	180.2	179.6	178.3	176.3	174.3	172.3	170.3	169.0
105°	228.3	227.7	227.0	226.5	225.9	224.9	223.7	222.4	221.3	220.0	218.8
107.5°	275.8	275.8	275.9	275.9	276.0	275.7	275.0	274.4	273.9	273.2	272.3
110°	311.2	311.3	311.6	311.7	312.0	311.7	311.2	310.5	309.9	309.3	308.7



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	345.8	346.1	346.5	346.9	347.2	347.3	347.0	346.7	346.4	346.1	345.3
115°	400.4	400.6	400.8	401.1	401.2	401.5	401.6	401.9	402.1	402.3	401.9
117.5°	453.8	454.6	455.5	456.3	457.1	457.4	457.2	457.1	456.9	456.8	456.4
120°	490.7	491.5	492.3	493.1	493.9	494.3	494.3	494.3	494.3	494.3	494.2
122.5°	527.5	528.1	528.8	529.4	530.1	530.5	530.7	530.8	531.0	531.2	530.6
125°	582.7	582.9	583.1	583.4	583.5	583.8	584.2	584.6	585.0	585.5	585.3
127.5°	635.7	636.1	636.5	637.0	637.4	637.7	637.9	638.1	638.3	638.5	638.3
130°	671.1	671.5	671.9	672.3	672.7	673.0	673.2	673.4	673.7	673.8	673.4
132.5°	704.3	704.8	705.4	705.9	706.5	706.9	707.1	707.3	707.5	707.7	707.8
135°	755.7	756.6	757.4	758.2	759.1	759.5	759.5	759.5	759.5	759.5	759.2
137.5°	806.2	807.2	808.3	809.3	810.3	810.7	810.5	810.2	809.9	809.7	809.3
140°	838.6	839.6	840.7	841.7	842.7	843.0	842.6	842.2	841.8	841.4	840.7
142.5°	869.6	870.6	871.6	872.6	873.6	874.0	873.8	873.5	873.3	873.1	872.3
145°	915.9	916.6	917.2	917.8	918.4	918.7	918.7	918.7	918.7	918.7	918.1
147.5°	955.5	957.0	958.3	959.7	961.1	961.6	961.1	960.6	960.0	959.6	959.1
150°	985.0	985.4	985.8	986.2	986.7	986.8	986.8	986.8	986.8	986.8	986.0
152.5°	1009.3	1010.0	1010.7	1011.5	1012.3	1012.3	1011.9	1011.4	1010.9	1010.4	1010.1
155°	1043.9	1045.0	1045.9	1046.9	1048.0	1048.1	1047.3	1046.5	1045.7	1044.8	1044.7
157.5°	1072.9	1074.2	1075.5	1076.9	1078.2	1078.5	1077.7	1076.8	1076.0	1075.2	1075.0
160°	1092.7	1093.7	1094.7	1095.7	1096.8	1096.9	1096.1	1095.3	1094.4	1093.6	1093.4
162.5°	1109.6	1110.8	1112.0	1113.2	1114.4	1114.5	1113.5	1112.5	1111.5	1110.6	1110.5
165°	1132.3	1133.5	1134.7	1136.0	1137.2	1137.4	1136.5	1135.8	1135.0	1134.1	1133.9
167.5°	1150.3	1151.6	1152.9	1154.1	1155.4	1155.4	1154.2	1152.9	1151.8	1150.5	1150.5
170°	1159.9	1161.3	1162.8	1164.2	1165.6	1165.7	1164.5	1163.2	1162.1	1160.8	1160.8
172.5°	1168.0	1169.3	1170.5	1171.8	1173.1	1173.1	1171.9	1170.6	1169.4	1168.2	1168.2
175°	1175.5	1176.9	1178.5	1179.9	1181.3	1181.4	1180.1	1178.9	1177.7	1176.5	1176.5
177.5°	1180.0	1181.1	1182.3	1183.4	1184.6	1184.6	1183.7	1182.6	1181.7	1180.7	1180.8
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	729.4	727.8	725.9	722.5	718.4	716.2	712.9	710.7	706.3	702.7	698.9
5°	766.4	758.7	751.5	742.1	731.9	725.2	717.4	708.7	699.7	690.3	680.1
7.5°	804.8	791.0	775.9	759.7	743.9	729.4	715.4	701.8	689.0	673.6	660.5
10°	830.6	813.1	794.5	772.5	751.1	732.5	713.5	697.0	680.1	662.0	646.1
12.5°	856.3	833.1	806.8	782.6	756.9	734.4	712.1	690.9	669.8	649.7	631.2
15°	874.5	854.1	829.7	795.4	766.4	735.5	706.0	678.6	653.0	630.7	607.3
17.5°	886.5	860.2	833.9	801.1	763.2	728.5	695.1	663.8	634.9	606.7	584.1
20°	888.7	861.6	834.2	802.0	763.2	723.4	690.1	652.4	621.4	592.2	564.5
22.5°	888.0	857.2	827.4	794.2	756.5	719.9	679.5	641.1	607.4	578.8	549.9
25°	881.1	848.3	811.0	777.6	740.3	701.5	660.5	620.8	586.5	553.7	525.1
27.5°	875.4	832.9	790.7	751.7	715.7	680.1	641.0	600.2	562.2	528.9	502.0
30°	868.5	821.8	774.3	733.6	696.6	662.0	625.0	585.3	545.6	513.1	484.2
32.5°	862.2	807.9	757.7	713.4	674.3	640.6	606.5	568.7	529.7	496.7	467.9
35°	850.2	787.3	729.8	679.8	637.9	603.4	574.8	539.6	503.7	471.8	444.2
37.5°	834.8	760.2	698.5	646.1	600.2	563.8	537.2	510.2	475.8	445.0	420.0
40°	822.8	740.9	675.6	622.0	574.5	536.5	511.9	486.3	457.7	429.1	402.7
42.5°	807.6	723.6	652.4	594.8	547.8	510.8	484.9	463.2	438.0	411.3	386.7
45°	779.7	692.1	615.1	553.1	505.6	469.1	442.4	426.1	407.2	381.9	361.2
47.5°	738.7	654.4	574.7	510.7	461.7	427.9	402.8	387.2	373.9	355.1	336.3
50°	702.3	626.2	545.6	482.1	433.0	399.0	375.9	361.7	350.3	335.8	319.9
52.5°	661.7	590.8	517.0	454.2	405.6	372.1	349.4	336.9	327.4	317.0	301.3
55°	597.1	536.9	468.3	408.7	363.8	331.1	311.2	300.3	292.5	284.7	275.0
57.5°	525.9	478.8	418.0	363.5	322.3	292.4	273.9	263.3	257.2	253.2	247.6
60°	475.8	435.5	383.1	333.4	293.1	266.6	248.6	240.4	235.4	232.0	227.8
62.5°	429.3	396.2	347.7	302.4	267.1	242.1	225.9	218.1	213.2	211.6	208.0
65°	360.8	335.3	295.2	257.6	227.5	206.1	192.6	185.1	182.0	180.2	180.5
67.5°	293.3	277.7	245.7	213.6	189.5	171.6	160.7	155.0	153.4	151.1	151.0
70°	252.2	240.4	213.3	185.4	164.0	150.2	140.5	134.5	133.0	131.8	131.5
72.5°	215.8	205.6	182.0	159.6	140.5	128.3	120.3	116.7	114.2	113.5	113.4
75°	162.2	156.5	137.8	120.1	106.9	98.4	93.0	89.7	87.9	87.5	87.9
77.5°	115.3	110.4	98.5	85.9	77.6	71.1	66.5	65.4	63.4	63.5	63.1
80°	86.7	83.3	75.8	65.9	59.0	53.6	51.2	49.0	48.5	47.5	48.5
82.5°	62.8	59.3	54.2	47.8	42.1	38.9	36.4	35.8	35.4	35.0	35.2
85°	31.0	31.3	28.3	23.4	21.1	19.3	17.7	17.7	17.4	17.2	17.4
87.5°	13.0	12.2	10.9	9.9	8.4	7.4	6.7	6.7	6.3	6.3	7.0
90°	11.9	10.5	9.0	7.4	5.9	4.2	2.5	1.0	2.5	4.2	5.9
92.5°	31.8	30.1	28.3	26.9	25.7	24.6	23.4	22.3	23.4	24.6	25.7
95°	66.8	64.7	62.7	61.5	61.1	60.7	60.2	59.8	60.2	60.7	61.1
97.5°	107.2	104.4	101.6	100.1	99.9	99.7	99.6	99.4	99.6	99.7	99.9
100°	135.5	132.8	130.2	128.9	128.9	128.9	128.9	128.9	128.9	128.9	128.9
102.5°	167.6	166.3	164.9	163.8	163.0	162.2	161.4	160.6	161.4	162.2	163.0
105°	217.5	216.3	215.1	214.0	212.9	211.9	210.9	209.8	210.9	211.9	212.9
107.5°	271.3	270.4	269.4	268.5	267.4	266.4	265.4	264.4	265.4	266.4	267.4
110°	308.1	307.4	306.8	306.0	305.0	304.0	302.9	302.0	302.9	304.0	305.0



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	344.6	343.8	343.0	342.4	341.8	341.3	340.8	340.2	340.8	341.3	341.8
115°	401.5	401.1	400.6	400.1	399.2	398.4	397.6	396.7	397.6	398.4	399.2
117.5°	456.1	455.7	455.3	455.0	454.6	454.2	453.8	453.4	453.8	454.2	454.6
120°	493.9	493.7	493.5	492.9	491.9	490.8	489.8	488.8	489.8	490.8	491.9
122.5°	530.1	529.6	529.0	528.5	528.2	527.8	527.5	527.1	527.5	527.8	528.2
125°	585.0	584.9	584.6	583.9	582.7	581.5	580.3	579.0	580.3	581.5	582.7
127.5°	638.0	637.8	637.5	637.1	636.4	635.6	634.9	634.3	634.9	635.6	636.4
130°	673.0	672.6	672.2	671.5	670.5	669.5	668.4	667.4	668.4	669.5	670.5
132.5°	707.9	708.0	708.1	707.3	705.6	703.9	702.2	700.5	702.2	703.9	705.6
135°	759.1	758.8	758.7	758.0	756.7	755.5	754.2	753.0	754.2	755.5	756.7
137.5°	808.8	808.3	807.9	807.1	805.9	804.7	803.5	802.3	803.5	804.7	805.9
140°	840.2	839.6	838.9	838.1	837.1	836.1	835.0	834.0	835.0	836.1	837.1
142.5°	871.5	870.7	870.0	869.1	868.2	867.4	866.6	865.7	866.6	867.4	868.2
145°	917.5	916.9	916.2	915.5	914.7	913.9	913.1	912.3	913.1	913.9	914.7
147.5°	958.6	958.1	957.6	957.1	956.7	956.2	955.8	955.4	955.8	956.2	956.7
150°	985.2	984.4	983.6	983.3	983.5	983.7	983.9	984.0	983.9	983.7	983.5
152.5°	1009.7	1009.4	1009.1	1008.8	1008.5	1008.2	1007.9	1007.7	1007.9	1008.2	1008.5
155°	1044.4	1044.3	1044.0	1043.9	1043.9	1043.9	1043.9	1043.9	1043.9	1043.9	1043.9
157.5°	1074.8	1074.6	1074.4	1074.5	1075.0	1075.4	1075.9	1076.3	1075.9	1075.4	1075.0
160°	1093.2	1093.0	1092.8	1093.0	1093.6	1094.2	1094.9	1095.4	1094.9	1094.2	1093.6
162.5°	1110.5	1110.4	1110.4	1110.6	1111.0	1111.5	1112.0	1112.4	1112.0	1111.5	1111.0
165°	1133.7	1133.5	1133.3	1133.4	1133.9	1134.2	1134.6	1135.0	1134.6	1134.2	1133.9
167.5°	1150.5	1150.5	1150.5	1150.9	1151.8	1152.5	1153.3	1154.2	1153.3	1152.5	1151.8
170°	1160.8	1160.8	1160.8	1161.3	1162.1	1162.8	1163.7	1164.5	1163.7	1162.8	1162.1
172.5°	1168.2	1168.2	1168.2	1168.6	1169.4	1170.2	1171.1	1171.9	1171.1	1170.2	1169.4
175°	1176.5	1176.5	1176.5	1176.9	1177.7	1178.5	1179.3	1180.1	1179.3	1178.5	1177.7
177.5°	1181.1	1181.2	1181.4	1181.8	1182.4	1183.0	1183.8	1184.4	1183.8	1183.0	1182.4
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	696.7	694.0	691.9	687.1	684.4	680.8	677.9	681.0	677.7	679.1	677.0
5°	675.0	666.5	660.5	651.8	644.3	637.4	632.2	631.4	628.9	627.7	624.2
7.5°	648.9	638.3	628.0	616.6	606.9	597.1	590.8	585.7	582.3	577.7	574.6
10°	633.4	619.3	607.3	593.4	581.4	570.8	562.4	558.3	554.3	548.6	546.5
12.5°	614.4	599.8	585.1	570.3	558.8	547.0	539.8	533.5	530.8	524.3	523.6
15°	591.6	569.7	555.2	540.2	524.2	514.6	508.6	501.7	498.7	494.2	490.8
17.5°	564.4	544.8	526.7	511.2	497.5	489.4	481.9	477.1	472.0	469.1	463.6
20°	544.7	526.0	507.9	491.4	480.9	471.6	465.6	461.1	455.6	454.1	448.7
22.5°	528.1	507.5	490.1	476.3	464.8	454.2	447.7	444.7	440.9	436.3	435.2
25°	501.1	479.7	464.9	451.1	440.8	431.3	426.7	422.8	419.2	415.9	414.7
27.5°	477.7	458.6	441.1	428.6	419.7	410.9	406.9	402.2	399.5	396.9	393.6
30°	461.4	441.8	426.4	414.4	404.7	397.0	392.7	389.4	387.0	384.6	382.8
32.5°	444.5	426.4	411.5	399.7	390.1	384.2	380.4	378.1	375.4	372.6	370.3
35°	422.2	402.3	387.9	377.6	370.1	365.6	361.4	359.3	356.3	356.3	353.9
37.5°	397.1	379.9	367.2	357.8	351.1	347.1	342.5	341.1	339.1	337.9	337.1
40°	382.1	366.2	354.2	344.8	337.6	334.3	330.7	328.3	327.1	325.6	325.0
42.5°	366.8	351.6	340.0	331.4	325.1	322.3	318.9	317.3	314.8	312.8	312.5
45°	343.3	328.6	318.1	311.2	305.8	302.5	300.3	296.8	295.5	293.1	292.8
47.5°	321.2	307.0	296.7	291.0	286.2	283.5	280.2	276.6	275.2	274.0	273.9
50°	304.5	291.6	281.9	276.6	272.0	268.2	264.8	262.4	261.5	261.5	262.1
52.5°	287.7	276.7	268.5	261.9	257.6	253.4	250.4	248.9	247.6	249.0	250.1
55°	263.0	251.9	245.9	239.6	235.4	230.5	229.0	228.4	227.5	229.9	231.1
57.5°	236.9	229.1	222.0	215.8	212.0	209.2	207.2	206.8	208.5	209.6	213.6
60°	220.3	211.3	204.9	200.1	195.6	193.8	193.2	192.6	193.8	197.1	202.2
62.5°	202.0	194.6	187.8	184.3	180.9	177.9	177.8	178.2	180.5	184.3	189.5
65°	175.2	168.8	164.3	160.1	157.4	155.6	156.2	157.4	160.1	165.2	171.0
67.5°	147.9	143.5	139.5	136.1	133.5	133.5	134.1	135.9	139.1	145.0	150.2
70°	130.3	125.5	122.2	120.6	118.6	117.4	119.1	122.2	124.8	130.3	134.8
72.5°	112.7	108.6	106.1	105.0	104.1	103.1	103.8	107.0	110.7	116.1	121.4
75°	86.7	85.2	83.3	82.1	81.3	81.8	82.5	85.5	88.5	94.2	100.2
77.5°	63.3	61.7	60.6	60.3	59.8	60.1	61.8	64.0	67.0	71.1	75.7
80°	47.8	47.2	46.7	46.3	46.3	46.7	49.0	50.5	53.2	57.2	60.8
82.5°	34.9	34.5	34.4	34.3	34.5	34.6	36.0	38.0	40.2	43.3	46.3
85°	18.4	17.7	18.7	18.9	18.4	19.3	19.9	21.1	21.9	23.4	25.0
87.5°	7.5	8.3	8.3	8.9	9.2	9.9	9.9	11.1	11.7	12.4	12.4
90°	7.4	9.0	10.5	11.9	13.3	14.7	15.8	16.8	17.8	18.9	19.6
92.5°	26.9	28.3	30.1	31.8	33.6	35.3	36.7	38.0	39.4	40.7	41.7
95°	61.5	62.7	64.7	66.8	68.8	70.9	72.3	73.8	75.2	76.6	77.6
97.5°	100.1	101.6	104.4	107.2	110.0	112.9	114.2	115.6	116.9	118.3	119.1
100°	128.9	130.2	132.8	135.5	138.2	140.9	142.7	144.5	146.4	148.2	149.3
102.5°	163.8	164.9	166.3	167.6	169.0	170.3	172.3	174.3	176.3	178.3	179.6
105°	214.0	215.1	216.3	217.5	218.8	220.0	221.3	222.4	223.7	224.9	225.9
107.5°	268.5	269.4	270.4	271.3	272.3	273.2	273.9	274.4	275.0	275.7	276.0
110°	306.0	306.8	307.4	308.1	308.7	309.3	309.9	310.5	311.2	311.7	312.0



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	342.4	343.0	343.8	344.6	345.3	346.1	346.4	346.7	347.0	347.3	347.2
115°	400.1	400.6	401.1	401.5	401.9	402.3	402.1	401.9	401.6	401.5	401.2
117.5°	455.0	455.3	455.7	456.1	456.4	456.8	456.9	457.1	457.2	457.4	457.1
120°	492.9	493.5	493.7	493.9	494.2	494.3	494.3	494.3	494.3	494.3	493.9
122.5°	528.5	529.0	529.6	530.1	530.6	531.2	531.0	530.8	530.7	530.5	530.1
125°	583.9	584.6	584.9	585.0	585.3	585.5	585.0	584.6	584.2	583.8	583.5
127.5°	637.1	637.5	637.8	638.0	638.3	638.5	638.3	638.1	637.9	637.7	637.4
130°	671.5	672.2	672.6	673.0	673.4	673.8	673.7	673.4	673.2	673.0	672.7
132.5°	707.3	708.1	708.0	707.9	707.8	707.7	707.5	707.3	707.1	706.9	706.5
135°	758.0	758.7	758.8	759.1	759.2	759.5	759.5	759.5	759.5	759.5	759.1
137.5°	807.1	807.9	808.3	808.8	809.3	809.7	809.9	810.2	810.5	810.7	810.3
140°	838.1	838.9	839.6	840.2	840.7	841.4	841.8	842.2	842.6	843.0	842.7
142.5°	869.1	870.0	870.7	871.5	872.3	873.1	873.3	873.5	873.8	874.0	873.6
145°	915.5	916.2	916.9	917.5	918.1	918.7	918.7	918.7	918.7	918.7	918.4
147.5°	957.1	957.6	958.1	958.6	959.1	959.6	960.0	960.6	961.1	961.6	961.1
150°	983.3	983.6	984.4	985.2	986.0	986.8	986.8	986.8	986.8	986.8	986.7
152.5°	1008.8	1009.1	1009.4	1009.7	1010.1	1010.4	1010.9	1011.4	1011.9	1012.3	1012.3
155°	1043.9	1044.0	1044.3	1044.4	1044.7	1044.8	1045.7	1046.5	1047.3	1048.1	1048.0
157.5°	1074.5	1074.4	1074.6	1074.8	1075.0	1075.2	1076.0	1076.8	1077.7	1078.5	1078.2
160°	1093.0	1092.8	1093.0	1093.2	1093.4	1093.6	1094.4	1095.3	1096.1	1096.9	1096.8
162.5°	1110.6	1110.4	1110.4	1110.5	1110.5	1110.6	1111.5	1112.5	1113.5	1114.5	1114.4
165°	1133.4	1133.3	1133.5	1133.7	1133.9	1134.1	1135.0	1135.8	1136.5	1137.4	1137.2
167.5°	1150.9	1150.5	1150.5	1150.5	1150.5	1150.5	1151.8	1152.9	1154.2	1155.4	1155.4
170°	1161.3	1160.8	1160.8	1160.8	1160.8	1160.8	1162.1	1163.2	1164.5	1165.7	1165.6
172.5°	1168.6	1168.2	1168.2	1168.2	1168.2	1168.2	1169.4	1170.6	1171.9	1173.1	1173.1
175°	1176.9	1176.5	1176.5	1176.5	1176.5	1176.5	1177.7	1178.9	1180.1	1181.4	1181.3
177.5°	1181.8	1181.4	1181.2	1181.1	1180.8	1180.7	1181.7	1182.6	1183.7	1184.6	1184.6
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	675.5	677.2	675.8	677.7	675.8	677.2	675.5	677.0	679.1	677.7	681.0
5°	622.7	619.9	621.7	620.5	621.7	619.9	622.7	624.2	627.7	628.9	631.4
7.5°	573.8	571.2	568.2	566.8	568.2	571.2	573.8	574.6	577.7	582.3	585.7
10°	543.2	539.9	539.6	537.5	539.6	539.9	543.2	546.5	548.6	554.3	558.3
12.5°	520.8	517.7	514.3	513.4	514.3	517.7	520.8	523.6	524.3	530.8	533.5
15°	489.0	486.6	484.5	486.3	484.5	486.6	489.0	490.8	494.2	498.7	501.7
17.5°	462.6	460.6	460.3	458.0	460.3	460.6	462.6	463.6	469.1	472.0	477.1
20°	446.0	444.5	445.0	441.2	445.0	444.5	446.0	448.7	454.1	455.6	461.1
22.5°	432.8	429.8	429.4	428.6	429.4	429.8	432.8	435.2	436.3	440.9	444.7
25°	412.0	410.5	409.0	410.5	409.0	410.5	412.0	414.7	415.9	419.2	422.8
27.5°	393.9	392.1	391.7	391.8	391.7	392.1	393.9	393.6	396.9	399.5	402.2
30°	382.8	379.8	380.1	379.8	380.1	379.8	382.8	382.8	384.6	387.0	389.4
32.5°	370.7	368.7	368.3	367.7	368.3	368.7	370.7	370.3	372.6	375.4	378.1
35°	353.0	353.0	351.5	351.5	351.5	353.0	353.0	353.9	356.3	356.3	359.3
37.5°	336.3	336.0	335.1	335.3	335.1	336.0	336.3	337.1	337.9	339.1	341.1
40°	323.8	323.5	322.6	320.8	322.6	323.5	323.8	325.0	325.6	327.1	328.3
42.5°	311.8	310.8	310.3	309.7	310.3	310.8	311.8	312.5	312.8	314.8	317.3
45°	292.8	292.8	292.2	291.9	292.2	292.8	292.8	292.8	293.1	295.5	296.8
47.5°	274.4	275.0	276.1	275.9	276.1	275.0	274.4	273.9	274.0	275.2	276.6
50°	263.3	263.6	264.5	264.8	264.5	263.6	263.3	262.1	261.5	261.5	262.4
52.5°	251.0	252.8	253.9	253.7	253.9	252.8	251.0	250.1	249.0	247.6	248.9
55°	233.9	235.9	238.1	238.4	238.1	235.9	233.9	231.1	229.9	227.5	228.4
57.5°	216.8	219.8	222.0	222.7	222.0	219.8	216.8	213.6	209.6	208.5	206.8
60°	205.3	209.1	211.8	213.1	211.8	209.1	205.3	202.2	197.1	193.8	192.6
62.5°	194.2	198.5	201.3	201.5	201.3	198.5	194.2	189.5	184.3	180.5	178.2
65°	176.0	180.5	183.0	184.7	183.0	180.5	176.0	171.0	165.2	160.1	157.4
67.5°	156.5	161.1	163.7	165.2	163.7	161.1	156.5	150.2	145.0	139.1	135.9
70°	142.4	146.9	150.4	151.7	150.4	146.9	142.4	134.8	130.3	124.8	122.2
72.5°	128.4	132.4	135.3	136.7	135.3	132.4	128.4	121.4	116.1	110.7	107.0
75°	104.1	109.6	112.3	113.8	112.3	109.6	104.1	100.2	94.2	88.5	85.5
77.5°	80.3	85.2	86.8	87.6	86.8	85.2	80.3	75.7	71.1	67.0	64.0
80°	64.4	67.4	69.6	69.8	69.6	67.4	64.4	60.8	57.2	53.2	50.5
82.5°	49.5	52.0	52.7	53.5	52.7	52.0	49.5	46.3	43.3	40.2	38.0
85°	27.1	28.3	28.6	28.3	28.6	28.3	27.1	25.0	23.4	21.9	21.1
87.5°	13.0	12.8	13.0	13.5	13.0	12.8	13.0	12.4	12.4	11.7	11.1
90°	20.3	20.8	21.5	22.1	21.5	20.8	20.3	19.6	18.9	17.8	16.8
92.5°	42.1	42.5	43.0	43.4	43.0	42.5	42.1	41.7	40.7	39.4	38.0
95°	78.0	78.3	78.7	79.1	78.7	78.3	78.0	77.6	76.6	75.2	73.8
97.5°	119.3	119.5	119.8	120.0	119.8	119.5	119.3	119.1	118.3	116.9	115.6
100°	149.7	150.1	150.6	151.0	150.6	150.1	149.7	149.3	148.2	146.4	144.5
102.5°	180.2	180.8	181.3	181.9	181.3	180.8	180.2	179.6	178.3	176.3	174.3
105°	226.5	227.0	227.7	228.3	227.7	227.0	226.5	225.9	224.9	223.7	222.4
107.5°	275.9	275.9	275.8	275.8	275.8	275.9	275.9	276.0	275.7	275.0	274.4
110°	311.7	311.6	311.3	311.2	311.3	311.6	311.7	312.0	311.7	311.2	310.5



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	346.9	346.5	346.1	345.8	346.1	346.5	346.9	347.2	347.3	347.0	346.7
115°	401.1	400.8	400.6	400.4	400.6	400.8	401.1	401.2	401.5	401.6	401.9
117.5°	456.3	455.5	454.6	453.8	454.6	455.5	456.3	457.1	457.4	457.2	457.1
120°	493.1	492.3	491.5	490.7	491.5	492.3	493.1	493.9	494.3	494.3	494.3
122.5°	529.4	528.8	528.1	527.5	528.1	528.8	529.4	530.1	530.5	530.7	530.8
125°	583.4	583.1	582.9	582.7	582.9	583.1	583.4	583.5	583.8	584.2	584.6
127.5°	637.0	636.5	636.1	635.7	636.1	636.5	637.0	637.4	637.7	637.9	638.1
130°	672.3	671.9	671.5	671.1	671.5	671.9	672.3	672.7	673.0	673.2	673.4
132.5°	705.9	705.4	704.8	704.3	704.8	705.4	705.9	706.5	706.9	707.1	707.3
135°	758.2	757.4	756.6	755.7	756.6	757.4	758.2	759.1	759.5	759.5	759.5
137.5°	809.3	808.3	807.2	806.2	807.2	808.3	809.3	810.3	810.7	810.5	810.2
140°	841.7	840.7	839.6	838.6	839.6	840.7	841.7	842.7	843.0	842.6	842.2
142.5°	872.6	871.6	870.6	869.6	870.6	871.6	872.6	873.6	874.0	873.8	873.5
145°	917.8	917.2	916.6	915.9	916.6	917.2	917.8	918.4	918.7	918.7	918.7
147.5°	959.7	958.3	957.0	955.5	957.0	958.3	959.7	961.1	961.6	961.1	960.6
150°	986.2	985.8	985.4	985.0	985.4	985.8	986.2	986.7	986.8	986.8	986.8
152.5°	1011.5	1010.7	1010.0	1009.3	1010.0	1010.7	1011.5	1012.3	1012.3	1011.9	1011.4
155°	1046.9	1045.9	1045.0	1043.9	1045.0	1045.9	1046.9	1048.0	1048.1	1047.3	1046.5
157.5°	1076.9	1075.5	1074.2	1072.9	1074.2	1075.5	1076.9	1078.2	1078.5	1077.7	1076.8
160°	1095.7	1094.7	1093.7	1092.7	1093.7	1094.7	1095.7	1096.8	1096.9	1096.1	1095.3
162.5°	1113.2	1112.0	1110.8	1109.6	1110.8	1112.0	1113.2	1114.4	1114.5	1113.5	1112.5
165°	1136.0	1134.7	1133.5	1132.3	1133.5	1134.7	1136.0	1137.2	1137.4	1136.5	1135.8
167.5°	1154.1	1152.9	1151.6	1150.3	1151.6	1152.9	1154.1	1155.4	1155.4	1154.2	1152.9
170°	1164.2	1162.8	1161.3	1159.9	1161.3	1162.8	1164.2	1165.6	1165.7	1164.5	1163.2
172.5°	1171.8	1170.5	1169.3	1168.0	1169.3	1170.5	1171.8	1173.1	1173.1	1171.9	1170.6
175°	1179.9	1178.5	1176.9	1175.5	1176.9	1178.5	1179.9	1181.3	1181.4	1180.1	1178.9
177.5°	1183.4	1182.3	1181.1	1180.0	1181.1	1182.3	1183.4	1184.6	1184.6	1183.7	1182.6
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	677.9	680.8	684.4	687.1	691.9	694.0	696.7	698.9	702.7	706.3	710.7
5°	632.2	637.4	644.3	651.8	660.5	666.5	675.0	680.1	690.3	699.7	708.7
7.5°	590.8	597.1	606.9	616.6	628.0	638.3	648.9	660.5	673.6	689.0	701.8
10°	562.4	570.8	581.4	593.4	607.3	619.3	633.4	646.1	662.0	680.1	697.0
12.5°	539.8	547.0	558.8	570.3	585.1	599.8	614.4	631.2	649.7	669.8	690.9
15°	508.6	514.6	524.2	540.2	555.2	569.7	591.6	607.3	630.7	653.0	678.6
17.5°	481.9	489.4	497.5	511.2	526.7	544.8	564.4	584.1	606.7	634.9	663.8
20°	465.6	471.6	480.9	491.4	507.9	526.0	544.7	564.5	592.2	621.4	652.4
22.5°	447.7	454.2	464.8	476.3	490.1	507.5	528.1	549.9	578.8	607.4	641.1
25°	426.7	431.3	440.8	451.1	464.9	479.7	501.1	525.1	553.7	586.5	620.8
27.5°	406.9	410.9	419.7	428.6	441.1	458.6	477.7	502.0	528.9	562.2	600.2
30°	392.7	397.0	404.7	414.4	426.4	441.8	461.4	484.2	513.1	545.6	585.3
32.5°	380.4	384.2	390.1	399.7	411.5	426.4	444.5	467.9	496.7	529.7	568.7
35°	361.4	365.6	370.1	377.6	387.9	402.3	422.2	444.2	471.8	503.7	539.6
37.5°	342.5	347.1	351.1	357.8	367.2	379.9	397.1	420.0	445.0	475.8	510.2
40°	330.7	334.3	337.6	344.8	354.2	366.2	382.1	402.7	429.1	457.7	486.3
42.5°	318.9	322.3	325.1	331.4	340.0	351.6	366.8	386.7	411.3	438.0	463.2
45°	300.3	302.5	305.8	311.2	318.1	328.6	343.3	361.2	381.9	407.2	426.1
47.5°	280.2	283.5	286.2	291.0	296.7	307.0	321.2	336.3	355.1	373.9	387.2
50°	264.8	268.2	272.0	276.6	281.9	291.6	304.5	319.9	335.8	350.3	361.7
52.5°	250.4	253.4	257.6	261.9	268.5	276.7	287.7	301.3	317.0	327.4	336.9
55°	229.0	230.5	235.4	239.6	245.9	251.9	263.0	275.0	284.7	292.5	300.3
57.5°	207.2	209.2	212.0	215.8	222.0	229.1	236.9	247.6	253.2	257.2	263.3
60°	193.2	193.8	195.6	200.1	204.9	211.3	220.3	227.8	232.0	235.4	240.4
62.5°	177.8	177.9	180.9	184.3	187.8	194.6	202.0	208.0	211.6	213.2	218.1
65°	156.2	155.6	157.4	160.1	164.3	168.8	175.2	180.5	180.2	182.0	185.1
67.5°	134.1	133.5	133.5	136.1	139.5	143.5	147.9	151.0	151.1	153.4	155.0
70°	119.1	117.4	118.6	120.6	122.2	125.5	130.3	131.5	131.8	133.0	134.5
72.5°	103.8	103.1	104.1	105.0	106.1	108.6	112.7	113.4	113.5	114.2	116.7
75°	82.5	81.8	81.3	82.1	83.3	85.2	86.7	87.9	87.5	87.9	89.7
77.5°	61.8	60.1	59.8	60.3	60.6	61.7	63.3	63.1	63.5	63.4	65.4
80°	49.0	46.7	46.3	46.3	46.7	47.2	47.8	48.5	47.5	48.5	49.0
82.5°	36.0	34.6	34.5	34.3	34.4	34.5	34.9	35.2	35.0	35.4	35.8
85°	19.9	19.3	18.4	18.9	18.7	17.7	18.4	17.4	17.2	17.4	17.7
87.5°	9.9	9.9	9.2	8.9	8.3	8.3	7.5	7.0	6.3	6.3	6.7
90°	15.8	14.7	13.3	11.9	10.5	9.0	7.4	5.9	4.2	2.5	1.0
92.5°	36.7	35.3	33.6	31.8	30.1	28.3	26.9	25.7	24.6	23.4	22.3
95°	72.3	70.9	68.8	66.8	64.7	62.7	61.5	61.1	60.7	60.2	59.8
97.5°	114.2	112.9	110.0	107.2	104.4	101.6	100.1	99.9	99.7	99.6	99.4
100°	142.7	140.9	138.2	135.5	132.8	130.2	128.9	128.9	128.9	128.9	128.9
102.5°	172.3	170.3	169.0	167.6	166.3	164.9	163.8	163.0	162.2	161.4	160.6
105°	221.3	220.0	218.8	217.5	216.3	215.1	214.0	212.9	211.9	210.9	209.8
107.5°	273.9	273.2	272.3	271.3	270.4	269.4	268.5	267.4	266.4	265.4	264.4
110°	309.9	309.3	308.7	308.1	307.4	306.8	306.0	305.0	304.0	302.9	302.0



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	346.4	346.1	345.3	344.6	343.8	343.0	342.4	341.8	341.3	340.8	340.2
115°	402.1	402.3	401.9	401.5	401.1	400.6	400.1	399.2	398.4	397.6	396.7
117.5°	456.9	456.8	456.4	456.1	455.7	455.3	455.0	454.6	454.2	453.8	453.4
120°	494.3	494.3	494.2	493.9	493.7	493.5	492.9	491.9	490.8	489.8	488.8
122.5°	531.0	531.2	530.6	530.1	529.6	529.0	528.5	528.2	527.8	527.5	527.1
125°	585.0	585.5	585.3	585.0	584.9	584.6	583.9	582.7	581.5	580.3	579.0
127.5°	638.3	638.5	638.3	638.0	637.8	637.5	637.1	636.4	635.6	634.9	634.3
130°	673.7	673.8	673.4	673.0	672.6	672.2	671.5	670.5	669.5	668.4	667.4
132.5°	707.5	707.7	707.8	707.9	708.0	708.1	707.3	705.6	703.9	702.2	700.5
135°	759.5	759.5	759.2	759.1	758.8	758.7	758.0	756.7	755.5	754.2	753.0
137.5°	809.9	809.7	809.3	808.8	808.3	807.9	807.1	805.9	804.7	803.5	802.3
140°	841.8	841.4	840.7	840.2	839.6	838.9	838.1	837.1	836.1	835.0	834.0
142.5°	873.3	873.1	872.3	871.5	870.7	870.0	869.1	868.2	867.4	866.6	865.7
145°	918.7	918.7	918.1	917.5	916.9	916.2	915.5	914.7	913.9	913.1	912.3
147.5°	960.0	959.6	959.1	958.6	958.1	957.6	957.1	956.7	956.2	955.8	955.4
150°	986.8	986.8	986.0	985.2	984.4	983.6	983.3	983.5	983.7	983.9	984.0
152.5°	1010.9	1010.4	1010.1	1009.7	1009.4	1009.1	1008.8	1008.5	1008.2	1007.9	1007.7
155°	1045.7	1044.8	1044.7	1044.4	1044.3	1044.0	1043.9	1043.9	1043.9	1043.9	1043.9
157.5°	1076.0	1075.2	1075.0	1074.8	1074.6	1074.4	1074.5	1075.0	1075.4	1075.9	1076.3
160°	1094.4	1093.6	1093.4	1093.2	1093.0	1092.8	1093.0	1093.6	1094.2	1094.9	1095.4
162.5°	1111.5	1110.6	1110.5	1110.5	1110.4	1110.4	1110.6	1111.0	1111.5	1112.0	1112.4
165°	1135.0	1134.1	1133.9	1133.7	1133.5	1133.3	1133.4	1133.9	1134.2	1134.6	1135.0
167.5°	1151.8	1150.5	1150.5	1150.5	1150.5	1150.5	1150.9	1151.8	1152.5	1153.3	1154.2
170°	1162.1	1160.8	1160.8	1160.8	1160.8	1160.8	1161.3	1162.1	1162.8	1163.7	1164.5
172.5°	1169.4	1168.2	1168.2	1168.2	1168.2	1168.2	1168.6	1169.4	1170.2	1171.1	1171.9
175°	1177.7	1176.5	1176.5	1176.5	1176.5	1176.5	1176.9	1177.7	1178.5	1179.3	1180.1
177.5°	1181.7	1180.7	1180.8	1181.1	1181.2	1181.4	1181.8	1182.4	1183.0	1183.8	1184.4
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	712.9	716.2	718.4	722.5	725.9	727.8	729.4	730.9	732.6	734.0	738.2
5°	717.4	725.2	731.9	742.1	751.5	758.7	766.4	773.4	779.1	787.3	793.5
7.5°	715.4	729.4	743.9	759.7	775.9	791.0	804.8	817.8	829.5	843.7	856.1
10°	713.5	732.5	751.1	772.5	794.5	813.1	830.6	848.3	861.3	879.3	894.7
12.5°	712.1	734.4	756.9	782.6	806.8	833.1	856.3	869.3	889.0	903.4	921.6
15°	706.0	735.5	766.4	795.4	829.7	854.1	874.5	899.8	918.1	936.5	956.3
17.5°	695.1	728.5	763.2	801.1	833.9	860.2	886.5	910.9	932.8	957.4	982.1
20°	690.1	723.4	763.2	802.0	834.2	861.6	888.7	915.4	939.5	971.1	999.7
22.5°	679.5	719.9	756.5	794.2	827.4	857.2	888.0	918.3	950.3	986.0	1021.8
25°	660.5	701.5	740.3	777.6	811.0	848.3	881.1	921.8	962.7	1010.0	1054.5
27.5°	641.0	680.1	715.7	751.7	790.7	832.9	875.4	921.5	975.2	1034.7	1097.6
30°	625.0	662.0	696.6	733.6	774.3	821.8	868.5	923.3	985.2	1052.3	1127.0
32.5°	606.5	640.6	674.3	713.4	757.7	807.9	862.2	922.3	996.8	1073.1	1149.9
35°	574.8	603.4	637.9	679.8	729.8	787.3	850.2	921.1	1006.6	1094.2	1158.9
37.5°	537.2	563.8	600.2	646.1	698.5	760.2	834.8	919.0	1009.8	1079.6	1100.5
40°	511.9	536.5	574.5	622.0	675.6	740.9	822.8	911.8	999.7	1044.3	1027.1
42.5°	484.9	510.8	547.8	594.8	652.4	723.6	807.6	896.7	970.3	987.1	927.9
45°	442.4	469.1	505.6	553.1	615.1	692.1	779.7	860.6	903.1	872.7	780.9
47.5°	402.8	427.9	461.7	510.7	574.7	654.4	738.7	803.3	806.7	734.1	636.1
50°	375.9	399.0	433.0	482.1	545.6	626.2	702.3	753.2	730.4	648.2	554.1
52.5°	349.4	372.1	405.6	454.2	517.0	590.8	661.7	697.4	654.3	570.0	489.5
55°	311.2	331.1	363.8	408.7	468.3	536.9	597.1	609.3	553.4	470.3	405.0
57.5°	273.9	292.4	322.3	363.5	418.0	478.8	525.9	523.2	464.1	392.8	341.0
60°	248.6	266.6	293.1	333.4	383.1	435.5	475.8	466.1	407.5	346.1	302.5
62.5°	225.9	242.1	267.1	302.4	347.7	396.2	429.3	415.1	357.6	304.0	269.4
65°	192.6	206.1	227.5	257.6	295.2	335.3	360.8	342.5	293.4	251.6	223.9
67.5°	160.7	171.6	189.5	213.6	245.7	277.7	293.3	274.9	235.6	205.1	184.6
70°	140.5	150.2	164.0	185.4	213.3	240.4	252.2	235.6	201.9	175.7	161.0
72.5°	120.3	128.3	140.5	159.6	182.0	205.6	215.8	200.0	172.3	150.2	136.4
75°	93.0	98.4	106.9	120.1	137.8	156.5	162.2	148.4	130.6	114.1	105.0
77.5°	66.5	71.1	77.6	85.9	98.5	110.4	115.3	107.3	93.6	83.1	75.7
80°	51.2	53.6	59.0	65.9	75.8	83.3	86.7	81.5	71.9	64.1	58.4
82.5°	36.4	38.9	42.1	47.8	54.2	59.3	62.8	59.4	52.4	46.3	42.9
85°	17.7	19.3	21.1	23.4	28.3	31.3	31.0	28.9	26.1	23.8	21.9
87.5°	6.7	7.4	8.4	9.9	10.9	12.2	13.0	12.8	12.1	11.6	11.1
90°	2.5	4.2	5.9	7.4	9.0	10.5	11.9	13.3	14.7	15.8	16.8
92.5°	23.4	24.6	25.7	26.9	28.3	30.1	31.8	33.6	35.3	36.7	38.0
95°	60.2	60.7	61.1	61.5	62.7	64.7	66.8	68.8	70.9	72.3	73.8
97.5°	99.6	99.7	99.9	100.1	101.6	104.4	107.2	110.0	112.9	114.2	115.6
100°	128.9	128.9	128.9	128.9	130.2	132.8	135.5	138.2	140.9	142.7	144.5
102.5°	161.4	162.2	163.0	163.8	164.9	166.3	167.6	169.0	170.3	172.3	174.3
105°	210.9	211.9	212.9	214.0	215.1	216.3	217.5	218.8	220.0	221.3	222.4
107.5°	265.4	266.4	267.4	268.5	269.4	270.4	271.3	272.3	273.2	273.9	274.4
110°	302.9	304.0	305.0	306.0	306.8	307.4	308.1	308.7	309.3	309.9	310.5



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	340.8	341.3	341.8	342.4	343.0	343.8	344.6	345.3	346.1	346.4	346.7
115°	397.6	398.4	399.2	400.1	400.6	401.1	401.5	401.9	402.3	402.1	401.9
117.5°	453.8	454.2	454.6	455.0	455.3	455.7	456.1	456.4	456.8	456.9	457.1
120°	489.8	490.8	491.9	492.9	493.5	493.7	493.9	494.2	494.3	494.3	494.3
122.5°	527.5	527.8	528.2	528.5	529.0	529.6	530.1	530.6	531.2	531.0	530.8
125°	580.3	581.5	582.7	583.9	584.6	584.9	585.0	585.3	585.5	585.0	584.6
127.5°	634.9	635.6	636.4	637.1	637.5	637.8	638.0	638.3	638.5	638.3	638.1
130°	668.4	669.5	670.5	671.5	672.2	672.6	673.0	673.4	673.8	673.7	673.4
132.5°	702.2	703.9	705.6	707.3	708.1	708.0	707.9	707.8	707.7	707.5	707.3
135°	754.2	755.5	756.7	758.0	758.7	758.8	759.1	759.2	759.5	759.5	759.5
137.5°	803.5	804.7	805.9	807.1	807.9	808.3	808.8	809.3	809.7	809.9	810.2
140°	835.0	836.1	837.1	838.1	838.9	839.6	840.2	840.7	841.4	841.8	842.2
142.5°	866.6	867.4	868.2	869.1	870.0	870.7	871.5	872.3	873.1	873.3	873.5
145°	913.1	913.9	914.7	915.5	916.2	916.9	917.5	918.1	918.7	918.7	918.7
147.5°	955.8	956.2	956.7	957.1	957.6	958.1	958.6	959.1	959.6	960.0	960.6
150°	983.9	983.7	983.5	983.3	983.6	984.4	985.2	986.0	986.8	986.8	986.8
152.5°	1007.9	1008.2	1008.5	1008.8	1009.1	1009.4	1009.7	1010.1	1010.4	1010.9	1011.4
155°	1043.9	1043.9	1043.9	1043.9	1044.0	1044.3	1044.4	1044.7	1044.8	1045.7	1046.5
157.5°	1075.9	1075.4	1075.0	1074.5	1074.4	1074.6	1074.8	1075.0	1075.2	1076.0	1076.8
160°	1094.9	1094.2	1093.6	1093.0	1092.8	1093.0	1093.2	1093.4	1093.6	1094.4	1095.3
162.5°	1112.0	1111.5	1111.0	1110.6	1110.4	1110.4	1110.5	1110.5	1110.6	1111.5	1112.5
165°	1134.6	1134.2	1133.9	1133.4	1133.3	1133.5	1133.7	1133.9	1134.1	1135.0	1135.8
167.5°	1153.3	1152.5	1151.8	1150.9	1150.5	1150.5	1150.5	1150.5	1150.5	1151.8	1152.9
170°	1163.7	1162.8	1162.1	1161.3	1160.8	1160.8	1160.8	1160.8	1160.8	1162.1	1163.2
172.5°	1171.1	1170.2	1169.4	1168.6	1168.2	1168.2	1168.2	1168.2	1168.2	1169.4	1170.6
175°	1179.3	1178.5	1177.7	1176.9	1176.5	1176.5	1176.5	1176.5	1176.5	1177.7	1178.9
177.5°	1183.8	1183.0	1182.4	1181.8	1181.4	1181.2	1181.1	1180.8	1180.7	1181.7	1182.6
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	709.0	709.0	709.0	709.0	709.0	709.0	709.0
2.5°	741.5	743.4	747.5	746.1	748.0	748.9	750.0
5°	801.4	811.0	815.2	814.6	820.9	819.4	817.9
7.5°	869.0	879.2	884.8	891.8	896.0	896.2	899.8
10°	907.3	920.5	926.0	933.5	938.3	941.0	940.7
12.5°	936.7	947.1	959.2	962.9	969.4	972.8	971.5
15°	972.0	988.6	1001.2	1007.5	1015.7	1018.0	1021.4
17.5°	1003.5	1025.7	1040.5	1060.1	1067.5	1072.1	1069.4
20°	1027.4	1056.5	1071.3	1094.8	1107.7	1114.7	1112.2
22.5°	1055.6	1087.1	1114.4	1134.7	1154.4	1163.8	1165.7
25°	1103.8	1147.2	1187.2	1213.9	1238.3	1244.0	1256.7
27.5°	1157.8	1208.9	1251.6	1279.8	1296.8	1303.1	1307.1
30°	1191.7	1242.5	1274.8	1292.8	1298.2	1297.6	1297.0
32.5°	1208.3	1240.2	1246.3	1241.3	1228.9	1218.4	1207.4
35°	1184.8	1161.0	1125.5	1079.7	1046.1	1012.0	1008.7
37.5°	1065.6	989.5	930.4	864.4	826.3	802.8	786.5
40°	953.3	867.0	795.4	739.7	700.8	685.6	670.5
42.5°	831.6	749.0	685.6	639.1	609.9	592.9	580.9
45°	675.6	602.8	553.1	519.4	496.2	483.0	475.5
47.5°	553.6	499.7	457.6	433.2	417.2	406.9	406.9
50°	488.1	436.7	408.7	389.4	375.6	367.4	368.9
52.5°	430.1	391.7	367.7	351.6	341.4	336.4	336.2
55°	359.7	331.9	316.3	304.5	297.6	291.9	293.1
57.5°	307.6	284.2	273.8	264.0	259.2	256.9	253.7
60°	275.4	257.3	248.3	240.4	235.6	233.9	230.5
62.5°	246.7	232.5	223.7	217.3	213.0	212.4	209.8
65°	207.3	196.5	188.7	185.7	181.2	180.0	180.0
67.5°	171.0	163.2	157.1	154.3	152.3	152.7	151.1
70°	148.1	141.7	137.8	134.8	133.3	133.6	132.4
72.5°	129.5	122.5	119.1	117.2	115.3	116.1	115.6
75°	98.1	94.5	92.7	90.9	89.7	89.0	88.5
77.5°	72.0	68.8	67.5	66.5	66.6	65.2	66.3
80°	55.7	53.0	52.0	50.5	50.2	50.2	50.0
82.5°	40.7	39.2	38.6	37.3	36.8	37.2	36.4
85°	21.1	19.9	19.6	19.6	18.9	18.4	19.9
87.5°	11.2	10.5	10.7	10.5	10.7	10.5	10.2
90°	17.8	18.9	19.6	20.3	20.8	21.5	22.1
92.5°	39.4	40.7	41.7	42.1	42.5	43.0	43.4
95°	75.2	76.6	77.6	78.0	78.3	78.7	79.1
97.5°	116.9	118.3	119.1	119.3	119.5	119.8	120.0
100°	146.4	148.2	149.3	149.7	150.1	150.6	151.0
102.5°	176.3	178.3	179.6	180.2	180.8	181.3	181.9
105°	223.7	224.9	225.9	226.5	227.0	227.7	228.3
107.5°	275.0	275.7	276.0	275.9	275.9	275.8	275.8
110°	311.2	311.7	312.0	311.7	311.6	311.3	311.2



TEST NUMBER: P333197-927

CATALOG NUMBER: S125DIP-S610D1205U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	347.0	347.3	347.2	346.9	346.5	346.1	345.8
115°	401.6	401.5	401.2	401.1	400.8	400.6	400.4
117.5°	457.2	457.4	457.1	456.3	455.5	454.6	453.8
120°	494.3	494.3	493.9	493.1	492.3	491.5	490.7
122.5°	530.7	530.5	530.1	529.4	528.8	528.1	527.5
125°	584.2	583.8	583.5	583.4	583.1	582.9	582.7
127.5°	637.9	637.7	637.4	637.0	636.5	636.1	635.7
130°	673.2	673.0	672.7	672.3	671.9	671.5	671.1
132.5°	707.1	706.9	706.5	705.9	705.4	704.8	704.3
135°	759.5	759.5	759.1	758.2	757.4	756.6	755.7
137.5°	810.5	810.7	810.3	809.3	808.3	807.2	806.2
140°	842.6	843.0	842.7	841.7	840.7	839.6	838.6
142.5°	873.8	874.0	873.6	872.6	871.6	870.6	869.6
145°	918.7	918.7	918.4	917.8	917.2	916.6	915.9
147.5°	961.1	961.6	961.1	959.7	958.3	957.0	955.5
150°	986.8	986.8	986.7	986.2	985.8	985.4	985.0
152.5°	1011.9	1012.3	1012.3	1011.5	1010.7	1010.0	1009.3
155°	1047.3	1048.1	1048.0	1046.9	1045.9	1045.0	1043.9
157.5°	1077.7	1078.5	1078.2	1076.9	1075.5	1074.2	1072.9
160°	1096.1	1096.9	1096.8	1095.7	1094.7	1093.7	1092.7
162.5°	1113.5	1114.5	1114.4	1113.2	1112.0	1110.8	1109.6
165°	1136.5	1137.4	1137.2	1136.0	1134.7	1133.5	1132.3
167.5°	1154.2	1155.4	1155.4	1154.1	1152.9	1151.6	1150.3
170°	1164.5	1165.7	1165.6	1164.2	1162.8	1161.3	1159.9
172.5°	1171.9	1173.1	1173.1	1171.8	1170.5	1169.3	1168.0
175°	1180.1	1181.4	1181.3	1179.9	1178.5	1176.9	1175.5
177.5°	1183.7	1184.6	1184.6	1183.4	1182.3	1181.1	1180.0
180°	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9	1182.9

(END OF REPORT)