

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333631

Luminaire Tested: **S125RDIP-S1270D1035U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333631  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D1035U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9015.7 lumens  
Efficiency: N/A  
Efficacy: 135.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 66.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333631

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333631

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	67	66	62	59	56	54	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	30	25	30	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13332	13332	13332
5°	13363	13211	13291
10°	13262	13088	13088
15°	13104	12822	12718
20°	12902	12451	12302
25°	12666	12088	11821
30°	12371	11662	11290
35°	12071	11223	10694
40°	11790	10765	10108
45°	11449	10253	9470
50°	11106	9697	8804
55°	10709	9164	8094
60°	10311	8519	7330
65°	9840	7768	6457
70°	9304	6830	5565
75°	8559	5757	4629
80°	7539	4523	3887
85°	6358	3698	3468



TEST NUMBER: P333631

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	194.1	2.2
10°-20°	542.5	6.0
20°-30°	786.6	8.7
30°-40°	896.5	9.9
40°-50°	873.9	9.7
50°-60°	735.6	8.2
60°-70°	515.6	5.7
70°-80°	265.0	2.9
80°-90°	69.7	0.8
90°-100°	49.0	0.5
100°-110°	301.7	3.3
110°-120°	547.1	6.1
120°-130°	702.2	7.8
130°-140°	755.2	8.4
140°-150°	708.9	7.9
150°-160°	573.4	6.4
160°-170°	370.9	4.1
170°-180°	127.9	1.4
0°-30°	1523.2	16.9
0°-40°	2419.7	26.8
0°-60°	4029.1	44.7
0°-90°	4879.5	54.1
90°-120°	897.7	10.0
90°-150°	3064.0	34.0
90°-180°	4136.0	45.9
0°-180°	9015.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2064	2064	2064	2064	2064	
5°	2061	2054	2038	2052	2050	195
15°	1960	1949	1918	1915	1902	552
25°	1777	1752	1696	1676	1659	817
35°	1531	1492	1424	1380	1356	958
45°	1254	1206	1123	1062	1037	967
55°	951	899	814	746	719	850
65°	644	589	508	448	422	638
75°	343	295	231	198	186	363
85°	86	59	50	48	47	96
90°	1	9	16	21	24	6
95°	57	52	16	21	21	73
105°	294	297	298	297	296	311
115°	551	556	557	553	547	546
125°	784	790	791	787	784	700
135°	978	983	982	979	974	753
145°	1133	1135	1135	1136	1130	708
155°	1248	1243	1244	1246	1239	575
165°	1317	1311	1312	1317	1310	372
175°	1347	1341	1342	1349	1341	128
180°	1347	1347	1347	1347	1347	



TEST NUMBER: P333631

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2068.0	2067.2	2066.3	2065.5	2064.7	2062.9	2060.1	2057.3	2054.6	2051.8	2054.6
5°	2061.2	2059.8	2058.4	2057.0	2055.6	2053.0	2049.2	2045.4	2041.6	2037.8	2041.2
7.5°	2040.9	2039.6	2038.3	2036.9	2035.6	2032.7	2028.1	2023.5	2019.0	2014.4	2016.8
10°	2022.2	2021.1	2020.1	2019.1	2018.0	2015.1	2010.2	2005.4	2000.5	1995.7	1996.7
12.5°	2001.0	1999.7	1998.3	1997.0	1995.7	1991.8	1985.3	1978.8	1972.2	1965.7	1966.5
15°	1959.8	1957.7	1955.7	1953.6	1951.5	1946.8	1939.5	1932.3	1925.0	1917.7	1917.4
17.5°	1913.3	1910.2	1907.0	1903.8	1900.6	1894.4	1885.3	1876.1	1867.0	1857.8	1856.1
20°	1877.2	1873.7	1870.2	1866.8	1863.3	1856.0	1845.0	1833.9	1822.8	1811.7	1810.0
22.5°	1837.3	1833.8	1830.3	1826.9	1823.4	1815.9	1804.2	1792.6	1780.9	1769.3	1765.9
25°	1777.4	1772.2	1767.0	1761.8	1756.6	1747.6	1734.8	1722.0	1709.1	1696.3	1691.8
27.5°	1708.8	1702.5	1696.2	1689.9	1683.6	1673.6	1659.8	1646.1	1632.4	1618.7	1612.4
30°	1658.9	1652.3	1645.7	1639.2	1632.6	1622.0	1607.4	1592.9	1578.3	1563.8	1555.8
32.5°	1610.3	1602.6	1594.9	1587.2	1579.5	1568.2	1553.4	1538.6	1523.7	1508.9	1500.1
35°	1531.1	1522.7	1514.4	1506.1	1497.8	1485.8	1470.2	1454.7	1439.1	1423.5	1413.4
37.5°	1453.4	1443.3	1433.2	1423.1	1412.9	1399.8	1383.8	1367.7	1351.6	1335.5	1323.5
40°	1398.5	1388.1	1377.7	1367.3	1357.0	1343.4	1326.8	1310.2	1293.5	1276.9	1263.8
42.5°	1341.2	1330.5	1319.8	1309.1	1298.5	1284.5	1267.4	1250.2	1233.0	1215.8	1203.2
45°	1253.5	1243.5	1233.4	1223.4	1213.3	1198.8	1179.7	1160.7	1141.6	1122.6	1108.7
47.5°	1162.8	1152.2	1141.6	1131.0	1120.4	1105.5	1086.3	1067.1	1047.9	1028.7	1014.4
50°	1105.4	1094.0	1082.5	1071.1	1059.7	1044.1	1024.3	1004.6	984.8	965.1	950.5
52.5°	1043.0	1031.3	1019.6	1007.9	996.2	981.0	962.4	943.8	925.1	906.5	890.8
55°	951.1	940.0	928.9	917.8	906.7	891.5	872.1	852.7	833.3	813.9	798.3
57.5°	858.1	846.3	834.4	822.6	810.7	795.5	776.8	758.0	739.3	720.6	705.4
60°	798.3	786.1	774.0	761.9	749.8	734.3	715.6	696.9	678.2	659.5	644.3
62.5°	734.7	723.1	711.5	699.9	688.4	673.1	654.1	635.1	616.1	597.1	583.0
65°	643.9	632.1	620.4	608.6	596.8	581.7	563.4	545.0	526.6	508.3	494.4
67.5°	553.8	542.0	530.2	518.5	506.7	492.0	474.4	456.8	439.2	421.6	408.9
70°	492.7	480.9	469.1	457.3	445.6	431.0	413.7	396.4	379.0	361.7	351.0
72.5°	432.8	421.3	409.8	398.3	386.8	372.9	356.7	340.5	324.3	308.1	298.2
75°	343.0	332.6	322.2	311.8	301.4	289.0	274.4	259.9	245.3	230.7	223.1
77.5°	253.8	245.5	237.2	228.9	220.6	210.6	198.9	187.3	175.7	164.0	158.7
80°	202.7	194.4	186.1	177.7	169.4	160.4	150.7	141.0	131.3	121.6	118.5
82.5°	152.8	145.3	137.8	130.3	122.9	115.8	109.1	102.5	95.8	89.2	87.7
85°	85.8	79.5	73.3	67.0	60.8	56.8	55.1	53.4	51.6	49.9	49.5
87.5°	28.9	27.3	25.7	24.1	22.5	21.8	21.8	21.8	21.9	21.9	22.1
90°	1.0	2.8	4.5	6.3	8.1	9.8	11.3	12.9	14.4	16.0	17.1
92.5°	15.4	14.1	12.9	11.6	10.4	10.5	11.8	13.2	14.6	16.0	17.1
95°	56.9	56.2	55.6	54.9	54.3	49.7	41.3	32.8	24.4	16.0	17.1
97.5°	118.8	120.0	121.2	122.4	123.6	115.9	99.2	82.5	65.8	49.1	42.9
100°	166.7	167.4	168.1	168.7	169.4	170.2	171.1	172.0	172.8	173.7	140.7
102.5°	215.5	216.3	217.2	218.0	218.8	219.5	220.1	220.6	221.1	221.7	215.4
105°	293.5	294.4	295.3	296.2	297.1	297.5	297.5	297.5	297.5	297.5	297.5
107.5°	374.6	374.6	374.6	374.6	374.6	374.8	375.3	375.7	376.2	376.6	376.7
110°	427.3	427.3	427.3	427.3	427.3	427.6	428.0	428.5	428.9	429.3	428.7



TEST NUMBER: P333631

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	476.9	477.4	477.9	478.5	479.0	479.4	479.7	479.9	480.2	480.5	479.6
115°	551.2	552.3	553.4	554.5	555.6	556.3	556.5	556.7	556.9	557.1	556.3
117.5°	628.0	628.0	627.9	627.9	627.9	628.3	629.1	629.9	630.8	631.6	630.5
120°	676.0	675.7	675.5	675.3	675.1	675.3	676.0	676.6	677.3	678.0	677.5
122.5°	718.3	719.1	720.0	720.8	721.7	722.2	722.6	722.9	723.2	723.5	723.0
125°	783.8	785.3	786.9	788.5	790.0	790.8	790.8	790.8	790.8	790.8	789.9
127.5°	846.3	847.4	848.5	849.6	850.7	851.2	851.1	851.0	850.8	850.7	850.2
130°	884.6	885.8	886.9	888.0	889.1	889.7	890.0	890.2	890.4	890.6	890.0
132.5°	923.0	924.3	925.6	926.8	928.1	928.5	928.0	927.6	927.1	926.6	926.4
135°	977.5	978.8	980.2	981.5	982.8	983.3	982.8	982.4	981.9	981.5	981.0
137.5°	1027.6	1028.8	1029.9	1031.1	1032.2	1032.6	1032.2	1031.8	1031.4	1031.0	1031.1
140°	1060.4	1060.8	1061.3	1061.7	1062.1	1062.3	1062.0	1061.8	1061.6	1061.4	1061.8
142.5°	1089.9	1090.2	1090.5	1090.7	1091.0	1091.3	1091.6	1091.9	1092.2	1092.5	1092.6
145°	1133.3	1133.7	1134.1	1134.6	1135.0	1135.3	1135.3	1135.3	1135.3	1135.3	1135.5
147.5°	1171.2	1171.1	1171.0	1170.9	1170.8	1170.9	1171.2	1171.5	1171.7	1172.0	1172.3
150°	1195.2	1194.7	1194.3	1193.8	1193.4	1193.4	1193.8	1194.3	1194.7	1195.2	1195.6
152.5°	1218.3	1217.4	1216.4	1215.4	1214.4	1214.2	1214.6	1215.0	1215.5	1215.9	1216.4
155°	1248.1	1246.8	1245.4	1244.1	1242.8	1242.3	1242.8	1243.2	1243.6	1244.1	1244.8
157.5°	1271.0	1270.2	1269.5	1268.7	1267.9	1267.5	1267.5	1267.6	1267.6	1267.7	1268.4
160°	1287.0	1285.7	1284.4	1283.0	1281.7	1281.1	1281.4	1281.6	1281.8	1282.0	1282.9
162.5°	1299.8	1298.5	1297.1	1295.8	1294.5	1293.9	1294.1	1294.4	1294.6	1294.8	1296.1
165°	1317.0	1315.6	1314.3	1313.0	1311.7	1311.1	1311.3	1311.5	1311.8	1312.0	1313.3
167.5°	1329.8	1328.4	1327.0	1325.6	1324.3	1323.7	1323.9	1324.1	1324.3	1324.6	1326.2
170°	1336.9	1335.4	1333.8	1332.3	1330.7	1330.1	1330.3	1330.5	1330.7	1331.0	1332.7
172.5°	1341.7	1340.2	1338.6	1337.1	1335.5	1335.0	1335.3	1335.7	1336.1	1336.5	1338.1
175°	1346.9	1345.6	1344.3	1342.9	1341.6	1341.1	1341.3	1341.5	1341.7	1341.9	1343.7
177.5°	1349.3	1348.3	1347.2	1346.1	1345.1	1344.6	1344.8	1345.0	1345.2	1345.3	1346.6
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9



TEST NUMBER: P333631

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2057.3	2060.1	2062.9	2064.1	2063.9	2063.6	2063.3	2063.0
5°	2044.7	2048.2	2051.6	2053.0	2052.3	2051.6	2050.9	2050.2
7.5°	2019.2	2021.7	2024.1	2024.9	2024.1	2023.4	2022.6	2021.9
10°	1997.7	1998.8	1999.8	1999.8	1998.8	1997.7	1996.7	1995.7
12.5°	1967.3	1968.0	1968.8	1968.4	1966.8	1965.2	1963.6	1962.0
15°	1917.0	1916.7	1916.3	1914.6	1911.5	1908.4	1905.2	1902.1
17.5°	1854.4	1852.6	1850.9	1848.8	1846.2	1843.6	1841.1	1838.5
20°	1808.2	1806.5	1804.8	1802.3	1799.2	1796.1	1793.0	1789.9
22.5°	1762.5	1759.1	1755.7	1752.7	1750.2	1747.6	1745.0	1742.5
25°	1687.3	1682.8	1678.3	1674.1	1670.3	1666.5	1662.7	1658.9
27.5°	1606.1	1599.8	1593.5	1588.5	1584.8	1581.1	1577.4	1573.8
30°	1547.9	1539.9	1531.9	1526.4	1523.3	1520.1	1517.0	1513.9
32.5°	1491.3	1482.5	1473.7	1467.3	1463.4	1459.4	1455.5	1451.5
35°	1403.4	1393.3	1383.3	1375.8	1371.0	1366.1	1361.3	1356.4
37.5°	1311.4	1299.4	1287.3	1278.9	1274.2	1269.5	1264.8	1260.1
40°	1250.6	1237.4	1224.3	1215.6	1211.4	1207.3	1203.1	1199.0
42.5°	1190.6	1178.0	1165.4	1156.0	1149.9	1143.8	1137.7	1131.6
45°	1094.8	1081.0	1067.1	1057.6	1052.4	1047.2	1042.0	1036.8
47.5°	1000.2	985.9	971.6	961.6	955.8	950.1	944.3	938.6
50°	936.0	921.4	906.9	897.0	891.8	886.6	881.4	876.2
52.5°	875.1	859.5	843.8	833.4	828.2	823.0	817.8	812.6
55°	782.7	767.1	751.5	740.9	735.4	729.8	724.3	718.8
57.5°	690.1	674.9	659.6	649.6	644.6	639.7	634.8	629.9
60°	629.0	613.8	598.5	588.3	583.1	577.9	572.7	567.5
62.5°	568.9	554.7	540.6	530.9	525.7	520.5	515.3	510.1
65°	480.6	466.7	452.8	443.3	438.1	432.9	427.7	422.5
67.5°	396.2	383.5	370.9	362.4	358.3	354.1	350.0	345.8
70°	340.2	329.5	318.8	311.3	307.1	303.0	298.8	294.7
72.5°	288.3	278.4	268.4	262.1	259.3	256.6	253.8	251.0
75°	215.5	207.9	200.3	195.2	192.8	190.4	188.0	185.5
77.5°	153.3	148.0	142.7	139.1	137.3	135.5	133.7	131.9
80°	115.4	112.3	109.1	107.2	106.5	105.8	105.2	104.5
82.5°	86.3	84.8	83.4	82.4	82.0	81.6	81.2	80.8
85°	49.2	48.9	48.5	48.2	47.8	47.5	47.1	46.8
87.5°	22.3	22.6	22.8	22.8	22.7	22.5	22.4	22.3
90°	18.2	19.3	20.4	21.3	22.0	22.6	23.3	24.0
92.5°	18.2	19.3	20.4	21.1	21.4	21.7	22.1	22.4
95°	18.2	19.3	20.4	21.0	21.0	21.0	21.0	21.0
97.5°	36.6	30.4	24.1	21.0	21.0	21.0	21.0	21.0
100°	107.6	74.6	41.5	24.5	23.6	22.7	21.9	21.0
102.5°	209.1	202.9	196.6	186.0	170.9	155.8	140.7	125.6
105°	297.5	297.5	297.5	297.4	297.2	297.0	296.8	296.5
107.5°	376.7	376.8	376.8	376.5	375.8	375.2	374.5	373.8
110°	428.0	427.3	426.7	426.5	426.7	426.9	427.1	427.3





TEST NUMBER: P333631

CATALOG NUMBER: S125RDIP-S1270D1035U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	478.8	477.9	477.1	476.5	476.2	475.9	475.6	475.3
115°	555.4	554.5	553.6	552.5	551.2	549.8	548.5	547.2
117.5°	629.3	628.2	627.0	626.1	625.6	625.0	624.4	623.8
120°	677.1	676.6	676.2	675.4	674.3	673.2	672.1	671.0
122.5°	722.6	722.2	721.7	720.8	719.6	718.3	717.0	715.7
125°	789.0	788.1	787.2	786.5	785.8	785.1	784.5	783.8
127.5°	849.7	849.2	848.7	847.7	846.0	844.4	842.8	841.1
130°	889.3	888.6	888.0	887.1	886.0	884.9	883.8	882.6
132.5°	926.3	926.2	926.0	925.4	924.3	923.2	922.1	921.0
135°	980.6	980.2	979.7	978.8	977.5	976.2	974.8	973.5
137.5°	1031.2	1031.3	1031.4	1030.8	1029.7	1028.5	1027.4	1026.2
140°	1062.3	1062.7	1063.1	1062.7	1061.4	1060.0	1058.7	1057.4
142.5°	1092.7	1092.8	1092.9	1092.3	1090.9	1089.6	1088.3	1086.9
145°	1135.7	1135.9	1136.1	1135.6	1134.3	1132.9	1131.6	1130.3
147.5°	1172.5	1172.8	1173.1	1172.4	1170.8	1169.2	1167.6	1166.0
150°	1196.1	1196.5	1196.9	1196.3	1194.5	1192.7	1190.9	1189.2
152.5°	1216.8	1217.3	1217.7	1217.1	1215.5	1213.9	1212.3	1210.7
155°	1245.4	1246.1	1246.8	1246.2	1244.4	1242.6	1240.9	1239.1
157.5°	1269.1	1269.8	1270.5	1270.0	1268.2	1266.4	1264.6	1262.9
160°	1283.8	1284.7	1285.6	1285.1	1283.4	1281.6	1279.8	1278.0
162.5°	1297.3	1298.5	1299.8	1299.4	1297.5	1295.5	1293.6	1291.6
165°	1314.6	1316.0	1317.3	1317.1	1315.3	1313.5	1311.8	1310.0
167.5°	1327.8	1329.4	1331.0	1330.8	1328.8	1326.8	1324.8	1322.8
170°	1334.5	1336.3	1338.1	1337.9	1335.9	1334.0	1332.0	1330.0
172.5°	1339.7	1341.3	1342.9	1342.7	1340.7	1338.7	1336.7	1334.8
175°	1345.5	1347.3	1349.0	1348.9	1346.9	1344.9	1342.9	1340.9
177.5°	1347.8	1349.1	1350.3	1350.2	1348.8	1347.4	1346.0	1344.5
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9

(END OF REPORT)