

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333508

Luminaire Tested: **S125RDIP-S375D1035U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333508
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1035U835-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5597.3 lumens
Efficiency: N/A
Efficacy: 150.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	89	85	82	83	79	76	73	62	60	58	45	44	43	30	30	29	22
2	84	78	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	21	16
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19	14
5	65	54	46	40	58	48	42	37	38	33	30	28	25	23	20	18	16	12
6	59	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	36	28	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	23	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3635	3635	3635	3635
5°	4182	3640	3215	3640
10°	4798	3621	2837	3621
15°	5182	3584	2521	3584
20°	5714	3542	2328	3542
25°	6613	3484	2161	3484
30°	7196	3424	2051	3424
35°	6070	3354	1949	3354
40°	4239	3228	1862	3228
45°	3145	3058	1777	3058
50°	2508	2882	1704	2882
55°	2128	2662	1639	2662
60°	1838	2466	1535	2466
65°	1638	2253	1320	2253
70°	1441	2064	1205	2064
75°	1245	1787	1130	1787
80°	945	1503	945	1503
85°	785	1178	889	1178



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.0
10°-20°	158.2	2.8
20°-30°	250.8	4.5
30°-40°	302.5	5.4
40°-50°	270.1	4.8
50°-60°	207.1	3.7
60°-70°	134.6	2.4
70°-80°	65.4	1.2
80°-90°	18.4	0.3
90°-100°	49.0	0.9
100°-110°	301.7	5.4
110°-120°	547.1	9.8
120°-130°	702.2	12.5
130°-140°	755.2	13.5
140°-150°	708.9	12.7
150°-160°	573.4	10.2
160°-170°	370.9	6.6
170°-180°	127.9	2.3
0°-30°	463.0	8.3
0°-40°	765.4	13.7
0°-60°	1242.7	22.2
0°-90°	1461.1	26.1
90°-120°	897.7	16.0
90°-150°	3064.0	54.7
90°-180°	4136.0	73.9
0°-180°	5597.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	645	562	496	562	645	64
15°	775	536	377	536	775	222
25°	928	489	303	489	928	426
35°	770	425	247	425	770	465
45°	344	335	195	335	344	275
55°	189	236	146	236	189	172
65°	107	147	86	147	107	107
75°	50	72	45	72	50	53
85°	11	16	12	16	11	13
90°	24	1	24	1	24	11
95°	21	57	21	57	21	17
105°	296	294	296	294	296	268
115°	547	551	547	551	547	543
125°	784	784	784	784	784	697
135°	974	978	974	978	974	751
145°	1130	1133	1130	1133	1130	706
155°	1239	1248	1239	1248	1239	571
165°	1310	1317	1310	1317	1310	370
175°	1341	1347	1341	1347	1341	128
180°	1347	1347	1347	1347	1347	



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	592.1	591.7	592.5	590.4	590.6	587.5	587.5	585.1	581.9	579.5	578.4
5°	645.1	645.6	644.7	641.2	638.9	635.4	631.5	624.6	618.8	613.2	608.9
7.5°	699.8	700.1	697.0	696.0	690.1	685.9	677.2	667.7	659.4	648.7	640.6
10°	731.6	731.3	728.1	725.5	720.5	714.0	705.4	694.4	684.0	672.4	661.3
12.5°	750.0	749.4	748.4	745.3	740.6	734.9	727.6	716.7	703.9	691.3	678.3
15°	775.0	773.4	770.4	766.4	759.7	753.0	745.0	735.3	723.0	708.7	696.7
17.5°	805.9	805.9	801.3	795.8	786.7	774.9	762.4	746.8	730.1	714.4	701.6
20°	831.4	830.7	826.1	815.4	805.0	790.2	775.9	756.7	736.4	715.8	699.9
22.5°	868.0	866.2	861.4	847.4	831.3	812.2	790.3	766.9	742.3	719.0	698.0
25°	928.0	926.6	917.1	900.9	878.3	848.9	820.3	788.2	752.8	722.1	696.7
27.5°	969.0	967.5	960.4	947.0	926.1	895.2	856.5	813.5	769.4	727.1	690.5
30°	964.9	968.4	967.5	961.2	945.5	917.8	882.0	833.7	781.2	731.6	687.9
32.5°	906.9	910.0	918.1	930.4	931.3	920.2	893.4	848.8	794.5	738.0	685.8
35°	769.9	774.1	789.8	814.5	846.9	873.9	879.4	855.4	806.6	745.9	682.8
37.5°	591.9	614.6	627.9	653.9	702.8	752.5	800.3	817.9	797.2	742.6	677.9
40°	502.8	508.3	531.9	561.3	602.4	654.1	722.3	771.5	773.1	735.3	670.1
42.5°	430.3	437.4	453.5	477.0	512.2	563.9	634.3	699.3	729.3	714.9	659.9
45°	344.3	349.6	361.4	379.4	406.4	449.2	509.7	584.8	644.4	667.8	632.7
47.5°	282.8	285.7	295.9	309.7	329.7	360.8	407.7	472.9	544.4	594.5	589.6
50°	249.6	252.8	260.6	271.0	287.9	314.2	351.7	406.0	479.7	540.9	553.2
52.5°	223.7	226.4	231.3	241.1	255.0	275.2	305.5	354.6	420.9	486.0	514.4
55°	189.0	190.9	194.8	200.3	211.4	226.0	252.1	286.1	339.7	405.3	446.9
57.5°	160.5	161.4	163.9	169.0	176.7	187.3	206.2	234.9	273.4	332.5	378.4
60°	142.3	143.3	146.5	150.0	156.0	165.7	180.5	200.6	237.5	286.3	332.7
62.5°	127.9	128.5	129.9	133.3	138.6	146.1	157.7	174.1	203.5	246.4	290.2
65°	107.2	107.4	107.9	110.7	113.9	119.5	127.1	138.6	160.8	193.2	232.0
67.5°	87.3	87.7	89.3	90.3	93.6	96.5	101.0	109.8	125.5	147.3	177.5
70°	76.3	76.0	77.6	78.8	79.9	83.4	86.4	93.6	103.3	119.9	145.1
72.5°	65.9	65.3	66.0	66.4	67.9	70.3	73.3	77.7	85.2	96.6	115.9
75°	49.9	50.1	50.1	50.6	51.8	52.7	53.6	55.9	60.1	67.7	78.1
77.5°	35.0	34.7	35.6	35.8	36.5	37.5	38.3	39.2	40.9	44.0	49.4
80°	25.4	25.4	25.6	26.3	26.1	26.6	27.7	28.7	30.7	32.6	34.4
82.5°	19.5	19.3	19.5	19.7	19.6	20.1	20.5	20.7	21.5	22.4	23.7
85°	10.6	10.6	10.9	10.9	11.1	11.1	11.3	11.3	11.3	11.6	11.8
87.5°	8.9	8.5	8.2	8.1	8.1	8.3	7.9	7.5	7.3	7.1	7.0
90°	24.0	23.3	22.6	22.0	21.3	20.4	19.3	18.2	17.1	16.0	14.4
92.5°	22.4	22.1	21.7	21.4	21.1	20.4	19.3	18.2	17.1	16.0	14.6
95°	21.0	21.0	21.0	21.0	21.0	20.4	19.3	18.2	17.1	16.0	24.4
97.5°	21.0	21.0	21.0	21.0	21.0	24.1	30.4	36.6	42.9	49.1	65.8
100°	21.0	21.9	22.7	23.6	24.5	41.5	74.6	107.6	140.7	173.7	172.8
102.5°	125.6	140.7	155.8	170.9	186.0	196.6	202.9	209.1	215.4	221.7	221.1
105°	296.5	296.8	297.0	297.2	297.4	297.5	297.5	297.5	297.5	297.5	297.5
107.5°	373.8	374.5	375.2	375.8	376.5	376.8	376.8	376.7	376.7	376.6	376.2
110°	427.3	427.1	426.9	426.7	426.5	426.7	427.3	428.0	428.7	429.3	428.9



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	475.3	475.6	475.9	476.2	476.5	477.1	477.9	478.8	479.6	480.5	480.2
115°	547.2	548.5	549.8	551.2	552.5	553.6	554.5	555.4	556.3	557.1	556.9
117.5°	623.8	624.4	625.0	625.6	626.1	627.0	628.2	629.3	630.5	631.6	630.8
120°	671.0	672.1	673.2	674.3	675.4	676.2	676.6	677.1	677.5	678.0	677.3
122.5°	715.7	717.0	718.3	719.6	720.8	721.7	722.2	722.6	723.0	723.5	723.2
125°	783.8	784.5	785.1	785.8	786.5	787.2	788.1	789.0	789.9	790.8	790.8
127.5°	841.1	842.8	844.4	846.0	847.7	848.7	849.2	849.7	850.2	850.7	850.8
130°	882.6	883.8	884.9	886.0	887.1	888.0	888.6	889.3	890.0	890.6	890.4
132.5°	921.0	922.1	923.2	924.3	925.4	926.0	926.2	926.3	926.4	926.6	927.1
135°	973.5	974.8	976.2	977.5	978.8	979.7	980.2	980.6	981.0	981.5	981.9
137.5°	1026.2	1027.4	1028.5	1029.7	1030.8	1031.4	1031.3	1031.2	1031.1	1031.0	1031.4
140°	1057.4	1058.7	1060.0	1061.4	1062.7	1063.1	1062.7	1062.3	1061.8	1061.4	1061.6
142.5°	1086.9	1088.3	1089.6	1090.9	1092.3	1092.9	1092.8	1092.7	1092.6	1092.5	1092.2
145°	1130.3	1131.6	1132.9	1134.3	1135.6	1136.1	1135.9	1135.7	1135.5	1135.3	1135.3
147.5°	1166.0	1167.6	1169.2	1170.8	1172.4	1173.1	1172.8	1172.5	1172.3	1172.0	1171.7
150°	1189.2	1190.9	1192.7	1194.5	1196.3	1196.9	1196.5	1196.1	1195.6	1195.2	1194.7
152.5°	1210.7	1212.3	1213.9	1215.5	1217.1	1217.7	1217.3	1216.8	1216.4	1215.9	1215.5
155°	1239.1	1240.9	1242.6	1244.4	1246.2	1246.8	1246.1	1245.4	1244.8	1244.1	1243.6
157.5°	1262.9	1264.6	1266.4	1268.2	1270.0	1270.5	1269.8	1269.1	1268.4	1267.7	1267.6
160°	1278.0	1279.8	1281.6	1283.4	1285.1	1285.6	1284.7	1283.8	1282.9	1282.0	1281.8
162.5°	1291.6	1293.6	1295.5	1297.5	1299.4	1299.8	1298.5	1297.3	1296.1	1294.8	1294.6
165°	1310.0	1311.8	1313.5	1315.3	1317.1	1317.3	1316.0	1314.6	1313.3	1312.0	1311.8
167.5°	1322.8	1324.8	1326.8	1328.8	1330.8	1331.0	1329.4	1327.8	1326.2	1324.6	1324.3
170°	1330.0	1332.0	1334.0	1335.9	1337.9	1338.1	1336.3	1334.5	1332.7	1331.0	1330.7
172.5°	1334.8	1336.7	1338.7	1340.7	1342.7	1342.9	1341.3	1339.7	1338.1	1336.5	1336.1
175°	1340.9	1342.9	1344.9	1346.9	1348.9	1349.0	1347.3	1345.5	1343.7	1341.9	1341.7
177.5°	1344.5	1346.0	1347.4	1348.8	1350.2	1350.3	1349.1	1347.8	1346.6	1345.3	1345.2
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	578.4	577.1	574.7	572.5	569.7	567.3	565.6	563.6	561.0	557.9	555.3
5°	604.0	598.9	592.2	586.4	579.0	573.3	567.3	561.5	555.7	548.3	541.8
7.5°	632.4	621.9	611.7	598.8	587.2	576.8	566.8	556.7	546.8	536.3	526.2
10°	649.8	637.0	623.0	606.8	592.0	577.9	565.0	552.2	538.8	527.1	514.4
12.5°	666.0	649.6	633.5	613.1	595.3	578.1	561.6	545.8	531.5	516.2	502.5
15°	680.7	664.5	646.5	621.6	596.8	576.0	556.6	536.1	518.3	501.2	485.9
17.5°	686.4	669.4	648.5	624.5	597.5	571.3	546.3	523.8	502.8	482.9	465.8
20°	684.2	667.8	646.3	623.4	594.5	567.3	540.2	515.3	491.9	470.9	452.7
22.5°	678.8	661.9	641.1	616.9	589.5	560.6	531.7	505.1	480.7	458.9	439.0
25°	670.8	647.7	626.4	602.8	576.7	548.1	518.3	488.9	462.8	440.6	418.9
27.5°	662.4	633.6	606.5	583.1	555.5	530.0	501.2	471.1	443.7	421.1	398.8
30°	654.8	622.5	592.7	566.1	540.0	515.7	488.5	459.1	430.9	407.6	385.0
32.5°	645.4	611.0	578.3	547.6	522.4	498.4	473.7	445.6	418.2	394.1	371.1
35°	633.6	589.7	554.1	521.5	493.6	470.2	448.0	425.4	397.9	372.9	350.5
37.5°	618.1	568.2	527.1	491.6	462.1	438.7	421.1	400.4	375.3	351.5	330.7
40°	608.6	552.7	507.7	472.5	441.6	416.8	400.4	382.9	360.0	337.6	316.8
42.5°	596.1	538.5	488.1	451.5	420.3	396.5	379.9	364.6	345.4	324.3	302.0
45°	571.4	510.9	458.0	418.7	387.3	363.9	348.4	334.8	320.3	300.8	281.4
47.5°	539.4	482.1	426.7	383.8	353.1	331.4	316.4	305.6	295.2	278.7	259.9
50°	513.7	458.4	404.4	362.8	330.0	309.4	295.3	286.8	277.3	262.3	246.5
52.5°	483.3	434.0	381.1	338.6	307.6	288.3	274.8	266.2	258.4	246.2	231.2
55°	435.6	392.3	343.8	305.2	276.8	257.4	244.5	236.4	231.8	221.4	209.6
57.5°	380.4	349.5	306.7	269.5	244.3	225.2	215.7	208.8	203.6	196.2	187.9
60°	342.0	320.3	281.9	246.5	223.4	205.2	196.6	190.9	186.0	179.8	173.3
62.5°	303.0	287.2	253.8	223.4	202.2	186.9	178.9	173.7	168.1	163.9	157.6
65°	250.7	236.6	213.5	189.7	170.1	157.8	152.0	147.4	144.0	139.3	134.9
67.5°	195.0	189.3	173.3	156.9	142.8	131.9	126.9	123.7	119.6	116.8	113.8
70°	160.8	158.0	146.7	135.9	122.7	115.3	110.7	109.3	104.2	101.4	99.4
72.5°	130.5	129.2	122.7	115.2	105.9	99.4	95.2	93.6	90.3	88.1	86.8
75°	89.4	89.9	88.7	83.9	80.4	76.3	72.6	71.6	69.3	67.5	66.3
77.5°	56.6	58.9	59.0	58.8	57.4	54.9	53.3	52.6	50.4	49.7	49.4
80°	38.8	41.4	43.7	43.4	43.0	42.3	41.1	40.4	39.3	38.6	38.1
82.5°	25.9	28.2	30.2	31.4	31.3	30.6	29.9	29.5	29.3	28.8	28.7
85°	12.2	12.7	13.4	15.0	16.2	16.4	16.2	15.9	15.3	15.5	15.7
87.5°	6.8	6.5	6.4	6.1	5.5	6.1	6.3	6.1	6.1	6.1	6.1
90°	12.9	11.3	9.8	8.1	6.3	4.5	2.8	1.0	2.8	4.5	6.3
92.5°	13.2	11.8	10.5	10.4	11.6	12.9	14.1	15.4	14.1	12.9	11.6
95°	32.8	41.3	49.7	54.3	54.9	55.6	56.2	56.9	56.2	55.6	54.9
97.5°	82.5	99.2	115.9	123.6	122.4	121.2	120.0	118.8	120.0	121.2	122.4
100°	172.0	171.1	170.2	169.4	168.7	168.1	167.4	166.7	167.4	168.1	168.7
102.5°	220.6	220.1	219.5	218.8	218.0	217.2	216.3	215.5	216.3	217.2	218.0
105°	297.5	297.5	297.5	297.1	296.2	295.3	294.4	293.5	294.4	295.3	296.2
107.5°	375.7	375.3	374.8	374.6	374.6	374.6	374.6	374.6	374.6	374.6	374.6
110°	428.5	428.0	427.6	427.3	427.3	427.3	427.3	427.3	427.3	427.3	427.3



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	479.9	479.7	479.4	479.0	478.5	477.9	477.4	476.9	477.4	477.9	478.5
115°	556.7	556.5	556.3	555.6	554.5	553.4	552.3	551.2	552.3	553.4	554.5
117.5°	629.9	629.1	628.3	627.9	627.9	627.9	628.0	628.0	628.0	627.9	627.9
120°	676.6	676.0	675.3	675.1	675.3	675.5	675.7	676.0	675.7	675.5	675.3
122.5°	722.9	722.6	722.2	721.7	720.8	720.0	719.1	718.3	719.1	720.0	720.8
125°	790.8	790.8	790.8	790.0	788.5	786.9	785.3	783.8	785.3	786.9	788.5
127.5°	851.0	851.1	851.2	850.7	849.6	848.5	847.4	846.3	847.4	848.5	849.6
130°	890.2	890.0	889.7	889.1	888.0	886.9	885.8	884.6	885.8	886.9	888.0
132.5°	927.6	928.0	928.5	928.1	926.8	925.6	924.3	923.0	924.3	925.6	926.8
135°	982.4	982.8	983.3	982.8	981.5	980.2	978.8	977.5	978.8	980.2	981.5
137.5°	1031.8	1032.2	1032.6	1032.2	1031.1	1029.9	1028.8	1027.6	1028.8	1029.9	1031.1
140°	1061.8	1062.0	1062.3	1062.1	1061.7	1061.3	1060.8	1060.4	1060.8	1061.3	1061.7
142.5°	1091.9	1091.6	1091.3	1091.0	1090.7	1090.5	1090.2	1089.9	1090.2	1090.5	1090.7
145°	1135.3	1135.3	1135.3	1135.0	1134.6	1134.1	1133.7	1133.3	1133.7	1134.1	1134.6
147.5°	1171.5	1171.2	1170.9	1170.8	1170.9	1171.0	1171.1	1171.2	1171.1	1171.0	1170.9
150°	1194.3	1193.8	1193.4	1193.4	1193.8	1194.3	1194.7	1195.2	1194.7	1194.3	1193.8
152.5°	1215.0	1214.6	1214.2	1214.4	1215.4	1216.4	1217.4	1218.3	1217.4	1216.4	1215.4
155°	1243.2	1242.8	1242.3	1242.8	1244.1	1245.4	1246.8	1248.1	1246.8	1245.4	1244.1
157.5°	1267.6	1267.5	1267.5	1267.9	1268.7	1269.5	1270.2	1271.0	1270.2	1269.5	1268.7
160°	1281.6	1281.4	1281.1	1281.7	1283.0	1284.4	1285.7	1287.0	1285.7	1284.4	1283.0
162.5°	1294.4	1294.1	1293.9	1294.5	1295.8	1297.1	1298.5	1299.8	1298.5	1297.1	1295.8
165°	1311.5	1311.3	1311.1	1311.7	1313.0	1314.3	1315.6	1317.0	1315.6	1314.3	1313.0
167.5°	1324.1	1323.9	1323.7	1324.3	1325.6	1327.0	1328.4	1329.8	1328.4	1327.0	1325.6
170°	1330.5	1330.3	1330.1	1330.7	1332.3	1333.8	1335.4	1336.9	1335.4	1333.8	1332.3
172.5°	1335.7	1335.3	1335.0	1335.5	1337.1	1338.6	1340.2	1341.7	1340.2	1338.6	1337.1
175°	1341.5	1341.3	1341.1	1341.6	1342.9	1344.3	1345.6	1346.9	1345.6	1344.3	1342.9
177.5°	1345.0	1344.8	1344.6	1345.1	1346.1	1347.2	1348.3	1349.3	1348.3	1347.2	1346.1
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	553.4	550.9	549.0	545.3	542.7	541.6	539.6	539.0	541.1	539.6	539.4
5°	537.0	530.3	525.0	519.7	513.9	510.2	504.6	503.7	502.3	500.3	499.8
7.5°	517.3	508.5	501.7	492.9	485.3	479.1	472.2	468.9	467.1	464.4	460.8
10°	504.0	493.6	484.3	475.5	466.1	458.4	451.5	446.2	442.7	439.5	438.1
12.5°	490.8	480.2	468.4	457.8	447.2	438.7	431.0	427.5	423.7	419.9	416.7
15°	470.4	456.4	443.4	431.2	422.2	412.9	405.5	400.4	394.7	393.0	386.8
17.5°	448.8	435.0	419.8	407.0	396.5	386.3	378.2	372.4	368.1	362.1	359.3
20°	435.3	418.9	404.1	392.3	380.8	368.8	360.5	355.6	351.5	346.6	344.3
22.5°	420.9	404.9	389.7	375.9	364.2	352.3	346.4	341.4	336.7	332.2	329.1
25°	399.7	383.6	367.6	353.3	341.1	332.5	325.6	319.8	317.3	312.9	309.6
27.5°	378.8	361.6	345.1	330.8	321.2	312.7	307.0	302.5	297.9	294.1	291.2
30°	365.3	347.8	329.7	318.4	308.2	300.2	293.9	289.5	286.1	282.6	280.5
32.5°	351.8	333.7	317.7	305.5	295.9	288.9	282.5	278.2	274.6	270.8	268.3
35°	330.2	311.7	298.8	286.8	277.3	270.8	266.4	260.4	257.4	254.6	252.1
37.5°	310.1	292.9	278.9	268.4	260.1	253.7	248.0	244.8	241.1	238.6	236.5
40°	295.3	279.6	266.9	255.8	249.8	242.6	237.3	233.1	230.4	227.1	224.8
42.5°	282.0	267.4	255.0	245.1	237.6	231.5	226.4	222.2	218.7	216.4	214.5
45°	263.2	248.6	236.6	227.4	220.4	214.7	209.3	207.3	202.6	199.9	198.9
47.5°	243.7	230.7	219.1	210.6	203.5	198.0	193.0	188.8	186.2	183.5	182.0
50°	230.6	218.1	207.3	198.9	192.0	186.0	181.4	178.6	175.1	172.6	170.8
52.5°	217.5	205.9	195.1	187.1	181.1	175.1	169.9	167.2	163.9	162.3	161.0
55°	198.7	186.5	177.2	169.4	163.1	157.6	152.7	150.0	147.9	146.3	145.8
57.5°	177.5	167.8	159.2	152.1	145.6	140.4	136.1	133.5	131.7	131.4	130.0
60°	163.6	154.8	147.0	139.3	133.8	128.9	125.2	122.2	120.4	120.2	119.7
62.5°	149.7	141.3	134.0	127.3	122.3	117.7	114.1	110.8	109.7	108.5	107.5
65°	129.2	121.5	115.5	110.2	104.9	101.0	97.5	95.4	92.9	91.5	89.0
67.5°	109.0	103.1	97.3	92.8	88.6	84.9	82.0	78.9	77.2	76.1	74.3
70°	95.7	91.0	85.3	80.4	77.2	74.2	71.9	68.4	67.2	66.3	65.4
72.5°	83.1	79.0	74.2	70.2	67.0	64.2	61.5	59.9	58.7	57.8	57.3
75°	65.4	61.5	57.3	54.5	52.2	49.9	48.5	47.4	46.9	46.7	45.8
77.5°	48.0	45.9	42.6	40.4	38.9	37.9	36.7	36.1	36.0	35.0	34.7
80°	36.7	35.6	32.8	31.9	30.7	29.8	29.1	28.0	26.8	26.3	25.6
82.5°	27.3	26.2	25.0	23.6	22.6	22.0	21.4	20.9	21.1	20.4	20.1
85°	14.6	13.4	12.9	12.7	12.2	12.7	12.5	12.2	12.0	11.8	12.0
87.5°	6.2	6.6	6.7	7.4	7.1	7.6	7.9	7.9	8.1	8.3	8.3
90°	8.1	9.8	11.3	12.9	14.4	16.0	17.1	18.2	19.3	20.4	21.3
92.5°	10.4	10.5	11.8	13.2	14.6	16.0	17.1	18.2	19.3	20.4	21.1
95°	54.3	49.7	41.3	32.8	24.4	16.0	17.1	18.2	19.3	20.4	21.0
97.5°	123.6	115.9	99.2	82.5	65.8	49.1	42.9	36.6	30.4	24.1	21.0
100°	169.4	170.2	171.1	172.0	172.8	173.7	140.7	107.6	74.6	41.5	24.5
102.5°	218.8	219.5	220.1	220.6	221.1	221.7	215.4	209.1	202.9	196.6	186.0
105°	297.1	297.5	297.5	297.5	297.5	297.5	297.5	297.5	297.5	297.5	297.4
107.5°	374.6	374.8	375.3	375.7	376.2	376.6	376.7	376.7	376.8	376.8	376.5
110°	427.3	427.6	428.0	428.5	428.9	429.3	428.7	428.0	427.3	426.7	426.5



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	479.0	479.4	479.7	479.9	480.2	480.5	479.6	478.8	477.9	477.1	476.5
115°	555.6	556.3	556.5	556.7	556.9	557.1	556.3	555.4	554.5	553.6	552.5
117.5°	627.9	628.3	629.1	629.9	630.8	631.6	630.5	629.3	628.2	627.0	626.1
120°	675.1	675.3	676.0	676.6	677.3	678.0	677.5	677.1	676.6	676.2	675.4
122.5°	721.7	722.2	722.6	722.9	723.2	723.5	723.0	722.6	722.2	721.7	720.8
125°	790.0	790.8	790.8	790.8	790.8	790.8	789.9	789.0	788.1	787.2	786.5
127.5°	850.7	851.2	851.1	851.0	850.8	850.7	850.2	849.7	849.2	848.7	847.7
130°	889.1	889.7	890.0	890.2	890.4	890.6	890.0	889.3	888.6	888.0	887.1
132.5°	928.1	928.5	928.0	927.6	927.1	926.6	926.4	926.3	926.2	926.0	925.4
135°	982.8	983.3	982.8	982.4	981.9	981.5	981.0	980.6	980.2	979.7	978.8
137.5°	1032.2	1032.6	1032.2	1031.8	1031.4	1031.0	1031.1	1031.2	1031.3	1031.4	1030.8
140°	1062.1	1062.3	1062.0	1061.8	1061.6	1061.4	1061.8	1062.3	1062.7	1063.1	1062.7
142.5°	1091.0	1091.3	1091.6	1091.9	1092.2	1092.5	1092.6	1092.7	1092.8	1092.9	1092.3
145°	1135.0	1135.3	1135.3	1135.3	1135.3	1135.3	1135.5	1135.7	1135.9	1136.1	1135.6
147.5°	1170.8	1170.9	1171.2	1171.5	1171.7	1172.0	1172.3	1172.5	1172.8	1173.1	1172.4
150°	1193.4	1193.4	1193.8	1194.3	1194.7	1195.2	1195.6	1196.1	1196.5	1196.9	1196.3
152.5°	1214.4	1214.2	1214.6	1215.0	1215.5	1215.9	1216.4	1216.8	1217.3	1217.7	1217.1
155°	1242.8	1242.3	1242.8	1243.2	1243.6	1244.1	1244.8	1245.4	1246.1	1246.8	1246.2
157.5°	1267.9	1267.5	1267.5	1267.6	1267.6	1267.7	1268.4	1269.1	1269.8	1270.5	1270.0
160°	1281.7	1281.1	1281.4	1281.6	1281.8	1282.0	1282.9	1283.8	1284.7	1285.6	1285.1
162.5°	1294.5	1293.9	1294.1	1294.4	1294.6	1294.8	1296.1	1297.3	1298.5	1299.8	1299.4
165°	1311.7	1311.1	1311.3	1311.5	1311.8	1312.0	1313.3	1314.6	1316.0	1317.3	1317.1
167.5°	1324.3	1323.7	1323.9	1324.1	1324.3	1324.6	1326.2	1327.8	1329.4	1331.0	1330.8
170°	1330.7	1330.1	1330.3	1330.5	1330.7	1331.0	1332.7	1334.5	1336.3	1338.1	1337.9
172.5°	1335.5	1335.0	1335.3	1335.7	1336.1	1336.5	1338.1	1339.7	1341.3	1342.9	1342.7
175°	1341.6	1341.1	1341.3	1341.5	1341.7	1341.9	1343.7	1345.5	1347.3	1349.0	1348.9
177.5°	1345.1	1344.6	1344.8	1345.0	1345.2	1345.3	1346.6	1347.8	1349.1	1350.3	1350.2
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.2	537.2	536.6	537.4	536.6	537.2	539.2	539.4	539.6	541.1	539.0
5°	497.5	495.2	496.3	495.9	496.3	495.2	497.5	499.8	500.3	502.3	503.7
7.5°	460.8	457.9	454.9	455.8	454.9	457.9	460.8	460.8	464.4	467.1	468.9
10°	435.1	432.8	431.4	432.6	431.4	432.8	435.1	438.1	439.5	442.7	446.2
12.5°	413.5	412.1	410.9	410.4	410.9	412.1	413.5	416.7	419.9	423.7	427.5
15°	384.0	381.3	380.1	377.1	380.1	381.3	384.0	386.8	393.0	394.7	400.4
17.5°	356.9	356.0	353.0	351.7	353.0	356.0	356.9	359.3	362.1	368.1	372.4
20°	340.8	339.9	336.9	338.7	336.9	339.9	340.8	344.3	346.6	351.5	355.6
22.5°	327.5	325.5	324.5	324.0	324.5	325.5	327.5	329.1	332.2	336.7	341.4
25°	308.7	305.7	304.5	303.2	304.5	305.7	308.7	309.6	312.9	317.3	319.8
27.5°	289.9	288.3	286.8	286.4	286.8	288.3	289.9	291.2	294.1	297.9	302.5
30°	277.7	276.1	275.0	275.0	275.0	276.1	277.7	280.5	282.6	286.1	289.5
32.5°	266.8	265.6	264.4	264.2	264.4	265.6	266.8	268.3	270.8	274.6	278.2
35°	250.9	249.1	248.6	247.2	248.6	249.1	250.9	252.1	254.6	257.4	260.4
37.5°	234.4	232.9	232.9	232.7	232.9	232.9	234.4	236.5	238.6	241.1	244.8
40°	223.9	222.7	222.5	220.9	222.5	222.7	223.9	224.8	227.1	230.4	233.1
42.5°	212.6	212.0	211.2	210.5	211.2	212.0	212.6	214.5	216.4	218.7	222.2
45°	197.3	195.7	195.7	194.6	195.7	195.7	197.3	198.9	199.9	202.6	207.3
47.5°	181.5	180.3	180.4	179.2	180.4	180.3	181.5	182.0	183.5	186.2	188.8
50°	171.0	170.3	170.1	169.6	170.1	170.3	171.0	170.8	172.6	175.1	178.6
52.5°	160.5	160.1	161.0	160.0	161.0	160.1	160.5	161.0	162.3	163.9	167.2
55°	146.3	145.6	147.0	145.6	147.0	145.6	146.3	145.8	146.3	147.9	150.0
57.5°	130.0	129.3	130.6	129.9	130.6	129.3	130.0	130.0	131.4	131.7	133.5
60°	119.2	117.8	118.5	118.8	118.5	117.8	119.2	119.7	120.2	120.4	122.2
62.5°	106.5	105.6	106.2	105.1	106.2	105.6	106.5	107.5	108.5	109.7	110.8
65°	88.5	87.8	86.9	86.4	86.9	87.8	88.5	89.0	91.5	92.9	95.4
67.5°	74.4	72.7	72.6	73.0	72.6	72.7	74.4	74.3	76.1	77.2	78.9
70°	64.0	64.0	63.8	63.8	63.8	64.0	64.0	65.4	66.3	67.2	68.4
72.5°	56.8	56.6	56.2	56.0	56.2	56.6	56.8	57.3	57.8	58.7	59.9
75°	45.8	46.0	45.5	45.3	45.5	46.0	45.8	45.8	46.7	46.9	47.4
77.5°	33.8	32.8	33.3	32.8	33.3	32.8	33.8	34.7	35.0	36.0	36.1
80°	25.6	25.4	26.1	25.4	26.1	25.4	25.6	25.6	26.3	26.8	28.0
82.5°	20.3	20.1	20.4	19.9	20.4	20.1	20.3	20.1	20.4	21.1	20.9
85°	12.2	12.0	11.8	12.0	11.8	12.0	12.2	12.0	11.8	12.0	12.2
87.5°	8.6	8.6	8.7	8.9	8.7	8.6	8.6	8.3	8.3	8.1	7.9
90°	22.0	22.6	23.3	24.0	23.3	22.6	22.0	21.3	20.4	19.3	18.2
92.5°	21.4	21.7	22.1	22.4	22.1	21.7	21.4	21.1	20.4	19.3	18.2
95°	21.0	21.0	21.0	21.0	21.0	21.0	21.0	21.0	20.4	19.3	18.2
97.5°	21.0	21.0	21.0	21.0	21.0	21.0	21.0	21.0	24.1	30.4	36.6
100°	23.6	22.7	21.9	21.0	21.9	22.7	23.6	24.5	41.5	74.6	107.6
102.5°	170.9	155.8	140.7	125.6	140.7	155.8	170.9	186.0	196.6	202.9	209.1
105°	297.2	297.0	296.8	296.5	296.8	297.0	297.2	297.4	297.5	297.5	297.5
107.5°	375.8	375.2	374.5	373.8	374.5	375.2	375.8	376.5	376.8	376.8	376.7
110°	426.7	426.9	427.1	427.3	427.1	426.9	426.7	426.5	426.7	427.3	428.0



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	476.2	475.9	475.6	475.3	475.6	475.9	476.2	476.5	477.1	477.9	478.8
115°	551.2	549.8	548.5	547.2	548.5	549.8	551.2	552.5	553.6	554.5	555.4
117.5°	625.6	625.0	624.4	623.8	624.4	625.0	625.6	626.1	627.0	628.2	629.3
120°	674.3	673.2	672.1	671.0	672.1	673.2	674.3	675.4	676.2	676.6	677.1
122.5°	719.6	718.3	717.0	715.7	717.0	718.3	719.6	720.8	721.7	722.2	722.6
125°	785.8	785.1	784.5	783.8	784.5	785.1	785.8	786.5	787.2	788.1	789.0
127.5°	846.0	844.4	842.8	841.1	842.8	844.4	846.0	847.7	848.7	849.2	849.7
130°	886.0	884.9	883.8	882.6	883.8	884.9	886.0	887.1	888.0	888.6	889.3
132.5°	924.3	923.2	922.1	921.0	922.1	923.2	924.3	925.4	926.0	926.2	926.3
135°	977.5	976.2	974.8	973.5	974.8	976.2	977.5	978.8	979.7	980.2	980.6
137.5°	1029.7	1028.5	1027.4	1026.2	1027.4	1028.5	1029.7	1030.8	1031.4	1031.3	1031.2
140°	1061.4	1060.0	1058.7	1057.4	1058.7	1060.0	1061.4	1062.7	1063.1	1062.7	1062.3
142.5°	1090.9	1089.6	1088.3	1086.9	1088.3	1089.6	1090.9	1092.3	1092.9	1092.8	1092.7
145°	1134.3	1132.9	1131.6	1130.3	1131.6	1132.9	1134.3	1135.6	1136.1	1135.9	1135.7
147.5°	1170.8	1169.2	1167.6	1166.0	1167.6	1169.2	1170.8	1172.4	1173.1	1172.8	1172.5
150°	1194.5	1192.7	1190.9	1189.2	1190.9	1192.7	1194.5	1196.3	1196.9	1196.5	1196.1
152.5°	1215.5	1213.9	1212.3	1210.7	1212.3	1213.9	1215.5	1217.1	1217.7	1217.3	1216.8
155°	1244.4	1242.6	1240.9	1239.1	1240.9	1242.6	1244.4	1246.2	1246.8	1246.1	1245.4
157.5°	1268.2	1266.4	1264.6	1262.9	1264.6	1266.4	1268.2	1270.0	1270.5	1269.8	1269.1
160°	1283.4	1281.6	1279.8	1278.0	1279.8	1281.6	1283.4	1285.1	1285.6	1284.7	1283.8
162.5°	1297.5	1295.5	1293.6	1291.6	1293.6	1295.5	1297.5	1299.4	1299.8	1298.5	1297.3
165°	1315.3	1313.5	1311.8	1310.0	1311.8	1313.5	1315.3	1317.1	1317.3	1316.0	1314.6
167.5°	1328.8	1326.8	1324.8	1322.8	1324.8	1326.8	1328.8	1330.8	1331.0	1329.4	1327.8
170°	1335.9	1334.0	1332.0	1330.0	1332.0	1334.0	1335.9	1337.9	1338.1	1336.3	1334.5
172.5°	1340.7	1338.7	1336.7	1334.8	1336.7	1338.7	1340.7	1342.7	1342.9	1341.3	1339.7
175°	1346.9	1344.9	1342.9	1340.9	1342.9	1344.9	1346.9	1348.9	1349.0	1347.3	1345.5
177.5°	1348.8	1347.4	1346.0	1344.5	1346.0	1347.4	1348.8	1350.2	1350.3	1349.1	1347.8
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.6	541.6	542.7	545.3	549.0	550.9	553.4	555.3	557.9	561.0	563.6
5°	504.6	510.2	513.9	519.7	525.0	530.3	537.0	541.8	548.3	555.7	561.5
7.5°	472.2	479.1	485.3	492.9	501.7	508.5	517.3	526.2	536.3	546.8	556.7
10°	451.5	458.4	466.1	475.5	484.3	493.6	504.0	514.4	527.1	538.8	552.2
12.5°	431.0	438.7	447.2	457.8	468.4	480.2	490.8	502.5	516.2	531.5	545.8
15°	405.5	412.9	422.2	431.2	443.4	456.4	470.4	485.9	501.2	518.3	536.1
17.5°	378.2	386.3	396.5	407.0	419.8	435.0	448.8	465.8	482.9	502.8	523.8
20°	360.5	368.8	380.8	392.3	404.1	418.9	435.3	452.7	470.9	491.9	515.3
22.5°	346.4	352.3	364.2	375.9	389.7	404.9	420.9	439.0	458.9	480.7	505.1
25°	325.6	332.5	341.1	353.3	367.6	383.6	399.7	418.9	440.6	462.8	488.9
27.5°	307.0	312.7	321.2	330.8	345.1	361.6	378.8	398.8	421.1	443.7	471.1
30°	293.9	300.2	308.2	318.4	329.7	347.8	365.3	385.0	407.6	430.9	459.1
32.5°	282.5	288.9	295.9	305.5	317.7	333.7	351.8	371.1	394.1	418.2	445.6
35°	266.4	270.8	277.3	286.8	298.8	311.7	330.2	350.5	372.9	397.9	425.4
37.5°	248.0	253.7	260.1	268.4	278.9	292.9	310.1	330.7	351.5	375.3	400.4
40°	237.3	242.6	249.8	255.8	266.9	279.6	295.3	316.8	337.6	360.0	382.9
42.5°	226.4	231.5	237.6	245.1	255.0	267.4	282.0	302.0	324.3	345.4	364.6
45°	209.3	214.7	220.4	227.4	236.6	248.6	263.2	281.4	300.8	320.3	334.8
47.5°	193.0	198.0	203.5	210.6	219.1	230.7	243.7	259.9	278.7	295.2	305.6
50°	181.4	186.0	192.0	198.9	207.3	218.1	230.6	246.5	262.3	277.3	286.8
52.5°	169.9	175.1	181.1	187.1	195.1	205.9	217.5	231.2	246.2	258.4	266.2
55°	152.7	157.6	163.1	169.4	177.2	186.5	198.7	209.6	221.4	231.8	236.4
57.5°	136.1	140.4	145.6	152.1	159.2	167.8	177.5	187.9	196.2	203.6	208.8
60°	125.2	128.9	133.8	139.3	147.0	154.8	163.6	173.3	179.8	186.0	190.9
62.5°	114.1	117.7	122.3	127.3	134.0	141.3	149.7	157.6	163.9	168.1	173.7
65°	97.5	101.0	104.9	110.2	115.5	121.5	129.2	134.9	139.3	144.0	147.4
67.5°	82.0	84.9	88.6	92.8	97.3	103.1	109.0	113.8	116.8	119.6	123.7
70°	71.9	74.2	77.2	80.4	85.3	91.0	95.7	99.4	101.4	104.2	109.3
72.5°	61.5	64.2	67.0	70.2	74.2	79.0	83.1	86.8	88.1	90.3	93.6
75°	48.5	49.9	52.2	54.5	57.3	61.5	65.4	66.3	67.5	69.3	71.6
77.5°	36.7	37.9	38.9	40.4	42.6	45.9	48.0	49.4	49.7	50.4	52.6
80°	29.1	29.8	30.7	31.9	32.8	35.6	36.7	38.1	38.6	39.3	40.4
82.5°	21.4	22.0	22.6	23.6	25.0	26.2	27.3	28.7	28.8	29.3	29.5
85°	12.5	12.7	12.2	12.7	12.9	13.4	14.6	15.7	15.5	15.3	15.9
87.5°	7.9	7.6	7.1	7.4	6.7	6.6	6.2	6.1	6.1	6.1	6.1
90°	17.1	16.0	14.4	12.9	11.3	9.8	8.1	6.3	4.5	2.8	1.0
92.5°	17.1	16.0	14.6	13.2	11.8	10.5	10.4	11.6	12.9	14.1	15.4
95°	17.1	16.0	24.4	32.8	41.3	49.7	54.3	54.9	55.6	56.2	56.9
97.5°	42.9	49.1	65.8	82.5	99.2	115.9	123.6	122.4	121.2	120.0	118.8
100°	140.7	173.7	172.8	172.0	171.1	170.2	169.4	168.7	168.1	167.4	166.7
102.5°	215.4	221.7	221.1	220.6	220.1	219.5	218.8	218.0	217.2	216.3	215.5
105°	297.5	297.5	297.5	297.5	297.5	297.5	297.1	296.2	295.3	294.4	293.5
107.5°	376.7	376.6	376.2	375.7	375.3	374.8	374.6	374.6	374.6	374.6	374.6
110°	428.7	429.3	428.9	428.5	428.0	427.6	427.3	427.3	427.3	427.3	427.3



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	479.6	480.5	480.2	479.9	479.7	479.4	479.0	478.5	477.9	477.4	476.9
115°	556.3	557.1	556.9	556.7	556.5	556.3	555.6	554.5	553.4	552.3	551.2
117.5°	630.5	631.6	630.8	629.9	629.1	628.3	627.9	627.9	627.9	628.0	628.0
120°	677.5	678.0	677.3	676.6	676.0	675.3	675.1	675.3	675.5	675.7	676.0
122.5°	723.0	723.5	723.2	722.9	722.6	722.2	721.7	720.8	720.0	719.1	718.3
125°	789.9	790.8	790.8	790.8	790.8	790.8	790.0	788.5	786.9	785.3	783.8
127.5°	850.2	850.7	850.8	851.0	851.1	851.2	850.7	849.6	848.5	847.4	846.3
130°	890.0	890.6	890.4	890.2	890.0	889.7	889.1	888.0	886.9	885.8	884.6
132.5°	926.4	926.6	927.1	927.6	928.0	928.5	928.1	926.8	925.6	924.3	923.0
135°	981.0	981.5	981.9	982.4	982.8	983.3	982.8	981.5	980.2	978.8	977.5
137.5°	1031.1	1031.0	1031.4	1031.8	1032.2	1032.6	1032.2	1031.1	1029.9	1028.8	1027.6
140°	1061.8	1061.4	1061.6	1061.8	1062.0	1062.3	1062.1	1061.7	1061.3	1060.8	1060.4
142.5°	1092.6	1092.5	1092.2	1091.9	1091.6	1091.3	1091.0	1090.7	1090.5	1090.2	1089.9
145°	1135.5	1135.3	1135.3	1135.3	1135.3	1135.3	1135.0	1134.6	1134.1	1133.7	1133.3
147.5°	1172.3	1172.0	1171.7	1171.5	1171.2	1170.9	1170.8	1170.9	1171.0	1171.1	1171.2
150°	1195.6	1195.2	1194.7	1194.3	1193.8	1193.4	1193.4	1193.8	1194.3	1194.7	1195.2
152.5°	1216.4	1215.9	1215.5	1215.0	1214.6	1214.2	1214.4	1215.4	1216.4	1217.4	1218.3
155°	1244.8	1244.1	1243.6	1243.2	1242.8	1242.3	1242.8	1244.1	1245.4	1246.8	1248.1
157.5°	1268.4	1267.7	1267.6	1267.6	1267.5	1267.5	1267.9	1268.7	1269.5	1270.2	1271.0
160°	1282.9	1282.0	1281.8	1281.6	1281.4	1281.1	1281.7	1283.0	1284.4	1285.7	1287.0
162.5°	1296.1	1294.8	1294.6	1294.4	1294.1	1293.9	1294.5	1295.8	1297.1	1298.5	1299.8
165°	1313.3	1312.0	1311.8	1311.5	1311.3	1311.1	1311.7	1313.0	1314.3	1315.6	1317.0
167.5°	1326.2	1324.6	1324.3	1324.1	1323.9	1323.7	1324.3	1325.6	1327.0	1328.4	1329.8
170°	1332.7	1331.0	1330.7	1330.5	1330.3	1330.1	1330.7	1332.3	1333.8	1335.4	1336.9
172.5°	1338.1	1336.5	1336.1	1335.7	1335.3	1335.0	1335.5	1337.1	1338.6	1340.2	1341.7
175°	1343.7	1341.9	1341.7	1341.5	1341.3	1341.1	1341.6	1342.9	1344.3	1345.6	1346.9
177.5°	1346.6	1345.3	1345.2	1345.0	1344.8	1344.6	1345.1	1346.1	1347.2	1348.3	1349.3
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	565.6	567.3	569.7	572.5	574.7	577.1	578.4	578.4	579.5	581.9	585.1
5°	567.3	573.3	579.0	586.4	592.2	598.9	604.0	608.9	613.2	618.8	624.6
7.5°	566.8	576.8	587.2	598.8	611.7	621.9	632.4	640.6	648.7	659.4	667.7
10°	565.0	577.9	592.0	606.8	623.0	637.0	649.8	661.3	672.4	684.0	694.4
12.5°	561.6	578.1	595.3	613.1	633.5	649.6	666.0	678.3	691.3	703.9	716.7
15°	556.6	576.0	596.8	621.6	646.5	664.5	680.7	696.7	708.7	723.0	735.3
17.5°	546.3	571.3	597.5	624.5	648.5	669.4	686.4	701.6	714.4	730.1	746.8
20°	540.2	567.3	594.5	623.4	646.3	667.8	684.2	699.9	715.8	736.4	756.7
22.5°	531.7	560.6	589.5	616.9	641.1	661.9	678.8	698.0	719.0	742.3	766.9
25°	518.3	548.1	576.7	602.8	626.4	647.7	670.8	696.7	722.1	752.8	788.2
27.5°	501.2	530.0	555.5	583.1	606.5	633.6	662.4	690.5	727.1	769.4	813.5
30°	488.5	515.7	540.0	566.1	592.7	622.5	654.8	687.9	731.6	781.2	833.7
32.5°	473.7	498.4	522.4	547.6	578.3	611.0	645.4	685.8	738.0	794.5	848.8
35°	448.0	470.2	493.6	521.5	554.1	589.7	633.6	682.8	745.9	806.6	855.4
37.5°	421.1	438.7	462.1	491.6	527.1	568.2	618.1	677.9	742.6	797.2	817.9
40°	400.4	416.8	441.6	472.5	507.7	552.7	608.6	670.1	735.3	773.1	771.5
42.5°	379.9	396.5	420.3	451.5	488.1	538.5	596.1	659.9	714.9	729.3	699.3
45°	348.4	363.9	387.3	418.7	458.0	510.9	571.4	632.7	667.8	644.4	584.8
47.5°	316.4	331.4	353.1	383.8	426.7	482.1	539.4	589.6	594.5	544.4	472.9
50°	295.3	309.4	330.0	362.8	404.4	458.4	513.7	553.2	540.9	479.7	406.0
52.5°	274.8	288.3	307.6	338.6	381.1	434.0	483.3	514.4	486.0	420.9	354.6
55°	244.5	257.4	276.8	305.2	343.8	392.3	435.6	446.9	405.3	339.7	286.1
57.5°	215.7	225.2	244.3	269.5	306.7	349.5	380.4	378.4	332.5	273.4	234.9
60°	196.6	205.2	223.4	246.5	281.9	320.3	342.0	332.7	286.3	237.5	200.6
62.5°	178.9	186.9	202.2	223.4	253.8	287.2	303.0	290.2	246.4	203.5	174.1
65°	152.0	157.8	170.1	189.7	213.5	236.6	250.7	232.0	193.2	160.8	138.6
67.5°	126.9	131.9	142.8	156.9	173.3	189.3	195.0	177.5	147.3	125.5	109.8
70°	110.7	115.3	122.7	135.9	146.7	158.0	160.8	145.1	119.9	103.3	93.6
72.5°	95.2	99.4	105.9	115.2	122.7	129.2	130.5	115.9	96.6	85.2	77.7
75°	72.6	76.3	80.4	83.9	88.7	89.9	89.4	78.1	67.7	60.1	55.9
77.5°	53.3	54.9	57.4	58.8	59.0	58.9	56.6	49.4	44.0	40.9	39.2
80°	41.1	42.3	43.0	43.4	43.7	41.4	38.8	34.4	32.6	30.7	28.7
82.5°	29.9	30.6	31.3	31.4	30.2	28.2	25.9	23.7	22.4	21.5	20.7
85°	16.2	16.4	16.2	15.0	13.4	12.7	12.2	11.8	11.6	11.3	11.3
87.5°	6.3	6.1	5.5	6.1	6.4	6.5	6.8	7.0	7.1	7.3	7.5
90°	2.8	4.5	6.3	8.1	9.8	11.3	12.9	14.4	16.0	17.1	18.2
92.5°	14.1	12.9	11.6	10.4	10.5	11.8	13.2	14.6	16.0	17.1	18.2
95°	56.2	55.6	54.9	54.3	49.7	41.3	32.8	24.4	16.0	17.1	18.2
97.5°	120.0	121.2	122.4	123.6	115.9	99.2	82.5	65.8	49.1	42.9	36.6
100°	167.4	168.1	168.7	169.4	170.2	171.1	172.0	172.8	173.7	140.7	107.6
102.5°	216.3	217.2	218.0	218.8	219.5	220.1	220.6	221.1	221.7	215.4	209.1
105°	294.4	295.3	296.2	297.1	297.5	297.5	297.5	297.5	297.5	297.5	297.5
107.5°	374.6	374.6	374.6	374.6	374.8	375.3	375.7	376.2	376.6	376.7	376.7
110°	427.3	427.3	427.3	427.3	427.6	428.0	428.5	428.9	429.3	428.7	428.0



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	477.4	477.9	478.5	479.0	479.4	479.7	479.9	480.2	480.5	479.6	478.8
115°	552.3	553.4	554.5	555.6	556.3	556.5	556.7	556.9	557.1	556.3	555.4
117.5°	628.0	627.9	627.9	627.9	628.3	629.1	629.9	630.8	631.6	630.5	629.3
120°	675.7	675.5	675.3	675.1	675.3	676.0	676.6	677.3	678.0	677.5	677.1
122.5°	719.1	720.0	720.8	721.7	722.2	722.6	722.9	723.2	723.5	723.0	722.6
125°	785.3	786.9	788.5	790.0	790.8	790.8	790.8	790.8	790.8	789.9	789.0
127.5°	847.4	848.5	849.6	850.7	851.2	851.1	851.0	850.8	850.7	850.2	849.7
130°	885.8	886.9	888.0	889.1	889.7	890.0	890.2	890.4	890.6	890.0	889.3
132.5°	924.3	925.6	926.8	928.1	928.5	928.0	927.6	927.1	926.6	926.4	926.3
135°	978.8	980.2	981.5	982.8	983.3	982.8	982.4	981.9	981.5	981.0	980.6
137.5°	1028.8	1029.9	1031.1	1032.2	1032.6	1032.2	1031.8	1031.4	1031.0	1031.1	1031.2
140°	1060.8	1061.3	1061.7	1062.1	1062.3	1062.0	1061.8	1061.6	1061.4	1061.8	1062.3
142.5°	1090.2	1090.5	1090.7	1091.0	1091.3	1091.6	1091.9	1092.2	1092.5	1092.6	1092.7
145°	1133.7	1134.1	1134.6	1135.0	1135.3	1135.3	1135.3	1135.3	1135.3	1135.5	1135.7
147.5°	1171.1	1171.0	1170.9	1170.8	1170.9	1171.2	1171.5	1171.7	1172.0	1172.3	1172.5
150°	1194.7	1194.3	1193.8	1193.4	1193.4	1193.8	1194.3	1194.7	1195.2	1195.6	1196.1
152.5°	1217.4	1216.4	1215.4	1214.4	1214.2	1214.6	1215.0	1215.5	1215.9	1216.4	1216.8
155°	1246.8	1245.4	1244.1	1242.8	1242.3	1242.8	1243.2	1243.6	1244.1	1244.8	1245.4
157.5°	1270.2	1269.5	1268.7	1267.9	1267.5	1267.5	1267.6	1267.6	1267.7	1268.4	1269.1
160°	1285.7	1284.4	1283.0	1281.7	1281.1	1281.4	1281.6	1281.8	1282.0	1282.9	1283.8
162.5°	1298.5	1297.1	1295.8	1294.5	1293.9	1294.1	1294.4	1294.6	1294.8	1296.1	1297.3
165°	1315.6	1314.3	1313.0	1311.7	1311.1	1311.3	1311.5	1311.8	1312.0	1313.3	1314.6
167.5°	1328.4	1327.0	1325.6	1324.3	1323.7	1323.9	1324.1	1324.3	1324.6	1326.2	1327.8
170°	1335.4	1333.8	1332.3	1330.7	1330.1	1330.3	1330.5	1330.7	1331.0	1332.7	1334.5
172.5°	1340.2	1338.6	1337.1	1335.5	1335.0	1335.3	1335.7	1336.1	1336.5	1338.1	1339.7
175°	1345.6	1344.3	1342.9	1341.6	1341.1	1341.3	1341.5	1341.7	1341.9	1343.7	1345.5
177.5°	1348.3	1347.2	1346.1	1345.1	1344.6	1344.8	1345.0	1345.2	1345.3	1346.6	1347.8
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	587.5	587.5	590.6	590.4	592.5	591.7	592.1
5°	631.5	635.4	638.9	641.2	644.7	645.6	645.1
7.5°	677.2	685.9	690.1	696.0	697.0	700.1	699.8
10°	705.4	714.0	720.5	725.5	728.1	731.3	731.6
12.5°	727.6	734.9	740.6	745.3	748.4	749.4	750.0
15°	745.0	753.0	759.7	766.4	770.4	773.4	775.0
17.5°	762.4	774.9	786.7	795.8	801.3	805.9	805.9
20°	775.9	790.2	805.0	815.4	826.1	830.7	831.4
22.5°	790.3	812.2	831.3	847.4	861.4	866.2	868.0
25°	820.3	848.9	878.3	900.9	917.1	926.6	928.0
27.5°	856.5	895.2	926.1	947.0	960.4	967.5	969.0
30°	882.0	917.8	945.5	961.2	967.5	968.4	964.9
32.5°	893.4	920.2	931.3	930.4	918.1	910.0	906.9
35°	879.4	873.9	846.9	814.5	789.8	774.1	769.9
37.5°	800.3	752.5	702.8	653.9	627.9	614.6	591.9
40°	722.3	654.1	602.4	561.3	531.9	508.3	502.8
42.5°	634.3	563.9	512.2	477.0	453.5	437.4	430.3
45°	509.7	449.2	406.4	379.4	361.4	349.6	344.3
47.5°	407.7	360.8	329.7	309.7	295.9	285.7	282.8
50°	351.7	314.2	287.9	271.0	260.6	252.8	249.6
52.5°	305.5	275.2	255.0	241.1	231.3	226.4	223.7
55°	252.1	226.0	211.4	200.3	194.8	190.9	189.0
57.5°	206.2	187.3	176.7	169.0	163.9	161.4	160.5
60°	180.5	165.7	156.0	150.0	146.5	143.3	142.3
62.5°	157.7	146.1	138.6	133.3	129.9	128.5	127.9
65°	127.1	119.5	113.9	110.7	107.9	107.4	107.2
67.5°	101.0	96.5	93.6	90.3	89.3	87.7	87.3
70°	86.4	83.4	79.9	78.8	77.6	76.0	76.3
72.5°	73.3	70.3	67.9	66.4	66.0	65.3	65.9
75°	53.6	52.7	51.8	50.6	50.1	50.1	49.9
77.5°	38.3	37.5	36.5	35.8	35.6	34.7	35.0
80°	27.7	26.6	26.1	26.3	25.6	25.4	25.4
82.5°	20.5	20.1	19.6	19.7	19.5	19.3	19.5
85°	11.3	11.1	11.1	10.9	10.9	10.6	10.6
87.5°	7.9	8.3	8.1	8.1	8.2	8.5	8.9
90°	19.3	20.4	21.3	22.0	22.6	23.3	24.0
92.5°	19.3	20.4	21.1	21.4	21.7	22.1	22.4
95°	19.3	20.4	21.0	21.0	21.0	21.0	21.0
97.5°	30.4	24.1	21.0	21.0	21.0	21.0	21.0
100°	74.6	41.5	24.5	23.6	22.7	21.9	21.0
102.5°	202.9	196.6	186.0	170.9	155.8	140.7	125.6
105°	297.5	297.5	297.4	297.2	297.0	296.8	296.5
107.5°	376.8	376.8	376.5	375.8	375.2	374.5	373.8
110°	427.3	426.7	426.5	426.7	426.9	427.1	427.3



TEST NUMBER: P333508

CATALOG NUMBER: S125RDIP-S375D1035U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	477.9	477.1	476.5	476.2	475.9	475.6	475.3
115°	554.5	553.6	552.5	551.2	549.8	548.5	547.2
117.5°	628.2	627.0	626.1	625.6	625.0	624.4	623.8
120°	676.6	676.2	675.4	674.3	673.2	672.1	671.0
122.5°	722.2	721.7	720.8	719.6	718.3	717.0	715.7
125°	788.1	787.2	786.5	785.8	785.1	784.5	783.8
127.5°	849.2	848.7	847.7	846.0	844.4	842.8	841.1
130°	888.6	888.0	887.1	886.0	884.9	883.8	882.6
132.5°	926.2	926.0	925.4	924.3	923.2	922.1	921.0
135°	980.2	979.7	978.8	977.5	976.2	974.8	973.5
137.5°	1031.3	1031.4	1030.8	1029.7	1028.5	1027.4	1026.2
140°	1062.7	1063.1	1062.7	1061.4	1060.0	1058.7	1057.4
142.5°	1092.8	1092.9	1092.3	1090.9	1089.6	1088.3	1086.9
145°	1135.9	1136.1	1135.6	1134.3	1132.9	1131.6	1130.3
147.5°	1172.8	1173.1	1172.4	1170.8	1169.2	1167.6	1166.0
150°	1196.5	1196.9	1196.3	1194.5	1192.7	1190.9	1189.2
152.5°	1217.3	1217.7	1217.1	1215.5	1213.9	1212.3	1210.7
155°	1246.1	1246.8	1246.2	1244.4	1242.6	1240.9	1239.1
157.5°	1269.8	1270.5	1270.0	1268.2	1266.4	1264.6	1262.9
160°	1284.7	1285.6	1285.1	1283.4	1281.6	1279.8	1278.0
162.5°	1298.5	1299.8	1299.4	1297.5	1295.5	1293.6	1291.6
165°	1316.0	1317.3	1317.1	1315.3	1313.5	1311.8	1310.0
167.5°	1329.4	1331.0	1330.8	1328.8	1326.8	1324.8	1322.8
170°	1336.3	1338.1	1337.9	1335.9	1334.0	1332.0	1330.0
172.5°	1341.3	1342.9	1342.7	1340.7	1338.7	1336.7	1334.8
175°	1347.3	1349.0	1348.9	1346.9	1344.9	1342.9	1340.9
177.5°	1349.1	1350.3	1350.2	1348.8	1347.4	1346.0	1344.5
180°	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9	1346.9

(END OF REPORT)