

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333507

Luminaire Tested: **S125RDIP-S375D810U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333507
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D810U835-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4356.1 lumens
Efficiency: N/A
Efficacy: 139.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333507

CATALOG NUMBER: S125RDIP-S375D810U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333507

CATALOG NUMBER: S125RDIP-S375D810U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29	24
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	28	27	25	20
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	25	23	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3952	3952	3952
5°	3961	3916	3940
10°	3931	3880	3880
15°	3884	3801	3770
20°	3824	3691	3647
25°	3755	3583	3504
30°	3667	3457	3347
35°	3578	3327	3170
40°	3495	3191	2996
45°	3394	3040	2807
50°	3293	2875	2609
55°	3174	2716	2399
60°	3056	2525	2173
65°	2917	2303	1913
70°	2757	2024	1648
75°	2538	1707	1372
80°	2235	1339	1153
85°	1882	1097	1030



TEST NUMBER: P333507

CATALOG NUMBER: S125RDIP-S375D810U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	1.3
10°-20°	160.8	3.7
20°-30°	233.2	5.4
30°-40°	265.7	6.1
40°-50°	259.0	5.9
50°-60°	218.0	5.0
60°-70°	152.8	3.5
70°-80°	78.6	1.8
80°-90°	22.0	0.5
90°-100°	281.1	6.5
100°-110°	604.3	13.9
110°-120°	567.1	13.0
120°-130°	459.6	10.6
130°-140°	368.8	8.5
140°-150°	278.3	6.4
150°-160°	195.9	4.5
160°-170°	115.5	2.7
170°-180°	37.6	0.9
0°-30°	451.5	10.4
0°-40°	717.3	16.5
0°-60°	1194.3	27.4
0°-90°	1447.7	33.2
90°-120°	1452.5	33.3
90°-150°	2559.3	58.8
90°-180°	2908.0	66.8
0°-180°	4356.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	612	612	612	612	612	
5°	611	609	604	608	608	58
15°	581	578	568	568	564	164
25°	527	519	503	497	492	242
35°	454	442	422	409	402	284
45°	372	358	333	315	307	287
55°	282	267	241	221	213	252
65°	191	175	151	133	125	189
75°	102	88	68	59	55	108
85°	25	17	15	14	14	29
90°	1	7	12	16	18	3
95°	26	76	693	314	184	27
105°	88	124	567	1116	1036	93
115°	158	190	455	981	1154	155
125°	219	256	436	780	909	194
135°	256	308	433	654	755	199
145°	299	342	435	541	596	187
155°	341	367	424	479	500	157
165°	372	382	407	431	438	105
175°	387	387	390	395	393	37
180°	388	388	388	388	388	



TEST NUMBER: P333507

CATALOG NUMBER: S125RDIP-S375D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9
2.5°	613.0	612.8	612.5	612.3	612.0	611.5	610.7	609.8	609.0	608.2	609.0
5°	611.0	610.6	610.2	609.7	609.3	608.6	607.4	606.3	605.2	604.0	605.1
7.5°	605.0	604.6	604.2	603.8	603.4	602.5	601.2	599.8	598.5	597.1	597.8
10°	599.4	599.1	598.8	598.5	598.2	597.3	595.9	594.4	593.0	591.6	591.9
12.5°	593.1	592.7	592.4	592.0	591.6	590.4	588.5	586.6	584.6	582.7	582.9
15°	580.9	580.3	579.7	579.1	578.5	577.1	574.9	572.8	570.6	568.5	568.4
17.5°	567.2	566.2	565.3	564.3	563.4	561.6	558.8	556.1	553.4	550.7	550.2
20°	556.4	555.4	554.4	553.4	552.3	550.2	546.9	543.6	540.3	537.0	536.5
22.5°	544.6	543.6	542.6	541.5	540.5	538.3	534.8	531.4	527.9	524.5	523.5
25°	526.9	525.3	523.8	522.2	520.7	518.0	514.2	510.4	506.6	502.8	501.5
27.5°	506.5	504.7	502.8	500.9	499.0	496.1	492.0	487.9	483.9	479.8	477.9
30°	491.7	489.8	487.8	485.9	483.9	480.8	476.5	472.2	467.9	463.5	461.2
32.5°	477.3	475.0	472.8	470.5	468.2	464.9	460.5	456.1	451.7	447.3	444.7
35°	453.8	451.4	448.9	446.4	444.0	440.4	435.8	431.2	426.6	422.0	419.0
37.5°	430.8	427.8	424.8	421.8	418.8	414.9	410.2	405.4	400.7	395.9	392.3
40°	414.6	411.5	408.4	405.3	402.2	398.2	393.3	388.4	383.4	378.5	374.6
42.5°	397.5	394.4	391.2	388.1	384.9	380.8	375.7	370.6	365.5	360.4	356.7
45°	371.6	368.6	365.6	362.6	359.7	355.3	349.7	344.1	338.4	332.8	328.6
47.5°	344.7	341.5	338.4	335.2	332.1	327.7	322.0	316.3	310.6	304.9	300.7
50°	327.7	324.3	320.9	317.5	314.1	309.5	303.6	297.8	291.9	286.1	281.8
52.5°	309.2	305.7	302.2	298.8	295.3	290.8	285.3	279.7	274.2	268.7	264.1
55°	281.9	278.6	275.3	272.1	268.8	264.3	258.5	252.7	247.0	241.2	236.6
57.5°	254.4	250.9	247.3	243.8	240.3	235.8	230.2	224.7	219.2	213.6	209.1
60°	236.6	233.0	229.4	225.8	222.2	217.7	212.1	206.6	201.0	195.5	191.0
62.5°	217.8	214.3	210.9	207.5	204.0	199.5	193.9	188.3	182.6	177.0	172.8
65°	190.9	187.4	183.9	180.4	176.9	172.4	167.0	161.6	156.1	150.7	146.6
67.5°	164.2	160.7	157.2	153.7	150.2	145.8	140.6	135.4	130.2	125.0	121.2
70°	146.0	142.6	139.1	135.6	132.1	127.8	122.6	117.5	112.4	107.2	104.0
72.5°	128.3	124.9	121.5	118.1	114.7	110.5	105.7	100.9	96.1	91.3	88.4
75°	101.7	98.6	95.5	92.4	89.4	85.7	81.3	77.0	72.7	68.4	66.1
77.5°	75.2	72.8	70.3	67.8	65.4	62.4	59.0	55.5	52.1	48.6	47.0
80°	60.1	57.6	55.2	52.7	50.2	47.6	44.7	41.8	38.9	36.0	35.1
82.5°	45.3	43.1	40.9	38.6	36.4	34.3	32.4	30.4	28.4	26.4	26.0
85°	25.4	23.6	21.7	19.9	18.0	16.8	16.3	15.8	15.3	14.8	14.7
87.5°	8.7	8.2	8.0	7.7	7.5	7.4	7.5	7.7	7.8	8.0	8.2
90°	0.8	1.6	3.1	4.7	6.3	7.8	8.6	10.2	10.9	12.5	13.3
92.5°	9.5	11.6	18.1	27.8	41.3	64.1	106.8	178.4	256.1	252.1	204.1
95°	25.8	26.6	32.8	41.4	58.6	93.8	177.5	349.5	565.3	692.8	677.9
97.5°	42.8	43.8	48.2	56.8	72.2	97.6	152.9	279.0	504.8	739.8	857.7
100°	54.7	56.3	59.4	68.0	82.9	106.3	151.7	253.3	450.4	706.1	901.5
102.5°	67.9	68.8	71.3	80.5	94.1	117.0	157.3	242.7	409.1	646.6	875.3
105°	88.4	88.4	92.3	100.1	112.6	134.5	168.9	238.5	369.1	566.9	791.3
107.5°	108.4	109.9	113.7	120.1	133.1	152.8	186.1	245.7	352.2	512.0	705.6
110°	122.8	124.3	127.4	134.5	146.2	166.5	198.6	252.6	347.2	486.3	656.8



TEST NUMBER: P333507

CATALOG NUMBER: S125RDIP-S375D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	137.1	138.7	141.2	148.2	160.0	179.7	210.5	261.3	347.2	471.3	620.5
115°	157.9	159.5	161.9	168.9	180.6	200.2	229.1	274.4	349.5	455.1	580.9
117.5°	176.7	179.1	181.6	188.6	201.9	220.8	248.2	289.5	354.7	447.1	557.3
120°	189.2	191.6	194.7	201.7	215.0	234.6	261.9	299.5	359.7	443.3	544.2
122.5°	202.4	204.1	206.6	213.6	228.2	247.7	275.1	310.7	364.0	440.2	532.9
125°	218.9	220.5	224.4	231.4	246.3	266.6	292.4	326.0	371.4	436.3	517.6
127.5°	231.9	234.3	239.3	248.2	264.0	284.3	309.2	340.1	379.7	434.4	503.5
130°	240.0	242.4	248.6	258.8	275.2	295.6	319.8	349.5	384.7	433.2	494.2
132.5°	246.3	249.3	256.8	268.2	285.2	305.6	329.8	357.6	390.3	433.2	486.7
135°	256.5	259.6	269.0	281.5	297.9	319.0	343.3	369.1	398.0	433.2	477.7
137.5°	269.3	271.6	280.4	292.9	309.0	330.7	352.8	377.5	405.0	434.1	469.8
140°	276.8	279.1	288.5	301.0	315.9	337.0	359.7	383.1	408.1	434.7	466.0
142.5°	285.5	287.3	296.0	308.5	322.8	342.6	364.0	386.3	410.0	435.4	462.9
145°	298.7	300.2	308.1	319.0	333.1	351.1	371.4	390.9	412.1	434.7	458.2
147.5°	312.4	313.4	320.1	330.3	342.5	358.3	376.1	393.8	412.8	432.7	453.3
150°	320.6	322.1	327.6	337.8	348.7	362.0	379.2	395.6	412.8	430.8	449.6
152.5°	329.3	330.3	335.1	344.0	354.4	366.4	382.3	396.9	412.2	428.3	445.2
155°	340.9	340.9	345.6	353.4	361.2	372.2	385.5	398.0	410.5	423.8	437.9
157.5°	351.2	351.1	354.8	361.5	368.4	376.7	388.1	398.8	408.5	419.1	431.0
160°	358.1	357.3	360.5	365.9	372.2	379.2	389.4	398.8	406.6	416.0	425.4
162.5°	363.7	363.0	366.1	370.9	375.9	381.7	390.6	398.1	404.7	412.2	420.3
165°	372.2	370.6	373.0	376.9	380.0	384.7	390.9	397.2	401.9	406.6	412.8
167.5°	377.8	377.0	378.4	380.6	382.8	385.8	390.9	395.3	397.5	401.1	405.5
170°	381.6	380.8	381.6	383.1	384.7	387.0	390.9	394.1	395.6	398.0	401.1
172.5°	384.1	382.7	383.4	385.0	385.9	387.0	390.3	392.8	393.1	394.2	396.7
175°	387.0	385.5	386.3	387.0	387.0	387.0	389.4	390.9	390.2	390.2	390.9
177.5°	388.4	387.2	387.2	387.8	387.2	387.2	388.4	389.1	387.8	387.8	388.4
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8



TEST NUMBER: P333507

CATALOG NUMBER: S125RDIP-S375D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9
2.5°	609.8	610.7	611.5	611.9	611.8	611.7	611.6	611.5
5°	606.1	607.1	608.1	608.6	608.4	608.1	607.9	607.7
7.5°	598.5	599.3	600.0	600.2	600.0	599.8	599.6	599.3
10°	592.2	592.5	592.8	592.8	592.5	592.2	591.9	591.6
12.5°	583.1	583.4	583.6	583.5	583.0	582.5	582.1	581.6
15°	568.2	568.1	568.0	567.5	566.6	565.7	564.8	563.8
17.5°	549.7	549.2	548.7	548.0	547.3	546.5	545.7	545.0
20°	536.0	535.5	535.0	534.3	533.3	532.4	531.5	530.6
22.5°	522.4	521.4	520.4	519.5	518.8	518.0	517.3	516.5
25°	500.2	498.8	497.5	496.3	495.1	494.0	492.9	491.7
27.5°	476.1	474.2	472.3	470.9	469.8	468.7	467.6	466.5
30°	458.8	456.5	454.1	452.5	451.5	450.6	449.7	448.8
32.5°	442.1	439.5	436.8	435.0	433.8	432.6	431.4	430.3
35°	416.0	413.0	410.0	407.8	406.4	405.0	403.5	402.1
37.5°	388.7	385.2	381.6	379.1	377.7	376.3	374.9	373.5
40°	370.7	366.8	362.9	360.3	359.1	357.9	356.6	355.4
42.5°	352.9	349.2	345.4	342.7	340.9	339.0	337.2	335.4
45°	324.5	320.4	316.3	313.5	312.0	310.4	308.9	307.3
47.5°	296.5	292.2	288.0	285.0	283.3	281.6	279.9	278.2
50°	277.4	273.1	268.8	265.9	264.4	262.8	261.3	259.7
52.5°	259.4	254.8	250.1	247.0	245.5	244.0	242.4	240.9
55°	232.0	227.4	222.8	219.6	218.0	216.3	214.7	213.1
57.5°	204.6	200.1	195.5	192.5	191.1	189.6	188.2	186.7
60°	186.5	181.9	177.4	174.4	172.8	171.3	169.8	168.2
62.5°	168.6	164.4	160.2	157.4	155.8	154.3	152.8	151.2
65°	142.4	138.3	134.2	131.4	129.9	128.3	126.8	125.2
67.5°	117.4	113.7	109.9	107.4	106.2	105.0	103.7	102.5
70°	100.9	97.7	94.5	92.3	91.0	89.8	88.6	87.3
72.5°	85.4	82.5	79.6	77.7	76.9	76.1	75.2	74.4
75°	63.9	61.6	59.4	57.9	57.2	56.4	55.7	55.0
77.5°	45.5	43.9	42.3	41.2	40.7	40.2	39.6	39.1
80°	34.2	33.3	32.4	31.8	31.6	31.4	31.2	31.0
82.5°	25.6	25.1	24.7	24.4	24.3	24.2	24.1	23.9
85°	14.6	14.5	14.4	14.3	14.2	14.1	14.0	13.9
87.5°	8.4	8.5	8.7	8.9	8.9	8.8	8.9	8.8
90°	14.1	14.9	15.6	17.2	17.2	17.2	18.0	18.0
92.5°	138.6	100.6	75.7	64.1	54.1	52.2	51.1	49.9
95°	562.2	443.3	347.2	281.5	226.0	202.5	196.3	183.7
97.5°	837.3	753.9	660.2	568.9	520.6	476.8	454.1	444.1
100°	961.7	923.4	842.9	761.6	707.6	651.3	622.4	609.9
102.5°	1003.6	1027.3	988.6	933.6	875.9	835.8	804.4	795.0
105°	978.9	1086.1	1120.5	1111.9	1086.8	1061.0	1045.4	1036.0
107.5°	890.7	1033.7	1122.0	1162.8	1175.5	1175.3	1170.2	1163.9
110°	825.7	974.2	1084.5	1150.9	1186.1	1201.0	1206.5	1206.5



TEST NUMBER: P333507

CATALOG NUMBER: S125RDIP-S375D810U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	774.4	915.4	1026.9	1105.3	1156.7	1182.2	1195.8	1201.5
115°	710.0	831.2	938.3	1023.5	1084.5	1122.0	1143.9	1154.1
117.5°	668.4	772.8	865.1	943.3	1004.3	1043.0	1064.8	1071.0
120°	645.8	739.7	825.7	894.5	952.3	989.9	1011.0	1017.2
122.5°	629.0	715.9	792.5	857.0	908.6	943.0	964.1	969.7
125°	604.4	684.2	752.2	808.5	852.3	884.3	901.5	909.3
127.5°	579.4	653.8	717.3	770.0	809.7	838.0	854.3	857.7
130°	563.7	632.6	693.5	744.4	783.5	809.3	824.9	829.6
132.5°	548.1	612.5	667.9	716.8	755.9	781.7	796.1	801.4
135°	527.8	581.7	631.8	676.3	710.7	736.5	750.6	755.3
137.5°	510.6	554.2	595.8	633.6	664.5	687.9	700.9	706.1
140°	501.2	537.9	573.9	606.7	635.7	656.0	667.7	671.6
142.5°	493.1	524.2	555.1	583.6	608.2	625.4	636.5	639.7
145°	482.4	506.7	530.9	552.0	570.8	584.1	592.7	595.8
147.5°	472.4	492.1	510.7	526.7	541.5	552.2	557.2	558.6
150°	466.8	484.0	498.8	512.9	524.7	534.0	537.2	537.9
152.5°	460.5	475.9	489.5	500.4	510.3	517.8	520.9	521.7
155°	451.2	463.7	474.6	483.2	491.0	496.5	498.8	499.6
157.5°	441.8	452.1	460.5	467.3	473.4	477.9	480.1	479.9
160°	435.5	443.3	451.2	456.6	462.1	466.0	467.6	466.8
162.5°	428.6	435.8	442.4	447.2	451.5	454.7	455.1	454.9
165°	419.1	424.6	429.3	433.2	436.3	437.9	437.9	437.9
167.5°	410.0	413.6	417.2	420.0	421.6	423.0	422.4	422.2
170°	405.0	407.4	409.7	411.3	412.8	413.6	413.6	412.8
172.5°	399.4	401.7	403.5	404.4	404.7	406.1	404.9	404.1
175°	393.3	393.3	394.9	394.9	394.9	395.6	394.1	393.3
177.5°	389.1	389.7	389.7	389.7	389.1	389.7	387.8	387.8
180°	387.8	387.8	387.8	387.8	387.8	387.8	387.8	387.8

(END OF REPORT)